Planned Agenda

NRC Introduction & Meeting Purpose: M. Srinivasan 1. **Overview of PNNL Research Project:** 2. S. Bruemmer **Review of SCC Crack-Growth Test Systems:** 3. M. Toloczko **Test Plans and Initial Test Results:** 4. Bruemmer, Toloczko 5. **Discussion of Programmatic Challenges:** S. Bruemmer 6. **Opportunity for Public Questions/Comments** 7. Crack and Crack-Tip Observations on Alloy 600 and Alloy 182 **CRDM Components:** S. Bruemmer

> Pacific Northwest National Laboratory



Battelle

SCC Crack Growth System Design and Construction

Mychailo Toloczko, John Keaveney and Steve Bruemmer Pacific Northwest National Laboratory

> Project Kick-Off Meeting Richland, Washington

> > May 3, 2005

Research Supported by U.S. Nuclear Regulatory Commission

Presentation Outline

CGR System Design Requirements and Decision

Review and Assessment of CGR System

- Loadline & load control
- Pressure & temperature control
- Water chemistry control
- DCPD measurement
- System control & automation

Review and Assessment of Peripheral Systems

- Pre-cracking station
- Ultra-high purity make-up water system

Construction & Assembly Status

SCC Crack Growth System Essentials

- Long term static loading with load control
- Water temperatures to 360°C (3000 psi)
- Circulating ultra pure water (18 Mohm-cm) with chemistry control for simulated BWR/PWR conditions
- In-situ, high-res. crack length measurement
- Active control of key system variables
- Continuous data acquisition
 - load, crack length, temperature, water resistivity, oxygen content, ECP

Pacific Northwest National Laboratory

Options for System Design

Design our own

- Lengthy design cycle
- Unproven design
- Finding appropriate components

Purchase ready-made system

- Few vendors
- System limitations (expandability, repairability)
- Potentially high cost

Base the design on an existing system

- Fast design cycle
- Proven design

Battelle

• Cost efficient to achieve project objectives

Existing Crack-Growth System Design Decision

General Electric Global Research

- World leader for quantitative SCC crack-growth-rate testing of LWR materials and they have led key international round-robin test programs.
- 25 years of development and test system evolution, unmatched experience with ECP control and DCPD, unique control and data acquisition software.
- Pioneered ultra-high-purity, make-up water system (outlet resistivity better than 15 Mohm-cm) for BWR applications and for isolation of impurity effects
- Recent PWR experience (290-360°C, B/Li water) evaluating Ni-base alloys and stainless steels

Battelle

Peter Andresen and his team have advised in the construction of SCC crack-growth systems for many laboratories over the last 10 years.

Elements of G.E. SCC CGR System

CGR System

Battelle

- Loadline and loading
- Water system (flow, pressure, temperature, chemistry control)
- Temperature controller
- In-situ crack length measurement (DCPD)
- System control & data acquisition

Peripheral Systems

- Pre-cracking station
- Ultra-high purity make-up water system

Features of G.E. Systems

> Many parts are "off-the-shelf"

- Inexpensive
- Most items are rebuildable
- Full control over loading system, incl. const K
- State-of-the-art DC potential drop for crack length measurement
- Low pressure loop for chemistry control
- > High pressure loop

Battelle

- Careful attention to seal materials
- Mature software package for continuous system control and data acquisition

PNNL Approach to SCC System Design

- Subcontract with GE Global to enable rapid and cost effective construction of state-ofthe-art crack-growth test systems
- Assess individual elements of the elements of the GE system design and components
- Determine where improvements are possible
 - System layout
 - Major components
 - Wetted materials

Incorporate improvements into design and establish cost basis for complete system

Evaluation of Loadline

- Sturdy loadframe
- Selected servo-electric motor
 - Excellent long term static loading & positioning
- Four-bar cage to support upper pullrod & clevis
- One mechanical feed-through on autoclave base
 - feed-through sealed with a virgin teflon seal good to ~280°C
 - water pressure applies a load on pullrod
 - pressure load factored into total specimen load
- Sufficient room for two 0.5T specimens

Battelle

Components are manually aligned using a special alignment rod



Pacific Northwest National Laborato[®]y



Evaluation of Water System

General features

- 316L SS tubing and compression fittings
- Low-leaching seals (viton, virgin teflon)
- Low pressure loop for chemistry control
- High pressure loop

Battelle

• All water runs through a demineralizer and submicron filter



Battelle

Pacific Northwest National Laborato শৃর্য

Evaluation of Water System

> High pressure loop

- Piston pump creates high pressure
 - adjustable flow rate

• Back pressure regulator

pressure control

• Pulsation damper

less than 3 psi peak-to-peak

• Water conductivity measured at end of high pressure loop

measure of water purity

• Water flows from top to bottom of autoclave

minimizes stagnation



Pacific Northwest National Laborato®y

Evaluation of Water System

- Cost effective, efficient design
- Very little to improve upon
- Upgraded conductivity sensors and meters
 - temperature measurement, more analog outputs
- Careful evaluation of pulsation damper specs
- Careful evaluation of seal materials in flow meter, back pressure regulators, pulsation damper, etc.
- Reduced length of heated tubing to improve purity of water entering the autoclave

Evaluation of Temperature Control

> Heating

- Step 1: coaxial heat exchanger
- Step 2: preheater
- Step 3: autoclave heater

Cooling

- Step 1: coaxial heat exchanger with incoming water
- Step 2: coaxial water cooler with building coolant
- Control: Temperature controllers for preheater and autoclave heater
- Will evaluate magnitude of temperature gradients in autoclave



current

source

solid state

switch

inputs 🕑

DCPD V

ref V

Evaluation of Crack Length

Reversing DC notential drop Measurement

- compensates for work function between dissimilar metals
- setup to read stabilized voltage

Reference potential

- compensate for temperature effects on resistivity
- DCPD estimates crack length via existing calibration curve

All DCPD data written to data file



Evaluation of Data Acq. & System Control

Data acquisition

- DCPD, reference voltage, applied current, water mixing loop conductivity, water outlet conductivity, autoclave water temperature, corrosion potential, dissolved oxygen
- May add: water pressure logging, mixing loop water temperature logging

PC used to control load on specimen

- Inputs for load control include specimen crack length from DCPD and water pressure which is entered manually
- Constant K testing
- Cyclic K with variable hold time

> Automatic shutdown

• run-away crack

Battelle

• system overtemperature

Evaluation of Make-up Water System

- VV light kills organics
- Demineralizer for ions
- Submicron filter for particulates
- \succ N₂ gas to displace oxygen
- 18.18 Mohm-cm is the typical water resistivity (theoretical purity)

Battelle



Pre-cracking

- Instron servohydraulic used for pre-cracking
- Crack length measured from DCPD
- GE software package controls the Instron and pre-cracking routine.



Construction & Assembly Status

- System #1 running continuously for 60 days
 - Simultaneously oxidizing autoclave internals and performing a shakedown test on cold-worked 316 SS sample
 - Excellent system cleanliness with outlet resistivity better than 10 Mohm-cm and still rising
 - Excellent system performance
- System #2 is 80% complete
 - Completion expected by end of May
 - Oxidation and shakedown test will follow
- System #3 is 30% complete
 - Completion next fiscal year

Battelle