DETECTOR	PROBE	Туре	ENERGY DETECTED	RANGE	COMMENTS	Quantity
E500B	Closable side window (HP-77)	GM	β/γ	.01 - 200 mR/hr	Good for general surveys and frisking. Open window for beta surveying, closed window for gamma surveying.	2
Xetex 305B		GM	β/γ	.001-99 R/hr	Alarming digital ratemeter with closable beta shield. Small andLightweight.	6
PRM-5-3	Pancake (HP-260)	GM	β/γ	100-500K cpm	Best for contamination surveys, personnel frisking, and counting smears.	1
PAC ISAG	Open Window (AC-3)	Scintillation	α	0-25 R/hr	Good for alpha surveys and frisking.	1
PRM-6	Open Window (AC-3)	Scintillation	α	100-500K cpm	Good for alpha surveys and frisking.	1
RM-21-1	Shielded pancake (HP-210)	GM	β/γ	.5-50 mR/hr 100-60K cpm	Good for personnel frisking and counting beta/gamma smears (runs on AC).	1