

CATEGORY 1

REGULATORY INFORMATION DISTRIBUTION SYSTEM (RIDS)

ACCESSION NBR: 9609300106 DOC. DATE: 96/09/19 NOTARIZED: NO DOCKET # 05000400
 FACIL: 50-400 Shearon Harris Nuclear Power Plant, Unit 1, Carolina
 AUTH. NAME AUTHOR AFFILIATION
 ROBINSON, W.R. Carolina Power & Light Co.
 RECIP. NAME RECIPIENT AFFILIATION
 Document Control Branch (Document Control Desk)

See lpt.

SUBJECT: Forwards special rept which provides results of SG tube ISI performed in Sept 1995 during plant refueling outage 6.

DISTRIBUTION CODE: A047D COPIES RECEIVED: LTR 1 ENCL 1 SIZE: 1+759
 TITLE: OR Submittal: Inservice/Testing/Relief from ASME Code - GL-89-04


NOTES: Application for permit renewal filed. 05000400

	RECIPIENT		COPIES			RECIPIENT		COPIES	
	ID CODE/NAME	LTR	ENCL	ID CODE/NAME		LTR	ENCL		
	PD2-1 LA	1	1		PD2-1 PD	1	1		
	LE,N	1	1						
INTERNAL:	ACRS	1	1		AEOD/SPD/RAB	1	1		
	FILE CENTER 01	1	1		NRR/DE/EMEB	1	1		
	NUDOCS-ABSTRACT	1	1		OGC/HDS2	1	0		
	RES/DET/EMEB	1	1		RES/DSIR/EIB	1	1		
EXTERNAL:	LITCO ANDERSON	1	1		NOAC	1	1		
	NRC PDR	1	1						

C
A
T
E
G
O
R
Y
1
D
O
C
U
M
E
N
T

NOTE TO ALL "RIDS" RECIPIENTS:
 PLEASE HELP US TO REDUCE WASTE! CONTACT THE DOCUMENT CONTROL DESK,
 ROOM OWFN 5D-5 (EXT. 415-2083) TO ELIMINATE YOUR NAME FROM
 DISTRIBUTION LISTS FOR DOCUMENTS YOU DON'T NEED!

TOTAL NUMBER OF COPIES REQUIRED: LTR 14 ENCL 13





Carolina Power & Light Company
PO Box 165
New Hill NC 27562

William R. Robinson
Vice President
Harris Nuclear Plant

SEP 19, 1996

SERIAL: HNP-96-141

United States Nuclear Regulatory Commission
ATTENTION: Document Control Desk
Washington, DC 20555

SHEARON HARRIS NUCLEAR POWER PLANT
DOCKET NO. 50-400/LICENSE NO. NPF-63
SPECIAL REPORT - STEAM GENERATOR TUBE INSERVICE INSPECTION RESULTS

Dear Sir or Madam:

Carolina Power & Light Company hereby submits the enclosed Special Report pursuant to Technical Specification 4.4.5.5.b. for the Harris Nuclear Plant. This report provides the results of the steam generator tube inservice inspections performed in September 1995 during the Harris Plant's Refueling Outage No. 6.

Questions regarding this submittal may be referred to Mr. T. D. Walt at (919) 362-2711.

Sincerely,

MGW


Enclosure

- c: Mr. J. B. Brady (NRC Senior Resident Inspector, HNP)
- Mr. S. D. Ebnetter (NRC Regional Administrator, Region II)
- Mr. N. B. Le (NRR Project Manager, HNP)

AD 4/17
1/1

9609300106	960919	
PDR	ADOCK	05000400
Q	PDR	

300020



CAROLINA POWER & LIGHT COMPANY

SHEARON HARRIS

NUCLEAR PLANT

STEAM GENERATOR
EDDY CURRENT EXAMINATION
REPORT

VOLUME II

RFO-6
SEPTEMBER
1995

50-400
9609300/06
9/19/96

UTILITY: Carolina Power & Light

Sep. 23.1995 15:21

PLANT: Shearon Harris

UNIT: 1

SG: A

DATABASE: Harris_SGA_1995

PAGE 1 of 124

* INSPECTION FINAL REPORT LISTING *

*** This report contains all report entries appended to the database for the following test plans ***

All Test Plans in the database are included in summary: 7

Test Plan Name:	Probe Type:	Probe Size:	Type:
1. Top of Tubesheet Exam	MRPC	B620MRPC3C	HL
2. Row 1&2 Ubend Exam	MRPC	B580MRPCPH	CL
3. Bobbin Exam	BOBBIN	A610MULC	CL
4. 20% of Dented Intersections	MRPC	B620MRPC3C	HL
5. Previous Indications	BOBBIN	A610MULC	CL
6. Special Interest	MRPC	B620MRPC3C	CL
7. Special Interest	MRPC	B620MRPC3C	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: A
 DATABASE: Harris_SGA_1995

Sep. 23,1995 15:21

PAGE 2 of 124

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
1.	1	1					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00060	HL
2.							11CTEC	S7675	rpri	A610MULC	SG10CCAL00015	CL
3.	1	2					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00060	HL
4.							11CTEC	S7675	rpri	A610MULC	SG10CCAL00015	CL
5.	1	3					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00060	HL
6.							11CTEC	S7675	rpri	A610MULC	SG10CCAL00015	CL
7.	1	4					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00060	HL
8.							11CTEC	S7675	rpri	A610MULC	SG10CCAL00015	CL
9.	1	5					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00060	HL
10.							11CTEC	S7675	rpri	A610MULC	SG10CCAL00015	CL
11.	1	6					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00060	HL
12.							11CTEC	S7675	rpri	A610MULC	SG10CCAL00015	CL
13.	1	7					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00060	HL
14.							11CTEC	S7675	rpri	A610MULC	SG10CCAL00015	CL
15.	1	8					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00060	HL
16.							11CTEC	S7675	rpri	A610MULC	SG10CCAL00015	CL
17.	1	9					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00060	HL
18.							11CTEC	S7675	rpri	A610MULC	SG10CCAL00015	CL
19.	1	10					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00060	HL
20.							11CTEC	S7675	rpri	A610MULC	SG10CCAL00015	CL
21.	1	11					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00060	HL
22.							11CTEC	S7675	rpri	A610MULC	SG10CCAL00015	CL
23.	1	12					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00060	HL
24.							11H11C	T9924	rpri	B580MRPCPH	SG10CCAL00020	CL
25.							11CTEC	S7675	rpri	A610MULC	SG10CCAL00015	CL
26.	1	13					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00060	HL
27.							11CTEC	S7675	rpri	A610MULC	SG10CCAL00015	CL
28.	1	14					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00060	HL
29.							11CTEC	S7675	rpri	A610MULC	SG10CCAL00015	CL
30.	1	15					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00060	HL
31.							11CTEC	S7675	rpri	A610MULC	SG10CCAL00015	CL
32.	1	16					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00060	HL
33.							11CTEC	S7675	rpri	A610MULC	SG10CCAL00015	CL
34.	1	17					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00060	HL
35.							11H11C	T9924	rpri	B580MRPCPH	SG10CCAL00020	CL
36.							11CTEC	S7675	rpri	A610MULC	SG10CCAL00015	CL
37.	1	18					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00060	HL
38.							11CTEC	S7675	rpri	A610MULC	SG10CCAL00015	CL
39.	1	19					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00060	HL
40.							11CTEC	S7675	rpri	A610MULC	SG10CCAL00015	CL
41.	1	20					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00054	HL
42.							11CTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
43.	1	21					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00054	HL
44.							11CTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
45.	1	22					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00054	HL
46.							11CTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
47.	1	23					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00054	HL
48.							11CTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
49.	1	24					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00054	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: A
 DATABASE: Harris_SGA_1995

Sep. 23.1995 15:21

PAGE 3 of 124

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
50.								11CTEC	S7675	rpri	A610MJLC	SG10CCAL00014	CL
51.	1	25						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00054	HL
52.								11CTEC	S7675	rpri	A610MJLC	SG10CCAL00014	CL
53.	1	26						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00054	HL
54.								11CTEC	S7675	rpri	A610MJLC	SG10CCAL00014	CL
55.	1	27						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00056	HL
56.								11H11C	T9924	rpri	B580MRPCPH	SG10CCAL00020	CL
57.								11CTEC	S7675	rpri	A610MJLC	SG10CCAL00014	CL
58.	1	28						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00056	HL
59.								11CTEC	S7675	rpri	A610MJLC	SG10CCAL00014	CL
60.	1	29						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00056	HL
61.								11CTEC	S7675	rpri	A610MJLC	SG10CCAL00014	CL
62.	1	30						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00056	HL
63.								11CTEC	S7675	rpri	A610MJLC	SG10CCAL00014	CL
64.	1	31						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00056	HL
65.								11CTEC	S7675	rpri	A610MJLC	SG10CCAL00014	CL
66.	1	32						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00056	HL
67.								11H11C	T9924	rpri	B580MRPCPH	SG10CCAL00020	CL
68.								11CTEC	S7675	rpri	A610MJLC	SG10CCAL00014	CL
69.	1	33						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00056	HL
70.								11CTEC	S7675	rpri	A610MJLC	SG10CCAL00014	CL
71.	1	34						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00056	HL
72.								11CTEC	S7675	rpri	A610MJLC	SG10CCAL00014	CL
73.	1	35						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00056	HL
74.								11CTEC	F3325	rsec	A610MJLC	SG10CCAL00014	CL
75.	1	36						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00056	HL
76.								11CTEC	S7675	rpri	A610MJLC	SG10CCAL00014	CL
77.	1	37						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00008	HL
78.								11CTEC	G1931	rpri	A610MJLC	SG10CCAL00001	CL
79.	1	38						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00008	HL
80.								11CTEC	G1931	rpri	A610MJLC	SG10CCAL00001	CL
81.	1	39						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00008	HL
82.								11H11C	T9924	rpri	B580MRPCPH	SG10CCAL00020	CL
83.								11CTEC	G1931	rpri	A610MJLC	SG10CCAL00001	CL
84.	1	40						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00008	HL
85.								11CTEC	G1931	rpri	A610MJLC	SG10CCAL00001	CL
86.	1	41						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00008	HL
87.								11CTEC	G1931	rpri	A610MJLC	SG10CCAL00001	CL
88.	1	42						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00008	HL
89.								11H11C	T9924	rpri	B580MRPCPH	SG10CCAL00020	CL
90.								11CTEC	G1931	rpri	A610MJLC	SG10CCAL00001	CL
91.	1	43						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00008	HL
92.								11CTEC	G1931	rpri	A610MJLC	SG10CCAL00001	CL
93.	1	44						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00008	HL
94.								11H11C	T9924	rpri	B580MRPCPH	SG10CCAL00020	CL
95.								11CTEC	G1931	rpri	A610MJLC	SG10CCAL00001	CL
96.	1	45						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00008	HL
97.								11CTEC	G1931	rpri	A610MJLC	SG10CCAL00001	CL
98.	1	46						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00008	HL



**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: A
 DATABASE: Harris_SGA_1995

Sep. 23.1995 15:21

PAGE 4 of 124

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
99.							11CTEC	G1931	rpri	A610MJLC	SG10CCAL00003	CL
100.	1	47					TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00008	HL
101.							11H11C	T9924	rpri	B580MRPCPH	SG10CCAL00020	CL
102.							11CTEC	G1931	rpri	A610MJLC	SG10CCAL00003	CL
103.	1	48					TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00008	HL
104.							11CTEC	G1931	rpri	A610MJLC	SG10CCAL00003	CL
105.	1	49					TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00008	HL
106.							11CTEC	G1931	rpri	A610MJLC	SG10CCAL00003	CL
107.	1	50					TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00008	HL
108.							11H11C	T9924	rpri	B580MRPCPH	SG10CCAL00020	CL
109.							11CTEC	G1931	rpri	A610MJLC	SG10CCAL00003	CL
110.	1	51					TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00008	HL
111.							11CTEC	G1931	rpri	A610MJLC	SG10CCAL00003	CL
112.	1	52					TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00008	HL
113.							11CTEC	G1931	rpri	A610MJLC	SG10CCAL00003	CL
114.	1	53					TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00008	HL
115.							11H11C	T9924	rpri	B580MRPCPH	SG10CCAL00020	CL
116.							11CTEC	G1931	rpri	A610MJLC	SG10CCAL00003	CL
117.	1	54					TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00008	HL
118.							11CTEC	G1931	rpri	A610MJLC	SG10CCAL00003	CL
119.	1	55					TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00008	HL
120.							11CTEC	G1931	rpri	A610MJLC	SG10CCAL00003	CL
121.	1	56					TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00008	HL
122.							11H11C	T9924	rpri	B580MRPCPH	SG10CCAL00020	CL
123.							11CTEC	G1931	rpri	A610MJLC	SG10CCAL00003	CL
124.	1	57					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00046	HL
125.							11CTEC	S7675	rpri	A610MJLC	SG10CCAL00010	CL
126.	1	58					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00046	HL
127.							11CTEC	S7675	rpri	A610MJLC	SG10CCAL00010	CL
128.	1	59					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00046	HL
129.							11H11C	I2393	rpri	B580MRPCPH	SG10CCAL00021	CL
130.							11CTEC	S7675	rpri	A610MJLC	SG10CCAL00010	CL
131.	1	60					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00046	HL
132.							11CTEC	S7675	rpri	A610MJLC	SG10CCAL00010	CL
133.	1	61					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00046	HL
134.							11CTEC	S7675	rpri	A610MJLC	SG10CCAL00010	CL
135.	1	62					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00046	HL
136.							11CTEC	M9082	rsec	A610MJLC	SG10CCAL00010	CL
137.	1	63					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00046	HL
138.							11CTEC	S7675	rpri	A610MJLC	SG10CCAL00010	CL
139.	1	64					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00046	HL
140.							11H11C	T9924	rpri	B580MRPCPH	SG10CCAL00020	CL
141.							11CTEC	S7675	rpri	A610MJLC	SG10CCAL00010	CL
142.	1	65					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00046	HL
143.							11CTEC	S7675	rpri	A610MJLC	SG10CCAL00010	CL
144.	1	66					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00046	HL
145.							11CTEC	S7675	rpri	A610MJLC	SG10CCAL00010	CL
146.	1	67					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00046	HL
147.							11CTEC	S7675	rpri	A610MJLC	SG10CCAL00010	CL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: A
 DATABASE: Harris_SGA_1995

Sep. 23,1995 15:21

PAGE 6 of 124

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
197.	1	89					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00024	HL
198.							11CTEC	F2217	rpri	A610MULC	SG10CCAL00007	CL
199.	1	90					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00024	HL
200.							11CTEC	F2217	rpri	A610MULC	SG10CCAL00007	CL
201.	1	91					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00024	HL
202.							11CTEC	F2217	rpri	A610MULC	SG10CCAL00007	CL
203.	1	92					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00024	HL
204.							11CTEC	F2217	rpri	A610MULC	SG10CCAL00007	CL
205.	1	93					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00024	HL
206.							11CTEC	F2217	rpri	A610MULC	SG10CCAL00007	CL
207.	1	94					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00010	HL
208.							11CTEC	G1931	rpri	A610MULC	SG10CCAL00003	CL
209.	1	95					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00010	HL
210.							11CTEC	G1931	rpri	A610MULC	SG10CCAL00003	CL
211.	1	96					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00010	HL
212.							11CTEC	G1931	rpri	A610MULC	SG10CCAL00003	CL
213.	1	97					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00010	HL
214.							11CTEC	G1931	rpri	A610MULC	SG10CCAL00003	CL
215.	1	98					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00010	HL
216.							11CTEC	G1931	rpri	A610MULC	SG10CCAL00003	CL
17.	1	99					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00010	HL
19.							11CTEC	G1931	rpri	A610MULC	SG10CCAL00003	CL
199.	1	100					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00010	HL
220.							11CTEC	G1931	rpri	A610MULC	SG10CCAL00003	CL
221.	1	101					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00010	HL
222.							11CTEC	G1931	rpri	A610MULC	SG10CCAL00003	CL
223.	1	102					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00010	HL
224.							11H11C	T9924	rpri	B580MRPCPH	SG10CCAL00020	CL
225.							11CTEC	G1931	rpri	A610MULC	SG10CCAL00003	CL
226.	1	103					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00010	HL
227.							11CTEC	G1931	rpri	A610MULC	SG10CCAL00003	CL
228.	1	104					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00010	HL
229.							11H11C	T9924	rpri	B580MRPCPH	SG10CCAL00020	CL
230.							11CTEC	G1931	rpri	A610MULC	SG10CCAL00003	CL
231.	1	105					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00010	HL
232.							11CTEC	G1931	rpri	A610MULC	SG10CCAL00003	CL
233.	1	106					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00010	HL
234.							11CTEC	G1931	rpri	A610MULC	SG10CCAL00003	CL
235.	1	107					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00010	HL
236.							11CTEC	G1931	rpri	A610MULC	SG10CCAL00003	CL
237.	1	108					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00010	HL
238.							11CTEC	G1931	rpri	A610MULC	SG10CCAL00003	CL
239.	1	109					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00010	HL
240.							11CTEC	G1931	rpri	A610MULC	SG10CCAL00003	CL
241.	1	110					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00010	HL
242.							11CTEC	G1931	rpri	A610MULC	SG10CCAL00003	CL
243.	1	111					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00010	HL
244.							11CTEC	G1931	rpri	A610MULC	SG10CCAL00003	CL
245.	1	112					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00010	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: A
 DATABASE: Harris_SGA_1995

Sep. 23.1995 15:21

PAGE 7 of 124

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
246.								11CTEC	G1931	rpri	A610MULC	SG10CCAL00003	CL
247.	1	113						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00010	HL
248.								11CTEC	G1931	rpri	A610MULC	SG10CCAL00003	CL
249.	1	114							G1931	rpri	A610MULC	SG10CCAL00003	CL
250.								11CTEC	S7675	rpri	A610MULC	SG10CCAL00016	CL
251.		1.07	92	23	P1	TSH	0.15	TSHTSH	F3453	reso	B620MRPC3C	SG11HCAL00010	HL
252.		0.09	78	PLP	11	TSH	0.15	TSHTSH	F3453	reso	B620MRPC3C	SG11HCAL00010	HL
253.	2	1						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00058	HL
254.								11CTEC	S7675	rpri	A610MULC	SG10CCAL00015	CL
255.	2	2						TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00059	HL
256.								11CTEC	S7675	rpri	A610MULC	SG10CCAL00015	CL
257.	2	3						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00060	HL
258.								11CTEC	S7675	rpri	A610MULC	SG10CCAL00015	CL
259.	2	4						TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00061	HL
260.								11CTEC	S7675	rpri	A610MULC	SG10CCAL00015	CL
261.	2	5						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00060	HL
262.								11CTEC	S7675	rpri	A610MULC	SG10CCAL00015	CL
263.	2	6						TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00061	HL
264.								11CTEC	S7675	rpri	A610MULC	SG10CCAL00015	CL
265.	2	7						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00060	HL
266.								11CTEC	S7675	rpri	A610MULC	SG10CCAL00015	CL
267.	2	8						TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00061	HL
268.								11CTEC	S7675	rpri	A610MULC	SG10CCAL00015	CL
269.	2	9						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00060	HL
270.								11CTEC	S7675	rpri	A610MULC	SG10CCAL00015	CL
271.	2	10						TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00061	HL
272.								11H11C	T9924	rpri	B580MRPCPH	SG10CCAL00020	CL
273.								11CTEC	S7675	rpri	A610MULC	SG10CCAL00015	CL
274.	2	11						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00060	HL
275.								11CTEC	S7675	rpri	A610MULC	SG10CCAL00015	CL
276.	2	12						TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00061	HL
277.								11CTEC	S7675	rpri	A610MULC	SG10CCAL00015	CL
278.	2	13						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00060	HL
279.								11CTEC	S7675	rpri	A610MULC	SG10CCAL00015	CL
280.	2	14						TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00061	HL
281.								11H11C	T9924	rpri	B580MRPCPH	SG10CCAL00020	CL
282.								11CTEC	S7675	rpri	A610MULC	SG10CCAL00015	CL
283.	2	15						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00060	HL
284.								11CTEC	S7675	rpri	A610MULC	SG10CCAL00015	CL
285.	2	16						TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00061	HL
286.								11H11C	T9924	rpri	B580MRPCPH	SG10CCAL00020	CL
287.								11CTEC	S7675	rpri	A610MULC	SG10CCAL00015	CL
288.	2	17						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00060	HL
289.								11CTEC	S7675	rpri	A610MULC	SG10CCAL00015	CL
290.	2	18						TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00061	HL
291.								11H11C	T9924	rpri	B580MRPCPH	SG10CCAL00020	CL
292.								11CTEC	S7675	rpri	A610MULC	SG10CCAL00015	CL
293.	2	19						TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00061	HL
294.								11CTEC	S7675	rpri	A610MULC	SG10CCAL00015	CL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: A
 DATABASE: Harris_SGA_1995

Sep. 23.1995 15:21

PAGE 8 of 124

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
295.	2	20					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00053	HL
296.							11CTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
297.	2	21					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00053	HL
298.							11CTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
299.	2	22					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00053	HL
300.							11CTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
301.	2	23					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00053	HL
302.							11H11C	T9924	rpri	B580MRPCPH	SG10CCAL00020	CL
303.							11CTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
304.	2	24					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00053	HL
305.							11CTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
306.	2	25					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00053	HL
307.							11CTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
308.	2	26					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00053	HL
309.							11CTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
310.	2	27					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00055	HL
311.							11CTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
312.	2	28					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00055	HL
313.							11CTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
314.	2	29					TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00057	HL
15.							11CTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
315.	2	30					TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00057	HL
317.							11H11C	T9924	rpri	B580MRPCPH	SG10CCAL00020	CL
318.							11CTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
319.	2	31					TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00057	HL
320.							11CTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
321.	2	32					TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00057	HL
322.							11CTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
323.	2	33					TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00057	HL
324.							11CTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
325.	2	34					TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00057	HL
326.							11CTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
327.	2	35					TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00057	HL
328.							11H11C	T9924	rpri	B580MRPCPH	SG10CCAL00020	CL
329.							11CTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
330.	2	36					TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00057	HL
331.							11CTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
332.	2	37					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00007	HL
333.							11H11C	T9924	rpri	B580MRPCPH	SG10CCAL00020	CL
334.							11CTEC	G1931	rpri	A610MULC	SG10CCAL00001	CL
335.	2	38					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00007	HL
336.							11CTEC	G1931	rpri	A610MULC	SG10CCAL00001	CL
337.	2	39					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00007	HL
338.							11CTEC	G1931	rpri	A610MULC	SG10CCAL00001	CL
339.	2	40					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00007	HL
340.							11CTEC	G1931	rpri	A610MULC	SG10CCAL00001	CL
341.	2	41					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00007	HL
342.							11CTEC	G1931	rpri	A610MULC	SG10CCAL00001	CL
343.	2	42					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00007	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: A
 DATABASE: Harris_SGA_1995

Sep. 23.1995 15:21

PAGE 9 of 124

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
344.							11CTEC	G1931	rpri	A610MULC	SG10CCAL00001	CL
345.	2	43					TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00007	HL
346.							11CTEC	G1931	rpri	A610MULC	SG10CCAL00001	CL
347.	2	44					TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00007	HL
348.							11CTEC	G1931	rpri	A610MULC	SG10CCAL00001	CL
349.	2	45					TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00007	HL
350.							11CTEC	G1931	rpri	A610MULC	SG10CCAL00001	CL
351.	2	46					TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00007	HL
352.							11H11C	T9924	rpri	B580MRPCPH	SG10CCAL00020	CL
353.							11CTEC	F9284	rpri	A610MULC	SG10CCAL00002	CL
354.	2	47					TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00007	HL
355.							11CTEC	G1931	rpri	A610MULC	SG10CCAL00003	CL
356.	2	48					TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00007	HL
357.							11CTEC	G1931	rpri	A610MULC	SG10CCAL00003	CL
358.	2	49					TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00007	HL
359.							11H11C	T9924	rpri	B580MRPCPH	SG10CCAL00020	CL
360.							11CTEC	G1931	rpri	A610MULC	SG10CCAL00003	CL
361.	2	50					TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00007	HL
362.							11CTEC	G1931	rpri	A610MULC	SG10CCAL00003	CL
363.	2	51					TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00007	HL
364.							11CTEC	G1931	rpri	A610MULC	SG10CCAL00003	CL
365.	2	52					TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00007	HL
366.							11CTEC	G1931	rpri	A610MULC	SG10CCAL00003	CL
367.	2	53					TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00007	HL
368.							11CTEC	G1931	rpri	A610MULC	SG10CCAL00003	CL
369.	2	54					TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00007	HL
370.							11CTEC	G1931	rpri	A610MULC	SG10CCAL00003	CL
371.	2	55					TSHTSH	H3464	rsec	B620MRPC3C	SG11HCAL00007	HL
372.							11H11C	T9924	rpri	B580MRPCPH	SG10CCAL00020	CL
373.							11CTEC	G1931	rpri	A610MULC	SG10CCAL00003	CL
374.	2	56					TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00007	HL
375.							11CTEC	G1931	rpri	A610MULC	SG10CCAL00003	CL
376.	2	57					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00045	HL
377.							11CTEC	S7675	rpri	A610MULC	SG10CCAL00010	CL
378.	2	58					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00045	HL
379.							11CTEC	S7675	rpri	A610MULC	SG10CCAL00010	CL
380.	2	60					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00045	HL
381.							11CTEC	S7675	rpri	A610MULC	SG10CCAL00010	CL
382.	2	61					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00045	HL
383.							11CTEC	S7675	rpri	A610MULC	SG10CCAL00010	CL
384.	2	62					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00045	HL
385.							11H11C	I2393	rpri	B580MRPCPH	SG10CCAL00021	CL
386.							11CTEC	M9082	rsec	A610MULC	SG10CCAL00010	CL
387.	2	63					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00045	HL
388.							11CTEC	S7675	rpri	A610MULC	SG10CCAL00010	CL
389.	2	64					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00045	HL
390.							11CTEC	S7675	rpri	A610MULC	SG10CCAL00010	CL
391.	2	65					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00045	HL
392.							11CTEC	S7675	rpri	A610MULC	SG10CCAL00010	CL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: A
 DATABASE: Harris_SGA_1995

Sep. 23.1995 15:21

PAGE 10 of 124

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
393.	2	66					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00045	HL
394.							11H11C	T9924	rpri	B580MRPCPH	SG10CCAL00020	CL
395.							11CTEC	S7675	rpri	A610MULC	SG10CCAL00010	CL
396.	2	67					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00045	HL
397.							11CTEC	S7675	rpri	A610MULC	SG10CCAL00010	CL
398.	2	68					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00045	HL
399.							11CTEC	S7675	rpri	A610MULC	SG10CCAL00010	CL
400.	2	69					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00045	HL
401.							11CTEC	S7675	rpri	A610MULC	SG10CCAL00010	CL
402.	2	70					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00045	HL
403.							11CTEC	S7675	rpri	A610MULC	SG10CCAL00010	CL
404.	2	71					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00045	HL
405.							11H11C	T9924	rpri	B580MRPCPH	SG10CCAL00020	CL
406.							11CTEC	S7675	rpri	A610MULC	SG10CCAL00010	CL
407.	2	72					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00045	HL
408.							11CTEC	S7675	rpri	A610MULC	SG10CCAL00010	CL
409.	2	73					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00045	HL
410.							11CTEC	S7675	rpri	A610MULC	SG10CCAL00010	CL
411.	2	74					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00045	HL
412.							11CTEC	S7675	rpri	A610MULC	SG10CCAL00010	CL
413.	2	75					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00045	HL
414.							11CTEC	S7675	rpri	A610MULC	SG10CCAL00010	CL
415.	2	76					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00045	HL
416.							11CTEC	S7675	rpri	A610MULC	SG10CCAL00010	CL
417.	2	77					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00023	HL
418.							11CTEC	F2217	rpri	A610MULC	SG10CCAL00007	CL
419.	2	78					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00023	HL
420.							11CTEC	F2217	rpri	A610MULC	SG10CCAL00007	CL
421.	2	79					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00023	HL
422.							11CTEC	F2217	rpri	A610MULC	SG10CCAL00007	CL
423.	2	80					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00023	HL
424.							11H11C	T9924	rpri	B580MRPCPH	SG10CCAL00020	CL
425.							11CTEC	F2217	rpri	A610MULC	SG10CCAL00006	CL
426.	2	81					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00023	HL
427.							11H11C	T9924	rpri	B580MRPCPH	SG10CCAL00020	CL
428.							11CTEC	F2217	rpri	A610MULC	SG10CCAL00006	CL
429.	2	82					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00023	HL
430.							11CTEC	F2217	rpri	A610MULC	SG10CCAL00006	CL
431.	2	83					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00023	HL
432.							11H11C	T9924	rpri	B580MRPCPH	SG10CCAL00020	CL
433.							11CTEC	F2217	rpri	A610MULC	SG10CCAL00006	CL
434.	2	84					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00023	HL
435.							11CTEC	F2217	rpri	A610MULC	SG10CCAL00006	CL
436.	2	85					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00023	HL
437.							11CTEC	F2217	rpri	A610MULC	SG10CCAL00007	CL
438.	2	86					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00023	HL
439.							11CTEC	F2217	rpri	A610MULC	SG10CCAL00007	CL
440.	2	87					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00023	HL
441.							11H11C	T9924	rpri	B580MRPCPH	SG10CCAL00020	CL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: A
 DATABASE: Harris_SGA_1995

Sep. 23.1995 15:21

PAGE 11 of 124

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
442.							11CTEC	F2217	rpri	A610MULC	SG10CCAL00007	CL
443.	2	88					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00023	HL
444.							11CTEC	F2217	rpri	A610MULC	SG10CCAL00007	CL
445.	2	89					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00023	HL
446.							11H11C	T9924	rpri	B580MRPCPH	SG10CCAL00020	CL
447.							11CTEC	F2217	rpri	A610MULC	SG10CCAL00007	CL
448.	2	90					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00023	HL
449.							11CTEC	F2217	rpri	A610MULC	SG10CCAL00007	CL
450.	2	91					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00023	HL
451.							11CTEC	F2217	rpri	A610MULC	SG10CCAL00007	CL
452.	2	92					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00023	HL
453.							11H11C	T9924	rpri	B580MRPCPH	SG10CCAL00020	CL
454.							11CTEC	F2217	rpri	A610MULC	SG10CCAL00007	CL
455.	2	93					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00023	HL
456.							11CTEC	F2217	rpri	A610MULC	SG10CCAL00007	CL
457.	2	94					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00009	HL
458.							11H11C	T9924	rpri	B580MRPCPH	SG10CCAL00020	CL
459.					RBD		G1931	G1931	rpri	A610MULC	SG10CCAL00003	CL
460.							11CTEC	S7675	rpri	A610MULC	SG10CCAL00016	CL
461.	2	95					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00011	HL
462.							11CTEC	G1931	rpri	A610MULC	SG10CCAL00004	CL
463.	2	96					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00009	HL
464.							11H11C	T9924	rpri	B580MRPCPH	SG10CCAL00020	CL
465.							11CTEC	G1931	rpri	A610MULC	SG10CCAL00004	CL
466.	2	97					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00011	HL
467.							11CTEC	G1931	rpri	A610MULC	SG10CCAL00004	CL
468.	2	98					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00009	HL
469.							11H11C	T9924	rpri	B580MRPCPH	SG10CCAL00020	CL
470.							11CTEC	G1931	rpri	A610MULC	SG10CCAL00004	CL
471.	2	99					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00011	HL
472.							11CTEC	G1931	rpri	A610MULC	SG10CCAL00004	CL
473.	2	100					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00009	HL
474.							11H11C	T9924	rpri	B580MRPCPH	SG10CCAL00020	CL
475.							11CTEC	G1931	rpri	A610MULC	SG10CCAL00004	CL
476.	2	101					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00011	HL
477.							11CTEC	G1931	rpri	A610MULC	SG10CCAL00004	CL
478.	2	102					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00009	HL
479.							11CTEC	G1931	rpri	A610MULC	SG10CCAL00004	CL
480.	2	103					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00011	HL
481.							11CTEC	G1931	rpri	A610MULC	SG10CCAL00004	CL
482.	2	104					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00009	HL
483.							11CTEC	G1931	rpri	A610MULC	SG10CCAL00004	CL
484.	2	105					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00011	HL
485.							11CTEC	G1931	rpri	A610MULC	SG10CCAL00004	CL
486.	2	106					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00009	HL
487.							11CTEC	G1931	rpri	A610MULC	SG10CCAL00004	CL
488.	2	107					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00011	HL
489.							11CTEC	G1931	rpri	A610MULC	SG10CCAL00004	CL
490.	2	108					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00009	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: A
 DATABASE: Harris_SGA_1995

Sep. 23.1995 15:21

PAGE 12 of 124

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
491.							11CTEC	G1931	rpri	A610MULC	SG10CCAL00004	CL
492.	2	109					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00011	HL
493.							11CTEC	G1931	rpri	A610MULC	SG10CCAL00004	CL
494.	2	110					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00009	HL
495.							11CTEC	G1931	rpri	A610MULC	SG10CCAL00005	CL
496.	2	111					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00033	HL
497.							11CTEC	G1931	rpri	A610MULC	SG10CCAL00005	CL
498.	2	112					TSHTSH	H3464	rsec	B620MRPC3C	SG11HCAL00012	HL
499.							11CTEC	G1931	rpri	A610MULC	SG10CCAL00005	CL
500.	2	113					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00013	HL
501.							11CTEC	G1931	rpri	A610MULC	SG10CCAL00005	CL
502.	2	114					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00012	HL
503.							11CTEC	G1931	rpri	A610MULC	SG10CCAL00005	CL
504.	3	1					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00060	HL
505.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00015	CL
506.	3	2					TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00061	HL
507.	3	3					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00060	HL
508.	3	4					TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00061	HL
509.	3	5					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00060	HL
510.	3	6					TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00061	HL
11.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00015	CL
12.	3	7					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00060	HL
13.	3	8					TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00061	HL
514.	3	9					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00060	HL
515.	3	10					TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00061	HL
516.	3	11					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00060	HL
517.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00015	CL
518.	3	12					TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00061	HL
519.	3	13					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00060	HL
520.	3	14					TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00061	HL
521.	3	15					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00060	HL
522.	3	16					TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00061	HL
523.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00015	CL
524.	3	17					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00060	HL
525.	3	18					TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00061	HL
526.	3	19					TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00061	HL
527.	3	20					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00054	HL
528.	3	21					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00054	HL
529.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
530.	3	22					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00054	HL
531.	3	23					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00054	HL
532.	3	24					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00054	HL
533.	3	25					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00054	HL
534.	3	26					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00054	HL
535.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
536.	3	27					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00056	HL
537.	3	28					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00056	HL
538.	3	29					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00056	HL
539.	3	30					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00056	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: A
 DATABASE: Harris_SGA_1995

Sep. 23, 1995 15:21

PAGE 13 of 124

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
540.	3	31						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00056	HL
541.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
542.	3	32						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00056	HL
543.	3	33						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00056	HL
544.	3	34						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00056	HL
545.	3	35						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00056	HL
546.	3	36						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00056	HL
547.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
548.	3	37						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00008	HL
549.	3	38						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00008	HL
550.	3	39						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00008	HL
551.	3	40						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00008	HL
552.	3	41						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00008	HL
553.								TEHTEC	G1931	rpri	A610MULC	SG10CCAL00001	CL
554.	3	42						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00008	HL
555.	3	43						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00008	HL
556.	3	44						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00008	HL
557.	3	45						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00008	HL
558.	3	46						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00008	HL
559.								TEHTEC	G1931	rpri	A610MULC	SG10CCAL00001	CL
60.	3	47						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00008	HL
61.	3	48						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00008	HL
62.	3	49						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00008	HL
63.	3	50						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00008	HL
64.	3	51						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00008	HL
65.								TEHTEC	G1931	rpri	A610MULC	SG10CCAL00003	CL
66.	3	52						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00008	HL
67.	3	53						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00008	HL
68.	3	54						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00008	HL
69.	3	55						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00008	HL
70.	3	56						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00008	HL
71.								TEHTEC	G1931	rpri	A610MULC	SG10CCAL00003	CL
72.	3	57						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00046	HL
73.	3	58						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00046	HL
74.	3	59						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00046	HL
75.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00016	CL
76.								11CTEC	S7675	rpri	A610MULC	SG10CCAL00010	CL
77.	3	60						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00046	HL
78.	3	61						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00046	HL
79.	3	62						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00046	HL
80.			4.61	162	MBM	1	01C 5.28	TEHTEC	F3453	reso	A610MULC	SG10CCAL00010	CL
81.	3	63						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00046	HL
82.	3	64						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00046	HL
83.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00010	CL
84.	3	65						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00046	HL
85.	3	66						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00046	HL
86.	3	67						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00046	HL
87.	3	68						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00046	HL
88.	3	69						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00046	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: A
 DATABASE: Harris_SGA_1995

Sep. 23.1995 15:21

PAGE 14 of 124

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
589.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00010	CL
590.	3	70					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00046	HL
591.	3	71					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00046	HL
592.	3	72					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00046	HL
593.	3	73					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00046	HL
594.	3	74					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00046	HL
595.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00010	CL
596.	3	75					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00046	HL
597.	3	76					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00046	HL
598.	3	77					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00024	HL
599.	3	78					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00024	HL
600.	3	79					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00024	HL
601.							TEHTEC	F2217	rpri	A610MULC	SG10CCAL00007	CL
602.	3	80					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00024	HL
603.	3	81					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00024	HL
604.	3	82					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00024	HL
605.	3	83					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00024	HL
606.	3	84					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00024	HL
607.							TEHTEC	F2217	rpri	A610MULC	SG10CCAL00007	CL
608.	3	85					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00024	HL
609.	3	86					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00024	HL
610.	3	87					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00024	HL
611.	3	88					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00024	HL
612.	3	89					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00024	HL
613.							TEHTEC	F2217	rpri	A610MULC	SG10CCAL00007	CL
614.	3	90					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00024	HL
615.	3	91					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00024	HL
616.	3	92					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00024	HL
617.	3	93					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00024	HL
618.	3	94					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00009	HL
619.							TEHTEC	G1931	rpri	A610MULC	SG10CCAL00004	CL
620.	3	95					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00011	HL
621.	3	96					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00009	HL
622.	3	97					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00011	HL
623.	3	98					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00009	HL
624.	3	99					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00011	HL
625.							TEHTEC	G1931	rpri	A610MULC	SG10CCAL00004	CL
626.	3	100					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00009	HL
627.	3	101					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00011	HL
628.	3	102					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00009	HL
629.	3	103					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00011	HL
630.	3	104					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00009	HL
631.							TEHTEC	G1931	rpri	A610MULC	SG10CCAL00004	CL
632.	3	105					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00011	HL
633.	3	106					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00009	HL
634.	3	107					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00011	HL
635.	3	108					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00009	HL
636.	3	109					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00011	HL
637.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00016	CL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: A
 DATABASE: Harris_SGA_1995

Sep. 23,1995 15:21

PAGE 15 of 124

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
638.	3	110						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00009	HL
639.	3	111						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00011	HL
640.	3	112						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00012	HL
641.	3	113						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00013	HL
642.	3	114						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00012	HL
643.								TEHTEC	G1931	rpri	A610MULC	SG10CCAL00005	CL
644.	4	1						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00060	HL
645.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00015	CL
646.	4	2						TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00061	HL
647.	4	3						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00060	HL
648.	4	4						TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00061	HL
649.	4	5						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00060	HL
650.	4	6						TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00061	HL
651.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00015	CL
652.	4	7						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00060	HL
653.	4	8						TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00061	HL
654.	4	9						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00060	HL
655.	4	10						TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00061	HL
656.	4	11						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00060	HL
657.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00015	CL
658.	4	12						TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00061	HL
659.	4	13						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00060	HL
660.	4	14						TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00061	HL
661.	4	15						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00060	HL
662.	4	16						TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00061	HL
663.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00015	CL
664.	4	17						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00060	HL
665.	4	18						TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00061	HL
666.	4	19						TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00061	HL
667.	4	20						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00053	HL
668.	4	21						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00053	HL
669.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
670.	4	22						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00053	HL
671.	4	23						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00053	HL
672.	4	24						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00053	HL
673.	4	25						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00053	HL
674.	4	26						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00053	HL
675.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
676.	4	27						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00055	HL
677.	4	28						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00055	HL
678.	4	29						TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00057	HL
679.	4	30						TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00057	HL
680.	4	31						TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00057	HL
681.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
682.	4	32						TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00057	HL
683.	4	33						TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00057	HL
684.	4	34						TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00057	HL
685.	4	35						TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00057	HL
686.	4	36						TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00057	HL

*** INSPECTION FINAL REPORT LISTING ***

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: A
 DATABASE: Harris_SGA_1995

Sep. 23.1995 15:21

PAGE 16 of 124

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
687.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
688.	4	37					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00007	HL
689.	4	38					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00007	HL
690.	4	39					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00007	HL
691.	4	40					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00007	HL
692.	4	41					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00007	HL
693.							TEHTEC	G1931	rpri	A610MULC	SG10CCAL00001	CL
694.	4	42					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00007	HL
695.	4	43					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00007	HL
696.	4	44					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00007	HL
697.	4	45					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00007	HL
698.	4	46					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00007	HL
699.							TEHTEC	G1931	rpri	A610MULC	SG10CCAL00001	CL
700.	4	47					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00007	HL
701.	4	48					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00007	HL
702.	4	49					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00007	HL
703.	4	50					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00007	HL
704.	4	51					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00007	HL
705.							TEHTEC	G1931	rpri	A610MULC	SG10CCAL00003	CL
706.	4	52					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00007	HL
707.	4	53					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00007	HL
708.	4	54					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00007	HL
709.	4	55					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00007	HL
710.	4	56					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00007	HL
711.							TEHTEC	G1931	rpri	A610MULC	SG10CCAL00003	CL
712.	4	57					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00045	HL
713.	4	58					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00045	HL
714.	4	59					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00045	HL
715.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00010	CL
716.	4	60					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00045	HL
717.	4	61					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00045	HL
718.	4	62					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00045	HL
719.	4	63					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00045	HL
720.	4	64					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00045	HL
721.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00010	CL
722.	4	65					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00045	HL
723.	4	66					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00045	HL
724.	4	67					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00045	HL
725.	4	68					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00045	HL
726.	4	69					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00045	HL
727.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00010	CL
728.	4	70					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00045	HL
729.	4	71					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00045	HL
730.	4	72					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00045	HL
731.	4	73					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00045	HL
732.	4	74					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00045	HL
733.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00010	CL
734.	4	75					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00045	HL
735.	4	76					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00045	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: A
 DATABASE: Harris_SGA_1995

Sep. 23.1995 15:21

PAGE 17 of 124

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
736.	4	77					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00023	HL
737.	4	78					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00023	HL
738.	4	79					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00023	HL
739.							TEHTEC	F2217	rpri	A610MULC	SG10CCAL00007	CL
740.	4	80					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00023	HL
741.	4	81					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00023	HL
742.	4	82					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00023	HL
743.	4	83					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00023	HL
744.	4	84					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00023	HL
745.							TEHTEC	F2217	rpri	A610MULC	SG10CCAL00007	CL
746.	4	85					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00023	HL
747.	4	86					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00023	HL
748.	4	87					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00023	HL
749.	4	88					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00023	HL
750.	4	89					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00023	HL
751.							TEHTEC	F2217	rpri	A610MULC	SG10CCAL00007	CL
752.	4	90					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00023	HL
753.	4	91					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00023	HL
754.	4	92					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00023	HL
755.	4	93					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00023	HL
56.	4	94					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00009	HL
							TEHTEC	G1931	rpri	A610MULC	SG10CCAL00004	CL
759.	4	95					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00011	HL
759.	4	96					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00009	HL
760.	4	97					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00011	HL
761.	4	98					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00009	HL
762.	4	99					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00011	HL
763.							TEHTEC	G1931	rpri	A610MULC	SG10CCAL00004	CL
764.	4	100					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00009	HL
765.	4	101					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00011	HL
766.	4	102					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00009	HL
767.	4	103					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00011	HL
768.	4	104					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00009	HL
769.							TEHTEC	G1931	rpri	A610MULC	SG10CCAL00004	CL
770.	4	105					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00011	HL
771.	4	106					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00009	HL
772.	4	107					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00011	HL
773.	4	108					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00009	HL
774.	4	109					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00011	HL
775.							TEHTEC	G1931	rpri	A610MULC	SG10CCAL00005	CL
776.	4	110					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00009	HL
777.	4	111					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00011	HL
778.	4	112					TSHTSH	H3464	rsec	B620MRPC3C	SG11HCAL00012	HL
779.	4	113					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00013	HL
780.	4	114					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00012	HL
781.							TEHTEC	G1931	rpri	A610MULC	SG10CCAL00005	CL
782.	5	1					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00060	HL
							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00015	CL
784.	5	2					TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00061	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: A
 DATABASE: Harris_SGA_1995

Sep. 23,1995 15:21

PAGE 18 of 124

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
785.	5	3					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00060	HL
786.	5	4					TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00061	HL
787.	5	5					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00060	HL
788.	5	6					TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00061	HL
789.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00015	CL
790.	5	7					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00060	HL
791.	5	8					TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00061	HL
792.	5	9					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00060	HL
793.	5	10					TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00061	HL
794.	5	11					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00060	HL
795.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00015	CL
796.	5	12					TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00061	HL
797.	5	13					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00060	HL
798.	5	14					TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00061	HL
799.	5	15					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00060	HL
800.	5	16					TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00061	HL
801.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00015	CL
802.	5	17					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00060	HL
803.	5	18					TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00061	HL
804.	5	19					TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00061	HL
805.	5	20					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00054	HL
806.	5	21					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00054	HL
807.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
808.	5	22					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00054	HL
809.	5	23					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00054	HL
810.	5	24					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00054	HL
811.	5	25					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00054	HL
812.	5	26					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00054	HL
813.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
814.	5	27					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00056	HL
815.	5	28					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00056	HL
816.	5	29					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00056	HL
817.	5	30					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00056	HL
818.	5	31					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00056	HL
819.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
820.	5	32					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00056	HL
821.	5	33					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00056	HL
822.	5	34					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00056	HL
823.	5	35					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00056	HL
824.	5	36					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00056	HL
825.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
826.	5	37					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00008	HL
827.	5	38					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00008	HL
828.	5	39					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00008	HL
829.	5	40					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00008	HL
830.	5	41					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00008	HL
831.							TEHTEC	G1931	rpri	A610MULC	SG10CCAL00001	CL
832.	5	42					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00008	HL
833.	5	43					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00008	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: A
 DATABASE: Harris_SGA_1995

Sep. 23.1995 15:21

PAGE 19 of 124

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
834.	5	44					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00008	HL
835.	5	45					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00008	HL
836.	5	46					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00008	HL
837.							TEHTEC	G1931	rpri	A610MULC	SG10CCAL00001	CL
838.	5	47					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00008	HL
839.	5	48					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00008	HL
840.	5	49					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00008	HL
841.	5	50					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00008	HL
842.	5	51					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00008	HL
843.							TEHTEC	G1931	rpri	A610MULC	SG10CCAL00003	CL
844.	5	52					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00008	HL
845.	5	53					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00008	HL
846.	5	54					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00008	HL
847.	5	55					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00008	HL
848.	5	56					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00008	HL
849.							TEHTEC	T9924	rpri	A610MULC	SG10CCAL00017	CL
850.	5	57					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00046	HL
851.	5	58					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00046	HL
852.	5	59					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00046	HL
853.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00010	CL
854.	5	60					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00046	HL
855.	5	61					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00046	HL
856.	5	62					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00046	HL
857.	5	63					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00046	HL
858.	5	64					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00046	HL
859.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00010	CL
860.	5	65					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00046	HL
861.	5	66					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00046	HL
862.	5	67					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00046	HL
863.	5	68					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00046	HL
864.	5	69					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00046	HL
865.							TEHTEC	F3453	reso	A610MULC	SG10CCAL00010	CL
866.	5	70					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00046	HL
867.	5	71					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00046	HL
868.	5	72					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00046	HL
869.	5	73					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00046	HL
870.	5	74					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00046	HL
871.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00010	CL
872.	5	75					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00046	HL
873.	5	76					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00046	HL
874.	5	77					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00024	HL
875.	5	78					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00024	HL
876.	5	79					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00024	HL
877.							TEHTEC	F2217	rpri	A610MULC	SG10CCAL00007	CL
878.	5	80					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00024	HL
879.	5	81					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00024	HL
880.	5	82					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00024	HL
881.	5	83					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00024	HL
882.	5	84					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00024	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: A
 DATABASE: Harris_SGA_1995

Sep. 23.1995 15:21

PAGE 20 of 124

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
883.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00007	CL
884.	5	85						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00024	HL
885.	5	86						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00024	HL
886.	5	87						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00024	HL
887.	5	88						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00024	HL
888.	5	89						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00024	HL
889.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00007	CL
890.	5	90						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00024	HL
891.	5	91						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00024	HL
892.	5	92						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00024	HL
893.	5	93						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00024	HL
894.	5	94						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00009	HL
895.								TEHTEC	G1931	rpri	A610MULC	SG10CCAL00004	CL
896.	5	95						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00011	HL
897.	5	96						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00009	HL
898.	5	97	0.42	101	PIT	1	TSH -1.69	TSHTSH	04825	reso	B620MRPC3C	SG11HCAL00011	HL
899.	5	98						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00009	HL
900.	5	99						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00011	HL
901.								TEHTEC	G1931	rpri	A610MULC	SG10CCAL00004	CL
902.	5	100						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00009	HL
903.	5	101						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00011	HL
904.	5	102						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00009	HL
905.	5	103						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00011	HL
906.	5	104						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00009	HL
907.								TEHTEC	G1931	rpri	A610MULC	SG10CCAL00004	CL
908.	5	105						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00011	HL
909.	5	106						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00009	HL
910.	5	107						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00011	HL
911.	5	108						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00009	HL
912.	5	109						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00011	HL
913.								TEHTEC	G1931	rpri	A610MULC	SG10CCAL00005	CL
914.	5	110						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00009	HL
915.	5	111						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00011	HL
916.	5	112						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00012	HL
917.	5	113						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00013	HL
918.	5	114						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00012	HL
919.								TEHTEC	G1931	rpri	A610MULC	SG10CCAL00005	CL
920.	6	1						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00060	HL
921.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00015	CL
922.	6	2						TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00061	HL
923.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00015	CL
924.	6	3						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00060	HL
925.	6	4						TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00061	HL
926.	6	5						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00060	HL
927.	6	6						TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00061	HL
928.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00015	CL
929.	6	7						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00060	HL
930.	6	8						TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00061	HL
931.	6	9						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00060	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: A
 DATABASE: Harris_SGA_1995

Sep. 23,1995 15:21

PAGE 21 of 124

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
932.	6	10						TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00061	HL
933.	6	11						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00060	HL
934.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00015	CL
935.	6	12						TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00061	HL
936.	6	13						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00060	HL
937.	6	14						TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00061	HL
938.	6	15						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00060	HL
939.	6	16						TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00061	HL
940.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00015	CL
941.	6	17						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00060	HL
942.	6	18						TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00061	HL
943.	6	19						TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00061	HL
944.	6	20						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00053	HL
945.	6	21						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00053	HL
946.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
947.	6	22						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00053	HL
948.	6	23						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00053	HL
949.	6	24						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00053	HL
950.	6	25						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00053	HL
951.	6	26						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00053	HL
52.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
53.	6	27						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00055	HL
954.	6	28						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00055	HL
955.	6	29						TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00057	HL
956.	6	30						TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00057	HL
957.	6	31						TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00057	HL
958.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
959.	6	32						TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00057	HL
960.	6	33						TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00057	HL
961.	6	34						TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00057	HL
962.	6	35						TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00057	HL
963.	6	36						TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00057	HL
964.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
965.	6	37						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00007	HL
966.	6	38						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00007	HL
967.	6	39			RBD				85534	rpri	B620MRPC3C	SG11HCAL00007	HL
968.								TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00033	HL
969.	6	40						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00007	HL
970.	6	41						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00007	HL
971.								TEHTEC	G1931	rpri	A610MULC	SG10CCAL00001	CL
972.	6	42						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00007	HL
973.	6	43						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00007	HL
974.	6	44						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00007	HL
975.	6	45						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00007	HL
976.	6	46						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00007	HL
977.								TEHTEC	G1931	rpri	A610MULC	SG10CCAL00001	CL
978.	6	47						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00007	HL
979.	6	48						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00007	HL
980.	6	49						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00007	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: A
 DATABASE: Harris_SGA_1995

Sep. 23.1995 15:21

PAGE 22 of 124

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG	
981.	6	50						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00007	HL	
982.	6	51						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00007	HL	
983.								TEHTEC	G1931	rpri	A610MULC	SG10CCAL00003	CL	
984.	6	52						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00007	HL	
985.	6	53						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00007	HL	
986.	6	54						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00007	HL	
987.	6	55						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00007	HL	
988.	6	56						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00007	HL	
989.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00017	CL	
990.	6	57						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00045	HL	
991.	6	58						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00045	HL	
992.			7.15	153	MEM	1	01C	2.58	TEHTEC	F3453	reso	A610MULC	SG10CCAL00010	CL
993.	6	59						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00045	HL	
994.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00010	CL	
995.	6	60						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00045	HL	
996.	6	61						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00045	HL	
997.	6	62						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00045	HL	
998.	6	63						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00045	HL	
999.	6	64						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00045	HL	
1000.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00010	CL	
01.	6	65						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00045	HL	
02.	6	66						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00045	HL	
03.	6	67						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00045	HL	
1004.	6	68						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00045	HL	
1005.	6	69						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00045	HL	
1006.								TEHTEC	F3453	reso	A610MULC	SG10CCAL00010	CL	
1007.	6	70						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00045	HL	
1008.	6	71						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00045	HL	
1009.	6	72						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00045	HL	
1010.	6	73						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00045	HL	
1011.	6	74						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00045	HL	
1012.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00010	CL	
1013.	6	75						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00045	HL	
1014.	6	76						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00045	HL	
1015.	6	77						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00023	HL	
1016.	6	78						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00023	HL	
1017.	6	79						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00023	HL	
1018.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00007	CL	
1019.	6	80						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00023	HL	
1020.	6	81						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00023	HL	
1021.	6	82						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00023	HL	
1022.	6	83						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00023	HL	
1023.	6	84						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00023	HL	
1024.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00007	CL	
1025.	6	85						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00023	HL	
1026.	6	86						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00023	HL	
1027.	6	87						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00023	HL	
1028.	6	88						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00023	HL	
1029.	6	89						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00023	HL	

*** INSPECTION FINAL REPORT LISTING ***

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: A
 DATABASE: Harris_SGA_1995

Sep. 23.1995 15:21

PAGE 23 of 124

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
1030.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00007	CL
1031.	6	90						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00023	HL
1032.	6	91						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00023	HL
1033.	6	92						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00023	HL
1034.	6	93						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00023	HL
1035.	6	95						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00011	HL
1036.	6	96						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00009	HL
1037.	6	97						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00011	HL
1038.	6	98						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00009	HL
1039.	6	99						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00011	HL
1040.								TEHTEC	G1931	rpri	A610MULC	SG10CCAL00004	CL
1041.	6	100						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00009	HL
1042.	6	101						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00011	HL
1043.	6	102						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00009	HL
1044.	6	103						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00011	HL
1045.	6	104						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00009	HL
1046.								TEHTEC	G1931	rpri	A610MULC	SG10CCAL00004	CL
1047.	6	105						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00011	HL
1048.	6	106						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00009	HL
1049.	6	107						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00011	HL
1050.	6	108						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00009	HL
1051.	6	109						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00011	HL
1052.			5.40	184	DNT	1	10H 23.75	TEHTEC	G1931	rpri	A610MULC	SG10CCAL00005	CL
1053.			7.13	184	DNT	1	10C 20.71	TEHTEC	G1931	rpri	A610MULC	SG10CCAL00005	CL
1054.	6	110						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00009	HL
1055.	6	111						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00011	HL
1056.	6	112						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00012	HL
1057.	6	114						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00012	HL
1058.								TEHTEC	G1931	rpri	A610MULC	SG10CCAL00005	CL
1059.	7	2						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00060	HL
1060.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00015	CL
1061.	7	3						TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00061	HL
1062.	7	4						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00060	HL
1063.	7	5						TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00061	HL
1064.	7	6						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00060	HL
1065.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00015	CL
1066.	7	7						TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00061	HL
1067.	7	8						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00060	HL
1068.	7	9						TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00061	HL
1069.	7	10						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00060	HL
1070.	7	11						TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00061	HL
1071.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00015	CL
1072.	7	12						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00060	HL
1073.	7	13						TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00061	HL
1074.	7	14						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00060	HL
1075.	7	15						TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00061	HL
1076.	7	16						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00060	HL
1077.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00015	CL
1078.	7	17						TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00061	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: A
 DATABASE: Harris_SGA_1995

Sep. 23, 1995 15:21

PAGE 24 of 124

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
1079.	7	18					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00060	HL
1080.	7	19					TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00061	HL
1081.	7	20					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00054	HL
1082.	7	21					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00054	HL
1083.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
1084.	7	22					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00054	HL
1085.	7	23					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00054	HL
1086.	7	24					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00054	HL
1087.	7	25					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00054	HL
1088.	7	26					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00054	HL
1089.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
1090.	7	27					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00056	HL
1091.	7	28					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00056	HL
1092.	7	29					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00056	HL
1093.	7	30					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00056	HL
1094.	7	31					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00056	HL
1095.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
1096.	7	32					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00056	HL
1097.	7	33					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00056	HL
1098.	7	34					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00056	HL
99.	7	35					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00056	HL
101.	7	36					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00056	HL
101.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
1102.	7	37					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00008	HL
1103.	7	38					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00008	HL
1104.	7	39					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00008	HL
1105.	7	40					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00008	HL
1106.	7	41					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00008	HL
1107.							TEHTEC	G1931	rpri	A610MULC	SG10CCAL00001	CL
1108.	7	42					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00008	HL
1109.	7	43					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00008	HL
1110.	7	44					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00008	HL
1111.	7	45					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00008	HL
1112.	7	46					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00008	HL
1113.							TEHTEC	G1931	rpri	A610MULC	SG10CCAL00001	CL
1114.	7	47					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00008	HL
1115.	7	48					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00008	HL
1116.	7	49					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00008	HL
1117.	7	50					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00008	HL
1118.	7	51					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00008	HL
1119.							TEHTEC	G1931	rpri	A610MULC	SG10CCAL00003	CL
1120.	7	52					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00008	HL
1121.	7	53					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00008	HL
1122.	7	54					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00008	HL
1123.	7	55					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00008	HL
1124.	7	56					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00008	HL
1125.							TEHTEC	G1931	rpri	A610MULC	SG10CCAL00003	CL
1126.	7	57					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00046	HL
1127.	7	58					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00046	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: A
 DATABASE: Harris_SGA_1995

Sep. 23.1995 15:21

PAGE 25 of 124

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
1128.	7	59					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00046	HL
1129.							TEHTEC	S7675	rpri	A610MJLC	SG10CCAL00010	CL
1130.	7	60					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00046	HL
1131.	7	61					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00046	HL
1132.	7	62					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00046	HL
1133.	7	63					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00046	HL
1134.	7	64					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00046	HL
1135.							TEHTEC	F3453	reso	A610MJLC	SG10CCAL00010	CL
1136.	7	65					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00046	HL
1137.	7	66					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00046	HL
1138.	7	67					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00046	HL
1139.	7	68					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00046	HL
1140.	7	69					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00046	HL
1141.							TEHTEC	F3453	reso	A610MJLC	SG10CCAL00010	CL
1142.	7	70					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00046	HL
1143.	7	71					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00046	HL
1144.	7	72					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00046	HL
1145.	7	73					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00046	HL
1146.	7	74					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00046	HL
1147.							TEHTEC	F3453	reso	A610MJLC	SG10CCAL00010	CL
1148.	7	75					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00046	HL
1149.	7	76					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00046	HL
1150.	7	77					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00024	HL
1151.	7	78					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00024	HL
1152.	7	79					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00024	HL
1153.							TEHTEC	F2217	rpri	A610MJLC	SG10CCAL00007	CL
1154.	7	80					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00024	HL
1155.	7	81					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00024	HL
1156.	7	82					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00024	HL
1157.	7	83					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00024	HL
1158.	7	84					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00024	HL
1159.							TEHTEC	F2217	rpri	A610MJLC	SG10CCAL00007	CL
1160.	7	85					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00024	HL
1161.	7	86					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00024	HL
1162.	7	87					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00024	HL
1163.	7	88					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00024	HL
1164.	7	89					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00024	HL
1165.							TEHTEC	F2217	rpri	A610MJLC	SG10CCAL00007	CL
1166.	7	90					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00024	HL
1167.	7	91					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00024	HL
1168.	7	92					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00024	HL
1169.	7	93					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00024	HL
1170.	7	94					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00009	HL
1171.							TEHTEC	G1931	rpri	A610MJLC	SG10CCAL00004	CL
1172.	7	95					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00011	HL
1173.	7	96					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00009	HL
1174.	7	97					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00011	HL
1175.	7	98					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00009	HL
1176.	7	99					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00011	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: A
 DATABASE: Harris_SGA_1995

Sep. 23.1995 15:21

PAGE 26 of 124

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
1177.								TEHTEC	G1931	rpri	A610MULC	SG10CCAL00004	CL
1178.	7	100						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00009	HL
1179.	7	101						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00011	HL
1180.	7	102						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00009	HL
1181.	7	103						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00011	HL
1182.	7	104						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00009	HL
1183.								TEHTEC	G1931	rpri	A610MULC	SG10CCAL00004	CL
1184.	7	105						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00011	HL
1185.	7	106						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00009	HL
1186.	7	107						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00011	HL
1187.	7	108						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00009	HL
1188.	7	109						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00011	HL
1189.								TEHTEC	G1931	rpri	A610MULC	SG10CCAL00005	CL
1190.	7	110						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00009	HL
1191.	7	111	0.51	58	PIT	1	TSH -2.40	TSHTSH	D4825	reso	B620MRPC3C	SG11HCAL00011	HL
1192.	7	112						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00012	HL
1193.	7	113						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00013	HL
1194.								TEHTEC	G1931	rpri	A610MULC	SG10CCAL00005	CL
1195.	8	2						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00060	HL
1196.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00015	CL
1197.	8	3						TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00061	HL
1198.	8	4						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00060	HL
1199.	8	5						TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00061	HL
1200.	8	6						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00060	HL
1201.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00015	CL
1202.	8	7						TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00061	HL
1203.	8	8						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00060	HL
1204.	8	9						TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00061	HL
1205.	8	10						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00060	HL
1206.	8	11						TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00061	HL
1207.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00015	CL
1208.	8	12						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00060	HL
1209.	8	13						TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00061	HL
1210.	8	14						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00060	HL
1211.	8	15						TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00061	HL
1212.	8	16						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00060	HL
1213.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00015	CL
1214.	8	17						TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00061	HL
1215.	8	18						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00060	HL
1216.	8	19						TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00061	HL
1217.	8	20						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00053	HL
1218.	8	21						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00053	HL
1219.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
1220.	8	22						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00053	HL
1221.	8	23						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00053	HL
1222.	8	24						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00053	HL
1223.	8	25						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00053	HL
1224.	8	26						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00053	HL
1225.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: A
 DATABASE: Harris_SGA_1995

Sep. 23.1995 15:21

PAGE 27 of 124

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
1226.	8	27					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00055	HL
1227.	8	28					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00055	HL
1228.	8	29					TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00057	HL
1229.	8	30					TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00057	HL
1230.	8	31					TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00057	HL
1231.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
1232.	8	32					TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00057	HL
1233.	8	33					TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00057	HL
1234.	8	34					TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00057	HL
1235.	8	35					TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00057	HL
1236.	8	36					TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00057	HL
1237.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
1238.	8	37					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00007	HL
1239.	8	38					TSHTSH	H3464	rsec	B620MRPC3C	SG11HCAL00007	HL
1240.	8	39					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00007	HL
1241.	8	40					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00007	HL
1242.	8	41					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00007	HL
1243.							TEHTEC	G1931	rpri	A610MULC	SG10CCAL00001	CL
1244.	8	42					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00007	HL
1245.	8	43					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00007	HL
46.	8	44					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00007	HL
47.	8	45					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00007	HL
1248.	8	46					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00007	HL
1249.							TEHTEC	G1931	rpri	A610MULC	SG10CCAL00001	CL
1250.	8	47					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00007	HL
1251.	8	48					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00007	HL
1252.	8	49					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00007	HL
1253.	8	50					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00007	HL
1254.	8	51					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00007	HL
1255.							TEHTEC	G1931	rpri	A610MULC	SG10CCAL00003	CL
1256.	8	52					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00007	HL
1257.	8	53					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00007	HL
1258.	8	54					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00007	HL
1259.	8	55					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00007	HL
1260.	8	56					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00007	HL
1261.							TEHTEC	G1931	rpri	A610MULC	SG10CCAL00003	CL
1262.	8	57					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00045	HL
1263.	8	58					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00045	HL
1264.	8	59					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00045	HL
1265.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00010	CL
1266.	8	60					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00045	HL
1267.	8	61					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00045	HL
1268.	8	62					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00045	HL
1269.	8	63					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00045	HL
1270.	8	64					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00045	HL
1271.							TEHTEC	F3453	reso	A610MULC	SG10CCAL00010	CL
1272.	8	65					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00045	HL
1273.	8	66					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00045	HL
1274.	8	67					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00045	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: A
 DATABASE: Harris_SGA_1995

Sep. 23.1995 15:21

PAGE 28 of 124

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
1275.	8	68						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00045	HL
1276.	8	69						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00045	HL
1277.								TEHTEC	F3453	reso	A610MULC	SG10CCAL00010	CL
1278.	8	70						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00045	HL
1279.	8	71						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00045	HL
1280.	8	72						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00045	HL
1281.	8	73						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00045	HL
1282.	8	74						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00045	HL
1283.								TEHTEC	F3453	reso	A610MULC	SG10CCAL00010	CL
1284.	8	75						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00045	HL
1285.	8	76						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00045	HL
1286.	8	77						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00023	HL
1287.	8	78						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00023	HL
1288.	8	79						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00023	HL
1289.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00007	CL
1290.	8	80						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00023	HL
1291.	8	81						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00023	HL
1292.	8	82						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00023	HL
1293.	8	83						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00023	HL
1294.	8	84						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00023	HL
95.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00007	CL
1295.	8	85						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00023	HL
1297.	8	86						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00023	HL
1298.	8	87						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00023	HL
1299.	8	88						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00023	HL
1300.		15.72	157	9	1	01C	3.14	TEHTEC	D4825	reso	A610MULC	SG10CCAL00007	CL
1301.	8	89						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00023	HL
1302.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00007	CL
1303.	8	90						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00023	HL
1304.	8	91						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00023	HL
1305.	8	92						TSHTSH	K6733	rsec	B620MRPC3C	SG11HCAL00023	HL
1306.	8	93						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00023	HL
1307.	8	94						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00009	HL
1308.								TEHTEC	G1931	rpri	A610MULC	SG10CCAL00004	CL
1309.	8	95						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00011	HL
1310.	8	96						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00009	HL
1311.	8	97						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00011	HL
1312.	8	98						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00009	HL
1313.	8	99						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00011	HL
1314.								TEHTEC	G1931	rpri	A610MULC	SG10CCAL00004	CL
1315.	8	100						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00009	HL
1316.	8	101						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00011	HL
1317.	8	102						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00009	HL
1318.	8	103						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00011	HL
1319.	8	104						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00009	HL
1320.								TEHTEC	G1931	rpri	A610MULC	SG10CCAL00004	CL
1321.	8	105						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00011	HL
1322.	8	106						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00009	HL
1323.	8	107						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00011	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: A
 DATABASE: Harris_SGA_1995

Sep. 23.1995 15:21

PAGE 29 of 124

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
1324.	8	108						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00009	HL
1325.	8	109						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00011	HL
1326.								TEHTEC	G1931	rpri	A610MULC	SG10CCAL00005	CL
1327.	8	110						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00012	HL
1328.	8	111						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00013	HL
1329.	8	112						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00012	HL
1330.	8	113						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00013	HL
1331.								TEHTEC	G1931	rpri	A610MULC	SG10CCAL00005	CL
1332.	9	2						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00060	HL
1333.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00015	CL
1334.	9	3						TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00061	HL
1335.	9	4						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00060	HL
1336.	9	5						TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00061	HL
1337.	9	6						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00060	HL
1338.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00015	CL
1339.	9	7						TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00061	HL
1340.	9	8						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00060	HL
1341.	9	9						TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00061	HL
1342.	9	10						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00060	HL
1343.	9	11						TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00061	HL
44.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00015	CL
5.	9	12						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00060	HL
46.	9	13						TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00061	HL
1347.	9	14						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00060	HL
1348.	9	15						TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00061	HL
1349.	9	16						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00060	HL
1350.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00015	CL
1351.	9	17						TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00061	HL
1352.	9	18						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00060	HL
1353.	9	19						TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00061	HL
1354.	9	20						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00054	HL
1355.	9	21						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00054	HL
1356.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
1357.	9	22						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00054	HL
1358.	9	23						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00054	HL
1359.	9	24						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00054	HL
1360.	9	25						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00054	HL
1361.	9	26						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00054	HL
1362.								TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00056	HL
1363.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
1364.	9	27						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00056	HL
1365.	9	30						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00056	HL
1366.	9	31						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00056	HL
1367.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
1368.	9	32						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00056	HL
1369.	9	33						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00056	HL
70.	9	34						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00056	HL
1.	9	35						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00056	HL
1372.	9	36						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00056	HL

*** INSPECTION FINAL REPORT LISTING ***

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: A
 DATABASE: Harris_SGA_1995

Sep. 23.1995 15:21

PAGE 30 of 124

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
1373.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
1374.	9	37						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00008	HL
1375.	9	38						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00008	HL
1376.	9	39						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00008	HL
1377.	9	40						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00008	HL
1378.	9	41						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00008	HL
1379.								TEHTEC	G1931	rpri	A610MULC	SG10CCAL00001	CL
1380.	9	42						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00008	HL
1381.	9	43						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00008	HL
1382.	9	44						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00008	HL
1383.	9	45						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00008	HL
1384.	9	46						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00008	HL
1385.								TEHTEC	G1931	rpri	A610MULC	SG10CCAL00001	CL
1386.	9	47						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00008	HL
1387.	9	48						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00008	HL
1388.	9	49						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00008	HL
1389.	9	50						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00008	HL
1390.	9	51						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00008	HL
1391.								TEHTEC	G1931	rpri	A610MULC	SG10CCAL00003	CL
1392.	9	52						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00008	HL
93.	9	53						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00008	HL
.	9	54						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00008	HL
1395.	9	55						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00008	HL
1396.	9	56						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00008	HL
1397.					RBD			G1931	rpri	A610MULC	SG10CCAL00003	CL	
1398.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00016	CL
1399.	9	59						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00046	HL
1400.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00010	CL
1401.	9	60						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00046	HL
1402.	9	61						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00046	HL
1403.	9	62						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00046	HL
1404.	9	63						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00046	HL
1405.	9	64						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00046	HL
1406.								TEHTEC	F3453	reso	A610MULC	SG10CCAL00010	CL
1407.	9	65						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00046	HL
1408.	9	66						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00046	HL
1409.	9	67						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00046	HL
1410.	9	68						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00046	HL
1411.	9	69						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00046	HL
1412.								TEHTEC	F3453	reso	A610MULC	SG10CCAL00010	CL
1413.	9	70						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00046	HL
1414.	9	71						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00046	HL
1415.	9	72						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00046	HL
1416.	9	73						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00046	HL
1417.	9	74						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00046	HL
1418.								TEHTEC	F3453	reso	A610MULC	SG10CCAL00010	CL
1419.	9	75						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00046	HL
1420.	9	76						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00046	HL
1421.	9	77						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00024	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: A
 DATABASE: Harris_SGA_1995

Sep. 23.1995 15:21

PAGE 31 of 124

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
1422.	9	78					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00024	HL
1423.	9	79					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00024	HL
1424.							TEHTEC	F2217	rpri	A610MULC	SG10CCAL00007	CL
1425.	9	80					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00024	HL
1426.	9	81					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00024	HL
1427.	9	82					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00024	HL
1428.	9	83					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00024	HL
1429.	9	84					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00024	HL
1430.							TEHTEC	F2217	rpri	A610MULC	SG10CCAL00007	CL
1431.	9	85					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00024	HL
1432.	9	88					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00024	HL
1433.	9	89					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00024	HL
1434.							TEHTEC	F2217	rpri	A610MULC	SG10CCAL00007	CL
1435.	9	90					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00024	HL
1436.	9	91					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00024	HL
1437.	9	92					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00024	HL
1438.	9	93					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00024	HL
1439.	9	94					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00009	HL
1440.							TEHTEC	G1931	rpri	A610MULC	SG10CCAL00004	CL
1441.	9	95					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00011	HL
1442.	9	96					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00009	HL
1443.	9	97					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00011	HL
1444.	9	98					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00009	HL
1445.	9	99					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00011	HL
1446.							TEHTEC	G1931	rpri	A610MULC	SG10CCAL00004	CL
1447.	9	100					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00009	HL
1448.	9	101					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00011	HL
1449.	9	102					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00009	HL
1450.	9	103					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00011	HL
1451.	9	104					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00009	HL
1452.							TEHTEC	G1931	rpri	A610MULC	SG10CCAL00004	CL
1453.	9	105					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00011	HL
1454.	9	106					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00009	HL
1455.	9	107					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00011	HL
1456.	9	108					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00009	HL
1457.	9	109					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00011	HL
1458.							TEHTEC	G1931	rpri	A610MULC	SG10CCAL00005	CL
1459.	9	110					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00012	HL
1460.	9	111					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00013	HL
1461.	9	113					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00013	HL
1462.							TEHTEC	G1931	rpri	A610MULC	SG10CCAL00005	CL
1463.	10	2					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00060	HL
1464.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00015	CL
1465.	10	3					TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00061	HL
1466.	10	4					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00060	HL
1467.	10	5					TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00061	HL
1468.	10	6					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00060	HL
1469.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00015	CL
1470.	10	7					TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00061	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: A
 DATABASE: Harris_SGA_1995

Sep. 23.1995 15:21

PAGE 32 of 124

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
1471.	10	8					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00060	HL
1472.	10	9					TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00061	HL
1473.	10	10					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00060	HL
1474.	10	11					TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00061	HL
1475.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00015	CL
1476.	10	12					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00060	HL
1477.	10	13					TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00061	HL
1478.	10	14					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00060	HL
1479.	10	15					TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00061	HL
1480.	10	16					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00060	HL
1481.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00015	CL
1482.	10	17					TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00061	HL
1483.	10	18					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00060	HL
1484.	10	19					TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00061	HL
1485.	10	20					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00053	HL
1486.	10	21					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00053	HL
1487.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
1488.	10	22					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00053	HL
1489.	10	23					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00053	HL
1490.	10	24					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00053	HL
91.	10	25					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00053	HL
2.	10	26					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00053	HL
1493.							TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00055	HL
1494.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
1495.	10	27					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00055	HL
1496.	10	30					TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00057	HL
1497.	10	31					TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00057	HL
1498.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
1499.	10	32					TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00057	HL
1500.	10	33					TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00057	HL
1501.	10	34					TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00057	HL
1502.	10	35					TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00057	HL
1503.	10	36					TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00057	HL
1504.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
1505.	10	37					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00007	HL
1506.	10	38					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00007	HL
1507.	10	39					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00007	HL
1508.	10	40					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00007	HL
1509.	10	41					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00007	HL
1510.							TEHTEC	F7460	rsec	A610MULC	SG10CCAL00001	CL
1511.	10	42					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00007	HL
1512.	10	43					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00007	HL
1513.	10	44					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00007	HL
1514.	10	45					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00007	HL
1515.	10	46					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00007	HL
16.							TEHTEC	F7460	rsec	A610MULC	SG10CCAL00001	CL
7.	10	47					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00007	HL
8.	10	48					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00007	HL
1519.	10	49					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00007	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: A
 DATABASE: Harris_SGA_1995

Sep. 23.1995 15:21

PAGE 33 of 124

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
1520.	10	50						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00007	HL
1521.	10	51						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00007	HL
1522.								TEHTEC	G1931	rpri	A610MULC	SG10CCAL00003	CL
1523.	10	52						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00007	HL
1524.	10	53						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00007	HL
1525.	10	54						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00007	HL
1526.	10	55						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00007	HL
1527.	10	56						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00007	HL
1528.								TEHTEC	G1931	rpri	A610MULC	SG10CCAL00003	CL
1529.	10	59						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00045	HL
1530.								TEHTEC	M9082	rsec	A610MULC	SG10CCAL00010	CL
1531.	10	60						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00045	HL
1532.	10	61						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00045	HL
1533.	10	62						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00045	HL
1534.	10	63						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00045	HL
1535.	10	64						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00045	HL
1536.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00010	CL
1537.	10	65						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00045	HL
1538.	10	66						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00045	HL
1539.	10	67						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00045	HL
40.	10	68						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00045	HL
1.	10	69						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00045	HL
1542.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00010	CL
1543.	10	70						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00045	HL
1544.	10	71						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00045	HL
1545.	10	72						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00045	HL
1546.	10	73						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00045	HL
1547.	10	74						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00045	HL
1548.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00010	CL
1549.	10	75						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00045	HL
1550.	10	76						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00045	HL
1551.	10	77						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00023	HL
1552.	10	78						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00023	HL
1553.	10	79						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00023	HL
1554.		3.01	124	NQI	P1	TEC	13.29	TEHTEC	04825	reso	A610MULC	SG10CCAL00007	CL
1555.		4.64	163	NQI	P1	TEC	13.29	TEHTEC	S7675	rpri	A610MULC	SG10CCAL00017	CL
1556.				DMR	1	TEC	13.29	TECTSC	03858	reso	B620MRPC3C	SG10CCAL00023	CL
1557.	10	80						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00023	HL
1558.	10	81						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00023	HL
1559.	10	82						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00023	HL
1560.	10	83						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00023	HL
1561.	10	84						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00023	HL
1562.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00007	CL
1563.	10	85						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00023	HL
1564.	10	88						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00023	HL
1565.	10	89						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00023	HL
1566.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00007	CL
1567.	10	90						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00023	HL
1568.	10	91						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00023	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: A
 DATABASE: Harris_SGA_1995

Sep. 23.1995 15:21

PAGE 34 of 124

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
1569.	10	92						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00023	HL
1570.	10	93						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00023	HL
1571.	10	94						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00009	HL
1572.								TEHTEC	G1931	rpri	A610MULC	SG10CCAL00004	CL
1573.	10	95						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00011	HL
1574.	10	96						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00009	HL
1575.	10	97						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00011	HL
1576.	10	98						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00009	HL
1577.	10	99						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00011	HL
1578.								TEHTEC	G1931	rpri	A610MULC	SG10CCAL00004	CL
1579.	10	100						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00009	HL
1580.	10	101						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00011	HL
1581.	10	102						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00009	HL
1582.	10	103						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00011	HL
1583.	10	104						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00009	HL
1584.								TEHTEC	G1931	rpri	A610MULC	SG10CCAL00004	CL
1585.	10	105						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00011	HL
1586.	10	106						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00009	HL
1587.	10	107						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00011	HL
1588.	10	108						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00009	HL
89.	10	109						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00011	HL
90.								TEHTEC	G1931	rpri	A610MULC	SG10CCAL00005	CL
91.	10	110						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00012	HL
1592.	10	111						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00013	HL
1593.	10	112						TSHTSH	H3464	rsec	B620MRPC3C	SG11HCAL00012	HL
1594.	11	2						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00056	HL
1595.			5.42	182	DNT	P1	11C -0.30	TEHTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
1596.	11	3						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00056	HL
1597.	11	4						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00056	HL
1598.	11	5						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00056	HL
1599.	11	6						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00058	HL
1600.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
1601.	11	7						TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00059	HL
1602.	11	8						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00058	HL
1603.	11	9						TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00059	HL
1604.	11	10						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00058	HL
1605.	11	11						TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00059	HL
1606.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
1607.	11	12						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00058	HL
1608.	11	13						TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00059	HL
1609.	11	14						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00058	HL
1610.	11	15						TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00059	HL
1611.	11	16						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00058	HL
1612.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
1613.	11	17						TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00059	HL
1614.	11	18						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00058	HL
1615.	11	19						TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00059	HL
1616.	11	20						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00052	HL
1617.	11	21						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00052	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: A
 DATABASE: Harris_SGA_1995

Sep. 23.1995 15:21

PAGE 35 of 124

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
1618.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
1619.	11	22					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00052	HL
1620.	11	23					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00052	HL
1621.	11	24					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00052	HL
1622.	11	25					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00052	HL
1623.	11	26					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00052	HL
1624.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
1625.	11	27					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00052	HL
1626.	11	28					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00052	HL
1627.	11	29					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00054	HL
1628.	11	30					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00054	HL
1629.	11	31					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00054	HL
1630.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
1631.	11	32					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00054	HL
1632.	11	33					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00054	HL
1633.	11	34					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00054	HL
1634.	11	35					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00054	HL
1635.	11	36					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00054	HL
1636.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
1637.	11	37					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00006	HL
1638.	11	38					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00006	HL
1639.	11	39					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00006	HL
1640.	11	40					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00006	HL
1641.	11	41					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00006	HL
1642.							TEHTEC	G1931	rpri	A610MULC	SG10CCAL00001	CL
1643.	11	42					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00006	HL
1644.	11	43					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00006	HL
1645.	11	44					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00006	HL
1646.	11	45					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00006	HL
1647.	11	46					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00006	HL
1648.							TEHTEC	G1931	rpri	A610MULC	SG10CCAL00001	CL
1649.	11	47					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00006	HL
1650.	11	48					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00006	HL
1651.	11	49					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00006	HL
1652.	11	50					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00006	HL
1653.	11	51					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00006	HL
1654.							TEHTEC	G1931	rpri	A610MULC	SG10CCAL00001	CL
1655.	11	52					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00006	HL
1656.	11	53					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00006	HL
1657.	11	54					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00006	HL
1658.	11	55					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00006	HL
1659.	11	56					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00006	HL
1660.							TEHTEC	G1931	rpri	A610MULC	SG10CCAL00001	CL
1661.	11	57					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
1662.	11	58					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
1663.	11	59					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
1664.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00009	CL
1665.	11	60					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
1666.	11	61					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: A
 DATABASE: Harris_SGA_1995

Sep. 23.1995 15:21

PAGE 36 of 124

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
1667.	11	62					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
1668.	11	63					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
1669.	11	64					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
1670.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00009	CL
1671.	11	65					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
1672.	11	66					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
1673.	11	67					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
1674.	11	68					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
1675.	11	69					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
1676.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00009	CL
1677.	11	70					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
1678.	11	71					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
1679.	11	72					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
1680.	11	73					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
1681.	11	74					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
1682.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00009	CL
1683.	11	75					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
1684.	11	76					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
1685.	11	77					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00021	HL
1686.	11	78					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00021	HL
1687.	11	79					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00021	HL
1688.							TEHTEC	F2217	rpri	A610MULC	SG10CCAL00006	CL
1689.	11	80					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00021	HL
1690.	11	81					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00021	HL
1691.	11	82					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00021	HL
1692.	11	83					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00021	HL
1693.	11	84					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00021	HL
1694.							TEHTEC	F2217	rpri	A610MULC	SG10CCAL00006	CL
1695.	11	85					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00021	HL
1696.	11	86					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00021	HL
1697.	11	87					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00021	HL
1698.	11	88					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00024	HL
1699.	11	89					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00024	HL
1700.							TEHTEC	F2217	rpri	A610MULC	SG10CCAL00006	CL
1701.	11	90					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00024	HL
1702.	11	91					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00024	HL
1703.	11	92					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00024	HL
1704.	11	93					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00024	HL
1705.	11	94					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00012	HL
1706.							TEHTEC	G1931	rpri	A610MULC	SG10CCAL00005	CL
1707.	11	95					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00013	HL
1708.	11	96					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00012	HL
1709.	11	97					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00013	HL
1710.	11	98					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00012	HL
1711.	11	99					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00013	HL
1712.							TEHTEC	G1931	rpri	A610MULC	SG10CCAL00005	CL
1713.	11	100					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00012	HL
1714.	11	101					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00013	HL
1715.	11	102					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00012	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: A
 DATABASE: Harris_SGA_1995

Sep. 23,1995 15:21

PAGE 37 of 124

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
1716.	11	103						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00013	HL
1717.	11	104						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00012	HL
1718.								TEHTEC	G1931	rpri	A610MULC	SG10CCAL00005	CL
1719.	11	105						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00013	HL
1720.	11	106						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00014	HL
1721.	11	107						TSHTSH	J9815	rsec	B620MRPC3C	SG11HCAL00015	HL
1722.	11	108						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00014	HL
1723.	11	109						TSHTSH	J9815	rsec	B620MRPC3C	SG11HCAL00015	HL
1724.								TEHTEC	G1931	rpri	A610MULC	SG10CCAL00005	CL
1725.	11	110						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00014	HL
1726.	11	111						TSHTSH	J9815	rsec	B620MRPC3C	SG11HCAL00015	HL
1727.	11	112						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00014	HL
1728.	11	113						TSHTSH	J9815	rsec	B620MRPC3C	SG11HCAL00015	HL
1729.								TEHTEC	G1931	rpri	A610MULC	SG10CCAL00005	CL
1730.	12	3						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00056	HL
1731.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
1732.	12	4						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00056	HL
1733.	12	5						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00056	HL
1734.	12	6						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00058	HL
1735.								TEHTEC	F3325	rsec	A610MULC	SG10CCAL00014	CL
1736.	12	7						TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00059	HL
1737.	12	8						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00058	HL
1738.	12	9						TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00059	HL
1739.	12	10						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00058	HL
1740.	12	11						TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00059	HL
1741.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
1742.	12	12						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00058	HL
1743.	12	13						TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00059	HL
1744.	12	14						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00058	HL
1745.	12	15						TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00059	HL
1746.	12	16						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00058	HL
1747.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
1748.	12	17						TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00059	HL
1749.	12	18						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00058	HL
1750.	12	19						TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00059	HL
1751.	12	20						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00051	HL
1752.	12	21						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00051	HL
1753.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
1754.	12	22						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00051	HL
1755.	12	23						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00051	HL
1756.	12	24						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00051	HL
1757.	12	25						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00051	HL
1758.	12	26						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00051	HL
1759.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
1760.	12	27						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00051	HL
1761.	12	28						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00051	HL
1762.	12	29						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00053	HL
1763.	12	30						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00053	HL
1764.	12	31						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00053	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: A
 DATABASE: Harris_SGA_1995

Sep. 23.1995 15:21

PAGE 38 of 124

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
1765.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
1766.	12	32					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00053	HL
1767.	12	33					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00053	HL
1768.	12	34					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00053	HL
1769.	12	35					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00053	HL
1770.	12	36					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00053	HL
1771.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
1772.	12	37					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00005	HL
1773.	12	38					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00005	HL
1774.	12	39					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00005	HL
1775.	12	40					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00005	HL
1776.	12	41					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00005	HL
1777.							TEHTEC	G1931	rpri	A610MULC	SG10CCAL00001	CL
1778.	12	42					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00005	HL
1779.	12	43					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00005	HL
1780.	12	44					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00005	HL
1781.	12	45					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00005	HL
1782.	12	46					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00005	HL
1783.							TEHTEC	G1931	rpri	A610MULC	SG10CCAL00001	CL
1784.	12	47					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00005	HL
1785.	12	48					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00005	HL
1786.	12	49					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00005	HL
1787.	12	50					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00005	HL
1788.	12	51					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00005	HL
1789.							TEHTEC	G1931	rpri	A610MULC	SG10CCAL00001	CL
1790.	12	52					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00005	HL
1791.	12	53					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00005	HL
1792.	12	54					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00005	HL
1793.	12	55					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00005	HL
1794.	12	56					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00005	HL
1795.							TEHTEC	G1931	rpri	A610MULC	SG10CCAL00001	CL
1796.	12	57					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
1797.	12	58					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
1798.	12	59					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
1799.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00009	CL
1800.	12	60					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
1801.	12	61					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
1802.	12	62					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
1803.	12	63					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
1804.	12	64					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
1805.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00009	CL
1806.	12	65					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
1807.	12	66					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
1808.	12	67					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
1809.	12	68					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
1810.	12	69					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
1811.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00009	CL
1812.	12	70					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
1813.	12	71					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: A
 DATABASE: Harris_SGA_1995

Sep. 23,1995 15:21

PAGE 39 of 124

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
1814.	12	72					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
1815.	12	73					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
1816.	12	74					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
1817.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00009	CL
1818.	12	75					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
1819.	12	76					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
1820.	12	77					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00020	HL
1821.	12	78					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00020	HL
1822.	12	79					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00020	HL
1823.							TEHTEC	F2217	rpri	A610MULC	SG10CCAL00006	CL
1824.	12	80					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00020	HL
1825.	12	81					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00020	HL
1826.	12	82					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00020	HL
1827.	12	83					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00020	HL
1828.	12	84					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00020	HL
1829.							TEHTEC	F2217	rpri	A610MULC	SG10CCAL00006	CL
1830.	12	85					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00020	HL
1831.	12	86					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00020	HL
1832.	12	87					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00020	HL
1833.	12	88					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00023	HL
1834.	12	89					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00023	HL
							TEHTEC	F2217	rpri	A610MULC	SG10CCAL00006	CL
1835.	12	90					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00023	HL
1837.	12	91					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00023	HL
1838.	12	92					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00023	HL
1839.	12	93					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00023	HL
1840.	12	94					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00012	HL
1841.							TEHTEC	G1931	rpri	A610MULC	SG10CCAL00005	CL
1842.	12	95					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00013	HL
1843.	12	96					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00012	HL
1844.	12	97					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00013	HL
1845.	12	98					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00012	HL
1846.	12	99					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00013	HL
1847.							TEHTEC	G1931	rpri	A610MULC	SG10CCAL00005	CL
1848.	12	100					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00012	HL
1849.	12	101					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00013	HL
1850.	12	102					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00012	HL
1851.	12	103					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00013	HL
1852.	12	104					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00012	HL
1853.							TEHTEC	G1931	rpri	A610MULC	SG10CCAL00005	CL
1854.	12	105					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00013	HL
1855.	12	106					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00014	HL
1856.	12	107					TSHTSH	J9815	rsec	B620MRPC3C	SG11HCAL00015	HL
1857.	12	108					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00014	HL
1858.	12	109					TSHTSH	J9815	rsec	B620MRPC3C	SG11HCAL00015	HL
1859.							TEHTEC	G1931	rpri	A610MULC	SG10CCAL00005	CL
1860.	12	110					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00014	HL
1861.	12	111					TSHTSH	J9815	rsec	B620MRPC3C	SG11HCAL00015	HL
1862.	12	112					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00014	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: A
 DATABASE: Harris_SGA_1995

Sep. 23.1995 15:21

PAGE 40 of 124

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
1863.								TEHTEC	G1931	rpri	A610MULC	SG10CCAL00005	CL
1864.	12	113						TSHTSH	J9815	rsec	B620MRPC3C	SG11HCAL00015	HL
1865.		17.08	181	DNT	P1	09C	0.00	TEHTEC	G1931	rpri	A610MULC	SG10CCAL00005	CL
1866.		64.19	183	DNT	1	09C	2.03	TEHTEC	G1931	rpri	A610MULC	SG10CCAL00005	CL
1867.	13	3						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00056	HL
1868.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
1869.	13	4						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00056	HL
1870.	13	5						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00058	HL
1871.	13	6						TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00059	HL
1872.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
1873.	13	7						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00058	HL
1874.	13	8						TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00059	HL
1875.	13	9						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00058	HL
1876.	13	10						TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00059	HL
1877.	13	11						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00058	HL
1878.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
1879.	13	12						TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00059	HL
1880.	13	13						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00058	HL
1881.	13	14						TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00059	HL
1882.	13	15						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00058	HL
83.	13	16						TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00059	HL
								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
	13	17						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00058	HL
1885.	13	18						TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00059	HL
1886.	13	19						TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00059	HL
1887.	13	20						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00052	HL
1888.	13	21						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00052	HL
1889.	13	21						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00052	HL
1890.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
1891.	13	22						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00052	HL
1892.	13	23						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00052	HL
1893.	13	24						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00052	HL
1894.	13	25						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00052	HL
1895.	13	26						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00052	HL
1896.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
1897.	13	27						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00052	HL
1898.	13	28						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00052	HL
1899.	13	29						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00054	HL
1900.	13	30						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00054	HL
1901.	13	31						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00054	HL
1902.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
1903.	13	32						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00054	HL
1904.	13	33						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00054	HL
1905.	13	34						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00054	HL
1906.	13	35						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00054	HL
1907.	13	36						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00054	HL
1908.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
1909.	13	37						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00006	HL
1910.	13	38						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00006	HL
1911.	13	39						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00006	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: A
 DATABASE: Harris_SGA_1995

Sep. 23.1995 15:21

PAGE 41 of 124

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
1912.	13	40					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00006	HL
1913.	13	41					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00006	HL
1914.							TEHTEC	G1931	rpri	A610MULC	SG10CCAL00001	CL
1915.	13	42					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00006	HL
1916.	13	43					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00006	HL
1917.	13	44					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00006	HL
1918.	13	45					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00006	HL
1919.	13	46					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00006	HL
1920.							TEHTEC	G1931	rpri	A610MULC	SG10CCAL00001	CL
1921.	13	47					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00006	HL
1922.	13	48					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00006	HL
1923.	13	49					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00006	HL
1924.	13	50					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00006	HL
1925.	13	51					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00006	HL
1926.							TEHTEC	G1931	rpri	A610MULC	SG10CCAL00001	CL
1927.	13	52					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00006	HL
1928.	13	53					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00006	HL
1929.	13	54					TSHTSH	F3325	rsec	B620MRPC3C	SG11HCAL00006	HL
1930.	13	55					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00006	HL
1931.	13	56					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00006	HL
32.							TEHTEC	G1931	rpri	A610MULC	SG10CCAL00001	CL
33.	13	57					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
34.	13	58					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
1935.	13	59					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
1936.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00009	CL
1937.	13	60					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
1938.	13	61					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
1939.	13	62					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
1940.	13	63					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
1941.	13	64					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
1942.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00009	CL
1943.	13	65					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
1944.	13	66					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
1945.	13	67					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
1946.	13	68					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
1947.	13	69					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
1948.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00009	CL
1949.	13	70					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
1950.	13	71					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
1951.	13	72					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
1952.	13	73					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
1953.	13	74					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
1954.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00009	CL
1955.	13	75					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
1956.	13	76					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
1957.	13	77					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00021	HL
1958.	13	78					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00021	HL
1959.	13	79					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00021	HL
1960.							TEHTEC	F2217	rpri	A610MULC	SG10CCAL00006	CL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: A
 DATABASE: Harris_SGA_1995

Sep. 23.1995 15:21

PAGE 42 of 124

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
1961.	13	80					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00021	HL
1962.	13	81					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00021	HL
1963.	13	82					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00021	HL
1964.	13	83					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00021	HL
1965.	13	84					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00021	HL
1966.							TEHTEC	F2217	rpri	A610MULC	SG10CCAL00006	CL
1967.	13	85					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00021	HL
1968.	13	86					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00021	HL
1969.	13	87					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00021	HL
1970.	13	88					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00024	HL
1971.	13	89					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00024	HL
1972.							TEHTEC	F2217	rpri	A610MULC	SG10CCAL00006	CL
1973.	13	90					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00024	HL
1974.	13	91					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00024	HL
1975.	13	92					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00024	HL
1976.	13	93					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00024	HL
1977.	13	94					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00012	HL
1978.							TEHTEC	G1931	rpri	A610MULC	SG10CCAL00005	CL
1979.	13	95					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00013	HL
1980.	13	96					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00012	HL
1981.	13	97					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00013	HL
1982.	13	98					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00012	HL
1983.	13	99					TSHTSH	J9815	rsec	B620MRPC3C	SG11HCAL00013	HL
1984.							TEHTEC	G1931	rpri	A610MULC	SG10CCAL00005	CL
1985.	13	100					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00012	HL
1986.	13	101					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00013	HL
1987.	13	102					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00012	HL
1988.	13	103					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00013	HL
1989.	13	104					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00014	HL
1990.							TEHTEC	G1931	rpri	A610MULC	SG10CCAL00005	CL
1991.	13	105					TSHTSH	J9815	rsec	B620MRPC3C	SG11HCAL00015	HL
1992.	13	106					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00014	HL
1993.	13	107					TSHTSH	J9815	rsec	B620MRPC3C	SG11HCAL00015	HL
1994.	13	108					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00014	HL
1995.	13	109					TSHTSH	J9815	rsec	B620MRPC3C	SG11HCAL00015	HL
1996.							TEHTEC	G1931	rpri	A610MULC	SG10CCAL00005	CL
1997.	13	110					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00014	HL
1998.	13	111					TSHTSH	J9815	rsec	B620MRPC3C	SG11HCAL00015	HL
1999.	13	112					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00014	HL
2000.							TEHTEC	G1931	rpri	A610MULC	SG10CCAL00005	CL
2001.	14	3					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00056	HL
2002.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
2003.	14	4					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00056	HL
2004.	14	5					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00058	HL
2005.	14	6					TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00059	HL
2006.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
2007.	14	7					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00058	HL
2008.	14	8					TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00059	HL
2009.	14	9					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00058	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: A
 DATABASE: Harris_SGA_1995

Sep. 23,1995 15:21

PAGE 43 of 124

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG	
2010.	14	10	0.29	91	PLP	11	TSH	1.05	TSHTSH	H3464	rsec	B620MRPC3C	SG11HCAL00059	HL
2011.	14	11							TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00058	HL
2012.									TEHTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
2013.	14	12							TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00059	HL
2014.	14	13							TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00058	HL
2015.	14	14							TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00059	HL
2016.	14	15							TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00058	HL
2017.	14	16							TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00059	HL
2018.									TEHTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
2019.	14	17							TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00058	HL
2020.	14	18							TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00059	HL
2021.	14	19							TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00059	HL
2022.	14	20							TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00051	HL
2023.	14	21							TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00051	HL
2024.									TEHTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
2025.	14	22							TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00051	HL
2026.	14	23							TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00051	HL
2027.	14	24							TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00051	HL
2028.	14	25							TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00051	HL
2029.	14	26							TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00051	HL
30.									TEHTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
31.	14	27							TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00051	HL
2032.	14	28							TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00051	HL
2033.	14	29							TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00053	HL
2034.	14	30							TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00053	HL
2035.	14	31							TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00053	HL
2036.									TEHTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
2037.	14	32							TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00053	HL
2038.	14	33							TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00053	HL
2039.	14	34							TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00053	HL
2040.	14	35							TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00053	HL
2041.	14	36							TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00053	HL
2042.									TEHTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
2043.	14	37							TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00005	HL
2044.	14	38							TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00005	HL
2045.	14	39							TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00005	HL
2046.	14	40							TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00005	HL
2047.	14	41							TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00005	HL
2048.									TEHTEC	G1931	rpri	A610MULC	SG10CCAL00001	CL
2049.	14	42							TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00005	HL
2050.	14	43							TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00005	HL
2051.	14	44							TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00005	HL
2052.	14	45							TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00005	HL
2053.	14	46							TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00005	HL
2054.									TEHTEC	G1931	rpri	A610MULC	SG10CCAL00001	CL
2055.	14	47							TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00005	HL
2056.	14	48							TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00005	HL
2057.	14	49							TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00005	HL
2058.	14	50							TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00005	HL

*** INSPECTION FINAL REPORT LISTING ***

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: A
 DATABASE: Harris_SGA_1995

Sep. 23, 1995 15:21

PAGE 44 of 124

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
2059.	14	51						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00005	HL
2060.								TEHTEC	G1931	rpri	A610MULC	SG10CCAL00001	CL
2061.	14	52						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00005	HL
2062.	14	53						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00005	HL
2063.	14	54						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00005	HL
2064.	14	55						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00005	HL
2065.	14	56						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00033	HL
2066.								TEHTEC	G1931	rpri	A610MULC	SG10CCAL00001	CL
2067.	14	57						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
2068.	14	58						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
2069.	14	59						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
2070.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00009	CL
2071.	14	60						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
2072.	14	61						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
2073.		0.75	171	INR	1	09H	36.98	TEHTEC	M9082	rsec	A610MULC	SG10CCAL00009	CL
2074.	14	62						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
2075.		0.55	148	MBM	1	08H	33.44	TEHTEC	D3858	reso	A610MULC	SG10CCAL00009	CL
2076.		1.24	148	MBM	1	09H	25.88	TEHTEC	D3858	reso	A610MULC	SG10CCAL00009	CL
2077.	14	63						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
2078.	14	64						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
2079.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00009	CL
2080.	14	65						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
2081.	14	66						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
2082.	14	67						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
2083.	14	68						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
2084.	14	69						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
2085.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00009	CL
2086.	14	70						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
2087.	14	71						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
2088.	14	72						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
2089.	14	73						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
2090.	14	74						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
2091.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00009	CL
2092.	14	75						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
2093.	14	76						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
2094.	14	77						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00020	HL
2095.	14	78						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00020	HL
2096.	14	79						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00020	HL
2097.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00006	CL
2098.	14	80						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00020	HL
2099.	14	81						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00020	HL
2100.	14	82						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00020	HL
2101.	14	83						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00020	HL
2102.	14	84						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00020	HL
2103.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00006	CL
2104.	14	85						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00020	HL
2105.	14	86						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00020	HL
2106.	14	87						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00020	HL
2107.	14	88						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00023	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: A
 DATABASE: Harris_SGA_1995

Sep. 23.1995 15:21

PAGE 45 of 124

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG	
2108.	14	89						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00023	HL	
2109.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00006	CL	
2110.	14	90						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00023	HL	
2111.	14	91						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00023	HL	
2112.	14	92						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00023	HL	
2113.	14	93						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00023	HL	
2114.	14	94						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00012	HL	
2115.								TEHTEC	G1931	rpri	A610MULC	SG10CCAL00005	CL	
2116.	14	95						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00013	HL	
2117.	14	96						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00012	HL	
2118.	14	97						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00013	HL	
2119.	14	98						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00012	HL	
2120.	14	99						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00013	HL	
2121.								TEHTEC	G1931	rpri	A610MULC	SG10CCAL00005	CL	
2122.	14	100	4.47	87	PLP	11	TSH	0.17	TSHTSH	C1115	rsec	B620MRPC3C	SG11HCAL00012	HL
2123.	14	101							TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00013	HL
2124.	14	102	5.24	88	PLP	11	TSH	0.19	TSHTSH	C1115	rsec	B620MRPC3C	SG11HCAL00012	HL
2125.	14	103							TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00013	HL
2126.	14	104							TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00014	HL
2127.									TEHTEC	G1931	rpri	A610MULC	SG10CCAL00005	CL
2128.	14	105							TSHTSH	J9815	rsec	B620MRPC3C	SG11HCAL00015	HL
2129.	14	106							TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00014	HL
2130.	14	107							TSHTSH	J9815	rsec	B620MRPC3C	SG11HCAL00015	HL
2131.	14	108							TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00014	HL
2132.	14	109							TSHTSH	J9815	rsec	B620MRPC3C	SG11HCAL00015	HL
2133.									TEHTEC	G1931	rpri	A610MULC	SG10CCAL00005	CL
2134.	14	110							TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00014	HL
2135.	14	111							TSHTSH	J9815	rsec	B620MRPC3C	SG11HCAL00015	HL
2136.	14	112							TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00014	HL
2137.									TEHTEC	G1931	rpri	A610MULC	SG10CCAL00005	CL
2138.	15	4							TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00056	HL
2139.									TEHTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
2140.	15	5							TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00058	HL
2141.	15	6							TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00059	HL
2142.									TEHTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
2143.	15	7							TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00058	HL
2144.	15	8							TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00059	HL
2145.	15	9							TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00058	HL
2146.	15	10	0.14	103	PLP	11	TSH	1.10	TSHTSH	H3464	rsec	B620MRPC3C	SG11HCAL00059	HL
2147.	15	11							TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00058	HL
2148.									TEHTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
2149.	15	12							TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00059	HL
2150.	15	13							TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00058	HL
2151.	15	14							TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00059	HL
2152.	15	15							TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00058	HL
2153.	15	16							TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00059	HL
2154.									TEHTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
2155.	15	17							TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00058	HL
2156.	15	18							TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00059	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: A
 DATABASE: Harris_SGA_1995

Sep. 23.1995 15:21

PAGE 46 of 124

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
2157.	15	19					TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00059	HL
2158.	15	20					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00052	HL
2159.	15	21					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00052	HL
2160.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
2161.	15	22					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00052	HL
2162.	15	23					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00052	HL
2163.	15	24					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00052	HL
2164.	15	25					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00052	HL
2165.	15	26					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00052	HL
2166.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
2167.	15	27					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00052	HL
2168.	15	28					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00052	HL
2169.	15	29					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00054	HL
2170.	15	30					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00054	HL
2171.	15	31					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00054	HL
2172.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
2173.	15	32					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00054	HL
2174.	15	33					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00054	HL
2175.	15	34					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00054	HL
2176.	15	35					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00054	HL
77.	15	36					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00054	HL
78.							TEHTEC	F3325	rsec	A610MULC	SG10CCAL00014	CL
79.	15	37					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00006	HL
2180.	15	38					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00006	HL
2181.	15	39					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00006	HL
2182.	15	40					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00006	HL
2183.	15	41					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00006	HL
2184.							TEHTEC	G1931	rpri	A610MULC	SG10CCAL00001	CL
2185.	15	42					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00006	HL
2186.	15	43					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00006	HL
2187.	15	44					TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00006	HL
2188.	15	45					TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00006	HL
2189.	15	46					TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00006	HL
2190.							TEHTEC	G1931	rpri	A610MULC	SG10CCAL00001	CL
2191.	15	47					TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00006	HL
2192.	15	48					TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00006	HL
2193.	15	49					TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00006	HL
2194.	15	50					TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00006	HL
2195.	15	51					TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00006	HL
2196.							TEHTEC	G1931	rpri	A610MULC	SG10CCAL00001	CL
2197.	15	52					TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00006	HL
2198.	15	53					TSHTSH	F3325	rsec	B620MRPC3C	SG11HCAL00006	HL
2199.	15	54					TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00006	HL
2200.	15	55					TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00006	HL
2201.	15	56					TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00006	HL
2202.							TEHTEC	G1931	rpri	A610MULC	SG10CCAL00001	CL
2203.	15	57					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
2204.	15	58					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
2205.	15	59					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: A
 DATABASE: Harris_SGA_1995

Sep. 23.1995 15:21

PAGE 47 of 124

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
2206.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00009	CL
2207.	15	60					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
2208.	15	61					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
2209.	15	62					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
2210.	15	63					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
2211.	15	64					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
2212.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00009	CL
2213.	15	65					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
2214.	15	66					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
2215.	15	67					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
2216.	15	68					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
2217.	15	69					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
2218.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00009	CL
2219.	15	70					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
2220.	15	71					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
2221.	15	72					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
2222.	15	73					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
2223.	15	74					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
2224.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00009	CL
2225.	15	75					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
26.	15	76					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
	15	77					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00021	HL
	15	78					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00021	HL
2229.	15	79					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00021	HL
2230.							TEHTEC	F2217	rpri	A610MULC	SG10CCAL00006	CL
2231.	15	80					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00021	HL
2232.	15	81					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00021	HL
2233.	15	82					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00021	HL
2234.	15	83					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00021	HL
2235.	15	84					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00021	HL
2236.							TEHTEC	F2217	rpri	A610MULC	SG10CCAL00006	CL
2237.	15	85					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00021	HL
2238.	15	86					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00021	HL
2239.	15	87					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00024	HL
2240.	15	88					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00024	HL
2241.	15	89					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00024	HL
2242.							TEHTEC	F2217	rpri	A610MULC	SG10CCAL00006	CL
2243.	15	90					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00024	HL
2244.	15	91					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00024	HL
2245.	15	92					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00024	HL
2246.	15	93					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00024	HL
2247.	15	94					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00012	HL
2248.							TEHTEC	G1931	rpri	A610MULC	SG10CCAL00005	CL
2249.	15	95					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00013	HL
2250.	15	96					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00012	HL
2251.	15	97					TSHTSH	J9815	rsec	B620MRPC3C	SG11HCAL00013	HL
	15	98					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00012	HL
	15	99					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00013	HL
2254.							TEHTEC	G1931	rpri	A610MULC	SG10CCAL00005	CL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: A
 DATABASE: Harris_SGA_1995

Sep. 23.1995 15:21

PAGE 48 of 124

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
2255.	15	100						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00012	HL
2256.	15	101						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00013	HL
2257.	15	102						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00012	HL
2258.	15	103						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00013	HL
2259.	15	104						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00014	HL
2260.								TEHTEC	G1931	rpri	A610MULC	SG10CCAL00005	CL
2261.	15	105						TSHTSH	J9815	rsec	B620MRPC3C	SG11HCAL00015	HL
2262.	15	106						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00014	HL
2263.	15	107						TSHTSH	J9815	rsec	B620MRPC3C	SG11HCAL00015	HL
2264.	15	108						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00014	HL
2265.	15	109						TSHTSH	J9815	rsec	B620MRPC3C	SG11HCAL00015	HL
2266.								TEHTEC	G1931	rpri	A610MULC	SG10CCAL00005	CL
2267.	15	110						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00014	HL
2268.	15	111						TSHTSH	J9815	rsec	B620MRPC3C	SG11HCAL00015	HL
2269.								TEHTEC	G1931	rpri	A610MULC	SG10CCAL00005	CL
2270.	15	112						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00014	HL
2271.					RES			AVITEC	F3453	reso	A610MULC	SG10CCAL00005	CL
2272.					RES			11CTEC	F3453	reso	A590SFRM	SG10CCAL00018	CL
2273.					RBD			K6733	rsec	B590MRPC3C	SG11HCAL00035	HL	
2274.								10H10H	B5534	rpri	B620MRPC3C	SG11HCAL00036	HL
75.		76.23	173	DNT	P1	10H	0.11	TEHTEC	T9924	rpri	A560SFRM	SG10CCAL00019	CL
76.		53.88	169	DNT	P1	10H	0.97	TEHTEC	T9924	rpri	A560SFRM	SG10CCAL00019	CL
77.		111.80	172	DNT	P1	11H	0.15	TEHTEC	T9924	rpri	A560SFRM	SG10CCAL00019	CL
2278.	16	4						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00056	HL
2279.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
2280.	16	5						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00056	HL
2281.	16	6						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00058	HL
2282.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
2283.	16	7						TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00059	HL
2284.	16	8						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00058	HL
2285.	16	9						TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00059	HL
2286.	16	10						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00058	HL
2287.	16	11						TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00059	HL
2288.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
2289.	16	12						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00058	HL
2290.	16	13						TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00059	HL
2291.	16	14						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00058	HL
2292.	16	15						TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00059	HL
2293.	16	16						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00058	HL
2294.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
2295.	16	17						TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00059	HL
2296.	16	18						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00058	HL
2297.	16	19						TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00059	HL
2298.	16	20						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00051	HL
2299.	16	21						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00051	HL
2300.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
2301.	16	22						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00051	HL
2302.	16	23						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00051	HL
2303.	16	24						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00051	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: A
 DATABASE: Harris_SGA_1995

Sep. 23.1995 15:21

PAGE 49 of 124

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
2304.	16	25						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00051	HL
2305.	16	26						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00051	HL
2306.		7.78	184	ONT	1	01H	2.68	TEHTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
2307.	16	27						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00051	HL
2308.	16	28						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00051	HL
2309.	16	29						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00053	HL
2310.	16	30						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00053	HL
2311.	16	31						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00053	HL
2312.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
2313.	16	32						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00053	HL
2314.	16	33						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00053	HL
2315.	16	34						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00053	HL
2316.	16	35						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00053	HL
2317.	16	36						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00053	HL
2318.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
2319.	16	37						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00005	HL
2320.	16	38						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00005	HL
2321.	16	39						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00005	HL
2322.	16	40						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00005	HL
2323.	16	41						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00005	HL
24.								TEHTEC	G1931	rpri	A610MULC	SG10CCAL00001	CL
2325.	16	42						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00005	HL
2326.	16	43						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00005	HL
2327.	16	44						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00005	HL
2328.	16	45						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00005	HL
2329.	16	46						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00005	HL
2330.		0.44	151	MBM	1	01H	9.70	TEHTEC	F7460	rsec	A610MULC	SG10CCAL00001	CL
2331.	16	47						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00005	HL
2332.	16	48						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00005	HL
2333.	16	49						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00005	HL
2334.	16	50						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00005	HL
2335.	16	51						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00005	HL
2336.								TEHTEC	G1931	rpri	A610MULC	SG10CCAL00001	CL
2337.	16	52						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00005	HL
2338.	16	53						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00005	HL
2339.	16	54						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00005	HL
2340.	16	55						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00005	HL
2341.	16	56						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00005	HL
2342.								TEHTEC	G1931	rpri	A610MULC	SG10CCAL00001	CL
2343.	16	57						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
2344.	16	58						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
2345.	16	59						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
2346.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00009	CL
2347.	16	60						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
2348.	16	61						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
2349.	16	62						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
2350.	16	63						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
2351.	16	64						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
2352.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00009	CL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: A
 DATABASE: Harris_SGA_1995

Sep. 23.1995 15:21

PAGE 50 of 124

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
2353.	16	65						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
2354.	16	66						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
2355.	16	67						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
2356.	16	68						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
2357.	16	69						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
2358.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00009	CL
2359.	16	70						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
2360.	16	71						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
2361.	16	72						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
2362.	16	73						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
2363.	16	74						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
2364.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00009	CL
2365.	16	75						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
2366.	16	76						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
2367.	16	77						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00020	HL
2368.	16	78						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00020	HL
2369.	16	79						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00020	HL
2370.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00006	CL
2371.	16	80						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00020	HL
2372.	16	81						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00020	HL
73.	16	82						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00020	HL
74.	16	83						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00020	HL
75.	16	84						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00020	HL
2376.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00006	CL
2377.	16	85						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00020	HL
2378.	16	86						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00020	HL
2379.	16	87						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00023	HL
2380.	16	88						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00023	HL
2381.	16	89						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00023	HL
2382.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00006	CL
2383.	16	90						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00023	HL
2384.	16	91						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00023	HL
2385.	16	92						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00023	HL
2386.	16	93						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00023	HL
2387.	16	94						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00012	HL
2388.								TEHTEC	G1931	rpri	A610MULC	SG10CCAL00005	CL
2389.	16	95						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00013	HL
2390.	16	96						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00012	HL
2391.	16	97						TSHTSH	J9815	rsec	B620MRPC3C	SG11HCAL00013	HL
2392.	16	98						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00012	HL
2393.	16	99						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00013	HL
2394.								TEHTEC	G1931	rpri	A610MULC	SG10CCAL00005	CL
2395.	16	100						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00012	HL
2396.	16	101						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00013	HL
2397.	16	102						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00012	HL
2398.	16	103						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00013	HL
2399.	16	104						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00014	HL
2400.								TEHTEC	G1931	rpri	A610MULC	SG10CCAL00005	CL
2401.	16	105						TSHTSH	J9815	rsec	B620MRPC3C	SG11HCAL00015	HL

*** INSPECTION FINAL REPORT LISTING ***

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: A
 DATABASE: Harris_SGA_1995

Sep. 23,1995 15:21

PAGE 51 of 124

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
2402.	16	106					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00014	HL
2403.	16	107					TSHTSH	J9815	rsec	B620MRPC3C	SG11HCAL00015	HL
2404.	16	108					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00014	HL
2405.	16	109					TSHTSH	J9815	rsec	B620MRPC3C	SG11HCAL00015	HL
2406.							TEHTEC	G1931	rpri	A610MULC	SG10CCAL00005	CL
2407.	16	110					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00014	HL
2408.	16	111					TSHTSH	J9815	rsec	B620MRPC3C	SG11HCAL00015	HL
2409.							TEHTEC	G1931	rpri	A610MULC	SG10CCAL00005	CL
2410.	17	4					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00056	HL
2411.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
2412.	17	5					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00056	HL
2413.	17	6					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00058	HL
2414.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
2415.	17	7					TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00059	HL
2416.	17	8					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00058	HL
2417.	17	9					TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00059	HL
2418.	17	10					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00058	HL
2419.	17	11					TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00059	HL
2420.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
2421.	17	12					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00058	HL
2422.	17	13					TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00059	HL
2423.	17	14					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00058	HL
2424.	17	15					TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00059	HL
2425.	17	16					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00058	HL
2426.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
2427.	17	17					TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00059	HL
2428.	17	18					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00058	HL
2429.	17	19					TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00059	HL
2430.	17	20					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00052	HL
2431.	17	21					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00052	HL
2432.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
2433.	17	22					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00052	HL
2434.	17	23					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00052	HL
2435.	17	24					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00052	HL
2436.	17	25					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00052	HL
2437.	17	26					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00052	HL
2438.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
2439.	17	27					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00052	HL
2440.	17	28					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00052	HL
2441.	17	29					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00054	HL
2442.	17	30					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00054	HL
2443.	17	31					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00054	HL
2444.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
2445.	17	32					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00054	HL
2446.	17	33					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00054	HL
2447.	17	34					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00054	HL
2448.	17	35					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00054	HL
2449.	17	36					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00054	HL
2450.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: A
 DATABASE: Harris_SGA_1995

Sep. 23.1995 15:21

PAGE 52 of 124

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
2451.	17	37						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00006	HL
2452.	17	38						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00006	HL
2453.	17	39						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00006	HL
2454.	17	40						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00006	HL
2455.	17	41						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00006	HL
2456.								TEHTEC	G1931	rpri	A610MULC	SG10CCAL00001	CL
2457.	17	42						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00006	HL
2458.	17	43						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00006	HL
2459.	17	44						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00006	HL
2460.	17	45						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00006	HL
2461.	17	46						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00006	HL
2462.								TEHTEC	G1931	rpri	A610MULC	SG10CCAL00001	CL
2463.	17	47						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00006	HL
2464.	17	48						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00006	HL
2465.	17	49						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00006	HL
2466.	17	50						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00006	HL
2467.	17	51						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00006	HL
2468.								TEHTEC	G1931	rpri	A610MULC	SG10CCAL00001	CL
2469.	17	52						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00006	HL
2470.	17	53						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00006	HL
71.	17	54						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00006	HL
72.	17	55						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00006	HL
73.	17	56						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00006	HL
2474.								TEHTEC	G1931	rpri	A610MULC	SG10CCAL00001	CL
2475.	17	57						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
2476.	17	58						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
2477.	17	59						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
2478.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00009	CL
2479.	17	60						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
2480.	17	61						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
2481.	17	62						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
2482.	17	63						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
2483.	17	64						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
2484.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00009	CL
2485.	17	65						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
2486.	17	66						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
2487.	17	67						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
2488.	17	68						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
2489.	17	69						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
2490.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00009	CL
2491.	17	70						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
2492.	17	71						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
2493.	17	72						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
2494.	17	73						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
2495.	17	74						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
2496.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00009	CL
77.	17	75						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
78.	17	76						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
2499.	17	77						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00021	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: A
 DATABASE: Harris_SGA_1995

Sep. 23.1995 15:21

PAGE 53 of 124

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
2500.	17	78						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00021	HL
2501.	17	79						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00021	HL
2502.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00006	CL
2503.	17	80						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00021	HL
2504.	17	81						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00021	HL
2505.	17	82						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00021	HL
2506.	17	83						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00021	HL
2507.	17	84						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00021	HL
2508.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00006	CL
2509.	17	85						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00021	HL
2510.	17	86						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00021	HL
2511.	17	87						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00024	HL
2512.	17	88						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00024	HL
2513.	17	89						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00024	HL
2514.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00006	CL
2515.	17	90						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00024	HL
2516.	17	91						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00024	HL
2517.	17	92						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00024	HL
2518.	17	93						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00024	HL
2519.	17	94						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00012	HL
2520.								TEHTEC	G1931	rpri	A610MULC	SG10CCAL00005	CL
2521.	17	95						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00013	HL
2522.	17	96						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00012	HL
2523.	17	97						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00013	HL
2524.	17	98						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00012	HL
2525.	17	99						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00013	HL
2526.								TEHTEC	G1931	rpri	A610MULC	SG10CCAL00005	CL
2527.	17	100						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00012	HL
2528.	17	101						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00013	HL
2529.	17	102						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00012	HL
2530.	17	103						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00013	HL
2531.	17	104						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00014	HL
2532.								TEHTEC	G1931	rpri	A610MULC	SG10CCAL00005	CL
2533.	17	105						TSHTSH	J9815	rsec	B620MRPC3C	SG11HCAL00015	HL
2534.	17	106						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00014	HL
2535.	17	107						TSHTSH	J9815	rsec	B620MRPC3C	SG11HCAL00015	HL
2536.	17	108						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00014	HL
2537.	17	109						TSHTSH	J9815	rsec	B620MRPC3C	SG11HCAL00015	HL
2538.								TEHTEC	G1931	rpri	A610MULC	SG10CCAL00005	CL
2539.	17	110						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00014	HL
2540.	17	111						TSHTSH	J9815	rsec	B620MRPC3C	SG11HCAL00015	HL
2541.								TEHTEC	G1931	rpri	A610MULC	SG10CCAL00005	CL
2542.	18	4						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00056	HL
2543.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
2544.	18	5						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00056	HL
2545.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
2546.	18	6						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00058	HL
2547.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
2548.	18	7						TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00059	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: A
 DATABASE: Harris_SGA_1995

Sep. 23.1995 15:21

PAGE 54 of 124

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
2549.	18	8					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00058	HL
2550.	18	9					TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00059	HL
2551.	18	10					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00058	HL
2552.	18	11					TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00059	HL
2553.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
2554.	18	12					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00058	HL
2555.	18	13					TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00059	HL
2556.	18	14					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00058	HL
2557.	18	15					TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00059	HL
2558.	18	16					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00058	HL
2559.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
2560.	18	17					TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00059	HL
2561.	18	18					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00058	HL
2562.	18	19					TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00059	HL
2563.	18	20					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00051	HL
2564.	18	21					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00051	HL
2565.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
2566.	18	22					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00051	HL
2567.	18	23					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00051	HL
2568.	18	24					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00051	HL
2569.	18	25					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00051	HL
	18	26					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00051	HL
							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
2572.	18	27					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00051	HL
2573.	18	28					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00051	HL
2574.	18	29					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00053	HL
2575.	18	30					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00053	HL
2576.	18	31					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00053	HL
2577.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
2578.	18	32					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00053	HL
2579.	18	33					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00053	HL
2580.	18	34					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00053	HL
2581.	18	35					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00053	HL
2582.	18	36					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00053	HL
2583.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
2584.	18	37					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00005	HL
2585.	18	38					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00005	HL
2586.	18	39					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00005	HL
2587.	18	40					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00005	HL
2588.	18	41					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00005	HL
2589.							TEHTEC	G1931	rpri	A610MULC	SG10CCAL00001	CL
2590.	18	42					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00005	HL
2591.	18	43					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00005	HL
2592.	18	44					TSHTSH	J9815	rsec	B620MRPC3C	SG11HCAL00005	HL
2593.	18	45					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00005	HL
2594.	18	46					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00005	HL
2595.							TEHTEC	G1931	rpri	A610MULC	SG10CCAL00001	CL
2596.	18	47					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00005	HL
2597.	18	48					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00005	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: A
 DATABASE: Harris_SGA_1995

Sep. 23, 1995 15:21

PAGE 55 of 124

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL-GROUP	LEG
2598.	18	49						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00005	HL
2599.	18	50						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00005	HL
2600.	18	51						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00005	HL
2601.								TEHTEC	G1931	rpri	A610MULC	SG10CCAL00001	CL
2602.	18	52						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00005	HL
2603.	18	53						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00005	HL
2604.	18	54						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00005	HL
2605.	18	55						TSHTSH	J9815	rsec	B620MRPC3C	SG11HCAL00005	HL
2606.	18	56						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00005	HL
2607.								TEHTEC	G1931	rpri	A610MULC	SG10CCAL00001	CL
2608.	18	57						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
2609.	18	58						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
2610.	18	59						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
2611.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00009	CL
2612.	18	60						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
2613.	18	61						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
2614.	18	62						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
2615.	18	63						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
2616.	18	64						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
2617.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00009	CL
18.	18	65						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
	18	66						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
2618.	18	67						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
2619.	18	68						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
2620.	18	69						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
2621.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00009	CL
2622.	18	70						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
2623.	18	71						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
2624.	18	72						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
2625.	18	73						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
2626.	18	74						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
2627.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00009	CL
2628.	18	75						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
2629.	18	76						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
2630.	18	77						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00020	HL
2631.	18	78						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00020	HL
2632.	18	79						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00020	HL
2633.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00006	CL
2634.	18	80						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00020	HL
2635.	18	81						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00020	HL
2636.	18	82						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00020	HL
2637.	18	83						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00020	HL
2638.	18	84						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00020	HL
2639.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00006	CL
2640.	18	85						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00020	HL
2641.	18	86						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00020	HL
2642.	18	87						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00023	HL
2643.	18	88						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00023	HL
2644.	18	89						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00023	HL
2645.								TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00023	HL
2646.	18	89						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00023	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: A
 DATABASE: Harris_SGA_1995

Sep. 23.1995 15:21

PAGE 56 of 124

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
2647.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00006	CL
2648.	18	90						TSHTSH	B5534	rpri.	B620MRPC3C	SG11HCAL00023	HL
2649.	18	91						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00023	HL
2650.	18	92						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00023	HL
2651.	18	93						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00023	HL
2652.	18	94						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00012	HL
2653.								TEHTEC	G1931	rpri	A610MULC	SG10CCAL00005	CL
2654.	18	95						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00013	HL
2655.	18	96						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00012	HL
2656.	18	97						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00013	HL
2657.	18	98						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00012	HL
2658.	18	99						TSHTSH	J9815	rsec	B620MRPC3C	SG11HCAL00013	HL
2659.								TEHTEC	G1931	rpri	A610MULC	SG10CCAL00005	CL
2660.	18	100						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00012	HL
2661.	18	101						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00013	HL
2662.	18	102						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00012	HL
2663.	18	103						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00013	HL
2664.	18	104						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00014	HL
2665.		6.96	185	DNT	1	01C	4.39	TEHTEC	G1931	rpri	A610MULC	SG10CCAL00005	CL
2666.	18	105						TSHTSH	J9815	rsec	B620MRPC3C	SG11HCAL00015	HL
2667.	18	106						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00014	HL
2668.	18	107						TSHTSH	J9815	rsec	B620MRPC3C	SG11HCAL00015	HL
2669.	18	108						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00014	HL
2670.	18	109						TSHTSH	J9815	rsec	B620MRPC3C	SG11HCAL00015	HL
2671.								TEHTEC	G1931	rpri	A610MULC	SG10CCAL00005	CL
2672.	18	110						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00014	HL
2673.								TEHTEC	G1931	rpri	A610MULC	SG10CCAL00005	CL
2674.	18	111						TSHTSH	J9815	rsec	B620MRPC3C	SG11HCAL00015	HL
2675.					RES			AV1TEC	F3453	reso	A610MULC	SG10CCAL00005	CL
2676.					RES			11CTEC	F3453	reso	A590SFRM	SG10CCAL00018	CL
2677.		35.88	177	DNT	P1	11H	-0.43	TEHTEC	F3453	reso	A560SFRM	SG10CCAL00019	CL
2678.		33.29	180	DNT	P1	11H	0.52	TEHTEC	F3453	reso	A560SFRM	SG10CCAL00019	CL
2679.		18.15	181	DNT	1	11H	1.44	TEHTEC	F3453	reso	A560SFRM	SG10CCAL00019	CL
2680.		7.75	183	DNT	1	11H	1.90	TEHTEC	F3453	reso	A560SFRM	SG10CCAL00019	CL
2681.	19	5						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00058	HL
2682.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
2683.	19	6						TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00059	HL
2684.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
2685.	19	7						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00058	HL
2686.	19	8						TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00059	HL
2687.	19	9						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00058	HL
2688.	19	10						TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00059	HL
2689.	19	11						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00058	HL
2690.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
2691.	19	13						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00058	HL
2692.	19	14						TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00059	HL
2693.	19	15						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00058	HL
2694.	19	16						TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00059	HL
2695.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: A
 DATABASE: Harris_SGA_1995

Sep. 23.1995 15:21

PAGE 57 of 124

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
2696.	19	17						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00058	HL
2697.	19	18						TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00059	HL
2698.	19	19						TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00059	HL
2699.	19	20						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00052	HL
2700.	19	21						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00052	HL
2701.		7.67	186	DNT	1	01H	6.87	TEHTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
2702.	19	22						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00052	HL
2703.	19	23						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00052	HL
2704.	19	24						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00052	HL
2705.	19	25						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00052	HL
2706.	19	26						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00052	HL
2707.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
2708.	19	27						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00052	HL
2709.	19	28						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00054	HL
2710.	19	29						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00054	HL
2711.	19	30						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00054	HL
2712.	19	31						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00054	HL
2713.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
2714.	19	32						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00054	HL
2715.	19	33						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00054	HL
16.	19	34						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00054	HL
17.	19	35						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00054	HL
18.	19	36						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00054	HL
2719.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
2720.	19	37						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00006	HL
2721.	19	38						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00006	HL
2722.	19	39						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00006	HL
2723.	19	40						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00006	HL
2724.	19	41						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00006	HL
2725.								TEHTEC	G1931	rpri	A610MULC	SG10CCAL00001	CL
2726.	19	42						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00006	HL
2727.	19	43						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00006	HL
2728.	19	44						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00006	HL
2729.	19	45						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00006	HL
2730.	19	46						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00006	HL
2731.								TEHTEC	G1931	rpri	A610MULC	SG10CCAL00001	CL
2732.	19	47						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00006	HL
2733.	19	48						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00006	HL
2734.	19	49						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00006	HL
2735.	19	50						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00006	HL
2736.	19	51						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00006	HL
2737.								TEHTEC	G1931	rpri	A610MULC	SG10CCAL00001	CL
2738.	19	52						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00006	HL
2739.	19	53						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00006	HL
2740.	19	54						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00006	HL
2741.	19	55						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00006	HL
2742.	19	56						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00006	HL
2743.								TEHTEC	G1931	rpri	A610MULC	SG10CCAL00001	CL
2744.	19	57						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: A
 DATABASE: Harris_SGA_1995

Sep. 23.1995 15:21

PAGE 58 of 124

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
2745.	19	58					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
2746.	19	59					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
2747.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00009	CL
2748.	19	60					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
2749.	19	61					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
2750.	19	62					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
2751.	19	63					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
2752.	19	64					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
2753.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00009	CL
2754.	19	65					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
2755.	19	66					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
2756.	19	67					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
2757.	19	68					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
2758.	19	69					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
2759.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00009	CL
2760.	19	70					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
2761.	19	71					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
2762.	19	72					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
2763.	19	73					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
2764.	19	74					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
2765.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00009	CL
2766.	19	75					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
2767.	19	76					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
2768.	19	77					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00021	HL
2769.	19	78					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00021	HL
2770.	19	79					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00021	HL
2771.							TEHTEC	F2217	rpri	A610MULC	SG10CCAL00006	CL
2772.	19	80					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00021	HL
2773.	19	81					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00021	HL
2774.	19	82					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00021	HL
2775.	19	83					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00021	HL
2776.	19	84					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00021	HL
2777.							TEHTEC	F2217	rpri	A610MULC	SG10CCAL00006	CL
2778.	19	85					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00021	HL
2779.	19	86					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00021	HL
2780.	19	87					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00024	HL
2781.	19	88					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00024	HL
2782.	19	89					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00024	HL
2783.							TEHTEC	F2217	rpri	A610MULC	SG10CCAL00006	CL
2784.	19	90					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00024	HL
2785.	19	91					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00024	HL
2786.	19	92					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00024	HL
2787.	19	93					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00024	HL
2788.	19	94					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00012	HL
2789.							TEHTEC	G1931	rpri	A610MULC	SG10CCAL00005	CL
2790.	19	95					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00013	HL
2791.	19	96					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00012	HL
2792.	19	97					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00013	HL
2793.	19	98					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00012	HL

*** INSPECTION FINAL REPORT LISTING ***

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: A
 DATABASE: Harris_SGA_1995

Sep. 23, 1995 15:21

PAGE 59 of 124

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
2794.	19	99					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00013	HL
2795.							TEHTEC	G1931	rpri	A610MULC	SG10CCAL00005	CL
2796.	19	100					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00012	HL
2797.	19	101					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00013	HL
2798.	19	102					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00012	HL
2799.	19	103					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00013	HL
2800.	19	104					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00014	HL
2801.							TEHTEC	G1931	rpri	A610MULC	SG10CCAL00005	CL
2802.	19	105					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00015	HL
2803.	19	106					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00014	HL
2804.	19	107					TSHTSH	J9815	rsec	B620MRPC3C	SG11HCAL00015	HL
2805.	19	108					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00014	HL
2806.	19	109					TSHTSH	J9815	rsec	B620MRPC3C	SG11HCAL00015	HL
2807.							TEHTEC	G1931	rpri	A610MULC	SG10CCAL00005	CL
2808.	19	110					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00014	HL
2809.							TEHTEC	G1931	rpri	A610MULC	SG10CCAL00005	CL
2810.	20	5					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00058	HL
2811.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
2812.	20	6					TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00059	HL
2813.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
14.	20	7					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00058	HL
15.	20	8					TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00059	HL
16.	20	9					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00058	HL
2817.	20	10					TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00059	HL
2818.	20	11					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00058	HL
2819.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
2820.	20	12					TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00059	HL
2821.	20	13					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00058	HL
2822.	20	14					TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00059	HL
2823.	20	15					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00058	HL
2824.	20	16					TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00059	HL
2825.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
2826.	20	17					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00058	HL
2827.	20	18					TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00059	HL
2828.	20	19					TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00059	HL
2829.	20	20					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00051	HL
2830.	20	21					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00051	HL
2831.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
2832.	20	22					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00051	HL
2833.	20	23					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00051	HL
2834.	20	24					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00051	HL
2835.	20	25					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00051	HL
2836.	20	26					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00051	HL
2837.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
2838.	20	27					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00051	HL
2839.	20	28					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00053	HL
2840.	20	29					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00053	HL
2841.	20	30					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00053	HL
2842.	20	31					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00053	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: A
 DATABASE: Harris_SGA_1995

Sep. 23,1995 15:21

PAGE 60 of 124

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
2843.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
2844.	20	32					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00053	HL
2845.	20	33					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00053	HL
2846.	20	34					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00053	HL
2847.	20	35					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00053	HL
2848.	20	36					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00053	HL
2849.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
2850.	20	37					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00005	HL
2851.	20	38					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00005	HL
2852.	20	39					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00005	HL
2853.	20	40					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00005	HL
2854.	20	41					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00005	HL
2855.							TEHTEC	G1931	rpri	A610MULC	SG10CCAL00001	CL
2856.	20	42					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00005	HL
2857.	20	43					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00005	HL
2858.	20	44					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00005	HL
2859.	20	45					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00005	HL
2860.	20	46					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00005	HL
2861.							TEHTEC	G1931	rpri	A610MULC	SG10CCAL00001	CL
2862.	20	47					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00005	HL
2863.	20	48					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00005	HL
2864.	20	49					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00005	HL
2865.	20	50					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00005	HL
2866.	20	51					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00005	HL
2867.							TEHTEC	G1931	rpri	A610MULC	SG10CCAL00001	CL
2868.	20	52					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00005	HL
2869.	20	53					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00005	HL
2870.	20	54					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00005	HL
2871.	20	55					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00005	HL
2872.	20	56					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00005	HL
2873.							TEHTEC	G1931	rpri	A610MULC	SG10CCAL00001	CL
2874.	20	57					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
2875.	20	58					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
2876.	20	59					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
2877.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00009	CL
2878.	20	60					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
2879.	20	61					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
2880.	20	62					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
2881.	20	63					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
2882.	20	64					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
2883.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00009	CL
2884.	20	65					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
2885.	20	66					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
2886.	20	67					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
2887.	20	68					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
2888.	20	69					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
2889.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00009	CL
2890.	20	70					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
2891.	20	71					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: A
 DATABASE: Harris_SGA_1995

Sep. 23.1995 15:21

PAGE 61 of 124

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
2892.	20	72					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
2893.	20	73					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
2894.	20	74					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
2895.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00009	CL
2896.	20	75					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
2897.	20	76					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
2898.	20	77					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00020	HL
2899.	20	78					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00020	HL
2900.	20	79					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00020	HL
2901.							TEHTEC	F2217	rpri	A610MULC	SG10CCAL00006	CL
2902.	20	80					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00020	HL
2903.	20	81					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00020	HL
2904.	20	82					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00020	HL
2905.	20	83					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00020	HL
2906.	20	84					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00020	HL
2907.							TEHTEC	F7460	rsec	A610MULC	SG10CCAL00006	CL
2908.	20	85					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00020	HL
2909.	20	86					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00020	HL
2910.	20	87					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00023	HL
2911.	20	88					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00023	HL
12.	20	89					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00023	HL
							TEHTEC	F2217	rpri	A610MULC	SG10CCAL00006	CL
2914.	20	90					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00023	HL
2915.	20	91					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00023	HL
2916.	20	92					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00023	HL
2917.	20	93					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00023	HL
2918.	20	94					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00012	HL
2919.							TEHTEC	G1931	rpri	A610MULC	SG10CCAL00005	CL
2920.	20	95					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00013	HL
2921.	20	96					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00012	HL
2922.	20	97					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00013	HL
2923.	20	98					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00012	HL
2924.	20	100					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00012	HL
2925.	20	101					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00013	HL
2926.	20	102					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00012	HL
2927.	20	103					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00013	HL
2928.	20	104					TSHTSH	D4825	reso	B620MRPC3C	SG11HCAL00014	HL
2929.							TEHTEC	G1931	rpri	A610MULC	SG10CCAL00005	CL
2930.	20	105					TSHTSH	D4825	reso	B620MRPC3C	SG11HCAL00015	HL
2931.	20	106					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00014	HL
2932.	20	107					TSHTSH	J9815	rsec	B620MRPC3C	SG11HCAL00015	HL
2933.	20	108					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00014	HL
2934.	20	109					TSHTSH	J9815	rsec	B620MRPC3C	SG11HCAL00015	HL
2935.							TEHTEC	G1931	rpri	A610MULC	SG10CCAL00005	CL
2936.	20	110					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00014	HL
2937.							TEHTEC	G1931	rpri	A610MULC	SG10CCAL00005	CL
2939.	21	5					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00058	HL
2940.	21	6					TEHTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
2940.	21	6					TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00059	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: A
 DATABASE: Harris_SGA_1995

Sep. 23.1995 15:21

PAGE 62 of 124

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
2941.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
2942.	21	7						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00058	HL
2943.	21	8						TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00059	HL
2944.	21	9						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00058	HL
2945.	21	10						TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00059	HL
2946.	21	11						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00058	HL
2947.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
2948.	21	12						TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00059	HL
2949.	21	13						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00058	HL
2950.	21	14						TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00059	HL
2951.	21	15						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00058	HL
2952.	21	16						TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00059	HL
2953.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
2954.	21	17						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00058	HL
2955.	21	18						TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00059	HL
2956.	21	19						TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00059	HL
2957.	21	20						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00052	HL
2958.	21	21						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00052	HL
2959.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
2960.	21	22						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00052	HL
61.	21	23						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00052	HL
2961.	21	24						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00052	HL
2962.	21	25						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00052	HL
2963.	21	26						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00052	HL
2964.	21	26						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00052	HL
2965.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
2966.	21	27						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00052	HL
2967.	21	28						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00054	HL
2968.	21	29						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00054	HL
2969.	21	30						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00054	HL
2970.	21	31						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00054	HL
2971.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
2972.	21	32						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00054	HL
2973.	21	33						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00054	HL
2974.	21	34						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00054	HL
2975.	21	35						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00054	HL
2976.	21	36						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00054	HL
2977.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL
2978.	21	37						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00002	HL
2979.	21	38						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00001	HL
2980.	21	39						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00002	HL
2981.	21	40						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00001	HL
2982.	21	41						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00002	HL
2983.								TEHTEC	N0698	rpri	A610MULC	SG10CCAL00001	CL
2984.	21	42						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00001	HL
2985.	21	43						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00004	HL
2986.	21	44						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00003	HL
2987.	21	45						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00004	HL
2988.	21	46						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00003	HL
2989.								TEHTEC	G1931	rpri	A610MULC	SG10CCAL00001	CL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: A
 DATABASE: Harris_SGA_1995

Sep. 23.1995 15:21

PAGE 63 of 124

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
2990.	21	47						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00004	HL
2991.	21	48						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00003	HL
2992.	21	49						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00004	HL
2993.	21	50						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00003	HL
2994.	21	51						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00004	HL
2995.								TEHTEC	G1931	rpri	A610MULC	SG10CCAL00001	CL
2996.	21	52						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00003	HL
2997.	21	53						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00004	HL
2998.	21	54						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00003	HL
2999.	21	55						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00003	HL
3000.	21	56						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00003	HL
3001.								TEHTEC	G1931	rpri	A610MULC	SG10CCAL00001	CL
3002.	21	57						TSHTSH	T7665	rpri	B620MRPC3C	SG11HCAL00038	HL
3003.	21	58						TSHTSH	T7665	rpri	B620MRPC3C	SG11HCAL00038	HL
3004.	21	59						TSHTSH	T7665	rpri	B620MRPC3C	SG11HCAL00038	HL
3005.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00009	CL
3006.	21	60						TSHTSH	T7665	rpri	B620MRPC3C	SG11HCAL00038	HL
3007.	21	61						TSHTSH	T7665	rpri	B620MRPC3C	SG11HCAL00038	HL
3008.	21	62						TSHTSH	T7665	rpri	B620MRPC3C	SG11HCAL00038	HL
3009.	21	63						TSHTSH	T7665	rpri	B620MRPC3C	SG11HCAL00038	HL
3010.	21	64						TSHTSH	T7665	rpri	B620MRPC3C	SG11HCAL00038	HL
3011.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00009	CL
3012.	21	65						TSHTSH	T7665	rpri	B620MRPC3C	SG11HCAL00038	HL
3013.	21	66						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00041	HL
3014.	21	67						TSHTSH	T9924	rpri	B620MRPC3C	SG11HCAL00042	HL
3015.	21	68						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00041	HL
3016.			0.50	158	MBM	1	09H 31.18	TEHTEC	S7675	rpri	A610MULC	SG10CCAL00009	CL
3017.	21	69						TSHTSH	T9924	rpri	B620MRPC3C	SG11HCAL00042	HL
3018.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00009	CL
3019.	21	70						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00041	HL
3020.	21	71						TSHTSH	T9924	rpri	B620MRPC3C	SG11HCAL00042	HL
3021.	21	72						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00041	HL
3022.	21	73						TSHTSH	T9924	rpri	B620MRPC3C	SG11HCAL00042	HL
3023.	21	74						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
3024.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00009	CL
3025.	21	75						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
3026.	21	76						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
3027.	21	77						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
3028.	21	78						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
3029.	21	79						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
3030.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00009	CL
3031.	21	80						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
3032.	21	81						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
3033.	21	82						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00020	HL
3034.	21	83						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00021	HL
3035.	21	84						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00020	HL
3036.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00006	CL
3037.	21	85						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00021	HL
3038.	21	86						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00020	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: A
 DATABASE: Harris_SGA_1995

Sep. 23.1995 15:21

PAGE 64 of 124

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
3039.	21	87					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00021	HL
3040.	21	88					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00020	HL
3041.	21	89					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00021	HL
3042.							TEHTEC	F2217	rpri	A610MJLC	SG10CCAL00006	CL
3043.	21	90					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00020	HL
3044.	21	91					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00021	HL
3045.	21	92					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00020	HL
3046.	21	93					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00021	HL
3047.	21	94					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00014	HL
3048.							TEHTEC	F2217	rpri	A610MJLC	SG10CCAL00005	CL
3049.	21	95					TSHTSH	J9815	rsec	B620MRPC3C	SG11HCAL00015	HL
3050.	21	96					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00014	HL
3051.	21	97					TSHTSH	J9815	rsec	B620MRPC3C	SG11HCAL00015	HL
3052.	21	98					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00014	HL
3053.	21	99					TSHTSH	J9815	rsec	B620MRPC3C	SG11HCAL00015	HL
3054.							TEHTEC	F2217	rpri	A610MJLC	SG10CCAL00005	CL
3055.	21	100					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00014	HL
3056.	21	101					TSHTSH	J9815	rsec	B620MRPC3C	SG11HCAL00015	HL
3057.	21	102					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00014	HL
3058.	21	103					TSHTSH	J9815	rsec	B620MRPC3C	SG11HCAL00015	HL
59.	21	104					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00014	HL
							TEHTEC	F2217	rpri	A610MJLC	SG10CCAL00005	CL
	21	105					TSHTSH	J9815	rsec	B620MRPC3C	SG11HCAL00015	HL
3062.	21	106					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00016	HL
3063.	21	107					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00017	HL
3064.	21	108					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00016	HL
3065.	21	109					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00017	HL
3066.							TEHTEC	F2217	rpri	A610MJLC	SG10CCAL00005	CL
3067.	21	110					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00016	HL
3068.							TEHTEC	F2217	rpri	A610MJLC	SG10CCAL00005	CL
3069.	22	6					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00058	HL
3070.							TEHTEC	S7675	rpri	A610MJLC	SG10CCAL00014	CL
3071.	22	7					TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00059	HL
3072.	22	8					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00058	HL
3073.	22	9					TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00059	HL
3074.	22	10					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00058	HL
3075.	22	11					TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00059	HL
3076.							TEHTEC	S7675	rpri	A610MJLC	SG10CCAL00014	CL
3077.	22	12					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00058	HL
3078.	22	13					TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00059	HL
3079.	22	14					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00058	HL
3080.	22	15					TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00059	HL
3081.	22	16					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00058	HL
3082.							TEHTEC	S7675	rpri	A610MJLC	SG10CCAL00013	CL
3083.							TEHTEC	S7675	rpri	A610MJLC	SG10CCAL00014	CL
3084.	22	17					TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00059	HL
3085.	22	18					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00058	HL
	22	19					TSHTSH	F2217	rpri	B620MRPC3C	SG11HCAL00059	HL
3087.	22	20					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00051	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: A
 DATABASE: Harris_SGA_1995

Sep. 23,1995 15:21

PAGE 65 of 124

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE	SIZE	CAL GROUP	LEG
3088.	22	21						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00051	HL	
3089.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL	
3090.	22	22						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00051	HL	
3091.	22	23						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00051	HL	
3092.	22	24						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00051	HL	
3093.	22	25						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00051	HL	
3094.	22	26						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00051	HL	
3095.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL	
3096.	22	27						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00051	HL	
3097.	22	28						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00053	HL	
3098.	22	29						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00053	HL	
3099.	22	30						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00053	HL	
3100.	22	31						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00053	HL	
3101.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL	
3102.	22	32						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00053	HL	
3103.	22	33						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00053	HL	
3104.	22	34						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00053	HL	
3105.	22	35						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00053	HL	
3106.	22	36						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00053	HL	
3107.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00014	CL	
08.	22	37						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00002	HL	
9.	22	38						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00001	HL	
10.	22	39						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00002	HL	
3111.	22	40						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00001	HL	
3112.	22	41						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00002	HL	
3113.								TEHTEC	N0698	rpri	A610MULC	SG10CCAL00001	CL	
3114.	22	42						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00001	HL	
3115.	22	43						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00004	HL	
3116.	22	44						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00003	HL	
3117.	22	45						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00003	HL	
3118.	22	70						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00041	HL	
3119.	22	71						TSHTSH	T9924	rpri	B620MRPC3C	SG11HCAL00042	HL	
3120.	22	72						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00041	HL	
3121.	22	73						TSHTSH	T9924	rpri	B620MRPC3C	SG11HCAL00042	HL	
3122.	22	74						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL	
3123.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00009	CL	
3124.	22	75						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL	
3125.	22	76						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL	
3126.	22	77						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL	
3127.	22	78						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL	
3128.	22	79						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL	
3129.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00009	CL	
3130.	22	80						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL	
3131.	22	81						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL	
3132.	22	82						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00020	HL	
3133.	22	83						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00021	HL	
3134.	22	84						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00020	HL	
3135.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00006	CL	
3136.	22	85						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00021	HL	

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: A
 DATABASE: Harris_SGA_1995

Sep. 23.1995 15:21

PAGE 66 of 124

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
3137.	22	86						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00020	HL
3138.	22	87						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00021	HL
3139.	22	88						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00020	HL
3140.	22	89						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00021	HL
3141.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00006	CL
3142.	22	90						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00020	HL
3143.	22	91						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00021	HL
3144.	22	92						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00020	HL
3145.	22	93						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00021	HL
3146.	22	94						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00014	HL
3147.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00005	CL
3148.	22	95						TSHTSH	J9815	rsec	B620MRPC3C	SG11HCAL00015	HL
3149.	22	96						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00014	HL
3150.	22	97						TSHTSH	J9815	rsec	B620MRPC3C	SG11HCAL00015	HL
3151.	22	98						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00014	HL
3152.	22	99						TSHTSH	J9815	rsec	B620MRPC3C	SG11HCAL00015	HL
3153.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00005	CL
3154.	22	100						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00014	HL
3155.	22	101						TSHTSH	J9815	rsec	B620MRPC3C	SG11HCAL00015	HL
3156.	22	102						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00014	HL
57.	22	103						TSHTSH	J9815	rsec	B620MRPC3C	SG11HCAL00015	HL
58.	22	104						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00014	HL
59.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00005	CL
3160.	22	105						TSHTSH	J9815	rsec	B620MRPC3C	SG11HCAL00015	HL
3161.								07H07H	B5534	rpri	B590MRPC3C	SG11HCAL00035	HL
3162.		0.63	163	13	1	01H	1.01	TEHTEC	F3453	reso	A610MULC	SG10CCAL00005	CL
3163.		8.05	181	DNT	P1	07H	0.36	TEHTEC	F2217	rpri	A610MULC	SG10CCAL00005	CL
3164.	22	106						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00016	HL
3165.								07H07H	B5534	rpri	B590MRPC3C	SG11HCAL00035	HL
3166.	22	107						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00017	HL
3167.	22	108						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00016	HL
3168.	22	109						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00017	HL
3169.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00005	CL
3170.	23	6						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00050	HL
3171.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00013	CL
3172.	23	7						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00049	HL
3173.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00013	CL
3174.	23	8						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00050	HL
3175.	23	9						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00049	HL
3176.	23	10						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00050	HL
3177.	23	11						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00049	HL
3178.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00013	CL
3179.	23	12						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00050	HL
3180.	23	13						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00049	HL
3181.	23	14						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00050	HL
3182.	23	15						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00049	HL
3183.	23	16						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00050	HL
3184.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00013	CL
3185.	23	17						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00049	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: A
 DATABASE: Harris_SGA_1995

Sep. 23.1995 15:21

PAGE 67 of 124

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
3186.	23	18					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00050	HL
3187.	23	19					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00049	HL
3188.	23	20					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00050	HL
3189.	23	21					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00049	HL
3190.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00013	CL
3191.	23	22					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00052	HL
3192.	23	23					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00051	HL
3193.	23	24					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00052	HL
3194.	23	25					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00051	HL
3195.	23	26					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00052	HL
3196.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00013	CL
3197.	23	27					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00051	HL
3198.	23	28					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00052	HL
3199.	23	29					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00051	HL
3200.	23	30					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00052	HL
3201.	23	31					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00051	HL
3202.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00013	CL
3203.	23	32					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00052	HL
3204.	23	33					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00051	HL
3205.	23	34					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00052	HL
06.	23	35					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00051	HL
7.	23	36					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00051	HL
8.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00013	CL
3209.	23	37					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00002	HL
3210.	23	38					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00001	HL
3211.	23	39					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00002	HL
3212.	23	40					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00001	HL
3213.	23	41					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00004	HL
3214.							TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00002	HL
3215.							TEHTEC	N0698	rpri	A610MULC	SG10CCAL00001	CL
3216.	23	42					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00001	HL
3217.							TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00003	HL
3218.	23	43					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00004	HL
3219.	23	44					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00003	HL
3220.	23	45					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00003	HL
3221.	23	70					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00041	HL
3222.	23	71					TSHTSH	T9924	rpri	B620MRPC3C	SG11HCAL00042	HL
3223.	23	72					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00041	HL
3224.	23	73					TSHTSH	T9924	rpri	B620MRPC3C	SG11HCAL00042	HL
3225.	23	74					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
3226.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00009	CL
3227.	23	75					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
3228.	23	76					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
3229.	23	77					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
3230.	23	78					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
31.	23	79					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
2.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00009	CL
3.	23	80					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
3234.	23	81					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: A
 DATABASE: Harris_SGA_1995

Sep. 23.1995 15:21

PAGE 68 of 124

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG	
3235.	23	82						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00020	HL	
3236.	23	83						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00021	HL	
3237.	23	84						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00020	HL	
3238.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00006	CL	
3239.	23	85						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00021	HL	
3240.	23	86						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00020	HL	
3241.	23	87						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00021	HL	
3242.	23	88						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00020	HL	
3243.	23	89						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00021	HL	
3244.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00006	CL	
3245.	23	90						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00020	HL	
3246.	23	91						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00021	HL	
3247.	23	92						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00020	HL	
3248.	23	93						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00021	HL	
3249.	23	94						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00014	HL	
3250.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00005	CL	
3251.	23	95						TSHTSH	J9815	rsec	B620MRPC3C	SG11HCAL00015	HL	
3252.	23	96						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00014	HL	
3253.	23	97						TSHTSH	J9815	rsec	B620MRPC3C	SG11HCAL00015	HL	
3254.	23	98						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00014	HL	
55.	23	100						TSHTSH	J9815	rsec	B620MRPC3C	SG11HCAL00014	HL	
5.	23	101						TSHTSH	J9815	rsec	B620MRPC3C	SG11HCAL00015	HL	
57.	23	102						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00014	HL	
3258.	23	103						TSHTSH	J9815	rsec	B620MRPC3C	SG11HCAL00015	HL	
3259.	23	104						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00016	HL	
3260.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00005	CL	
3261.	23	105						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00017	HL	
3262.			0.49	91	PLP	11	07H	1.36	07H07H	F3453	reso	B590MRPC3C	SG11HCAL00035	HL
3263.	23	106						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00016	HL	
3264.	23	107						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00017	HL	
3265.	23	108						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00016	HL	
3266.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00005	CL	
3267.	23	109						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00017	HL	
3268.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00005	CL	
3269.	24	7						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00050	HL	
3270.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00013	CL	
3271.	24	8						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00049	HL	
3272.	24	9						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00050	HL	
3273.	24	10						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00049	HL	
3274.	24	11						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00050	HL	
3275.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00013	CL	
3276.	24	12						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00049	HL	
3277.	24	13						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00050	HL	
3278.	24	14						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00049	HL	
3279.	24	15						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00050	HL	
80.	24	16						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00049	HL	
1.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00013	CL	
2.	24	17						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00050	HL	
3283.	24	18						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00049	HL	

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: A
 DATABASE: Harris_SGA_1995

Sep. 23,1995 15:21

PAGE 69 of 124

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE	SIZE	CAL	GROUP	LEG
3284.	24	19						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00050	HL		
3285.	24	20						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00049	HL		
3286.	24	21						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00052	HL		
3287.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00013	CL		
3288.	24	22						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00051	HL		
3289.	24	23						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00052	HL		
3290.	24	24						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00051	HL		
3291.	24	25						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00052	HL		
3292.	24	26						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00051	HL		
3293.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00013	CL		
3294.	24	27						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00052	HL		
3295.	24	28						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00051	HL		
3296.	24	29						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00052	HL		
3297.	24	30						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00051	HL		
3298.	24	31						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00052	HL		
3299.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00013	CL		
3300.	24	32						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00051	HL		
3301.	24	33						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00052	HL		
3302.	24	34						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00051	HL		
3303.	24	35						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00052	HL		
04.	24	36						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00051	HL		
5.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00013	CL		
06.	24	37						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00002	HL		
3307.	24	38						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00001	HL		
3308.	24	39						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00002	HL		
3309.	24	40						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00001	HL		
3310.	24	41						TSHTSH	J9815	rsec	B620MRPC3C	SG11HCAL00004	HL		
3311.								TEHTEC	N0698	rpri	A610MULC	SG10CCAL00001	CL		
3312.	24	42						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00003	HL		
3313.	24	43						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00004	HL		
3314.	24	44						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00003	HL		
3315.	24	45						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00004	HL		
3316.	24	46						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00003	HL		
3317.								TEHTEC	G1931	rpri	A610MULC	SG10CCAL00001	CL		
3318.	24	47						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00004	HL		
3319.	24	48						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00003	HL		
3320.	24	49						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00004	HL		
3321.	24	50						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00003	HL		
3322.	24	51						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00004	HL		
3323.								TEHTEC	G1931	rpri	A610MULC	SG10CCAL00001	CL		
3324.	24	52						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00003	HL		
3325.	24	53						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00004	HL		
3326.	24	54						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00003	HL		
3327.	24	55						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00003	HL		
3328.	24	60						TSHTSH	S7675	rpri	B620MRPC3C	SG11HCAL00039	HL		
29.	24	61						TSHTSH	S7675	rpri	B620MRPC3C	SG11HCAL00039	HL		
30.	24	62						TSHTSH	S7675	rpri	B620MRPC3C	SG11HCAL00039	HL		
1.	24	63						TSHTSH	S7675	rpri	B620MRPC3C	SG11HCAL00039	HL		
3332.	24	64						TSHTSH	S7675	rpri	B620MRPC3C	SG11HCAL00039	HL		

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: A
 DATABASE: Harris_SGA_1995

Sep. 23,1995 15:21

PAGE 70 of 124

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
3333.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00009	CL
3334.	24	65					TSHTSH	G1931	rpri	B620MRPC3C	SG11HCAL00039	HL
3335.	24	66					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00041	HL
3336.	24	67					TSHTSH	T9924	rpri	B620MRPC3C	SG11HCAL00042	HL
3337.	24	68					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00041	HL
3338.	24	69					TSHTSH	T9924	rpri	B620MRPC3C	SG11HCAL00042	HL
3339.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00009	CL
3340.	24	70					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00041	HL
3341.	24	71					TSHTSH	T9924	rpri	B620MRPC3C	SG11HCAL00042	HL
3342.	24	72					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00041	HL
3343.	24	73					TSHTSH	T9924	rpri	B620MRPC3C	SG11HCAL00042	HL
3344.	24	74					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
3345.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00009	CL
3346.	24	75					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
3347.	24	76					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
3348.	24	77					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
3349.	24	78					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
3350.	24	79					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
3351.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00009	CL
3352.	24	80					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
53.	24	81					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
54.	24	82					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00020	HL
55.	24	83					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00021	HL
3356.	24	84					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00020	HL
3357.							TEHTEC	F2217	rpri	A610MULC	SG10CCAL00006	CL
3358.	24	85					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00021	HL
3359.	24	86					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00020	HL
3360.	24	87					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00021	HL
3361.	24	88					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00020	HL
3362.	24	89					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00021	HL
3363.							TEHTEC	F2217	rpri	A610MULC	SG10CCAL00006	CL
3364.	24	90					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00020	HL
3365.	24	91					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00021	HL
3366.	24	92					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00020	HL
3367.	24	93					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00021	HL
3368.	24	94					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00014	HL
3369.							TEHTEC	F2217	rpri	A610MULC	SG10CCAL00005	CL
3370.	24	95					TSHTSH	J9815	rsec	B620MRPC3C	SG11HCAL00015	HL
3371.	24	96					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00014	HL
3372.	24	97					TSHTSH	J9815	rsec	B620MRPC3C	SG11HCAL00015	HL
3373.	24	98					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00014	HL
3374.	24	99					TSHTSH	J9815	rsec	B620MRPC3C	SG11HCAL00015	HL
3375.							TEHTEC	F2217	rpri	A610MULC	SG10CCAL00005	CL
3376.	24	100					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00014	HL
3377.	24	101					TSHTSH	J9815	rsec	B620MRPC3C	SG11HCAL00015	HL
3378.	24	102					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00014	HL
79.	24	103					TSHTSH	J9815	rsec	B620MRPC3C	SG11HCAL00015	HL
0.	24	104					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00016	HL
3381.							TEHTEC	F2217	rpri	A610MULC	SG10CCAL00005	CL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: A
 DATABASE: Harris_SGA_1995

Sep. 23.1995 15:21

PAGE 71 of 124

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
3382.	24	105						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00017	HL
3383.	24	106						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00016	HL
3384.	24	107						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00017	HL
3385.	24	108						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00016	HL
3386.								TEHTEC	F2217	rpri	A610MJLC	SG10CCAL00005	CL
3387.	25	7						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00050	HL
3388.		5.99	183	DNT	1	AV1	1.18	TEHTEC	S7675	rpri	A610MJLC	SG10CCAL00013	CL
3389.		7.21	185	DNT	P1	AV3	0.00	TEHTEC	S7675	rpri	A610MJLC	SG10CCAL00013	CL
3390.	25	8						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00049	HL
3391.								TEHTEC	S7675	rpri	A610MJLC	SG10CCAL00013	CL
3392.	25	9						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00050	HL
3393.	25	10						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00049	HL
3394.	25	11						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00050	HL
3395.								TEHTEC	S7675	rpri	A610MJLC	SG10CCAL00013	CL
3396.	25	12						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00049	HL
3397.	25	13						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00050	HL
3398.	25	14						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00049	HL
3399.	25	15						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00050	HL
3400.	25	16						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00049	HL
3401.								TEHTEC	S7675	rpri	A610MJLC	SG10CCAL00013	CL
02.	25	17						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00050	HL
3.	25	18						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00049	HL
4.	25	19						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00050	HL
3405.	25	20						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00049	HL
3406.	25	21						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00052	HL
3407.					RBD				S7675	rpri	A610MJLC	SG10CCAL00013	CL
3408.								TEHTEC	S7675	rpri	A610MJLC	SG10CCAL00016	CL
3409.	25	22						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00051	HL
3410.	25	23						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00052	HL
3411.	25	24						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00051	HL
3412.	25	25						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00052	HL
3413.	25	26						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00051	HL
3414.								TEHTEC	S7675	rpri	A610MJLC	SG10CCAL00013	CL
3415.	25	27						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00052	HL
3416.	25	28						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00051	HL
3417.	25	29						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00052	HL
3418.	25	30						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00051	HL
3419.	25	31						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00052	HL
3420.								TEHTEC	S7675	rpri	A610MJLC	SG10CCAL00013	CL
3421.	25	32						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00051	HL
3422.	25	33						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00052	HL
3423.	25	34						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00051	HL
3424.	25	35						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00052	HL
3425.	25	36						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00051	HL
3426.								TEHTEC	S7675	rpri	A610MJLC	SG10CCAL00013	CL
27.	25	37						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00002	HL
28.	25	38						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00001	HL
29.	25	39						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00002	HL
3430.	25	40						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00001	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: A
 DATABASE: Harris_SGA_1995

Sep. 23.1995 15:21

PAGE 72 of 124

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG	
3431.	25	41						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00004	HL	
3432.								TEHTEC	N0698	rpri	A610MULC	SG10CCAL00001	CL	
3433.	25	42						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00003	HL	
3434.	25	43						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00004	HL	
3435.	25	44						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00003	HL	
3436.	25	45						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00004	HL	
3437.	25	46						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00003	HL	
3438.								TEHTEC	G1931	rpri	A610MULC	SG10CCAL00001	CL	
3439.	25	47						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00004	HL	
3440.	25	48						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00003	HL	
3441.	25	49						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00004	HL	
3442.	25	50						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00003	HL	
3443.	25	51						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00004	HL	
3444.								TEHTEC	G1931	rpri	A610MULC	SG10CCAL00001	CL	
3445.	25	52						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00003	HL	
3446.	25	53						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00004	HL	
3447.	25	54						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00003	HL	
3448.	25	55						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00003	HL	
3449.	25	56						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00003	HL	
3450.								TEHTEC	G1931	rpri	A610MULC	SG10CCAL00001	CL	
51.	25	59						TSHTSH	S7675	rpri	B620MRPC3C	SG11HCAL00039	HL	
?								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00009	CL	
3451.	25	60						TSHTSH	T7665	rpri	B620MRPC3C	SG11HCAL00038	HL	
3454.	25	61						TSHTSH	T7665	rpri	B620MRPC3C	SG11HCAL00038	HL	
3455.	25	62						TSHTSH	T7665	rpri	B620MRPC3C	SG11HCAL00038	HL	
3456.	25	63						TSHTSH	T7665	rpri	B620MRPC3C	SG11HCAL00038	HL	
3457.	25	64						TSHTSH	T7665	rpri	B620MRPC3C	SG11HCAL00038	HL	
3458.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00009	CL	
3459.	25	65						TSHTSH	T7665	rpri	B620MRPC3C	SG11HCAL00038	HL	
3460.	25	66						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00041	HL	
3461.	25	67						TSHTSH	T9924	rpri	B620MRPC3C	SG11HCAL00042	HL	
3462.	25	68						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00041	HL	
3463.	25	69						TSHTSH	T9924	rpri	B620MRPC3C	SG11HCAL00042	HL	
3464.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00009	CL	
3465.	25	70						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00041	HL	
3466.	25	71	0.45	88	POS	1	TSH	0.04	TSHTSH	F3453	reso	B620MRPC3C	SG11HCAL00042	HL
3467.			0.94	129	SCI	1	TSH	0.09	TSHTSH	C3335	reso	B620MRPC3C	SG11HCAL00044	HL
3468.					PID	1	TSH	0.09	TSHTSH	C3335	reso	B620MRPC3C	SG11HCAL00044	HL
3469.	25	72						TSHTSH	J9815	rsec	B620MRPC3C	SG11HCAL00041	HL	
3470.	25	73						TSHTSH	T9924	rpri	B620MRPC3C	SG11HCAL00042	HL	
3471.	25	74						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL	
3472.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00009	CL	
3473.	25	75						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL	
3474.	25	76						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL	
3475.	25	77						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL	
3476.	25	78						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL	
3477.	25	79						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL	
3478.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00009	CL	
3479.	25	80						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL	

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: A
 DATABASE: Harris_SGA_1995

Sep. 23,1995 15:21

PAGE 73 of 124

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
3480.	25	81						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
3481.	25	82						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00020	HL
3482.	25	83						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00021	HL
3483.	25	84						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00020	HL
3484.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00006	CL
3485.	25	85						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00021	HL
3486.	25	86						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00020	HL
3487.	25	87						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00021	HL
3488.	25	88						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00020	HL
3489.	25	89						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00021	HL
3490.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00006	CL
3491.	25	90						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00020	HL
3492.	25	91						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00021	HL
3493.	25	92						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00020	HL
3494.	25	93						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00021	HL
3495.	25	94						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00014	HL
3496.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00005	CL
3497.	25	95						TSHTSH	J9815	rsec	B620MRPC3C	SG11HCAL00015	HL
3498.	25	96						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00014	HL
3499.	25	97						TSHTSH	J9815	rsec	B620MRPC3C	SG11HCAL00015	HL
00.	25	98						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00014	HL
.	25	99						TSHTSH	J9815	rsec	B620MRPC3C	SG11HCAL00015	HL
.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00005	CL
3503.	25	100						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00014	HL
3504.	25	101						TSHTSH	J9815	rsec	B620MRPC3C	SG11HCAL00015	HL
3505.	25	102						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00014	HL
3506.	25	103						TSHTSH	J9815	rsec	B620MRPC3C	SG11HCAL00015	HL
3507.	25	104						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00016	HL
3508.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00005	CL
3509.	25	105						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00017	HL
3510.	25	106						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00016	HL
3511.	25	107						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00017	HL
3512.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00005	CL
3513.	25	108						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00016	HL
3514.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00005	CL
3515.	26	8						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00050	HL
3516.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00013	CL
3517.	26	9						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00049	HL
3518.	26	10						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00050	HL
3519.	26	11						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00049	HL
3520.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00013	CL
3521.	26	12						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00050	HL
3522.	26	13						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00049	HL
3523.	26	14						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00050	HL
3524.	26	15						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00049	HL
3525.	26	16						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00050	HL
3526.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00013	CL
3527.	26	17						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00049	HL
3528.	26	18						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00050	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: A
 DATABASE: Harris_SGA_1995

Sep. 23,1995 15:21

PAGE 74 of 124



ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
3529.	26	19					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00049	HL
3530.	26	20					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00050	HL
3531.	26	21					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00049	HL
3532.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00013	CL
3533.	26	22					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00052	HL
3534.	26	23					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00051	HL
3535.	26	24					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00052	HL
3536.	26	25					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00051	HL
3537.	26	26					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00052	HL
3538.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00013	CL
3539.	26	27					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00051	HL
3540.	26	28					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00052	HL
3541.	26	29					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00051	HL
3542.	26	30					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00052	HL
3543.	26	31					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00051	HL
3544.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00013	CL
3545.	26	32					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00052	HL
3546.	26	33					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00051	HL
3547.	26	34					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00052	HL
3548.	26	35					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00051	HL
49.	26	36					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00051	HL
50.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00013	CL
51.	26	37					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00002	HL
3552.	26	38					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00001	HL
3553.	26	39					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00002	HL
3554.	26	40					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00001	HL
3555.	26	41					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00004	HL
3556.							TEHTEC	N0698	rpri	A610MULC	SG10CCAL00001	CL
3557.	26	42					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00003	HL
3558.	26	43					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00004	HL
3559.	26	44					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00003	HL
3560.	26	45					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00004	HL
3561.	26	46					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00003	HL
3562.							TEHTEC	G1931	rpri	A610MULC	SG10CCAL00001	CL
3563.	26	47					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00004	HL
3564.	26	48					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00003	HL
3565.	26	49					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00004	HL
3566.	26	50					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00003	HL
3567.	26	51					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00004	HL
3568.							TEHTEC	G1931	rpri	A610MULC	SG10CCAL00001	CL
3569.	26	52					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00003	HL
3570.	26	53					TSHTSH	J9815	rsec	B620MRPC3C	SG11HCAL00004	HL
3571.	26	54					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00003	HL
3572.	26	55					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00003	HL
3573.	26	56					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00003	HL
74.							TEHTEC	G1931	rpri	A610MULC	SG10CCAL00001	CL
75.	26	59					TSHTSH	T7665	rpri	B620MRPC3C	SG11HCAL00038	HL
75.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00009	CL
77.	26	60					TSHTSH	S7675	rpri	B620MRPC3C	SG11HCAL00039	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: A
 DATABASE: Harris_SGA_1995

Sep. 23,1995 15:21

PAGE 75 of 124

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
3578.	26	61					TSHTSH	S7675	rpri	B620MRPC3C	SG11HCAL00039	HL
3579.	26	62					TSHTSH	S7675	rpri	B620MRPC3C	SG11HCAL00039	HL
3580.	26	63					TSHTSH	S7675	rpri	B620MRPC3C	SG11HCAL00039	HL
3581.	26	64					TSHTSH	S7675	rpri	B620MRPC3C	SG11HCAL00039	HL
3582.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00009	CL
3583.	26	65					TSHTSH	G1931	rpri	B620MRPC3C	SG11HCAL00039	HL
3584.	26	66					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00041	HL
3585.	26	67					TSHTSH	T9924	rpri	B620MRPC3C	SG11HCAL00042	HL
3586.	26	68					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00041	HL
3587.	26	69					TSHTSH	T9924	rpri	B620MRPC3C	SG11HCAL00042	HL
3588.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00009	CL
3589.	26	70					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00041	HL
3590.	26	71					TSHTSH	T9924	rpri	B620MRPC3C	SG11HCAL00042	HL
3591.	26	72					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00041	HL
3592.	26	73					TSHTSH	T9924	rpri	B620MRPC3C	SG11HCAL00042	HL
3593.	26	74					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
3594.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00009	CL
3595.	26	75					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
3596.	26	76					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
3597.	26	77					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
3598.	26	78					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
3599.	26	79					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
3600.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00009	CL
3601.	26	80					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
3602.	26	81					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
3603.	26	82					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00020	HL
3604.	26	83					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00021	HL
3605.	26	84					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00020	HL
3606.							TEHTEC	F2217	rpri	A610MULC	SG10CCAL00006	CL
3607.	26	85					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00021	HL
3608.	26	86					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00020	HL
3609.	26	87					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00021	HL
3610.							TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00021	HL
3611.	26	88					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00020	HL
3612.	26	89					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00021	HL
3613.							TEHTEC	F2217	rpri	A610MULC	SG10CCAL00006	CL
3614.	26	90					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00020	HL
3615.	26	91					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00021	HL
3616.	26	92					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00020	HL
3617.	26	93					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00021	HL
3618.	26	94					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00014	HL
3619.							TEHTEC	F2217	rpri	A610MULC	SG10CCAL00005	CL
3620.	26	95					TSHTSH	J9815	rsec	B620MRPC3C	SG11HCAL00015	HL
3621.	26	96					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00014	HL
3622.	26	97					TSHTSH	J9815	rsec	B620MRPC3C	SG11HCAL00015	HL
3623.	26	98					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00014	HL
3624.	26	99					TSHTSH	J9815	rsec	B620MRPC3C	SG11HCAL00015	HL
3625.							TEHTEC	F2217	rpri	A610MULC	SG10CCAL00005	CL
3626.	26	100					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00014	HL

*** INSPECTION FINAL REPORT LISTING ***

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: A
 DATABASE: Harris_SGA_1995

Sep. 23, 1995 15:21

PAGE 76 of 124

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG	
3627.	26	101						TSHTSH	J9815	rsec	B620MRPC3C	SG11HCAL00015	HL	
3628.	26	102						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00014	HL	
3629.	26	103						TSHTSH	J9815	rsec	B620MRPC3C	SG11HCAL00015	HL	
3630.	26	104						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00016	HL	
3631.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00005	CL	
3632.	26	105						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00017	HL	
3633.	26	106						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00016	HL	
3634.	26	107						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00017	HL	
3635.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00005	CL	
3636.	27	8						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00050	HL	
3637.			11.68	183	DNT	P1	AV2	0.00	TEHTEC	S7675	rpri	A610MULC	SG10CCAL00013	CL
3638.	27	9						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00049	HL	
3639.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00013	CL	
3640.	27	10						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00050	HL	
3641.	27	11						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00049	HL	
3642.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00013	CL	
3643.	27	12						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00050	HL	
3644.	27	13						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00049	HL	
3645.	27	14						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00050	HL	
3646.	27	15						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00049	HL	
47.	27	16						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00050	HL	
49.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00013	CL	
50.	27	17						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00049	HL	
3650.	27	18						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00050	HL	
3651.	27	19						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00049	HL	
3652.	27	20						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00050	HL	
3653.	27	21						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00049	HL	
3654.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00013	CL	
3655.	27	22						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00052	HL	
3656.	27	23						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00051	HL	
3657.	27	24						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00052	HL	
3658.	27	25						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00051	HL	
3659.	27	26						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00052	HL	
3660.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00013	CL	
3661.	27	27						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00051	HL	
3662.	27	28						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00052	HL	
3663.	27	29						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00051	HL	
3664.	27	30						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00052	HL	
3665.	27	31						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00051	HL	
3666.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00013	CL	
3667.	27	32						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00052	HL	
3668.	27	33						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00051	HL	
3669.	27	34						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00052	HL	
3670.	27	35						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00051	HL	
3671.	27	36						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00051	HL	
72.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00013	CL	
73.	27	37						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00002	HL	
74.	27	38						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00001	HL	
75.	27	39						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00002	HL	

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: A
 DATABASE: Harris_SGA_1995

Sep. 23.1995 15:21

PAGE 77 of 124

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
3676.	27	40						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00001	HL
3677.	27	41						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00004	HL
3678.								TEHTEC	N0698	rpri	A610MULC	SG10CCAL00001	CL
3679.	27	42						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00003	HL
3680.	27	43						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00004	HL
3681.	27	44						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00003	HL
3682.	27	45						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00004	HL
3683.	27	46						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00003	HL
3684.								TEHTEC	G1931	rpri	A610MULC	SG10CCAL00001	CL
3685.	27	47						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00004	HL
3686.	27	48						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00003	HL
3687.	27	49						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00004	HL
3688.	27	50						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00003	HL
3689.	27	51						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00004	HL
3690.								TEHTEC	G1931	rpri	A610MULC	SG10CCAL00001	CL
3691.	27	52						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00003	HL
3692.	27	53						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00004	HL
3693.	27	54						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00003	HL
3694.	27	55						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00003	HL
3695.	27	56						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00003	HL
96.								TEHTEC	G1931	rpri	A610MULC	SG10CCAL00001	CL
97.	27	59						TSHTSH	S7675	rpri	B620MRPC3C	SG11HCAL00039	HL
98.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00009	CL
3699.	27	60						TSHTSH	T7665	rpri	B620MRPC3C	SG11HCAL00038	HL
3700.	27	61						TSHTSH	T7665	rpri	B620MRPC3C	SG11HCAL00038	HL
3701.	27	62						TSHTSH	T7665	rpri	B620MRPC3C	SG11HCAL00038	HL
3702.	27	63						TSHTSH	T7665	rpri	B620MRPC3C	SG11HCAL00038	HL
3703.	27	64						TSHTSH	T7665	rpri	B620MRPC3C	SG11HCAL00038	HL
3704.			0.98	151	M8M	1	05C 15.74	TEHTEC	S7675	rpri	A610MULC	SG10CCAL00009	CL
3705.	27	65						TSHTSH	T7665	rpri	B620MRPC3C	SG11HCAL00038	HL
3706.	27	66						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00041	HL
3707.	27	67						TSHTSH	T9924	rpri	B620MRPC3C	SG11HCAL00042	HL
3708.	27	68						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00041	HL
3709.	27	69						TSHTSH	T9924	rpri	B620MRPC3C	SG11HCAL00042	HL
3710.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00009	CL
3711.	27	70						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00041	HL
3712.	27	71						TSHTSH	T9924	rpri	B620MRPC3C	SG11HCAL00042	HL
3713.	27	72						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
3714.	27	73						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
3715.	27	74						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
3716.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00009	CL
3717.	27	75						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
3718.	27	76						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
3719.	27	77						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
3720.	27	78						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
3721.	27	79						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
3722.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00009	CL
3723.	27	80						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
3724.	27	81						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: A
 DATABASE: Harris_SGA_1995

Sep. 23,1995 15:21

PAGE 78 of 124

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG	
3725.	27	82						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00020	HL	
3726.	27	83						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00021	HL	
3727.	27	84						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00020	HL	
3728.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00006	CL	
3729.	27	85						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00021	HL	
3730.	27	86						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00020	HL	
3731.	27	87						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00021	HL	
3732.	27	88						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00020	HL	
3733.	27	89						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00021	HL	
3734.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00006	CL	
3735.	27	90						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00020	HL	
3736.	27	91						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00021	HL	
3737.	27	92						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00020	HL	
3738.	27	93						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00021	HL	
3739.	27	94						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00014	HL	
3740.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00005	CL	
3741.	27	95						TSHTSH	J9815	rsec	B620MRPC3C	SG11HCAL00015	HL	
3742.	27	96						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00014	HL	
3743.	27	97						TSHTSH	J9815	rsec	B620MRPC3C	SG11HCAL00015	HL	
3744.	27	98						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00014	HL	
45.	27	99						TSHTSH	J9815	rsec	B620MRPC3C	SG11HCAL00015	HL	
								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00005	CL	
	27	100						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00014	HL	
3748.	27	101						TSHTSH	J9815	rsec	B620MRPC3C	SG11HCAL00015	HL	
3749.	27	102						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00014	HL	
3750.	27	103						TSHTSH	J9815	rsec	B620MRPC3C	SG11HCAL00015	HL	
3751.	27	104						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00016	HL	
3752.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00005	CL	
3753.	27	105						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00017	HL	
3754.	27	106						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00016	HL	
3755.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00005	CL	
3756.	27	107						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00017	HL	
3757.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00005	CL	
3758.	28	9						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00050	HL	
3759.			8.53	184	DNT	P1	AV2	0.00	TEHTEC	S7675	rpri	A610MULC	SG10CCAL00013	CL
3760.	28	10						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00049	HL	
3761.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00013	CL	
3762.	28	11						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00050	HL	
3763.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00013	CL	
3764.	28	12						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00049	HL	
3765.	28	13						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00050	HL	
3766.	28	14						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00049	HL	
3767.	28	15						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00050	HL	
3768.	28	16						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00049	HL	
3769.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00013	CL	
770.	28	17						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00050	HL	
771.	28	18						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00049	HL	
772.	28	19						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00050	HL	
773.	28	20						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00049	HL	

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: A
 DATABASE: Harris_SGA_1995

Sep. 23.1995 15:21

PAGE 79 of 124

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
3774.	28	21					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00052	HL
3775.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00013	CL
3776.	28	22					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00051	HL
3777.	28	23					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00052	HL
3778.	28	24					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00051	HL
3779.	28	25					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00052	HL
3780.	28	26					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00051	HL
3781.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00013	CL
3782.	28	27					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00052	HL
3783.	28	28					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00051	HL
3784.	28	29					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00052	HL
3785.	28	30					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00051	HL
3786.	28	31					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00052	HL
3787.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00013	CL
3788.	28	32					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00051	HL
3789.	28	33					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00052	HL
3790.	28	34					01HTSH	J9815	rsec	B620MRPC3C	SG11HCAL00051	HL
3791.	28	35					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00052	HL
3792.	28	36					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00051	HL
3793.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00013	CL
94.	28	37					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00002	HL
95.	28	38					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00001	HL
96.	28	39					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00002	HL
3797.	28	40					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00001	HL
3798.	28	41					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00004	HL
3799.							TEHTEC	N0698	rpri	A610MULC	SG10CCAL00001	CL
3800.	28	42					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00003	HL
3801.	28	43					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00004	HL
3802.	28	44					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00003	HL
3803.	28	45					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00004	HL
3804.	28	46					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00003	HL
3805.							TEHTEC	G1931	rpri	A610MULC	SG10CCAL00001	CL
3806.	28	47					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00004	HL
3807.	28	48					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00003	HL
3808.	28	49					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00004	HL
3809.	28	50					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00003	HL
3810.	28	51					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00004	HL
3811.							TEHTEC	G1931	rpri	A610MULC	SG10CCAL00001	CL
3812.	28	52					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00003	HL
3813.	28	53					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00004	HL
3814.	28	54					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00003	HL
3815.	28	55					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00003	HL
3816.	28	56					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00003	HL
3817.							TEHTEC	G1931	rpri	A610MULC	SG10CCAL00001	CL
3818.	28	59					TSHTSH	T7665	rpri	B620MRPC3C	SG11HCAL00038	HL
3819.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00009	CL
3820.	28	60					TSHTSH	S7675	rpri	B620MRPC3C	SG11HCAL00039	HL
3821.	28	61					TSHTSH	S7675	rpri	B620MRPC3C	SG11HCAL00039	HL
3822.	28	62					TSHTSH	S7675	rpri	B620MRPC3C	SG11HCAL00039	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: A
 DATABASE: Harris_SGA_1995

Sep. 23,1995 15:21

PAGE 80 of 124

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
3823.	28	63					TSHTSH	S7675	rpri	B620MRPC3C	SG11HCAL00039	HL
3824.	28	64					TSHTSH	G1931	rpri	B620MRPC3C	SG11HCAL00039	HL
3825.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00009	CL
3826.	28	65					TSHTSH	G1931	rpri	B620MRPC3C	SG11HCAL00039	HL
3827.	28	66					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00041	HL
3828.	28	67					TSHTSH	T9924	rpri	B620MRPC3C	SG11HCAL00042	HL
3829.	28	68					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00041	HL
3830.	28	69					TSHTSH	T9924	rpri	B620MRPC3C	SG11HCAL00042	HL
3831.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00009	CL
3832.	28	70					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00041	HL
3833.	28	71					TSHTSH	T9924	rpri	B620MRPC3C	SG11HCAL00042	HL
3834.	28	72					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
3835.	28	73					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
3836.	28	74					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
3837.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00009	CL
3838.	28	75					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
3839.	28	76					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
3840.	28	77					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
3841.	28	78					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
3842.	28	79					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
43.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00009	CL
44.	28	80					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
45.	28	81					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
3846.	28	82					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00020	HL
3847.	28	83					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00021	HL
3848.	28	84					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00020	HL
3849.							TEHTEC	F2217	rpri	A610MULC	SG10CCAL00006	CL
3850.	28	85					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00021	HL
3851.	28	86					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00020	HL
3852.	28	87					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00021	HL
3853.	28	88					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00020	HL
3854.	28	89					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00021	HL
3855.							TEHTEC	F7460	rsec	A610MULC	SG10CCAL00006	CL
3856.	28	90					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00020	HL
3857.	28	91					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00033	HL
3858.	28	92					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00020	HL
3859.	28	93					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00021	HL
3860.	28	94					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00014	HL
3861.							TEHTEC	F2217	rpri	A610MULC	SG10CCAL00005	CL
3862.	28	95					TSHTSH	J9815	rsec	B620MRPC3C	SG11HCAL00015	HL
3863.	28	96					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00014	HL
3864.	28	97					TSHTSH	J9815	rsec	B620MRPC3C	SG11HCAL00015	HL
3865.	28	98					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00014	HL
3866.	28	99					TSHTSH	J9815	rsec	B620MRPC3C	SG11HCAL00015	HL
3867.							TEHTEC	F2217	rpri	A610MULC	SG10CCAL00005	CL
3868.	28	100					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00014	HL
3869.	28	101					TSHTSH	J9815	rsec	B620MRPC3C	SG11HCAL00015	HL
3870.	28	102					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00014	HL
3871.	28	103					TSHTSH	J9815	rsec	B620MRPC3C	SG11HCAL00015	HL

*** INSPECTION FINAL REPORT LISTING ***

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: A
 DATABASE: Harris_SGA_1995

Sep. 23.1995 15:21

PAGE 81 of 124

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
3872.	28	104					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00016	HL
3873.							TEHTEC	F2217	rpri	A610MULC	SG10CCAL00005	CL
3874.	28	105					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00017	HL
3875.							TEHTEC	F2217	rpri	A610MULC	SG10CCAL00005	CL
3876.	28	106					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00016	HL
3877.							TEHTEC	F2217	rpri	A610MULC	SG10CCAL00005	CL
3878.	29	10					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00050	HL
3879.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00013	CL
3880.	29	11					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00049	HL
3881.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00013	CL
3882.	29	12					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00050	HL
3883.	29	13					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00049	HL
3884.	29	14					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00050	HL
3885.	29	15					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00049	HL
3886.	29	16					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00050	HL
3887.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00013	CL
3888.	29	17					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00049	HL
3889.	29	18					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00050	HL
3890.	29	19					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00049	HL
3891.	29	20					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00052	HL
92.	29	21					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00051	HL
93.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00013	CL
94.	29	22					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00052	HL
3895.	29	23					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00051	HL
3896.	29	24					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00052	HL
3897.	29	25					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00051	HL
3898.	29	26					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00052	HL
3899.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00013	CL
3900.	29	27					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00051	HL
3901.	29	28					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00052	HL
3902.	29	29					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00051	HL
3903.	29	30					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00052	HL
3904.	29	31					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00051	HL
3905.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00013	CL
3906.	29	32					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00052	HL
3907.	29	33					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00051	HL
3908.	29	34					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00052	HL
3909.	29	35					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00051	HL
3910.	29	36					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00051	HL
3911.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00013	CL
3912.	29	37					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00002	HL
3913.	29	38					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00001	HL
3914.	29	39					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00002	HL
3915.	29	40					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00001	HL
3916.	29	41					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00004	HL
3917.							TEHTEC	N0698	rpri	A610MULC	SG10CCAL00001	CL
3918.	29	42					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00003	HL
3919.	29	43					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00004	HL
3920.	29	44					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00003	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: A
 DATABASE: Harris_SGA_1995

Sep. 23,1995 15:21

PAGE 82 of 124

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
3921.	29	45						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00004	HL
3922.	29	46						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00003	HL
3923.								TEHTEC	G1931	rpri	A610MULC	SG10CCAL00001	CL
3924.	29	47						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00004	HL
3925.	29	48						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00003	HL
3926.	29	49						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00004	HL
3927.	29	50						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00003	HL
3928.	29	51						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00004	HL
3929.								TEHTEC	G1931	rpri	A610MULC	SG10CCAL00001	CL
3930.	29	52						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00003	HL
3931.	29	53						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00004	HL
3932.	29	54						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00003	HL
3933.	29	55						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00003	HL
3934.	29	56						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00003	HL
3935.								TEHTEC	G1931	rpri	A610MULC	SG10CCAL00001	CL
3936.	29	59						TSHTSH	S7675	rpri	B620MRPC3C	SG11HCAL00039	HL
3937.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00009	CL
3938.	29	60						TSHTSH	T7665	rpri	B620MRPC3C	SG11HCAL00038	HL
3939.	29	61						TSHTSH	T7665	rpri	B620MRPC3C	SG11HCAL00038	HL
3940.	29	62						TSHTSH	T7665	rpri	B620MRPC3C	SG11HCAL00038	HL
41.	29	63						TSHTSH	T7665	rpri	B620MRPC3C	SG11HCAL00038	HL
42.	29	64						TSHTSH	T7665	rpri	B620MRPC3C	SG11HCAL00038	HL
43.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00009	CL
3944.	29	65						TSHTSH	T7665	rpri	B620MRPC3C	SG11HCAL00038	HL
3945.	29	66						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00041	HL
3946.	29	67						TSHTSH	T9924	rpri	B620MRPC3C	SG11HCAL00042	HL
3947.	29	68						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00041	HL
3948.	29	69						TSHTSH	T9924	rpri	B620MRPC3C	SG11HCAL00042	HL
3949.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00009	CL
3950.	29	70						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00041	HL
3951.	29	71						TSHTSH	T9924	rpri	B620MRPC3C	SG11HCAL00042	HL
3952.	29	72						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
3953.		0.40		INR	1	03H	29.09	TEHTEC	M9082	rsec	A610MULC	SG10CCAL00009	CL
3954.	29	73						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
3955.	29	74						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
3956.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00009	CL
3957.	29	75						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
3958.	29	76						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
3959.	29	77						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
3960.	29	78						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
3961.	29	79						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
3962.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00009	CL
3963.	29	80						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
3964.	29	81						TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
3965.	29	82						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00020	HL
3966.	29	83						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00021	HL
3967.	29	84			RBD			TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00020	HL
3968.								TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00033	HL
3969.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00006	CL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: A
 DATABASE: Harris_SGA_1995

Sep. 23,1995 15:21

PAGE 83 of 124

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
3970.	29	85						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00021	HL
3971.	29	86						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00020	HL
3972.	29	87						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00021	HL
3973.	29	88						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00020	HL
3974.	29	89						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00021	HL
3975.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00006	CL
3976.	29	90						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00020	HL
3977.	29	91						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00021	HL
3978.	29	92						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00020	HL
3979.	29	93						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00021	HL
3980.	29	94						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00014	HL
3981.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00005	CL
3982.	29	95						TSHTSH	J9815	rsec	B620MRPC3C	SG11HCAL00015	HL
3983.	29	96						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00014	HL
3984.	29	97						TSHTSH	J9815	rsec	B620MRPC3C	SG11HCAL00015	HL
3985.	29	98						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00014	HL
3986.	29	99						TSHTSH	J9815	rsec	B620MRPC3C	SG11HCAL00015	HL
3987.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00005	CL
3988.	29	100						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00014	HL
3989.	29	101						TSHTSH	J9815	rsec	B620MRPC3C	SG11HCAL00015	HL
90.	29	102						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00014	HL
91.	29	103						TSHTSH	J9815	rsec	B620MRPC3C	SG11HCAL00015	HL
92.	29	104						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00016	HL
3993.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00005	CL
3994.	29	105						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00017	HL
3995.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00005	CL
3996.	30	10						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00050	HL
3997.		15.21	185	DNT	P1	AV2	0.00	TEHTEC	S7675	rpri	A610MULC	SG10CCAL00013	CL
3998.		7.37	185	DNT	P1	AV3	0.00	TEHTEC	S7675	rpri	A610MULC	SG10CCAL00013	CL
3999.	30	11						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00049	HL
4000.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00013	CL
4001.	30	12						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00050	HL
4002.	30	13						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00049	HL
4003.	30	14						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00050	HL
4004.	30	15						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00049	HL
4005.	30	16						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00050	HL
4006.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00013	CL
4007.	30	17						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00049	HL
4008.	30	18						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00050	HL
4009.	30	19						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00049	HL
4010.	30	20						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00052	HL
4011.	30	21						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00051	HL
4012.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00013	CL
4013.	30	22						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00052	HL
4014.	30	23						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00051	HL
4015.	30	24						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00052	HL
4016.	30	25						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00051	HL
4017.	30	26						TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00052	HL
4018.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00013	CL



**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: A
 DATABASE: Harris_SGA_1995

Sep. 23.1995 15:21

PAGE 84 of 124



ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
4019.	30	27					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00051	HL
4020.	30	28					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00052	HL
4021.	30	29					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00051	HL
4022.	30	30					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00052	HL
4023.	30	31					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00051	HL
4024.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00013	CL
4025.	30	32					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00052	HL
4026.	30	33					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00051	HL
4027.	30	34					TSHTSH	05305	rpri	B620MRPC3C	SG11HCAL00052	HL
4028.	30	35					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00051	HL
4029.	30	36					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00051	HL
4030.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00013	CL
4031.	30	37					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00002	HL
4032.	30	38					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00001	HL
4033.	30	39					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00002	HL
4034.	30	40					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00001	HL
4035.	30	41					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00004	HL
4036.							TEHTEC	N0698	rpri	A610MULC	SG10CCAL00001	CL
4037.	30	42					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00003	HL
4038.	30	43					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00004	HL
J39.	30	44					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00003	HL
4039.	30	45					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00004	HL
4040.	30	46					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00003	HL
4041.							TEHTEC	N0698	rpri	A610MULC	SG10CCAL00001	CL
4042.							TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00004	HL
4043.	30	47					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00003	HL
4044.	30	48					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00004	HL
4045.	30	49					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00004	HL
4046.	30	50					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00003	HL
4047.	30	51					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00004	HL
4048.							TEHTEC	G1931	rpri	A610MULC	SG10CCAL00001	CL
4049.	30	52					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00003	HL
4050.	30	53					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00004	HL
4051.	30	54					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00003	HL
4052.	30	55					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00003	HL
4053.	30	56					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00003	HL
4054.							TEHTEC	G1931	rpri	A610MULC	SG10CCAL00001	CL
4055.	30	59					TSHTSH	T7665	rpri	B620MRPC3C	SG11HCAL00038	HL
4056.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00009	CL
4057.	30	60					TSHTSH	T7665	rpri	B620MRPC3C	SG11HCAL00038	HL
4058.	30	61					TSHTSH	T7665	rpri	B620MRPC3C	SG11HCAL00038	HL
4059.	30	62					TSHTSH	T7665	rpri	B620MRPC3C	SG11HCAL00038	HL
4060.	30	63					TSHTSH	T7665	rpri	B620MRPC3C	SG11HCAL00038	HL
4061.	30	64					TSHTSH	T7665	rpri	B620MRPC3C	SG11HCAL00038	HL
4062.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00009	CL
4063.	30	65					TSHTSH	T7665	rpri	B620MRPC3C	SG11HCAL00038	HL
4064.	30	66					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00041	HL
4065.	30	67					TSHTSH	T9924	rpri	B620MRPC3C	SG11HCAL00042	HL
4066.	30	68					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00041	HL
4067.	30	69					TSHTSH	T9924	rpri	B620MRPC3C	SG11HCAL00042	HL

*** INSPECTION FINAL REPORT LISTING ***

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: A
 DATABASE: Harris_SGA_1995

Sep. 23.1995 15:21

PAGE 85 of 124

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
4068.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00009	CL
4069.	30	70					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00041	HL
4070.	30	71					TSHTSH	T9924	rpri	B620MRPC3C	SG11HCAL00042	HL
4071.	30	72					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
4072.	30	73					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
4073.	30	74					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
4074.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00009	CL
4075.	30	75					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
4076.	30	76					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
4077.	30	77					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
4078.	30	78					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
4079.	30	79					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
4080.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00009	CL
4081.	30	80					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00043	HL
4082.	30	81					TSHTSH	T7072	rpri	B620MRPC3C	SG11HCAL00044	HL
4083.	30	82					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00020	HL
4084.	30	83					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00021	HL
4085.	30	84					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00020	HL
4086.							TEHTEC	F2217	rpri	A610MULC	SG10CCAL00006	CL
4087.	30	85					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00021	HL
88.	30	86					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00020	HL
89.	30	87					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00021	HL
90.	30	88					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00020	HL
4091.	30	89					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00021	HL
4092.							TEHTEC	F2217	rpri	A610MULC	SG10CCAL00006	CL
4093.	30	90					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00020	HL
4094.	30	91					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00021	HL
4095.	30	92					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00020	HL
4096.	30	93					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00021	HL
4097.	30	94					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00014	HL
4098.							TEHTEC	F2217	rpri	A610MULC	SG10CCAL00005	CL
4099.	30	95					TSHTSH	J9815	rsec	B620MRPC3C	SG11HCAL00015	HL
4100.	30	96					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00014	HL
4101.	30	97					TSHTSH	J9815	rsec	B620MRPC3C	SG11HCAL00015	HL
4102.	30	98					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00014	HL
4103.	30	99					TSHTSH	J9815	rsec	B620MRPC3C	SG11HCAL00015	HL
4104.							TEHTEC	F2217	rpri	A610MULC	SG10CCAL00005	CL
4105.	30	100					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00014	HL
4106.	30	101					TSHTSH	J9815	rsec	B620MRPC3C	SG11HCAL00015	HL
4107.	30	102					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00014	HL
4108.	30	103					TSHTSH	J9815	rsec	B620MRPC3C	SG11HCAL00015	HL
4109.	30	104					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00016	HL
4110.							TEHTEC	F2217	rpri	A610MULC	SG10CCAL00005	CL
4111.	30	105					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00017	HL
4112.							TEHTEC	F2217	rpri	A610MULC	SG10CCAL00005	CL
113.	31	11					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00048	HL
114.							TEHTEC	F2217	rpri	A610MULC	SG10CCAL00011	CL
115.	31	12					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00047	HL
116.							TEHTEC	F2217	rpri	A610MULC	SG10CCAL00011	CL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: A
 DATABASE: Harris_SGA_1995

Sep. 23.1995 15:21

PAGE 86 of 124

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE	SIZE	CAL GROUP	LEG
4117.	31	13						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00048	HL	
4118.	31	14						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00047	HL	
4119.	31	15						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00048	HL	
4120.	31	16						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00047	HL	
4121.					RBD				H3464	rsec	A610MULC	SG10CCAL00012	CL	
4122.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00016	CL	
4123.	31	17						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00048	HL	
4124.	31	18						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00047	HL	
4125.	31	19						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00048	HL	
4126.	31	20						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00047	HL	
4127.	31	21						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00048	HL	
4128.					RBD				H3464	rsec	A610MULC	SG10CCAL00012	CL	
4129.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00016	CL	
4130.	31	22						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00047	HL	
4131.	31	23						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00048	HL	
4132.	31	24						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00047	HL	
4133.	31	25						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00050	HL	
4134.	31	26						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00049	HL	
4135.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00013	CL	
4136.	31	27						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00050	HL	
4137.	31	28						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00049	HL	
4138.	31	29						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00050	HL	
4139.	31	30						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00049	HL	
4140.	31	31						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00050	HL	
4141.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00013	CL	
4142.	31	32						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00049	HL	
4143.	31	33						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00050	HL	
4144.	31	34						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00049	HL	
4145.	31	35						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00050	HL	
4146.	31	36						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00049	HL	
4147.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00013	CL	
4148.	31	37						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00034	HL	
4149.	31	38						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00033	HL	
4150.	31	39						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00034	HL	
4151.	31	40						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00033	HL	
4152.	31	41						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00034	HL	
4153.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00009	CL	
4154.	31	42						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00033	HL	
4155.	31	43						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00034	HL	
4156.	31	44						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00033	HL	
4157.	31	45						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00034	HL	
4158.	31	46						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00033	HL	
4159.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00009	CL	
4160.	31	47						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00034	HL	
4161.	31	48						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00033	HL	
4162.	31	49						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00034	HL	
4163.	31	50						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00033	HL	
4164.	31	51						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00034	HL	
4165.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00009	CL	

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: A
 DATABASE: Harris_SGA_1995

Sep. 23, 1995 15:21

PAGE 87 of 124

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
4166.	31	52						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00033	HL
4167.	31	53						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00034	HL
4168.	31	54						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00033	HL
4169.	31	55						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00034	HL
4170.	31	56						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00033	HL
4171.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00009	CL
4172.	31	59						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00025	HL
4173.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00007	CL
4174.	31	60						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00026	HL
4175.	31	61						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00025	HL
4176.	31	62						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00026	HL
4177.	31	63						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00025	HL
4178.	31	64						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00026	HL
4179.		1.43		30	P2	AV2	0.51	TEHTEC	F2217	rpri	A610MULC	SG10CCAL00007	CL
4180.	31	65						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00025	HL
4181.	31	66						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00026	HL
4182.	31	67						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00025	HL
4183.	31	68						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00026	HL
4184.	31	69						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00025	HL
4185.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00007	CL
4186.	31	70						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00026	HL
4187.	31	71						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00025	HL
4188.	31	72						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00026	HL
4189.	31	73						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00025	HL
4190.	31	74						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00026	HL
4191.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00007	CL
4192.	31	75						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00025	HL
4193.	31	76						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00026	HL
4194.	31	77						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00025	HL
4195.	31	78						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00026	HL
4196.	31	79						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00025	HL
4197.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00007	CL
4198.	31	80						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00026	HL
4199.	31	81						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00027	HL
4200.	31	82						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00018	HL
4201.	31	83						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00019	HL
4202.	31	84						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00018	HL
4203.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00006	CL
4204.	31	85						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00019	HL
4205.	31	86						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00018	HL
4206.	31	87						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00019	HL
4207.	31	88						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00018	HL
4208.	31	89						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00019	HL
4209.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00006	CL
4210.	31	90						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00018	HL
4211.	31	91						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00019	HL
4212.	31	92						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00018	HL
4213.	31	93						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00019	HL
4214.	31	94						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00016	HL

*** INSPECTION FINAL REPORT LISTING ***

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: A
 DATABASE: Harris_SGA_1995

Sep. 23.1995 15:21

PAGE 88 of 124

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
4215.							TEHTEC	F2217	rpri	A610MULC	SG10CCAL00005	CL
4216.	31	95					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00017	HL
4217.	31	96					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00016	HL
4218.	31	97					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00017	HL
4219.	31	98					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00016	HL
4220.	31	99					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00017	HL
4221.							TEHTEC	F2217	rpri	A610MULC	SG10CCAL00006	CL
4222.	31	100					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00016	HL
4223.	31	101			RBD			F3453	reso	B620MRPC3C	SG11HCAL00017	HL
4224.							TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00033	HL
4225.	31	102					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00016	HL
4226.	31	103					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00017	HL
4227.							TEHTEC	F2217	rpri	A610MULC	SG10CCAL00006	CL
4228.	31	104					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00019	HL
4229.							TEHTEC	F2217	rpri	A610MULC	SG10CCAL00006	CL
4230.	32	12					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00048	HL
4231.							TEHTEC	F2217	rpri	A610MULC	SG10CCAL00011	CL
4232.	32	13					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00047	HL
4233.	32	14					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00048	HL
4234.	32	15					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00047	HL
4235.	32	16					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00048	HL
4236.					RBD			H3464	rsec	A610MULC	SG10CCAL00012	CL
4237.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00016	CL
4238.	32	17					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00047	HL
4239.	32	18					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00048	HL
4240.	32	19					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00047	HL
4241.	32	20					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00048	HL
4242.	32	21					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00047	HL
4243.					RBD			H3464	rsec	A610MULC	SG10CCAL00012	CL
4244.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00016	CL
4245.	32	22					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00048	HL
4246.	32	23					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00047	HL
4247.	32	24					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00048	HL
4248.	32	25					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00047	HL
4249.	32	26					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00050	HL
4250.							TEHTEC	F2217	rpri	A610MULC	SG10CCAL00013	CL
4251.	32	27					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00049	HL
4252.	32	28					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00050	HL
4253.	32	29					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00049	HL
4254.	32	30					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00050	HL
4255.	32	31					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00049	HL
4256.							TEHTEC	F2217	rpri	A610MULC	SG10CCAL00013	CL
4257.	32	32					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00050	HL
4258.	32	33					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00049	HL
4259.	32	34					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00050	HL
4260.	32	35					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00049	HL
4261.	32	36					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00049	HL
4262.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00013	CL
4263.	32	37					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00034	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: A
 DATABASE: Harris_SGA_1995

Sep. 23,1995 15:21

PAGE 89 of 124

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG	
4264.	32	38						TSHTSH	85534	rpr1	B620MRPC3C	SG11HCAL00033	HL	
4265.	32	39						TSHTSH	85534	rpr1	B620MRPC3C	SG11HCAL00034	HL	
4266.	32	40						TSHTSH	85534	rpr1	B620MRPC3C	SG11HCAL00033	HL	
4267.	32	41						TSHTSH	85534	rpr1	B620MRPC3C	SG11HCAL00034	HL	
4268.								TEHTEC	S7675	rpr1	A610MULC	SG10CCAL00009	CL	
4269.	32	42						TSHTSH	85534	rpr1	B620MRPC3C	SG11HCAL00033	HL	
4270.	32	43						TSHTSH	85534	rpr1	B620MRPC3C	SG11HCAL00034	HL	
4271.	32	44						TSHTSH	85534	rpr1	B620MRPC3C	SG11HCAL00033	HL	
4272.	32	45						TSHTSH	85534	rpr1	B620MRPC3C	SG11HCAL00034	HL	
4273.	32	46						TSHTSH	85534	rpr1	B620MRPC3C	SG11HCAL00033	HL	
4274.								TEHTEC	S7675	rpr1	A610MULC	SG10CCAL00009	CL	
4275.	32	47						TSHTSH	85534	rpr1	B620MRPC3C	SG11HCAL00034	HL	
4276.	32	48						TSHTSH	85534	rpr1	B620MRPC3C	SG11HCAL00033	HL	
4277.	32	49						TSHTSH	85534	rpr1	B620MRPC3C	SG11HCAL00034	HL	
4278.	32	50						TSHTSH	85534	rpr1	B620MRPC3C	SG11HCAL00033	HL	
4279.	32	51						TSHTSH	85534	rpr1	B620MRPC3C	SG11HCAL00034	HL	
4280.								TEHTEC	S7675	rpr1	A610MULC	SG10CCAL00009	CL	
4281.	32	52						TSHTSH	85534	rpr1	B620MRPC3C	SG11HCAL00033	HL	
4282.	32	53						TSHTSH	85534	rpr1	B620MRPC3C	SG11HCAL00034	HL	
4283.	32	54						TSHTSH	85534	rpr1	B620MRPC3C	SG11HCAL00033	HL	
4284.	32	55						TSHTSH	85534	rpr1	B620MRPC3C	SG11HCAL00034	HL	
4285.	32	56						TSHTSH	85534	rpr1	B620MRPC3C	SG11HCAL00033	HL	
4286.			5.21	182	DNT	1	02C	1.20	TEHTEC	S7675	rpr1	A610MULC	SG10CCAL00009	CL
4287.	32	59						TSHTSH	S7067	rpr1	B620MRPC3C	SG11HCAL00025	HL	
4288.								TEHTEC	F2217	rpr1	A610MULC	SG10CCAL00007	CL	
4289.	32	60						TSHTSH	S7067	rpr1	B620MRPC3C	SG11HCAL00026	HL	
4290.	32	61						TSHTSH	S7067	rpr1	B620MRPC3C	SG11HCAL00025	HL	
4291.	32	62						TSHTSH	S7067	rpr1	B620MRPC3C	SG11HCAL00026	HL	
4292.	32	63						TSHTSH	S7067	rpr1	B620MRPC3C	SG11HCAL00025	HL	
4293.	32	64						TSHTSH	S7067	rpr1	B620MRPC3C	SG11HCAL00026	HL	
4294.								TEHTEC	F2217	rpr1	A610MULC	SG10CCAL00007	CL	
4295.	32	65						TSHTSH	S7067	rpr1	B620MRPC3C	SG11HCAL00025	HL	
4296.	32	66						TSHTSH	S7067	rpr1	B620MRPC3C	SG11HCAL00026	HL	
4297.	32	67						TSHTSH	S7067	rpr1	B620MRPC3C	SG11HCAL00025	HL	
4298.	32	68						TSHTSH	S7067	rpr1	B620MRPC3C	SG11HCAL00026	HL	
4299.	32	69						TSHTSH	S7067	rpr1	B620MRPC3C	SG11HCAL00025	HL	
4300.								TEHTEC	F2217	rpr1	A610MULC	SG10CCAL00007	CL	
4301.	32	70						TSHTSH	S7067	rpr1	B620MRPC3C	SG11HCAL00026	HL	
4302.	32	71						TSHTSH	S7067	rpr1	B620MRPC3C	SG11HCAL00025	HL	
4303.	32	72						TSHTSH	S7067	rpr1	B620MRPC3C	SG11HCAL00026	HL	
4304.	32	73						TSHTSH	S7067	rpr1	B620MRPC3C	SG11HCAL00025	HL	
4305.	32	74						TSHTSH	S7067	rpr1	B620MRPC3C	SG11HCAL00026	HL	
4306.								TEHTEC	F2217	rpr1	A610MULC	SG10CCAL00007	CL	
4307.	32	75						TSHTSH	S7067	rpr1	B620MRPC3C	SG11HCAL00025	HL	
4308.	32	76						TSHTSH	S7067	rpr1	B620MRPC3C	SG11HCAL00026	HL	
4309.	32	77						TSHTSH	S7067	rpr1	B620MRPC3C	SG11HCAL00025	HL	
4310.	32	78						TSHTSH	S7067	rpr1	B620MRPC3C	SG11HCAL00026	HL	
4311.	32	79						TSHTSH	S7067	rpr1	B620MRPC3C	SG11HCAL00025	HL	
4312.								TEHTEC	F2217	rpr1	A610MULC	SG10CCAL00007	CL	

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: A
 DATABASE: Harris_SGA_1995

Sep. 23.1995 15:21

PAGE 90 of 124

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
4313.	32	80						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00026	HL
4314.	32	81						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00027	HL
4315.	32	82			RBD				B5534	rpri	B620MRPC3C	SG11HCAL00018	HL
4316.								TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00033	HL
4317.	32	83						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00019	HL
4318.	32	84						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00018	HL
4319.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00006	CL
4320.	32	85						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00019	HL
4321.	32	86						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00018	HL
4322.	32	87						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00019	HL
4323.	32	88						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00018	HL
4324.	32	89						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00019	HL
4325.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00006	CL
4326.	32	90						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00018	HL
4327.	32	91						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00019	HL
4328.	32	92						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00018	HL
4329.	32	93						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00019	HL
4330.	32	94						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00016	HL
4331.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00005	CL
4332.	32	95						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00017	HL
4333.	32	96						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00016	HL
4334.	32	97						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00017	HL
4335.	32	98						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00016	HL
4336.	32	99						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00017	HL
4337.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00006	CL
4338.	32	100						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00016	HL
4339.	32	101						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00017	HL
4340.	32	102						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00016	HL
4341.	32	103						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00017	HL
4342.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00006	CL
4343.	33	12						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00048	HL
4344.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00011	CL
4345.	33	13						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00047	HL
4346.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00011	CL
4347.	33	14						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00048	HL
4348.	33	15						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00047	HL
4349.	33	16						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00048	HL
4350.					RBD				H3464	rsec	A610MULC	SG10CCAL00012	CL
4351.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00016	CL
4352.	33	17						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00047	HL
4353.	33	18						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00048	HL
4354.	33	19						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00047	HL
4355.	33	20						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00048	HL
4356.	33	21						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00047	HL
4357.					RBD				H3464	rsec	A610MULC	SG10CCAL00012	CL
4358.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00016	CL
4359.	33	22						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00048	HL
4360.	33	23						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00047	HL
4361.	33	24						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00048	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: A
 DATABASE: Harris_SGA_1995

Sep. 23.1995 15:21

PAGE 91 of 124

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
4362.	33	25					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00047	HL
4363.	33	26					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00050	HL
4364.							TEHTEC	F2217	rpri	A610MULC	SG10CCAL00013	CL
4365.	33	27					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00049	HL
4366.	33	28					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00050	HL
4367.	33	29					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00049	HL
4368.	33	30					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00050	HL
4369.	33	31					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00049	HL
4370.							TEHTEC	F2217	rpri	A610MULC	SG10CCAL00013	CL
4371.	33	32					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00050	HL
4372.	33	33					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00049	HL
4373.	33	34					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00050	HL
4374.	33	35					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00049	HL
4375.	33	36					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00049	HL
4376.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00013	CL
4377.	33	37					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00034	HL
4378.	33	38					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00033	HL
4379.	33	39					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00034	HL
4380.	33	40					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00033	HL
4381.	33	41					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00034	HL
4382.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00009	CL
4383.	33	42					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00033	HL
4384.	33	43					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00034	HL
4385.	33	44					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00033	HL
4386.	33	45					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00034	HL
4387.	33	46					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00033	HL
4388.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00009	CL
4389.	33	47					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00034	HL
4390.	33	48					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00033	HL
4391.	33	49					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00034	HL
4392.	33	50					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00033	HL
4393.	33	51					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00034	HL
4394.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00009	CL
4395.	33	52					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00033	HL
4396.	33	53					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00034	HL
4397.	33	54					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00033	HL
4398.	33	55					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00034	HL
4399.	33	56					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00033	HL
4400.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00009	CL
4401.	33	59					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00025	HL
4402.							TEHTEC	F2217	rpri	A610MULC	SG10CCAL00007	CL
4403.	33	60					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00026	HL
4404.	33	61					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00025	HL
4405.	33	62					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00026	HL
4406.	33	63					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00025	HL
4407.	33	64					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00026	HL
4408.							TEHTEC	F2217	rpri	A610MULC	SG10CCAL00007	CL
4409.	33	65					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00025	HL
4410.	33	66					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00026	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: A
 DATABASE: Harris_SGA_1995

Sep. 23.1995 15:21

PAGE 92 of 124

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
4411.	33	67						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00025	HL
4412.	33	68						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00026	HL
4413.	33	69						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00025	HL
4414.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00007	CL
4415.	33	70						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00026	HL
4416.	33	71						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00025	HL
4417.	33	72						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00026	HL
4418.	33	73						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00025	HL
4419.	33	74						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00026	HL
4420.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00007	CL
4421.	33	75						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00025	HL
4422.	33	76						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00026	HL
4423.	33	77						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00025	HL
4424.	33	78						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00026	HL
4425.	33	79						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00025	HL
4426.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00007	CL
4427.	33	80						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00026	HL
4428.	33	81						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00027	HL
4429.	33	82						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00018	HL
4430.	33	83						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00019	HL
4431.	33	84						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00018	HL
4432.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00006	CL
4433.	33	85						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00019	HL
4434.	33	86						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00018	HL
4435.	33	87						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00019	HL
4436.	33	88						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00018	HL
4437.	33	89						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00019	HL
4438.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00006	CL
4439.	33	90						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00018	HL
4440.	33	91						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00019	HL
4441.	33	92						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00018	HL
4442.	33	93						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00019	HL
4443.	33	94						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00016	HL
4444.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00005	CL
4445.	33	95						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00017	HL
4446.	33	96						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00016	HL
4447.	33	97						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00017	HL
4448.	33	98						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00016	HL
4449.	33	99						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00017	HL
4450.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00006	CL
4451.	33	100						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00016	HL
4452.	33	101						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00017	HL
4453.	33	102						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00016	HL
4454.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00006	CL
4455.	33	103						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00017	HL
4456.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00006	CL
4457.	34	13						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00048	HL
4458.		16.25	189	ONT	P1	AV2	0.00	TEHTEC	F2217	rpri	A610MULC	SG10CCAL00011	CL
4459.		34.37	186	ONT	P1	11C	-0.67	TEHTEC	F2217	rpri	A610MULC	SG10CCAL00011	CL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: A
 DATABASE: Harris_SGA_1995

Sep. 23.1995 15:21

PAGE 93 of 124

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG	
4460.	34	14						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00047	HL	
4461.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00011	CL	
4462.	34	15						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00048	HL	
4463.	34	16						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00047	HL	
4464.					RBD			H3464	rsec		A610MULC	SG10CCAL00012	CL	
4465.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00016	CL	
4466.	34	17						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00048	HL	
4467.	34	18						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00047	HL	
4468.	34	19						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00048	HL	
4469.	34	20						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00047	HL	
4470.	34	21						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00048	HL	
4471.					RBD			H3464	rsec		A610MULC	SG10CCAL00012	CL	
4472.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00016	CL	
4473.	34	22						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00047	HL	
4474.	34	23						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00048	HL	
4475.	34	24						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00047	HL	
4476.	34	25						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00050	HL	
4477.	34	26						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00049	HL	
4478.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00013	CL	
4479.	34	27						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00050	HL	
4480.	34	28						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00049	HL	
4481.	34	29						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00050	HL	
4482.	34	30						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00049	HL	
4483.	34	31						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00050	HL	
4484.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00013	CL	
4485.	34	32	2.94	6	SAI	1	TEH	9.32	TSHTEH	F9284	rpri	B620MRPC3C	SG11HCAL00051	HL
4486.					PID	1	TEH	9.32	TSHTEH	F3453	reso	B620MRPC3C	SG11HCAL00059	HL
4487.					PID	1	TSH	-1.72	TSHTEH	C3335	reso	B620MRPC3C	SG11HCAL00051	HL
4488.			4.31	13	SAI	1	TSH	-1.72	TSHTSH	H1274	reso	B620MRPC3C	SG11HCAL00049	HL
4489.	34	33						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00050	HL	
4490.	34	34						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00049	HL	
4491.	34	35						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00050	HL	
4492.	34	36						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00049	HL	
4493.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00013	CL	
4494.	34	37						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00034	HL	
4495.	34	38						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00033	HL	
4496.	34	39						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00034	HL	
4497.	34	40						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00033	HL	
4498.	34	41						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00034	HL	
4499.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00009	CL	
4500.	34	42						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00033	HL	
4501.	34	43						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00034	HL	
4502.	34	44						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00033	HL	
4503.	34	45						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00034	HL	
4504.	34	46						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00033	HL	
4505.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00009	CL	
4506.	34	47						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00034	HL	
4507.	34	48						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00033	HL	
4508.	34	49						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00034	HL	

*** INSPECTION FINAL REPORT LISTING ***

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: A
 DATABASE: Harris_SGA_1995

Sep. 23, 1995 15:21

PAGE 94 of 124

ROW	COLUMN	VOLTS	DEG	PCT	.CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
4509.	34	50						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00033	HL
4510.	34	51						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00034	HL
4511.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00009	CL
4512.	34	52						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00033	HL
4513.	34	53						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00034	HL
4514.	34	54						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00033	HL
4515.	34	55						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00034	HL
4516.	34	56						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00033	HL
4517.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00009	CL
4518.	34	59						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00025	HL
4519.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00007	CL
4520.	34	60						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00026	HL
4521.	34	61						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00025	HL
4522.	34	62						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00026	HL
4523.	34	63						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00025	HL
4524.	34	64						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00026	HL
4525.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00007	CL
4526.	34	65						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00025	HL
4527.	34	66						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00026	HL
4528.	34	67						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00025	HL
4529.	34	68						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00026	HL
4530.	34	69						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00025	HL
4531.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00007	CL
4532.	34	70						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00026	HL
4533.	34	71						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00025	HL
4534.	34	72						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00026	HL
4535.	34	73						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00025	HL
4536.	34	74						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00026	HL
4537.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00007	CL
4538.	34	75						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00025	HL
4539.	34	76						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00026	HL
4540.	34	77						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00025	HL
4541.	34	78						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00026	HL
4542.	34	79						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00025	HL
4543.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00007	CL
4544.	34	80						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00026	HL
4545.	34	81						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00027	HL
4546.	34	82			RBD				B5534	rpri	B620MRPC3C	SG11HCAL00018	HL
4547.								TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00033	HL
4548.	34	83						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00019	HL
4549.	34	84						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00018	HL
4550.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00006	CL
4551.	34	85						TSHTSH	K6733	rsec	B620MRPC3C	SG11HCAL00019	HL
4552.	34	86						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00018	HL
4553.	34	87						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00019	HL
4554.	34	88						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00018	HL
4555.	34	89						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00019	HL
4556.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00006	CL
4557.	34	90						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00018	HL

*** INSPECTION FINAL REPORT LISTING ***

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: A
 DATABASE: Harris_SGA_1995

Sep. 23.1995 15:21

PAGE 95 of 124

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
4558.	34	91						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00019	HL
4559.	34	92						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00018	HL
4560.	34	93						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00019	HL
4561.	34	94						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00016	HL
4562.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00005	CL
4563.	34	95						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00017	HL
4564.	34	96						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00016	HL
4565.	34	97						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00017	HL
4566.	34	98						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00016	HL
4567.	34	99						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00017	HL
4568.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00005	CL
4569.	34	100						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00016	HL
4570.	34	101						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00017	HL
4571.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00006	CL
4572.	34	102						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00019	HL
4573.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00006	CL
4574.	35	14						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00048	HL
4575.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00011	CL
4576.	35	15						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00047	HL
4577.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00011	CL
78.	35	16						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00048	HL
9.									H3464	rsec	A610MULC	SG10CCAL00012	CL
10.					RBD			TEHTEC	S7675	rpri	A610MULC	SG10CCAL00016	CL
4581.	35	17						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00047	HL
4582.	35	18						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00048	HL
4583.	35	19						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00047	HL
4584.	35	20						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00048	HL
4585.	35	21						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00047	HL
4586.									H3464	rsec	A610MULC	SG10CCAL00012	CL
4587.					RBD			TEHTEC	F2217	rpri	A610MULC	SG10CCAL00013	CL
4588.	35	22						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00048	HL
4589.	35	23						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00047	HL
4590.	35	24						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00050	HL
4591.	35	25						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00049	HL
4592.	35	26						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00050	HL
4593.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00013	CL
4594.	35	27						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00049	HL
4595.	35	28						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00050	HL
4596.	35	29						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00049	HL
4597.	35	30						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00050	HL
4598.	35	31						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00049	HL
4599.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00013	CL
4600.	35	32						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00050	HL
4601.	35	33						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00049	HL
4602.	35	34						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00050	HL
4603.	35	35						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00049	HL
4604.	35	36						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00049	HL
4605.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00013	CL
4606.	35	37						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00034	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: A
 DATABASE: Harris_SGA_1995

Sep. 23.1995 15:21

PAGE 96 of 124

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
4607.	35	38					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00033	HL
4608.	35	39					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00034	HL
4609.	35	40					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00033	HL
4610.	35	41					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00034	HL
4611.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00009	CL
4612.	35	42					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00033	HL
4613.	35	43					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00034	HL
4614.	35	44					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00033	HL
4615.	35	47					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00034	HL
4616.	35	48					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00033	HL
4617.	35	49					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00034	HL
4618.	35	50					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00033	HL
4619.	35	51					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00034	HL
4620.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00009	CL
4621.	35	52					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00033	HL
4622.	35	53					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00034	HL
4623.	35	54					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00033	HL
4624.	35	55					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00034	HL
4625.	35	56					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00033	HL
4626.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00009	CL
27.	35	59					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00025	HL
28.							TEHTEC	F2217	rpri	A610MULC	SG10CCAL00007	CL
29.	35	60					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00026	HL
4630.	35	61					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00025	HL
4631.	35	62					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00026	HL
4632.	35	63					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00025	HL
4633.	35	64					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00026	HL
4634.							TEHTEC	F2217	rpri	A610MULC	SG10CCAL00007	CL
4635.	35	65					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00025	HL
4636.	35	66					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00026	HL
4637.	35	67					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00025	HL
4638.	35	68					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00026	HL
4639.	35	71					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00025	HL
4640.	35	72					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00026	HL
4641.	35	73					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00025	HL
4642.	35	74					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00026	HL
4643.							TEHTEC	F2217	rpri	A610MULC	SG10CCAL00007	CL
4644.	35	75					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00025	HL
4645.	35	76					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00026	HL
4646.	35	77					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00025	HL
4647.	35	78					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00026	HL
4648.	35	79					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00025	HL
4649.							TEHTEC	F2217	rpri	A610MULC	SG10CCAL00007	CL
4650.	35	80					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00026	HL
4651.	35	81					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00027	HL
4652.	35	82					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00018	HL
3.	35	83					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00019	HL
4.	35	84					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00018	HL
5.							TEHTEC	F2217	rpri	A610MULC	SG10CCAL00006	CL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: A
 DATABASE: Harris_SGA_1995

Sep. 23.1995 15:21

PAGE 97 of 124

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG	
4656.	35	85						TSHTSH	85534	rpr1	B620MRPC3C	SG11HCAL00019	HL	
4657.	35	86						TSHTSH	85534	rpr1	B620MRPC3C	SG11HCAL00018	HL	
4658.	35	87						TSHTSH	85534	rpr1	B620MRPC3C	SG11HCAL00019	HL	
4659.	35	88						TSHTSH	85534	rpr1	B620MRPC3C	SG11HCAL00018	HL	
4660.	35	89						TSHTSH	85534	rpr1	B620MRPC3C	SG11HCAL00019	HL	
4661.								TEHTEC	F2217	rpr1	A610MULC	SG10CCAL00006	CL	
4662.	35	90						TSHTSH	85534	rpr1	B620MRPC3C	SG11HCAL00018	HL	
4663.	35	91						TSHTSH	85534	rpr1	B620MRPC3C	SG11HCAL00019	HL	
4664.	35	92						TSHTSH	85534	rpr1	B620MRPC3C	SG11HCAL00018	HL	
4665.	35	93						TSHTSH	85534	rpr1	B620MRPC3C	SG11HCAL00019	HL	
4666.	35	94						TSHTSH	S7067	rpr1	B620MRPC3C	SG11HCAL00016	HL	
4667.								TEHTEC	F2217	rpr1	A610MULC	SG10CCAL00005	CL	
4668.	35	95						TSHTSH	S7067	rpr1	B620MRPC3C	SG11HCAL00017	HL	
4669.	35	96						TSHTSH	S7067	rpr1	B620MRPC3C	SG11HCAL00016	HL	
4670.	35	97						TSHTSH	S7067	rpr1	B620MRPC3C	SG11HCAL00017	HL	
4671.	35	98						TSHTSH	85534	rpr1	B620MRPC3C	SG11HCAL00016	HL	
4672.	35	99						TSHTSH	85534	rpr1	B620MRPC3C	SG11HCAL00017	HL	
4673.								TEHTEC	F2217	rpr1	A610MULC	SG10CCAL00005	CL	
4674.	35	100						TSHTSH	85534	rpr1	B620MRPC3C	SG11HCAL00016	HL	
4675.								TEHTEC	F2217	rpr1	A610MULC	SG10CCAL00006	CL	
76.	35	101						TSHTSH	85534	rpr1	B620MRPC3C	SG11HCAL00017	HL	
7.								TEHTEC	F2217	rpr1	A610MULC	SG10CCAL00006	CL	
78.	36	15						TSHTSH	F9284	rpr1	B620MRPC3C	SG11HCAL00048	HL	
4679.			13.04	188	DNT	P1	AV3	0.18	TEHTEC	F2217	rpr1	A610MULC	SG10CCAL00011	CL
4680.			21.81	187	DNT	P1	11C	-0.43	TEHTEC	F2217	rpr1	A610MULC	SG10CCAL00011	CL
4681.			56.73	186	DNT	1	10C	38.46	TEHTEC	F2217	rpr1	A610MULC	SG10CCAL00011	CL
4682.	36	16							TSHTSH	F9284	rpr1	B620MRPC3C	SG11HCAL00047	HL
4683.									TEHTEC	F2217	rpr1	A610MULC	SG10CCAL00011	CL
4684.	36	17							TSHTSH	F9284	rpr1	B620MRPC3C	SG11HCAL00048	HL
4685.	36	18							TSHTSH	F9284	rpr1	B620MRPC3C	SG11HCAL00047	HL
4686.	36	19							TSHTSH	F9284	rpr1	B620MRPC3C	SG11HCAL00048	HL
4687.	36	20							TSHTSH	F9284	rpr1	B620MRPC3C	SG11HCAL00047	HL
4688.	36	21							TSHTSH	F9284	rpr1	B620MRPC3C	SG11HCAL00048	HL
4689.					RBD				H3464	rsec	A610MULC	SG10CCAL00012	CL	
4690.									TEHTEC	H3464	rsec	A610MULC	SG10CCAL00013	CL
4691.	36	22							TSHTSH	F9284	rpr1	B620MRPC3C	SG11HCAL00047	HL
4692.	36	23							TSHTSH	F9284	rpr1	B620MRPC3C	SG11HCAL00048	HL
4693.	36	24							TSHTSH	F9284	rpr1	B620MRPC3C	SG11HCAL00047	HL
4694.	36	25							TSHTSH	F9284	rpr1	B620MRPC3C	SG11HCAL00050	HL
4695.	36	26							TSHTSH	F9284	rpr1	B620MRPC3C	SG11HCAL00049	HL
4696.									TEHTEC	F2217	rpr1	A610MULC	SG10CCAL00013	CL
4697.	36	27							TSHTSH	F9284	rpr1	B620MRPC3C	SG11HCAL00050	HL
4698.	36	28							TSHTSH	F9284	rpr1	B620MRPC3C	SG11HCAL00049	HL
4699.	36	29							TSHTSH	F9284	rpr1	B620MRPC3C	SG11HCAL00050	HL
4700.	36	30							TSHTSH	F9284	rpr1	B620MRPC3C	SG11HCAL00049	HL
701.	36	31							TSHTSH	F9284	rpr1	B620MRPC3C	SG11HCAL00050	HL
2.									TEHTEC	F2217	rpr1	A610MULC	SG10CCAL00013	CL
03.	36	32	2.66	21	MAI	1	TSH	-0.02	TSHTSH	F9284	rpr1	B620MRPC3C	SG11HCAL00049	HL
04.					PID	1	TSH	-0.02	01HTEH	J9815	rsec	B620MRPC3C	SG11HCAL00051	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: A
 DATABASE: Harris_SGA_1995

Sep. 23.1995 15:21

PAGE 98 of 124

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
4705.	36	33					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00050	HL
4706.	36	34					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00049	HL
4707.	36	35					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00050	HL
4708.	36	36					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00049	HL
4709.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00013	CL
4710.	36	37					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00034	HL
4711.	36	38					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00033	HL
4712.	36	39					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00034	HL
4713.	36	40					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00033	HL
4714.	36	41					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00034	HL
4715.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00009	CL
4716.	36	42					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00033	HL
4717.	36	43					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00034	HL
4718.	36	44					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00033	HL
4719.	36	47					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00034	HL
4720.	36	48					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00033	HL
4721.	36	49					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00034	HL
4722.	36	50					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00033	HL
4723.	36	51					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00034	HL
4724.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00009	CL
4725.	36	52					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00033	HL
4726.	36	53					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00034	HL
4727.	36	54					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00033	HL
4728.	36	55					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00034	HL
4729.	36	56					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00033	HL
4730.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00009	CL
4731.	36	59					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00025	HL
4732.							TEHTEC	F2217	rpri	A610MULC	SG10CCAL00007	CL
4733.	36	60					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00026	HL
4734.	36	61					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00025	HL
4735.	36	62					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00026	HL
4736.	36	63					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00025	HL
4737.	36	64					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00026	HL
4738.							TEHTEC	F2217	rpri	A610MULC	SG10CCAL00007	CL
4739.	36	65					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00025	HL
4740.	36	66					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00026	HL
4741.	36	67					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00025	HL
4742.	36	68					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00026	HL
4743.	36	71					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00025	HL
4744.	36	72					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00026	HL
4745.	36	73					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00025	HL
4746.	36	74					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00026	HL
4747.							TEHTEC	F2217	rpri	A610MULC	SG10CCAL00007	CL
4748.	36	75					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00025	HL
4749.	36	76					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00026	HL
4750.	36	77					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00025	HL
4751.	36	78					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00026	HL
4752.	36	79					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00025	HL
4753.							TEHTEC	F2217	rpri	A610MULC	SG10CCAL00007	CL

*** INSPECTION FINAL REPORT LISTING ***

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: A
 DATABASE: Harris_SGA_1995

Sep. 23, 1995 15:21

PAGE 99 of 124

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG	
4754.	36	80						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00026	HL	
4755.	36	81						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00027	HL	
4756.	36	82						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00018	HL	
4757.	36	83						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00019	HL	
4758.	36	84						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00018	HL	
4759.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00006	CL	
4760.	36	85						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00019	HL	
4761.	36	86						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00018	HL	
4762.	36	87						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00019	HL	
4763.	36	88						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00018	HL	
4764.	36	89						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00019	HL	
4765.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00006	CL	
4766.	36	90						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00018	HL	
4767.	36	91						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00019	HL	
4768.	36	92						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00018	HL	
4769.	36	93						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00019	HL	
4770.	36	94						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00016	HL	
4771.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00005	CL	
4772.	36	95						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00017	HL	
4773.	36	96						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00016	HL	
4774.	36	97						TSHTSH	J9815	rsec	B620MRPC3C	SG11HCAL00017	HL	
4775.	36	98						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00016	HL	
4776.	36	99						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00017	HL	
4777.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00005	CL	
4778.	36	100						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00019	HL	
4779.			34.11	182	DNT	1	09H	1.49	TEHTEC	F2217	rpri	A610MULC	SG10CCAL00006	CL
4780.			8.61	184	DNT	1	09H	39.59	TEHTEC	F2217	rpri	A610MULC	SG10CCAL00006	CL
4781.			5.24	184	DNT	1	09C	2.78	TEHTEC	F2217	rpri	A610MULC	SG10CCAL00006	CL
4782.	37	16						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00048	HL	
4783.			1.20	147	25	1	01H	0.99	TEHTEC	F3453	reso	A610MULC	SG10CCAL00011	CL
4784.	37	17						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00047	HL	
4785.	37	18						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00048	HL	
4786.	37	19						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00047	HL	
4787.	37	20						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00048	HL	
4788.	37	21						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00047	HL	
4789.					RBD				H3464	rsec	A610MULC	SG10CCAL00012	CL	
4790.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00013	CL	
4791.	37	22						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00048	HL	
4792.	37	23						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00047	HL	
4793.	37	24						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00050	HL	
4794.	37	25						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00049	HL	
4795.	37	26						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00050	HL	
4796.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00013	CL	
4797.	37	27						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00049	HL	
4798.	37	28						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00050	HL	
4799.	37	29						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00049	HL	
4800.	37	30						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00050	HL	
4801.	37	31						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00049	HL	
4802.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00013	CL	

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: A
 DATABASE: Harris_SGA_1995

Sep. 23,1995 15:21

PAGE 100 of 124

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
4803.	37	32					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00050	HL
4804.	37	33					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00049	HL
4805.	37	34					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00050	HL
4806.	37	35					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00049	HL
4807.	37	36					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00049	HL
4808.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00013	CL
4809.	37	37					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00034	HL
4810.	37	38					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00033	HL
4811.	37	39					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00034	HL
4812.	37	40					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00033	HL
4813.	37	41					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00034	HL
4814.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00009	CL
4815.	37	42					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00033	HL
4816.	37	43					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00034	HL
4817.	37	44					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00033	HL
4818.	37	45					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00034	HL
4819.	37	46					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00033	HL
4820.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00009	CL
4821.	37	47					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00034	HL
4822.	37	48					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00033	HL
4823.	37	49					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00034	HL
4824.	37	50					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00033	HL
4825.	37	51					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00034	HL
4826.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00009	CL
4827.	37	52					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00033	HL
4828.	37	53					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00034	HL
4829.	37	54					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00033	HL
4830.	37	55					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00034	HL
4831.	37	56					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00033	HL
4832.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00009	CL
4833.	37	59					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00025	HL
4834.							TEHTEC	F2217	rpri	A610MULC	SG10CCAL00007	CL
4835.	37	60					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00026	HL
4836.	37	61					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00025	HL
4837.	37	62					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00026	HL
4838.	37	63					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00025	HL
4839.	37	64					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00026	HL
4840.							TEHTEC	F2217	rpri	A610MULC	SG10CCAL00007	CL
4841.	37	65					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00025	HL
4842.	37	66					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00026	HL
4843.	37	67					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00025	HL
4844.	37	68					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00026	HL
4845.	37	69					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00025	HL
4846.							TEHTEC	F2217	rpri	A610MULC	SG10CCAL00007	CL
4847.	37	70					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00026	HL
4848.	37	71					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00025	HL
4849.	37	72					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00026	HL
4850.	37	73					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00025	HL
4851.	37	74					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00026	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: A
 DATABASE: Harris_SGA_1995

Sep. 23,1995 15:21

PAGE 101 of 124

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE	SIZE	CAL	GROUP	LEG
4852.								TEHTEC	F2217	rpri	A610MULC		SG10CCAL00007	CL	
4853.	37	75						TSHTSH	S7067	rpri	B620MRPC3C		SG11HCAL00025	HL	
4854.	37	76						TSHTSH	S7067	rpri	B620MRPC3C		SG11HCAL00026	HL	
4855.	37	77						TSHTSH	S7067	rpri	B620MRPC3C		SG11HCAL00025	HL	
4856.	37	78						TSHTSH	S7067	rpri	B620MRPC3C		SG11HCAL00026	HL	
4857.	37	79						TSHTSH	S7067	rpri	B620MRPC3C		SG11HCAL00027	HL	
4858.								TEHTEC	F2217	rpri	A610MULC		SG10CCAL00007	CL	
4859.	37	80						TSHTSH	S7067	rpri	B620MRPC3C		SG11HCAL00028	HL	
4860.	37	81						TSHTSH	S7067	rpri	B620MRPC3C		SG11HCAL00027	HL	
4861.	37	82						TSHTSH	B5534	rpri	B620MRPC3C		SG11HCAL00018	HL	
4862.	37	83						TSHTSH	B5534	rpri	B620MRPC3C		SG11HCAL00019	HL	
4863.	37	84						TSHTSH	B5534	rpri	B620MRPC3C		SG11HCAL00018	HL	
4864.								TEHTEC	F2217	rpri	A610MULC		SG10CCAL00006	CL	
4865.	37	85						TSHTSH	B5534	rpri	B620MRPC3C		SG11HCAL00019	HL	
4866.	37	86						TSHTSH	B5534	rpri	B620MRPC3C		SG11HCAL00018	HL	
4867.	37	87						TSHTSH	B5534	rpri	B620MRPC3C		SG11HCAL00019	HL	
4868.	37	88						TSHTSH	B5534	rpri	B620MRPC3C		SG11HCAL00018	HL	
4869.	37	89						TSHTSH	B5534	rpri	B620MRPC3C		SG11HCAL00019	HL	
4870.								TEHTEC	F2217	rpri	A610MULC		SG10CCAL00006	CL	
4871.	37	90						TSHTSH	B5534	rpri	B620MRPC3C		SG11HCAL00018	HL	
72.	37	91						TSHTSH	B5534	rpri	B620MRPC3C		SG11HCAL00019	HL	
3.	37	92						TSHTSH	B5534	rpri	B620MRPC3C		SG11HCAL00018	HL	
4874.	37	93						TSHTSH	B5534	rpri	B620MRPC3C		SG11HCAL00019	HL	
4875.	37	94						TSHTSH	S7067	rpri	B620MRPC3C		SG11HCAL00016	HL	
4876.								TEHTEC	F2217	rpri	A610MULC		SG10CCAL00005	CL	
4877.	37	95						TSHTSH	S7067	rpri	B620MRPC3C		SG11HCAL00017	HL	
4878.	37	96						TSHTSH	B5534	rpri	B620MRPC3C		SG11HCAL00016	HL	
4879.	37	97						TSHTSH	B5534	rpri	B620MRPC3C		SG11HCAL00017	HL	
4880.	37	98						TSHTSH	B5534	rpri	B620MRPC3C		SG11HCAL00016	HL	
4881.	37	99						TSHTSH	B5534	rpri	B620MRPC3C		SG11HCAL00017	HL	
4882.								TEHTEC	F2217	rpri	A610MULC		SG10CCAL00005	CL	
4883.	38	17						TSHTSH	F9284	rpri	B620MRPC3C		SG11HCAL00047	HL	
4884.					RBD				H3464	rsec	A610MULC		SG10CCAL00012	CL	
4885.								TEHTEC	S7675	rpri	A610MULC		SG10CCAL00016	CL	
4886.	38	18						TSHTSH	F9284	rpri	B620MRPC3C		SG11HCAL00048	HL	
4887.	38	19						TSHTSH	F9284	rpri	B620MRPC3C		SG11HCAL00047	HL	
4888.	38	20						TSHTSH	F9284	rpri	B620MRPC3C		SG11HCAL00048	HL	
4889.	38	21						TSHTSH	F9284	rpri	B620MRPC3C		SG11HCAL00047	HL	
4890.					RBD				D3858	reso	A610MULC		SG10CCAL00013	CL	
4891.								TEHTEC	S7675	rpri	A610MULC		SG10CCAL00016	CL	
4892.	38	22						TSHTSH	F9284	rpri	B620MRPC3C		SG11HCAL00048	HL	
4893.	38	23						TSHTSH	F9284	rpri	B620MRPC3C		SG11HCAL00047	HL	
4894.	38	24						TSHTSH	F9284	rpri	B620MRPC3C		SG11HCAL00050	HL	
4895.	38	25						TSHTSH	F9284	rpri	B620MRPC3C		SG11HCAL00049	HL	
4896.	38	26						TSHTSH	F9284	rpri	B620MRPC3C		SG11HCAL00050	HL	
97.								TEHTEC	F2217	rpri	A610MULC		SG10CCAL00013	CL	
8.	38	27						TSHTSH	F9284	rpri	B620MRPC3C		SG11HCAL00049	HL	
99.	38	28						TSHTSH	F9284	rpri	B620MRPC3C		SG11HCAL00050	HL	
100.	38	29						TSHTSH	F9284	rpri	B620MRPC3C		SG11HCAL00049	HL	

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: A
 DATABASE: Harris_SGA_1995

Sep. 23.1995 15:21

PAGE 102 of 124

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
4901.	38	30					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00050	HL
4902.	38	31					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00049	HL
4903.							TEHTEC	F2217	rpri	A610MULC	SG10CCAL00013	CL
4904.	38	32					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00050	HL
4905.	38	33					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00049	HL
4906.	38	34					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00050	HL
4907.	38	35					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00049	HL
4908.	38	36					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00049	HL
4909.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00013	CL
4910.	38	37					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00034	HL
4911.	38	38					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00033	HL
4912.	38	39					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00034	HL
4913.	38	40					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00033	HL
4914.	38	41					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00034	HL
4915.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00009	CL
4916.	38	42					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00033	HL
4917.	38	43					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00034	HL
4918.	38	44					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00033	HL
4919.	38	45					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00034	HL
4920.	38	46					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00033	HL
1.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00009	CL
2.	38	47					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00034	HL
23.	38	48					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00033	HL
4924.	38	49					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00034	HL
4925.	38	50					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00033	HL
4926.	38	51					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00034	HL
4927.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00009	CL
4928.	38	52					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00033	HL
4929.	38	53					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00034	HL
4930.	38	54					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00033	HL
4931.	38	55					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00034	HL
4932.	38	56					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00033	HL
4933.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00009	CL
4934.	38	59					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00025	HL
4935.							TEHTEC	F2217	rpri	A610MULC	SG10CCAL00007	CL
4936.	38	60					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00026	HL
4937.	38	61					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00025	HL
4938.	38	62					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00026	HL
4939.	38	63					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00025	HL
4940.	38	64					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00026	HL
4941.							TEHTEC	F2217	rpri	A610MULC	SG10CCAL00007	CL
4942.	38	65					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00025	HL
4943.	38	66					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00026	HL
4944.	38	67					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00025	HL
4945.	38	68					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00026	HL
46.	38	69					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00025	HL
7.							TEHTEC	F2217	rpri	A610MULC	SG10CCAL00007	CL
48.	38	70					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00026	HL
49.	38	71					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00025	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: A
 DATABASE: Harris_SGA_1995

Sep. 23.1995 15:21

PAGE 103 of 124

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
4950.	38	72						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00026	HL
4951.	38	73						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00025	HL
4952.	38	74						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00026	HL
4953.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00007	CL
4954.	38	75						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00025	HL
4955.	38	76						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00026	HL
4956.	38	77						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00025	HL
4957.	38	78						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00026	HL
4958.	38	79						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00027	HL
4959.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00007	CL
4960.	38	80						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00028	HL
4961.	38	81						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00027	HL
4962.	38	82						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00018	HL
4963.	38	83						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00019	HL
4964.	38	84						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00018	HL
4965.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00006	CL
4966.	38	85						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00019	HL
4967.	38	86						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00018	HL
4968.	38	87						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00019	HL
4969.	38	88						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00018	HL
70.	38	89						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00019	HL
71.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00006	CL
72.	38	90						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00018	HL
4973.	38	91						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00019	HL
4974.	38	92						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00018	HL
4975.	38	93						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00019	HL
4976.	38	94						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00016	HL
4977.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00005	CL
4978.	38	95						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00017	HL
4979.	38	96						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00016	HL
4980.	38	97						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00017	HL
4981.	38	98						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00033	HL
4982.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00005	CL
4983.	38	99						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00016	HL
4984.								TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00017	HL
4985.								08CTEC	F2217	rpri	A610MULC	SG10CCAL00005	CL
4986.								08CTEC	F3453	reso	A590SFRM	SG10CCAL00018	CL
4987.									K6733	rsec	B590MRPC3C	SG11HCAL00035	HL
4988.								08H07H	B5534	rpri	B620MRPC3C	SG11HCAL00036	HL
4989.		65.61	178	DNT	1	07H	39.61	TEHTEC	T9924	rpri	A560SFRM	SG10CCAL00019	CL
4990.		13.38	177	DNT	P1	08H	1.28	TEHTEC	T9924	rpri	A560SFRM	SG10CCAL00019	CL
4991.		23.44	174	DNT	P1	09C	-1.07	TEHTEC	T9924	rpri	A560SFRM	SG10CCAL00019	CL
4992.		139.30	171	DNT	P1	09C	-0.23	TEHTEC	T9924	rpri	A560SFRM	SG10CCAL00019	CL
4993.		30.32	178	DNT	P1	09C	0.59	TEHTEC	T9924	rpri	A560SFRM	SG10CCAL00019	CL
4994.		29.85	180	DNT	P1	08C	-0.45	08CTEC	F2217	rpri	A610MULC	SG10CCAL00005	CL
95.		30.84	175	DNT	P1	08C	-0.33	TEHTEC	T9924	rpri	A560SFRM	SG10CCAL00019	CL
96.		21.50	185	DNT	P1	08C	0.00	08CTEC	F3325	rsec	A590SFRM	SG10CCAL00018	CL
97.	39	17						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00048	HL
98.									H3464	rsec	A610MULC	SG10CCAL00012	CL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: A
 DATABASE: Harris_SGA_1995

Sep. 23.1995 15:21

PAGE 104 of 124

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
4999.		16.91	186	DNT	P1	11C	-0.41	TEHTEC	S7675	rpri	A610MULC	SG10CCAL00016	CL
5000.	39	18						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00047	HL
5001.				RBD					H3464	rsec	A610MULC	SG10CCAL00012	CL
5002.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00016	CL
5003.	39	19						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00048	HL
5004.	39	20						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00047	HL
5005.	39	21						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00048	HL
5006.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00013	CL
5007.	39	22						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00047	HL
5008.	39	23						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00048	HL
5009.	39	24						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00047	HL
5010.	39	25						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00050	HL
5011.	39	26						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00049	HL
5012.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00013	CL
5013.	39	27						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00050	HL
5014.	39	28						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00049	HL
5015.	39	29						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00050	HL
5016.	39	30						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00049	HL
5017.	39	31						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00050	HL
5018.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00013	CL
5019.	39	32						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00049	HL
5020.	39	33						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00050	HL
5021.	39	34						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00049	HL
5022.	39	35						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00050	HL
5023.	39	36						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00049	HL
5024.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00013	CL
5025.	39	37						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00034	HL
5026.	39	38						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00033	HL
5027.	39	39						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00034	HL
5028.	39	40						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00033	HL
5029.	39	41						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00034	HL
5030.		12.18	181	DNT	1	06C	4.12	TEHTEC	F7460	rséc	A610MULC	SG10CCAL00009	CL
5031.	39	42						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00033	HL
5032.	39	43						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00034	HL
5033.	39	44						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00033	HL
5034.	39	45						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00034	HL
5035.	39	46						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00033	HL
5036.		7.93	183	DNT	1	05C	6.44	TEHTEC	S7675	rpri	A610MULC	SG10CCAL00009	CL
5037.	39	47						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00034	HL
5038.	39	48						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00033	HL
5039.	39	49						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00034	HL
5040.	39	50						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00033	HL
5041.	39	51						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00034	HL
5042.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00009	CL
5043.	39	52						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00033	HL
5044.	39	53						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00034	HL
5045.	39	54						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00033	HL
5046.	39	55						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00034	HL
5047.	39	56						TSHTSH	85534	rpri	B620MRPC3C	SG11HCAL00033	HL

*** INSPECTION FINAL REPORT LISTING ***

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: A
 DATABASE: Harris_SGA_1995

Sep. 23, 1995 15:21

PAGE 105 of 124

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
5048.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00009	CL
5049.	39	59						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00025	HL
5050.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00007	CL
5051.	39	60						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00026	HL
5052.	39	61						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00025	HL
5053.	39	62						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00026	HL
5054.	39	63						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00025	HL
5055.	39	64						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00026	HL
5056.		0.75		20	P2	AV3	0.03	TEHTEC	F2217	rpri	A610MULC	SG10CCAL00007	CL
5057.	39	65						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00025	HL
5058.	39	66						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00026	HL
5059.	39	67						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00025	HL
5060.	39	68						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00026	HL
5061.	39	69						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00025	HL
5062.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00007	CL
5063.	39	70						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00026	HL
5064.	39	71						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00025	HL
5065.	39	72						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00026	HL
5066.	39	73						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00025	HL
5067.	39	74						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00026	HL
5068.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00007	CL
5069.	39	75						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00025	HL
5070.	39	76						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00026	HL
5071.	39	77						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00025	HL
5072.	39	78						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00026	HL
5073.	39	79						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00027	HL
5074.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00007	CL
5075.	39	80						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00028	HL
5076.	39	81						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00027	HL
5077.	39	82						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00018	HL
5078.	39	83						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00019	HL
5079.	39	84						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00018	HL
5080.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00006	CL
5081.	39	85						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00019	HL
5082.	39	86						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00018	HL
5083.	39	87						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00019	HL
5084.	39	88						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00018	HL
5085.	39	89						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00019	HL
5086.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00006	CL
5087.	39	90						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00018	HL
5088.	39	91						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00019	HL
5089.	39	92						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00018	HL
5090.	39	93						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00019	HL
5091.	39	94						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00016	HL
5092.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00005	CL
5093.	39	95						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00017	HL
5094.	39	96						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00016	HL
5095.	39	97						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00017	HL
5096.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00005	CL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: A
 DATABASE: Harris_SGA_1995

Sep. 23,1995 15:21

PAGE 106 of 124

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
5097.	39	98					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00019	HL
5098.							TEHTEC	F3325	rsec	A610MULC	SG10CCAL00005	CL
5099.	40	18					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00048	HL
5100.					RBD			H3464	rsec	A610MULC	SG10CCAL00012	CL
5101.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00016	CL
5102.	40	19					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00047	HL
5103.					RBD			H3464	rsec	A610MULC	SG10CCAL00012	CL
5104.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00016	CL
5105.	40	20					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00048	HL
5106.					RBD			H3464	rsec	A610MULC	SG10CCAL00012	CL
5107.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00016	CL
5108.	40	21					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00047	HL
5109.					RBD			D3858	reso	A610MULC	SG10CCAL00013	CL
5110.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00016	CL
5111.	40	22					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00048	HL
5112.	40	23					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00047	HL
5113.	40	24					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00050	HL
5114.	40	25					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00049	HL
5115.	40	26					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00050	HL
5116.							TEHTEC	F2217	rpri	A610MULC	SG10CCAL00013	CL
17.	40	27					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00049	HL
18.	40	28					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00050	HL
19.	40	29					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00049	HL
5120.	40	30					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00050	HL
5121.	40	31					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00049	HL
5122.							TEHTEC	F2217	rpri	A610MULC	SG10CCAL00013	CL
5123.	40	32					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00050	HL
5124.	40	33					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00049	HL
5125.	40	34					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00050	HL
5126.	40	35					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00049	HL
5127.	40	36					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00049	HL
5128.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00013	CL
5129.	40	37					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00034	HL
5130.	40	38					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00033	HL
5131.	40	39					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00034	HL
5132.	40	40					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00033	HL
5133.	40	41					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00034	HL
5134.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00009	CL
5135.	40	42					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00033	HL
5136.	40	43					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00034	HL
5137.	40	44					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00033	HL
5138.	40	45					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00034	HL
5139.	40	46					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00033	HL
5140.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00009	CL
5141.	40	47					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00034	HL
42.	40	48					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00033	HL
43.	40	49					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00034	HL
44.	40	50					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00033	HL
45.	40	51					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00034	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: A
 DATABASE: Harris_SGA_1995

Sep. 23, 1995 15:21

PAGE 107 of 124

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
5146.								TEHTEC	F7460	rsec	A610MULC	SG10CCAL00009	CL
5147.	40	52						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00033	HL
5148.	40	53						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00034	HL
5149.	40	54						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00033	HL
5150.	40	55						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00034	HL
5151.	40	56						TSHTSH	D4825	reso	B620MRPC3C	SG11HCAL00033	HL
5152.			1.29	70	NQI	P3	TSH -1.21	TEHTEC	S7675	rpri	A610MULC	SG10CCAL00009	CL
5153.	40	59						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00025	HL
5154.			0.83		21	P2	AV4 -0.03	TEHTEC	F2217	rpri	A610MULC	SG10CCAL00007	CL
5155.	40	60						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00026	HL
5156.	40	61						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00025	HL
5157.	40	62						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00026	HL
5158.	40	63						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00025	HL
5159.	40	64						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00026	HL
5160.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00007	CL
5161.	40	65						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00025	HL
5162.	40	66						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00026	HL
5163.	40	67						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00025	HL
5164.	40	68						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00026	HL
5165.	40	69						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00025	HL
66.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00007	CL
67.	40	70						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00026	HL
68.	40	71						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00025	HL
5169.	40	72						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00026	HL
5170.	40	73						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00025	HL
5171.	40	74						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00026	HL
5172.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00007	CL
5173.	40	75						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00025	HL
5174.	40	76						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00026	HL
5175.	40	77						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00025	HL
5176.	40	78						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00026	HL
5177.	40	79						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00027	HL
5178.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00007	CL
5179.	40	80						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00028	HL
5180.	40	81						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00027	HL
5181.	40	82						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00018	HL
5182.	40	83						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00019	HL
5183.	40	84						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00018	HL
5184.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00006	CL
5185.	40	85						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00019	HL
5186.	40	86						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00018	HL
5187.	40	87						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00019	HL
5188.	40	88						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00018	HL
5189.	40	89						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00019	HL
5190.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00006	CL
91.	40	90						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00018	HL
92.	40	91						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00019	HL
93.	40	92						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00018	HL
94.	40	93						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00019	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: A
 DATABASE: Harris_SGA_1995

Sep. 23,1995 15:21

PAGE 108 of 124

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
5195.	40	94						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00016	HL
5196.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00005	CL
5197.	40	95						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00017	HL
5198.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00005	CL
5199.	40	96						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00016	HL
5200.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00005	CL
5201.	40	97						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00017	HL
5202.			0.47	170	MBM	1	10C 20.04	TEHTEC	F3453	reso	A610MULC	SG10CCAL00005	CL
5203.	41	20						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00048	HL
5204.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00011	CL
5205.	41	21						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00047	HL
5206.			6.09	187	DNT	1	10H 28.18	TEHTEC	F2217	rpri	A610MULC	SG10CCAL00011	CL
5207.	41	22						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00048	HL
5208.	41	23						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00047	HL
5209.	41	24						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00048	HL
5210.	41	25						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00047	HL
5211.	41	26						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00048	HL
5212.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00011	CL
5213.	41	27						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00047	HL
5214.	41	28						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00048	HL
15.	41	29						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00047	HL
5.	41	30						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00048	HL
7.	41	31						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00047	HL
5218.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00011	CL
5219.	41	32						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00048	HL
5220.	41	33						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00047	HL
5221.	41	34						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00048	HL
5222.	41	35						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00047	HL
5223.	41	36						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00047	HL
5224.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00011	CL
5225.	41	37						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00030	HL
5226.	41	38						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00029	HL
5227.	41	39						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00030	HL
5228.	41	40						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00029	HL
5229.	41	41						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00030	HL
5230.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00008	CL
5231.	41	42						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00029	HL
5232.	41	43						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00032	HL
5233.	41	44						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00031	HL
5234.	41	45						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00032	HL
5235.	41	46						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00031	HL
5236.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00008	CL
5237.	41	47						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00032	HL
5238.	41	48						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00031	HL
5239.	41	49						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00032	HL
40.	41	50						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00031	HL
41.	41	51						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00032	HL
2.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00008	CL
43.	41	52						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00031	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: A
 DATABASE: Harris_SGA_1995

Sep. 23.1995 15:21

PAGE 109 of 124

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
5244.	41	53						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00032	HL
5245.	41	54						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00031	HL
5246.	41	55						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00032	HL
5247.	41	56						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00031	HL
5248.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00008	CL
5249.	41	60						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00027	HL
5250.	41	61						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00027	HL
5251.	41	62						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00027	HL
5252.	41	63						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00027	HL
5253.	41	64						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00027	HL
5254.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00007	CL
5255.	41	65						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00027	HL
5256.	41	66						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00027	HL
5257.	41	67						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00027	HL
5258.	41	68						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00027	HL
5259.	41	69						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00027	HL
5260.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00008	CL
5261.	41	70						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00027	HL
5262.	41	71						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00027	HL
5263.	41	72						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00027	HL
64.	41	73						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00027	HL
5.	41	74						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00027	HL
5263.			0.71	164	M8M	1	09H 40.39	TEHTEC	S7675	rpri	A610MULC	SG10CCAL00008	CL
5267.	41	75						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00027	HL
5268.	41	76						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00027	HL
5269.	41	77						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00033	HL
5270.	41	78						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00027	HL
5271.	41	79						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00027	HL
5272.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00008	CL
5273.	41	80						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00027	HL
5274.	41	81						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00027	HL
5275.	41	82						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00018	HL
5276.	41	83						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00019	HL
5277.	41	84						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00018	HL
5278.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00006	CL
5279.	41	85						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00019	HL
5280.	41	86			RBD				B5534	rpri	B620MRPC3C	SG11HCAL00018	HL
5281.								TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00033	HL
5282.	41	87						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00019	HL
5283.	41	88						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00018	HL
5284.	41	89						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00019	HL
5285.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00006	CL
5286.	41	90						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00018	HL
5287.	41	91						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00019	HL
5288.	41	92						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00018	HL
5289.	41	93						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00019	HL
5290.	41	94						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00016	HL
								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00005	CL
5292.	41	95						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00017	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: A
 DATABASE: Harris_SGA_1995

Sep. 23, 1995 15:21

PAGE 110 of 124

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
5293.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00005	CL
5294.	42	21						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00048	HL
5295.		8.95	188	DNT	1	AV3	25.84	TEHTEC	F3325	rsec	A610MULC	SG10CCAL00011	CL
5296.		9.62	184	DNT	P1	AV4	0.00	TEHTEC	F3325	rsec	A610MULC	SG10CCAL00011	CL
5297.	42	22						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00047	HL
5298.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00011	CL
5299.	42	23						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00048	HL
5300.	42	24						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00047	HL
5301.	42	25						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00048	HL
5302.	42	26						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00047	HL
5303.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00011	CL
5304.	42	27						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00048	HL
5305.	42	28						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00047	HL
5306.	42	29						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00048	HL
5307.	42	30						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00047	HL
5308.	42	31						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00048	HL
5309.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00011	CL
5310.	42	32						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00047	HL
5311.	42	33						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00048	HL
5312.	42	34						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00047	HL
5313.	42	35						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00048	HL
5314.	42	36						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00047	HL
5315.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00011	CL
5316.	42	37						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00030	HL
5317.	42	38						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00029	HL
5318.	42	39						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00030	HL
5319.	42	40						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00029	HL
5320.	42	41						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00030	HL
5321.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00008	CL
5322.	42	42						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00029	HL
5323.	42	43						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00032	HL
5324.	42	44						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00031	HL
5325.	42	45						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00032	HL
5326.	42	46						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00031	HL
5327.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00008	CL
5328.	42	47						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00032	HL
5329.	42	48						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00031	HL
5330.	42	49						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00032	HL
5331.	42	50						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00031	HL
5332.	42	51						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00032	HL
5333.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00008	CL
5334.	42	52						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00031	HL
5335.	42	53						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00032	HL
5336.	42	54						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00031	HL
5337.	42	55						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00032	HL
5338.	42	56						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00031	HL
5339.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00008	CL
5340.	42	59						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00028	HL
5341.		0.73		19	P2	AV1	-0.03	TEHTEC	F2217	rpri	A610MULC	SG10CCAL00007	CL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: A
 DATABASE: Harris_SGA_1995

Sep. 23,1995 15:21

PAGE 111 of 124

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
5342.		0.90		23	P2	AV3	0.06	TEHTEC	F2217	rpri	A610MULC	SG10CCAL00007	CL
5343.	42	60						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00028	HL
5344.	42	61						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00028	HL
5345.	42	62						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00028	HL
5346.	42	63						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00028	HL
5347.	42	64						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00028	HL
5348.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00007	CL
5349.	42	65						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00028	HL
5350.	42	66						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00028	HL
5351.	42	67						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00028	HL
5352.	42	68						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00028	HL
5353.	42	69						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00028	HL
5354.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00008	CL
5355.	42	70						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00028	HL
5356.	42	71						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00028	HL
5357.	42	72						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00028	HL
5358.	42	73						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00028	HL
5359.	42	74						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00028	HL
5360.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00008	CL
5361.	42	75						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00028	HL
5362.	42	76						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00028	HL
5363.	42	77						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00033	HL
5364.	42	78						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00028	HL
5365.	42	79						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00028	HL
5366.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00008	CL
5367.	42	80						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00028	HL
5368.	42	81						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00028	HL
5369.	42	82						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00018	HL
5370.	42	83						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00019	HL
5371.	42	84						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00018	HL
5372.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00006	CL
5373.	42	85						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00019	HL
5374.	42	86						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00018	HL
5375.	42	87						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00019	HL
5376.	42	88						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00018	HL
5377.	42	89						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00019	HL
5378.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00006	CL
5379.	42	90						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00018	HL
5380.	42	91						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00019	HL
5381.	42	92						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00018	HL
5382.	42	93						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00019	HL
5383.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00006	CL
5384.	42	94			RBD			F3453	reso		B620MRPC3C	SG11HCAL00017	HL
5385.								TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00019	HL
5386.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00005	CL
5387.	43	22						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00048	HL
5388.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00011	CL
5389.	43	23						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00047	HL
5390.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00011	CL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: A
 DATABASE: Harris_SGA_1995

Sep. 23.1995 15:21

PAGE 112 of 124

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
5391.	43	24						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00048	HL
5392.	43	25						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00047	HL
5393.	43	26						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00048	HL
5394.								TEHTEC	F2217	rpri	A610MJLC	SG10CCAL00011	CL
5395.	43	27						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00047	HL
5396.	43	28						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00048	HL
5397.	43	29						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00047	HL
5398.	43	30						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00048	HL
5399.	43	31						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00047	HL
5400.								TEHTEC	F2217	rpri	A610MJLC	SG10CCAL00011	CL
5401.	43	32						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00048	HL
5402.	43	33						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00047	HL
5403.	43	34						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00048	HL
5404.	43	35						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00047	HL
5405.	43	36						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00047	HL
5406.								TEHTEC	F2217	rpri	A610MJLC	SG10CCAL00011	CL
5407.	43	37						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00030	HL
5408.	43	38						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00029	HL
5409.	43	39						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00030	HL
5410.	43	40						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00029	HL
11.	43	41						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00030	HL
12.								TEHTEC	S7675	rpri	A610MJLC	SG10CCAL00008	CL
13.	43	42						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00029	HL
5414.	43	43						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00032	HL
5415.	43	44						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00031	HL
5416.	43	45						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00032	HL
5417.	43	46						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00031	HL
5418.								TEHTEC	S7675	rpri	A610MJLC	SG10CCAL00008	CL
5419.	43	47						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00032	HL
5420.	43	48						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00031	HL
5421.	43	49						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00032	HL
5422.	43	50						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00031	HL
5423.	43	51						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00032	HL
5424.								TEHTEC	S7675	rpri	A610MJLC	SG10CCAL00008	CL
5425.	43	52						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00031	HL
5426.	43	53						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00032	HL
5427.	43	54						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00031	HL
5428.	43	55						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00032	HL
5429.	43	56						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00031	HL
5430.								TEHTEC	S7675	rpri	A610MJLC	SG10CCAL00008	CL
5431.	43	59						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00027	HL
5432.		0.58		16	P2	AV1	0.18	TEHTEC	F2217	rpri	A610MJLC	SG10CCAL00007	CL
5433.	43	60						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00027	HL
5434.	43	61						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00027	HL
5435.	43	62						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00027	HL
5436.	43	63						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00027	HL
5437.	43	64						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00027	HL
5438.								TEHTEC	F2217	rpri	A610MJLC	SG10CCAL00007	CL
5439.	43	65						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00027	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: A
 DATABASE: Harris_SGA_1995

Sep. 23,1995 15:21

PAGE 113 of 124

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
5440.	43	66					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00027	HL
5441.	43	67					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00027	HL
5442.	43	68					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00027	HL
5443.	43	69					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00027	HL
5444.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00008	CL
5445.	43	70					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00027	HL
5446.	43	71					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00027	HL
5447.	43	72					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00027	HL
5448.	43	73					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00027	HL
5449.	43	74					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00027	HL
5450.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00008	CL
5451.	43	75					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00027	HL
5452.	43	76					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00027	HL
5453.	43	77					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00027	HL
5454.	43	78					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00027	HL
5455.	43	79					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00027	HL
5456.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00008	CL
5457.	43	80					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00027	HL
5458.	43	81					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00027	HL
5459.	43	82					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00018	HL
5460.	43	83					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00019	HL
5461.	43	84					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00018	HL
5462.							TEHTEC	F2217	rpri	A610MULC	SG10CCAL00006	CL
5463.	43	85					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00019	HL
5464.	43	86					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00018	HL
5465.	43	87					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00019	HL
5466.	43	88					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00018	HL
5467.	43	89					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00019	HL
5468.							TEHTEC	F2217	rpri	A610MULC	SG10CCAL00006	CL
5469.	43	90					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00018	HL
5470.	43	91					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00019	HL
5471.	43	92					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00018	HL
5472.							TEHTEC	F2217	rpri	A610MULC	SG10CCAL00006	CL
5473.	43	93					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00019	HL
5474.							TEHTEC	F2217	rpri	A610MULC	SG10CCAL00006	CL
5475.	44	23					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00048	HL
5476.							TEHTEC	F2217	rpri	A610MULC	SG10CCAL00011	CL
5477.	44	24					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00047	HL
5478.							TEHTEC	F2217	rpri	A610MULC	SG10CCAL00011	CL
5479.	44	25					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00048	HL
5480.	44	26					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00047	HL
5481.							TEHTEC	F2217	rpri	A610MULC	SG10CCAL00011	CL
5482.	44	27					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00048	HL
5483.	44	28					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00047	HL
5484.	44	29					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00048	HL
5485.	44	30					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00047	HL
5486.	44	31					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00048	HL
5487.							TEHTEC	F2217	rpri	A610MULC	SG10CCAL00011	CL
5488.	44	32					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00047	HL

*** INSPECTION FINAL REPORT LISTING ***

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: A
 DATABASE: Harris_SGA_1995

Sep. 23, 1995 15:21

PAGE 114 of 124

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
5489.	44	33					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00048	HL
5490.	44	34					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00047	HL
5491.	44	35					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00048	HL
5492.	44	36					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00047	HL
5493.							TEHTEC	F2217	rpri	A610MULC	SG10CCAL00011	CL
5494.	44	37					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00030	HL
5495.	44	38					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00029	HL
5496.	44	39					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00030	HL
5497.	44	40					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00029	HL
5498.	44	41					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00030	HL
5499.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00008	CL
5500.	44	42					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00029	HL
5501.	44	43					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00032	HL
5502.	44	44					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00031	HL
5503.	44	45					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00032	HL
5504.	44	46					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00031	HL
5505.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00008	CL
5506.	44	47					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00032	HL
5507.	44	48					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00031	HL
5508.	44	49					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00032	HL
5509.	44	50					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00031	HL
5510.	44	51					TSHTSH	C7651	rsec	B620MRPC3C	SG11HCAL00032	HL
5511.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00008	CL
5512.	44	52					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00031	HL
5513.	44	53					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00032	HL
5514.	44	54					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00031	HL
5515.	44	55					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00032	HL
5516.	44	56					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00031	HL
5517.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00008	CL
5518.	44	60					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00028	HL
5519.	44	61					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00028	HL
5520.	44	62					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00028	HL
5521.	44	63					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00028	HL
5522.	44	64					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00028	HL
5523.							TEHTEC	F2217	rpri	A610MULC	SG10CCAL00007	CL
5524.	44	65					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00028	HL
5525.	44	66					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00028	HL
5526.	44	67					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00028	HL
5527.	44	68					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00028	HL
5528.	44	69					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00028	HL
5529.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00008	CL
5530.	44	70					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00028	HL
5531.	44	71					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00028	HL
5532.	44	72					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00028	HL
5533.	44	73					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00028	HL
5534.	44	74					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00028	HL
5535.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00008	CL
5536.	44	75					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00028	HL
5537.	44	76					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00028	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: A
 DATABASE: Harris_SGA_1995

Sep. 23.1995 15:21

PAGE 115 of 124

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
5538.	44	77					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00028	HL
5539.	44	78					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00028	HL
5540.	44	79					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00028	HL
5541.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00008	CL
5542.	44	80					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00028	HL
5543.	44	81					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00028	HL
5544.	44	82					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00018	HL
5545.	44	83					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00019	HL
5546.	44	84					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00018	HL
5547.							TEHTEC	F2217	rpri	A610MULC	SG10CCAL00006	CL
5548.	44	85					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00019	HL
5549.	44	86					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00018	HL
5550.	44	87					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00019	HL
5551.	44	88					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00018	HL
5552.	44	89					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00019	HL
5553.							TEHTEC	F2217	rpri	A610MULC	SG10CCAL00006	CL
5554.	44	90					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00018	HL
5555.	44	91					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00019	HL
5556.							TEHTEC	F2217	rpri	A610MULC	SG10CCAL00006	CL
5557.	44	92					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00019	HL
5558.							TEHTEC	F2217	rpri	A610MULC	SG10CCAL00006	CL
5559.	45	24					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00048	HL
5560.							TEHTEC	F2217	rpri	A610MULC	SG10CCAL00011	CL
5561.	45	25					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00047	HL
5562.							TEHTEC	F2217	rpri	A610MULC	SG10CCAL00011	CL
5563.	45	26					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00048	HL
5564.							TEHTEC	F2217	rpri	A610MULC	SG10CCAL00011	CL
5565.	45	27					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00047	HL
5566.	45	28					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00048	HL
5567.	45	29					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00047	HL
5568.	45	30					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00048	HL
5569.	45	31					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00047	HL
5570.							TEHTEC	F2217	rpri	A610MULC	SG10CCAL00011	CL
5571.	45	32					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00048	HL
5572.	45	33					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00047	HL
5573.	45	34					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00048	HL
5574.	45	35					TSHTSH	F7460	rsec	B620MRPC3C	SG11HCAL00047	HL
5575.	45	36					TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00047	HL
5576.							TEHTEC	F2217	rpri	A610MULC	SG10CCAL00011	CL
5577.	45	37					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00030	HL
5578.	45	38					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00029	HL
5579.	45	39					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00030	HL
5580.	45	40					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00029	HL
5581.	45	41					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00030	HL
5582.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00008	CL
5583.	45	42					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00029	HL
5584.	45	43					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00032	HL
5585.	45	44					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00031	HL
5586.	45	45					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00032	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: A
 DATABASE: Harris_SGA_1995

Sep. 23.1995 15:21

PAGE 116 of 124

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
5587.	45	46					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00031	HL
5588.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00008	CL
5589.	45	47					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00032	HL
5590.	45	48					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00031	HL
5591.	45	49					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00032	HL
5592.	45	50					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00031	HL
5593.	45	51					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00032	HL
5594.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00008	CL
5595.	45	52					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00031	HL
5596.	45	53					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00032	HL
5597.	45	54					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00031	HL
5598.	45	55					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00032	HL
5599.	45	56					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00031	HL
5600.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00008	CL
5601.	45	60					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00027	HL
5602.	45	61					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00027	HL
5603.	45	62					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00027	HL
5604.	45	63					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00027	HL
5605.	45	64					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00027	HL
5606.							TEHTEC	F2217	rpri	A610MULC	SG10CCAL00007	CL
07.	45	65					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00027	HL
09.	45	66					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00027	HL
11.	45	67					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00027	HL
5610.	45	68					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00027	HL
5611.	45	69					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00027	HL
5612.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00008	CL
5613.	45	70					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00027	HL
5614.	45	71					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00027	HL
5615.	45	72					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00027	HL
5616.	45	73					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00027	HL
5617.	45	74					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00027	HL
5618.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00008	CL
5619.	45	75					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00027	HL
5620.	45	76					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00027	HL
5621.	45	77					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00027	HL
5622.	45	78					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00027	HL
5623.	45	79					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00027	HL
5624.							TEHTEC	S7675	rpri	A610MULC	SG10CCAL00008	CL
5625.	45	80					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00027	HL
5626.	45	81					TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00027	HL
5627.	45	82			RBD			B5534	rpri	B620MRPC3C	SG11HCAL00018	HL
5628.							TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00033	HL
5629.							TEHTEC	F2217	rpri	A610MULC	SG10CCAL00006	CL
5630.	45	83					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00019	HL
5631.	45	84					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00018	HL
5632.							TEHTEC	F2217	rpri	A610MULC	SG10CCAL00006	CL
5633.	45	85					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00019	HL
5634.	45	86					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00018	HL
5635.	45	87					TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00019	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: A
 DATABASE: Harris_SGA_1995

Sep. 23, 1995 15:21

PAGE 117 of 124

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
5636.	45	88						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00018	HL
5637.	45	89						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00019	HL
5638.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00006	CL
5639.	45	90						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00018	HL
5640.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00006	CL
5641.	45	91						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00019	HL
5642.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00006	CL
5643.	46	26						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00048	HL
5644.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00011	CL
5645.	46	27						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00047	HL
5646.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00011	CL
5647.	46	28						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00048	HL
5648.	46	29						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00047	HL
5649.	46	30						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00048	HL
5650.	46	31						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00047	HL
5651.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00011	CL
5652.	46	32						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00048	HL
5653.	46	33						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00047	HL
5654.	46	34						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00048	HL
5655.	46	35						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00047	HL
56.	46	36						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00047	HL
57.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00011	CL
58.	46	37						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00030	HL
5659.	46	38						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00029	HL
5660.	46	39						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00030	HL
5661.	46	40						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00029	HL
5662.	46	41						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00030	HL
5663.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00008	CL
5664.	46	42						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00029	HL
5665.	46	43						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00032	HL
5666.	46	44						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00031	HL
5667.	46	45						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00032	HL
5668.	46	46						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00031	HL
5669.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00008	CL
5670.	46	47						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00032	HL
5671.	46	48						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00031	HL
5672.	46	49						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00032	HL
5673.	46	50						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00031	HL
5674.	46	51						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00032	HL
5675.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00008	CL
5676.	46	52						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00031	HL
5677.	46	53						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00032	HL
5678.	46	54						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00031	HL
5679.	46	55						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00032	HL
5680.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00008	CL
581.	46	56						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00031	HL
582.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00008	CL
583.	46	59						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00028	HL
584.			0.63	17	P2	AV3	0.06	TEHTEC	F2217	rpri	A610MULC	SG10CCAL00007	CL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: A
 DATABASE: Harris_SGA_1995

Sep. 23.1995 15:21

PAGE 118 of 124

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
5685.		0.93		23	P2	AV4	0.09	TEHTEC	F2217	rpri	A610MULC	SG10CCAL00007	CL
5686.	46	60						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00028	HL
5687.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00007	CL
5688.	46	61						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00028	HL
5689.	46	62						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00028	HL
5690.	46	63						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00028	HL
5691.	46	64						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00028	HL
5692.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00007	CL
5693.	46	65						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00028	HL
5694.	46	66						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00028	HL
5695.	46	67						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00028	HL
5696.	46	68						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00028	HL
5697.	46	69						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00028	HL
5698.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00008	CL
5699.	46	70						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00028	HL
5700.	46	71						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00028	HL
5701.	46	72						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00028	HL
5702.	46	73						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00028	HL
5703.	46	74						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00028	HL
5704.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00008	CL
05.	46	75						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00028	HL
06.	46	76						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00028	HL
07.	46	77						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00028	HL
5708.	46	78						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00028	HL
5709.	46	79						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00028	HL
5710.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00008	CL
5711.	46	80						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00028	HL
5712.	46	81						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00028	HL
5713.	46	82						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00018	HL
5714.	46	83						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00019	HL
5715.	46	84						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00018	HL
5716.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00006	CL
5717.	46	85						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00019	HL
5718.	46	86						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00018	HL
5719.	46	87						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00019	HL
5720.	46	88						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00018	HL
5721.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00006	CL
5722.	46	89						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00019	HL
5723.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00006	CL
5724.	47	27						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00048	HL
5725.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00011	CL
5726.	47	28						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00047	HL
5727.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00011	CL
5728.	47	29						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00048	HL
5729.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00011	CL
5730.	47	30						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00047	HL
5731.	47	31						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00048	HL
5732.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00011	CL
5733.	47	32						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00047	HL

*** INSPECTION FINAL REPORT LISTING ***

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: A
 DATABASE: Harris_SGA_1995

Sep. 23.1995 15:21

PAGE 119 of 124

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
5734.	47	33						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00048	HL
5735.	47	34						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00047	HL
5736.	47	35						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00048	HL
5737.	47	36						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00047	HL
5738.								TEHTEC	F3325	rsec	A610MULC	SG10CCAL00011	CL
5739.	47	37						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00030	HL
5740.	47	38						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00029	HL
5741.	47	39						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00030	HL
5742.	47	40						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00029	HL
5743.	47	41						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00030	HL
5744.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00008	CL
5745.	47	42						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00029	HL
5746.	47	43						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00032	HL
5747.	47	44						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00031	HL
5748.	47	45						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00032	HL
5749.	47	46						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00031	HL
5750.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00008	CL
5751.	47	47						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00032	HL
5752.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00008	CL
5753.	47	48						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00031	HL
54.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00008	CL
55.	47	49						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00032	HL
56.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00008	CL
5757.	47	50						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00031	HL
5758.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00008	CL
5759.	47	51						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00032	HL
5760.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00008	CL
5761.	47	52						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00031	HL
5762.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00008	CL
5763.	47	53						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00032	HL
5764.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00008	CL
5765.	47	54						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00031	HL
5766.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00008	CL
5767.	47	55						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00032	HL
5768.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00008	CL
5769.	47	56						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00031	HL
5770.		0.20		9	P2	AV1	0.00	TEHTEC	F3453	reso	A610MULC	SG10CCAL00008	CL
5771.		0.71		26	P2	AV2	0.00	TEHTEC	F3453	reso	A610MULC	SG10CCAL00008	CL
5772.		0.52		21	P2	AV3	0.00	TEHTEC	F3453	reso	A610MULC	SG10CCAL00008	CL
5773.		0.69		26	P2	AV4	0.00	TEHTEC	F3453	reso	A610MULC	SG10CCAL00008	CL
5774.	47	60						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00027	HL
5775.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00007	CL
5776.	47	61						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00027	HL
5777.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00007	CL
5778.	47	62						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00027	HL
5779.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00007	CL
5780.	47	63						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00027	HL
5781.		0.55		15	P2	AV2	0.00	TEHTEC	D4825	reso	A610MULC	SG10CCAL00007	CL
5782.	47	64						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00027	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: A
 DATABASE: Harris_SGA_1995

Sep. 23, 1995 15:21

PAGE 120 of 124

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
5783.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00007	CL
5784.	47	65						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00027	HL
5785.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00007	CL
5786.	47	66						TSHTSH	D3858	reso	B620MRPC3C	SG11HCAL00027	HL
5787.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00007	CL
5788.	47	67						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00027	HL
5789.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00007	CL
5790.	47	68						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00027	HL
5791.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00007	CL
5792.	47	69						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00027	HL
5793.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00008	CL
5794.	47	70						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00027	HL
5795.	47	71						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00027	HL
5796.			0.79	152	MBM	1	07C 19.98	TEHTEC	S7675	rpri	A610MULC	SG10CCAL00008	CL
5797.	47	72						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00027	HL
5798.	47	73						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00027	HL
5799.	47	74						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00027	HL
5800.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00008	CL
5801.	47	75						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00027	HL
5802.	47	76						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00027	HL
03.	47	77						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00027	HL
04.	47	78						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00027	HL
05.	47	79						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00027	HL
5806.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00008	CL
5807.	47	80						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00027	HL
5808.	47	81						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00027	HL
5809.	47	82						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00018	HL
5810.	47	83						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00019	HL
5811.	47	84						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00018	HL
5812.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00006	CL
5813.	47	85						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00019	HL
5814.	47	86						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00018	HL
5815.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00006	CL
5816.	47	87						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00019	HL
5817.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00006	CL
5818.	47	88						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00019	HL
5819.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00006	CL
5820.	48	29						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00048	HL
5821.			8.89	186	DNT	1	AV2 30.71	TEHTEC	F2217	rpri	A610MULC	SG10CCAL00011	CL
5822.	48	30						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00047	HL
5823.			10.22	186	DNT	1	AV1 27.40	TEHTEC	F2217	rpri	A610MULC	SG10CCAL00011	CL
5824.	48	31						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00048	HL
5825.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00011	CL
5826.	48	32						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00047	HL
5827.	48	33						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00048	HL
28.	48	34						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00047	HL
29.	48	35						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00048	HL
).	48	36						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00047	HL
1.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00011	CL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: A
 DATABASE: Harris_SGA_1995

Sep. 23.1995 15:21

PAGE 121 of 124

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
5832.	48	37						TSHTSH	C7651	rsec	B620MRPC3C	SG11HCAL00030	HL
5833.	48	38						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00029	HL
5834.	48	39						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00030	HL
5835.	48	40						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00029	HL
5836.	48	41						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00030	HL
5837.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00008	CL
5838.	48	42						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00029	HL
5839.	48	43						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00032	HL
5840.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00008	CL
5841.	48	44						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00031	HL
5842.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00008	CL
5843.	48	45						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00032	HL
5844.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00008	CL
5845.	48	46						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00031	HL
5846.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00008	CL
5847.	48	47						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00032	HL
5848.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00008	CL
5849.	48	48						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00031	HL
5850.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00008	CL
5851.	48	49						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00032	HL
52.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00008	CL
53.	48	50						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00031	HL
54.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00008	CL
5855.	48	51						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00032	HL
5856.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00008	CL
5857.	48	52						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00031	HL
5858.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00008	CL
5859.	48	53						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00032	HL
5860.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00008	CL
5861.	48	54						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00031	HL
5862.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00008	CL
5863.	48	55						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00032	HL
5864.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00008	CL
5865.	48	56						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00031	HL
5866.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00008	CL
5867.	48	59						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00028	HL
5868.		0.63	157	MBM	1	09H	18.62	TEHTEC	F2217	rpri	A610MULC	SG10CCAL00007	CL
5869.		0.52	151	MBM	1	07C	38.91	TEHTEC	F7460	rsec	A610MULC	SG10CCAL00007	CL
5870.	48	60						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00028	HL
5871.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00007	CL
5872.	48	61						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00028	HL
5873.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00007	CL
5874.	48	62						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00028	HL
5875.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00007	CL
5876.	48	63						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00028	HL
577.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00007	CL
578.	48	64						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00028	HL
579.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00007	CL
580.	48	65						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00028	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: A
 DATABASE: Harris_SGA_1995

Sep. 23.1995 15:21

PAGE 122 of 124

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG	
5881.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00007	CL	
5882.	48	66						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00028	HL	
5883.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00007	CL	
5884.	48	67						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00028	HL	
5885.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00007	CL	
5886.	48	68						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00028	HL	
5887.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00007	CL	
5888.	48	69						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00028	HL	
5889.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00008	CL	
5890.	48	70						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00028	HL	
5891.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00008	CL	
5892.	48	71						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00028	HL	
5893.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00008	CL	
5894.	48	72						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00028	HL	
5895.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00008	CL	
5896.	48	73						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00028	HL	
5897.	48	74						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00028	HL	
5898.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00008	CL	
5899.	48	75						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00028	HL	
5900.	48	76						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00028	HL	
01.	48	77						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00028	HL	
?	48	78						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00028	HL	
.3.	48	79						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00028	HL	
5904.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00008	CL	
5905.	48	80						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00028	HL	
5906.	48	81						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00028	HL	
5907.	48	82						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00018	HL	
5908.	48	83						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00019	HL	
5909.	48	84						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00018	HL	
5910.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00006	CL	
5911.	48	85						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00019	HL	
5912.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00006	CL	
5913.	48	86						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00019	HL	
5914.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00006	CL	
5915.	49	31						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00048	HL	
5916.			7.11	190	DNT	P1	AV2	0.24	TEHTEC	F2217	rpri	A610MULC	SG10CCAL00011	CL
5917.	49	32						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00047	HL	
5918.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00011	CL	
5919.	49	33						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00048	HL	
5920.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00011	CL	
5921.	49	34						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00047	HL	
5922.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00011	CL	
5923.	49	35						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00048	HL	
5924.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00011	CL	
5925.	49	36						TSHTSH	F9284	rpri	B620MRPC3C	SG11HCAL00047	HL	
5926.		12.06	186	DNT	1	11H	8.74	TEHTEC	F3325	rsec	A610MULC	SG10CCAL00011	CL	
5927.		7.72	187	DNT	1	11H	9.38	TEHTEC	F3325	rsec	A610MULC	SG10CCAL00011	CL	
j.	49	37						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00030	HL	
29.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00008	CL	

*** INSPECTION FINAL REPORT LISTING ***

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: A
 DATABASE: Harris_SGA_1995

Sep. 23, 1995 15:21

PAGE 123 of 124

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
5930.	49	38						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00029	HL
5931.					RND			TEHTEC	D4825	reso	A610MULC	SG10CCAL00016	CL
5932.		4.07	37		NQI	P3	TEC 6.08	TEHTEC	S7675	rpri	A610MULC	SG10CCAL00008	CL
5933.					DMR	1	TEC 6.08	TECTSC	D3858	reso	B620MRPC3C	SG10CCAL00023	CL
5934.	49	39						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00030	HL
5935.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00008	CL
5936.	49	40						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00029	HL
5937.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00008	CL
5938.	49	41						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00032	HL
5939.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00008	CL
5940.	49	42						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00031	HL
5941.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00008	CL
5942.	49	43						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00032	HL
5943.		0.60		26	P2	07C	0.39	TEHTEC	S7675	rpri	A610MULC	SG10CCAL00008	CL
5944.	49	44						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00031	HL
5945.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00008	CL
5946.	49	45						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00032	HL
5947.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00008	CL
5948.	49	46						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00031	HL
5949.		0.40		19	P2	07C	0.42	TEHTEC	S7675	rpri	A610MULC	SG10CCAL00008	CL
50.	49	47						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00032	HL
51.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00008	CL
52.	49	48						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00031	HL
5953.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00008	CL
5954.	49	49						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00032	HL
5955.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00008	CL
5956.	49	50						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00031	HL
5957.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00008	CL
5958.	49	51						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00032	HL
5959.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00008	CL
5960.	49	52						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00031	HL
5961.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00008	CL
5962.	49	53						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00032	HL
5963.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00008	CL
5964.	49	54						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00031	HL
5965.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00008	CL
5966.	49	55						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00032	HL
5967.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00008	CL
5968.	49	56						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00031	HL
5969.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00008	CL
5970.	49	59						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00027	HL
5971.		7.24	182	DNT	1	AV4	28.60	TEHTEC	F2217	rpri	A610MULC	SG10CCAL00007	CL
5972.	49	60						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00027	HL
5973.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00007	CL
5974.	49	61						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00027	HL
75.		1.83	109	30	P1	09C	0.09	TEHTEC	F2217	rpri	A610MULC	SG10CCAL00007	CL
76.	49	62						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00027	HL
77.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00007	CL
78.	49	63						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00027	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: A
 DATABASE: Harris_SGA_1995

Sep. 23,1995 15:21

PAGE 124 of 124

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG	
5979.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00007	CL	
5980.	49	64						TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00033	HL	
5981.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00007	CL	
5982.	49	65						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00027	HL	
5983.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00007	CL	
5984.	49	66						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00027	HL	
5985.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00007	CL	
5986.	49	67						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00027	HL	
5987.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00007	CL	
5988.	49	68						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00027	HL	
5989.								TEHTEC	F2217	rpri	A610MULC	SG10CCAL00007	CL	
5990.	49	69						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00027	HL	
5991.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00008	CL	
5992.	49	70						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00027	HL	
5993.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00008	CL	
5994.	49	71						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00027	HL	
5995.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00008	CL	
5996.	49	72						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00027	HL	
5997.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00008	CL	
5998.	49	73						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00027	HL	
99.								TEHTEC	F7460	rsec	A610MULC	SG10CCAL00008	CL	
99.	49	74						TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00027	HL	
99.								TEHTEC	S7675	rpri	A610MULC	SG10CCAL00008	CL	
6002.	49	75	5.94	181	DNT	P1	05C	0.39	TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00027	HL
6003.									TEHTEC	S7675	rpri	A610MULC	SG10CCAL00008	CL
6004.	49	76							TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00027	HL
6005.									TEHTEC	S7675	rpri	A610MULC	SG10CCAL00008	CL
6006.	49	77							TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00027	HL
6007.									TEHTEC	S7675	rpri	A610MULC	SG10CCAL00008	CL
6008.	49	78							TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00027	HL
6009.			6.75	179	DNT	1	10H	29.16	TEHTEC	S7675	rpri	A610MULC	SG10CCAL00008	CL
6010.	49	79							TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00027	HL
6011.									TEHTEC	S7675	rpri	A610MULC	SG10CCAL00008	CL
6012.	49	80							TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00027	HL
6013.									TEHTEC	S7675	rpri	A610MULC	SG10CCAL00008	CL
6014.	49	81							TSHTSH	S7067	rpri	B620MRPC3C	SG11HCAL00027	HL
6015.									TEHTEC	S7675	rpri	A610MULC	SG10CCAL00008	CL
6016.	49	82							TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00018	HL
6017.									TEHTEC	F2217	rpri	A610MULC	SG10CCAL00006	CL
6018.	49	83							TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00019	HL
6019.									TEHTEC	F2217	rpri	A610MULC	SG10CCAL00006	CL
6020.	49	84							TSHTSH	B5534	rpri	B620MRPC3C	SG11HCAL00019	HL
6021.			5.99	185	DNT	1	10C	34.36	TEHTEC	F2217	rpri	A610MULC	SG10CCAL00006	CL
6022.			0.20	143	34	1	03C	25.79	TEHTEC	F7460	rsec	A610MULC	SG10CCAL00006	CL

G.T - "A"

ABB Combustion Engineering		Multi-Frequency Eddy Current Calibration Data Sheet		Disk #	Side
Owner: CP&L		Site/Unit: SHEARON HARRIS	Component: S/G: <u>A/B/C</u>	Leg: <u>HOT</u> /COLD	Date: 9-18-95
MIZ-18A / <u>MIZ-30</u> S/N- <u>897</u>		Procedure: HNP-004 RO	Defect Std. (1) <u>Z-14289</u>	Additional Std. (2) <u>N/A</u>	
Cal	Date	Row Line	Standard Run	Comments	Examiner Init/Level
	Time				
001	9/18/95 22:10	21/38	BEGIN CAL GRP		JL II
001	9/19/95 00:57	22/42	END CAL GRP	ROTATION SPEED	JL II
003	9/19/95 01:12	23/42	BEGIN CAL GRP		JL II
003	9/19/95 04:28	22/45	END CAL GRP	END ZONE 1	JL II
005	9/19/95 03:18	12/37	BEGIN CAL GRP	BEG ZONE 2	JL II
005	9-19-95 08:46	20/56	END CAL GRP	END ZONE 2	JL II
007	9-19-95 09:18	2/37	NEW CAL GRP	NEW ZONE 3	JL II
007	9-19-95 12:56	10/56	END CAL GRP	END ZONE 3	JL II
009	9-19-95 13:36	1/94	BEGIN CAL GRP	DISREGARD THIS CAL	JL II
009	9-19-95 01:34	2/94	BEGIN CAL GRP		JL II
009	9-19-95 19:40	7/110	END CAL GRP.		JL II
Additional Comments:					
Shift Supervisor Final Review of Acceptance					
Reviewed by: <u>David A. Shoch</u> Level <u>II</u>					
Approved by: _____ ET Level III					

GT-"B"

ABB Combustion Engineering		Multi-Frequency Eddy Current Calibration Data Sheet			Disk #	Side
Owner: CP&L		Site/Unit: SHEARON HARRIS	Component: SIG: (A) B / C		Leg: HOT / COLD	Date: 9/18/95
MIZ-18A / MIZ-30 S/N- 297		Procedure: HNP-004 RO		Defect Std. (1) Z-140 90	Additional Std. (2) N/A	
Cal	Date Time	Row Line	Standard Run	Comments	Examiner Init/Level	
002	9-18-95 22:16	21 37	BEGIN CAL GRP		JR II	
002	9-19-95 00:59	22 41	END CAL GRP	ROTATION SPEED	JR II	
004	9-19-95 01:19	23 41	BEGIN CAL GRP		JR II	
004	9-19-95 04:34	30 53	END CAL GRP	END ZONE 1	JR II	
006	9-19-95 05:20	11 37	BEG CAL GRP	BEG ZONE 2	JR II	
006	9-19-95 08:49	19 56	END CAL GRP	End zone 2	JR II	
008	9-19-95 09:28	1 37	NEW CAL GRP	beg zone 3	JR II	
008	9-19-95 13:00	9 56	END CAL GRP	End zone 3	JR II	
010	9-19-95 13:43	21 114	BEGIN CAL GRP		JR II	
010	9-19-95 16:17	1 114	END CAL		JR II	
Additional Comments:						
Shift Supervisor Final Review of Acceptance						
Reviewed by: <u>David G. Alcock</u> Level <u>II</u>						
Approved by: _____ ET Level III						

"A" GT

ABB Combustion Engineering		Multi-Frequency Eddy Current Calibration Data Sheet		Disk #	Side
Owner: CP&L		Site/Unit: SHEARON HARRIS	Component: SIG: (A) B / C	Leg: HOT / COLD	Date: 9-19-95
MIZ-18A / MIZ-30 SN- 97		Procedure: HNP-004 RO	Defect Std. (1) Z-14259	Additional Std. (2) N/A	
Cal	Date Time	Row Line	Standard Run	Comments	Examiner Init/Level
012	9-19-95 20:08	9/110	BEGIN CAL GRP		JR II
012	9-19-95 23:20	12/104	END CAL GRP		JR II
014	9-19-95 23:42	13/104	BEGIN CAL GRP		JR II
014	9-20-95 02:43	22/104	END CAL GRP	HEAD PROBE CHANGE	JR II
016	9-20-95 04:20	23/104	BEGIN CAL GRP	NEW HEAD PROBE	JR II
016	9-20-95 0741	33/102	END CAL GRP		JR II
018	9-20-95 0855	41/82	NEW CAL GRP	ZONE 9.	JR II
018	9-20-95 1158	40/92	END CAL GRP	ZONE 9, 10	JR II
020	9-20-95 1213	21/82	NEW CAL GRP	ZONE 11,	JR II
020	9-20-95 1510	12/87	END CAL GRP	ZONE 11, 12	JR II
Additional Comments:					
Shift Supervisor Final Review of Acceptance					
Reviewed by: <u>David C. Alford</u>		Level <u>II</u>			
Approved by: _____		ET Level III			

"B" GT

ABB Combustion Engineering		Multi-Frequency Eddy Current Calibration Data Sheet		Disk # <i>N/A</i>	Side <i>N/A</i>
Owner: CP&L		Site/Unit: SHEARON HARRIS	Component: S/G: <u>A</u> / B / C	Leg: (HOT) COLD	Date: 9-19-95
MIZ-18A / MIZ-30 S/N- 097		Procedure: HNP-004 RO	Defect Std. (1) Z 14090	Additional Std. (2) NA	
Cal	Date Time	Row Line	Standard Run	Comments	Examiner Init/Level
011	9-19-95 16:40	2/95	BEGIN CAL GRP		<i>QJ II</i>
011	9-19-95 19:45	7/111	END CAL GRP		<i>QJ II</i>
013	9-19-95 20:11	8/111	BEGIN CAL GRP		<i>QJ II</i>
013	9-19-95 23:23	12/105	END CAL GRP		<i>QJ II</i>
015	9-19-95 23:45	13/105	BEGIN CAL GRP		<i>QJ II</i>
015	9-20-95 02:51	22/105	END CAL GRP	HEAD PROBE CHANGE	<i>QJ II</i>
017	9-20-95 04:24	23/105	BEGIN CAL GRP	NEW HEAD PROBE	<i>QJ II</i>
019	9-20-95 08:10	33/102	END CAL GRP	MOTOR UNIT Dreid. can not cal	<i>QJ II</i>
019	9-20-95 08:58	42/94	NEW CAL GRP	NEW MOTOR UNIT / ZONE 8,9	<i>QJ II</i>
019	9-20-95 12:00	40/93	END CAL GRP	ZONE 8,9,10	<i>QJ II</i>
Additional Comments:					
Shift Supervisor Final Review of Acceptance					
Reviewed by: <i>David G. Shock</i> Level <i>II</i>					
Approved by: _____ ET Level III					

"A" GT

ABB Combustion Engineering		Multi-Frequency Eddy Current Calibration Data Sheet			Disk # N/A	Side N/A
Owner: CP&L		Site/Unit: SHEARON HARRIS	Component: SIG: A/B/C		Leg: HOT/COLD	Date: 9-20-95
MIZ-18A (MIZ-30) S/N- 097		Procedure: HNP-004 RO	Defect Std. (1) Z-14089		Additional Std. (2) N/A	
Cal	Date	Row	Standard Run	Comments	Examiner	
	Time	Line				Init/Level
023	9-20-95 1535	16/87	NEW CAL GRP		APP II	
025	9-20-95 1810	18/93	END CAL GRP	ZONE 12,13	APP II	
025	9-26-95 19:36	31/59	NEW CAL GRP	ZONE 14	APP II	
025	9-20-95 21:30	36/79	END CAL GRP	ZONE 14	APP II	
027	9-20-95 21:40	37/79	NEW CAL GRP	ZONE 14	APP II	
027	9/21/95 00:53	49/81	END CAL	ZONE 15	APP II	
029	9/21/95 01:19	41/78	NEW CAL GRP	ZONE 16	APP II	
029	9-21-95 04:56	48/42	END CAL GRP	ZONE 16	APP II	
031	9-21-95 05:13	49/42	NEW CAL GRP	ZONE 16	APP II	
031	9-21-95 0706	45/56	END CAL GRP	ZONE 16		
Additional Comments:						
Shift Supervisor Final Review of Acceptance						
Reviewed by: <u>David A. Stock</u> Level <u>II</u>						
Approved by: _____ ET Level III						

-11 B GT

ABB Combustion Engineering		Multi-Frequency Eddy Current Calibration Data Sheet		Disk # N/A	Side N/A
Owner: CP&L		Site/Unit: SHEARON HARRIS	Component: SIG: (A) B/C	Leg: HOT COLD	Date: 9-20-95
MIZ-18A (MIZ-30) S/N- Q97	Procedure: HNP-004 RO		Defect Std. (1) 2-14090	Additional Std. (2) N/A	
Cal	Date	Row	Standard Run	Comments	Examiner
	Time	Line			Init/Level
021	9-20-95 12:15	21/86	NEW CAL GRP	ZONE 11,	JAL II
021	9-20-95 15:13	23/87	END CAL GRP	ZONE 11, 12	JAL II
023	9-20-95 15:13	26/87	NEW CAL GRP	ZONE 12.	
024	9-20-95 15:30	15/87	NEW CAL GRP	ZONE 12	RRP II
024	9-20-95 18:14	9/93	END CAL GRP	ZONE 12, 13	JAL II
026	9-20-95 19:39	31/60	NEW CAL GRP	ZONE 14	JAL II
026	9-20-95 21:33	36/90	END CAL GRP	ZONE 14	JAL II
029	9-20-95 21:43	37/50	NEW CAL GRP	ZONE 14,	JAL II
028	9/21/95 00:59	48/81	END CAL.	ZONE 15	RRP II
030	9/21/95 01:21	41/37	NEW CAL GRP	ZONE 16	JAL II
030	9-24-95 04:58	48/41	END CAL GRP	ZONE 16	JAL II
Additional Comments:					
Shift Supervisor Final Review of Acceptance					
Reviewed by: <u>David A. Shuck</u> Level <u>II</u>					
Approved by: _____ ET Level III					

" A " GT

ABB Combustion Engineering		Multi-Frequency Eddy Current Calibration Data Sheet		Disk # N/A	Side N/A
Owner: CP&L		Site/Unit: SHEARON HARRIS	Component: SIG: A/B/C	Leg: HOT/COLD	Date: 9-21-95
MIZ-18A / MIZ-30 S/N- 097	Procedure: HNP-004 RO		Defect Std. (1) 2-14089	Additional Std. (2) N/A	
Cal	Date	Row Line	Standard Run	Comments	Examiner Init/Level
	Time				
033	9-21-95 0716	31/38	NEW CAL GRP	ZONE 17	DI II
033	9-21-95 0720	2/111	END CAL GRP	ZONE 17 + Retest	DI II
035	9-21-95 1004	15/112	NEW CAL GRP	EXAM OF DENTS	DI II
035	9-21-95 1037	15/112	NEW CAL	NEW PROBE 590	DI II
035	9-21-95 1232	15/112	NEW CAL	NEW PROBE	DI II
038	9-21-95 1405	38/45	END CAL GRP	END OF DENT EXAM	DI II
036	9-21-95 1502	45/112	NEW CAL GRP	Retest	DI II
036	9-21-95 1536	38/45	END CAL	END. Retest	DI II
038	9-21-95 0140	20/59	NEW CAL	ZONE 18	SPHA
038	9-22-95 0605	20/65	END CAL	THIS EQUIP. PROBLEMS COULD NOT PULL DATA	ZONE 18 SPHA
41	9-22-95 0612	21/66	NEW CAL GRP	ZONE 19	SPHA
Additional Comments: Equip. Mgmt Failure Could not pull 4 hr. cal. Pulled when equipment problems fixed. CAL 038					
Shift Supervisor Final Review of Acceptance					
Reviewed by: <u>Paul A. Shook</u> Level <u>II</u>					
Approved by: <u>Thomas A. ...</u> ET Level III					

"B" GT

ABB Combustion Engineering		Multi-Frequency Eddy Current Calibration Data Sheet			Disk # <i>N/A</i>	Side <i>N/A</i>
Owner: CP&L		Site/Unit: SHEARON HARRIS	Component: SIG (A) B/C		Leg: HOT/COLD	Date: 9-21-95
MIZ-18A / MIZ-30 S/N- <i>097</i>		Procedure: HNP-004 RO	Defect Std. (1) <i>Z-14090</i>		Additional Std. (2) <i>N/A</i>	
Cal	Date	Row Line	Standard Run	Comments	Examiner	
	Time				Init/Level	
<i>032</i>	<i>9-21-95</i> <i>09:16</i>	<i>49/41</i>	<i>NEW CAL GRP</i>	<i>ZONE 16</i>	<i>JL II</i>	
<i>033</i>	<i>9-21-95</i> <i>0707</i>	<i>49/55</i>	<i>END CAL GRP</i>	<i>ZONE 16</i>	<i>JL II</i>	
<i>034</i>	<i>9-21-95</i> <i>0722</i>	<i>31/37</i>	<i>NEW CAL GRP</i>	<i>ZONE 17</i>	<i>JL II</i>	
<i>034</i>	<i>9-21-95</i> <i>0723</i>	<i>40/55</i>	<i>END CAL GRP</i>	<i>ZONE 17</i>	<i>JL II</i>	
<i>039</i>	<i>9-21-95</i> <i>0140</i>	<i>25/59</i>	<i>NEW CAL GROUP</i>	<i>ZONE 18</i>	<i>SP III</i>	
<i>039</i>	<i>9/22/95</i> <i>0330</i>	<i>28/65</i>	<i>END PROBE CAL</i>	<i>ZONE 18</i>	<i>SP III</i>	
<i>040</i>	<i>0340</i>	<i>VOID</i> <i>29/22/95</i>	<i>NEW PROBE CAL</i>	<i>ZONE 18</i>	<i>SP III</i>	
<i>42</i>	<i>9-22-95</i> <i>0612</i>	<i>21/68</i>	<i>NEW CAL GRP.</i>	<i>ZONE 19</i>	<i>SP IIIA</i>	
Additional Comments:						
Shift Supervisor Final Review of Acceptance						
Reviewed by: <i>David A. Shook</i> Level <i>II</i>						
Approved by: _____ ET Level III						

A" 50

ABB Combustion Engineering		Multi-Frequency Eddy Current Calibration Data Sheet			Disk # N/A	Side N/A
Owner: CP&L		Site/Unit: SHEARON HARRIS	Component: S/G: (A) B/C	Leg: (HOT) COLD	Date: 9-22-95	
MIZ-18A / MIZ-30 S/N- 097		Procedure: HNP-004 RO	Defect Std. (1) E-14089	Additional Std. (2) N/A		
Cal	Date	Row Line	Standard Run	Comments	Examiner	
	Time				Init/Level	
041	9-22-95 0855	26/72	END CAL	NEED NEW Probe	DL II	
043	9-22-95 0932	27/72	NEW CAL Group		DL II	
043	1135 9-22-95	26/76	END CAL Group		DL II	
045	9-22-95 1252	2/57	NEW CAL GRP		DL II	
045	9-22-95 1430	10/76	END CAL GRP		MB II	
047	9-22-95 1431	41/21	NEW CAL RP		MB II	
047	9-22-95 1759	41/21	NEW CAL SRP		MB II	
047	9-22-95 21:22	33/25	END CAL GRP		DL II	
049	9-22-95 21:35	35/25	NEW CAL GRP		DL II	
049	9-22-95 23:54	27/21	END CAL GRP		DL II	
Additional Comments:						
Shift Supervisor Final Review of Acceptance						
Reviewed by: <u>David G. Alford</u> Level <u>II</u>						
Approved by: _____ ET Level III						

"B" G.T.

ABB Combustion Engineering		Multi-Frequency Eddy Current Calibration Data Sheet		Disk # N/A	Side N/A
Owner: CP&L		Site/Unit: SHEARON HARRIS	Component: SIG: <u>A</u> B / C	Log: <u>HOT</u> COLD	Date: 9-21-95
MIZ-18A <u>MIZ-30</u> S/N- <u>097</u>		Procedure: HNP-004 RO	Defect Std. (1) <u>Z-14090</u>	Additional Std. (2) N/A	
Cal	Date	Row	Standard Run	Comments	Examiner
	Time	Line			Init/Level
042	9-22-95 0734	26 73	END CAL	NEED NEW Probe	MB II
044	9-22-95 0935	28 73	NEW CAL Group		MB II
044	9-22-95 1238	11/76	END CAL Group		MB II
046	9-22-95 1259	1/57	NEW CAL GRP		MB II
046	9-22-95 1430	9/76	END CAL GRP		MB II
048	9-22-95 1431	41/20	NEW CAL GRP		MB II
048	9-22-95 1759	41/20	NEW CAL GRP		MB II
048	9-22-95 21:24	33/24	END CAL GRP		MB II
050	9-22-95 21:38	35/24	NEW CAL GRP		MB II
050	9-22-95 23:56	27/20	END CAL GRP		MB II
Additional Comments:					
Shift Supervisor Final Review of Acceptance					
Reviewed by: <u>David A. Shook</u> Level <u>II</u>					
Approved by: _____ ET Level III					

"A" GT

ABB Combustion Engineering		Multi-Frequency Eddy Current Calibration Data Sheet			Disk # <i>N/A</i>	Side <i>N/A</i>
Owner: CP&L		Site/Unit: SHEARON HARRIS	Component: SIG (A) B / C	Leg: HOT / COLD	Date: 9-23-95	
MIZ-18A / MIZ-30 S/N- 297		Procedure: HNP-004 RO	Defect Std. (1) Z 14089	Additional Std. (2) N/A		
Cal	Date	Row Line	Standard Run	Comments	Examiner	
	Time				Init/Level	
<i>051</i>	<i>9-23-95</i> <i>0018</i>	<i>29/21</i>	<i>Begin Cal Group</i>		<i>JA/II</i>	
<i>051</i>	<i>9-23-95</i> <i>02:55</i>	<i>18/28</i>	<i>END CAL GRP</i>		<i>JA/II</i>	
<i>053</i>	<i>9-23-95</i> <i>03:07</i>	<i>20/25</i>	<i>NEW CAL GRP</i>		<i>JA/II</i>	
<i>053</i>	<i>9-23-95</i> <i>03:02</i>	<i>10/26</i>	<i>END CAL GRP</i>	<i>POWER OUT</i>	<i>JA/II</i>	
<i>053</i>	<i>9-23-95</i> <i>05:16</i>	<i>10/26</i>	<i>NEW CAL GRP</i>		<i>JA/II</i>	
<i>055</i>	<i>9-23-95</i> <i>06:11</i>	<i>8/28</i>	<i>END CAL GRP</i>	<i>NO CAL OUT</i>	<i>JA/II</i>	
<i>057</i>	<i>9-23-95</i> <i>06:31</i>	<i>2/29</i>	<i>NEW CAL GRP</i>	<i>NEW MOTOR</i>	<i>JA/II</i>	
<i>057</i>	<i>9-23-95</i> <i>0843</i>	<i>10/36</i>	<i>Probe died - No Cal</i>		<i>JA/IIA</i>	
<i>059</i>	<i>9-23-95</i> <i>0900</i>	<i>13/6</i>	<i>New Cal</i>		<i>JA/IIA</i>	
<i>059</i>	<i>9-23-95</i>	<i>2/2</i>	<i>Probe died No Cal</i>		<i>JA/IIA</i>	
Additional Comments:						
Shift Supervisor Final Review of Acceptance _____						
Reviewed by: <i>David A. Shock</i> Level <i>II</i>						
Approved by: _____ ET Level III						

ABB Combustion Engineering		Multi-Frequency Eddy Current Calibration Data Sheet		Disk #	Side
Owner: CP&L		Site/Unit: SHEARON HARRIS	Component: S/G (A) B/C	Leg: HOT (COLD)	Date: 9-18-95
MIZ-18A / MIZ-30 S/N- 056		Procedure: HNP-004 RO	Defect Std. (1) ASMG Z-8711	Additional Std. (2) Z-8715	
Cal	Date	Row Line	Standard Run	Comments	Examiner
	Time				Init/Level
001	9-18-95 1614	21-45	START CAL		MR II
001	9-18-95 2007	3-46	END CAL		RXB II
002	9-18-95 2012	2-46	START CAL		RXB II
002	9-18-95 2019	2-46	END CAL		RXB II
003	9-18-95 2146	1-46	START CAL		RXB II
003	9-18-95 2323	2-94	END CAL		RXB II
004	9-19-95 0039	10-94	START CAL		RXB II
004	9-19-95 0254	2-109	END CAL		RXB II
005	9-19-95 0404	10-109	START CAL		RXB II
005	9-19-95 0722	34-99	END CAL	PROBE SPIKING	LGCTL
006	9-19-95 910	33-99	START CAL		
Additional Comments:					
Shift Supervisor Final Review of Acceptance					
Reviewed by: <u>David S. Stewart</u>		Level <u>II</u>			
Approved by: _____		ET Level III			

ABB Combustion Engineering		Multi-Frequency Eddy Current Calibration Data Sheet		Disk #	Side
Owner: CP&L		Site/Unit: SHEARON HARRIS	Component: SIG: <u>A</u> / B / C	Log: HOT <u>X</u> COLD	Date: 9-18-95
MIZ-18A MIZ-30 S/N: 056		Procedure: HNP-004 RO	Defect Std. (1) Z-8711	Additional Std. (2) Z-8715	
Cal	Date	Row	Standard Run	Comments	Examiner
	Time	Line			Init/Level
006	9-18-95 1245	1-80	END CAL		MB/II
007	9-18-95 1300	1-79	START CAL		MB/II
007	9-19-95 1645	47-68	END CAL		LRO/II
008	9-19-95 1654	41-69	START CAL		LRO/II
008	9-19-95 2030	41-56	End CAL		R224/II
009	9-19-95 2041	31-41	START CAL		R224/II
009	9-20-95 0023	14-62	END CAL		JCG II
010	9-20-95 0026	3-59	START CAL		JCG II
010	9-20-95 0642	6-58	End CAL	4hr. cal late due to conduit problem	DLP II
011	9-20-95 0700	41-20	START CAL		DLP II
011	9-20 924	36-16	END CAL		DLP II
Additional Comments:					
CAL 010 could not pull cal due to conduit problems, pulled when conduit fixed					
Shift Supervisor Final Review of Acceptance					
Reviewed by: <u>James G. Alcock</u>		Level <u>II</u>			
Approved by: <u>Tom B...</u>		ET Level III			

ABB Combustion Engineering		Multi-Frequency Eddy Current Calibration Data Sheet			Disk #		Side		
Owner: CP&L		Site/Unit: SHEARON HARRIS		Component: S/G: <u>A</u> / B / C		Leg: HOT / <u>COLD</u>		Date: 9-20-95	
<u>MIZ-18A</u> MIZ-30 S/N- 056		Procedure: HNP-004 RO		Defect Std. (1) Z-8711		Additional Std. (2) Z-8715			
Cal	Date	Row	Line	Standard Run		Comments	Examiner		
	Time						Init/Level		
012	9-20-95 1030	35-16		Start Cal.		PROBE DIED NO END CAL	DLP II		
013	9-20-95 1645	35-21		START CAL			MB II		
013	9-20-95 2041	23-6		END Cal.			KBJ II		
014	9-20-95 20:58	11-21		Start Cal.			KBJ II		
014	9-20-95 60:20	22-16		END Cal.			KBJ II		
015	9-21-95 00:30	2-1		Start Cal.			KBJ II		
015	9-21-95 01:57	H		End Cal.			KBJ II		
016	9-21-95 02:13	31-16		Start Cal.		Retest	KBJ II		
016	9-21-95 4:00			END CAL		RETESTS	KBJ II		
017	9-21-95 5:00			START CAL		RETESTS	KBJ II		
017	9-21-95 0900	5-56		END CAL		RETESTS	MB II		
Additional Comments:									
Shift Supervisor Final Review of Acceptance _____									
Reviewed by: <u>Frank A. Shoch</u> Level <u>II</u>									
Approved by: _____ ET Level III									

ABB Combustion Engineering		Multi-Frequency Eddy Current Calibration Data Sheet			Disk #		Side		
Owner: CP&L		Site/Unit: SHEARON HARRIS		Component: S/G: (A) B / C		Leg: HOT / (COLD)		Date: 9-21-95	
MIZ-18A / MIZ-30 STN- 056			Procedure: HNP-004 RO		Defect Std. (1) Z-8711		Additional Std. (2) Z-8715		
Cal	Date	Row Line	Standard Run			Comments	Examiner		
	Time						Init/Level		
018	0816	15/112	START CAL			RETESTS	MB II		
	9-21-95								
018	0930		END CAL				MB II		
	0900								
019	9-21-95		START CAL				MB II		
	1000								
019	9-21-95		END CAL				MB II		
	1210								
020	9-21-95		START CAL			UBENDS	MB II		
	1610								
021	9-21-95	1/59	START CAL				MB II		
	1615								
021	9-21-95	2/62	END CAL				MB II		
	1638								
022	9-21-95	10-79	START CAL			SI	RLB II		
	2030								
022	9-21-95	N/A	END CAL			SI	RLB II		
	2032								
023	9-21-95	10-79	START CAL				RLB II		
	2221								
Additional Comments:									
Shift Supervisor Final Review of Acceptance _____									
Reviewed by: <u>Frank A. Steinhilber</u> Level <u>II</u>									
Approved by: _____ ET Level III									

UTILITY: Carolina Power & Light

Sep. 23, 1995 14:15

PLANT: Shearon Harris

UNIT: 1

SG: B

DATABASE: Harris_SGB_1995

PAGE 1 of 125

* INSPECTION FINAL REPORT LISTING *

*** This report contains all report entries appended to the database for the following test plans ***

All Test Plans in the database are included in summary: 7

Test Plan Name:	Probe Type:	Probe Size:	Type:
1. Top of Tubesheet HL Exam	MRPC	B620MRPC3C	HL
2. CL Bobbin Exam	BOBBIN	A610MULC	CL
3. Row 1&2 Ubend Exam	MRPC	B580MRPCPH	CL
4. 20% of Dented Intersections	MRPC	B620MRPC3C	HL
5. 20% of Dented Intersections	MRPC	B620MRPC3C	CL
6. Previous Indications	BOBBIN	A610MULC	CL
7. Special Interest	MRPC	B620MRPC3C	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: B
 DATABASE: Harris_SGB_1995

Sep. 23, 1995 14:15

PAGE 2 of 125

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
1.	1	1						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00049	HL
2.		5.26	175	DNT	P1	02C	-0.38	11CTEC	P5436	rsec	A610MULC	SG20CCAL00014	CL
3.	1	2						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00049	HL
4.								11CTEC	T7072	rpri	A610MULC	SG20CCAL00014	CL
5.	1	3						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00049	HL
6.								11CTEC	T7072	rpri	A610MULC	SG20CCAL00014	CL
7.								02C02C	05305	rpri	B620MRPC3C	SG20CCAL00023	CL
8.	1	4						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00049	HL
9.								11CTEC	T7072	rpri	A610MULC	SG20CCAL00014	CL
10.	1	5						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00049	HL
11.								11CTEC	T7072	rpri	A610MULC	SG20CCAL00014	CL
12.	1	6						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00049	HL
13.								11CTEC	T7072	rpri	A610MULC	SG20CCAL00014	CL
14.	1	7						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00049	HL
15.								11CTEC	T7072	rpri	A610MULC	SG20CCAL00014	CL
16.	1	8						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00049	HL
17.								11CTEC	T7072	rpri	A610MULC	SG20CCAL00014	CL
18.	1	9						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00049	HL
19.								11CTEC	T7072	rpri	A610MULC	SG20CCAL00014	CL
20.	1	10						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00049	HL
21.								11CTEC	T7072	rpri	A610MULC	SG20CCAL00014	CL
22.	1	11						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00049	HL
23.								11CTEC	T7072	rpri	A610MULC	SG20CCAL00014	CL
24.	1	12						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00049	HL
25.								11CTEC	T7072	rpri	A610MULC	SG20CCAL00014	CL
26.					RBD				D3858	reso	B580MRPCPH	SG20CCAL00019	CL
27.								11H11C	T9924	rpri	B580MRPCPH	SG20CCAL00027	CL
28.	1	13						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00049	HL
29.								11CTEC	T7072	rpri	A610MULC	SG20CCAL00014	CL
30.	1	14						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00049	HL
31.								11CTEC	T7072	rpri	A610MULC	SG20CCAL00014	CL
32.	1	15						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00049	HL
33.								11CTEC	T7072	rpri	A610MULC	SG20CCAL00014	CL
34.	1	16						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00049	HL
35.								11CTEC	T7072	rpri	A610MULC	SG20CCAL00014	CL
36.	1	17						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00049	HL
37.								11CTEC	T7072	rpri	A610MULC	SG20CCAL00014	CL
38.					RBD				D3858	reso	B580MRPCPH	SG20CCAL00019	CL
39.								11H11C	T9924	rpri	B580MRPCPH	SG20CCAL00027	CL
40.	1	18						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00049	HL
41.								11CTEC	T7072	rpri	A610MULC	SG20CCAL00014	CL
42.	1	19						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00049	HL
43.								11CTEC	T7072	rpri	A610MULC	SG20CCAL00014	CL
44.	1	20						TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL
45.								11CTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL
46.	1	21						TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL
47.								11CTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL
48.	1	22						TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL
49.								11CTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: B
 DATABASE: Harris_SGB_1995

Sep. 23.1995 14:15

PAGE 3 of 125

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
50.	1	23					TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL
51.							11CTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL
52.	1	24					TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL
53.							11CTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL
54.	1	25					TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL
55.							11CTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL
56.	1	26					TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL
57.							11CTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL
58.	1	27					TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL
59.							11CTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL
60.					RBD			03858	reso	B580MRPCPH	SG20CCAL00019	CL
61.							11H11C	T9924	rpri	B580MRPCPH	SG20CCAL00026	CL
62.	1	28					TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL
63.							11CTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL
64.	1	29					TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL
65.							11CTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL
66.	1	30					TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL
67.							11CTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL
68.	1	31					TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL
69.							11CTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL
70.	1	32					TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL
71.							11CTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL
72.							11H11C	04825	reso	B580MRPCPH	SG20CCAL00019	CL
73.	1	33					TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL
74.							11CTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL
75.	1	34					TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL
76.							11CTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL
77.	1	35					TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL
78.							11CTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL
79.	1	36					TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL
80.							11CTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL
81.	1	37					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00008	HL
82.							11CTEC	user5	rpri	A610MULC	SG20CCAL00001	CL
83.	1	38					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00008	HL
84.							11CTEC	user5	rpri	A610MULC	SG20CCAL00001	CL
85.	1	39					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00008	HL
86.							11CTEC	user5	rpri	A610MULC	SG20CCAL00001	CL
87.							11H11C	05305	rpri	B580MRPCPH	SG20CCAL00019	CL
88.	1	40					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00008	HL
89.							11CTEC	user5	rpri	A610MULC	SG20CCAL00001	CL
90.	1	41					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00008	HL
91.							11CTEC	user5	rpri	A610MULC	SG20CCAL00001	CL
92.	1	42					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00008	HL
93.							11CTEC	user5	rpri	A610MULC	SG20CCAL00001	CL
94.							11H11C	04825	reso	B580MRPCPH	SG20CCAL00019	CL
95.	1	43					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00008	HL
96.							11CTEC	user5	rpri	A610MULC	SG20CCAL00001	CL
97.	1	44					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00008	HL
98.							11CTEC	user5	rpri	A610MULC	SG20CCAL00001	CL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: B
 DATABASE: Harris_SGB_1995

Sep. 23.1995 14:15

PAGE 4 of 125

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
99.					RBD				D3858	reso	B580MRPCPH	SG20CCAL00019	CL
100.								11H11C	T9924	rpri	B580MRPCPH	SG20CCAL00026	CL
101.	1	45						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00010	HL
102.								11CTEC	user5	rpri	A610MULC	SG20CCAL00001	CL
103.	1	46						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00010	HL
104.								11CTEC	user5	rpri	A610MULC	SG20CCAL00001	CL
105.	1	47						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00010	HL
106.								11CTEC	user5	rpri	A610MULC	SG20CCAL00001	CL
107.								11H11C	D4825	reso	B580MRPCPH	SG20CCAL00019	CL
108.	1	48						TSHTSH	C1115	rsec	B620MRPC3C	SG21HCAL00010	HL
109.								11CTEC	user5	rpri	A610MULC	SG20CCAL00001	CL
110.	1	49						TSHTSH	C1115	rsec	B620MRPC3C	SG21HCAL00010	HL
111.								11CTEC	user5	rpri	A610MULC	SG20CCAL00001	CL
112.	1	50						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00010	HL
113.								11CTEC	user5	rpri	A610MULC	SG20CCAL00001	CL
114.								11H11C	05305	rpri	B580MRPCPH	SG20CCAL00019	CL
115.	1	51						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00010	HL
116.								11CTEC	n0698	rpri	A610MULC	SG20CCAL00001	CL
117.	1	52						TSHTSH	C1115	rsec	B620MRPC3C	SG21HCAL00010	HL
118.								11CTEC	n0698	rpri	A610MULC	SG20CCAL00001	CL
119.	1	53						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00010	HL
120.								11CTEC	n0698	rpri	A610MULC	SG20CCAL00001	CL
121.								11H11C	05305	rpri	B580MRPCPH	SG20CCAL00019	CL
122.	1	54						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00010	HL
123.								11CTEC	n0698	rpri	A610MULC	SG20CCAL00001	CL
124.	1	55						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00010	HL
125.								11CTEC	n0698	rpri	A610MULC	SG20CCAL00001	CL
126.	1	56						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00010	HL
127.								11CTEC	n0698	rpri	A610MULC	SG20CCAL00001	CL
128.								11H11C	05305	rpri	B580MRPCPH	SG20CCAL00019	CL
129.	1	57						TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
130.								11CTEC	T7072	rpri	A610MULC	SG20CCAL00011	CL
131.	1	58						TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
132.								11CTEC	T7072	rpri	A610MULC	SG20CCAL00011	CL
133.	1	59						TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
134.								11CTEC	T7072	rpri	A610MULC	SG20CCAL00011	CL
135.								11H11C	05305	rpri	B580MRPCPH	SG20CCAL00021	CL
136.	1	60						TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
137.								11CTEC	T7072	rpri	A610MULC	SG20CCAL00011	CL
138.	1	61						TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
139.								11CTEC	T7072	rpri	A610MULC	SG20CCAL00011	CL
140.	1	62						TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
141.								11CTEC	T7072	rpri	A610MULC	SG20CCAL00011	CL
142.	1	63						TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
143.								11CTEC	T7072	rpri	A610MULC	SG20CCAL00011	CL
144.	1	64						TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
145.								11CTEC	T7072	rpri	A610MULC	SG20CCAL00011	CL
146.								11H11C	D4825	reso	B580MRPCPH	SG20CCAL00021	CL
147.	1	65						TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: B
 DATABASE: Harris_SGB_1995

Sep. 23.1995 14:15

PAGE 5 of 125

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
148.							11CTEC	T7072	rpri	A610MULC	SG20CCAL00011	CL
149.	1	66					TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
150.							11CTEC	T7072	rpri	A610MULC	SG20CCAL00011	CL
151.	1	67					TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
152.							11CTEC	T7072	rpri	A610MULC	SG20CCAL00011	CL
153.	1	68					TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
154.							11CTEC	T7072	rpri	A610MULC	SG20CCAL00011	CL
155.							11H11C	05305	rpri	B580MRPCPH	SG20CCAL00021	CL
156.	1	69					TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
157.							11CTEC	T7072	rpri	A610MULC	SG20CCAL00011	CL
158.	1	70					TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
159.							11CTEC	T7072	rpri	A610MULC	SG20CCAL00011	CL
160.							11H11C	05305	rpri	B580MRPCPH	SG20CCAL00021	CL
161.	1	71					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
162.							11CTEC	T7072	rpri	A610MULC	SG20CCAL00011	CL
163.	1	72					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
164.							11CTEC	T7072	rpri	A610MULC	SG20CCAL00011	CL
165.	1	73					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
166.							11CTEC	T7072	rpri	A610MULC	SG20CCAL00011	CL
167.	1	74					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
168.							11CTEC	T7072	rpri	A610MULC	SG20CCAL00011	CL
169.	1	75					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
170.							11CTEC	T7072	rpri	A610MULC	SG20CCAL00011	CL
171.							11H11C	05305	rpri	B580MRPCPH	SG20CCAL00021	CL
172.	1	76					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
173.							11CTEC	T7072	rpri	A610MULC	SG20CCAL00011	CL
174.	1	77					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00022	HL
175.							11CTEC	F9284	rpri	A610MULC	SG20CCAL00005	CL
176.							11H11C	D3858	reso	B580MRPCPH	SG20CCAL00019	CL
177.	1	78					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00022	HL
178.							11CTEC	T7072	rpri	A610MULC	SG20CCAL00016	CL
179.	1	79					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00022	HL
180.							11CTEC	F9284	rpri	A610MULC	SG20CCAL00005	CL
181.	1	80					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00022	HL
182.							11CTEC	F9284	rpri	A610MULC	SG20CCAL00005	CL
183.	1	81					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00022	HL
184.							11CTEC	F9284	rpri	A610MULC	SG20CCAL00005	CL
185.	1	82					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00022	HL
186.							11CTEC	F9284	rpri	A610MULC	SG20CCAL00005	CL
187.	1	83					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00022	HL
188.							11CTEC	F9284	rpri	A610MULC	SG20CCAL00005	CL
189.	1	84					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00022	HL
190.							11CTEC	F9284	rpri	A610MULC	SG20CCAL00005	CL
191.							11H11C	D3858	reso	B580MRPCPH	SG20CCAL00019	CL
192.	1	85					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00022	HL
193.							11CTEC	F9284	rpri	A610MULC	SG20CCAL00005	CL
194.	1	86					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00022	HL
195.							11CTEC	F9284	rpri	A610MULC	SG20CCAL00005	CL
196.							11H11C	05305	rpri	B580MRPCPH	SG20CCAL00019	CL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: B
 DATABASE: Harris_SGB_1995

Sep. 23,1995 14:15

PAGE 6 of 125

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
197.	1	87					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00022	HL
198.							11CTEC	F9284	rpri	A610MULC	SG20CCAL00005	CL
199.	1	88					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00022	HL
200.							11CTEC	F9284	rpri	A610MULC	SG20CCAL00005	CL
201.							11H11C	05305	rpri	B580MRPCPH	SG20CCAL00019	CL
202.	1	89					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00022	HL
203.							11CTEC	F9284	rpri	A610MULC	SG20CCAL00005	CL
204.	1	90					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00022	HL
205.							11CTEC	F9284	rpri	A610MULC	SG20CCAL00005	CL
206.	1	91					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00022	HL
207.							11CTEC	F9284	rpri	A610MULC	SG20CCAL00005	CL
208.	1	92					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00022	HL
209.							11CTEC	F9284	rpri	A610MULC	SG20CCAL00005	CL
210.	1	93					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00022	HL
211.							11CTEC	F9284	rpri	A610MULC	SG20CCAL00005	CL
212.	1	94					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00010	HL
213.							11CTEC	B5534	rpri	A610MULC	SG20CCAL00002	CL
214.	1	95					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00010	HL
215.							11CTEC	B5534	rpri	A610MULC	SG20CCAL00002	CL
216.	1	96					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00010	HL
217.							11CTEC	B5534	rpri	A610MULC	SG20CCAL00002	CL
218.	1	97					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00010	HL
219.							11CTEC	B5534	rpri	A610MULC	SG20CCAL00002	CL
220.	1	98					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00010	HL
221.							11CTEC	B5534	rpri	A610MULC	SG20CCAL00002	CL
222.	1	99					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00010	HL
223.							11CTEC	B5534	rpri	A610MULC	SG20CCAL00002	CL
224.	1	100					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00010	HL
225.							11CTEC	B5534	rpri	A610MULC	SG20CCAL00002	CL
226.	1	101					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00010	HL
227.							11CTEC	B5534	rpri	A610MULC	SG20CCAL00002	CL
228.	1	102					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00010	HL
229.							11CTEC	B5534	rpri	A610MULC	SG20CCAL00002	CL
230.							11H11C	05305	rpri	B580MRPCPH	SG20CCAL00019	CL
231.	1	103					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00010	HL
232.							11CTEC	B5534	rpri	A610MULC	SG20CCAL00002	CL
233.	1	104					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00010	HL
234.							11CTEC	B5534	rpri	A610MULC	SG20CCAL00002	CL
235.							11H11C	05305	rpri	B580MRPCPH	SG20CCAL00019	CL
236.	1	105					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00010	HL
237.							11CTEC	B5534	rpri	A610MULC	SG20CCAL00002	CL
238.	1	106					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00010	HL
239.							11CTEC	B5534	rpri	A610MULC	SG20CCAL00002	CL
240.	1	107					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00010	HL
241.							11CTEC	B5534	rpri	A610MULC	SG20CCAL00002	CL
242.	1	108					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00010	HL
243.							11CTEC	B5534	rpri	A610MULC	SG20CCAL00002	CL
244.	1	109					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00010	HL
245.							11CTEC	B5534	rpri	A610MULC	SG20CCAL00002	CL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: B
 DATABASE: Harris_SGB_1995

Sep. 23.1995 14:15

PAGE 7 of 125

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
246.	1	110					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00010	HL
247.							11CTEC	B5534	rpri	A610MULC	SG20CCAL00002	CL
248.	1	111					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00010	HL
249.							11CTEC	B5534	rpri	A610MULC	SG20CCAL00002	CL
250.	1	112					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00010	HL
251.							11CTEC	B5534	rpri	A610MULC	SG20CCAL00002	CL
252.	1	113					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00010	HL
253.							11CTEC	B5534	rpri	A610MULC	SG20CCAL00002	CL
254.	1	114					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00010	HL
255.							11CTEC	B5534	rpri	A610MULC	SG20CCAL00002	CL
256.	2	1					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00047	HL
257.							11CTEC	T7072	rpri	A610MULC	SG20CCAL00014	CL
258.							02C02C	05305	rpri	B620MRPC3C	SG20CCAL00023	CL
259.	2	2					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL
260.							11CTEC	T7072	rpri	A610MULC	SG20CCAL00014	CL
261.	2	3					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00047	HL
262.							11CTEC	T7072	rpri	A610MULC	SG20CCAL00014	CL
263.	2	4					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL
264.							11CTEC	T7072	rpri	A610MULC	SG20CCAL00014	CL
265.	2	5					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00047	HL
266.							11CTEC	T7072	rpri	A610MULC	SG20CCAL00014	CL
267.	2	6					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL
268.							11CTEC	T7072	rpri	A610MULC	SG20CCAL00014	CL
269.	2	7					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00047	HL
270.							11CTEC	T7072	rpri	A610MULC	SG20CCAL00014	CL
271.	2	8					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL
272.							11CTEC	T7072	rpri	A610MULC	SG20CCAL00014	CL
273.	2	9					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00047	HL
274.							11CTEC	T7072	rpri	A610MULC	SG20CCAL00014	CL
275.	2	10					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL
276.							11CTEC	T7072	rpri	A610MULC	SG20CCAL00014	CL
277.					RBD			D3858	reso	B580MRPCPH	SG20CCAL00019	CL
278.							11H11C	T9924	rpri	B580MRPCPH	SG20CCAL00027	CL
279.	2	11					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00047	HL
280.							11CTEC	T7072	rpri	A610MULC	SG20CCAL00014	CL
281.	2	12					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL
282.							11CTEC	T7072	rpri	A610MULC	SG20CCAL00014	CL
283.	2	13					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00049	HL
284.							11CTEC	T7072	rpri	A610MULC	SG20CCAL00014	CL
285.	2	14					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00048	HL
286.							11CTEC	T7072	rpri	A610MULC	SG20CCAL00014	CL
287.					RBD			D3858	reso	B580MRPCPH	SG20CCAL00019	CL
288.							11H11C	T9924	rpri	B580MRPCPH	SG20CCAL00026	CL
289.	2	15					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00049	HL
290.							11CTEC	T7072	rpri	A610MULC	SG20CCAL00014	CL
291.	2	16					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00048	HL
292.							11CTEC	T7072	rpri	A610MULC	SG20CCAL00014	CL
293.					RBD			D3858	reso	B580MRPCPH	SG20CCAL00019	CL
294.							11H11C	T9924	rpri	B580MRPCPH	SG20CCAL00026	CL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: B
 DATABASE: Harris_SGB_1995

Sep. 23.1995 14:15

PAGE 8 of 125

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
295.	2	17						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00049	HL
296.								11CTEC	T7072	rpri	A610MULC	SG20CCAL00014	CL
297.	2	18						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00049	HL
298.								11CTEC	T7072	rpri	A610MULC	SG20CCAL00014	CL
299.					RBD				D3858	reso	B580MRPCPH	SG20CCAL00019	CL
300.								11H11C	T9924	rpri	B580MRPCPH	SG20CCAL00026	CL
301.	2	19						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00049	HL
302.								11CTEC	T7072	rpri	A610MULC	SG20CCAL00014	CL
303.	2	20						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
304.								11CTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL
305.	2	21						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
306.								11CTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL
307.	2	22						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
308.								11CTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL
309.	2	23						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
310.								11CTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL
311.					RBD				D3858	reso	B580MRPCPH	SG20CCAL00019	CL
312.								11H11C	T9924	rpri	B580MRPCPH	SG20CCAL00026	CL
313.	2	24						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
314.								11CTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL
315.	2	25						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
316.								11CTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL
317.	2	26						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
318.								11CTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL
319.	2	27						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
320.								11CTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL
321.	2	28						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
322.								11CTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL
323.	2	29						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
324.								11CTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL
325.	2	30						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
326.								11CTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL
327.								11H11C	05305	rpri	B580MRPCPH	SG20CCAL00019	CL
328.	2	31						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
329.								11CTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL
330.	2	32						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
331.								11CTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL
332.	2	33						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
333.								11CTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL
334.	2	34						TSHTSH	F3325	rsec	B620MRPC3C	SG21HCAL00044	HL
335.								11CTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL
336.	2	35						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
337.								11CTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL
338.					RBD				D3858	reso	B580MRPCPH	SG20CCAL00019	CL
339.								11H11C	T9924	rpri	B580MRPCPH	SG20CCAL00026	CL
340.	2	36						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
341.								11CTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL
342.	2	37						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00007	HL
343.								11CTEC	user5	rpri	A610MULC	SG20CCAL00001	CL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: B
 DATABASE: Harris_SGB_1995

Sep. 23.1995 14:15

PAGE 9 of 125

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
344.							11H11C	04825	reso	B580MRPCPH	SG20CCAL00019	CL
345.	2	38					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00007	HL
346.							11CTEC	user5	rpri	A610MULC	SG20CCAL00001	CL
347.	2	39					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00007	HL
348.							11CTEC	user5	rpri	A610MULC	SG20CCAL00001	CL
349.	2	40					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00007	HL
350.							11CTEC	user5	rpri	A610MULC	SG20CCAL00001	CL
351.	2	41					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00007	HL
352.							11CTEC	user5	rpri	A610MULC	SG20CCAL00001	CL
353.	2	42					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00007	HL
354.							11CTEC	user5	rpri	A610MULC	SG20CCAL00001	CL
355.	2	43					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00007	HL
356.							11CTEC	user5	rpri	A610MULC	SG20CCAL00001	CL
357.	2	44					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00007	HL
358.							11CTEC	user5	rpri	A610MULC	SG20CCAL00001	CL
359.	2	45					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00009	HL
360.							11CTEC	user5	rpri	A610MULC	SG20CCAL00001	CL
361.	2	46					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00009	HL
362.							11CTEC	user5	rpri	A610MULC	SG20CCAL00001	CL
363.							11H11C	05305	rpri	B580MRPCPH	SG20CCAL00019	CL
64.	2	47					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00009	HL
65.							11CTEC	user5	rpri	A610MULC	SG20CCAL00001	CL
66.	2	48					TSHTSH	J1978	rsec	B620MRPC3C	SG21HCAL00009	HL
367.							TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00009	HL
368.							11CTEC	user5	rpri	A610MULC	SG20CCAL00001	CL
369.	2	49					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00020	HL
370.							11CTEC	user5	rpri	A610MULC	SG20CCAL00001	CL
371.							11H11C	05305	rpri	B580MRPCPH	SG20CCAL00019	CL
372.	2	50					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00009	HL
373.							11CTEC	user5	rpri	A610MULC	SG20CCAL00001	CL
374.	2	51					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00009	HL
375.							11CTEC	n0698	rpri	A610MULC	SG20CCAL00001	CL
376.	2	52					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00009	HL
377.							11CTEC	P5436	rsec	A610MULC	SG20CCAL00001	CL
378.	2	53					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00009	HL
379.							11CTEC	n0698	rpri	A610MULC	SG20CCAL00001	CL
380.	2	54					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00009	HL
381.							11CTEC	n0698	rpri	A610MULC	SG20CCAL00001	CL
382.	2	55					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00009	HL
383.							11CTEC	P5436	rsec	A610MULC	SG20CCAL00001	CL
384.							11H11C	05305	rpri	B580MRPCPH	SG20CCAL00019	CL
385.	2	56					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00009	HL
386.							11CTEC	P5436	rsec	A610MULC	SG20CCAL00001	CL
387.	2	57					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL
388.							11CTEC	T7072	rpri	A610MULC	SG20CCAL00011	CL
389.	2	58					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL
390.							11CTEC	T7072	rpri	A610MULC	SG20CCAL00011	CL
391.	2	59					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL
392.							11CTEC	T7072	rpri	A610MULC	SG20CCAL00011	CL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: B
 DATABASE: Harris_SGB_1995

Sep. 23.1995 14:15

PAGE 10 of 125

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
393.	2	60						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL
394.								11CTEC	T7072	rpri	A610MULC	SG20CCAL00011	CL
395.	2	61						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL
396.								11CTEC	T7072	rpri	A610MULC	SG20CCAL00011	CL
397.	2	62						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL
398.								11CTEC	T7072	rpri	A610MULC	SG20CCAL00011	CL
399.								11H11C	05305	rpri	B580MRPCPH	SG20CCAL00021	CL
400.	2	63						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL
401.								11CTEC	T7072	rpri	A610MULC	SG20CCAL00011	CL
402.	2	64						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL
403.								11CTEC	T7072	rpri	A610MULC	SG20CCAL00011	CL
404.	2	65						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL
405.								11CTEC	T7072	rpri	A610MULC	SG20CCAL00011	CL
406.	2	66						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL
407.								11CTEC	T7072	rpri	A610MULC	SG20CCAL00011	CL
408.								11H11C	05305	rpri	B580MRPCPH	SG20CCAL00021	CL
409.	2	67						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL
410.								11CTEC	T7072	rpri	A610MULC	SG20CCAL00011	CL
411.	2	68						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL
412.								11CTEC	T7072	rpri	A610MULC	SG20CCAL00011	CL
413.	2	69						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL
414.								11CTEC	T7072	rpri	A610MULC	SG20CCAL00011	CL
415.	2	70						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL
416.								11CTEC	T7072	rpri	A610MULC	SG20CCAL00011	CL
417.	2	71						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00040	HL
418.								11CTEC	T7072	rpri	A610MULC	SG20CCAL00011	CL
419.								11H11C	05305	rpri	B580MRPCPH	SG20CCAL00019	CL
420.	2	72						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00040	HL
421.								11CTEC	T7072	rpri	A610MULC	SG20CCAL00011	CL
422.	2	73						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00040	HL
423.								11CTEC	T7072	rpri	A610MULC	SG20CCAL00011	CL
424.	2	74						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00040	HL
425.								11CTEC	T7072	rpri	A610MULC	SG20CCAL00011	CL
426.	2	75						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00040	HL
427.								11CTEC	T7072	rpri	A610MULC	SG20CCAL00011	CL
428.	2	76						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00040	HL
429.								11CTEC	T7072	rpri	A610MULC	SG20CCAL00011	CL
430.	2	77						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00021	HL
431.								11CTEC	F9284	rpri	A610MULC	SG20CCAL00005	CL
432.	2	78						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00021	HL
433.								11CTEC	F9284	rpri	A610MULC	SG20CCAL00005	CL
434.	2	79						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00021	HL
435.								11CTEC	F9284	rpri	A610MULC	SG20CCAL00005	CL
436.	2	80						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00021	HL
437.								11CTEC	F9284	rpri	A610MULC	SG20CCAL00005	CL
438.								11H11C	05305	rpri	B580MRPCPH	SG20CCAL00019	CL
439.	2	81						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00021	HL
440.								11CTEC	F9284	rpri	A610MULC	SG20CCAL00005	CL
441.								11H11C	05305	rpri	B580MRPCPH	SG20CCAL00019	CL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: B
 DATABASE: Harris_SGB_1995

Sep. 23.1995 14:15

PAGE 11 of 125

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
442.	2	82					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00021	HL
443.							11CTEC	F9284	rpri	A610MULC	SG20CCAL00005	CL
444.	2	83					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00021	HL
445.							11CTEC	F9284	rpri	A610MULC	SG20CCAL00005	CL
446.							11H11C	05305	rpri	B580MRPCPH	SG20CCAL00019	CL
447.	2	84					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00021	HL
448.							11CTEC	F9284	rpri	A610MULC	SG20CCAL00005	CL
449.	2	85					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00021	HL
450.							11CTEC	F9284	rpri	A610MULC	SG20CCAL00005	CL
451.	2	86					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00021	HL
452.							11CTEC	F9284	rpri	A610MULC	SG20CCAL00005	CL
453.	2	87					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00021	HL
454.							11CTEC	F9284	rpri	A610MULC	SG20CCAL00005	CL
455.							11H11C	05305	rpri	B580MRPCPH	SG20CCAL00019	CL
456.	2	88					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00021	HL
457.							11CTEC	F9284	rpri	A610MULC	SG20CCAL00005	CL
458.	2	89					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00021	HL
459.							11CTEC	F9284	rpri	A610MULC	SG20CCAL00005	CL
460.							11H11C	05305	rpri	B580MRPCPH	SG20CCAL00019	CL
461.	2	90					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00021	HL
462.							11CTEC	F9284	rpri	A610MULC	SG20CCAL00005	CL
463.	2	91					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00021	HL
464.							11CTEC	F9284	rpri	A610MULC	SG20CCAL00005	CL
465.	2	92					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00021	HL
466.							11CTEC	F9284	rpri	A610MULC	SG20CCAL00005	CL
467.							11H11C	05305	rpri	B580MRPCPH	SG20CCAL00019	CL
468.	2	93					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00021	HL
469.							11CTEC	F9284	rpri	A610MULC	SG20CCAL00005	CL
470.	2	94					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00011	HL
471.							11CTEC	B5534	rpri	A610MULC	SG20CCAL00002	CL
472.							11H11C	05305	rpri	B580MRPCPH	SG20CCAL00019	CL
473.	2	95					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00012	HL
474.							11CTEC	B5534	rpri	A610MULC	SG20CCAL00002	CL
475.	2	96					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00011	HL
476.							11CTEC	B5534	rpri	A610MULC	SG20CCAL00002	CL
477.							11H11C	05305	rpri	B580MRPCPH	SG20CCAL00019	CL
478.	2	97					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00012	HL
479.							11CTEC	B5534	rpri	A610MULC	SG20CCAL00002	CL
480.	2	98					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00011	HL
481.							11CTEC	B5534	rpri	A610MULC	SG20CCAL00002	CL
482.							11H11C	05305	rpri	B580MRPCPH	SG20CCAL00019	CL
483.	2	99					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00012	HL
484.							11CTEC	B5534	rpri	A610MULC	SG20CCAL00002	CL
485.	2	100					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00011	HL
486.							11CTEC	B5534	rpri	A610MULC	SG20CCAL00002	CL
487.							11H11C	05305	rpri	B580MRPCPH	SG20CCAL00019	CL
488.	2	101					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00012	HL
489.							11CTEC	B5534	rpri	A610MULC	SG20CCAL00002	CL
490.	2	102					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00011	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: B
 DATABASE: Harris_SGB_1995

Sep. 23.1995 14:15

PAGE 12 of 125

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
491.							11CTEC	85534	rpri	A610MULC	SG20CCAL00002	CL
492.	2	103					TSHTSH	7665	rpri	B620MRPC3C	SG21HCAL00012	HL
493.							11CTEC	85534	rpri	A610MULC	SG20CCAL00002	CL
494.	2	104					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00011	HL
495.							11CTEC	85534	rpri	A610MULC	SG20CCAL00002	CL
496.	2	105					TSHTSH	7665	rpri	B620MRPC3C	SG21HCAL00012	HL
497.							11CTEC	85534	rpri	A610MULC	SG20CCAL00002	CL
498.	2	106					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00011	HL
499.							11CTEC	85534	rpri	A610MULC	SG20CCAL00002	CL
500.	2	107					TSHTSH	7665	rpri	B620MRPC3C	SG21HCAL00012	HL
501.							11CTEC	85534	rpri	A610MULC	SG20CCAL00002	CL
502.	2	108					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00011	HL
503.							11CTEC	85534	rpri	A610MULC	SG20CCAL00002	CL
504.	2	109					TSHTSH	7665	rpri	B620MRPC3C	SG21HCAL00012	HL
505.							11CTEC	85534	rpri	A610MULC	SG20CCAL00002	CL
506.	2	110					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00011	HL
507.							11CTEC	85534	rpri	A610MULC	SG20CCAL00002	CL
508.	2	111					TSHTSH	7665	rpri	B620MRPC3C	SG21HCAL00012	HL
509.							11CTEC	85534	rpri	A610MULC	SG20CCAL00002	CL
510.	2	112					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00011	HL
511.							11CTEC	85534	rpri	A610MULC	SG20CCAL00002	CL
512.	2	113					TSHTSH	7665	rpri	B620MRPC3C	SG21HCAL00012	HL
513.							11CTEC	85534	rpri	A610MULC	SG20CCAL00002	CL
514.	2	114					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00013	HL
515.							11CTEC	T7072	rpri	A610MULC	SG20CCAL00017	CL
516.	3	1					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00047	HL
517.							TEHTEC	T7072	rpri	A610MULC	SG20CCAL00014	CL
518.	3	2					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL
519.	3	3					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00047	HL
520.	3	4					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL
521.	3	5					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00047	HL
522.	3	6					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL
523.							TEHTEC	T7072	rpri	A610MULC	SG20CCAL00014	CL
524.	3	7					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00047	HL
525.	3	8					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL
526.	3	9					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00047	HL
527.	3	10					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL
528.	3	11					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00047	HL
529.							TEHTEC	T7072	rpri	A610MULC	SG20CCAL00014	CL
530.	3	12					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL
531.	3	13					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00049	HL
532.	3	14					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00048	HL
533.	3	15					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00049	HL
534.	3	16					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00048	HL
535.							TEHTEC	T7072	rpri	A610MULC	SG20CCAL00014	CL
536.	3	17					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00049	HL
537.	3	18					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00049	HL
538.	3	19					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00049	HL
539.	3	20					TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: B
 DATABASE: Harris_SGB_1995

Sep. 23.1995 14:15

PAGE 13 of 125

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
540.	3	21						TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL
541.				RES				11CTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL
542.								TEHTEC	T7072	rpri	A590MULC	SG20CCAL00018	CL
543.	3	22						TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL
544.	3	23						TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL
545.	3	24						TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL
546.	3	25						TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL
547.	3	26						TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL
548.				RES				11CTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL
549.								TEHTEC	T7072	rpri	A590MULC	SG20CCAL00018	CL
550.	3	27						TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL
551.	3	28						TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL
552.	3	29						TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL
553.	3	30						TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL
554.	3	31						TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL
555.				RES				11CTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL
556.								TEHTEC	T7072	rpri	A590MULC	SG20CCAL00018	CL
557.	3	32						TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL
558.	3	33						TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL
559.	3	34						TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL
60.	3	35						TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL
61.	3	36						TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL
62.				RES				11CTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL
63.								TEHTEC	T7072	rpri	A590MULC	SG20CCAL00018	CL
564.	3	37						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00008	HL
565.	3	38						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00008	HL
566.	3	39						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00008	HL
567.	3	40						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00020	HL
568.	3	41						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00008	HL
569.								TEHTEC	user5	rpri	A610MULC	SG20CCAL00001	CL
570.	3	42						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00008	HL
571.	3	43						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00008	HL
572.	3	44						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00008	HL
573.	3	45						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00010	HL
574.	3	46						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00010	HL
575.								TEHTEC	user5	rpri	A610MULC	SG20CCAL00001	CL
576.	3	47						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00010	HL
577.	3	48						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00010	HL
578.	3	49						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00010	HL
579.	3	50						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00010	HL
580.	3	51						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00010	HL
581.								TEHTEC	n0698	rpri	A610MULC	SG20CCAL00001	CL
582.	3	52						TSHTSH	C1115	rsec	B620MRPC3C	SG21HCAL00010	HL
583.	3	53						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00010	HL
584.	3	54						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00010	HL
585.	3	55						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00010	HL
586.	3	56						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00010	HL
587.								TEHTEC	n0698	rpri	A610MULC	SG20CCAL00001	CL
588.	3	57						TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL

*** INSPECTION FINAL REPORT LISTING ***

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: B
 DATABASE: Harris_SGB_1995

Sep. 23.1995 14:15

PAGE 14 of 125

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
589.	3	58						TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
590.	3	59						TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
591.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00011	CL
592.	3	60						TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
593.	3	61						TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
594.	3	62						TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
595.	3	63						TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
596.	3	64						TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
597.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00011	CL
598.	3	65						TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
599.	3	66						TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
600.	3	67						TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
601.	3	68						TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
602.	3	69						TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
603.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00011	CL
604.	3	70						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
605.	3	71						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
606.	3	72						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
607.	3	73						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
608.	3	74						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
09.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00011	CL
1.	3	75						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
11.	3	76						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
612.	3	77						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00022	HL
613.	3	78						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00022	HL
614.	3	79						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00022	HL
615.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00005	CL
616.	3	80						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00022	HL
617.	3	81						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00022	HL
618.	3	82						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00022	HL
619.	3	83						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00022	HL
620.	3	84						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00022	HL
621.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00005	CL
622.	3	85						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00022	HL
623.	3	86						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00022	HL
624.	3	87						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00022	HL
625.	3	88						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00022	HL
626.	3	89						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00022	HL
627.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00005	CL
628.	3	90						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00022	HL
629.	3	91						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00022	HL
630.	3	92						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00022	HL
631.	3	93						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00022	HL
632.	3	94						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00011	HL
633.								TEHTEC	B5534	rpri	A610MULC	SG20CCAL00002	CL
634.	3	95						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00012	HL
635.	3	96						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00011	HL
636.	3	97						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00012	HL
637.	3	98						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00011	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: B
 DATABASE: Harris_SGB_1995

Sep. 23.1995 14:15

PAGE 15 of 125

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
638.	3	99					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00012	HL
639.							TEHTEC	B5534	rpri	A610MULC	SG20CCAL00002	CL
640.	3	100					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00011	HL
641.	3	101					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00012	HL
642.	3	102					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00011	HL
643.	3	103					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00012	HL
644.	3	104					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00011	HL
645.							TEHTEC	B5534	rpri	A610MULC	SG20CCAL00002	CL
646.	3	105					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00012	HL
647.	3	106					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00011	HL
648.	3	107					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00012	HL
649.	3	108					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00011	HL
650.	3	109					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00012	HL
651.							TEHTEC	B5534	rpri	A610MULC	SG20CCAL00002	CL
652.	3	110					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00011	HL
653.	3	111					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00012	HL
654.	3	112					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00011	HL
655.	3	113					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00012	HL
656.	3	114					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00013	HL
657.							TEHTEC	T7072	rpri	A610MULC	SG20CCAL00017	CL
58.	4	1					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00047	HL
59.							TEHTEC	T7072	rpri	A610MULC	SG20CCAL00014	CL
60.	4	2					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL
61.	4	3					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00047	HL
661.	4	3					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00047	HL
662.	4	4					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL
663.	4	5					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00047	HL
664.	4	6					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL
665.							TEHTEC	T7072	rpri	A610MULC	SG20CCAL00014	CL
666.	4	7					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00047	HL
667.	4	8					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL
668.	4	9					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00047	HL
669.	4	10					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL
670.	4	11					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00047	HL
671.							TEHTEC	T7072	rpri	A610MULC	SG20CCAL00014	CL
672.	4	12					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL
673.	4	13					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00049	HL
674.	4	14					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00048	HL
675.	4	15					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00049	HL
676.	4	16					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00049	HL
677.							TEHTEC	T7072	rpri	A610MULC	SG20CCAL00014	CL
678.	4	17					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00049	HL
679.	4	18					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00049	HL
680.	4	19					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00049	HL
681.	4	20					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
682.	4	21					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
583.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL
584.	4	22					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
	4	23					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
	4	24					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: B
 DATABASE: Harris_SGB_1995

Sep. 23.1995 14:15

PAGE 16 of 125

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
687.	4	25					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
688.	4	26					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
689.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL
690.	4	27					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
691.	4	28					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
692.	4	29					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
693.	4	30					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
694.	4	31					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
695.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL
696.	4	32					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
697.	4	33					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
698.	4	34					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
699.	4	35					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
700.	4	36					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
701.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL
702.	4	37					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00007	HL
703.	4	38					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00007	HL
704.	4	39					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00007	HL
705.	4	40					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00020	HL
706.	4	41					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00007	HL
707.							TEHTEC	user5	rpri	A610MULC	SG20CCAL00001	CL
708.	4	42					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00007	HL
709.	4	43					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00007	HL
710.	4	44					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00007	HL
711.	4	45					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00009	HL
712.	4	46					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00009	HL
713.							TEHTEC	user5	rpri	A610MULC	SG20CCAL00001	CL
714.	4	47					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00009	HL
715.	4	48					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00009	HL
716.	4	49					TSHTSH	04825	reso	B620MRPC3C	SG21HCAL00009	HL
717.	4	50					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00009	HL
718.	4	51					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00009	HL
719.							TEHTEC	n0698	rpri	A610MULC	SG20CCAL00001	CL
720.	4	52					TSHTSH	04825	reso	B620MRPC3C	SG21HCAL00009	HL
721.	4	53					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00009	HL
722.	4	54					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00009	HL
723.	4	55					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00009	HL
724.	4	56					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00009	HL
725.							TEHTEC	n0698	rpri	A610MULC	SG20CCAL00001	CL
726.	4	57					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL
727.	4	58					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL
728.	4	59					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL
729.							TEHTEC	T7072	rpri	A610MULC	SG20CCAL00011	CL
730.	4	60					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL
731.	4	61					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL
732.	4	62					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL
733.	4	63					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL
734.	4	64					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL
735.							TEHTEC	T7072	rpri	A610MULC	SG20CCAL00011	CL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: B
 DATABASE: Harris_SGB_1995

Sep. 23,1995 14:15

PAGE 17 of 125



ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
736.	4	65					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL
737.	4	66					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL
738.	4	67					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL
739.	4	68					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL
740.	4	69					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL
741.							TEHTEC	T7072	rpri	A610MULC	SG20CCAL00011	CL
742.	4	70					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00040	HL
743.	4	71					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00040	HL
744.	4	72					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00040	HL
745.	4	73					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00040	HL
746.	4	74					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00040	HL
747.							TEHTEC	T7072	rpri	A610MULC	SG20CCAL00011	CL
748.	4	75					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00040	HL
749.	4	76					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00040	HL
750.	4	77					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00021	HL
751.	4	78					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00021	HL
752.	4	79					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00021	HL
753.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00005	CL
754.	4	80					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00021	HL
755.	4	81					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00021	HL
56.	4	82					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00021	HL
7.	4	83					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00021	HL
7.	4	84					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00021	HL
759.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00005	CL
760.	4	85					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00021	HL
761.	4	86					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00021	HL
762.	4	87					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00021	HL
763.	4	88					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00021	HL
764.	4	89					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00021	HL
765.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00005	CL
766.	4	90					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00021	HL
767.	4	91					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00021	HL
768.	4	92					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00021	HL
769.	4	93					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00021	HL
770.	4	94					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00011	HL
771.							TEHTEC	85534	rpri	A610MULC	SG20CCAL00002	CL
772.	4	95					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00012	HL
773.	4	96					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00011	HL
774.	4	97					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00012	HL
775.	4	98					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00011	HL
776.	4	99					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00012	HL
777.							TEHTEC	85534	rpri	A610MULC	SG20CCAL00002	CL
778.	4	100					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00011	HL
779.	4	101					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00012	HL
780.	4	102					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00011	HL
781.	4	103					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00012	HL
82.	4	104					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00011	HL
.							TEHTEC	85534	rpri	A610MULC	SG20CCAL00002	CL
84.	4	105					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00012	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: B
 DATABASE: Harris_SGB_1995

Sep. 23,1995 14:15

PAGE 18 of 125

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
785.	4	106						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00011	HL
786.	4	107						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00012	HL
787.	4	108						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00011	HL
788.	4	109						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00012	HL
789.								TEHTEC	B5534	rpri	A610MULC	SG20CCAL00002	CL
790.	4	110						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00011	HL
791.	4	111						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00012	HL
792.	4	112						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00011	HL
793.	4	113						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00012	HL
794.	4	114						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00013	HL
795.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00017	CL
796.	5	1						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00047	HL
797.			0.72	163	MBM	1	09C 17.77	TEHTEC	F3453	reso	A610MULC	SG20CCAL00014	CL
798.			0.94	166	MBM	1	08C 6.62	TEHTEC	F3453	reso	A610MULC	SG20CCAL00014	CL
799.	5	2						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL
800.	5	3						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00047	HL
801.	5	4						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL
802.	5	5						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00047	HL
803.	5	6						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL
804.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00014	CL
805.	5	7						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00047	HL
806.	5	8						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL
807.	5	9						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00047	HL
808.	5	10						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL
809.	5	11						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00047	HL
810.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00014	CL
811.	5	12						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL
812.	5	13						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00049	HL
813.	5	14						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00048	HL
814.	5	15						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00049	HL
815.	5	16						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00049	HL
816.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00014	CL
817.	5	17						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00049	HL
818.	5	18						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00049	HL
819.	5	19						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00049	HL
820.	5	20						TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL
821.	5	21						TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL
822.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL
823.	5	22						TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL
824.	5	23						TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL
825.	5	24						TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL
826.	5	25						TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL
827.	5	26						TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL
828.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL
829.	5	27						TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL
830.	5	28						TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL
831.	5	29						TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL
832.	5	30						TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL
833.	5	31						TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: B
 DATABASE: Harris_SGB_1995

Sep. 23.1995 14:15

PAGE 19 of 125

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
834.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL
835.	5	32						TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL
836.	5	33						TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL
837.	5	34						TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL
838.	5	35						TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL
839.	5	36						TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL
840.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL
841.	5	37						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00008	HL
842.	5	38						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00008	HL
843.	5	39						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00008	HL
844.	5	40						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00008	HL
845.	5	41						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00008	HL
846.								TEHTEC	user5	rpri	A610MULC	SG20CCAL00001	CL
847.	5	42						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00008	HL
848.	5	43						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00008	HL
849.	5	44						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00008	HL
850.	5	45						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00010	HL
851.	5	46						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00010	HL
852.								TEHTEC	user5	rpri	A610MULC	SG20CCAL00001	CL
853.	5	47						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00010	HL
854.	5	48						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00010	HL
855.	5	49						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00010	HL
856.	5	50						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00010	HL
857.	5	51						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00010	HL
858.								TEHTEC	n0698	rpri	A610MULC	SG20CCAL00001	CL
859.	5	52						TSHTSH	C1115	rsec	B620MRPC3C	SG21HCAL00010	HL
860.	5	53						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00010	HL
861.	5	54						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00010	HL
862.	5	55						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00010	HL
863.	5	56						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00010	HL
864.								TEHTEC	P5436	rsec	A610MULC	SG20CCAL00001	CL
865.	5	57						TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
866.	5	58						TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
867.	5	59						TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
868.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00011	CL
869.	5	60						TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
870.	5	61						TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
871.	5	62						TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
872.			0.48	166	MBM	1	10C 15.56	TEHTEC	D3858	reso	A610MULC	SG20CCAL00011	CL
873.	5	63						TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
874.	5	64						TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
875.								TEHTEC	D3858	reso	A610MULC	SG20CCAL00011	CL
876.	5	65						TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
877.	5	66						TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
878.	5	67						TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
879.	5	68						TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
880.	5	69						TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
881.								TEHTEC	C3335	reso	A610MULC	SG20CCAL00011	CL
882.	5	70						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: B
 DATABASE: Harris_SGB_1995

Sep. 23.1995 14:15

PAGE 20 of 125

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
883.	5	71					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
884.	5	72					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
885.	5	73					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
886.	5	74					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
887.							TEHTEC	T7072	rpri	A610MULC	SG20CCAL00011	CL
888.	5	75					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
889.	5	76					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
890.	5	77					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00022	HL
891.	5	78					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00022	HL
892.	5	79					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00022	HL
893.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00005	CL
894.	5	80					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00022	HL
895.	5	81					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00022	HL
896.	5	82					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00022	HL
897.	5	83					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00022	HL
898.	5	84					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00022	HL
899.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00005	CL
900.	5	85					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00022	HL
901.	5	86					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00022	HL
902.	5	87					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00022	HL
903.	5	88					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00022	HL
904.	5	89					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00022	HL
905.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00005	CL
906.	5	90					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00022	HL
907.	5	91					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00022	HL
908.	5	92					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00022	HL
909.	5	93					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00022	HL
910.	5	94					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00022	HL
911.							TEHTEC	B5534	rpri	A610MULC	SG20CCAL00002	CL
912.	5	95					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00012	HL
913.	5	96					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00011	HL
914.	5	97					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00012	HL
915.	5	98					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00011	HL
916.	5	99					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00012	HL
917.							TEHTEC	B5534	rpri	A610MULC	SG20CCAL00002	CL
918.	5	100					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00011	HL
919.	5	101					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00012	HL
920.	5	102					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00011	HL
921.	5	103					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00012	HL
922.	5	104					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00011	HL
923.							TEHTEC	B5534	rpri	A610MULC	SG20CCAL00002	CL
924.	5	105					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00012	HL
925.	5	106					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00011	HL
926.	5	107					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00012	HL
927.	5	108					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00011	HL
928.	5	109					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00012	HL
929.							TEHTEC	B5534	rpri	A610MULC	SG20CCAL00002	CL
930.	5	110					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00011	HL
931.	5	111					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00012	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: B
 DATABASE: Harris_SGB_1995

Sep. 23.1995 14:15

PAGE 21 of 125

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
932.	5	112						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00011	HL
933.	5	113						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00012	HL
934.	5	114						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00013	HL
935.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00017	CL
936.	6	1						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00047	HL
937.								11H11H	T9924	rpri	B620MRPC3C	SG21HCAL00052	HL
938.		6.51	185	DNT	1	10H	41.64	TEHTEC	F3453	reso	A610MULC	SG20CCAL00014	CL
939.		23.88	183	DNT	1	10H	42.34	TEHTEC	F3453	reso	A610MULC	SG20CCAL00014	CL
940.		18.02	174	DNT	P1	11H	-0.11	TEHTEC	F3453	reso	A610MULC	SG20CCAL00014	CL
941.		5.79	184	DNT	1	11H	13.86	TEHTEC	F3453	reso	A610MULC	SG20CCAL00014	CL
942.		11.50	174	DNT	P1	11C	-0.38	TEHTEC	F3453	reso	A610MULC	SG20CCAL00014	CL
943.		10.86	182	DNT	1	10C	42.02	TEHTEC	F3453	reso	A610MULC	SG20CCAL00014	CL
944.	6	2						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL
945.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00014	CL
946.	6	3						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00047	HL
947.	6	4						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL
948.	6	5						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00047	HL
949.	6	6						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL
950.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00014	CL
951.	6	7						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00047	HL
952.	6	8						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL
953.	6	9						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00047	HL
954.	6	10						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL
955.	6	11						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00047	HL
956.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00014	CL
957.	6	12						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL
958.	6	13						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00049	HL
959.	6	14						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00048	HL
960.	6	15						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00049	HL
961.	6	16						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00049	HL
962.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00014	CL
963.	6	17						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00049	HL
964.	6	18						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00049	HL
965.	6	19						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00049	HL
966.	6	20						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
967.	6	21						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
968.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL
969.	6	22						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
970.	6	23						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
971.	6	24						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
972.	6	25						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
973.	6	26						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
974.		18.97	179	DNT	P1	10C	-0.23	TEHTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL
975.	6	27						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
976.	6	28						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
977.	6	29						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
978.	6	30						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
979.	6	31						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
980.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL

*** INSPECTION FINAL REPORT LISTING ***

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: B
 DATABASE: Harris_SGB_1995

Sep. 23.1995 14:15

PAGE 22 of 125

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
981.	6	32					TSHTSH	F3325	rsec	B620MRPC3C	SG21HCAL00044	HL
982.	6	33					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
983.	6	34					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
984.	6	35					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
985.	6	36					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
986.							TEHTEC	F9284	rpri	A610MJLC	SG20CCAL00013	CL
987.	6	37					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00007	HL
988.	6	38					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00007	HL
989.	6	39					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00007	HL
990.	6	40					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00007	HL
991.	6	41					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00007	HL
992.							TEHTEC	user5	rpri	A610MJLC	SG20CCAL00001	CL
993.	6	42					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00007	HL
994.	6	43					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00007	HL
995.	6	44					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00007	HL
996.	6	45					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00009	HL
997.	6	46					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00009	HL
998.							TEHTEC	user5	rpri	A610MJLC	SG20CCAL00001	CL
999.	6	47					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00009	HL
1000.	6	48					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00009	HL
01.	6	49					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00009	HL
02.	6	50					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00009	HL
03.	6	51					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00009	HL
1004.							TEHTEC	n0698	rpri	A610MJLC	SG20CCAL00001	CL
1005.	6	52					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00009	HL
1006.	6	53					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00009	HL
1007.	6	54					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00009	HL
1008.	6	55					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00009	HL
1009.	6	56					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00009	HL
1010.							TEHTEC	T7072	rpri	A610MJLC	SG20CCAL00017	CL
1011.	6	57					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL
1012.	6	58					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL
1013.	6	59					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL
1014.							TEHTEC	T7072	rpri	A610MJLC	SG20CCAL00011	CL
1015.	6	60					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL
1016.	6	61					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL
1017.	6	62					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL
1018.	6	63					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL
1019.	6	64					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL
1020.							TEHTEC	C3335	reso	A610MJLC	SG20CCAL00011	CL
1021.	6	65					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL
1022.	6	66					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL
1023.	6	67					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL
1024.	6	68					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL
1025.	6	69					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL
026.							TEHTEC	C3335	reso	A610MJLC	SG20CCAL00011	CL
027.	6	70					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00040	HL
028.	6	71					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00040	HL
029.	6	72					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00040	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: B
 DATABASE: Harris_SGB_1995

Sep. 23.1995 14:15

PAGE 23 of 125

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
1030.	6	73						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00040	HL
1031.	6	74						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00040	HL
1032.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00011	CL
1033.	6	75						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00040	HL
1034.	6	76						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00040	HL
1035.	6	77						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00021	HL
1036.	6	78						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00021	HL
1037.	6	79						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00021	HL
1038.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00005	CL
1039.	6	80						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00021	HL
1040.	6	81						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00021	HL
1041.	6	82						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00021	HL
1042.	6	83						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00021	HL
1043.	6	84						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00021	HL
1044.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00005	CL
1045.	6	85						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00021	HL
1046.	6	86						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00021	HL
1047.	6	87						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00021	HL
1048.	6	88						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00021	HL
1049.	6	89						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00021	HL
50.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00005	CL
1.	6	90						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00021	HL
2.	6	91						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00021	HL
1053.	6	92						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00021	HL
1054.			0.30	145	MBM	1	03H 18.09	TEHTEC	H1274	reso	A610MULC	SG20CCAL00005	CL
1055.	6	93						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00021	HL
1056.	6	94						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00011	HL
1057.								TEHTEC	B5534	rpri	A610MULC	SG20CCAL00002	CL
1058.	6	95						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00012	HL
1059.	6	96						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00011	HL
1060.	6	97						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00012	HL
1061.	6	98						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00011	HL
1062.	6	99						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00012	HL
1063.								TEHTEC	B5534	rpri	A610MULC	SG20CCAL00002	CL
1064.	6	100						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00011	HL
1065.	6	101						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00012	HL
1066.	6	102						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00011	HL
1067.	6	103						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00012	HL
1068.	6	104						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00011	HL
1069.								TEHTEC	B5534	rpri	A610MULC	SG20CCAL00002	CL
1070.	6	105						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00012	HL
1071.	6	106						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00011	HL
1072.	6	107						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00012	HL
1073.	6	108						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00011	HL
1074.	6	109						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00012	HL
1075.								TEHTEC	B5534	rpri	A610MULC	SG20CCAL00002	CL
76.	6	110						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00011	HL
77.	6	111						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00012	HL
78.	6	112						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00011	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: B
 DATABASE: Harris_SGB_1995

Sep. 23,1995 14:15

PAGE 24 of 125

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG	
1079.	6	113						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00012	HL	
1080.								TEHTEC	B5534	rpri	A610MULC	SG20CCAL00002	CL	
1081.	6	114						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00013	HL	
1082.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00017	CL	
1083.	7	2						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00047	HL	
1084.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00014	CL	
1085.	7	3						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL	
1086.	7	4						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00047	HL	
1087.	7	5						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL	
1088.	7	6						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00047	HL	
1089.								TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00047	HL	
1090.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00014	CL	
1091.	7	7						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL	
1092.	7	8						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00047	HL	
1093.	7	9						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL	
1094.	7	10						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00047	HL	
1095.	7	11						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL	
1096.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00014	CL	
1097.	7	12						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00047	HL	
1098.	7	13						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL	
99.	7	14						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00049	HL	
100.	7	15						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00048	HL	
101.	7	16						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00049	HL	
1102.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00014	CL	
1103.	7	17						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00049	HL	
1104.	7	18						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00049	HL	
1105.	7	19						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00049	HL	
1106.	7	20						TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL	
1107.	7	21						TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL	
1108.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL	
1109.	7	22						TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL	
1110.	7	23						TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL	
1111.	7	24						TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL	
1112.	7	25						TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL	
1113.	7	26						TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL	
1114.			8.95	182	DNT	P1	10C	-0.32	TEHTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL
1115.	7	27						TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL	
1116.	7	28						TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL	
1117.	7	29						TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL	
1118.	7	30						TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL	
1119.	7	31						TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL	
1120.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL	
1121.	7	32						TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL	
1122.	7	33						TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL	
1123.	7	34						TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL	
124.	7	35						TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL	
125.	7	36						TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL	
126.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL	
127.	7	37						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00008	HL	

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: B
 DATABASE: Harris_SGB_1995

Sep. 23,1995 14:15

PAGE 25 of 125

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
1128.	7	38					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00008	HL
1129.	7	39					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00008	HL
1130.	7	40					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00008	HL
1131.	7	41					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00008	HL
1132.							TEHTEC	user5	rpri	A610MULC	SG20CCAL00001	CL
1133.	7	42					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00008	HL
1134.	7	43					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00008	HL
1135.	7	44					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00008	HL
1136.	7	45					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00010	HL
1137.	7	46					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00010	HL
1138.							TEHTEC	user5	rpri	A610MULC	SG20CCAL00001	CL
1139.	7	47					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00010	HL
1140.	7	48					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00010	HL
1141.	7	49					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00010	HL
1142.	7	50					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00010	HL
1143.	7	51					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00010	HL
1144.							TEHTEC	n0698	rpri	A610MULC	SG20CCAL00001	CL
1145.	7	52					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00010	HL
1146.	7	53					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00010	HL
1147.	7	54					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00010	HL
48.	7	55					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00010	HL
1148.	7	56					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00010	HL
1149.							TEHTEC	n0698	rpri	A610MULC	SG20CCAL00001	CL
1151.	7	57					TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
1152.	7	58					TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
1153.	7	59					TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
1154.							TEHTEC	T7072	rpri	A610MULC	SG20CCAL00011	CL
1155.	7	60					TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
1156.	7	61					TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
1157.	7	62					TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
1158.	7	63					TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
1159.	7	64					TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
1160.							TEHTEC	C3335	reso	A610MULC	SG20CCAL00011	CL
1161.	7	65					TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
1162.	7	66					TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
1163.	7	67					TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
1164.	7	68					TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
1165.	7	69					TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
1166.							TEHTEC	C3335	reso	A610MULC	SG20CCAL00011	CL
1167.	7	70					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
1168.	7	71					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
1169.	7	72					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
1170.	7	73					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00043	HL
1171.	7	74					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
1172.							TEHTEC	C3335	reso	A610MULC	SG20CCAL00011	CL
1173.	7	75					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
1174.	7	76					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
1175.	7	77					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00022	HL
1176.	7	78					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00022	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: B
 DATABASE: Harris_SGB_1995

Sep. 23.1995 14:15

PAGE 26 of 125

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
1177.	7	79						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00022	HL
1178.			0.58	171	MBM	1	09C 35.20	TEHTEC	F9284	rpri	A610MULC	SG20CCAL00005	CL
1179.	7	80						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00022	HL
1180.	7	81						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00022	HL
1181.	7	82						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00022	HL
1182.	7	83						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00022	HL
1183.	7	84						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00022	HL
1184.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00005	CL
1185.	7	85						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00022	HL
1186.	7	86						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00022	HL
1187.	7	87						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00022	HL
1188.	7	88						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00022	HL
1189.	7	89						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00022	HL
1190.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00005	CL
1191.	7	90						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00022	HL
1192.	7	91						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00022	HL
1193.	7	92						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00022	HL
1194.	7	93						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00022	HL
1195.	7	94						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00011	HL
1196.								TEHTEC	85534	rpri	A610MULC	SG20CCAL00002	CL
97.	7	95						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00012	HL
98.	7	96						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00011	HL
99.	7	97						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00012	HL
1200.	7	98						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00011	HL
1201.	7	99						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00012	HL
1202.								TEHTEC	85534	rpri	A610MULC	SG20CCAL00002	CL
1203.	7	100						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00011	HL
1204.	7	101						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00012	HL
1205.	7	102						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00011	HL
1206.	7	103						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00012	HL
1207.	7	104						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00011	HL
1208.								TEHTEC	85534	rpri	A610MULC	SG20CCAL00002	CL
1209.	7	105						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00012	HL
1210.	7	106						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00011	HL
1211.	7	107						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00012	HL
1212.	7	108						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00011	HL
1213.	7	109						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00012	HL
1214.								TEHTEC	85534	rpri	A610MULC	SG20CCAL00002	CL
1215.	7	110						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00011	HL
1216.	7	111						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00012	HL
1217.	7	112						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00011	HL
1218.	7	113						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00012	HL
1219.								TEHTEC	85534	rpri	A610MULC	SG20CCAL00002	CL
1220.	8	2						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00047	HL
1221.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00014	CL
1222.	8	3						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL
1223.	8	4						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00047	HL
1224.	8	5						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL
1225.	8	6						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00047	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: B
 DATABASE: Harris_SGB_1995

Sep. 23,1995 14:15

PAGE 27 of 125

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
1226.							TEHTEC	T7072	rpri	A610MULC	SG20CCAL00014	CL
1227.	8	7					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL
1228.	8	8					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00047	HL
1229.	8	9					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL
1230.	8	10					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00047	HL
1231.	8	11					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL
1232.							TEHTEC	T7072	rpri	A610MULC	SG20CCAL00014	CL
1233.	8	12					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00047	HL
1234.	8	13					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL
1235.	8	14					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00049	HL
1236.	8	15					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00048	HL
1237.	8	16					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00049	HL
1238.							TEHTEC	T7072	rpri	A610MULC	SG20CCAL00014	CL
1239.	8	17					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00049	HL
1240.	8	18					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00049	HL
1241.	8	19					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00049	HL
1242.	8	20					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
1243.	8	21					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
1244.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL
1245.	8	22					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
46.	8	23					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
47.	8	24					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
48.	8	25					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
1249.	8	26					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
1250.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL
1251.	8	27					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
1252.	8	28					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
1253.	8	29					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
1254.	8	30					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
1255.	8	31					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
1256.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL
1257.	8	32					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
1258.	8	33					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
1259.	8	34					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
1260.	8	35					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
1261.	8	36					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
1262.							TEHTEC	T7072	rpri	A610MULC	SG20CCAL00017	CL
1263.	8	37					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00007	HL
1264.	8	38					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00007	HL
1265.	8	39					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00007	HL
1266.	8	40					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00007	HL
1267.	8	41					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00007	HL
1268.							TEHTEC	user5	rpri	A610MULC	SG20CCAL00001	CL
1269.	8	42					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00007	HL
1270.	8	43					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00007	HL
1271.	8	44					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00007	HL
72.	8	45					TSHTSH	J1978	rsec	B620MRPC3C	SG21HCAL00009	HL
74.	8	46					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00009	HL
							TEHTEC	user5	rpri	A610MULC	SG20CCAL00001	CL

*** INSPECTION FINAL REPORT LISTING ***

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: B
 DATABASE: Harris_SGB_1995

Sep. 23.1995 14:15

PAGE 28 of 125

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
1275.	8	47					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00009	HL
1276.	8	48					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00009	HL
1277.	8	49					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00009	HL
1278.	8	50					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00009	HL
1279.	8	51					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00009	HL
1280.							TEHTEC	n0698	rpri	A610MJLC	SG20CCAL00001	CL
1281.	8	52					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00009	HL
1282.	8	53					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00009	HL
1283.	8	54					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00009	HL
1284.	8	55					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00009	HL
1285.	8	56					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00009	HL
1286.							TEHTEC	n0698	rpri	A610MJLC	SG20CCAL00001	CL
1287.	8	57					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL
1288.	8	58					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL
1289.	8	59					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL
1290.							TEHTEC	T7072	rpri	A610MJLC	SG20CCAL00011	CL
1291.	8	60					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL
1292.	8	61					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL
1293.	8	62					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL
1294.	8	63					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL
95.	8	64					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL
96.							TEHTEC	C3335	reso	A610MJLC	SG20CCAL00011	CL
97.	8	65					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL
1298.	8	66					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL
1299.	8	67					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL
1300.	8	68					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL
1301.	8	69					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL
1302.							TEHTEC	C3335	reso	A610MJLC	SG20CCAL00011	CL
1303.	8	70					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00040	HL
1304.	8	71					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00040	HL
1305.	8	72					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00040	HL
1306.	8	73					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00042	HL
1307.	8	74					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00040	HL
1308.							TEHTEC	C3335	reso	A610MJLC	SG20CCAL00011	CL
1309.	8	75					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00040	HL
1310.	8	76					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00040	HL
1311.	8	77					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00021	HL
1312.	8	78					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00021	HL
1313.	8	79					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00021	HL
1314.							TEHTEC	F9284	rpri	A610MJLC	SG20CCAL00005	CL
1315.	8	80					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00021	HL
1316.	8	81					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00021	HL
1317.	8	82					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00021	HL
1318.	8	83					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00021	HL
1319.	8	84					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00021	HL
1320.							TEHTEC	F9284	rpri	A610MJLC	SG20CCAL00005	CL
1321.	8	85					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00021	HL
1322.	8	86					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00021	HL
1323.	8	87					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00021	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: B
 DATABASE: Harris_SGB_1995

Sep. 23.1995 14:15

PAGE 29 of 125

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
1324.	8	88						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00021	HL
1325.	8	89						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00021	HL
1326.								TEHTEC	F9284	rpri	A610MJLC	SG20CCAL00005	CL
1327.	8	90						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00021	HL
1328.	8	91						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00021	HL
1329.	8	92						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00021	HL
1330.	8	93						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00021	HL
1331.	8	94						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00011	HL
1332.								TEHTEC	B5534	rpri	A610MJLC	SG20CCAL00002	CL
1333.	8	95						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00012	HL
1334.	8	96						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00011	HL
1335.	8	97						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00012	HL
1336.	8	98						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00011	HL
1337.	8	99						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00012	HL
1338.								TEHTEC	B5534	rpri	A610MJLC	SG20CCAL00002	CL
1339.	8	100						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00011	HL
1340.	8	101						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00012	HL
1341.	8	102						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00011	HL
1342.	8	103						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00012	HL
1343.	8	104						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00011	HL
1344.								TEHTEC	B5534	rpri	A610MJLC	SG20CCAL00002	CL
1345.	8	105						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00012	HL
1346.	8	106						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00011	HL
1347.	8	107						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00012	HL
1348.	8	108						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00011	HL
1349.	8	109						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00012	HL
1350.		7.10	187	DNT	1	10H	30.71	TEHTEC	B5534	rpri	A610MJLC	SG20CCAL00002	CL
1351.		10.25	184	DNT	1	10H	31.62	TEHTEC	B5534	rpri	A610MJLC	SG20CCAL00002	CL
1352.		6.85	186	DNT	1	10H	32.16	TEHTEC	B5534	rpri	A610MJLC	SG20CCAL00002	CL
1353.		8.68	187	DNT	1	10H	33.34	TEHTEC	B5534	rpri	A610MJLC	SG20CCAL00002	CL
1354.		6.63	186	DNT	1	10H	34.48	TEHTEC	B5534	rpri	A610MJLC	SG20CCAL00002	CL
1355.		6.78	187	DNT	1	10C	33.44	TEHTEC	B5534	rpri	A610MJLC	SG20CCAL00002	CL
1356.		10.69	186	DNT	1	10C	34.83	TEHTEC	B5534	rpri	A610MJLC	SG20CCAL00002	CL
1357.	8	110						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00011	HL
1358.	8	111						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00012	HL
1359.	8	112						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00011	HL
1360.	8	113						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00012	HL
1361.								TEHTEC	B5534	rpri	A610MJLC	SG20CCAL00002	CL
1362.	9	2						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00047	HL
1363.								TEHTEC	T7072	rpri	A610MJLC	SG20CCAL00014	CL
1364.	9	3						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL
1365.	9	4						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00047	HL
1366.	9	5						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL
1367.	9	6						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00047	HL
1368.								TEHTEC	T7072	rpri	A610MJLC	SG20CCAL00014	CL
1369.	9	7						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL
1370.	9	8						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00047	HL
1371.	9	9						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL
1372.	9	10						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00047	HL

*** INSPECTION FINAL REPORT LISTING ***

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: B
 DATABASE: Harris_SGB_1995

Sep. 23,1995 14:15

PAGE 30 of 125

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
1373.	9	11					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL
1374.							TEHTEC	T7072	rpri	A610MULC	SG20CCAL00014	CL
1375.	9	12					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00049	HL
1376.	9	13					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00048	HL
1377.	9	14					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00049	HL
1378.	9	15					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00048	HL
1379.	9	16					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00049	HL
1380.							TEHTEC	T7072	rpri	A610MULC	SG20CCAL00014	CL
1381.	9	17					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00049	HL
1382.	9	18					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00049	HL
1383.	9	19					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00049	HL
1384.	9	20					TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL
1385.	9	21					TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL
1386.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL
1387.	9	22					TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL
1388.	9	23					TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL
1389.	9	24					TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL
1390.	9	25					TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL
1391.	9	26					TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL
1392.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL
93.	9	27					TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL
.	9	30					TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL
.	9	31					TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL
1396.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL
1397.	9	32					TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL
1398.	9	33					TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL
1399.	9	34					TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL
1400.	9	35					TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL
1401.	9	36					TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL
1402.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL
1403.	9	37					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00008	HL
1404.	9	38					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00008	HL
1405.	9	39					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00008	HL
1406.	9	40					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00008	HL
1407.	9	41					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00008	HL
1408.							TEHTEC	user5	rpri	A610MULC	SG20CCAL00001	CL
1409.	9	42					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00008	HL
1410.	9	43					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00008	HL
1411.	9	44					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00008	HL
1412.	9	45					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00010	HL
1413.	9	46					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00010	HL
1414.							TEHTEC	user5	rpri	A610MULC	SG20CCAL00001	CL
1415.	9	47					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00010	HL
1416.	9	48					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00010	HL
1417.	9	49					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00010	HL
1418.	9	50					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00010	HL
1419.	9	51					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00010	HL
.							TEHTEC	n0698	rpri	A610MULC	SG20CCAL00001	CL
1.	9	52					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00010	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: B
 DATABASE: Harris_SGB_1995

Sep. 23,1995 14:15

PAGE 31 of 125

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
1422.	9	53					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00010	HL
1423.	9	54					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00010	HL
1424.	9	55					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00010	HL
1425.	9	56					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00010	HL
1426.							TEHTEC	n0698	rpri	A610MULC	SG20CCAL00001	CL
1427.	9	59					TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
1428.							TEHTEC	T7072	rpri	A610MULC	SG20CCAL00011	CL
1429.	9	60					TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
1430.	9	61					TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
1431.	9	62					TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
1432.	9	63					TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
1433.	9	64					TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
1434.							TEHTEC	C3335	reso	A610MULC	SG20CCAL00011	CL
1435.	9	65					TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
1436.	9	66					TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
1437.	9	67					TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
1438.	9	68					TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
1439.	9	69					TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
1440.							TEHTEC	C3335	reso	A610MULC	SG20CCAL00011	CL
1441.	9	70					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
1442.	9	71					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
1443.	9	72					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
1444.	9	73					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
1445.	9	74					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
1446.							TEHTEC	C3335	reso	A610MULC	SG20CCAL00011	CL
1447.	9	75					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
1448.	9	76					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
1449.	9	77					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00022	HL
1450.	9	78					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00022	HL
1451.	9	79					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00022	HL
1452.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00005	CL
1453.	9	80					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00022	HL
1454.	9	81					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00022	HL
1455.	9	82					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00022	HL
1456.	9	83					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00022	HL
1457.	9	84					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00022	HL
1458.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00005	CL
1459.	9	85					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00022	HL
1460.	9	88					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00022	HL
1461.	9	89					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00022	HL
1462.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00005	CL
1463.	9	90					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00022	HL
1464.	9	91					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00022	HL
1465.	9	92					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00022	HL
1466.	9	93					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00022	HL
1467.	9	94					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00011	HL
1468.							TEHTEC	B5534	rpri	A610MULC	SG20CCAL00002	CL
1469.	9	95					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00012	HL
1470.	9	96					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00011	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: B
 DATABASE: Harris_SGB_1995

Sep. 23.1995 14:15

PAGE 32 of 125

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
1471.	9	97						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00012	HL
1472.	9	98						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00011	HL
1473.			0.49	169	MBM	1	04C 12.74	TEHTEC	85534	rpri	A610MULC	SG20CCAL00002	CL
1474.	9	99			REC			TSHTSH	03858	reso	B620MRPC3C	SG21HCAL00012	HL
1475.								TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00020	HL
1476.								TEHTEC	85534	rpri	A610MULC	SG20CCAL00002	CL
1477.	9	100						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00011	HL
1478.	9	101						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00012	HL
1479.	9	102						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00011	HL
1480.	9	103						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00012	HL
1481.	9	104						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00011	HL
1482.								TEHTEC	85534	rpri	A610MULC	SG20CCAL00002	CL
1483.	9	105						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00012	HL
1484.	9	106						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00011	HL
1485.	9	107						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00012	HL
1486.	9	108						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00011	HL
1487.	9	109						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00012	HL
1488.								TEHTEC	85534	rpri	A610MULC	SG20CCAL00002	CL
1489.	9	110						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00011	HL
1490.	9	111						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00012	HL
91.	9	112						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00011	HL
92.	9	113						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00012	HL
93.								TEHTEC	85534	rpri	A610MULC	SG20CCAL00002	CL
1494.	10	2						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00047	HL
1495.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00014	CL
1496.	10	3						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL
1497.	10	4						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00047	HL
1498.	10	5						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL
1499.	10	6						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00047	HL
1500.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00014	CL
1501.	10	7						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL
1502.	10	8						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00047	HL
1503.	10	9						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL
1504.	10	10						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00047	HL
1505.	10	11						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL
1506.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00014	CL
1507.	10	12						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00049	HL
1508.	10	13						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00048	HL
1509.	10	14						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00049	HL
1510.	10	15						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00048	HL
1511.	10	16						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00049	HL
1512.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00014	CL
1513.	10	17						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00049	HL
1514.	10	18						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00049	HL
1515.	10	19						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00049	HL
1516.	10	20						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
1517.	10	21						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
1518.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL
1519.	10	22						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: B
 DATABASE: Harris_SGB_1995

Sep. 23.1995 14:15

PAGE 33 of 125

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
1520.	10	23					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
1521.	10	24					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
1522.	10	25					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
1523.	10	26					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
1524.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL
1525.	10	27					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
1526.	10	30					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
1527.	10	31					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
1528.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL
1529.	10	32					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
1530.	10	33					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
1531.	10	34					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
1532.	10	35					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
1533.	10	36					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
1534.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL
1535.	10	37					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00007	HL
1536.	10	38					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00007	HL
1537.	10	39					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00007	HL
1538.	10	40					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00007	HL
1539.	10	41					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00007	HL
40.							TEHTEC	user5	rpri	A610MULC	SG20CCAL00001	CL
1.	10	42					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00007	HL
2.	10	43					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00007	HL
1543.	10	44					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00007	HL
1544.	10	45					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00009	HL
1545.	10	46					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00009	HL
1546.							TEHTEC	user5	rpri	A610MULC	SG20CCAL00001	CL
1547.	10	47					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00009	HL
1548.	10	48					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00009	HL
1549.	10	49					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00009	HL
1550.	10	50					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00009	HL
1551.	10	51					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00009	HL
1552.							TEHTEC	n0698	rpri	A610MULC	SG20CCAL00001	CL
1553.	10	52					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00009	HL
1554.	10	53					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00009	HL
1555.	10	54					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00009	HL
1556.	10	55					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00009	HL
1557.	10	56					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00009	HL
1558.							TEHTEC	n0698	rpri	A610MULC	SG20CCAL00001	CL
1559.	10	59					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL
1560.							TEHTEC	T7072	rpri	A610MULC	SG20CCAL00011	CL
1561.	10	60					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL
1562.	10	61					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL
1563.	10	62					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL
1564.	10	63					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL
1565.	10	64					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL
1566.							TEHTEC	T7072	rpri	A610MULC	SG20CCAL00011	CL
1567.	10	65					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL
1568.	10	66					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: B
 DATABASE: Harris_SGB_1995

Sep. 23,1995 14:15

PAGE 34 of 125

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
1569.	10	67					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL
1570.	10	68					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL
1571.	10	69					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL
1572.							TEHTEC	T7072	rpri	A610MULC	SG20CCAL00011	CL
1573.	10	70					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00040	HL
1574.	10	71					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00040	HL
1575.	10	72					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00040	HL
1576.	10	73					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00040	HL
1577.	10	74					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00040	HL
1578.							TEHTEC	C3335	reso	A610MULC	SG20CCAL00011	CL
1579.	10	75					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00040	HL
1580.	10	76					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00040	HL
1581.	10	77					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00021	HL
1582.	10	78					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00021	HL
1583.	10	79					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00021	HL
1584.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00005	CL
1585.	10	80					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00021	HL
1586.	10	81					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00021	HL
1587.	10	82					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00021	HL
1588.	10	83					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00021	HL
89.	10	84					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00021	HL
9.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00005	CL
10.	10	85					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00021	HL
1592.	10	88					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00021	HL
1593.	10	89					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00021	HL
1594.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00005	CL
1595.	10	90					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00021	HL
1596.	10	91					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00021	HL
1597.	10	92					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00021	HL
1598.	10	93					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00021	HL
1599.	10	94					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00011	HL
1600.							TEHTEC	B5534	rpri	A610MULC	SG20CCAL00002	CL
1601.	10	95					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00012	HL
1602.	10	96					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00011	HL
1603.	10	97					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00012	HL
1604.	10	98					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00011	HL
1605.	10	99					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00020	HL
1606.							TEHTEC	B5534	rpri	A610MULC	SG20CCAL00002	CL
1607.	10	100					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00011	HL
1608.	10	101					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00012	HL
1609.	10	102					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00011	HL
1610.	10	103					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00012	HL
1611.	10	104					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00011	HL
1612.							TEHTEC	B5534	rpri	A610MULC	SG20CCAL00002	CL
1613.	10	105					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00012	HL
1614.	10	106					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00011	HL
1615.	10	107					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00012	HL
1616.	10	108					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00011	HL
1617.	10	109					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00012	HL

*** INSPECTION FINAL REPORT LISTING ***

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: B
 DATABASE: Harris_SGB_1995

Sep. 23.1995 14:15

PAGE 35 of 125

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
1618.								TEHTEC	B5534	rpri	A610MULC	SG20CCAL00002	CL
1619.	10	110						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00011	HL
1620.	10	111						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00012	HL
1621.	10	112						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00011	HL
1622.	10	113						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00012	HL
1623.								TEHTEC	B5534	rpri	A610MULC	SG20CCAL00002	CL
1624.	11	2						TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00047	HL
1625.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL
1626.	11	3						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL
1627.	11	4						TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00047	HL
1628.	11	5						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL
1629.	11	6						TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00047	HL
1630.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL
1631.	11	7						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL
1632.	11	8						TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00047	HL
1633.	11	9						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL
1634.	11	10						TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00047	HL
1635.	11	11						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL
1636.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL
1637.	11	12						TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00047	HL
38.	11	13						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL
39.	11	14						TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00047	HL
40.	11	15						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL
1641.	11	16						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00047	HL
1642.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL
1643.	11	17						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL
1644.	11	18						TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL
1645.	11	19						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
1646.	11	20						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00043	HL
1647.	11	21						TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00043	HL
1648.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
1649.	11	22						TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00043	HL
1650.	11	23						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00043	HL
1651.	11	24						TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00043	HL
1652.	11	25						TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00043	HL
1653.	11	26						TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00043	HL
1654.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
1655.	11	27						TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00043	HL
1656.	11	28						TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00043	HL
1657.	11	29						TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL
1658.	11	30						TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL
1659.	11	31						TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL
1660.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL
1661.	11	32						TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL
1662.	11	33						TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL
1663.	11	34						TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL
1664.	11	35						TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL
1665.	11	36						TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL
1666.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: B
 DATABASE: Harris_SGB_1995

Sep. 23,1995 14:15

PAGE 36 of 125

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
1667.	11	37						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00006	HL
1668.	11	38						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00006	HL
1669.	11	39						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00006	HL
1670.	11	40						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00008	HL
1671.	11	41						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00008	HL
1672.								TEHTEC	P5436	rsec	A610MULC	SG20CCAL00001	CL
1673.	11	42						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00008	HL
1674.	11	43						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00008	HL
1675.	11	44						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00008	HL
1676.	11	45						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00008	HL
1677.	11	46						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00008	HL
1678.								TEHTEC	user5	rpri	A610MULC	SG20CCAL00001	CL
1679.	11	47						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00008	HL
1680.	11	48						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00008	HL
1681.			0.43	156	M8M	1	03H 13.16	TEHTEC	user5	rpri	A610MULC	SG20CCAL00001	CL
1682.	11	49						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00008	HL
1683.	11	50						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00008	HL
1684.	11	51						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00008	HL
1685.								TEHTEC	user5	rpri	A610MULC	SG20CCAL00001	CL
1686.	11	52						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00008	HL
87.	11	53						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00008	HL
88.	11	54						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00008	HL
89.	11	55						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00008	HL
1690.	11	56						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00008	HL
1691.								TEHTEC	user5	rpri	A610MULC	SG20CCAL00001	CL
1692.	11	57						TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
1693.	11	58						TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
1694.	11	59						TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
1695.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00010	CL
1696.	11	60						TSHTSH	F3325	rsec	B620MRPC3C	SG21HCAL00039	HL
1697.	11	61						TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
1698.	11	62						TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
1699.	11	63						TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
1700.	11	64						TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
1701.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00010	CL
1702.	11	65						TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
1703.	11	66						TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
1704.	11	67						TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
1705.	11	68						TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
1706.	11	69						TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
1707.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00010	CL
1708.	11	70						TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
1709.	11	71						TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
1710.	11	72						TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
1711.	11	73						TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
1712.	11	74						TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
1713.								TEHTEC	F3453	reso	A610MULC	SG20CCAL00017	CL
1714.								TSHTSH	D3858	reso	A610MULC	SG20CCAL00010	CL
1715.	11	75						TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL

RES

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: B
 DATABASE: Harris_SGB_1995

Sep. 23.1995 14:15

PAGE 37 of 125

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
1716.	11	76					TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
1717.	11	77					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00020	HL
1718.	11	78					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00020	HL
1719.	11	79					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00020	HL
1720.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00005	CL
1721.	11	80					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00020	HL
1722.	11	81					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00020	HL
1723.	11	82					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00020	HL
1724.	11	83					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00020	HL
1725.	11	84					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00020	HL
1726.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00005	CL
1727.	11	85					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00020	HL
1728.	11	86					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00020	HL
1729.	11	87					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00020	HL
1730.	11	88					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00020	HL
1731.	11	89					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00020	HL
1732.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00005	CL
1733.	11	90					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00020	HL
1734.	11	91					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00020	HL
1735.	11	92					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00020	HL
36.	11	93					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00020	HL
37.	11	94			REC		TSHTSH	F3453	reso	B620MRPC3C	SG21HCAL00013	HL
38.							TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00019	HL
1739.							TEHTEC	85534	rpri	A610MULC	SG20CCAL00002	CL
1740.							TEHTEC	85534	rpri	A610MULC	SG20CCAL00003	CL
1741.	11	95			REC			F3453	reso	B620MRPC3C	SG21HCAL00014	HL
1742.							TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00020	HL
1743.	11	96			REC			F3453	reso	B620MRPC3C	SG21HCAL00013	HL
1744.							TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00019	HL
1745.	11	97			REC			F3453	reso	B620MRPC3C	SG21HCAL00014	HL
1746.							TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00020	HL
1747.	11	98					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00013	HL
1748.	11	99					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00014	HL
1749.							TEHTEC	85534	rpri	A610MULC	SG20CCAL00003	CL
1750.	11	100					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00013	HL
1751.	11	101					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00014	HL
1752.	11	102					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00013	HL
1753.	11	103					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00014	HL
1754.	11	104					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00013	HL
1755.							TEHTEC	85534	rpri	A610MULC	SG20CCAL00003	CL
1756.	11	105					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00014	HL
1757.	11	106					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00013	HL
1758.	11	107					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00014	HL
1759.	11	108					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00013	HL
1760.	11	109					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00014	HL
1761.							TEHTEC	85534	rpri	A610MULC	SG20CCAL00003	CL
62.	11	110					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00013	HL
63.	11	111					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00014	HL
64.	11	112					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00013	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: B
 DATABASE: Harris_SGB_1995

Sep. 23,1995 14:15

PAGE 38 of 125

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
1765.	11	113					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00014	HL
1766.							TEHTEC	B5534	rpri	A610MULC	SG20CCAL00003	CL
1767.	12	2					TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00047	HL
1768.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL
1769.	12	3					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL
1770.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL
1771.	12	4					TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00047	HL
1772.	12	5					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL
1773.	12	6					TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00047	HL
1774.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL
1775.	12	7					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL
1776.	12	8					TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00047	HL
1777.	12	9					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL
1778.	12	10					TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00047	HL
1779.	12	11					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL
1780.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL
1781.	12	12					TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00047	HL
1782.	12	13					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL
1783.	12	14					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00047	HL
1784.	12	15					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL
85.	12	16					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00047	HL
86.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL
87.	12	17					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL
1788.	12	18					TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL
1789.	12	19					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
1790.	12	20					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00042	HL
1791.	12	21					TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00042	HL
1792.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
1793.	12	22					TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00042	HL
1794.	12	23					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00042	HL
1795.	12	24					TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00042	HL
1796.	12	25					TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00042	HL
1797.	12	26					TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00042	HL
1798.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
1799.	12	27					TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00042	HL
1800.	12	28					TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00042	HL
1801.	12	29					01HTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
1802.	12	30					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
1803.	12	31					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
1804.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL
1805.	12	32					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
1806.	12	33					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
1807.	12	34					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
1808.	12	35					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
1809.	12	36					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
1810.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL
11.	12	37					TSHTSH	K6733	rsec	B620MRPC3C	SG21HCAL00005	HL
12.	12	38					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00005	HL
13.	12	39					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00005	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: B
 DATABASE: Harris_SGB_1995

Sep. 23,1995 14:15

PAGE 39 of 125

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
1814.	12	40						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00007	HL
1815.	12	41						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00007	HL
1816.								TEHTEC	user5	rpri	A610MULC	SG20CCAL00001	CL
1817.	12	42						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00007	HL
1818.	12	43						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00007	HL
1819.	12	44						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00007	HL
1820.	12	45						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00007	HL
1821.	12	46						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00007	HL
1822.								TEHTEC	user5	rpri	A610MULC	SG20CCAL00001	CL
1823.	12	47						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00007	HL
1824.	12	48						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00007	HL
1825.	12	49						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00007	HL
1826.	12	50						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00007	HL
1827.	12	51						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00007	HL
1828.								TEHTEC	user5	rpri	A610MULC	SG20CCAL00001	CL
1829.	12	52						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00007	HL
1830.	12	53						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00007	HL
1831.	12	54						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00007	HL
1832.	12	55						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00007	HL
1833.	12	56						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00007	HL
34.								TEHTEC	user5	rpri	A610MULC	SG20CCAL00001	CL
5.	12	57						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL
56.			0.68	164	MBM	1	07H 31.50	TEHTEC	D3858	reso	A610MULC	SG20CCAL00010	CL
1837.	12	58						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL
1838.	12	59						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL
1839.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00010	CL
1840.	12	60						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL
1841.	12	61						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL
1842.	12	62						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL
1843.	12	63						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL
1844.	12	64						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL
1845.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00010	CL
1846.	12	65						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL
1847.	12	66						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL
1848.	12	67						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL
1849.	12	68						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL
1850.	12	69						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL
1851.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00010	CL
1852.	12	70						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL
1853.	12	71						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL
1854.	12	72						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL
1855.	12	73						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL
1856.	12	74						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL
1857.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00010	CL
1858.	12	75						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL
1859.	12	76						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL
50:	12	77						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00019	HL
51:	12	78						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00019	HL
52:	12	79						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00019	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: B
 DATABASE: Harris_SGB_1995

Sep. 23.1995 14:15

PAGE 40 of 125

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG	
1863.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00005	CL	
1864.	12	80						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00019	HL	
1865.	12	81						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00019	HL	
1866.	12	82						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00019	HL	
1867.	12	83						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00019	HL	
1868.	12	84						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00019	HL	
1869.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00005	CL	
1870.	12	86						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00019	HL	
1871.	12	87						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00019	HL	
1872.	12	88						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00019	HL	
1873.	12	89						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00019	HL	
1874.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00005	CL	
1875.	12	90						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00019	HL	
1876.	12	91						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00019	HL	
1877.	12	92						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00019	HL	
1878.	12	93						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00019	HL	
1879.	12	94			REC				F3453	reso	B620MRPC3C	SG21HCAL00013	HL	
1880.								TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00019	HL	
1881.								TEHTEC	85534	rpri	A610MULC	SG20CCAL00003	CL	
1882.	12	95			REC				F3453	reso	B620MRPC3C	SG21HCAL00014	HL	
1883.								TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00020	HL	
1884.	12	96			REC				F3453	reso	B620MRPC3C	SG21HCAL00013	HL	
1885.								TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00019	HL	
1886.	12	97			REC				F3453	reso	B620MRPC3C	SG21HCAL00014	HL	
1887.								TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00020	HL	
1888.	12	98						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00013	HL	
1889.	12	99						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00014	HL	
1890.								TEHTEC	85534	rpri	A610MULC	SG20CCAL00003	CL	
1891.	12	100						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00013	HL	
1892.	12	101						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00014	HL	
1893.	12	102						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00013	HL	
1894.	12	103						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00014	HL	
1895.	12	104						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00013	HL	
1896.								TEHTEC	85534	rpri	A610MULC	SG20CCAL00003	CL	
1897.	12	105						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00014	HL	
1898.	12	106						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00013	HL	
1899.	12	107						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00014	HL	
1900.	12	108						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00013	HL	
1901.	12	109						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00014	HL	
1902.								TEHTEC	85534	rpri	A610MULC	SG20CCAL00003	CL	
1903.	12	110						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00013	HL	
1904.	12	111						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00014	HL	
1905.	12	112						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00013	HL	
1906.								TEHTEC	85534	rpri	A610MULC	SG20CCAL00003	CL	
1907.	12	113						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00014	HL	
1908.			12.48	181	DNT	1	09C	2.48	TEHTEC	85534	rpri	A610MULC	SG20CCAL00003	CL
1909.	13	3							TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00047	HL
1910.									TEHTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL
1911.	13	4							TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: B
 DATABASE: Harris_SGB_1995

Sep. 23, 1995 14:15

PAGE 41 of 125

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
1912.	13	5					TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00047	HL
1913.	13	6					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL
1914.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL
1915.	13	7					TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00047	HL
1916.	13	8					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL
1917.	13	9					TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00047	HL
1918.	13	10					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL
1919.	13	11					TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00047	HL
1920.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL
1921.	13	12					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL
1922.	13	13					TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00047	HL
1923.	13	14					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL
1924.	13	15					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00047	HL
1925.	13	16					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL
1926.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL
1927.	13	17					TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00047	HL
1928.	13	18					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL
1929.	13	19					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL
1930.	13	20					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00043	HL
1931.	13	21					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00050	HL
32.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
33.	13	22					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00050	HL
34.	13	23					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00043	HL
1935.	13	24					TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00043	HL
1936.	13	25					TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00043	HL
1937.	13	26					TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00043	HL
1938.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
1939.	13	27					TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00043	HL
1940.	13	28					TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00043	HL
1941.	13	29					TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL
1942.	13	30					TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL
1943.	13	31					TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL
1944.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL
1945.	13	32					TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL
1946.	13	33					TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL
1947.	13	34					TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL
1948.	13	35					TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL
1949.	13	36					TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL
1950.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL
1951.	13	37					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00006	HL
1952.	13	38					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00006	HL
1953.	13	39					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00006	HL
1954.	13	40					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00008	HL
1955.	13	41					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00008	HL
1956.							TEHTEC	user5	rpri	A610MULC	SG20CCAL00001	CL
1957.	13	42					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00008	HL
1958.	13	43					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00008	HL
1959.	13	44					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00008	HL
1960.	13	45					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00008	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: B
 DATABASE: Harris_SGB_1995

Sep. 23.1995 14:15

PAGE 42 of 125

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
1961.	13	46						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00008	HL
1962.								TEHTEC	user5	rpri	A610MULC	SG20CCAL00001	CL
1963.	13	47						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00008	HL
1964.	13	48						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00008	HL
1965.	13	49						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00008	HL
1966.	13	50						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00008	HL
1967.	13	51						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00008	HL
1968.								TEHTEC	user5	rpri	A610MULC	SG20CCAL00001	CL
1969.	13	52						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00008	HL
1970.	13	53						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00008	HL
1971.	13	54						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00008	HL
1972.	13	55						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00008	HL
1973.	13	56						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00008	HL
1974.								TEHTEC	user5	rpri	A610MULC	SG20CCAL00001	CL
1975.	13	57						TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
1976.	13	58						TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
1977.	13	59						TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
1978.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00010	CL
1979.	13	60						TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
1980.	13	61						TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
81.		0.55	165	MBM	1	05C	16.52	TEHTEC	D3858	reso	A610MULC	SG20CCAL00010	CL
?	13	62						TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
3.	13	63						TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
1984.	13	64						TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
1985.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00010	CL
1986.	13	65						TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
1987.	13	66						TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
1988.	13	67						TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
1989.		0.38	153	MBM	1	09C	29.45	TEHTEC	F7460	rsec	A610MULC	SG20CCAL00010	CL
1990.	13	68						TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
1991.	13	69						TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
1992.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00010	CL
1993.	13	70						TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
1994.	13	71						TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
1995.	13	72						TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
1996.	13	73						TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
1997.	13	74						TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
1998.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00010	CL
1999.	13	75						TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
2000.	13	76						TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
2001.	13	77						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00020	HL
2002.	13	78						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00020	HL
2003.	13	79						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00020	HL
2004.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00005	CL
2005.	13	80						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00020	HL
06.	13	81						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00020	HL
07.	13	82						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00020	HL
3.	13	83						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00020	HL
09.	13	84						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00020	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: B
 DATABASE: Harris_SGB_1995

Sep. 23,1995 14:15

PAGE 43 of 125

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
2010.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00005	CL
2011.	13	85						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00020	HL
2012.	13	86						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00020	HL
2013.	13	87						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00020	HL
2014.	13	88						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00020	HL
2015.	13	89						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00020	HL
2016.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00005	CL
2017.	13	90						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00020	HL
2018.	13	91						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00020	HL
2019.	13	92						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00020	HL
2020.	13	93						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00020	HL
2021.	13	94			REC				F3453	reso	B620MRPC3C	SG21HCAL00013	HL
2022.								TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00019	HL
2023.								TEHTEC	B5534	rpri	A610MULC	SG20CCAL00003	CL
2024.	13	95			REC				F3453	reso	B620MRPC3C	SG21HCAL00014	HL
2025.								TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00020	HL
2026.	13	96			REC				F3453	reso	B620MRPC3C	SG21HCAL00013	HL
2027.								TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00019	HL
2028.	13	97			REC				F3453	reso	B620MRPC3C	SG21HCAL00014	HL
2029.								TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00020	HL
30.	13	98						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00013	HL
1.	13	99						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00014	HL
2.								TEHTEC	B5534	rpri	A610MULC	SG20CCAL00003	CL
2033.	13	100						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00013	HL
2034.	13	101						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00014	HL
2035.	13	102						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00013	HL
2036.	13	103						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00014	HL
2037.	13	104						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00013	HL
2038.								TEHTEC	B5534	rpri	A610MULC	SG20CCAL00003	CL
2039.	13	105						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00014	HL
2040.	13	106						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00013	HL
2041.	13	107						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00014	HL
2042.	13	108						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00013	HL
2043.	13	109						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00014	HL
2044.								TEHTEC	B5534	rpri	A610MULC	SG20CCAL00003	CL
2045.	13	110						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00013	HL
2046.	13	111						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00014	HL
2047.	13	112						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00013	HL
2048.								TEHTEC	B5534	rpri	A610MULC	SG20CCAL00003	CL
2049.	14	3						TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00047	HL
2050.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL
2051.	14	4						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL
2052.	14	5						TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00047	HL
2053.	14	6						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL
2054.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL
2055.	14	7						TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00047	HL
2056.	14	8						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL
2057.	14	9						TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00047	HL
2058.	14	10						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: B
 DATABASE: Harris_SGB_1995

Sep. 23.1995 14:15

PAGE 44 of 125

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
2059.	14	11					TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00047	HL
2060.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL
2061.	14	12					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL
2062.	14	13					TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00047	HL
2063.	14	14					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL
2064.	14	15					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00047	HL
2065.	14	16					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL
2066.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL
2067.	14	17					TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00047	HL
2068.	14	18					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL
2069.	14	19					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL
2070.	14	20					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00042	HL
2071.	14	21					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00050	HL
2072.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
2073.	14	22					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00050	HL
2074.	14	23					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00042	HL
2075.	14	24					TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00042	HL
2076.	14	25					TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00042	HL
2077.	14	26					TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00042	HL
2078.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
79.	14	27					TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00042	HL
80.	14	28					TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00042	HL
81.	14	29					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
2082.	14	30					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
2083.	14	31					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
2084.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL
2085.	14	32					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
2086.	14	33					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
2087.	14	34					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
2088.	14	35					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
2089.	14	36					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
2090.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL
2091.	14	37					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00005	HL
2092.	14	38					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00005	HL
2093.	14	39					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00005	HL
2094.	14	40					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00007	HL
2095.	14	41					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00007	HL
2096.							TEHTEC	user5	rpri	A610MULC	SG20CCAL00001	CL
2097.	14	42					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00007	HL
2098.	14	43					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00007	HL
2099.	14	44					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00007	HL
2100.	14	45					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00007	HL
2101.	14	46					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00007	HL
2102.							TEHTEC	user5	rpri	A610MULC	SG20CCAL00001	CL
2103.	14	47					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00007	HL
2104.	14	48					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00007	HL
2105.	14	49					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00007	HL
2106.	14	50					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00007	HL
2107.	14	51					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00007	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: B
 DATABASE: Harris_SGB_1995

Sep. 23.1995 14:15

PAGE 45 of 125

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
2108.							TEHTEC	user5	rpri	A610MULC	SG20CCAL00001	CL
2109.	14	52					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00007	HL
2110.	14	53					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00007	HL
2111.	14	54					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00007	HL
2112.	14	55					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00007	HL
2113.	14	56					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00007	HL
2114.							TEHTEC	user5	rpri	A610MULC	SG20CCAL00001	CL
2115.	14	57					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL
2116.	14	58					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL
2117.	14	59					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL
2118.							TEHTEC	T7072	rpri	A610MULC	SG20CCAL00010	CL
2119.	14	60					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL
2120.	14	61					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL
2121.	14	62					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL
2122.	14	63					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL
2123.	14	64					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL
2124.							TEHTEC	T7072	rpri	A610MULC	SG20CCAL00010	CL
2125.	14	65					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL
2126.	14	66					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL
2127.	14	67					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL
2128.	14	68					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL
2129.	14	69					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL
2130.							TEHTEC	T7072	rpri	A610MULC	SG20CCAL00010	CL
2131.	14	70					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL
2132.	14	71					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL
2133.	14	72					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL
2134.	14	73					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL
2135.	14	74					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL
2136.							TEHTEC	T7072	rpri	A610MULC	SG20CCAL00010	CL
2137.	14	75					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL
2138.	14	76					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL
2139.	14	77					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00019	HL
2140.	14	78					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00019	HL
2141.	14	79					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00019	HL
2142.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00005	CL
2143.	14	80					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00019	HL
2144.	14	81					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00019	HL
2145.	14	82					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00019	HL
2146.	14	83					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00019	HL
2147.	14	84					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00019	HL
2148.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00005	CL
2149.	14	85					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00019	HL
2150.	14	86					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00019	HL
2151.	14	87					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00019	HL
2152.	14	88					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00019	HL
2153.	14	89					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00019	HL
2154.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00005	CL
2155.	14	90					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00019	HL
2156.	14	91					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00019	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: B
 DATABASE: Harris_SGB_1995

Sep. 23.1995 14:15

PAGE 46 of 125

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
2157.	14	92						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00019	HL
2158.	14	93						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00019	HL
2159.	14	94			REC				F3453	reso	B620MRPC3C	SG21HCAL00013	HL
2160.								TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00019	HL
2161.								TEHTEC	B5534	rpri	A610MULC	SG20CCAL00003	CL
2162.	14	95			REC				F3453	reso	B620MRPC3C	SG21HCAL00014	HL
2163.								TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00020	HL
2164.	14	96			REC				F3453	reso	B620MRPC3C	SG21HCAL00013	HL
2165.								TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00019	HL
2166.	14	97			REC				F3453	reso	B620MRPC3C	SG21HCAL00014	HL
2167.								TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00020	HL
2168.	14	98						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00013	HL
2169.	14	99						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00014	HL
2170.								TEHTEC	B5534	rpri	A610MULC	SG20CCAL00003	CL
2171.	14	100						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00013	HL
2172.	14	101						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00014	HL
2173.	14	102						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00013	HL
2174.	14	103						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00014	HL
2175.	14	104						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00013	HL
2176.								TEHTEC	B5534	rpri	A610MULC	SG20CCAL00003	CL
77.	14	105						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00014	HL
78.	14	106						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00013	HL
79.	14	107						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00014	HL
2180.	14	108						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00013	HL
2181.	14	109						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00014	HL
2182.			1.00	170	MBM	1	10H 11.30	TEHTEC	B5534	rpri	A610MULC	SG20CCAL00003	CL
2183.	14	110			RBD				05305	rpri	B620MRPC3C	SG21HCAL00013	HL
2184.								TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00019	HL
2185.	14	111						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00014	HL
2186.	14	112						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00013	HL
2187.								TEHTEC	B5534	rpri	A610MULC	SG20CCAL00003	CL
2188.	15	3						TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00047	HL
2189.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL
2190.	15	4						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL
2191.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL
2192.	15	5						TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00047	HL
2193.	15	6						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL
2194.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL
2195.	15	7						TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00047	HL
2196.	15	8						01HTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL
2197.	15	9						TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00047	HL
2198.	15	10						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL
2199.	15	11						TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00047	HL
2200.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL
2201.	15	12	1.36	85	MBM	1	TSH 3.62	TSHTSH	D4825	reso	B620MRPC3C	SG21HCAL00046	HL
2202.	15	13						TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00047	HL
2203.	15	14						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL
2204.	15	15						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00047	HL
2205.	15	16						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: B
 DATABASE: Harris_SGB_1995

Sep. 23.1995 14:15

PAGE 47 of 125

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
2206.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL
2207.	15	17						TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL
2208.	15	18						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
2209.	15	19						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL
2210.	15	20						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00043	HL
2211.	15	21						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00043	HL
2212.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
2213.	15	22						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00043	HL
2214.	15	23						TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00043	HL
2215.	15	24						TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00043	HL
2216.	15	25						TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00043	HL
2217.	15	26						TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00043	HL
2218.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
2219.	15	27						TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00043	HL
2220.	15	28						TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00043	HL
2221.	15	29						TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL
2222.	15	30						TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL
2223.	15	31						TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL
2224.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL
2225.	15	32						TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL
26.	15	33						TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL
27.	15	34						TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL
28.	15	35						TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL
2229.	15	36						TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL
2230.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL
2231.	15	37						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00006	HL
2232.	15	38						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00006	HL
2233.	15	39						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00006	HL
2234.	15	40						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00008	HL
2235.	15	41						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00008	HL
2236.								TEHTEC	user5	rpri	A610MULC	SG20CCAL00001	CL
2237.	15	42						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00008	HL
2238.	15	43						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00008	HL
2239.	15	44						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00008	HL
2240.	15	45						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00008	HL
2241.	15	46						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00008	HL
2242.								TEHTEC	user5	rpri	A610MULC	SG20CCAL00001	CL
2243.	15	47						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00008	HL
2244.	15	48						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00008	HL
2245.	15	49						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00008	HL
2246.	15	50						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00008	HL
2247.			0.70	167	MBM	1	07H 26.29	TEHTEC	user5	rpri	A610MULC	SG20CCAL00001	CL
2248.	15	51						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00008	HL
2249.								TEHTEC	user5	rpri	A610MULC	SG20CCAL00001	CL
2250.	15	52						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00020	HL
2251.	15	53						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00008	HL
2252.	15	54						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00008	HL
2253.	15	55						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00008	HL
2254.	15	56						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00008	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: B
 DATABASE: Harris_SGB_1995

Sep. 23.1995 14:15

PAGE 48 of 125

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
2255.								TEHTEC	user5	rpri	A610MULC	SG20CCAL00001	CL
2256.	15	57						TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
2257.	15	58						TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
2258.	15	59						TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
2259.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00010	CL
2260.	15	60						TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
2261.	15	61						TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
2262.	15	62						TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
2263.			0.58	151	MBM	1	03H 20.64	TEHTEC	F7460	rsec	A610MULC	SG20CCAL00010	CL
2264.			0.58	156	MBM	1	05H 30.06	TEHTEC	F7460	rsec	A610MULC	SG20CCAL00010	CL
2265.	15	63						TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
2266.	15	64						TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
2267.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00010	CL
2268.	15	65						TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
2269.	15	66						TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
2270.	15	67						TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
2271.			0.56	148	MBM	1	03C 14.60	TEHTEC	F7460	rsec	A610MULC	SG20CCAL00010	CL
2272.	15	68						TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
2273.	15	69						TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
2274.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00010	CL
2275.	15	70						TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
2276.	15	71						TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
2277.	15	72						TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
2278.	15	73						TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
2279.	15	74						TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
2280.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00010	CL
2281.	15	75						TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
2282.	15	76						TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
2283.	15	77						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00020	HL
2284.	15	78						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00020	HL
2285.	15	79						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00020	HL
2286.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00005	CL
2287.	15	80						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00020	HL
2288.			0.30	159	MBM	1	07C 5.48	TEHTEC	H1274	reso	A610MULC	SG20CCAL00005	CL
2289.	15	81						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00020	HL
2290.	15	82						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00020	HL
2291.	15	83						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00020	HL
2292.	15	84						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00020	HL
2293.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00005	CL
2294.	15	85						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00020	HL
2295.	15	86						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00020	HL
2296.	15	87						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00020	HL
2297.	15	88						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00020	HL
2298.	15	89						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00020	HL
2299.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00005	CL
2300.	15	90						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00020	HL
2301.	15	91						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00020	HL
2302.	15	92						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00020	HL
2303.	15	93						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00020	HL

*** INSPECTION FINAL REPORT LISTING ***

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: B
 DATABASE: Harris_SGB_1995

Sep. 23.1995 14:15

PAGE 49 of 125

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG	
2304.	15	94							F3453	reso	B620MRPC3C	SG21HCAL00013	HL	
2305.								TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00019	HL	
2306.								TEHTEC	B5534	rpri	A610MULC	SG20CCAL00003	CL	
2307.	15	95							F3453	reso	B620MRPC3C	SG21HCAL00014	HL	
2308.								TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00020	HL	
2309.	15	96						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00013	HL	
2310.	15	97						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00014	HL	
2311.	15	98						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00013	HL	
2312.	15	99						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00014	HL	
2313.								TEHTEC	B5534	rpri	A610MULC	SG20CCAL00003	CL	
2314.	15	100						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00013	HL	
2315.	15	101						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00014	HL	
2316.	15	102						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00013	HL	
2317.	15	103						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00014	HL	
2318.	15	104						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00013	HL	
2319.								TEHTEC	B5534	rpri	A610MULC	SG20CCAL00003	CL	
2320.	15	105						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00014	HL	
2321.	15	106						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00013	HL	
2322.	15	107						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00014	HL	
2323.	15	108						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00013	HL	
2324.	15	109						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00014	HL	
2325.								TEHTEC	B5534	rpri	A610MULC	SG20CCAL00003	CL	
2326.	15	110						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00013	HL	
2327.	15	111						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00014	HL	
2328.								TEHTEC	B5534	rpri	A610MULC	SG20CCAL00003	CL	
2329.	15	112						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00013	HL	
2330.								10CTEC	B5534	rpri	A610MULC	SG20CCAL00003	CL	
2331.		49.58	180		RES	P1	11C	-0.52	TEHTEC	T7072	rpri	A590MULC	SG20CCAL00018	CL
2332.	16	4							TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00047	HL
2333.									TEHTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL
2334.	16	5							TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL
2335.	16	6							TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00047	HL
2336.									TEHTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL
2337.	16	7							TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL
2338.									TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00047	HL
2339.	16	8							TSHTSH	D4825	reso	B620MRPC3C	SG21HCAL00046	HL
2340.									TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL
2341.									TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00047	HL
2342.	16	9							TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL
2343.	16	10							TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00047	HL
2344.	16	11							TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL
2345.									TEHTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL
2346.	16	12							TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00047	HL
2347.	16	13							TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL
2348.	16	14							TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00047	HL
2349.	16	15							TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL
2350.	16	16							TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00047	HL
2351.									TEHTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL
2352.	16	17							TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: B
 DATABASE: Harris_SGB_1995

Sep. 23,1995 14:15

PAGE 50 of 125

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
2353.	16	18					TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL
2354.	16	19					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
2355.	16	20					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00042	HL
2356.	16	21					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00042	HL
2357.							TEHTEC	F9284	rpri	A610MJLC	SG20CCAL00012	CL
2358.	16	22					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00042	HL
2359.	16	23					TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00042	HL
2360.	16	24					TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00042	HL
2361.	16	25					TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00042	HL
2362.	16	26					TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00042	HL
2363.							TEHTEC	F9284	rpri	A610MJLC	SG20CCAL00012	CL
2364.	16	27					TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00042	HL
2365.	16	28					TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00042	HL
2366.							TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00043	HL
2367.	16	29					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
2368.	16	30					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
2369.	16	31					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
2370.							TEHTEC	F9284	rpri	A610MJLC	SG20CCAL00013	CL
2371.	16	32					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
2372.	16	33					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
73.	16	34					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
74.	16	35					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
75.	16	36					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
2376.							TEHTEC	F9284	rpri	A610MJLC	SG20CCAL00013	CL
2377.	16	37					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00005	HL
2378.	16	38					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00005	HL
2379.	16	39					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00007	HL
2380.	16	40					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00007	HL
2381.	16	41					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00007	HL
2382.							TEHTEC	user5	rpri	A610MJLC	SG20CCAL00001	CL
2383.	16	42					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00007	HL
2384.	16	43					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00007	HL
2385.	16	44					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00007	HL
2386.	16	45					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00007	HL
2387.	16	46					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00007	HL
2388.							TEHTEC	user5	rpri	A610MJLC	SG20CCAL00001	CL
2389.	16	47					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00007	HL
2390.	16	48					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00007	HL
2391.	16	49					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00007	HL
2392.	16	50					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00007	HL
2393.	16	51					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00007	HL
2394.							TEHTEC	user5	rpri	A610MJLC	SG20CCAL00001	CL
2395.	16	52					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00031	HL
2396.	16	53					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00007	HL
2397.	16	54					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00007	HL
2398.	16	55					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00007	HL
2399.	16	56					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00007	HL
2400.							TEHTEC	user5	rpri	A610MJLC	SG20CCAL00001	CL
2401.	16	57					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: B
 DATABASE: Harris_SGB_1995

Sep. 23.1995 14:15

PAGE 51 of 125

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG	
2402.	16	58						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL	
2403.	16	59						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL	
2404.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00010	CL	
2405.	16	60						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL	
2406.	16	61						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL	
2407.	16	62						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL	
2408.	16	63						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL	
2409.	16	64						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL	
2410.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00010	CL	
2411.	16	65						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL	
2412.	16	66						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL	
2413.	16	67						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL	
2414.	16	68						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL	
2415.	16	69						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL	
2416.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00010	CL	
2417.	16	70						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL	
2418.	16	71						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL	
2419.	16	72						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL	
2420.			0.29	158	MBM	1	07C	5.29	TEHTEC	D3858	reso	A610MULC	SG20CCAL00010	CL
2421.	16	73						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL	
2422.	16	74						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL	
2423.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00010	CL	
2424.	16	75						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL	
2425.	16	76						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL	
2426.	16	77						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00019	HL	
2427.	16	78						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00019	HL	
2428.	16	79						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00019	HL	
2429.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00005	CL	
2430.	16	80						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00019	HL	
2431.	16	81						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00019	HL	
2432.	16	82						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00019	HL	
2433.	16	83						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00019	HL	
2434.	16	84						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00019	HL	
2435.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00005	CL	
2436.	16	85						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00019	HL	
2437.	16	86						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00019	HL	
2438.	16	87						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00019	HL	
2439.	16	88						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00019	HL	
2440.	16	89						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00019	HL	
2441.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00005	CL	
2442.	16	90						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00019	HL	
2443.	16	91						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00019	HL	
2444.	16	92						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00019	HL	
2445.	16	93						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00019	HL	
2446.	16	94			REC			F3453	reso		B620MRPC3C	SG21HCAL00013	HL	
2447.								TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00019	HL	
2448.								TEHTEC	B5534	rpri	A610MULC	SG20CCAL00003	CL	
2449.	16	95			REC			F3453	reso		B620MRPC3C	SG21HCAL00014	HL	
2450.								TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00020	HL	

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: B
 DATABASE: Harris_SGB_1995

Sep. 23.1995 14:15

PAGE 52 of 125

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
2451.	16	96					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00013	HL
2452.	16	97					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00014	HL
2453.	16	98					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00013	HL
2454.	16	99					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00014	HL
2455.							TEHTEC	85534	rpri	A610MULC	SG20CCAL00003	CL
2456.	16	100					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00013	HL
2457.	16	101					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00014	HL
2458.	16	102					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00013	HL
2459.	16	103					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00014	HL
2460.	16	104					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00013	HL
2461.							TEHTEC	85534	rpri	A610MULC	SG20CCAL00003	CL
2462.	16	105					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00014	HL
2463.	16	106					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00013	HL
2464.	16	107					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00014	HL
2465.	16	108					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00013	HL
2466.	16	109					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00014	HL
2467.							TEHTEC	85534	rpri	A610MULC	SG20CCAL00003	CL
2468.	16	110					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00013	HL
2469.	16	111					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00014	HL
2470.							TEHTEC	85534	rpri	A610MULC	SG20CCAL00003	CL
71.	17	4					TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00047	HL
72.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL
73.	17	5					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL
2474.	17	6					TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00047	HL
2475.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL
2476.	17	7					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL
2477.	17	8					TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00047	HL
2478.	17	9					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL
2479.	17	10					TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00047	HL
2480.	17	11					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL
2481.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL
2482.	17	12					TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00047	HL
2483.	17	13					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL
2484.	17	14					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00047	HL
2485.	17	15					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL
2486.	17	16					TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00047	HL
2487.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL
2488.	17	17					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL
2489.	17	18					TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL
2490.	17	19					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
2491.	17	20					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00043	HL
2492.	17	21					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00043	HL
2493.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
2494.	17	22					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00043	HL
2495.	17	23					TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00043	HL
2496.	17	24					TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00043	HL
2497.	17	25					TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00043	HL
2498.	17	26					TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00043	HL
2499.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: B
 DATABASE: Harris_SGB_1995

Sep. 23.1995 14:15

PAGE 53 of 125

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
2500.	17	27					TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00043	HL
2501.	17	28						04825	reso	B620MRPC3C	SG21HCAL00042	HL
2502.					REC			04825	reso	B620MRPC3C	SG21HCAL00043	HL
2503.					REC		TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00050	HL
2504.	17	29					TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL
2505.	17	30					TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL
2506.	17	31					TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL
2507.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL
2508.	17	32					TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL
2509.	17	33					TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL
2510.	17	34					TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL
2511.	17	35					TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL
2512.	17	36					TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL
2513.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL
2514.	17	37					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00006	HL
2515.	17	38					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00006	HL
2516.	17	39					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00008	HL
2517.	17	40					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00008	HL
2518.	17	41					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00008	HL
2519.							TEHTEC	user5	rpri	A610MULC	SG20CCAL00001	CL
20.	17	42					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00008	HL
21.	17	43					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00008	HL
22.	17	44					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00008	HL
2523.	17	45					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00008	HL
2524.	17	46					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00008	HL
2525.							TEHTEC	user5	rpri	A610MULC	SG20CCAL00001	CL
2526.	17	47					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00008	HL
2527.	17	48					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00008	HL
2528.	17	49					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00008	HL
2529.	17	50					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00008	HL
2530.	17	51					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00008	HL
2531.							TEHTEC	user5	rpri	A610MULC	SG20CCAL00001	CL
2532.	17	52					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00008	HL
2533.	17	53					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00008	HL
2534.	17	54					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00008	HL
2535.	17	55					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00008	HL
2536.	17	56					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00008	HL
2537.							TEHTEC	user5	rpri	A610MULC	SG20CCAL00001	CL
2538.	17	57					TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
2539.	17	58					TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
2540.	17	59					TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
2541.							TEHTEC	T7072	rpri	A610MULC	SG20CCAL00010	CL
2542.	17	60					TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
2543.	17	61					TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
2544.	17	62					TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
2545.	17	63					TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
2546.	17	64					TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
2547.							TEHTEC	T7072	rpri	A610MULC	SG20CCAL00010	CL
2548.	17	65					TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL

*** INSPECTION FINAL REPORT LISTING ***

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: B
 DATABASE: Harris_SGB_1995

Sep. 23.1995 14:15

PAGE 54 of 125

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
2549.	17	66						TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
2550.	17	67						TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
2551.	17	68						TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
2552.	17	69						TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
2553.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00010	CL
2554.	17	70						TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
2555.	17	71						TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
2556.	17	72						TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
2557.	17	73						TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
2558.	17	74						TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
2559.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00010	CL
2560.	17	75						TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
2561.	17	76						TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
2562.	17	77						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00020	HL
2563.	17	78	1.52	130	MBM	1	TSH 2.68	TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00020	HL
2564.	17	79						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00020	HL
2565.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00005	CL
2566.	17	80						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00020	HL
2567.	17	81						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00020	HL
2568.	17	82						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00020	HL
2569.	17	83						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00020	HL
2570.	17	84						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00020	HL
2571.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00005	CL
2572.	17	85						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00020	HL
2573.	17	86						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00020	HL
2574.	17	87						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00020	HL
2575.	17	88						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00020	HL
2576.	17	89						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00020	HL
2577.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00005	CL
2578.	17	90						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00020	HL
2579.	17	91						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00020	HL
2580.	17	92						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00020	HL
2581.	17	93						TSHTSH	D4825	reso	B620MRPC3C	SG21HCAL00020	HL
2582.	17	94							F3453	reso	B620MRPC3C	SG21HCAL00013	HL
2583.								TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00019	HL
2584.								TEHTEC	B5534	rpri	A610MULC	SG20CCAL00003	CL
2585.	17	95							F3453	reso	B620MRPC3C	SG21HCAL00014	HL
2586.								TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00020	HL
2587.	17	96						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00013	HL
2588.	17	97						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00014	HL
2589.	17	98						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00013	HL
2590.	17	99						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00014	HL
2591.								TEHTEC	B5534	rpri	A610MULC	SG20CCAL00003	CL
2592.	17	100						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00013	HL
2593.	17	101						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00014	HL
2594.	17	102						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00013	HL
2595.	17	103						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00014	HL
2596.	17	104						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00013	HL
2597.								TEHTEC	B5534	rpri	A610MULC	SG20CCAL00003	CL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: B
 DATABASE: Harris_SGB_1995

Sep. 23, 1995 14:15

PAGE 55 of 125

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
2598.	17	105					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00014	HL
2599.	17	106					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00013	HL
2600.	17	107					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00014	HL
2601.	17	108					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00013	HL
2602.	17	109					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00014	HL
2603.							TEHTEC	B5534	rpri	A610MULC	SG20CCAL00003	CL
2604.	17	110					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00013	HL
2605.	17	111					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00014	HL
2606.							TEHTEC	B5534	rpri	A610MULC	SG20CCAL00003	CL
2607.	18	4					TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00047	HL
2608.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL
2609.	18	5					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL
2610.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL
2611.	18	6					TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00047	HL
2612.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL
2613.	18	7					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL
2614.	18	8					TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00047	HL
2615.	18	9					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL
2616.	18	10					TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00047	HL
2617.	18	11					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL
18.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL
18.	18	12					TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00047	HL
18.	18	13					01HTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL
2621.	18	14					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00047	HL
2622.	18	15					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL
2623.	18	16					TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00047	HL
2624.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL
2625.	18	17					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL
2626.	18	18					TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL
2627.	18	19					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
2628.	18	20					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00042	HL
2629.	18	21					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00042	HL
2630.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
2631.	18	22					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00042	HL
2632.	18	23					TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00042	HL
2633.	18	24					TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00042	HL
2634.	18	25					01HTSH	D4825	reso	B620MRPC3C	SG21HCAL00042	HL
2635.	18	26					TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00042	HL
2636.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
2637.	18	27					TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00042	HL
2638.	18	28			REC			D4825	reso	B620MRPC3C	SG21HCAL00042	HL
2639.							TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00050	HL
2640.	18	29					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
2641.	18	30					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
2642.	18	31					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
2643.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL
2644.	18	32					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
2644.	18	33					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
2644.	18	34					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: B
 DATABASE: Harris_SGB_1995

Sep. 23,1995 14:15

PAGE 56 of 125

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE	SIZE	CAL	GROUP	LEG
2647.	18	35						TSHTSH	G1931	rpri	B620MRPC3C		SG21HCAL00044	HL	
2648.	18	36						TSHTSH	G1931	rpri	B620MRPC3C		SG21HCAL00044	HL	
2649.								TEHTEC	F9284	rpri	A610MULC		SG20CCAL00013	CL	
2650.	18	37						TSHTSH	I2393	rpri	B620MRPC3C		SG21HCAL00005	HL	
2651.	18	38						TSHTSH	I2393	rpri	B620MRPC3C		SG21HCAL00005	HL	
2652.	18	39						TSHTSH	I2393	rpri	B620MRPC3C		SG21HCAL00007	HL	
2653.	18	40						TSHTSH	I2393	rpri	B620MRPC3C		SG21HCAL00007	HL	
2654.	18	41						TSHTSH	I2393	rpri	B620MRPC3C		SG21HCAL00007	HL	
2655.								TEHTEC	user5	rpri	A610MULC		SG20CCAL00001	CL	
2656.	18	42						TSHTSH	I2393	rpri	B620MRPC3C		SG21HCAL00007	HL	
2657.	18	43						TSHTSH	I2393	rpri	B620MRPC3C		SG21HCAL00007	HL	
2658.	18	44						TSHTSH	I2393	rpri	B620MRPC3C		SG21HCAL00007	HL	
2659.	18	45						TSHTSH	I2393	rpri	B620MRPC3C		SG21HCAL00007	HL	
2660.	18	46						TSHTSH	I2393	rpri	B620MRPC3C		SG21HCAL00007	HL	
2661.								TEHTEC	user5	rpri	A610MULC		SG20CCAL00001	CL	
2662.	18	47						TSHTSH	I2393	rpri	B620MRPC3C		SG21HCAL00007	HL	
2663.	18	48						TSHTSH	I2393	rpri	B620MRPC3C		SG21HCAL00007	HL	
2664.	18	49						TSHTSH	I2393	rpri	B620MRPC3C		SG21HCAL00007	HL	
2665.	18	50						TSHTSH	I2393	rpri	B620MRPC3C		SG21HCAL00007	HL	
2666.	18	51						TSHTSH	I2393	rpri	B620MRPC3C		SG21HCAL00007	HL	
67.								TEHTEC	user5	rpri	A610MULC		SG20CCAL00001	CL	
68.	18	52						TSHTSH	I2393	rpri	B620MRPC3C		SG21HCAL00007	HL	
69.	18	53						TSHTSH	I2393	rpri	B620MRPC3C		SG21HCAL00007	HL	
2670.	18	54						TSHTSH	I2393	rpri	B620MRPC3C		SG21HCAL00007	HL	
2671.	18	55						TSHTSH	I2393	rpri	B620MRPC3C		SG21HCAL00007	HL	
2672.	18	56						TSHTSH	I2393	rpri	B620MRPC3C		SG21HCAL00007	HL	
2673.								TEHTEC	user5	rpri	A610MULC		SG20CCAL00001	CL	
2674.	18	57						TSHTSH	I2393	rpri	B620MRPC3C		SG21HCAL00038	HL	
2675.	18	58						TSHTSH	I2393	rpri	B620MRPC3C		SG21HCAL00038	HL	
2676.	18	59						TSHTSH	I2393	rpri	B620MRPC3C		SG21HCAL00038	HL	
2677.								TEHTEC	T7072	rpri	A610MULC		SG20CCAL00010	CL	
2678.	18	60						TSHTSH	I2393	rpri	B620MRPC3C		SG21HCAL00038	HL	
2679.	18	61						TSHTSH	I2393	rpri	B620MRPC3C		SG21HCAL00038	HL	
2680.	18	62						TSHTSH	I2393	rpri	B620MRPC3C		SG21HCAL00038	HL	
2681.	18	63						TSHTSH	I2393	rpri	B620MRPC3C		SG21HCAL00038	HL	
2682.	18	64						TSHTSH	I2393	rpri	B620MRPC3C		SG21HCAL00038	HL	
2683.								TEHTEC	T7072	rpri	A610MULC		SG20CCAL00010	CL	
2684.	18	65						TSHTSH	I2393	rpri	B620MRPC3C		SG21HCAL00038	HL	
2685.	18	66						TSHTSH	I2393	rpri	B620MRPC3C		SG21HCAL00038	HL	
2686.	18	67						TSHTSH	I2393	rpri	B620MRPC3C		SG21HCAL00038	HL	
2687.	18	68						TSHTSH	I2393	rpri	B620MRPC3C		SG21HCAL00038	HL	
2688.	18	69						TSHTSH	I2393	rpri	B620MRPC3C		SG21HCAL00038	HL	
2689.								TEHTEC	T7072	rpri	A610MULC		SG20CCAL00010	CL	
2690.	18	70						TSHTSH	I2393	rpri	B620MRPC3C		SG21HCAL00038	HL	
2691.	18	71						TSHTSH	I2393	rpri	B620MRPC3C		SG21HCAL00038	HL	
2692.	18	72						TSHTSH	I2393	rpri	B620MRPC3C		SG21HCAL00038	HL	
2693.	18	73						TSHTSH	I2393	rpri	B620MRPC3C		SG21HCAL00038	HL	
2694.	18	74						TSHTSH	I2393	rpri	B620MRPC3C		SG21HCAL00038	HL	
2695.								TEHTEC	T7072	rpri	A610MULC		SG20CCAL00010	CL	

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: B
 DATABASE: Harris_SGB_1995

Sep. 23,1995 14:15

PAGE 57 of 125

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
2696.	18	75					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL
2697.	18	76					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL
2698.	18	77					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00019	HL
2699.	18	78					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00019	HL
2700.	18	79					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00019	HL
2701.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00005	CL
2702.	18	80					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00019	HL
2703.	18	81					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00019	HL
2704.	18	82					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00019	HL
2705.	18	83					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00019	HL
2706.	18	84					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00019	HL
2707.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00005	CL
2708.	18	85					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00019	HL
2709.	18	86					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00019	HL
2710.	18	87					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00019	HL
2711.	18	88					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00019	HL
2712.	18	89					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00019	HL
2713.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00005	CL
2714.	18	90					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00019	HL
2715.	18	91					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00019	HL
16.	18	92					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00019	HL
17.	18	93					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00019	HL
13.	18	94			REC			F3453	reso	B620MRPC3C	SG21HCAL00013	HL
2719.							TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00019	HL
2720.							TEHTEC	B5534	rpri	A610MULC	SG20CCAL00003	CL
2721.	18	95			REC			F3453	reso	B620MRPC3C	SG21HCAL00014	HL
2722.							TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00020	HL
2723.	18	96					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00013	HL
2724.	18	97					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00014	HL
2725.	18	98					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00013	HL
2726.	18	99					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00014	HL
2727.							TEHTEC	B5534	rpri	A610MULC	SG20CCAL00003	CL
2728.	18	100					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00013	HL
2729.	18	101					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00014	HL
2730.	18	102					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00013	HL
2731.	18	103					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00014	HL
2732.	18	104					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00013	HL
2733.							TEHTEC	B5534	rpri	A610MULC	SG20CCAL00003	CL
2734.							TEHTEC	B5534	rpri	A610MULC	SG20CCAL00003	CL
2735.	18	105					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00014	HL
2736.	18	106					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00013	HL
2737.	18	107					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00014	HL
2738.	18	108					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00013	HL
2739.	18	109					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00014	HL
2740.							TEHTEC	B5534	rpri	A610MULC	SG20CCAL00003	CL
141.	18	110					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00013	HL
142.							TEHTEC	B5534	rpri	A610MULC	SG20CCAL00003	CL
143.	18	111					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00014	HL
144.							TEHTEC	B5534	rpri	A610MULC	SG20CCAL00003	CL

*** INSPECTION FINAL REPORT LISTING ***

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: B
 DATABASE: Harris_SGB_1995

Sep. 23,1995 14:15

PAGE 58 of 125

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
2745.	19	5					TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00047	HL
2746.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL
2747.	19	6					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL
2748.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL
2749.	19	7					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00052	HL
2750.	19	8					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00052	HL
2751.	19	9					TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00047	HL
2752.	19	10					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL
2753.	19	11					TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00047	HL
2754.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL
2755.	19	12					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL
2756.	19	13					TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00047	HL
2757.	19	14					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL
2758.	19	15					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00047	HL
2759.	19	16					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL
2760.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL
2761.	19	17					TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL
2762.	19	18					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
2763.	19	19					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL
2764.	19	20					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00043	HL
65.	19	21					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00043	HL
66.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
67.	19	22					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00043	HL
2768.	19	23					TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00043	HL
2769.	19	24					TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00043	HL
2770.	19	25					TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00043	HL
2771.	19	26					TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00043	HL
2772.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
2773.	19	27					TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00043	HL
2774.	19	28					TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL
2775.	19	29					TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL
2776.	19	30					TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL
2777.	19	31					TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL
2778.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL
2779.	19	32					TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL
2780.	19	33					TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL
2781.	19	34					TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL
2782.	19	35					TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL
2783.	19	36					TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL
2784.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL
2785.	19	37					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00006	HL
2786.	19	38					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00006	HL
2787.	19	39					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00008	HL
2788.	19	40					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00008	HL
2789.	19	41					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00008	HL
2790.							TEHTEC	user5	rpri	A610MULC	SG20CCAL00001	CL
91.	19	42					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00008	HL
92.	19	43					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00008	HL
93.	19	44					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00008	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: B
 DATABASE: Harris_SGB_1995

Sep. 23.1995 14:15

PAGE 59 of 125

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
2794.	19	45					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00008	HL
2795.	19	46					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00008	HL
2796.							TEHTEC	user5	rpri	A610MULC	SG20CCAL00001	CL
2797.	19	47					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00008	HL
2798.	19	48					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00008	HL
2799.	19	49					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00008	HL
2800.	19	50					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00008	HL
2801.	19	51					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00008	HL
2802.							TEHTEC	user5	rpri	A610MULC	SG20CCAL00001	CL
2803.	19	52					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00008	HL
2804.	19	53					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00008	HL
2805.	19	54					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00008	HL
2806.	19	55					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00008	HL
2807.	19	56					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00008	HL
2808.							TEHTEC	user5	rpri	A610MULC	SG20CCAL00001	CL
2809.	19	57					TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
2810.	19	58					TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
2811.	19	59					TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
2812.							TEHTEC	T7072	rpri	A610MULC	SG20CCAL00010	CL
2813.	19	60					TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
14.	19	61					TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
15.	19	62					TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
16.	19	63					TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
2817.	19	64					TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
2818.							TEHTEC	T7072	rpri	A610MULC	SG20CCAL00010	CL
2819.	19	65					TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
2820.	19	66					TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
2821.	19	67					TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
2822.	19	68					TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
2823.	19	69					TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
2824.							TEHTEC	T7072	rpri	A610MULC	SG20CCAL00010	CL
2825.	19	70					TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
2826.	19	71					TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
2827.	19	72					TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
2828.	19	73					TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
2829.	19	74					TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
2830.							TEHTEC	T7072	rpri	A610MULC	SG20CCAL00010	CL
2831.	19	75					TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
2832.	19	76					TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00039	HL
2833.	19	77					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00020	HL
2834.	19	78					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00020	HL
2835.	19	79					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00020	HL
2836.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00005	CL
2837.	19	80					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00020	HL
2838.	19	81					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00020	HL
2839.	19	82					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00020	HL
40.	19	83					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00020	HL
41.	19	84					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00020	HL
42.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00005	CL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: B
 DATABASE: Harris_SGB_1995

Sep. 23, 1995 14:15

PAGE 60 of 125

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
2843.	19	85						TSHTSH	D4825	reso	B620MRPC3C	SG21HCAL00020	HL
2844.	19	86						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00020	HL
2845.			0.56	169	MBM	1	10C 26.40	TEHTEC	F9284	rpri	A610MULC	SG20CCAL00005	CL
2846.	19	87						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00020	HL
2847.	19	88						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00020	HL
2848.	19	89						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00020	HL
2849.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00005	CL
2850.	19	90						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00020	HL
2851.	19	91						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00020	HL
2852.	19	92						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00020	HL
2853.	19	93						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00020	HL
2854.	19	94			REC				F3453	reso	B620MRPC3C	SG21HCAL00013	HL
2855.								TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00019	HL
2856.								TEHTEC	B5534	rpri	A610MULC	SG20CCAL00003	CL
2857.	19	95			REC				F3453	reso	B620MRPC3C	SG21HCAL00014	HL
2858.								TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00020	HL
2859.	19	96						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00013	HL
2860.	19	97						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00014	HL
2861.	19	98						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00013	HL
2862.	19	99						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00014	HL
.63.								TEHTEC	B5534	rpri	A610MULC	SG20CCAL00003	CL
.	19	100						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00013	HL
.5.	19	101						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00014	HL
2866.	19	102						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00013	HL
2867.	19	103						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00014	HL
2868.	19	104						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00013	HL
2869.								TEHTEC	B5534	rpri	A610MULC	SG20CCAL00003	CL
2870.								TEHTEC	B5534	rpri	A610MULC	SG20CCAL00003	CL
2871.	19	105						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00014	HL
2872.	19	106						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00013	HL
2873.	19	107						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00014	HL
2874.	19	108						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00013	HL
2875.	19	109						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00014	HL
2876.								TEHTEC	B5534	rpri	A610MULC	SG20CCAL00003	CL
2877.	19	110						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00013	HL
2878.								TEHTEC	B5534	rpri	A610MULC	SG20CCAL00003	CL
2879.	20	5						TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00047	HL
2880.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL
2881.	20	6						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL
2882.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL
2883.	20	7						TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00047	HL
2884.	20	8						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL
2885.	20	9						TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00047	HL
2886.	20	10						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL
2887.	20	11						TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00047	HL
288.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL
289.	20	12						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL
.	20	13						TSHTSH	C7651	rsec	B620MRPC3C	SG21HCAL00047	HL
91.	20	14						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: B
 DATABASE: Harris_SGB_1995

Sep. 23,1995 14:15

PAGE 61 of 125

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
2892.	20	15					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00047.	HL
2893.	20	16					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL
2894.							TEHTEC	F9284	rpri	A610MJLC	SG20CCAL00013	CL
2895.	20	17					01HTSH	C7651	rsec	B620MRPC3C	SG21HCAL00045	HL
2896.	20	18					01HTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
2897.	20	19					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL
2898.	20	20					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00042	HL
2899.	20	21					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00042	HL
2900.							TEHTEC	F9284	rpri	A610MJLC	SG20CCAL00012	CL
2901.	20	22					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00042	HL
2902.	20	23					TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00042	HL
2903.	20	24					TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00042	HL
2904.	20	25					TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00042	HL
2905.	20	26					TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00042	HL
2906.							TEHTEC	F9284	rpri	A610MJLC	SG20CCAL00013	CL
2907.	20	27					TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00042	HL
2908.	20	28					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
2909.	20	29					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
2910.	20	30					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
2911.	20	31					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
12.							TEHTEC	F9284	rpri	A610MJLC	SG20CCAL00013	CL
13.	20	32					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
14.	20	33					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
2915.	20	34					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
2916.	20	35					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
2917.	20	36					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
2918.							TEHTEC	F9284	rpri	A610MJLC	SG20CCAL00013	CL
2919.	20	37					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00005	HL
2920.	20	38					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00005	HL
2921.	20	39					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00007	HL
2922.	20	40					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00007	HL
2923.	20	41					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00007	HL
2924.							TEHTEC	user5	rpri	A610MJLC	SG20CCAL00001	CL
2925.	20	42					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00007	HL
2926.	20	43					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00007	HL
2927.	20	44					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00007	HL
2928.	20	45					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00007	HL
2929.	20	46					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00007	HL
2930.							TEHTEC	user5	rpri	A610MJLC	SG20CCAL00001	CL
2931.	20	47					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00007	HL
2932.	20	48					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00007	HL
2933.	20	49					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00007	HL
2934.	20	50					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00007	HL
2935.	20	51					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00007	HL
2936.							TEHTEC	user5	rpri	A610MJLC	SG20CCAL00001	CL
37.	20	52					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00007	HL
38.	20	53					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00007	HL
39.	20	54					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00007	HL
40.	20	55					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00007	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: B
 DATABASE: Harris_SGB_1995

Sep. 23.1995 14:15

PAGE 62 of 125

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
2941.	20	56						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00007	HL
2942.								TEHTEC	user5	rpri	A610MULC	SG20CCAL00001	CL
2943.	20	57						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL
2944.	20	58						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL
2945.	20	59						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL
2946.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00010	CL
2947.	20	60						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL
2948.	20	61						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL
2949.	20	62						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL
2950.	20	63						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL
2951.	20	64						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL
2952.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00017	CL
2953.								01HTEC	T7072	rpri	A610MULC	SG20CCAL00010	CL
2954.	20	65						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL
2955.	20	66						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL
2956.	20	67						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL
2957.	20	68						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL
2958.	20	69						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL
2959.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00010	CL
2960.	20	70						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL
61.	20	71						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL
2962.	20	72						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL
2963.	20	73						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL
2964.	20	74						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL
2965.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00010	CL
2966.	20	75						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL
2967.	20	76						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00038	HL
2968.	20	77						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00019	HL
2969.	20	78						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00019	HL
2970.	20	79						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00019	HL
2971.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00005	CL
2972.	20	80						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00019	HL
2973.	20	81						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00019	HL
2974.	20	82						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00019	HL
2975.	20	83						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00019	HL
2976.	20	84						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00019	HL
2977.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00005	CL
2978.	20	85						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00019	HL
2979.	20	86						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00019	HL
2980.	20	87						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00019	HL
2981.	20	88						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00019	HL
2982.	20	89						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00019	HL
2983.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00005	CL
2984.	20	90						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00019	HL
2985.	20	91						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00019	HL
2986.	20	92						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00019	HL
2987.	20	93						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00019	HL
2988.	20	94				REC			F3453	reso	B620MRPC3C	SG21HCAL00013	HL
2989.								TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00019	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: B
 DATABASE: Harris_SGB_1995

Sep. 23.1995 14:15

PAGE 63 of 125

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
2990.							TEHTEC	B5534	rpri	A610MULC	SG20CCAL00003	CL
2991.	20	95			REC			F3453	reso	B620MRPC3C	SG21HCAL00014	HL
2992.							TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00020	HL
2993.	20	96					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00013	HL
2994.	20	97					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00014	HL
2995.	20	98					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00013	HL
2996.	20	99					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00014	HL
2997.							TEHTEC	B5534	rpri	A610MULC	SG20CCAL00003	CL
2998.	20	100					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00013	HL
2999.	20	101					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00014	HL
3000.	20	102					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00013	HL
3001.	20	103					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00014	HL
3002.	20	104					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00013	HL
3003.							TEHTEC	B5534	rpri	A610MULC	SG20CCAL00003	CL
3004.							TEHTEC	B5534	rpri	A610MULC	SG20CCAL00003	CL
3005.	20	105					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00014	HL
3006.	20	106					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00013	HL
3007.	20	107					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00014	HL
3008.	20	108					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00013	HL
3009.	20	109					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00014	HL
10.							TEHTEC	B5534	rpri	A610MULC	SG20CCAL00003	CL
11.	20	110					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00013	HL
12.							TEHTEC	B5534	rpri	A610MULC	SG20CCAL00003	CL
3013.	21	5					TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00047	HL
3014.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL
3015.	21	6					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL
3016.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL
3017.	21	7					TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00047	HL
3018.	21	8					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL
3019.	21	9					TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00047	HL
3020.	21	10					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL
3021.	21	11					TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00047	HL
3022.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL
3023.	21	12					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL
3024.	21	13					TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00047	HL
3025.	21	14					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL
3026.	21	15					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00047	HL
3027.	21	16					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL
3028.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL
3029.	21	17					TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL
3030.	21	18					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
3031.	21	19					01HTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL
3032.	21	20					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00043	HL
3033.	21	21					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00043	HL
3034.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
3035.	21	22					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00043	HL
3036.	21	23					TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00043	HL
3037.	21	24					TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00043	HL
3038.	21	25					TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00043	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: B
 DATABASE: Harris_SGB_1995

Sep. 23,1995 14:15

PAGE 64 of 125

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
3039.	21	26						TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00043	HL
3040.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL
3041.	21	27						TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00043	HL
3042.	21	28						TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL
3043.	21	29						TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL
3044.	21	30						TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL
3045.	21	31						TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL
3046.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL
3047.	21	32						TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL
3048.	21	33						TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL
3049.	21	34						TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL
3050.	21	35						TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL
3051.	21	36						TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL
3052.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL
3053.	21	37						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00004	HL
3054.	21	38						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00003	HL
3055.	21	39						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00004	HL
3056.	21	40						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00003	HL
3057.	21	41						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00004	HL
3058.								TEHTEC	user5	rpri	A610MULC	SG20CCAL00001	CL
59.	21	42						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00003	HL
60.	21	43						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00004	HL
61.	21	44						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00003	HL
3062.	21	45						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00004	HL
3063.	21	46						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00003	HL
3064.								TEHTEC	user5	rpri	A610MULC	SG20CCAL00001	CL
3065.	21	47						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00004	HL
3066.	21	48						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00003	HL
3067.	21	49						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00004	HL
3068.	21	50						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00003	HL
3069.	21	51						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00004	HL
3070.								TEHTEC	user5	rpri	A610MULC	SG20CCAL00001	CL
3071.	21	52						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00003	HL
3072.	21	53						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00004	HL
3073.	21	54						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00003	HL
3074.	21	55						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00004	HL
3075.	21	56						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00003	HL
3076.								TEHTEC	user5	rpri	A610MULC	SG20CCAL00001	CL
3077.	21	57						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00036	HL
3078.	21	58						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00036	HL
3079.	21	59						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00036	HL
3080.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00010	CL
3081.	21	60						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00036	HL
3082.	21	61						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00036	HL
3083.	21	62						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00036	HL
3084.	21	63						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00036	HL
3085.	21	64						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00036	HL
3086.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00010	CL
3087.	21	65						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00036	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: B
 DATABASE: Harris_SGB_1995

Sep. 23.1995 14:15

PAGE 65 of 125

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
3088.	21	66						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00036	HL
3089.	21	67						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00037	HL
3090.	21	68						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00036	HL
3091.	21	69						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00037	HL
3092.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00010	CL
3093.	21	70						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00036	HL
3094.	21	71						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00037	HL
3095.	21	72						TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00036	HL
3096.				INR	1	02C	12.45	TEHTEC	B3052	reso	A610MULC	SG20CCAL00010	CL
3097.	21	73						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00037	HL
3098.	21	74						TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00036	HL
3099.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00010	CL
3100.	21	75						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00037	HL
3101.	21	76						TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00036	HL
3102.	21	77						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00037	HL
3103.	21	78						TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00036	HL
3104.	21	79						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00037	HL
3105.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00010	CL
3106.	21	80						TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00036	HL
3107.	21	81						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00037	HL
08.	21	82						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL
09.	21	83						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
10.	21	84						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL
3111.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00004	CL
3112.	21	85						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
3113.	21	86						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL
3114.	21	87						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
3115.	21	88						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL
3116.	21	89						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
3117.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00004	CL
3118.	21	90						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL
3119.	21	91						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
3120.	21	92						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
3121.	21	93						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
3122.	21	94						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00015	HL
3123.								TEHTEC	B5534	rpri	A610MULC	SG20CCAL00003	CL
3124.	21	95						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00016	HL
3125.	21	96						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00015	HL
3126.	21	97						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00016	HL
3127.	21	98						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00015	HL
3128.	21	99						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00016	HL
3129.								TEHTEC	B5534	rpri	A610MULC	SG20CCAL00003	CL
3130.	21	100						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00015	HL
3131.	21	101						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00016	HL
3132.	21	102						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00015	HL
3133.	21	103						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00016	HL
34.	21	104						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00015	HL
5.								TEHTEC	B5534	rpri	A610MULC	SG20CCAL00003	CL
6.	21	105						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00016	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: B
 DATABASE: Harris_SGB_1995

Sep. 23.1995 14:15

PAGE 66 of 125

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
3137.	21	106					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00015	HL
3138.	21	107					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00016	HL
3139.	21	108					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00015	HL
3140.	21	109					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00016	HL
3141.							TEHTEC	B5534	rpri	A610MULC	SG20CCAL00003	CL
3142.	21	110					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00015	HL
3143.							TEHTEC	B5534	rpri	A610MULC	SG20CCAL00003	CL
3144.	22	6					TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00047	HL
3145.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL
3146.	22	7					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL
3147.	22	8					TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00047	HL
3148.	22	9					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL
3149.	22	10					TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00047	HL
3150.	22	11					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL
3151.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL
3152.	22	12					TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00047	HL
3153.	22	13					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL
3154.	22	14					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00047	HL
3155.	22	15					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL
3156.	22	16					TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00047	HL
57.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL
58.	22	17					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00046	HL
59.	22	18					TSHTSH	S7067	rpri	B620MRPC3C	SG21HCAL00045	HL
3160.	22	19					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
3161.	22	20					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00042	HL
3162.	22	21					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00042	HL
3163.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
3164.	22	22					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00042	HL
3165.	22	23					TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00042	HL
3166.	22	24					TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00042	HL
3167.	22	25					TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00042	HL
3168.	22	26					TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00042	HL
3169.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL
3170.	22	27					TSHTSH	P4202	rpri	B620MRPC3C	SG21HCAL00042	HL
3171.	22	28					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
3172.	22	29					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
3173.	22	30					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
3174.	22	31					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
3175.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL
3176.	22	32					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
3177.	22	33					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
3178.	22	34					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
3179.	22	35					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
3180.	22	36					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00044	HL
3181.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00013	CL
3182.	22	37					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00020	HL
3183.	22	38					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00003	HL
3184.	22	39					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00004	HL
3185.	22	40					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00003	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: B
 DATABASE: Harris_SGB_1995

Sep. 23.1995 14:15

PAGE 67 of 125

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
3186.	22	41						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00004	HL
3187.								TEHTEC	user5	rpri	A610MULC	SG20CCAL00001	CL
3188.	22	42						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00003	HL
3189.	22	43						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00004	HL
3190.	22	44						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00003	HL
3191.	22	45						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00003	HL
3192.	22	70						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00036	HL
3193.	22	71						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00037	HL
3194.	22	72						TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00036	HL
3195.	22	73						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00037	HL
3196.	22	74						TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00036	HL
3197.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00010	CL
3198.	22	75						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00037	HL
3199.	22	76						TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00036	HL
3200.	22	77						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00037	HL
3201.	22	78						TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00036	HL
3202.	22	79						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00037	HL
3203.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00010	CL
3204.	22	80						TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00036	HL
3205.	22	81						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00037	HL
06.	22	82						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL
07.	22	83						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
08.	22	84						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL
3209.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00004	CL
3210.	22	85						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
3211.	22	86						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL
3212.	22	87						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
3213.	22	88						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL
3214.	22	89						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
3215.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00004	CL
3216.	22	90						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL
3217.	22	91						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
3218.	22	92						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
3219.	22	93						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
3220.	22	94						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00015	HL
3221.								TEHTEC	B5534	rpri	A610MULC	SG20CCAL00003	CL
3222.	22	95						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00016	HL
3223.	22	96						TSHTSH	M9082	rsec	B620MRPC3C	SG21HCAL00015	HL
3224.	22	97						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00016	HL
3225.	22	98						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00015	HL
3226.	22	99						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00016	HL
3227.								TEHTEC	B5534	rpri	A610MULC	SG20CCAL00003	CL
3228.	22	100						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00015	HL
3229.	22	101						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00016	HL
3230.	22	102						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00015	HL
3231.	22	103						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00016	HL
3232.	22	104						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00015	HL
3233.								TEHTEC	B5534	rpri	A610MULC	SG20CCAL00003	CL
3234.	22	105						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00016	HL

*** INSPECTION FINAL REPORT LISTING ***

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: B
 DATABASE: Harris_SGB_1995

Sep. 23.1995 14:15

PAGE 68 of 125

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
3235.	22	106					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00015	HL
3236.	22	107					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00016	HL
3237.	22	108					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00015	HL
3238.	22	109					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00016	HL
3239.							TEHTEC	85534	rpri	A610MULC	SG20CCAL00003	CL
3240.	23	6					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
3241.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
3242.	23	7					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00040	HL
3243.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
3244.	23	8					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
3245.	23	9					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
3246.	23	10					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
3247.	23	11					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
3248.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
3249.	23	12					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
3250.	23	13					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
3251.	23	14					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
3252.	23	15					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
3253.	23	16					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
3254.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
55.	23	17					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
56.	23	18					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
57.	23	19					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
3258.	23	20					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00042	HL
3259.	23	21					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00043	HL
3260.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
3261.	23	22					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00043	HL
3262.	23	23					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00042	HL
3263.	23	24					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00043	HL
3264.	23	25					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00042	HL
3265.	23	26					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00043	HL
3266.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
3267.	23	27					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00042	HL
3268.	23	28					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00035	HL
3269.	23	29					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00034	HL
3270.	23	30					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00035	HL
3271.	23	31					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00034	HL
3272.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
3273.	23	32					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00035	HL
3274.	23	33					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00034	HL
3275.	23	34					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00035	HL
3276.	23	35					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00034	HL
3277.	23	36					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00034	HL
3278.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
3279.	23	37					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00004	HL
3280.	23	38					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00003	HL
3281.	23	39					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00004	HL
3282.	23	40					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00003	HL
3283.	23	41					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00004	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: B
 DATABASE: Harris_SGB_1995

Sep. 23.1995 14:15

PAGE 69 of 125

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
3284.								TEHTEC	user5	rpri	A610MULC	SG20CCAL00001	CL
3285.	23	42						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00003	HL
3286.	23	43						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00004	HL
3287.	23	44						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00003	HL
3288.	23	45						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00003	HL
3289.	23	70						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00036	HL
3290.	23	71						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00037	HL
3291.	23	72						TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00036	HL
3292.	23	73						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00037	HL
3293.	23	74						TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00036	HL
3294.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00010	CL
3295.	23	75						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00037	HL
3296.	23	76						TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00036	HL
3297.	23	77						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00037	HL
3298.	23	78						TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00036	HL
3299.	23	79						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00037	HL
3300.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00010	CL
3301.	23	80						TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00036	HL
3302.	23	81						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00037	HL
3303.	23	82						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL
04.	23	83						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
05.	23	84						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL
06.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00004	CL
3307.	23	85						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
3308.	23	86						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL
3309.	23	87						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
3310.	23	88						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL
3311.	23	89						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
3312.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00004	CL
3313.	23	90						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL
3314.	23	91						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
3315.	23	92						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
3316.	23	93						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
3317.	23	94						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00015	HL
3318.								TEHTEC	B5534	rpri	A610MULC	SG20CCAL00003	CL
3319.	23	95						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00016	HL
3320.	23	96						TSHTSH	M9082	rsec	B620MRPC3C	SG21HCAL00015	HL
3321.	23	97						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00016	HL
3322.	23	98						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00015	HL
3323.	23	99						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00016	HL
3324.								TEHTEC	B5534	rpri	A610MULC	SG20CCAL00003	CL
3325.	23	100						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00015	HL
3326.	23	101						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00016	HL
3327.	23	102						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00015	HL
3328.	23	103						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00016	HL
3329.	23	104						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00015	HL
30.								TEHTEC	B5534	rpri	A610MULC	SG20CCAL00003	CL
31.	23	105						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00016	HL
32.	23	106						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00015	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: B
 DATABASE: Harris_SGB_1995

Sep. 23.1995 14:15

PAGE 70 of 125

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
3333.	23	107					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00016	HL
3334.	23	108					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00015	HL
3335.							TEHTEC	B5534	rpri	A610MULC	SG20CCAL00003	CL
3336.	23	109					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00016	HL
3337.							TEHTEC	B5534	rpri	A610MULC	SG20CCAL00003	CL
3338.	24	7					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
3339.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
3340.	24	8					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00040	HL
3341.	24	9					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
3342.	24	10					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
3343.	24	11					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
3344.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
3345.	24	12					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
3346.	24	13					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
3347.	24	14					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
3348.	24	15					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
3349.	24	16					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
3350.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
3351.	24	17					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
3352.	24	18					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
53.	24	19					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00043	HL
54.	24	20					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00042	HL
55.	24	21					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00043	HL
3356.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
3357.	24	22					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00042	HL
3358.	24	23					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00043	HL
3359.	24	24					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00042	HL
3360.	24	25					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00043	HL
3361.	24	26					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00042	HL
3362.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
3363.	24	27					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00035	HL
3364.	24	28					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00034	HL
3365.	24	29					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00035	HL
3366.	24	30					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00034	HL
3367.	24	31					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00035	HL
3368.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
3369.	24	32					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00034	HL
3370.	24	33					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00035	HL
3371.	24	34					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00034	HL
3372.	24	35					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00035	HL
3373.	24	36					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00034	HL
3374.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
3375.	24	37					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00004	HL
3376.	24	38					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00003	HL
3377.	24	39					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00004	HL
3378.	24	40					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00003	HL
3379.	24	41					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00004	HL
							TEHTEC	user5	rpri	A610MULC	SG20CCAL00001	CL
3380.	24	42					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00003	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: B
 DATABASE: Harris_SGB_1995

Sep. 23.1995 14:15

PAGE 71 of 125

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
3382.	24	43					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00004	HL
3383.	24	44					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00003	HL
3384.	24	45					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00004	HL
3385.	24	46					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00003	HL
3386.							TEHTEC	user5	rpri	A610MULC	SG20CCAL00001	CL
3387.	24	47					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00004	HL
3388.	24	48					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00003	HL
3389.	24	49					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00004	HL
3390.	24	50					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00003	HL
3391.	24	51					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00004	HL
3392.							TEHTEC	user5	rpri	A610MULC	SG20CCAL00001	CL
3393.	24	52					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00003	HL
3394.	24	53					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00004	HL
3395.	24	54					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00003	HL
3396.	24	55					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00003	HL
3397.	24	60					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00037	HL
3398.	24	61					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00037	HL
3399.	24	62					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00037	HL
3400.	24	63					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00037	HL
3401.	24	64					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00037	HL
02.							TEHTEC	T7072	rpri	A610MULC	SG20CCAL00010	CL
03.	24	65					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00037	HL
04.	24	66					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00036	HL
3405.	24	67					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00037	HL
3406.	24	68					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00036	HL
3407.	24	69					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00037	HL
3408.							TEHTEC	T7072	rpri	A610MULC	SG20CCAL00010	CL
3409.	24	70					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00036	HL
3410.	24	71					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00037	HL
3411.	24	72					TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00036	HL
3412.	24	73					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00037	HL
3413.	24	74					TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00036	HL
3414.							TEHTEC	T7072	rpri	A610MULC	SG20CCAL00010	CL
3415.	24	75					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00037	HL
3416.	24	76					TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00036	HL
3417.	24	77					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00037	HL
3418.	24	78					TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00036	HL
3419.	24	79					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00037	HL
3420.							TEHTEC	T7072	rpri	A610MULC	SG20CCAL00010	CL
3421.	24	80					TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00036	HL
3422.	24	81					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00037	HL
3423.	24	82					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL
3424.	24	83					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
3425.	24	84					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL
3426.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00004	CL
27.	24	85					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
28.	24	86					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL
29.	24	87					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
30.	24	88					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: B
 DATABASE: Harris_SGB_1995

Sep. 23, 1995 14:15

PAGE 72 of 125

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
3431.	24	89					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
3432.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00004	CL
3433.	24	90					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL
3434.	24	91					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
3435.	24	92					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
3436.	24	93					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
3437.	24	94					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00015	HL
3438.							TEHTEC	B5534	rpri	A610MULC	SG20CCAL00003	CL
3439.	24	95					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00016	HL
3440.	24	96					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00015	HL
3441.	24	97					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00016	HL
3442.	24	98					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00015	HL
3443.	24	99					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00016	HL
3444.							TEHTEC	B5534	rpri	A610MULC	SG20CCAL00003	CL
3445.	24	100					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00015	HL
3446.	24	101					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00016	HL
3447.	24	102					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00015	HL
3448.	24	103					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00016	HL
3449.	24	104					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00015	HL
3450.							TEHTEC	B5534	rpri	A610MULC	SG20CCAL00003	CL
51.	24	105					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00016	HL
52.	24	106					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00015	HL
53.	24	107					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00016	HL
3454.	24	108					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00015	HL
3455.							TEHTEC	B5534	rpri	A610MULC	SG20CCAL00003	CL
3456.	25	7					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
3457.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
3458.	25	8					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
3459.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
3460.	25	9					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
3461.	25	10					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
3462.	25	11					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
3463.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
3464.	25	12					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
3465.	25	13					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
3466.	25	14					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
3467.	25	15					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
3468.	25	16					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
3469.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
3470.	25	17					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
3471.	25	18					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
3472.	25	19					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00043	HL
3473.	25	20					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00042	HL
3474.	25	21					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00043	HL
3475.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
3476.	25	22					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00042	HL
3477.	25	23					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00043	HL
3478.	25	24					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00042	HL
3479.	25	25					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00043	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: B
 DATABASE: Harris_SGB_1995

Sep. 23.1995 14:15

PAGE 73 of 125

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
3480.	25	26					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00042	HL
3481.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
3482.	25	27					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00035	HL
3483.	25	28					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00034	HL
3484.	25	29					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00035	HL
3485.	25	30					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00034	HL
3486.	25	31					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00035	HL
3487.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
3488.	25	32					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00034	HL
3489.	25	33					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00035	HL
3490.	25	34					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00034	HL
3491.	25	35					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00035	HL
3492.	25	36					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00034	HL
3493.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
3494.	25	37					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00004	HL
3495.	25	38					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00003	HL
3496.	25	39					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00004	HL
3497.	25	40					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00003	HL
3498.	25	41					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00004	HL
3499.							TEHTEC	user5	rpri	A610MULC	SG20CCAL00001	CL
00.	25	42					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00003	HL
01.	25	43					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00004	HL
02.	25	44					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00003	HL
3503.	25	45					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00004	HL
3504.	25	46					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00003	HL
3505.							TEHTEC	user5	rpri	A610MULC	SG20CCAL00001	CL
3506.	25	47					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00004	HL
3507.	25	48					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00003	HL
3508.	25	49					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00004	HL
3509.	25	50					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00003	HL
3510.	25	51					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00004	HL
3511.							TEHTEC	user5	rpri	A610MULC	SG20CCAL00001	CL
3512.	25	52					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00003	HL
3513.	25	53					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00004	HL
3514.	25	54					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00003	HL
3515.	25	55					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00004	HL
3516.	25	56					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00003	HL
3517.							TEHTEC	user5	rpri	A610MULC	SG20CCAL00001	CL
3518.	25	59					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00037	HL
3519.							TEHTEC	T7072	rpri	A610MULC	SG20CCAL00010	CL
3520.	25	60					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00036	HL
3521.	25	61					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00036	HL
3522.	25	62					TSHTSH	F3325	rsec	B620MRPC3C	SG21HCAL00036	HL
3523.	25	63					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00036	HL
3524.	25	64					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00036	HL
3525.							TEHTEC	T7072	rpri	A610MULC	SG20CCAL00010	CL
3526.	25	65					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00036	HL
3527.	25	66					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00036	HL
3528.	25	67					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00037	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: B
 DATABASE: Harris_SGB_1995

Sep. 23.1995 14:15

PAGE 74 of 125

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
3529.	25	68					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00036	HL
3530.	25	69					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00037	HL
3531.							TEHTEC	T7072	rpri	A610MULC	SG20CCAL00010	CL
3532.	25	70					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00036	HL
3533.	25	71					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00037	HL
3534.	25	72					TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00036	HL
3535.	25	73					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00037	HL
3536.	25	74					TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00036	HL
3537.							TEHTEC	T7072	rpri	A610MULC	SG20CCAL00010	CL
3538.	25	75					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00037	HL
3539.	25	76					TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00036	HL
3540.	25	77					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00037	HL
3541.	25	78					TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00036	HL
3542.	25	79					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00037	HL
3543.							TEHTEC	T7072	rpri	A610MULC	SG20CCAL00010	CL
3544.	25	80					TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00036	HL
3545.	25	81					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00037	HL
3546.	25	82					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL
3547.	25	83					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
3548.	25	84					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL
49.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00004	CL
50.	25	85					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
51.	25	86					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL
3552.	25	87					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
3553.	25	88					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL
3554.	25	89					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
3555.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00004	CL
3556.	25	90					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL
3557.	25	91					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
3558.	25	92					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
3559.	25	93					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
3560.	25	94					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00015	HL
3561.							TEHTEC	B5534	rpri	A610MULC	SG20CCAL00003	CL
3562.	25	95					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00016	HL
3563.	25	96					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00015	HL
3564.	25	97					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00016	HL
3565.	25	98					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00015	HL
3566.	25	99					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00016	HL
3567.							TEHTEC	B5534	rpri	A610MULC	SG20CCAL00003	CL
3568.	25	100					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00015	HL
3569.	25	101					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00016	HL
3570.	25	102					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00015	HL
3571.	25	103					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00016	HL
3572.	25	104					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00015	HL
3573.							TEHTEC	B5534	rpri	A610MULC	SG20CCAL00003	CL
74.	25	105					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00016	HL
75.	25	106					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00015	HL
76.	25	107					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00016	HL
77.							TEHTEC	B5534	rpri	A610MULC	SG20CCAL00003	CL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: B
 DATABASE: Harris_SGB_1995

Sep. 23.1995 14:15

PAGE 75 of 125

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
3578.	25	108						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00015	HL
3579.								07H07H	I2393	rpri	B620MRPC3C	SG21HCAL00031	HL
3580.		11.86	178	DNT	P1	07H	0.32	TEHTEC	B5534	rpri	A610MULC	SG20CCAL00003	CL
3581.	26	8						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
3582.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
3583.	26	9						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
3584.	26	10						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
3585.	26	11						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
3586.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
3587.	26	12						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
3588.	26	13						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
3589.	26	14						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
3590.	26	15						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
3591.	26	16						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
3592.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
3593.	26	17						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
3594.	26	18						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
3595.	26	19						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00042	HL
3596.	26	20						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00043	HL
3597.	26	21						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00042	HL
98.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
99.	26	22						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00043	HL
100.	26	23						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00042	HL
3601.	26	24						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00043	HL
3602.	26	25						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00042	HL
3603.	26	26						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00043	HL
3604.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
3605.	26	27						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00042	HL
3606.	26	28						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00035	HL
3607.	26	29						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00034	HL
3608.	26	30						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00035	HL
3609.	26	31						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00034	HL
3610.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
3611.	26	32						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00035	HL
3612.	26	33						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00034	HL
3613.	26	34						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00035	HL
3614.	26	35						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00034	HL
3615.	26	36						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00034	HL
3616.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
3617.	26	37						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00004	HL
3618.	26	38						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00003	HL
3619.	26	39						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00004	HL
3620.	26	40						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00003	HL
3621.	26	41						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00004	HL
3622.								TEHTEC	user5	rpri	A610MULC	SG20CCAL00001	CL
3623.	26	42						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00003	HL
3624.	26	43						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00004	HL
3625.	26	44						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00003	HL
3626.	26	45						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00004	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: B
 DATABASE: Harris_SGB_1995

Sep. 23,1995 14:15

PAGE 76 of 125

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
3627.	26	46					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00003	HL
3628.							TEHTEC	user5	rpri	A610MULC	SG20CCAL00001	CL
3629.	26	47					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00004	HL
3630.	26	48					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00003	HL
3631.	26	49					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00004	HL
3632.	26	50					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00003	HL
3633.	26	51					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00004	HL
3634.							TEHTEC	user5	rpri	A610MULC	SG20CCAL00001	CL
3635.	26	52					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00003	HL
3636.	26	53					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00004	HL
3637.	26	54					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00003	HL
3638.	26	55					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00004	HL
3639.	26	56					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00003	HL
3640.							TEHTEC	user5	rpri	A610MULC	SG20CCAL00001	CL
3641.	26	59					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00036	HL
3642.							TEHTEC	T7072	rpri	A610MULC	SG20CCAL00010	CL
3643.	26	60					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00037	HL
3644.	26	61					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00037	HL
3645.	26	62					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00037	HL
3646.	26	63					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00037	HL
47.	26	64					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00037	HL
49.							TEHTEC	T7072	rpri	A610MULC	SG20CCAL00010	CL
50.	26	65					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00037	HL
3650.	26	66					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00036	HL
3651.	26	67					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00037	HL
3652.	26	68					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00036	HL
3653.	26	69					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00037	HL
3654.							TEHTEC	T7072	rpri	A610MULC	SG20CCAL00010	CL
3655.	26	70					TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00036	HL
3656.	26	71					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00037	HL
3657.	26	72					TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00036	HL
3658.	26	73					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00037	HL
3659.	26	74					TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00036	HL
3660.							TEHTEC	T7072	rpri	A610MULC	SG20CCAL00010	CL
3661.	26	75					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00037	HL
3662.	26	76					TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00036	HL
3663.	26	77					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00037	HL
3664.	26	78					TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00036	HL
3665.	26	79					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00037	HL
3666.							TEHTEC	T7072	rpri	A610MULC	SG20CCAL00010	CL
3667.	26	80					TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00036	HL
3668.	26	81					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00037	HL
3669.	26	82					TSHTSH	F7460	rsec	B620MRPC3C	SG21HCAL00017	HL
3670.	26	83					TSHTSH	F7460	rsec	B620MRPC3C	SG21HCAL00018	HL
3671.	26	84					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL
372.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00004	CL
73.	26	85					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
74.	26	86					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL
75.	26	87					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: 8
 DATABASE: Harris_SGB_1995

Sep. 23.1995 14:15

PAGE 77 of 125

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
3676.	26	88						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL
3677.	26	89						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
3678.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00004	CL
3679.	26	90						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL
3680.	26	91						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
3681.	26	92						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
3682.	26	93						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
3683.	26	94						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00015	HL
3684.								TEHTEC	B5534	rpri	A610MULC	SG20CCAL00003	CL
3685.	26	95						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00016	HL
3686.	26	96						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00015	HL
3687.	26	97						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00016	HL
3688.	26	98						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00015	HL
3689.	26	99						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00016	HL
3690.								TEHTEC	B5534	rpri	A610MULC	SG20CCAL00003	CL
3691.	26	100						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00015	HL
3692.	26	101						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00016	HL
3693.	26	102						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00015	HL
3694.	26	103						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00016	HL
3695.	26	104						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00015	HL
96.								TEHTEC	B5534	rpri	A610MULC	SG20CCAL00003	CL
3697.	26	105						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00016	HL
3698.	26	106						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00015	HL
3699.	26	107						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00016	HL
3700.								TEHTEC	B5534	rpri	A610MULC	SG20CCAL00003	CL
3701.	27	8						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
3702.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
3703.	27	9						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
3704.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
3705.	27	10						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
3706.	27	11						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
3707.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
3708.	27	12						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
3709.	27	13						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
3710.	27	14						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
3711.	27	15						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
3712.	27	16						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
3713.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
3714.	27	17						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
3715.	27	18						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
3716.	27	19						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00042	HL
3717.	27	20						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00043	HL
3718.	27	21						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00042	HL
3719.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
3720.	27	22						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00052	HL
3721.	27	23						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00042	HL
3722.	27	24						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00043	HL
3723.	27	25						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00042	HL
3724.	27	26						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00043	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: B
 DATABASE: Harris_SGB_1995

Sep. 23.1995 14:15

PAGE 78 of 125

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
3725.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
3726.	27	27						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00042	HL
3727.	27	28						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00035	HL
3728.	27	29						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00034	HL
3729.	27	30						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00035	HL
3730.	27	31						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00034	HL
3731.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
3732.	27	32						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00035	HL
3733.	27	33						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00034	HL
3734.	27	34						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00035	HL
3735.	27	35						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00034	HL
3736.	27	36						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00034	HL
3737.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
3738.	27	37						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00004	HL
3739.	27	38						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00003	HL
3740.	27	39						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00004	HL
3741.	27	40						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00003	HL
3742.	27	41						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00004	HL
3743.								TEHTEC	user5	rpri	A610MULC	SG20CCAL00001	CL
3744.	27	42						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00003	HL
45.	27	43						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00004	HL
46.	27	44						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00003	HL
47.	27	45						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00004	HL
3748.	27	46						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00003	HL
3749.								TEHTEC	user5	rpri	A610MULC	SG20CCAL00001	CL
3750.	27	47						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00004	HL
3751.	27	48						TSHTSH	C1115	rsec	B620MRPC3C	SG21HCAL00003	HL
3752.	27	49						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00004	HL
3753.	27	50						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00003	HL
3754.	27	51						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00004	HL
3755.								TEHTEC	user5	rpri	A610MULC	SG20CCAL00001	CL
3756.	27	52						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00003	HL
3757.	27	53						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00004	HL
3758.	27	54						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00003	HL
3759.	27	55						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00004	HL
3760.	27	56						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00003	HL
3761.								TEHTEC	user5	rpri	A610MULC	SG20CCAL00001	CL
3762.	27	59						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00037	HL
3763.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00010	CL
3764.	27	60						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00036	HL
3765.	27	61						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00036	HL
3766.	27	62						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00036	HL
3767.	27	63						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00036	HL
3768.	27	64						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00036	HL
3769.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00010	CL
3770.	27	65						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00036	HL
3771.	27	66						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00036	HL
3772.	27	67						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00037	HL
3773.	27	68						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00036	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: B
 DATABASE: Harris_SGB_1995

Sep. 23.1995 14:15

PAGE 79 of 125

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
3774.	27	69						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00037	HL
3775.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00010	CL
3776.	27	70						TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00036	HL
3777.	27	71						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00037	HL
3778.	27	72						TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00036	HL
3779.	27	73						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00037	HL
3780.	27	74						TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00036	HL
3781.		5.81	183	DNT	P1	05H	0.23	TEHTEC	T7072	rpri	A610MULC	SG20CCAL00010	CL
3782.		5.65	186	DNT	1	09H	41.12	TEHTEC	T7072	rpri	A610MULC	SG20CCAL00010	CL
3783.		5.86	183	DNT	P1	AV2	0.00	TEHTEC	T7072	rpri	A610MULC	SG20CCAL00010	CL
3784.	27	75						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00037	HL
3785.	27	76						TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00036	HL
3786.	27	77						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00037	HL
3787.	27	78						TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00036	HL
3788.	27	79						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00037	HL
3789.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00010	CL
3790.	27	80						TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00036	HL
3791.	27	81						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00037	HL
3792.	27	82						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL
3793.	27	83						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
3794.	27	84						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL
3795.								TEHTEC	H1274	reso	A610MULC	SG20CCAL00004	CL
3796.	27	85						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
3797.	27	86						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL
3798.	27	87						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
3799.	27	88						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL
3800.	27	89						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
3801.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00004	CL
3802.	27	90						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL
3803.	27	91						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
3804.	27	92						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
3805.	27	93						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
3806.	27	94						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00015	HL
3807.								TEHTEC	B5534	rpri	A610MULC	SG20CCAL00003	CL
3808.	27	95						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00016	HL
3809.	27	96						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00015	HL
3810.	27	97						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00016	HL
3811.	27	98						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00015	HL
3812.	27	99						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00016	HL
3813.								TEHTEC	B5534	rpri	A610MULC	SG20CCAL00003	CL
3814.	27	100						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00015	HL
3815.	27	101						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00016	HL
3816.	27	102						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00015	HL
3817.	27	103						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00016	HL
3818.	27	104						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00015	HL
3819.								TEHTEC	B5534	rpri	A610MULC	SG20CCAL00003	CL
3820.	27	105						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00016	HL
3821.	27	106						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00015	HL
3822.								TEHTEC	B5534	rpri	A610MULC	SG20CCAL00003	CL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: B
 DATABASE: Harris_SGB_1995

Sep. 23.1995 14:15

PAGE 80 of 125

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
3823.	27	107						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00016	HL
3824.			6.28	181	DNT	P1	AV2 -0.17	TEHTEC	B5534	rpri	A610MULC	SG20CCAL00003	CL
3825.	28	9						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
3826.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
3827.	28	10						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
3828.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
3829.	28	11						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
3830.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
3831.	28	12						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
3832.	28	13						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
3833.	28	14						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
3834.	28	15						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
3835.	28	16						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
3836.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
3837.	28	17						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
3838.	28	18						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
3839.	28	19						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00043	HL
3840.	28	20						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00042	HL
3841.	28	21						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00043	HL
3842.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
43.	28	22						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00042	HL
44.	28	23						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00043	HL
45.	28	24						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00042	HL
3846.	28	25						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00043	HL
3847.	28	26						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00042	HL
3848.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
3849.	28	27						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00035	HL
3850.	28	28						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00034	HL
3851.	28	29						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00035	HL
3852.								07H07H	T9924	rpri	B620MRPC3C	SG21HCAL00052	HL
3853.	28	30						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00034	HL
3854.	28	31						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00035	HL
3855.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
3856.	28	32						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00034	HL
3857.	28	33						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00035	HL
3858.	28	34						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00034	HL
3859.	28	35						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00035	HL
3860.	28	36						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00034	HL
3861.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
3862.	28	37						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00004	HL
3863.	28	38						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00003	HL
3864.	28	39						TSHTSH	C1115	rsec	B620MRPC3C	SG21HCAL00004	HL
3865.	28	40						TSHTSH	C1115	rsec	B620MRPC3C	SG21HCAL00003	HL
3866.	28	41						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00004	HL
3867.								TEHTEC	user5	rpri	A610MULC	SG20CCAL00001	CL
3868.	28	42						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00003	HL
3869.	28	43						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00004	HL
3870.	28	44						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00003	HL
3871.	28	45						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00004	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: B
 DATABASE: Harris_SGB_1995

Sep. 23.1995 14:15

PAGE 81 of 125

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE	SIZE	CAL GROUP	LEG
3872.	28	46						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00003	HL	
3873.								TEHTEC	user5	rpri	A610MULC	SG20CCAL00001	CL	
3874.	28	47						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00004	HL	
3875.	28	48						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00003	HL	
3876.	28	49						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00004	HL	
3877.	28	50						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00003	HL	
3878.	28	51						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00004	HL	
3879.								TEHTEC	user5	rpri	A610MULC	SG20CCAL00001	CL	
3880.	28	52						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00003	HL	
3881.	28	53						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00004	HL	
3882.	28	54						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00003	HL	
3883.	28	55						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00004	HL	
3884.	28	56						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00003	HL	
3885.								TEHTEC	user5	rpri	A610MULC	SG20CCAL00001	CL	
3886.	28	59						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00036	HL	
3887.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00010	CL	
3888.	28	60						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00037	HL	
3889.	28	61						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00037	HL	
3890.	28	62						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00037	HL	
3891.	28	63						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00037	HL	
92.	28	64						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00037	HL	
93.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00010	CL	
94.	28	65						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00037	HL	
3895.	28	66						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00036	HL	
3896.	28	67						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00037	HL	
3897.	28	68						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00036	HL	
3898.	28	69						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00037	HL	
3899.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00010	CL	
3900.	28	70						TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00036	HL	
3901.	28	71						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00037	HL	
3902.	28	72						TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00036	HL	
3903.	28	73						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00037	HL	
3904.	28	74						TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00036	HL	
3905.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00010	CL	
3906.	28	75						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00037	HL	
3907.	28	76						TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00036	HL	
3908.	28	77						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00037	HL	
3909.	28	78						TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00036	HL	
3910.	28	79						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00037	HL	
3911.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00010	CL	
3912.	28	80						TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00036	HL	
3913.	28	81						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00037	HL	
3914.	28	82						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL	
3915.	28	83						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL	
3916.	28	84						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL	
3917.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00004	CL	
3918.	28	85						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL	
3919.	28	86						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL	
3920.	28	87						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL	

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: B
 DATABASE: Harris_SGB_1995

Sep. 23.1995 14:15

PAGE 82 of 125

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
3921.	28	88						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL
3922.	28	89						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
3923.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00004	CL
3924.	28	90						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL
3925.	28	91						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
3926.	28	92						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
3927.	28	93						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
3928.	28	94						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00015	HL
3929.								TEHTEC	B5534	rpri	A610MULC	SG20CCAL00003	CL
3930.	28	95						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00016	HL
3931.	28	96						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00015	HL
3932.	28	97						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00016	HL
3933.			0.46	22	P2	AV4	0.17	TEHTEC	B5534	rpri	A610MULC	SG20CCAL00003	CL
3934.	28	98						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00015	HL
3935.	28	99						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00016	HL
3936.								TEHTEC	B5534	rpri	A610MULC	SG20CCAL00003	CL
3937.	28	100						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00015	HL
3938.	28	101						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00016	HL
3939.	28	102						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00015	HL
3940.	28	103						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00016	HL
41.	28	104						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00015	HL
42.								TEHTEC	B5534	rpri	A610MULC	SG20CCAL00003	CL
43.	28	105						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00016	HL
3944.								TEHTEC	B5534	rpri	A610MULC	SG20CCAL00003	CL
3945.	28	106						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00015	HL
3946.								TEHTEC	B5534	rpri	A610MULC	SG20CCAL00003	CL
3947.	29	10						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
3948.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
3949.	29	11						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
3950.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
3951.	29	12						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
3952.	29	13						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
3953.	29	14						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
3954.	29	15						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
3955.	29	16						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
3956.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
3957.	29	17						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
3958.	29	18						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
3959.	29	19						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00042	HL
3960.	29	20						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00043	HL
3961.	29	21						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00042	HL
3962.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
3963.	29	22						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00043	HL
3964.	29	23						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00042	HL
3965.	29	24						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00043	HL
3966.	29	25						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00042	HL
3967.	29	26						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00043	HL
3968.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
3969.	29	27						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00042	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: B
 DATABASE: Harris_SGB_1995

Sep. 23.1995 14:15

PAGE 83 of 125

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE	SIZE	CAL	GROUP	LEG
3970.	29	28						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00035	HL		
3971.	29	29						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00034	HL		
3972.	29	30						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00035	HL		
3973.	29	31						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00034	HL		
3974.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL		
3975.	29	32						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00035	HL		
3976.	29	33						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00034	HL		
3977.	29	34						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00035	HL		
3978.	29	35						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00034	HL		
3979.	29	36						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00034	HL		
3980.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL		
3981.	29	37						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00004	HL		
3982.	29	38						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00003	HL		
3983.	29	39						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00004	HL		
3984.	29	40						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00003	HL		
3985.	29	41						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00004	HL		
3986.								TEHTEC	user5	rpri	A610MULC	SG20CCAL00001	CL		
3987.	29	42						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00003	HL		
3988.	29	43						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00004	HL		
3989.	29	44						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00003	HL		
90.	29	45						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00004	HL		
91.	29	46						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00003	HL		
92.								TEHTEC	user5	rpri	A610MULC	SG20CCAL00001	CL		
3993.	29	47						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00004	HL		
3994.	29	48						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00003	HL		
3995.	29	49						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00004	HL		
3996.	29	50						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00003	HL		
3997.	29	51						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00004	HL		
3998.								TEHTEC	user5	rpri	A610MULC	SG20CCAL00001	CL		
3999.	29	52						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00003	HL		
4000.	29	53						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00004	HL		
4001.	29	54						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00003	HL		
4002.	29	55						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00004	HL		
4003.	29	56						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00003	HL		
4004.								TEHTEC	user5	rpri	A610MULC	SG20CCAL00001	CL		
4005.	29	59						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00037	HL		
4006.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00010	CL		
4007.	29	60						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00036	HL		
4008.	29	61						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00036	HL		
4009.	29	62						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00036	HL		
4010.	29	63						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00036	HL		
4011.	29	64						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00036	HL		
4012.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00010	CL		
4013.	29	65						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00036	HL		
4014.	29	66						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00036	HL		
4015.	29	67						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00037	HL		
4016.		0.72	155	19	1	10C	-0.83	TEHTEC	D3858	reso	A610MULC	SG20CCAL00010	CL		
4017.		0.63	157	MBM	1	10C	3.71	TEHTEC	D3858	reso	A610MULC	SG20CCAL00010	CL		
4018.	29	68						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00036	HL		

*** INSPECTION FINAL REPORT LISTING ***

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: B
 DATABASE: Harris_SGB_1995

Sep. 23.1995 14:15

PAGE 84 of 125

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
4019.	29	69					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00037	HL
4020.							TEHTEC	T7072	rpri	A610MULC	SG20CCAL00010	CL
4021.	29	70					TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00036	HL
4022.	29	71					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00037	HL
4023.	29	72					TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00036	HL
4024.	29	73					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00037	HL
4025.	29	74					TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00036	HL
4026.							TEHTEC	T7072	rpri	A610MULC	SG20CCAL00010	CL
4027.	29	75					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00037	HL
4028.	29	76					TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00036	HL
4029.	29	77					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00037	HL
4030.	29	78					TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00036	HL
4031.	29	79					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00037	HL
4032.							TEHTEC	T7072	rpri	A610MULC	SG20CCAL00010	CL
4033.	29	80					TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00036	HL
4034.	29	81					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00037	HL
4035.	29	82					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL
4036.	29	83					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
4037.	29	84					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL
4038.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00004	CL
39.	29	85					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
40.	29	86					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL
41.	29	87					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
4042.	29	88					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL
4043.	29	89					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
4044.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00004	CL
4045.	29	90					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL
4046.	29	91					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
4047.	29	92					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
4048.	29	93					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
4049.	29	94					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00015	HL
4050.							TEHTEC	B5534	rpri	A610MULC	SG20CCAL00003	CL
4051.	29	95					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00016	HL
4052.	29	96					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00015	HL
4053.	29	97					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00016	HL
4054.	29	98					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00015	HL
4055.	29	99					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00016	HL
4056.							TEHTEC	B5534	rpri	A610MULC	SG20CCAL00003	CL
4057.	29	100					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00015	HL
4058.	29	101					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00016	HL
4059.	29	102					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00015	HL
4060.	29	103					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00016	HL
4061.	29	104					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00015	HL
4062.							TEHTEC	B5534	rpri	A610MULC	SG20CCAL00003	CL
4063.	29	105					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00016	HL
4064.							TEHTEC	B5534	rpri	A610MULC	SG20CCAL00003	CL
4065.	30	10					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
4066.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
4067.							02C02C	05305	rpri	B620MRPC3C	SG20CCAL00023	CL

*** INSPECTION FINAL REPORT LISTING ***

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: 8
 DATABASE: Harris_SGB_1995

Sep. 23, 1995 14:15

PAGE 85 of 125

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
4068.	30	11					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
4069.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
4070.	30	12					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
4071.	30	13					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
4072.	30	14					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
4073.	30	15					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
4074.	30	16					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
4075.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
4076.	30	17					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
4077.	30	18					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
4078.	30	19					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00042	HL
4079.	30	20					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00043	HL
4080.	30	21					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00042	HL
4081.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
4082.	30	22					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00043	HL
4083.	30	23					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00042	HL
4084.	30	24					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00043	HL
4085.	30	25					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00042	HL
4086.	30	26					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00043	HL
4087.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
88.	30	27					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00042	HL
89.	30	28					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00035	HL
90.	30	29					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00034	HL
4091.	30	30					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00035	HL
4092.	30	31					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00034	HL
4093.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
4094.	30	32					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00035	HL
4095.	30	33					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00034	HL
4096.	30	34					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00035	HL
4097.	30	35					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00034	HL
4098.	30	36					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00034	HL
4099.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
4100.	30	37					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00004	HL
4101.	30	38					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00003	HL
4102.	30	39					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00004	HL
4103.	30	40					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00003	HL
4104.	30	41					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00004	HL
4105.							TEHTEC	user5	rpri	A610MULC	SG20CCAL00001	CL
4106.	30	42					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00003	HL
4107.	30	43					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00004	HL
4108.	30	44					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00003	HL
4109.	30	45					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00004	HL
4110.	30	46					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00003	HL
4111.							TEHTEC	user5	rpri	A610MULC	SG20CCAL00001	CL
4112.	30	47					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00004	HL
4113.	30	48					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00003	HL
4114.	30	49					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00004	HL
4115.	30	50					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00003	HL
4116.	30	51					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00004	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: B
 DATABASE: Harris_SGB_1995

Sep. 23,1995 14:15

PAGE 86 of 125

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
4117.							TEHTEC	user5	rpri	A610MULC	SG20CCAL00001	CL
4118.	30	52					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00003	HL
4119.	30	53					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00004	HL
4120.	30	54					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00003	HL
4121.	30	55					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00004	HL
4122.	30	56					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00003	HL
4123.							TEHTEC	user5	rpri	A610MULC	SG20CCAL00001	CL
4124.	30	59					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00036	HL
4125.							TEHTEC	T7072	rpri	A610MULC	SG20CCAL00010	CL
4126.	30	60					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00036	HL
4127.	30	61					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00036	HL
4128.	30	62					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00036	HL
4129.	30	63					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00036	HL
4130.	30	64					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00036	HL
4131.							TEHTEC	T7072	rpri	A610MULC	SG20CCAL00010	CL
4132.	30	65					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00036	HL
4133.	30	66					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00036	HL
4134.	30	67					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00037	HL
4135.	30	68					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00036	HL
4136.	30	69					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00037	HL
37.							TEHTEC	T7072	rpri	A610MULC	SG20CCAL00010	CL
38.	30	70					TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00036	HL
39.	30	71					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00037	HL
4140.	30	72					TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00036	HL
4141.	30	73					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00037	HL
4142.	30	74					TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00036	HL
4143.							TEHTEC	T7072	rpri	A610MULC	SG20CCAL00010	CL
4144.	30	75					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00037	HL
4145.	30	76					TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00036	HL
4146.	30	77					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00037	HL
4147.	30	78					TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00036	HL
4148.	30	79					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00037	HL
4149.							TEHTEC	T7072	rpri	A610MULC	SG20CCAL00010	CL
4150.	30	80					TSHTSH	F2217	rpri	B620MRPC3C	SG21HCAL00036	HL
4151.	30	81					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00037	HL
4152.	30	82					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL
4153.	30	83					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
4154.	30	84					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL
4155.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00004	CL
4156.	30	85					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
4157.	30	86					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL
4158.	30	87					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
4159.	30	88					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL
4160.	30	89					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
4161.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00004	CL
62.	30	90					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
63.	30	91					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
64.	30	92					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
65.	30	93					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: B
 DATABASE: Harris_SGB_1995

Sep. 23.1995 14:15

PAGE 87 of 125

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
4166.	30	94					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00015	HL
4167.							TEHTEC	85534	rpri	A610MULC	SG20CCAL00003	CL
4168.	30	95					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00016	HL
4169.	30	96					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00015	HL
4170.	30	97					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00016	HL
4171.	30	98					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00015	HL
4172.	30	99					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00016	HL
4173.							TEHTEC	85534	rpri	A610MULC	SG20CCAL00003	CL
4174.	30	100					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00015	HL
4175.	30	101					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00016	HL
4176.	30	102					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00015	HL
4177.	30	103					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00016	HL
4178.	30	104					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00015	HL
4179.							TEHTEC	85534	rpri	A610MULC	SG20CCAL00003	CL
4180.	30	105					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00016	HL
4181.							TEHTEC	85534	rpri	A610MULC	SG20CCAL00003	CL
4182.	31	11					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
4183.							TEHTEC	T7072	rpri	A610MULC	SG20CCAL00012	CL
4184.	31	12					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00040	HL
4185.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
4186.	31	13					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
4187.	31	14					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00040	HL
4188.	31	15					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
4189.	31	16					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00040	HL
4190.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
4191.	31	17					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
4192.	31	18					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00040	HL
4193.	31	19					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00035	HL
4194.	31	20					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00034	HL
4195.	31	21					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00035	HL
4196.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
4197.	31	22					01HTSH	G1931	rpri	B620MRPC3C	SG21HCAL00034	HL
4198.	31	23					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00035	HL
4199.	31	24					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00034	HL
4200.	31	25					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00033	HL
4201.	31	26					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00032	HL
4202.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
4203.	31	27					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00033	HL
4204.	31	28					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00032	HL
4205.	31	29					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00033	HL
4206.	31	30					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00032	HL
4207.	31	31					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00033	HL
4208.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
4209.	31	32					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00032	HL
4210.	31	33					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00033	HL
4211.	31	34					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00032	HL
4212.	31	35					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00033	HL
4213.	31	36					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00032	HL
4214.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: B
 DATABASE: Harris_SGB_1995

Sep. 23,1995 14:15

PAGE 88 of 125

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
4215.	31	37					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00027	HL
4216.	31	38					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00027	HL
4217.	31	39					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00027	HL
4218.	31	40					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00027	HL
4219.	31	41					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00027	HL
4220.							TEHTEC	T7072	rpri	A610MULC	SG20CCAL00009	CL
4221.	31	42					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00027	HL
4222.	31	43					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00030	HL
4223.	31	44					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00029	HL
4224.	31	45					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00030	HL
4225.	31	46					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00029	HL
4226.							TEHTEC	T7072	rpri	A610MULC	SG20CCAL00009	CL
4227.	31	47					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00030	HL
4228.	31	48					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00029	HL
4229.	31	49					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00030	HL
4230.	31	50					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00029	HL
4231.	31	51					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00030	HL
4232.							TEHTEC	T7072	rpri	A610MULC	SG20CCAL00009	CL
4233.	31	52					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00029	HL
4234.	31	53					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00030	HL
4235.	31	54					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00029	HL
4235.	31	55					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00030	HL
4236.	31	56					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00029	HL
4238.							TEHTEC	T7072	rpri	A610MULC	SG20CCAL00009	CL
4239.	31	59					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00021	HL
4240.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00005	CL
4241.	31	60					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00022	HL
4242.	31	61					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00021	HL
4243.	31	62					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00022	HL
4244.	31	63					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00021	HL
4245.	31	64					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00022	HL
4246.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00005	CL
4247.	31	65					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00021	HL
4248.	31	66					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00022	HL
4249.	31	67					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00021	HL
4250.	31	68					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00022	HL
4251.	31	69					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00021	HL
4252.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00005	CL
4253.	31	70					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00022	HL
4254.	31	71					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00023	HL
4255.	31	72					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00024	HL
4256.	31	73					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00023	HL
4257.	31	74					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00024	HL
4258.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00005	CL
4259.	31	75					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00023	HL
4260.	31	76					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00024	HL
4261.	31	77					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00023	HL
4262.	31	78					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00024	HL
4263.	31	79					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00023	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: B
 DATABASE: Harris_SGB_1995

Sep. 23,1995 14:15

PAGE 89 of 125

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
4264.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00005	CL
4265.	31	80					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00024	HL
4266.	31	81					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00023	HL
4267.							TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00023	HL
4268.	31	82					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL
4269.	31	83					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
4270.	31	84					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL
4271.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00004	CL
4272.	31	85					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
4273.	31	86					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL
4274.	31	87					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
4275.	31	88					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL
4276.	31	89					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
4277.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00004	CL
4278.	31	90					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL
4279.	31	91					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
4280.	31	92					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL
4281.	31	93					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
4282.	31	94					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00015	HL
4283.							TEHTEC	B5534	rpri	A610MULC	SG20CCAL00004	CL
84.	31	95					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00016	HL
85.	31	96					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00015	HL
86.	31	97					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00016	HL
4287.	31	98					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00015	HL
4288.	31	99					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00016	HL
4289.							TEHTEC	B5534	rpri	A610MULC	SG20CCAL00004	CL
4290.	31	100					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00015	HL
4291.	31	101					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00015	HL
4292.	31	102					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00015	HL
4293.	31	103					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00015	HL
4294.							TEHTEC	B5534	rpri	A610MULC	SG20CCAL00004	CL
4295.	31	104					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00015	HL
4296.							TEHTEC	B5534	rpri	A610MULC	SG20CCAL00004	CL
4297.	32	12					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
4298.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
4299.	32	13					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00040	HL
4300.	32	14					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
4301.	32	15					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00040	HL
4302.	32	16					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
4303.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
4304.	32	17					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00040	HL
4305.	32	18					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
4306.	32	19					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00040	HL
4307.	32	20					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00035	HL
4308.	32	21					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00034	HL
4309.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
4310.	32	22					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00035	HL
4311.	32	23					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00034	HL
4312.	32	24					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00035	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: B
 DATABASE: Harris_SGB_1995

Sep. 23,1995 14:15

PAGE 90 of 125

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
4313.	32	25					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00034	HL
4314.	32	26					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00033	HL
4315.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
4316.	32	27					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00032	HL
4317.	32	28					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00033	HL
4318.	32	29					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00032	HL
4319.	32	30					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00033	HL
4320.	32	31					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00032	HL
4321.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
4322.	32	32					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00033	HL
4323.	32	33					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00032	HL
4324.	32	34					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00033	HL
4325.	32	35					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00032	HL
4326.	32	36					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00040	HL
4327.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
4328.	32	37					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00027	HL
4329.	32	38					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00027	HL
4330.	32	39					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00027	HL
4331.	32	40					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00027	HL
4332.	32	41					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00032	HL
33.							TEHTEC	T7072	rpri	A610MULC	SG20CCAL00009	CL
4.	32	42					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00027	HL
5.	32	43					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00030	HL
4336.	32	44					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00029	HL
4337.	32	45					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00030	HL
4338.	32	46					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00029	HL
4339.							TEHTEC	T7072	rpri	A610MULC	SG20CCAL00009	CL
4340.	32	47					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00030	HL
4341.	32	48					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00029	HL
4342.	32	49					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00030	HL
4343.	32	50					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00029	HL
4344.	32	51					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00030	HL
4345.							TEHTEC	T7072	rpri	A610MULC	SG20CCAL00009	CL
4346.	32	52					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00029	HL
4347.	32	53					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00030	HL
4348.	32	54					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00029	HL
4349.	32	55					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00030	HL
4350.	32	56					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00029	HL
4351.							TEHTEC	T7072	rpri	A610MULC	SG20CCAL00009	CL
4352.	32	59					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00021	HL
4353.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00005	CL
4354.	32	60					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00022	HL
4355.	32	61					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00021	HL
4356.	32	62					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00022	HL
4357.	32	63					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00021	HL
4358.	32	64					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00022	HL
4359.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00005	CL
4360.	32	65					01HTSH	T7665	rpri	B620MRPC3C	SG21HCAL00021	HL
4361.	32	66					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00022	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: B
 DATABASE: Harris_SGB_1995

Sep. 23.1995 14:15

PAGE 91 of 125

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
4362.	32	67					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00021	HL
4363.	32	68					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00022	HL
4364.	32	69					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00021	HL
4365.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00005	CL
4366.	32	70					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00022	HL
4367.	32	71					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00023	HL
4368.	32	72					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00024	HL
4369.	32	73					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00023	HL
4370.	32	74					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00024	HL
4371.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00005	CL
4372.	32	75					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00023	HL
4373.	32	76					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00024	HL
4374.	32	77					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00023	HL
4375.	32	78					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00024	HL
4376.	32	79					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00023	HL
4377.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00005	CL
4378.	32	80					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00024	HL
4379.	32	81					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00023	HL
4380.	32	82					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL
4381.	32	83					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
.82.	32	84					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL
3.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00004	CL
4.	32	85					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
4385.	32	86					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL
4386.	32	87					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
4387.	32	88					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL
4388.	32	89					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00019	HL
4389.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00004	CL
4390.	32	90					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL
4391.	32	91					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
4392.	32	92					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL
4393.	32	93					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
4394.	32	94					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00015	HL
4395.							TEHTEC	85534	rpri	A610MULC	SG20CCAL00004	CL
4396.	32	95					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00016	HL
4397.	32	96					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00015	HL
4398.	32	97					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00016	HL
4399.	32	98					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00015	HL
4400.	32	99					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00016	HL
4401.							TEHTEC	85534	rpri	A610MULC	SG20CCAL00004	CL
4402.	32	100					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00015	HL
4403.	32	101					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00015	HL
4404.	32	102					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00015	HL
4405.	32	103					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00015	HL
4406.							TEHTEC	85534	rpri	A610MULC	SG20CCAL00004	CL
'07.	33	12					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
'08.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
9.	33	13					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00040	HL
10.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: B
 DATABASE: Harris_SGB_1995

Sep. 23.1995 14:15

PAGE 92 of 125

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
4411.	33	14						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
4412.	33	15						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00040	HL
4413.	33	16						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
4414.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
4415.	33	17						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00040	HL
4416.	33	18						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
4417.	33	19						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00040	HL
4418.	33	20						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00035	HL
4419.	33	21						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00034	HL
4420.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
4421.	33	22						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00035	HL
4422.	33	23						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00034	HL
4423.	33	24						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00035	HL
4424.	33	25						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00034	HL
4425.	33	26						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00033	HL
4426.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
4427.	33	27						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00032	HL
4428.	33	28						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00033	HL
4429.	33	29						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00032	HL
4430.	33	30						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00033	HL
31.	33	31						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00032	HL
32.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
33.	33	32						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00033	HL
4434.	33	33						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00032	HL
4435.	33	34						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00033	HL
4436.	33	35						01HTSH	G1931	rpri	B620MRPC3C	SG21HCAL00032	HL
4437.	33	36						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00040	HL
4438.					RBD				k6733	rsec	B620MRPC3C	SG21HCAL00041	HL
4439.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
4440.	33	37						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00027	HL
4441.	33	38						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00027	HL
4442.	33	39						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00027	HL
4443.	33	40						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00027	HL
4444.	33	41						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00027	HL
4445.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00009	CL
4446.	33	42						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00027	HL
4447.	33	43						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00030	HL
4448.	33	44						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00029	HL
4449.	33	45						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00030	HL
4450.	33	46						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00029	HL
4451.			1.23	161	MBM	1	10H 26.83	TEHTEC	C3335	reso	A610MULC	SG20CCAL00009	CL
4452.			1.14	163	MBM	1	10H 37.91	TEHTEC	C3335	reso	A610MULC	SG20CCAL00009	CL
4453.	33	47						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00030	HL
4454.	33	48						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00029	HL
4455.	33	49						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00030	HL
4456.	33	50						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00029	HL
4457.	33	51						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00030	HL
3.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00009	CL
4459.	33	52						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00029	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: B
 DATABASE: Harris_SGB_1995

Sep. 23.1995 14:15

PAGE 93 of 125

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
4460.	33	53					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00030	HL
4461.	33	54					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00029	HL
4462.	33	55					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00030	HL
4463.	33	56					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00029	HL
4464.							TEHTEC	T7072	rpri	A610MULC	SG20CCAL00009	CL
4465.	33	59					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00021	HL
4466.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00005	CL
4467.	33	60					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00022	HL
4468.	33	61					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00021	HL
4469.	33	62					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00022	HL
4470.	33	63					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00021	HL
4471.	33	64					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00022	HL
4472.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00005	CL
4473.	33	65					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00021	HL
4474.	33	66					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00022	HL
4475.	33	67					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00021	HL
4476.	33	68					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00022	HL
4477.	33	69					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00023	HL
4478.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00005	CL
4479.	33	70					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00024	HL
80.	33	71					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00023	HL
81.	33	72					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00024	HL
82.	33	73					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00023	HL
4483.	33	74					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00024	HL
4484.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00005	CL
4485.	33	75					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00023	HL
4486.	33	76					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00024	HL
4487.	33	77					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00023	HL
4488.	33	78					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00024	HL
4489.	33	79					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00023	HL
4490.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00005	CL
4491.	33	80					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00024	HL
4492.	33	81					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00023	HL
4493.	33	82					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL
4494.	33	83					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
4495.	33	84					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL
4496.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00004	CL
4497.	33	85					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
4498.	33	86					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL
4499.	33	87					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
4500.	33	88					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL
4501.	33	89					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
4502.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00004	CL
4503.	33	90					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL
4504.	33	91					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
4505.	33	92					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL
4506.	33	93					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
4507.	33	94					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00015	HL
4508.							TEHTEC	B5534	rpri	A610MULC	SG20CCAL00004	CL

*** INSPECTION FINAL REPORT LISTING ***

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: B
 DATABASE: Harris_SGB_1995

Sep. 23,1995 14:15

PAGE 94 of 125

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
4509.	33	95					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00016	HL
4510.	33	96					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00015	HL
4511.	33	97					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00016	HL
4512.	33	98					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00015	HL
4513.	33	99					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00016	HL
4514.							TEHTEC	B5534	rpri	A610MULC	SG20CCAL00004	CL
4515.	33	100					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00015	HL
4516.	33	101					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00015	HL
4517.	33	102					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00015	HL
4518.							TEHTEC	B5534	rpri	A610MULC	SG20CCAL00004	CL
4519.	33	103					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00015	HL
4520.							TEHTEC	B5534	rpri	A610MULC	SG20CCAL00004	CL
4521.	34	13					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
4522.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
4523.	34	14					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00040	HL
4524.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
4525.	34	15					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
4526.	34	16					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00040	HL
4527.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
4528.	34	17					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
4529.	34	18					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00040	HL
4530.	34	19					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00035	HL
4531.	34	20					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00034	HL
4532.	34	21					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00035	HL
4533.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
4534.	34	22					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00034	HL
4535.	34	23					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00035	HL
4536.	34	24					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00034	HL
4537.	34	25					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00033	HL
4538.	34	26					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00032	HL
4539.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
4540.	34	27					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00033	HL
4541.	34	28					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00032	HL
4542.	34	29					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00033	HL
4543.	34	30					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00032	HL
4544.	34	31					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00033	HL
4545.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
4546.	34	32					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00032	HL
4547.	34	33					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00033	HL
4548.	34	34					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00032	HL
4549.	34	35					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00033	HL
4550.	34	36					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00032	HL
4551.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
4552.	34	37					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00027	HL
4553.	34	38					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00027	HL
4554.	34	39					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00027	HL
4555.	34	40					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00027	HL
4556.	34	41					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00027	HL
4557.							TEHTEC	T7072	rpri	A610MULC	SG20CCAL00009	CL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: B
 DATABASE: Harris_SGB_1995

Sep. 23.1995 14:15

PAGE 95 of 125

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
4558.	34	42						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00027	HL
4559.	34	43						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00030	HL
4560.	34	44						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00029	HL
4561.	34	45						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00030	HL
4562.	34	46						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00029	HL
4563.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00009	CL
4564.	34	47						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00030	HL
4565.	34	48						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00029	HL
4566.	34	49						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00030	HL
4567.	34	50						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00029	HL
4568.	34	51						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00030	HL
4569.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00009	CL
4570.	34	52						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00029	HL
4571.	34	53						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00030	HL
4572.	34	54						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00029	HL
4573.	34	55						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00030	HL
4574.	34	56						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00029	HL
4575.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00009	CL
4576.	34	59						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00021	HL
4577.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00005	CL
78.	34	60						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00022	HL
79.	34	61						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00021	HL
80.	34	62						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00022	HL
4581.	34	63						01HTSH	T7665	rpri	B620MRPC3C	SG21HCAL00021	HL
4582.	34	64						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00022	HL
4583.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00005	CL
4584.	34	65						01HTSH	T7665	rpri	B620MRPC3C	SG21HCAL00021	HL
4585.	34	66						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00022	HL
4586.	34	67						01HTSH	T7665	rpri	B620MRPC3C	SG21HCAL00021	HL
4587.	34	68						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00022	HL
4588.	34	69						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00023	HL
4589.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00005	CL
4590.	34	70						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00024	HL
4591.	34	71						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00023	HL
4592.	34	72						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00024	HL
4593.	34	73						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00023	HL
4594.	34	74						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00024	HL
4595.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00005	CL
4596.	34	75						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00023	HL
4597.	34	76						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00024	HL
4598.	34	77						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00023	HL
4599.	34	78						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00024	HL
4600.	34	79						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00023	HL
4601.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00005	CL
4602.	34	80						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00024	HL
4603.	34	81						TSHTSH	C1115	rsec	B620MRPC3C	SG21HCAL00023	HL
4604.	34	82						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL
4605.	34	83						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
4606.	34	84						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: B
 DATABASE: Harris_SGB_1995

Sep. 23.1995 14:15

PAGE 96 of 125

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
4607.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00004	CL
4608.	34	85						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
4609.	34	86						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL
4610.	34	87						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
4611.	34	88						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL
4612.	34	89						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
4613.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00004	CL
4614.	34	90						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL
4615.	34	91						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
4616.	34	92						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL
4617.	34	93						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
4618.	34	94						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00015	HL
4619.								TEHTEC	85534	rpri	A610MULC	SG20CCAL00004	CL
4620.	34	95						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00016	HL
4621.	34	96						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00015	HL
4622.	34	97						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00016	HL
4623.	34	98						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00015	HL
4624.	34	99						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00016	HL
4625.								TEHTEC	85534	rpri	A610MULC	SG20CCAL00004	CL
4626.	34	100						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00015	HL
27.	34	101						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00015	HL
8.								TEHTEC	85534	rpri	A610MULC	SG20CCAL00004	CL
29.	34	102						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00015	HL
4630.								TEHTEC	85534	rpri	A610MULC	SG20CCAL00004	CL
4631.	35	14						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
4632.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
4633.	35	15						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00040	HL
4634.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
4635.	35	16						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
4636.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
4637.	35	17						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00040	HL
4638.	35	18						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
4639.	35	19						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00040	HL
4640.	35	20						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00035	HL
4641.	35	21						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00034	HL
4642.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
4643.	35	22						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00035	HL
4644.	35	23						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00034	HL
4645.	35	24						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00033	HL
4646.	35	25						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00032	HL
4647.	35	26						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00033	HL
4648.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
4649.	35	27						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00032	HL
4650.	35	28						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00033	HL
4651.	35	29						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00032	HL
4652.	35	30						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00033	HL
53.	35	31						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00032	HL
1.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
5.	35	32						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00033	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: B
 DATABASE: Harris_SGB_1995

Sep. 23.1995 14:15

PAGE 97 of 125

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE	SIZE	CAL	GROUP	LEG
4656.	35	33						TSHTSH	G1931	rpri	B620MRPC3C		SG21HCAL00032	HL	
4657.	35	34						TSHTSH	T7665	rpri	B620MRPC3C		SG21HCAL00033	HL	
4658.	35	35						TSHTSH	G1931	rpri	B620MRPC3C		SG21HCAL00032	HL	
4659.	35	36						TSHTSH	T9924	rpri	B620MRPC3C		SG21HCAL00042	HL	
4660.								TEHTEC	F9284	rpri	A610MULC		SG20CCAL00012	CL	
4661.	35	37						TSHTSH	I2393	rpri	B620MRPC3C		SG21HCAL00027	HL	
4662.	35	38						TSHTSH	I2393	rpri	B620MRPC3C		SG21HCAL00027	HL	
4663.	35	39						TSHTSH	I2393	rpri	B620MRPC3C		SG21HCAL00027	HL	
4664.	35	40						TSHTSH	I2393	rpri	B620MRPC3C		SG21HCAL00027	HL	
4665.	35	41						TSHTSH	I2393	rpri	B620MRPC3C		SG21HCAL00027	HL	
4666.								TEHTEC	T7072	rpri	A610MULC		SG20CCAL00009	CL	
4667.	35	42						TSHTSH	I2393	rpri	B620MRPC3C		SG21HCAL00027	HL	
4668.	35	43						TSHTSH	I2393	rpri	B620MRPC3C		SG21HCAL00030	HL	
4669.	35	44						TSHTSH	I2393	rpri	B620MRPC3C		SG21HCAL00029	HL	
4670.	35	47						TSHTSH	I2393	rpri	B620MRPC3C		SG21HCAL00030	HL	
4671.	35	48						TSHTSH	I2393	rpri	B620MRPC3C		SG21HCAL00029	HL	
4672.	35	49						TSHTSH	I2393	rpri	B620MRPC3C		SG21HCAL00030	HL	
4673.	35	50						TSHTSH	I2393	rpri	B620MRPC3C		SG21HCAL00029	HL	
4674.	35	51						TSHTSH	I2393	rpri	B620MRPC3C		SG21HCAL00030	HL	
4675.								TEHTEC	T7072	rpri	A610MULC		SG20CCAL00009	CL	
76.	35	52						TSHTSH	I2393	rpri	B620MRPC3C		SG21HCAL00029	HL	
77.	35	53						TSHTSH	I2393	rpri	B620MRPC3C		SG21HCAL00030	HL	
78.	35	54						TSHTSH	I2393	rpri	B620MRPC3C		SG21HCAL00029	HL	
4679.	35	55						TSHTSH	I2393	rpri	B620MRPC3C		SG21HCAL00030	HL	
4680.	35	56						TSHTSH	I2393	rpri	B620MRPC3C		SG21HCAL00029	HL	
4681.								TEHTEC	T7072	rpri	A610MULC		SG20CCAL00009	CL	
4682.	35	59						TSHTSH	T7665	rpri	B620MRPC3C		SG21HCAL00021	HL	
4683.								TEHTEC	F9284	rpri	A610MULC		SG20CCAL00005	CL	
4684.	35	60						TSHTSH	G1931	rpri	B620MRPC3C		SG21HCAL00022	HL	
4685.	35	61						01HTSH	T7665	rpri	B620MRPC3C		SG21HCAL00021	HL	
4686.	35	62						TSHTSH	G1931	rpri	B620MRPC3C		SG21HCAL00022	HL	
4687.								TSHTSH	G1931	rpri	B620MRPC3C		SG21HCAL00022	HL	
4688.	35	63						TSHTSH	T7665	rpri	B620MRPC3C		SG21HCAL00021	HL	
4689.	35	64						TSHTSH	G1931	rpri	B620MRPC3C		SG21HCAL00022	HL	
4690.								TEHTEC	F9284	rpri	A610MULC		SG20CCAL00005	CL	
4691.	35	65						TSHTSH	T7665	rpri	B620MRPC3C		SG21HCAL00021	HL	
4692.	35	66						TSHTSH	G1931	rpri	B620MRPC3C		SG21HCAL00022	HL	
4693.	35	67						TSHTSH	T7665	rpri	B620MRPC3C		SG21HCAL00021	HL	
4694.	35	68						TSHTSH	G1931	rpri	B620MRPC3C		SG21HCAL00022	HL	
4695.	35	71						TSHTSH	T7665	rpri	B620MRPC3C		SG21HCAL00023	HL	
4696.	35	72						TSHTSH	G1931	rpri	B620MRPC3C		SG21HCAL00024	HL	
4697.	35	73						TSHTSH	T7665	rpri	B620MRPC3C		SG21HCAL00023	HL	
4698.	35	74						TSHTSH	G1931	rpri	B620MRPC3C		SG21HCAL00024	HL	
4699.								TEHTEC	F9284	rpri	A610MULC		SG20CCAL00005	CL	
4700.	35	75						TSHTSH	G1931	rpri	B620MRPC3C		SG21HCAL00023	HL	
701.	35	76						TSHTSH	G1931	rpri	B620MRPC3C		SG21HCAL00024	HL	
702.	35	77						TSHTSH	G1931	rpri	B620MRPC3C		SG21HCAL00023	HL	
703.	35	78						TSHTSH	G1931	rpri	B620MRPC3C		SG21HCAL00024	HL	
704.	35	79						TSHTSH	G1931	rpri	B620MRPC3C		SG21HCAL00023	HL	

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: B
 DATABASE: Harris_SGB_1995

Sep. 23.1995 14:15

PAGE 98 of 125

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
4705.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00005	CL
4706.	35	80					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00024	HL
4707.	35	81					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00023	HL
4708.	35	82					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL
4709.	35	83					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
4710.	35	84					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL
4711.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00004	CL
4712.	35	85					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
4713.	35	86					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL
4714.	35	87					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
4715.	35	88					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL
4716.	35	89					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
4717.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00004	CL
4718.	35	90					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL
4719.	35	91					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
4720.	35	92					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL
4721.	35	93					TSHTSH	F7460	rsec	B620MRPC3C	SG21HCAL00018	HL
4722.	35	94					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00015	HL
4723.							TEHTEC	B5534	rpri	A610MULC	SG20CCAL00004	CL
4724.	35	95					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00016	HL
25.	35	96					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00015	HL
26.	35	97					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00016	HL
27.	35	98					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00015	HL
4728.	35	99					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00016	HL
4729.							TEHTEC	B5534	rpri	A610MULC	SG20CCAL00004	CL
4730.	35	100					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00015	HL
4731.							TEHTEC	B5534	rpri	A610MULC	SG20CCAL00004	CL
4732.	35	101					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00015	HL
4733.							TEHTEC	B5534	rpri	A610MULC	SG20CCAL00004	CL
4734.	36	15					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
4735.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
4736.	36	16					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00040	HL
4737.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
4738.	36	17					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
4739.	36	18					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00040	HL
4740.	36	19					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00035	HL
4741.	36	20					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00034	HL
4742.	36	21					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00035	HL
4743.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
4744.	36	22					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00034	HL
4745.	36	23					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00035	HL
4746.	36	24					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00034	HL
4747.	36	25					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00033	HL
4748.	36	26					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00032	HL
4749.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
50.	36	27					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00033	HL
51.	36	28					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00032	HL
52.	36	29					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00033	HL
53.	36	30					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00032	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: B
 DATABASE: Harris_SGB_1995

Sep. 23.1995 14:15

PAGE 99 of 125

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
4754.	36	31					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00033	HL
4755.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
4756.	36	32					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00032	HL
4757.	36	33					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00033	HL
4758.	36	34					01HTSH	G1931	rpri	B620MRPC3C	SG21HCAL00032	HL
4759.							01HTSH	D3858	reso	B620MRPC3C	SG21HCAL00032	HL
4760.	36	35					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00033	HL
4761.	36	36					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00032	HL
4762.							TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00040	HL
4763.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
4764.	36	37					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00027	HL
4765.	36	38					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00027	HL
4766.	36	39					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00027	HL
4767.	36	40					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00027	HL
4768.	36	41					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00027	HL
4769.							TEHTEC	T7072	rpri	A610MULC	SG20CCAL00009	CL
4770.	36	42					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00027	HL
4771.	36	43					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00030	HL
4772.	36	44					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00029	HL
4773.	36	47					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00030	HL
74.	36	48					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00029	HL
75.	36	49					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00030	HL
76.	36	50					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00029	HL
4777.	36	51					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00030	HL
4778.							TEHTEC	T7072	rpri	A610MULC	SG20CCAL00009	CL
4779.	36	52					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00029	HL
4780.	36	53					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00030	HL
4781.	36	54					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00029	HL
4782.	36	55					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00030	HL
4783.	36	56					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00029	HL
4784.							TEHTEC	T7072	rpri	A610MULC	SG20CCAL00009	CL
4785.	36	59					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00021	HL
4786.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00005	CL
4787.	36	60					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00022	HL
4788.	36	61					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00021	HL
4789.	36	62					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00022	HL
4790.	36	63					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00021	HL
4791.	36	64					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00022	HL
4792.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00005	CL
4793.	36	65					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00021	HL
4794.	36	66					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00022	HL
4795.	36	67					01HTSH	T7665	rpri	B620MRPC3C	SG21HCAL00021	HL
4796.	36	68					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00022	HL
4797.	36	71					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00023	HL
4798.	36	72					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00024	HL
4799.	36	73					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00023	HL
4800.	36	74					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00024	HL
..							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00005	CL
..	36	75					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00023	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: B
 DATABASE: Harris_SGB_1995

Sep. 23,1995 14:15

PAGE 100 of 125

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
4803.	36	76						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00024	HL
4804.	36	77						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00023	HL
4805.	36	78						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00024	HL
4806.	36	79						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00023	HL
4807.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00005	CL
4808.	36	80						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00024	HL
4809.	36	81						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00023	HL
4810.	36	82						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL
4811.	36	83						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
4812.	36	84						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL
4813.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00004	CL
4814.	36	85						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
4815.	36	86						TSHTSH	F7460	rsec	B620MRPC3C	SG21HCAL00017	HL
4816.	36	87						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
4817.	36	88						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL
4818.	36	89						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
4819.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00004	CL
4820.	36	90						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL
4821.	36	91						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
4822.	36	92						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL
23.	36	93						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
1.	36	94						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00015	HL
5.								TEHTEC	B5534	rpri	A610MULC	SG20CCAL00004	CL
4826.	36	95						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00016	HL
4827.	36	96						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00015	HL
4828.	36	97						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00016	HL
4829.	36	98						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00015	HL
4830.	36	99						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00016	HL
4831.								TEHTEC	B5534	rpri	A610MULC	SG20CCAL00004	CL
4832.	36	100						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00015	HL
4833.								TEHTEC	B5534	rpri	A610MULC	SG20CCAL00004	CL
4834.	37	16						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
4835.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
4836.	37	17						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00040	HL
4837.	37	18						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
4838.	37	19						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00040	HL
4839.	37	20						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00035	HL
4840.	37	21						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00034	HL
4841.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
4842.	37	22						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00035	HL
4843.	37	23						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00034	HL
4844.	37	24						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00033	HL
4845.	37	25						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00032	HL
4846.	37	26						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00033	HL
4847.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
48.	37	27						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00032	HL
49.	37	28						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00033	HL
50.	37	29						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00032	HL
51.	37	30						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00033	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: B
 DATABASE: Harris_SGB_1995

Sep. 23,1995 14:15

PAGE 101 of 125

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
4852.	37	31						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00032	HL
4853.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
4854.	37	32						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00033	HL
4855.	37	33						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00032	HL
4856.	37	34						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00033	HL
4857.	37	35						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00032	HL
4858.	37	36						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00040	HL
4859.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
4860.	37	37						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00027	HL
4861.	37	38						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00027	HL
4862.	37	39						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00027	HL
4863.	37	40						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00027	HL
4864.	37	41						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00030	HL
4865.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00009	CL
4866.	37	42						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00029	HL
4867.	37	43						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00030	HL
4868.	37	44						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00029	HL
4869.	37	45						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00030	HL
4870.	37	46						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00029	HL
4871.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00009	CL
72.	37	47						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00030	HL
73.	37	48						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00029	HL
74.	37	49						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00030	HL
4875.	37	50						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00029	HL
4876.	37	51						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00030	HL
4877.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00009	CL
4878.	37	52						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00029	HL
4879.	37	53						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00030	HL
4880.	37	54						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00029	HL
4881.	37	55						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00030	HL
4882.	37	56						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00029	HL
4883.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00009	CL
4884.	37	59						01HTSH	T7665	rpri	B620MRPC3C	SG21HCAL00021	HL
4885.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00005	CL
4886.	37	60						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00022	HL
4887.	37	61						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00021	HL
4888.	37	62						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00022	HL
4889.	37	63						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00021	HL
4890.	37	64						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00022	HL
4891.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00005	CL
4892.	37	65						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00021	HL
4893.	37	66						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00022	HL
4894.	37	67						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00021	HL
4895.	37	68						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00022	HL
4896.	37	69						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00023	HL
4897.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00005	CL
4898.	37	70						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00024	HL
4899.	37	71						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00023	HL
4900.	37	72						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00024	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: B
 DATABASE: Harris_SGB_1995

Sep. 23.1995 14:15

PAGE 102 of 125

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
4901.	37	73					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00023	HL
4902.	37	74					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00024	HL
4903.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00005	CL
4904.	37	75					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00023	HL
4905.	37	76					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00024	HL
4906.	37	77					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00023	HL
4907.	37	78					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00024	HL
4908.	37	79					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00023	HL
4909.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00005	CL
4910.	37	80					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00024	HL
4911.	37	81					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00023	HL
4912.	37	82					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL
4913.	37	83					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
4914.	37	84					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL
4915.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00004	CL
4916.	37	85					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
4917.	37	86					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL
4918.	37	87					TSHTSH	F7460	rsec	B620MRPC3C	SG21HCAL00018	HL
4919.	37	88					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL
4920.	37	89					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
21.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00004	CL
2.	37	90					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL
3.	37	91					TSHTSH	F7460	rsec	B620MRPC3C	SG21HCAL00018	HL
4924.	37	92					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL
4925.	37	93					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
4926.	37	94					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00015	HL
4927.							TEHTEC	B5534	rpri	A610MULC	SG20CCAL00004	CL
4928.	37	95					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00016	HL
4929.	37	96					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00015	HL
4930.	37	97					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00016	HL
4931.	37	98					TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00015	HL
4932.	37	99					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00016	HL
4933.							TEHTEC	B5534	rpri	A610MULC	SG20CCAL00004	CL
4934.	38	16					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
4935.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
4936.	38	17					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00040	HL
4937.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
4938.	38	18					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
4939.	38	19					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00040	HL
4940.	38	20					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00035	HL
4941.	38	21					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00034	HL
4942.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
4943.	38	22					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00035	HL
4944.	38	23					TSHTSH	J1978	rsec	B620MRPC3C	SG21HCAL00034	HL
4945.	38	24					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00033	HL
4946.	38	25					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00032	HL
4947.	38	26					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00033	HL
4948.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
4949.	38	27					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00032	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: B
 DATABASE: Harris_SGB_1995

Sep. 23.1995 14:15

PAGE 103 of 125

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
4950.	38	28					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00033	HL
4951.	38	29					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00032	HL
4952.	38	30					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00033	HL
4953.	38	31					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00032	HL
4954.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
4955.	38	32					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00033	HL
4956.	38	33					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00032	HL
4957.	38	34					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00033	HL
4958.	38	35					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00032	HL
4959.	38	36					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00040	HL
4960.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
4961.	38	37					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00027	HL
4962.	38	38					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00027	HL
4963.	38	39					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00027	HL
4964.	38	40					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00027	HL
4965.	38	41					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00030	HL
4966.							TEHTEC	T7072	rpri	A610MULC	SG20CCAL00009	CL
4967.	38	42					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00029	HL
4968.	38	43					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00030	HL
4969.	38	44					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00029	HL
70.	38	45					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00030	HL
71.	38	46					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00029	HL
2.							TEHTEC	T7072	rpri	A610MULC	SG20CCAL00009	CL
4973.	38	47					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00030	HL
4974.	38	48					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00029	HL
4975.	38	49					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00030	HL
4976.	38	50					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00029	HL
4977.	38	51					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00030	HL
4978.							TEHTEC	T7072	rpri	A610MULC	SG20CCAL00009	CL
4979.	38	52					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00029	HL
4980.	38	53					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00030	HL
4981.	38	54					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00029	HL
4982.	38	55					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00030	HL
4983.	38	56					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00029	HL
4984.							TEHTEC	T7072	rpri	A610MULC	SG20CCAL00009	CL
4985.	38	59					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00021	HL
4986.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00005	CL
4987.	38	60					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00022	HL
4988.	38	61					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00021	HL
4989.	38	62					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00022	HL
4990.	38	63					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00021	HL
4991.	38	64					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00022	HL
4992.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00005	CL
4993.	38	65					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00021	HL
4994.	38	66					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00022	HL
4995.	38	67					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00021	HL
4996.	38	68					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00022	HL
7.	38	69					TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00023	HL
98.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00005	CL

*** INSPECTION FINAL REPORT LISTING ***

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: B
 DATABASE: Harris_SGB_1995

Sep. 23.1995 14:15

PAGE 104 of 125

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
4999.	38	70						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00024	HL
5000.	38	71						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00023	HL
5001.	38	72						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00024	HL
5002.	38	73						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00023	HL
5003.	38	74						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00024	HL
5004.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00005	CL
5005.	38	75						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00023	HL
5006.	38	76						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00024	HL
5007.	38	77						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00023	HL
5008.	38	78						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00024	HL
5009.	38	79						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00023	HL
5010.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00005	CL
5011.	38	80						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00024	HL
5012.	38	81						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00023	HL
5013.	38	82						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL
5014.	38	83						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
5015.	38	84						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL
5016.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00004	CL
5017.	38	85						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
5018.	38	86						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL
19.	38	87						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
20.	38	88						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL
21.	38	89						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
5022.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00004	CL
5023.	38	90						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL
5024.	38	91						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
5025.	38	92						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL
5026.	38	93						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
5027.	38	94						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00015	HL
5028.								TEHTEC	B5534	rpri	A610MULC	SG20CCAL00004	CL
5029.	38	95						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00016	HL
5030.	38	96						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00015	HL
5031.	38	97						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00016	HL
5032.	38	98						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00015	HL
5033.								TEHTEC	B5534	rpri	A610MULC	SG20CCAL00004	CL
5034.	38	99						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00016	HL
5035.								11H11H	I2393	rpri	B620MRPC3C	SG21HCAL00031	HL
5036.		15.48	182	DNT	P1	11H	0.00	TEHTEC	T7072	rpri	A590MULC	SG20CCAL00018	CL
5037.		21.43	182	DNT	P1	10C	0.00	TEHTEC	F3453	reso	A590MULC	SG20CCAL00018	CL
5038.		8.56	184	DNT	P1	09C	-0.36	TEHTEC	T7072	rpri	A590MULC	SG20CCAL00018	CL
5039.		8.56	181	DNT	P1	09C	-0.26	09CTEC	B5534	rpri	A610MULC	SG20CCAL00004	CL
5040.				RES		09C	38.92	09CTEC	B5534	rpri	A610MULC	SG20CCAL00004	CL
5041.	39	17						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL
5042.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
5043.	39	18						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00040	HL
5044.		0.30		15	P2	11H	0.38	TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
5045.	39	19						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00035	HL
5046.	39	20						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00034	HL
5047.	39	21						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00035	HL

*** INSPECTION FINAL REPORT LISTING ***

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: B
 DATABASE: Harris_SGB_1995

Sep. 23.1995 14:15

PAGE 105 of 125

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
5048.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
5049.	39	22						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00034	HL
5050.	39	23						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00035	HL
5051.	39	24						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00034	HL
5052.	39	25						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00033	HL
5053.	39	26						TSHTSH	T6956	rsec	B620MRPC3C	SG21HCAL00032	HL
5054.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
5055.	39	27						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00033	HL
5056.	39	28						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00032	HL
5057.	39	29						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00033	HL
5058.	39	30						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00032	HL
5059.	39	31						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00033	HL
5060.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
5061.	39	32						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00032	HL
5062.	39	33						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00033	HL
5063.	39	34						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00032	HL
5064.	39	35						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00033	HL
5065.	39	36						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00032	HL
5066.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
5067.	39	37						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00027	HL
68.	39	38						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00027	HL
69.	39	39						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00027	HL
70.	39	40						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00027	HL
5071.	39	41						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00030	HL
5072.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00009	CL
5073.	39	42						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00029	HL
5074.	39	43						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00030	HL
5075.	39	44						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00029	HL
5076.	39	45						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00030	HL
5077.	39	46						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00029	HL
5078.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00009	CL
5079.	39	47						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00030	HL
5080.	39	48						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00029	HL
5081.	39	49						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00030	HL
5082.	39	50						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00029	HL
5083.	39	51						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00030	HL
5084.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00009	CL
5085.	39	52						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00029	HL
5086.	39	53						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00030	HL
5087.	39	54						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00029	HL
5088.	39	55						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00030	HL
5089.	39	56						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00029	HL
5090.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00009	CL
5091.	39	59						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00021	HL
5092.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00005	CL
5093.	39	60						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00022	HL
5094.	39	61						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00021	HL
5095.	39	62						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00022	HL
5096.	39	63						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00021	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: B
 DATABASE: Harris_SGB_1995

Sep. 23,1995 14:15

PAGE 106 of 125

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG	
5097.	39	64						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00022	HL	
5098.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00005	CL	
5099.	39	65						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00021	HL	
5100.	39	66						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00022	HL	
5101.	39	67						01HTSH	T7665	rpri	B620MRPC3C	SG21HCAL00021	HL	
5102.	39	68						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00022	HL	
5103.	39	69						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00023	HL	
5104.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00005	CL	
5105.	39	70						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00024	HL	
5106.	39	71						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00023	HL	
5107.	39	72						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00024	HL	
5108.	39	73						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00023	HL	
5109.	39	74						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00024	HL	
5110.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00005	CL	
5111.	39	75						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00023	HL	
5112.	39	76						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00024	HL	
5113.	39	77						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00023	HL	
5114.	39	78						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00024	HL	
5115.	39	79						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00023	HL	
5116.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00005	CL	
17.	39	80						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00024	HL	
18.	39	81			PID	1	TSH	0.10	TSHTSH	F3453	reso	B620MRPC3C	SG21HCAL00027	HL
19.			2.39	36	SAI	1	TSH	0.11	TSHTSH	C1115	rsec	B620MRPC3C	SG21HCAL00023	HL
5120.	39	82						TSHTSH	F7460	rsec	B620MRPC3C	SG21HCAL00017	HL	
5121.	39	83						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL	
5122.	39	84						TSHTSH	F7460	rsec	B620MRPC3C	SG21HCAL00017	HL	
5123.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00004	CL	
5124.	39	85						TSHTSH	F7460	rsec	B620MRPC3C	SG21HCAL00018	HL	
5125.	39	86						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL	
5126.	39	87						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL	
5127.	39	88						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL	
5128.	39	89						TSHTSH	F7460	rsec	B620MRPC3C	SG21HCAL00018	HL	
5129.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00004	CL	
5130.	39	90						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL	
5131.	39	91						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL	
5132.	39	92						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL	
5133.	39	93						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL	
5134.	39	94						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00015	HL	
5135.								TEHTEC	85534	rpri	A610MULC	SG20CCAL00004	CL	
5136.	39	95						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00016	HL	
5137.	39	96						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00015	HL	
5138.	39	97						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00016	HL	
5139.								TEHTEC	85534	rpri	A610MULC	SG20CCAL00004	CL	
5140.	39	98						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00015	HL	
5141.								TEHTEC	85534	rpri	A610MULC	SG20CCAL00004	CL	
42.	40	18						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00041	HL	
43.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL	
44.	40	19						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00040	HL	
45.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL	

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: B
 DATABASE: Harris_SGB_1995

Sep. 23,1995 14:15

PAGE 107 of 125

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
5146.	40	20						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00035	HL
5147.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
5148.	40	21						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00034	HL
5149.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
5150.	40	22						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00035	HL
5151.	40	23						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00034	HL
5152.	40	24						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00033	HL
5153.	40	25						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00032	HL
5154.	40	26						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00033	HL
5155.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
5156.	40	27						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00032	HL
5157.	40	28						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00033	HL
5158.	40	29						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00032	HL
5159.	40	30						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00033	HL
5160.	40	31						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00032	HL
5161.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
5162.	40	32						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00033	HL
5163.	40	33						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00032	HL
5164.	40	34						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00033	HL
5165.	40	35						01HTSH	G1931	rpri	B620MRPC3C	SG21HCAL00032	HL
66.	40	36						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00040	HL
7.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00012	CL
5168.	40	37						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00027	HL
5169.	40	38						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00027	HL
5170.	40	39						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00027	HL
5171.	40	40						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00027	HL
5172.	40	41						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00030	HL
5173.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00009	CL
5174.	40	42						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00029	HL
5175.	40	43						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00030	HL
5176.	40	44						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00029	HL
5177.	40	45						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00030	HL
5178.	40	46						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00029	HL
5179.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00009	CL
5180.	40	47						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00030	HL
5181.	40	48						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00029	HL
5182.	40	49						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00030	HL
5183.	40	50						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00029	HL
5184.	40	51						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00030	HL
5185.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00009	CL
5186.	40	52						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00029	HL
5187.	40	53						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00030	HL
5188.	40	54						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00029	HL
5189.	40	55						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00030	HL
5190.	40	56						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00029	HL
5191.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00009	CL
92.	40	59						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00021	HL
93.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00005	CL
94.	40	60						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00022	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: B
 DATABASE: Harris_SGB_1995

Sep. 23,1995 14:15

PAGE 108 of 125

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG	
5195.	40	61						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00021	HL	
5196.	40	62						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00022	HL	
5197.	40	63						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00021	HL	
5198.	40	64						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00022	HL	
5199.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00005	CL	
5200.	40	65						01HTSH	T7665	rpri	B620MRPC3C	SG21HCAL00021	HL	
5201.	40	66						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00022	HL	
5202.	40	67						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00021	HL	
5203.	40	68						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00022	HL	
5204.	40	69						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00023	HL	
5205.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00005	CL	
5206.	40	70						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00024	HL	
5207.	40	71						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00023	HL	
5208.	40	72						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00024	HL	
5209.	40	73						TSHTSH	T7665	rpri	B620MRPC3C	SG21HCAL00023	HL	
5210.	40	74						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00024	HL	
5211.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00005	CL	
5212.	40	75						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00023	HL	
5213.	40	76						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00024	HL	
5214.	40	77						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00023	HL	
15.	40	78						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00024	HL	
16.	40	79						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00023	HL	
17.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00005	CL	
5218.	40	80						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00024	HL	
5219.	40	81						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00023	HL	
5220.	40	82						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL	
5221.	40	83						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL	
5222.	40	84						TSHTSH	F7460	rsec	B620MRPC3C	SG21HCAL00017	HL	
5223.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00004	CL	
5224.	40	85						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL	
5225.	40	86						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL	
5226.	40	87						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL	
5227.	40	88						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL	
5228.	40	89						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL	
5229.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00004	CL	
5230.	40	90						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL	
5231.	40	91						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL	
5232.	40	92						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL	
5233.	40	93						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL	
5234.	40	94						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00015	HL	
5235.								TEHTEC	85534	rpri	A610MULC	SG20CCAL00004	CL	
5236.	40	95						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00016	HL	
5237.								TEHTEC	85534	rpri	A610MULC	SG20CCAL00004	CL	
5238.	40	96						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00015	HL	
5239.			0.82		25	P2	02C	0.52	TEHTEC	H1274	reso	A610MULC	SG20CCAL00004	CL
40.	40	97						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00016	HL	
41.								TEHTEC	85534	rpri	A610MULC	SG20CCAL00004	CL	
2.	41	20						TSHTSH	12393	rpri	B620MRPC3C	SG21HCAL00033	HL	
43.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00011	CL	

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: B
 DATABASE: Harris_SGB_1995

Sep. 23, 1995 14:15

PAGE 109 of 125

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
5244.	41	21						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00032	HL
5245.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00011	CL
5246.	41	22						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00033	HL
5247.	41	23						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00032	HL
5248.	41	24						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00033	HL
5249.	41	25						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00032	HL
5250.	41	26						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00033	HL
5251.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00011	CL
5252.	41	27						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00032	HL
5253.	41	28						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00033	HL
5254.	41	29						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00032	HL
5255.	41	30						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00033	HL
5256.	41	31						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00032	HL
5257.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00009	CL
5258.	41	32						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00033	HL
5259.	41	33						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00032	HL
5260.	41	34						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00033	HL
5261.					RBD				P5436	rsec	A610MULC	SG20CCAL00011	CL
5262.		0.18		7	P2	AV2	0.00	TEHTEC	B3052	reso	A610MULC	SG20CCAL00016	CL
5263.	41	35						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00032	HL
5264.	41	36						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00032	HL
5265.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00009	CL
5266.	41	37						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00026	HL
5267.	41	38						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00025	HL
5268.		0.44		17	P2	AV3	-0.12	TEHTEC	T7072	rpri	A610MULC	SG20CCAL00009	CL
5269.	41	39						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00026	HL
5270.	41	40						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00025	HL
5271.	41	41						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00026	HL
5272.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00009	CL
5273.	41	42						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00025	HL
5274.	41	43						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00025	HL
5275.	41	44						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00025	HL
5276.	41	45						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00028	HL
5277.	41	46						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00027	HL
5278.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00009	CL
5279.	41	47						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00028	HL
5280.	41	48						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00027	HL
5281.	41	49						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00028	HL
5282.	41	50						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00027	HL
5283.	41	51						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00028	HL
5284.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00009	CL
5285.	41	52						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00027	HL
5286.	41	53						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00028	HL
5287.	41	54						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00027	HL
5288.	41	55						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00028	HL
5289.	41	56						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00027	HL
5290.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00009	CL
5291.	41	59						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00023	HL
5292.								TEHTEC	H1274	reso	A610MULC	SG20CCAL00006	CL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: B
 DATABASE: Harris_SGB_1995

Sep. 23.1995 14:15

PAGE 110 of 125

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
5293.	41	60						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00023	HL
5294.	41	61						TSHTSH	F3453	reso	B620MRPC3C	SG21HCAL00023	HL
5295.	41	62						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00023	HL
5296.	41	63						TSHTSH	C1115	rsec	B620MRPC3C	SG21HCAL00023	HL
5297.	41	64						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00023	HL
5298.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00016	CL
5299.	41	65						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00023	HL
5300.	41	66						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00025	HL
5301.	41	67						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00025	HL
5302.	41	68						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00025	HL
5303.	41	69						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00025	HL
5304.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00008	CL
5305.	41	70						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00025	HL
5306.	41	71						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00025	HL
5307.	41	72						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00025	HL
5308.	41	73						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00025	HL
5309.	41	74						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00025	HL
5310.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00008	CL
5311.	41	75						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00025	HL
5312.	41	76						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00025	HL
13.	41	77						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00025	HL
14.	41	78						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00025	HL
15.	41	79						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00025	HL
5316.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00008	CL
5317.	41	80						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00025	HL
5318.	41	81						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00025	HL
5319.	41	82						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL
5320.	41	83						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
5321.	41	84						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL
5322.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00004	CL
5323.	41	85						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
5324.	41	86						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL
5325.	41	87						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
5326.	41	88						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL
5327.	41	89						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
5328.								TEHTEC	B5534	rpri	A610MULC	SG20CCAL00004	CL
5329.	41	90						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL
5330.	41	91						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
5331.	41	92						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL
5332.	41	93						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
5333.	41	94						TSHTSH	05305	rpri	B620MRPC3C	SG21HCAL00015	HL
5334.								TEHTEC	B5534	rpri	A610MULC	SG20CCAL00004	CL
5335.	41	95						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00016	HL
5336.		13.42	186	DNT	1	AV4	32.40	TEHTEC	B5534	rpri	A610MULC	SG20CCAL00004	CL
5337.		6.25	187	DNT	1	11C	0.90	TEHTEC	B5534	rpri	A610MULC	SG20CCAL00004	CL
338.	42	21						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00033	HL
39.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00011	CL
40.	42	22						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00032	HL
41.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00011	CL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: B
 DATABASE: Harris_SGB_1995

Sep. 23.1995 14:15

PAGE 111 of 125

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
5342.	42	23						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00033	HL
5343.	42	24						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00032	HL
5344.	42	25						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00033	HL
5345.	42	26						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00032	HL
5346.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00011	CL
5347.	42	27						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00033	HL
5348.	42	28						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00032	HL
5349.	42	29						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00033	HL
5350.	42	30						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00032	HL
5351.	42	31						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00033	HL
5352.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00009	CL
5353.	42	32						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00032	HL
5354.	42	33						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00033	HL
5355.	42	34						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00032	HL
5356.	42	35						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00033	HL
5357.	42	36						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00032	HL
5358.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00009	CL
5359.	42	37						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00026	HL
5360.	42	38						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00025	HL
5361.	42	39						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00026	HL
62.	42	40						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00025	HL
63.	42	41						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00026	HL
64.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00009	CL
5365.	42	42						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00025	HL
5366.	42	43						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00027	HL
5367.	42	44						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00025	HL
5368.	42	45						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00028	HL
5369.	42	46						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00027	HL
5370.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00009	CL
5371.	42	47						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00028	HL
5372.	42	48						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00027	HL
5373.	42	49						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00028	HL
5374.	42	50						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00027	HL
5375.	42	51						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00028	HL
5376.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00009	CL
5377.	42	52						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00027	HL
5378.	42	53						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00028	HL
5379.	42	54						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00027	HL
5380.	42	55						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00032	HL
5381.	42	56						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00032	HL
5382.		0.74		25	P2	AV2	-0.03	TEHTEC	C3335	reso	A610MULC	SG20CCAL00009	CL
5383.	42	59						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00024	HL
5384.								TEHTEC	H1274	reso	A610MULC	SG20CCAL00006	CL
5385.	42	60						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00024	HL
5386.	42	61						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00024	HL
5387.	42	62						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00024	HL
5388.	42	63						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00024	HL
5389.	42	64						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00024	HL
5390.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00006	CL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: 8
 DATABASE: Harris_SGB_1995

Sep. 23.1995 14:15

PAGE 112 of 125

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
5391.	42	65						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00024	HL
5392.	42	66						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00026	HL
5393.	42	67						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00026	HL
5394.	42	68						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00026	HL
5395.	42	69						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00026	HL
5396.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00008	CL
5397.	42	70						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00026	HL
5398.	42	71						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00026	HL
5399.	42	72						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00026	HL
5400.	42	73						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00026	HL
5401.	42	74						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00026	HL
5402.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00008	CL
5403.	42	75						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00026	HL
5404.	42	76						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00026	HL
5405.	42	77						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00026	HL
5406.	42	78						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00026	HL
5407.	42	79						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00026	HL
5408.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00008	CL
5409.	42	80						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00026	HL
5410.	42	81						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00026	HL
11.	42	82						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL
12.	42	83						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
13.	42	84						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL
5414.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00004	CL
5415.	42	85						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
5416.	42	86						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL
5417.	42	87						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
5418.	42	88						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL
5419.	42	89						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
5420.								TEHTEC	B5534	rpri	A610MULC	SG20CCAL00004	CL
5421.	42	90						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL
5422.	42	91						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
5423.	42	92						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL
5424.	42	93						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
5425.								TEHTEC	B5534	rpri	A610MULC	SG20CCAL00004	CL
5426.	42	94						TSHTSH	O5305	rpri	B620MRPC3C	SG21HCAL00015	HL
5427.								TEHTEC	B5534	rpri	A610MULC	SG20CCAL00004	CL
5428.	43	22						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00033	HL
5429.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00011	CL
5430.	43	23						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00032	HL
5431.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00011	CL
5432.	43	24						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00033	HL
5433.	43	25						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00032	HL
5434.	43	26						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00033	HL
5435.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00011	CL
5436.	43	27						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00032	HL
5437.	43	28						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00033	HL
5438.	43	29						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00032	HL
5439.	43	30						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00033	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: B
 DATABASE: Harris_SGB_1995

Sep. 23.1995 14:15

PAGE 113 of 125

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
5440.	43	31						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00032	HL
5441.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00009	CL
5442.	43	32						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00033	HL
5443.	43	33						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00032	HL
5444.	43	34						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00033	HL
5445.	43	35						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00032	HL
5446.	43	36						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00032	HL
5447.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00009	CL
5448.	43	37						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00026	HL
5449.	43	38						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00025	HL
5450.	43	39						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00026	HL
5451.	43	40						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00025	HL
5452.	43	41						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00026	HL
5453.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00009	CL
5454.	43	42						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00025	HL
5455.	43	43						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00027	HL
5456.	43	44						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00025	HL
5457.	43	45						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00028	HL
5458.	43	46						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00027	HL
5459.		4.65	19	MAI	1	TEH	13.15	TEHTSH	F7460	rsec	B620MRPC3C	SG21HCAL00020	HL
60.				PID		TEH	13.15	TSHTEH	D3858	reso	B620MRPC3C	SG21HCAL00032	HL
61.		12.76	16	NQI	P1	TEH	13.84	TEHTEC	C3335	reso	A610MULC	SG20CCAL00009	CL
62.	43	47						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00028	HL
5463.	43	48						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00027	HL
5464.	43	49						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00028	HL
5465.	43	50						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00027	HL
5466.	43	51						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00028	HL
5467.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00009	CL
5468.	43	52						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00027	HL
5469.	43	53						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00028	HL
5470.	43	54						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00027	HL
5471.	43	55						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00028	HL
5472.	43	56						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00027	HL
5473.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00009	CL
5474.	43	60						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00023	HL
5475.	43	61						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00023	HL
5476.	43	62						TSHTSH	F3453	reso	B620MRPC3C	SG21HCAL00023	HL
5477.	43	63						TSHTSH	F3453	reso	B620MRPC3C	SG21HCAL00023	HL
5478.	43	64						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00023	HL
5479.								TEHTEC	M9082	rsec	A610MULC	SG20CCAL00006	CL
5480.	43	65						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00023	HL
5481.	43	66						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00025	HL
5482.	43	67						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00025	HL
5483.	43	68						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00025	HL
5484.	43	69						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00025	HL
5485.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00008	CL
5486.	43	70						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00025	HL
5487.	43	71						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00025	HL
5488.	43	72						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00025	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: B
 DATABASE: Harris_SGB_1995

Sep. 23.1995 14:15

PAGE 114 of 125

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
5489.	43	73					TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00025	HL
5490.	43	74					TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00025	HL
5491.							TEHTEC	T7072	rpri	A610MULC	SG20CCAL00008	CL
5492.	43	75					TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00025	HL
5493.	43	76					TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00025	HL
5494.	43	77					TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00025	HL
5495.	43	78					TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00025	HL
5496.	43	79					TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00025	HL
5497.							TEHTEC	T7072	rpri	A610MULC	SG20CCAL00008	CL
5498.	43	80					TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00025	HL
5499.	43	81					TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00025	HL
5500.	43	82					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL
5501.	43	83					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
5502.	43	84					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL
5503.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00004	CL
5504.	43	85					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
5505.	43	86					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL
5506.	43	87					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
5507.	43	88					TSHTSH	F7460	rsec	B620MRPC3C	SG21HCAL00017	HL
5508.	43	89					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
09.							TEHTEC	B5534	rpri	A610MULC	SG20CCAL00004	CL
10.	43	90					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL
11.	43	91					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
5512.	43	92					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL
5513.							TEHTEC	B5534	rpri	A610MULC	SG20CCAL00004	CL
5514.	43	93					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
5515.							TEHTEC	B5534	rpri	A610MULC	SG20CCAL00004	CL
5516.	44	23					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00033	HL
5517.							TEHTEC	T7072	rpri	A610MULC	SG20CCAL00011	CL
5518.	44	24					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00032	HL
5519.							TEHTEC	T7072	rpri	A610MULC	SG20CCAL00011	CL
5520.	44	25					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00033	HL
5521.	44	26					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00032	HL
5522.							TEHTEC	T7072	rpri	A610MULC	SG20CCAL00011	CL
5523.	44	27					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00033	HL
5524.	44	28					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00032	HL
5525.	44	29					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00033	HL
5526.	44	30					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00032	HL
5527.	44	31					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00033	HL
5528.							TEHTEC	T7072	rpri	A610MULC	SG20CCAL00009	CL
5529.	44	32					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00032	HL
5530.	44	33					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00033	HL
5531.	44	34					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00032	HL
5532.	44	35					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00033	HL
5533.	44	36					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00032	HL
5534.							TEHTEC	T7072	rpri	A610MULC	SG20CCAL00009	CL
35.	44	37					TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00026	HL
36.	44	38					TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00025	HL
37.	44	39					TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00026	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: B
 DATABASE: Harris_SGB_1995

Sep. 23,1995 14:15

PAGE 115 of 125

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
5538.	44	40					TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00025	HL
5539.	44	41					TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00025	HL
5540.							TEHTEC	T7072	rpri	A610MULC	SG20CCAL00009	CL
5541.	44	42					TSHTSH	C1115	rsec	B620MRPC3C	SG21HCAL00025	HL
5542.	44	43					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00027	HL
5543.	44	44					TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00025	HL
5544.	44	45					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00028	HL
5545.	44	46					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00027	HL
5546.							TEHTEC	T7072	rpri	A610MULC	SG20CCAL00009	CL
5547.	44	47					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00028	HL
5548.	44	48					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00027	HL
5549.	44	49					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00028	HL
5550.	44	50					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00027	HL
5551.	44	51					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00028	HL
5552.							TEHTEC	T7072	rpri	A610MULC	SG20CCAL00009	CL
5553.	44	52					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00027	HL
5554.	44	53					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00028	HL
5555.	44	54					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00027	HL
5556.	44	55					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00028	HL
5557.	44	56					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00027	HL
5558.							TEHTEC	T7072	rpri	A610MULC	SG20CCAL00009	CL
5559.	44	60					TSHTSH	C1115	rsec	B620MRPC3C	SG21HCAL00024	HL
5560.	44	61					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00024	HL
5561.	44	62					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00024	HL
5562.	44	63					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00024	HL
5563.	44	64					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00024	HL
5564.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00006	CL
5565.	44	65					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00024	HL
5566.	44	66					TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00026	HL
5567.	44	67					TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00026	HL
5568.	44	68					TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00026	HL
5569.	44	69					TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00026	HL
5570.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00008	CL
5571.	44	70					TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00026	HL
5572.	44	71					TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00026	HL
5573.	44	72					TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00026	HL
5574.	44	73					TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00026	HL
5575.	44	74					TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00026	HL
5576.							TEHTEC	T7072	rpri	A610MULC	SG20CCAL00008	CL
5577.	44	75					TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00026	HL
5578.	44	76					TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00026	HL
5579.	44	77					TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00026	HL
5580.	44	78					TSHTSH	F3453	reso	B620MRPC3C	SG21HCAL00026	HL
5581.	44	79					TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00026	HL
5582.							TEHTEC	T7072	rpri	A610MULC	SG20CCAL00008	CL
5583.	44	80					TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00026	HL
5584.	44	81					TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00026	HL
5585.	44	82					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL
5586.	44	83					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: B
 DATABASE: Harris_SGB_1995

Sep. 23.1995 14:15

PAGE 116 of 125

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
5587.	44	84						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL
5588.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00004	CL
5589.	44	85						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
5590.	44	86						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL
5591.	44	87						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
5592.	44	88						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL
5593.	44	89						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
5594.								TEHTEC	B5534	rpri	A610MULC	SG20CCAL00004	CL
5595.	44	90						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL
5596.	44	91						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
5597.								TEHTEC	B5534	rpri	A610MULC	SG20CCAL00004	CL
5598.	44	92						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL
5599.		0.54	167	MBM	1	07H	27.68	TEHTEC	B5534	rpri	A610MULC	SG20CCAL00004	CL
5600.		8.11	183	DNT	P1	AV3	0.00	TEHTEC	B5534	rpri	A610MULC	SG20CCAL00004	CL
5601.	45	24						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00033	HL
5602.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00011	CL
5603.	45	25						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00032	HL
5604.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00011	CL
5605.	45	26						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00033	HL
5606.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00011	CL
5607.	45	27						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00032	HL
5608.	45	28						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00033	HL
5609.	45	29						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00032	HL
5610.	45	30						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00033	HL
5611.	45	31						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00032	HL
5612.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00009	CL
5613.	45	32						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00033	HL
5614.	45	33						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00032	HL
5615.	45	34						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00033	HL
5616.	45	35						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00032	HL
5617.	45	36						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00032	HL
5618.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00009	CL
5619.	45	37						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00026	HL
5620.	45	38						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00025	HL
5621.	45	39						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00026	HL
5622.	45	40						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00025	HL
5623.	45	41						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00025	HL
5624.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00009	CL
5625.	45	42						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00025	HL
5626.	45	43						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00027	HL
5627.	45	44						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00025	HL
5628.	45	45						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00028	HL
5629.	45	46						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00027	HL
5630.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00009	CL
5631.	45	47						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00028	HL
5632.	45	48						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00027	HL
5633.	45	49						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00028	HL
5634.	45	50						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00027	HL
5635.	45	51						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00028	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: B
 DATABASE: Harris_SGB_1995

Sep. 23.1995 14:15

PAGE 117 of 125

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
5636.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00009	CL
5637.	45	52						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00027	HL
5638.	45	53						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00028	HL
5639.	45	54						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00027	HL
5640.	45	55						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00028	HL
5641.	45	56						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00027	HL
5642.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00009	CL
5643.	45	59						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00023	HL
5644.					RBD				H1274	reso	A610MULC	SG20CCAL00006	CL
5645.		0.86		27	P2	AV1	0.00	TEHTEC	H3464	rsec	A610MULC	SG20CCAL00016	CL
5646.		0.77		25	P2	AV4	0.00	TEHTEC	H3464	rsec	A610MULC	SG20CCAL00016	CL
5647.	45	60						TSHTSH	F3453	reso	B620MRPC3C	SG21HCAL00023	HL
5648.	45	61						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00023	HL
5649.	45	62						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00023	HL
5650.	45	63						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00023	HL
5651.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00009	CL
5652.		0.43		13	P2	AV2	-0.06	TEHTEC	T7072	rpri	A610MULC	SG20CCAL00016	CL
5653.	45	64						TSHTSH	F3453	reso	B620MRPC3C	SG21HCAL00023	HL
5654.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00006	CL
5655.	45	65						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00025	HL
56.	45	66						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00025	HL
7.	45	67						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00025	HL
8.	45	68						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00025	HL
5659.	45	69						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00025	HL
5660.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00008	CL
5661.	45	70						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00025	HL
5662.	45	71						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00025	HL
5663.	45	72						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00025	HL
5664.	45	73						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00025	HL
5665.	45	74						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00025	HL
5666.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00008	CL
5667.	45	75						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00025	HL
5668.	45	76						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00025	HL
5669.	45	77						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00025	HL
5670.	45	78						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00025	HL
5671.	45	79						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00025	HL
5672.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00008	CL
5673.	45	80						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00025	HL
5674.	45	81						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00025	HL
5675.	45	82						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL
5676.	45	83						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
5677.	45	84						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL
5678.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00004	CL
5679.	45	85						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
5680.	45	86						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL
5681.	45	87						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
82.	45	88						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL
83.	45	89						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
84.								TEHTEC	B5534	rpri	A610MULC	SG20CCAL00004	CL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: B
 DATABASE: Harris_SGB_1995

Sep. 23.1995 14:15

PAGE 118 of 125

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
5685.	45	90						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL
5686.		5.39	179	DNT	P1	AV3	0.09	TEHTEC	B5534	rpri	A610MULC	SG20CCAL00004	CL
5687.	45	91						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
5688.								TEHTEC	B5534	rpri	A610MULC	SG20CCAL00004	CL
5689.	46	26						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00033	HL
5690.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00011	CL
5691.	46	27						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00032	HL
5692.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00011	CL
5693.	46	28						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00033	HL
5694.	46	29						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00032	HL
5695.	46	30						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00033	HL
5696.	46	31						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00032	HL
5697.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00009	CL
5698.	46	32						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00033	HL
5699.	46	33						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00032	HL
5700.	46	34						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00033	HL
5701.	46	35						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00032	HL
5702.	46	36						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00032	HL
5703.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00009	CL
5704.	46	37						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00026	HL
05.	46	38						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00025	HL
06.	46	39						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00026	HL
07.	46	40						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00025	HL
5708.	46	41						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00025	HL
5709.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00009	CL
5710.	46	42						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00025	HL
5711.	46	43						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00027	HL
5712.	46	44						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00025	HL
5713.	46	45						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00028	HL
5714.	46	46						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00027	HL
5715.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00009	CL
5716.	46	47						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00028	HL
5717.	46	48						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00027	HL
5718.	46	49						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00028	HL
5719.	46	50						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00027	HL
5720.	46	51						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00028	HL
5721.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00009	CL
5722.	46	52						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00027	HL
5723.	46	53						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00028	HL
5724.	46	54						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00027	HL
5725.	46	55						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00028	HL
5726.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00009	CL
5727.	46	56						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00027	HL
5728.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00009	CL
5729.	46	59						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00024	HL
030.					RBD				H1274	reso	A610MULC	SG20CCAL00006	CL
031.		0.88		27	P2	AV2	0.00	TEHTEC	H3464	rsec	A610MULC	SG20CCAL00016	CL
2.		0.50		18	P2	AV4	0.00	TEHTEC	H3464	rsec	A610MULC	SG20CCAL00016	CL
033.	46	60						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00024	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: B
 DATABASE: Harris_SGB_1995

Sep. 23.1995 14:15

PAGE 119 of 125

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
5734.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00006	CL
5735.	46	61						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00024	HL
5736.	46	62						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00024	HL
5737.	46	63						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00024	HL
5738.	46	64						TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00024	HL
5739.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00006	CL
5740.	46	65						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00026	HL
5741.	46	66						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00026	HL
5742.	46	67						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00026	HL
5743.	46	68						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00026	HL
5744.	46	69						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00026	HL
5745.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00008	CL
5746.	46	70						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00026	HL
5747.	46	71						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00026	HL
5748.	46	72						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00026	HL
5749.	46	73						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00026	HL
5750.	46	74						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00026	HL
5751.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00008	CL
5752.	46	75						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00026	HL
5753.	46	76						TSHTSH	C1115	rsec	B620MRPC3C	SG21HCAL00026	HL
54.	46	77						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00026	HL
55.	46	78						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00026	HL
56.	46	79						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00026	HL
5757.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00008	CL
5758.	46	80						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00026	HL
5759.	46	81						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00026	HL
5760.	46	82						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL
5761.	46	83						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
5762.	46	84						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL
5763.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00004	CL
5764.	46	85						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
5765.	46	86						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL
5766.	46	87						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
5767.	46	88						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL
5768.								TEHTEC	B5534	rpri	A610MULC	SG20CCAL00004	CL
5769.								TEHTEC	B5534	rpri	A610MULC	SG20CCAL00004	CL
5770.	46	89						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
5771.								TEHTEC	B5534	rpri	A610MULC	SG20CCAL00004	CL
5772.	47	27						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00033	HL
5773.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00011	CL
5774.	47	28						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00032	HL
5775.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00011	CL
5776.	47	29						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00033	HL
5777.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00011	CL
5778.	47	30						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00032	HL
5779.	47	31						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00033	HL
5780.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00009	CL
5781.	47	32						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00032	HL
5782.	47	33						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00033	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: B
 DATABASE: Harris_SGB_1995

Sep. 23,1995 14:15

PAGE 120 of 125

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
5783.	47	34					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00032	HL
5784.	47	35					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00033	HL
5785.	47	36					TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00032	HL
5786.							TEHTEC	T7072	rpri	A610MJLC	SG20CCAL00009	CL
5787.	47	37					TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00026	HL
5788.	47	38					TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00025	HL
5789.	47	39					TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00026	HL
5790.	47	40					TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00025	HL
5791.	47	41					TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00025	HL
5792.							TEHTEC	T7072	rpri	A610MJLC	SG20CCAL00009	CL
5793.	47	42					TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00025	HL
5794.	47	43					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00027	HL
5795.	47	44					TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00025	HL
5796.	47	45					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00028	HL
5797.	47	46					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00027	HL
5798.							TEHTEC	T7072	rpri	A610MJLC	SG20CCAL00009	CL
5799.	47	47					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00028	HL
5800.							TEHTEC	T7072	rpri	A610MJLC	SG20CCAL00009	CL
5801.	47	48					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00027	HL
5802.							TEHTEC	T7072	rpri	A610MJLC	SG20CCAL00009	CL
5803.	47	49					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00028	HL
5804.							TEHTEC	T7072	rpri	A610MJLC	SG20CCAL00009	CL
5805.	47	50					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00027	HL
5806.							TEHTEC	T7072	rpri	A610MJLC	SG20CCAL00009	CL
5807.	47	52					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00027	HL
5808.							TEHTEC	T7072	rpri	A610MJLC	SG20CCAL00009	CL
5809.	47	53					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00028	HL
5810.							TEHTEC	T7072	rpri	A610MJLC	SG20CCAL00009	CL
5811.	47	54					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00027	HL
5812.							TEHTEC	T7072	rpri	A610MJLC	SG20CCAL00009	CL
5813.	47	55					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00028	HL
5814.							TEHTEC	T7072	rpri	A610MJLC	SG20CCAL00009	CL
5815.	47	56					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00027	HL
5816.							TEHTEC	T7072	rpri	A610MJLC	SG20CCAL00009	CL
5817.	47	59					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00023	HL
5818.							TEHTEC	F9284	rpri	A610MJLC	SG20CCAL00006	CL
5819.	47	60					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00023	HL
5820.							TEHTEC	M9082	rsec	A610MJLC	SG20CCAL00006	CL
5821.	47	61					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00023	HL
5822.							TEHTEC	F9284	rpri	A610MJLC	SG20CCAL00006	CL
5823.	47	62					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00023	HL
5824.							TEHTEC	F9284	rpri	A610MJLC	SG20CCAL00006	CL
5825.	47	63					TSHTSH	F3453	reso	B620MRPC3C	SG21HCAL00023	HL
5826.							TEHTEC	F9284	rpri	A610MJLC	SG20CCAL00006	CL
5827.	47	64					TSHTSH	F3453	reso	B620MRPC3C	SG21HCAL00023	HL
5828.							TEHTEC	F9284	rpri	A610MJLC	SG20CCAL00006	CL
5829.	47	65					TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00025	HL
5830.							TEHTEC	F9284	rpri	A610MJLC	SG20CCAL00006	CL
5831.							TEHTEC	F9284	rpri	A610MJLC	SG20CCAL00008	CL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: B
 DATABASE: Harris_SGB_1995

Sep. 23,1995 14:15

PAGE 121 of 125

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
5832.	47	66						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00025	HL
5833.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00006	CL
5834.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00008	CL
5835.	47	67						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00025	HL
5836.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00008	CL
5837.	47	68						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00025	HL
5838.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00008	CL
5839.	47	69						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00025	HL
5840.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00008	CL
5841.	47	70						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00025	HL
5842.	47	71						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00025	HL
5843.	47	72						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00025	HL
5844.		0.42		16	P2	05C	0.65	TEHTEC	C3335	reso	A610MULC	SG20CCAL00008	CL
5845.	47	73						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00025	HL
5846.	47	74						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00025	HL
5847.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00008	CL
5848.	47	75						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00025	HL
5849.	47	76						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00025	HL
5850.	47	77						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00025	HL
5851.	47	78						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00025	HL
52.	47	79						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00025	HL
53.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00008	CL
54.	47	80						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00025	HL
5855.	47	81						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00025	HL
5856.	47	82						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL
5857.	47	83						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
5858.	47	84						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL
5859.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00004	CL
5860.	47	85						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
5861.	47	86						TSHTSH	F7460	rsec	B620MRPC3C	SG21HCAL00017	HL
5862.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00004	CL
5863.	47	87						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
5864.								TEHTEC	T6956	rsec	A610MULC	SG20CCAL00004	CL
5865.	47	88						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL
5866.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00016	CL
5867.	48	29						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00033	HL
5868.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00011	CL
5869.	48	30						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00032	HL
5870.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00011	CL
5871.	48	31						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00033	HL
5872.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00009	CL
5873.	48	32						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00032	HL
5874.	48	33						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00033	HL
5875.	48	34						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00032	HL
5876.	48	35						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00033	HL
77.	48	36						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00032	HL
78.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00009	CL
79.	48	37						TSHTSH	C1115	rsec	B620MRPC3C	SG21HCAL00026	HL
80.	48	38						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00025	HL

*** INSPECTION FINAL REPORT LISTING ***

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: 8
 DATABASE: Harris_SGB_1995

Sep. 23, 1995 14:15

PAGE 122 of 125

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
5881.	48	39					TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00026	HL
5882.	48	40					TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00025	HL
5883.	48	41					TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00025	HL
5884.							TEHTEC	T7072	rpri	A610MULC	SG20CCAL00009	CL
5885.	48	42					TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00025	HL
5886.	48	43					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00027	HL
5887.							TEHTEC	T7072	rpri	A610MULC	SG20CCAL00009	CL
5888.	48	44					TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00025	HL
5889.							TEHTEC	T7072	rpri	A610MULC	SG20CCAL00009	CL
5890.	48	45					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00028	HL
5891.							TEHTEC	T7072	rpri	A610MULC	SG20CCAL00009	CL
5892.	48	46					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00027	HL
5893.							TEHTEC	T7072	rpri	A610MULC	SG20CCAL00009	CL
5894.	48	47					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00028	HL
5895.							TEHTEC	T7072	rpri	A610MULC	SG20CCAL00009	CL
5896.	48	48					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00027	HL
5897.							TEHTEC	T7072	rpri	A610MULC	SG20CCAL00009	CL
5898.	48	49					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00028	HL
5899.							TEHTEC	T7072	rpri	A610MULC	SG20CCAL00009	CL
5900.	48	50					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00027	HL
01.							TEHTEC	T7072	rpri	A610MULC	SG20CCAL00009	CL
02.	48	51					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00028	HL
03.							TEHTEC	T7072	rpri	A610MULC	SG20CCAL00009	CL
5904.	48	52					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00027	HL
5905.							TEHTEC	T7072	rpri	A610MULC	SG20CCAL00009	CL
5906.	48	53					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00028	HL
5907.							TEHTEC	T7072	rpri	A610MULC	SG20CCAL00009	CL
5908.	48	54					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00027	HL
5909.							TEHTEC	T7072	rpri	A610MULC	SG20CCAL00009	CL
5910.	48	55					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00028	HL
5911.							TEHTEC	T7072	rpri	A610MULC	SG20CCAL00009	CL
5912.	48	56					TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00027	HL
5913.							TEHTEC	T7072	rpri	A610MULC	SG20CCAL00009	CL
5914.	48	59					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00024	HL
5915.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00006	CL
5916.	48	60					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00024	HL
5917.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00006	CL
5918.	48	61					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00024	HL
5919.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00006	CL
5920.	48	62					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00024	HL
5921.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00006	CL
5922.	48	63					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00024	HL
5923.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00006	CL
5924.	48	64					TSHTSH	G1931	rpri	B620MRPC3C	SG21HCAL00024	HL
5925.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00006	CL
026.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00008	CL
027.	48	65					TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00026	HL
03.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00006	CL
029.							TEHTEC	F9284	rpri	A610MULC	SG20CCAL00008	CL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: B
 DATABASE: Harris_SGB_1995

Sep. 23.1995 14:15

PAGE 123 of 125

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
5930.	48	66						TSHTSH	F3453	reso	B620MRPC3C	SG21HCAL00026	HL
5931.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00006	CL
5932.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00008	CL
5933.	48	67						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00026	HL
5934.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00008	CL
5935.	48	68						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00026	HL
5936.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00008	CL
5937.	48	69						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00026	HL
5938.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00008	CL
5939.	48	70						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00026	HL
5940.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00008	CL
5941.	48	71						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00026	HL
5942.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00008	CL
5943.	48	72						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00026	HL
5944.		0.30		12	P2	05C	0.47	TEHTEC	T7072	rpri	A610MULC	SG20CCAL00008	CL
5945.	48	73						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00026	HL
5946.	48	74						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00026	HL
5947.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00008	CL
5948.	48	75						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00026	HL
5949.	48	76						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00026	HL
50.	48	77						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00026	HL
51.	48	78						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00026	HL
52.	48	79						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00026	HL
5953.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00008	CL
5954.	48	80						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00026	HL
5955.	48	81						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00026	HL
5956.	48	82						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL
5957.	48	83						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
5958.	48	84						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL
5959.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00004	CL
5960.	48	85						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
5961.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00004	CL
5962.	48	86						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL
5963.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00004	CL
5964.	49	31						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00033	HL
5965.		12.59	182	DNT	P1	AV1	-0.12	TEHTEC	C3335	reso	A610MULC	SG20CCAL00009	CL
5966.		41.77	178	DNT	P1	AV4	0.30	TEHTEC	T7072	rpri	A610MULC	SG20CCAL00009	CL
5967.	49	32						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00032	HL
5968.		8.75	181	DNT	P1	AV4	0.00	TEHTEC	J1978	rsec	A610MULC	SG20CCAL00009	CL
5969.	49	33						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00033	HL
5970.								TEHTEC	J1978	rsec	A610MULC	SG20CCAL00009	CL
5971.	49	35						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00033	HL
5972.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00009	CL
5973.	49	36						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00032	HL
5974.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00009	CL
5975.	49	37						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00026	HL
5976.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00009	CL
5977.	49	38						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00025	HL
5978.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00009	CL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: B
 DATABASE: Harris_SGB_1995

Sep. 23,1995 14:15

PAGE 124 of 125

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG	
5979.	49	39						TSHTSH	C1115	rsec	B620MRPC3C	SG21HCAL00026	HL	
5980.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00009	CL	
5981.	49	40						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00025	HL	
5982.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00009	CL	
5983.	49	41						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00025	HL	
5984.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00009	CL	
5985.	49	42						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00025	HL	
5986.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00009	CL	
5987.	49	43						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00028	HL	
5988.			9.94	182	DNT	P1	AV4	-0.40	TEHTEC	J1978	rsec	A610MULC	SG20CCAL00009	CL
5989.	49	44						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00027	HL	
5990.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00009	CL	
5991.	49	45						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00028	HL	
5992.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00009	CL	
5993.	49	46						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00027	HL	
5994.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00009	CL	
5995.	49	47						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00028	HL	
5996.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00009	CL	
5997.	49	48						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00027	HL	
5998.			0.82	135	MBM	P1	07C	0.29	TEHTEC	C3335	reso	A610MULC	SG20CCAL00009	CL
99.	49	49						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00028	HL	
100.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00009	CL	
101.	49	50						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00027	HL	
6002.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00009	CL	
6003.	49	51						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00028	HL	
6004.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00009	CL	
6005.	49	52						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00027	HL	
6006.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00009	CL	
6007.	49	53						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00028	HL	
6008.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00009	CL	
6009.	49	54						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00027	HL	
6010.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00009	CL	
6011.	49	55						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00027	HL	
6012.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00009	CL	
6013.	49	56						TSHTSH	I2393	rpri	B620MRPC3C	SG21HCAL00027	HL	
6014.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00009	CL	
6015.	49	59						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00026	HL	
6016.								TEHTEC	M9082	rsec	A610MULC	SG20CCAL00006	CL	
6017.	49	60						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00026	HL	
6018.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00006	CL	
6019.	49	61						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00026	HL	
6020.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00006	CL	
6021.	49	62						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00026	HL	
6022.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00006	CL	
6023.	49	63						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00026	HL	
6024.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00006	CL	
6025.	49	64						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00026	HL	
6026.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00006	CL	
6027.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00008	CL	

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: B
 DATABASE: Harris_SGB_1995

Sep. 23.1995 14:15

PAGE 125 of 125

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
6028.	49	65						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00026	HL
6029.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00006	CL
6030.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00008	CL
6031.	49	66						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00026	HL
6032.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00008	CL
6033.	49	67						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00026	HL
6034.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00008	CL
6035.	49	68						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00026	HL
6036.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00008	CL
6037.	49	69						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00026	HL
6038.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00008	CL
6039.	49	70						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00026	HL
6040.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00008	CL
6041.	49	71						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00026	HL
6042.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00008	CL
6043.	49	72						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00026	HL
6044.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00008	CL
6045.	49	73						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00026	HL
6046.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00008	CL
6047.	49	74						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00026	HL
48.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00008	CL
49.	49	75						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00026	HL
50.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00008	CL
6051.	49	76						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00026	HL
6052.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00008	CL
6053.	49	77						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00026	HL
6054.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00008	CL
6055.	49	78						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00026	HL
6056.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00008	CL
6057.	49	79						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00026	HL
6058.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00008	CL
6059.	49	80						TSHTSH	N0698	rpri	B620MRPC3C	SG21HCAL00026	HL
6060.								TEHTEC	T7072	rpri	A610MULC	SG20CCAL00008	CL
6061.	49	83						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00018	HL
6062.		6.45	176	DNT	P1	11C	0.36	TEHTEC	T6956	rsec	A610MULC	SG20CCAL00004	CL
6063.		6.12	180	DNT	P1	07C	0.24	TEHTEC	F9284	rpri	A610MULC	SG20CCAL00004	CL
6064.	49	84						TSHTSH	T9924	rpri	B620MRPC3C	SG21HCAL00017	HL
6065.								TEHTEC	F9284	rpri	A610MULC	SG20CCAL00004	CL

ABB Combustion Engineering		Multi-Frequency Eddy Current Calibration Data Sheet			Disk #		Side GT-A		
Owner: CP&L		Site/Unit: SHEARON HARRIS		Component: S/G: A (B) / C		Leg: (HOT) COLD		Date: 9/19/95	
MIZ-18A (MIZ-30) S/N- 089		Procedure: HNP-004 RO			Defect Std. (1) 14091		Additional Std. (2)		
Cal	Date	Row Line	Standard Run	Comments	Examiner Init/Level				
	Time								
001	9/19/95 0505	21 / 38	BEGIN CAL	NOT USED					
003	9/19/95 0610	21 / 38	BEGIN CAL		SP IIA				
007	9/19/95 0945	24 / 55	End Cal		SP IIA				
005	9/19/95 09:57	12 / 37	Begin CAL						
005	9-19-95 1200	14 / 39		DEAD Probe COULD NOT CAL OUT	SP II				
007	9-19-95 12:36	16 / 39	BEG CAL		SP II				
007	9-19-95 16:37	10 / 44	End Cal		SP IIA				
008	9-19-95 17:04	2,45	Begin Cal		SP IIA				
009	9-19-95 20:54	10 / 56	END CAL		JLW II				
011	9-20-95 0133	2 / 94	BEGIN CAL		SP IIA				
011	9-20-95 0520	10 / 112	END CAL		SP II				
Additional Comments: Missed Cal by 1 min End Cal 007									
Shift Supervisor Final Review of Acceptance									
Reviewed by: <u>[Signature]</u> Level <u>II</u>									
Approved by: <u>[Signature]</u> ET Level III									

ABB Combustion Engineering		Multi-Frequency Eddy Current Calibration Data Sheet			Disk #		Side <u>GT-B</u>		
Owner: CP&L		Site/Unit: SHEARON HARRIS		Component: S/G: A (B) C		Leg: <u>HOT / COLD</u>		Date: 9-19-95	
MIZ-18A (MIZ-30) S/N- <u>089</u>		Procedure: HNP-004 RO			Defect Std. (1) 14902		Additional Std. (2)		
Cal	Date	Row	Line	Standard Run		Comments	Examiner		
	Time						Init/Level		
002	9-19-95	21	/ 37	BEGIN CAL		NOT USED			
	0505								
004	9-19-95	21	/ 37	BEGIN CAL					
	0610								
004	9-14-95	30	/ 55	END CAL			SP IIA		
	0945						KA		
006	9-19-95	11	/ 37	BEGIN CAL			SP II		
	0957								
506	9-19-95	15	/ 39	END CAL			SP II		
	12:00								
008	9-19-95	17	/ 39	BEG. CAL			SP II		
	12:40								
008	9-19-95	9	/ 44	END CAL			SP IIA		
	16.39								
010	9-19-95	1	/ 45	Begin Cal			SP IIA		
	17:04								
010	9-19-95	1	/ 114	END CAL			JLW II		
	2059								
012	9-20-95	2	/ 95	BEGIN CAL			SP IIA		
	0133								
012	9-20-95	10	/ 113	END CAL			KA II		
	0520								
Additional Comments:									
Shift Supervisor Final Review of Acceptance _____									
Reviewed by: <u>Amal S. Ghose</u> Level <u>II</u>									
Approved by: _____ ET Level III									

ABB Combustion Engineering		Multi-Frequency Eddy Current Calibration Data Sheet		Disk #		Side AT-B	
Owner: CP&L		Site/Unit: SHEARON HARRIS		Component: S/G: A (B) C		Leg: (HOT) COLD	
Date: 9-20-95		MIZ-18A / MIZ-30 S/N- 089		Procedure: HNP-004 RO		Defect Std. (1) 14092	
Additional Std. (2)		Procedure:		Defect Std. (1)		Additional Std. (2)	
Cal	Date	Row Line	Standard Run	Comments	Examiner	Init/Level	
	Time						
014	9/20/95 0555	11/95	BEGIN CAL	Zone 6	DA II		
014	9/20/95 807	12/113	END CAL	Zone 6	DA IIA		
016	9/20/95 0331	21/95	Begin Cal	Zone 7,8	DA IIA		
016	9-20-95 1116	31/101	END Cal	Zone 7,8	DA IIA		
018	9-20-95 1326	41/103	Begin Cal	Zone 9	DA IIA		
018	9-20-95 1734	30/93	End Cal	Zone 11	DA IIA		
020	9-20-95 1812	11/77	Bag Cal	Zone 12	DA IIA		
20	9-20-95 2205	19/93	END CAL	ZONE 12	SP IIA		
22	9/20/95 2217	21/77	BEG CAL	ZONE 13	SP IIA		
22	9/21/95 0159	32/70	END CAL	ZONE 14	SP IIA		
24	9/21/95 0211	33/70	BEGIN CAL	ZONE 14	SP IIA		
Additional Comments: Missed 4 hr cal 018 pulled cal when it was realized the time had run over							
.Shift Supervisor, Final Review of Acceptance _____							
Reviewed by: <u>David A. Alwood</u> Level _____							
Approved by: <u>John W. Bin</u> ET Level III							

ABB Combustion Engineering		Multi-Frequency Eddy Current Calibration Data Sheet		Disk #		Side ET-13	
Owner: CP&L		Site/Unit: SHEARON HARRIS		Component: S/G: A (B)C		Leg: (HOT) COLD	
MIZ-18A / MIZ-30 S/N- 089		Procedure: HNP-004 RO		Defect Std. (1) 14092		Additional Std. (2)	
Cal	Date	Row Line	Standard Run	Comments	Examiner		
	Time				Init/Level		
024	9/21/95 0000	44/ 165	END CAL	ZONE 15	SP IIA		
026	9/21/95 0618	46/ 165	BEGIN CAL	ZONE 15	SP IIA		
026	9-21-95	43/ 41	No End Cal	Zone 16	SP IIA		
028	9-21-95 1046	49/ 43	Basin Cal	Zone 16	SP IIA		
028	=	48/ 55	No End CAL PROBG.	Knicko	SP IV		
030	9-21-95 13:07	37/ 41	Bea. CAL	Zone 17	SP II		
030	9-21-95 1744	40/ 55	END Cal	Zone 17	SP IIA		
031	9-21-95 1526	25/ 108	Begin Cal	Dents	SP IIA		
031	9-21-95 1554	16/ 52	END Cal	Dents	SP IIA		
032	9-21-95 1636	41/ 20	Bas Cal	Zone 21	SP IIA		
33	9-21-25 2027	35/ 24	END CAL	ZONE 23	SP IIA		
Additional Comments:							
Shift Supervisor Final Review of Acceptance							
Reviewed by: <u>Amel G. Alwan</u> Level <u>II</u>							
Approved by: _____ ET Level III							

9-21-95
9-21-95

ABB Combustion Engineering		Multi-Frequency Eddy Current Calibration Data Sheet			Disk #		Side GT A		
Owner: CP&L		Site/Unit: SHEARON HARRIS		Component: S/G: A (B) C		Leg: HOT COLD		Date: 9-21-95	
MIZ-19A / MIZ-30 S/N-		Procedure: HNP-004 R0			Defect Std. (1) 14091		Additional Std. (2)		
Cal	Date	Row	Standard Run		Comments	Examiner			
	Time	Line				Init/Level			
34	9-21-95 2048	33/ 25	Begin CAL			JLW II			
34	9-21-95 2255	24/ 28	END CAL			JLW II			
36	9-22-95 04:10	26/ 59	Begin CAL		LOW SIDE ZONE 18	JLW II			
36	9-22-95 801	30/ 80	END CAL		Zone 19	JLW II			
38	9-22-95 828	12 157	Begin Cal		Zone 20	JLW II			
038	9-22-95 1100	2/ 20	END CAL		Zone 21	JLW II			
040	9-22-95 1113	4/ 40	Begin Cal new probe		Zone 21	JLW II			
040	9-22-95 1355	24/ 8	END Cal		Zone 24	JLW II			
042	9-22-95 1724	23/ 19	Begin Cal		Zone 24	JLW II			
042	9-22-95 19-54	18/ 28	END CAL		Zone 25	JLW II			
044	9-22-95 20:10	20/ 28	Begin CAL		Zone 25	JLW II			
Additional Comments:									
Shift Supervisor Final Review of Acceptance _____									
Reviewed by: <u>Aunt Gaskin</u> Level <u>II</u>									
Approved by: _____ ET Level III									

ABB Combustion Engineering		Multi-Frequency Eddy Current Calibration Data Sheet			Disk #		Side GT B		
Owner: CP&L		Site/Unit: SHEARON HARRIS		Component: S/G: A (B) C		Leg: (HOT) COLD		Date: 9-21-95	
MIZ-18A / MIZ-30 S/N-		Procedure: HNP-004 RO			Defect Std. (1) 14092		Additional Std. (2)		
Cal	Date	Row Line	Standard Run		Comments	Examiner			
	Time					Init/Level			
35	9-21-95	33/24	Begin CAL			JLW II			
	2046								
35	9-21-95	24/27	END CAL			JLW II			
	2255								
37	9-22-95	29/59	Begin CAL		LOW SIDE ZONIZ 18	JLW II			
	04:10								
037	9-22-95	30/81	END CAL			JLW II			
	801								
039	9-22-95	11/57	Begin CAL		Zone 20	JLW II			
	828								
039	9-22-95	1/70	END CAL		Zone 21	JLW II			
	1100								
041	9-22-95	3/70	Begin CAL		Zone 21	JLW II			
	1113								
041	9-22-95	30/18	END CAL		Zone 24	JLW II			
	1435								
043	9-22-95	24/19	Begin CAL		Zone 24	JLW II			
	1724								
043	9-22-95	17/28	END CAL		Zone 25	JLW II			
	1954								
045	9-22-95	19/28	Begin CAL		Zone 25	JLW II			
	20:12								
Additional Comments:									
Shift Supervisor Final Review of Acceptance									
Reviewed by: <u>Frank C. Slone</u> Level <u>II</u>									
Approved by: _____ ET Level III									

ABB Combustion Engineering		Multi-Frequency Eddy Current Calibration Data Sheet		Disk #	Side GCT-B
Owner: CP&L		Site/Unit: SHEARON HARRIS	Component: S/G: AFBDC	Leg: HOT/COLD	Date: 9/23/95
MIZ-18A / MIZ-30 S/N-		Procedure: HNP-004 RO	Defect Std. (1) 14092	Additional Std. (2)	
Cal	Date	Row Line	Standard Run	Comments	Examiner
	Time				Init/Level
045	9/22/95 0005	15/17	END CAL	ZONE 27	SPTIA
047	9/23/95 0025	14/17	NEW CAL GRP	ZONE 27	SPTIA
047	9/23/95 0415	8/12	END CAL	ZONE 28	SPTIA
049	9/23/95 0450	9/12	NEW CAL GRP	ZONE 28	SPTIA
049	9-23-95 19617	1/19	END CAL	ZONE 28	SPTIA
050	9-23-95 0744	13/21	Start CAL		DLP II
050	9-23-95 0756	18/28	END CAL		DLP II
051	9-23-95 0850		Start CAL (VOID) CAL		DLP II
052	9-23-95 0929	28/29	Start CAL		DLP II
052	9-23-95 1014	27/22	END CAL		DLP II
Additional Comments:					
Shift Supervisor Final Review of Acceptance					
Reviewed by: <u>David G. Alworth</u> Level <u>II</u>					
Approved by: _____ ET Level III					

ABB Combustion Engineering		Multi-Frequency Eddy Current Calibration Data Sheet		Disk # 4/A	Side 1/A
Owner: CP&L		Site/Unit: SHEARON HARRIS	Component: S/G: A (B) C	Leg: HOT (COLD)	Date: 9-18-95
MIZ-18A / MIZ-30 S/N 111		Procedure: HNP-004 RO	Defect Std. (1) Z-8712	Additional Std. (2) Z-8716	
Cal	Date	Row Line	Standard Run	Comments	Examiner Init/Level
	Time				
000 JR	6:50 9-18-95				JR
0001	9-18-95 6:50	21/41	BEGIN CAL		MB/II
001	9-18 9:36	10/56	END CAL		MB/II
002	9-18 9:38	1/94	BEGIN CAL		MB/II
002	9-18 1311	9/96	END CAL		MB/II
003	9-18 1320	11/94	START CAL		MB/II
003	9-18 1700	31-94			
003	9/18 1652	28-97	END CAL		MB/II
004	9/18 1700	31-94	START CAL		MB/II
004	9-18-95 2037	30-89	END CAL		WB/II
005	9-18-95 2043	2089	START CAL		WB/II
Additional Comments:					
Shift Supervisor Final Review of Acceptance					
Reviewed by: <u>Arund C. Alvarado</u> Level <u>II</u>					
Approved by: _____ ET Level III					

ABB Combustion Engineering		Multi-Frequency Eddy Current Calibration Data Sheet			Disk # N/A	Side N/A
Owner: CP&L		Site/Unit: SHEARON HARRIS	Component: SIG: A (B) C		Leg: HOT / COLD	Date: 9-18-95
MIZ-18A / MIZ-30 SAT 111		Procedure: HNP-004 R0		Defect Std. (1) Z-8712	Additional Std. (2) Z-8716	
Cal	Date	Row Line	Standard Run	Comments	Examiner	
	Time				Init/Level	
0005	9-19-95 12:30	31-59	END CALS.		WB	II
0006	9-19-95 12:33	41-59	START CALS.		WB	II
0006	9-19 01:54	48-66	END CALS.		WB	II
0007	9-19-95 02:38	49-66	START CALS.	VOID	WB	II
0008	9-19-95 05:26	48-64	START CAL		TE	II
0008	9-19-95 09:40	47-72	END CALS		GNF	II
0009	9-19-95 09:46	45-63	START CAL		RBW	II
0009	9-19-95 13:10	49-35	END CAL		RBW	II
0010	9-19-95 13:30	21-59	START CAL		RBW	II
0016	9-19-95 15:32	14-72	END CAL		RBW	II
0011	9-19-95 15:38	1-57	START CAL		RBW	II
Additional Comments: 4 hr cal missed end cal 008 pulled when realized it had been missed						
Shift Supervisor Final Review of Acceptance						
Reviewed by: <u>Samuel Alford</u>		Level: <u>9-24-95</u>				
Approved by: <u>John Boi</u>		ET Level III				

ABB Combustion Engineering		Multi-Frequency Eddy Current Calibration Data Sheet		Disk #	Side
Owner: CP&L		Site/Unit: SHEARON HARRIS	Component: S/G: A (B) C	Log: HOT (COLD)	Date: 9-19-95
(MIZ-18A) / MIZ-30 SIN- 111		Procedure: HNP-004 RO	Defect Std. (1) Z-8712	Additional Std. (2) Z-8716	
Cal	Date Time	Row Line	Standard Run	Comments	Examiner Init/Level
0011	9-19-95 18:18	41-34	END CAL		RWB II
0012	9-19-95 18:22	31-11	START CAL		WAB II
0012	9-19-95 22:15	19-26	End Cal		WAB II
0013	9-19-95 00107	20-26	Start Cal		WAB II
0013	9-20-95 03:43	22-16	End Cal		WAB II
0014	9-20-95 03:50	2-1	Start Cal		WAB II
0014	9-20-95 05:42	1-19	End Cal		KGS II
0015	9-20-95 7:10	Re Runs	Start Cals	Retest tubes	GAF II
0015	9-20-95 7:50	Re Runs	End Cals NA BAD Probe	READ ONLY 2 Tubes will re-run next cal group	GAF II
0016	9-20-95 09:26	Re RUNS	START CAL		MB II
0016	9-20-95 10:50	Re RUNS	END CAL		MB II
Additional Comments:					
Shift Supervisor Final Review of Acceptance					
Reviewed by: <u>Donald A. Storch</u> Level <u>II</u>					
Approved by: _____ ET Level III					

ABB Combustion Engineering		Multi-Frequency Eddy Current Calibration Data Sheet		Disk #		Side	
Owner: CP&L		Site/Unit: SHEARON HARRIS		Component: S/G: A (B) C		Leg: HOT (COLD)	
Date: 9-20-95		MIZ-18A MIZ-30 S/N: 111		Procedure: HNP-004 RO		Defect Std. (1) 2-8712	
						Additional Std. (2) Z-8716	
Cal	Date	Row Line	Standard Run	Comments	Examiner		
	Time					Init/Level	
017	9-20-95	11-74	START CAL	Retest	DLP II		
	1226						
017	9-20-95	6-56	END CAL		DLP II		
	1352						
018	9-20-95		START CAL	Res.	DLP II		
	1454						
018	9-20-95		END CAL	"	DLP II		
	1526						
019	9-20-95		START CAL	u-Bend MRPC	RLY II		
	1953						
019	9-20-95	1-17	END CAL	"	RLY II		
	2347						
020	9-20-95	1-70	START CAL	"	RLY II		
	2351						
020	9-21-95	1-70	END CAL	"	RLY II		
	0120						
021	9-21-95	1-70	START CAL	"	RLY II		
	0129						
021	9-21-95	1-75	END CAL	"	RLY II		
	0247						
022	9-21-95	1-3	START CAL	Dents	RLY II		
	0333						
Additional Comments:							
Shift Supervisor Final Review of Acceptance							
Reviewed by: <u>Amel A. Shoch</u> Level <u>II</u>							
Approved by: _____ ET Level III							

ABB Combustion Engineering		Multi-Frequency Eddy Current Calibration Data Sheet			Disk #		Side		
Owner: CP&L		Site/Unit: SHEARON HARRIS		Component: SIG: A / (B) C		Leg: HOT / (COLD)		Date: 9-21-95	
(MIZ-18A) MIZ-30 S/N 111		Procedure: HNP-004 RO		Defect Std. (1) Z-8712		Additional Std. (2) Z-8716			
Cal	Date	Row Line	Standard Run	Comments	Examiner				
	Time				Init/Level				
022	9-21-95 0406	30-10	END CAL		RLY II				
023	9-21-95 0424	30-10	START CAL		RLY II				
023	9-21-95 0440	1-3	END CAL		RLY II				
024	9-21-95 0619	1-12	START CAL		RLY II				
024	9-21-95 0800	2-10	END CAL	NO ENDING CAL BAD PROBE	LACTE				
025	9-21-95 0830		START CAL	NO TUBES RUN	LACTE				
			PROBE DIED NO ENDING CALS		LAC				
026	9-21-95 1027	2-14	START CAL		LAC				
026	9-21-95 1117	1-44	END CAL		LAC				
027	9-21-95 1326	2-10	START CAL	ReRun 3 Tubes	LRO				
027	9-21-95 1401	1-17	END CAL		LRO TE II				
Additional Comments:									
Shift Supervisor.Final.Review.of Acceptance _____									
Reviewed by: <u>Amal G. Alwakh</u> Level <u>II</u>									
Approved by: <u>Ther...</u> ET Level III									

UTILITY: Carolina Power & Light

Sep. 23.1995 14:28

PLANT: Shearon Harris

UNIT: 1

SG: C

DATABASE: Harris_SGC_1995

PAGE 1 of 128

* INSPECTION FINAL REPORT LISTING *

*** This report contains all report entries appended to the database for the following test plans ***

All Test Plans in the database are included in summary: 11

Test Plan Name:	Probe Type:	Probe Size:	Type:
1. Top of Tubesheet HL Exam	MRPC	B620MRPC3C	HL
2. CL Bobbin Exam	BOBBIN	A610MULC	CL
3. Row 1&2 Ubend CL Exam	MRPC	B580MRPCPH	CL
4. 20% of Dented Intersections	MRPC	B620MRPC3C	HL
5. 20% of Dented Intersection	MRPC	B620MRPC3C	HL
6. 20% of Dented Intersections	MRPC	B620MRPC3C	CL
7. 20% of Dented Intersection	MRPC	B620MRPC3C	CL
8. Previous Indications	BOBBIN	A610MULC	CL
9. Special Interest	MRPC	B620MRPC3C	HL
10. Special Interest	MRPC	B620MRPC3C	CL
11. Pre-Heater Expanded Exam	MRPC	B620MRPC3C	CL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: C
 DATABASE: Harris_SGC_1995

Sep. 23,1995 14:28

PAGE 2 of 128

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
1.	1	1						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00043	HL
2.								11CTEC	05305	rpri	A610MULC	SG30CCAL00012	CL
3.	1	2						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00043	HL
4.								11CTEC	05305	rpri	A610MULC	SG30CCAL00012	CL
5.	1	3						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00043	HL
6.								11CTEC	05305	rpri	A610MULC	SG30CCAL00012	CL
7.	1	4						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00043	HL
8.								11CTEC	05305	rpri	A610MULC	SG30CCAL00012	CL
9.	1	5						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00043	HL
10.								11CTEC	05305	rpri	A610MULC	SG30CCAL00012	CL
11.	1	6						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00043	HL
12.								11CTEC	05305	rpri	A610MULC	SG30CCAL00012	CL
13.	1	7						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00043	HL
14.								11CTEC	05305	rpri	A610MULC	SG30CCAL00012	CL
15.	1	8						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00043	HL
16.								11CTEC	05305	rpri	A610MULC	SG30CCAL00012	CL
17.	1	9						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00043	HL
18.								11CTEC	05305	rpri	A610MULC	SG30CCAL00012	CL
19.	1	10						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00043	HL
20.								11CTEC	05305	rpri	A610MULC	SG30CCAL00012	CL
21.	1	11						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00043	HL
22.								11CTEC	05305	rpri	A610MULC	SG30CCAL00012	CL
23.	1	12						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00043	HL
24.								11CTEC	05305	rpri	A610MULC	SG30CCAL00012	CL
25.								11H11C	S7675	rpri	B580MRPCPH	SG30CCAL00019	CL
26.	1	13						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00043	HL
27.								11CTEC	05305	rpri	A610MULC	SG30CCAL00012	CL
28.	1	14						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00043	HL
29.								11CTEC	T6956	rsec	A610MULC	SG30CCAL00012	CL
30.	1	15						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00043	HL
31.								11CTEC	05305	rpri	A610MULC	SG30CCAL00012	CL
32.	1	16						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00043	HL
33.					RIC			10CTEC	05305	rpri	A610MULC	SG30CCAL00012	CL
34.								11CTEC	T7665	rpri	A610MULC	SG30CCAL00014	CL
35.	1	17						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00043	HL
36.					RIC			10CTEC	05305	rpri	A610MULC	SG30CCAL00012	CL
37.								11CTEC	T7665	rpri	A610MULC	SG30CCAL00014	CL
38.								11H11C	N0698	rpri	B580MRPCPH	SG30CCAL00017	CL
39.	1	18						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00043	HL
40.					RIC			10CTEC	05305	rpri	A610MULC	SG30CCAL00012	CL
41.								11CTEC	T7665	rpri	A610MULC	SG30CCAL00014	CL
42.	1	19						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00043	HL
43.								11CTEC	05305	rpri	A610MULC	SG30CCAL00012	CL
44.	1	20						TSHTSH	D3858	reso	B620MRPC3C	SG31HCAL00040	HL
45.								TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL
46.								11CTEC	N0698	rpri	A610MULC	SG30CCAL00010	CL
47.	1	21						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL
48.								11CTEC	N0698	rpri	A610MULC	SG30CCAL00010	CL
49.	1	22						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: C
 DATABASE: Harris_SGC_1995

Sep. 23.1995 14:28

PAGE 3 of 128

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
50.								11CTEC	N0698	rpri	A610MULC	SG30CCAL00010	CL
51.	1	23						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL
52.								11CTEC	N0698	rpri	A610MULC	SG30CCAL00010	CL
53.	1	24						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL
54.								11CTEC	N0698	rpri	A610MULC	SG30CCAL00010	CL
55.	1	25						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL
56.								11CTEC	N0698	rpri	A610MULC	SG30CCAL00010	CL
57.	1	26						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL
58.								11CTEC	N0698	rpri	A610MULC	SG30CCAL00010	CL
59.	1	27						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL
60.								11CTEC	T9924	rpri	A610MULC	SG30CCAL00023	CL
61.								11H11C	I2393	rpri	B580MRPCPH	SG30CCAL00016	CL
62.	1	28						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL
63.								11CTEC	T9924	rpri	A610MULC	SG30CCAL00024	CL
64.	1	29						TSHTSH	F7460	rsec	B620MRPC3C	SG31HCAL00040	HL
65.								11CTEC	T9924	rpri	A610MULC	SG30CCAL00024	CL
66.	1	30						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL
67.								11CTEC	T9924	rpri	A610MULC	SG30CCAL00024	CL
68.	1	31						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL
69.								11CTEC	T9924	rpri	A610MULC	SG30CCAL00024	CL
70.	1	32						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL
71.								11CTEC	N0698	rpri	A610MULC	SG30CCAL00011	CL
72.								11H11C	I2393	rpri	B580MRPCPH	SG30CCAL00016	CL
73.	1	33						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00040	HL
74.								11CTEC	N0698	rpri	A610MULC	SG30CCAL00011	CL
75.	1	34						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00040	HL
76.								11CTEC	N0698	rpri	A610MULC	SG30CCAL00011	CL
77.	1	35						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00040	HL
78.								11CTEC	N0698	rpri	A610MULC	SG30CCAL00011	CL
79.	1	36						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00040	HL
80.								11CTEC	N0698	rpri	A610MULC	SG30CCAL00011	CL
81.	1	37						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00008	HL
82.								11CTEC	P4202	rpri	A610MULC	SG30CCAL00002	CL
83.	1	38						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00008	HL
84.								11CTEC	P4202	rpri	A610MULC	SG30CCAL00002	CL
85.	1	39						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00008	HL
86.								11CTEC	P4202	rpri	A610MULC	SG30CCAL00002	CL
87.						RBD			T7665	rpri	B580MRPCPH	SG30CCAL00015	CL
88.								11H11C	S7675	rpri	B580MRPCPH	SG30CCAL00019	CL
89.	1	40						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00008	HL
90.								11CTEC	P4202	rpri	A610MULC	SG30CCAL00002	CL
91.	1	41						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00023	HL
92.								TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00024	HL
93.								11CTEC	P4202	rpri	A610MULC	SG30CCAL00002	CL
94.	1	42						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00024	HL
95.								11CTEC	P4202	rpri	A610MULC	SG30CCAL00002	CL
96.						RBD			T7665	rpri	B580MRPCPH	SG30CCAL00015	CL
97.								11H11C	S7675	rpri	B580MRPCPH	SG30CCAL00019	CL
98.	1	43						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00008	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: C
 DATABASE: Harris_SGC_1995

Sep. 23,1995 14:28

PAGE 4 of 128

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
99.							11CTEC	P4202	rpri	A610MULC	SG30CCAL00002	CL
100.	1	44					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00008	HL
101.							11CTEC	P4202	rpri	A610MULC	SG30CCAL00002	CL
102.							11H11C	T7665	rpri	B580MRPCPH	SG30CCAL00015	CL
103.	1	45					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00008	HL
104.							11CTEC	P4202	rpri	A610MULC	SG30CCAL00002	CL
105.	1	46					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00008	HL
106.							11CTEC	P4202	rpri	A610MULC	SG30CCAL00002	CL
107.	1	47					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00008	HL
108.							11CTEC	P4202	rpri	A610MULC	SG30CCAL00002	CL
109.							11H11C	T7665	rpri	B580MRPCPH	SG30CCAL00015	CL
110.	1	48					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00008	HL
111.							11CTEC	P4202	rpri	A610MULC	SG30CCAL00002	CL
112.	1	49					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00008	HL
113.							11CTEC	P4202	rpri	A610MULC	SG30CCAL00002	CL
114.	1	50					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00008	HL
115.							11CTEC	P4202	rpri	A610MULC	SG30CCAL00002	CL
116.					RBD		T7665	rpri	B580MRPCPH	SG30CCAL00015	CL	
117.							11H11C	S7675	rpri	B580MRPCPH	SG30CCAL00019	CL
118.	1	51					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00008	HL
119.							11CTEC	P4202	rpri	A610MULC	SG30CCAL00002	CL
120.	1	52					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00008	HL
121.							11CTEC	P4202	rpri	A610MULC	SG30CCAL00002	CL
122.	1	53					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00008	HL
123.							11CTEC	P4202	rpri	A610MULC	SG30CCAL00002	CL
124.							11H11C	T7665	rpri	B580MRPCPH	SG30CCAL00015	CL
125.	1	54					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00008	HL
126.							11CTEC	P4202	rpri	A610MULC	SG30CCAL00002	CL
127.	1	55					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00008	HL
128.							11CTEC	P4202	rpri	A610MULC	SG30CCAL00002	CL
129.	1	56					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00008	HL
130.							11CTEC	P4202	rpri	A610MULC	SG30CCAL00002	CL
131.							11H11C	T7665	rpri	B580MRPCPH	SG30CCAL00016	CL
132.	1	57					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
133.							11CTEC	P4202	rpri	A610MULC	SG30CCAL00008	CL
134.	1	58					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
135.							11CTEC	P4202	rpri	A610MULC	SG30CCAL00008	CL
136.	1	59					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
137.							11CTEC	P4202	rpri	A610MULC	SG30CCAL00008	CL
138.							11H11C	S7675	rpri	B580MRPCPH	SG30CCAL00019	CL
139.	1	60					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
140.							11CTEC	P4202	rpri	A610MULC	SG30CCAL00008	CL
141.	1	61					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
142.							11CTEC	P4202	rpri	A610MULC	SG30CCAL00008	CL
143.	1	62					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
144.							11CTEC	P4202	rpri	A610MULC	SG30CCAL00008	CL
145.	1	63					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
146.							11CTEC	P4202	rpri	A610MULC	SG30CCAL00008	CL
147.	1	64					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: C
 DATABASE: Harris_SGC_1995

Sep. 23.1995 14:28

PAGE 5 of 128

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
148.							11CTEC	P4202	rpri	A610MULC	SG30CCAL00008	CL
149.							11H11C	N0698	rpri	B580MRPCPH	SG30CCAL00018	CL
150.	1	65					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
151.							11CTEC	P4202	rpri	A610MULC	SG30CCAL00008	CL
152.	1	66					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
153.							11CTEC	P4202	rpri	A610MULC	SG30CCAL00008	CL
154.	1	67					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
155.							11CTEC	P4202	rpri	A610MULC	SG30CCAL00008	CL
156.	1	68					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
157.							11CTEC	P4202	rpri	A610MULC	SG30CCAL00008	CL
158.							11H11C	N0698	rpri	B580MRPCPH	SG30CCAL00018	CL
159.	1	69					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
160.							11CTEC	P4202	rpri	A610MULC	SG30CCAL00008	CL
161.	1	70					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
162.							11CTEC	P4202	rpri	A610MULC	SG30CCAL00008	CL
163.							11H11C	N0698	rpri	B580MRPCPH	SG30CCAL00018	CL
164.	1	71					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
165.							11CTEC	P4202	rpri	A610MULC	SG30CCAL00008	CL
166.	1	72					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
167.							11CTEC	P4202	rpri	A610MULC	SG30CCAL00008	CL
68.	1	73					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
70.							11CTEC	P4202	rpri	A610MULC	SG30CCAL00008	CL
70.	1	74					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
171.							11CTEC	C1115	rsec	A610MULC	SG30CCAL00008	CL
172.	1	75					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
173.							11CTEC	P4202	rpri	A610MULC	SG30CCAL00008	CL
174.							11H11C	N0698	rpri	B580MRPCPH	SG30CCAL00018	CL
175.	1	76					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
176.							11CTEC	P4202	rpri	A610MULC	SG30CCAL00008	CL
177.							11H11C	T9924	rpri	B580MRPCPH	SG30CCAL00022	CL
178.	1	77					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00018	HL
179.							11CTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL
180.					RES		11C11C	F3453	reso	B580MRPCPH	SG30CCAL00022	CL
181.							11C11H	D4825	reso	B580MRPCPH	SG31HCAL00045	CL
182.					RES		11C11C	D4825	reso	B580MRPCPH	SG30CCAL00019	CL
183.	1	78					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00018	HL
184.							11CTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL
185.							11H11C	T9924	rpri	B580MRPCPH	SG30CCAL00022	CL
186.	1	79					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00018	HL
187.							11CTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL
188.	1	80					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00018	HL
189.							11CTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL
190.	1	81					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00018	HL
191.							11CTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL
192.	1	82					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00018	HL
193.							11CTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL
74.	1	83					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00018	HL
75.							11CTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL
96.	1	84					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00018	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: C
 DATABASE: Harris_SGC_1995

Sep. 23, 1995 14:28

PAGE 6 of 128

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
197.								11CTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL
198.								11H11C	N0698	rpri	B580MRPCPH	SG30CCAL00017	CL
199.	1	85						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00018	HL
200.								11CTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL
201.	1	86						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00018	HL
202.								11CTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL
203.								11H11C	N0698	rpri	B580MRPCPH	SG30CCAL00017	CL
204.	1	87						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00018	HL
205.								11CTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL
206.	1	88						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00018	HL
207.								11CTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL
208.								11H11C	N0698	rpri	B580MRPCPH	SG30CCAL00017	CL
209.	1	89						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
210.								11CTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL
211.	1	90						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
212.								11CTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL
213.	1	91						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
214.								11CTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL
215.	1	92						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
216.								11CTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL
17.	1	93						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
19.								11CTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL
19.	1	94						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
220.								11CTEC	P4202	rpri	A610MULC	SG30CCAL00002	CL
221.	1	95						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
222.								11CTEC	P4202	rpri	A610MULC	SG30CCAL00002	CL
223.	1	96						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
224.								11CTEC	P4202	rpri	A610MULC	SG30CCAL00002	CL
225.	1	97						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
226.								11CTEC	P4202	rpri	A610MULC	SG30CCAL00002	CL
227.	1	98						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
228.								11CTEC	P4202	rpri	A610MULC	SG30CCAL00002	CL
229.	1	99						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
230.								11CTEC	P4202	rpri	A610MULC	SG30CCAL00002	CL
231.	1	100						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
232.								11CTEC	P4202	rpri	A610MULC	SG30CCAL00002	CL
233.	1	101						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
234.								11CTEC	P4202	rpri	A610MULC	SG30CCAL00002	CL
235.	1	102						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
236.								11CTEC	P4202	rpri	A610MULC	SG30CCAL00002	CL
237.								11H11C	N0698	rpri	B580MRPCPH	SG30CCAL00017	CL
238.	1	103						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
239.								11CTEC	P4202	rpri	A610MULC	SG30CCAL00002	CL
240.	1	104						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
241.								11CTEC	P4202	rpri	A610MULC	SG30CCAL00002	CL
242.								11H11C	N0698	rpri	B580MRPCPH	SG30CCAL00017	CL
243.	1	105						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
244.								11CTEC	P4202	rpri	A610MULC	SG30CCAL00002	CL
245.	1	106						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: C
 DATABASE: Harris_SGC_1995

Sep. 23.1995 14:28

PAGE 7 of 128

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
246.							11CTEC	P4202	rpri	A610MULC	SG30CCAL00002	CL
247.	1	107					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
248.							11CTEC	P4202	rpri	A610MULC	SG30CCAL00002	CL
249.	1	108					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
250.							11CTEC	P4202	rpri	A610MULC	SG30CCAL00002	CL
251.	1	109					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
252.							11CTEC	P4202	rpri	A610MULC	SG30CCAL00002	CL
253.	1	110					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
254.							11CTEC	P4202	rpri	A610MULC	SG30CCAL00002	CL
255.	1	111					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
256.							11CTEC	P4202	rpri	A610MULC	SG30CCAL00002	CL
257.	1	112					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
258.							11CTEC	P4202	rpri	A610MULC	SG30CCAL00002	CL
259.	1	113					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
260.							11CTEC	P4202	rpri	A610MULC	SG30CCAL00002	CL
261.	1	114					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
262.							11CTEC	P4202	rpri	A610MULC	SG30CCAL00002	CL
263.	2	1					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00042	HL
264.							11CTEC	N0698	rpri	A610MULC	SG30CCAL00012	CL
265.	2	2					01HTSH	D3858	reso	B620MRPC3C	SG31HCAL00043	HL
266.							11CTEC	N0698	rpri	A610MULC	SG30CCAL00012	CL
267.	2	3					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00042	HL
268.							11CTEC	N0698	rpri	A610MULC	SG30CCAL00012	CL
269.	2	4					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00043	HL
270.							11CTEC	N0698	rpri	A610MULC	SG30CCAL00012	CL
271.	2	5					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00042	HL
272.							11CTEC	N0698	rpri	A610MULC	SG30CCAL00012	CL
273.	2	6					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00043	HL
274.							11CTEC	N0698	rpri	A610MULC	SG30CCAL00012	CL
275.	2	7					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00042	HL
276.							11CTEC	N0698	rpri	A610MULC	SG30CCAL00012	CL
277.	2	8					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00043	HL
278.							11CTEC	N0698	rpri	A610MULC	SG30CCAL00012	CL
279.	2	9					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00042	HL
280.							11CTEC	N0698	rpri	A610MULC	SG30CCAL00012	CL
281.	2	10					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00043	HL
282.							11CTEC	N0698	rpri	A610MULC	SG30CCAL00012	CL
283.							11H11C	N0698	rpri	B580MRPCPH	SG30CCAL00017	CL
284.	2	11					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00042	HL
285.							11CTEC	N0698	rpri	A610MULC	SG30CCAL00012	CL
286.	2	12					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00043	HL
287.							11CTEC	05305	rpri	A610MULC	SG30CCAL00012	CL
288.	2	13					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00042	HL
289.							11CTEC	05305	rpri	A610MULC	SG30CCAL00012	CL
290.	2	14					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00043	HL
291.							11CTEC	05305	rpri	A610MULC	SG30CCAL00012	CL
292.							11H11C	N0698	rpri	B580MRPCPH	SG30CCAL00017	CL
293.	2	15					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00042	HL
294.							11CTEC	05305	rpri	A610MULC	SG30CCAL00012	CL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: C
 DATABASE: Harris_SGC_1995

Sep. 23.1995 14:28

PAGE 8 of 128

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
295.	2	16					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00043	HL
296.							11CTEC	05305	rpri	A610MULC	SG30CCAL00012	CL
297.							11H11C	N0698	rpri	B580MRPCPH	SG30CCAL00017	CL
298.	2	17					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00042	HL
299.							11CTEC	05305	rpri	A610MULC	SG30CCAL00012	CL
300.	2	18					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00043	HL
301.							11CTEC	05305	rpri	A610MULC	SG30CCAL00012	CL
302.							11H11C	N0698	rpri	B580MRPCPH	SG30CCAL00017	CL
303.	2	19					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00043	HL
304.							11CTEC	05305	rpri	A610MULC	SG30CCAL00012	CL
305.	2	20					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL
306.							TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL
307.							11CTEC	N0698	rpri	A610MULC	SG30CCAL00010	CL
308.	2	21					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL
309.							11CTEC	N0698	rpri	A610MULC	SG30CCAL00010	CL
310.	2	22					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL
311.							11CTEC	N0698	rpri	A610MULC	SG30CCAL00010	CL
312.	2	23					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL
313.							11CTEC	N0698	rpri	A610MULC	SG30CCAL00010	CL
314.							11H11C	I2393	rpri	B580MRPCPH	SG30CCAL00016	CL
15.	2	24					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL
6.							11CTEC	N0698	rpri	A610MULC	SG30CCAL00010	CL
17.	2	25					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL
318.							11CTEC	N0698	rpri	A610MULC	SG30CCAL00010	CL
319.	2	26					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL
320.							11CTEC	N0698	rpri	A610MULC	SG30CCAL00010	CL
321.	2	27					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL
322.							11CTEC	T9924	rpri	A610MULC	SG30CCAL00023	CL
323.	2	28					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL
324.							11CTEC	T9924	rpri	A610MULC	SG30CCAL00024	CL
325.	2	29					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL
326.							TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL
327.							11CTEC	T9924	rpri	A610MULC	SG30CCAL00024	CL
328.	2	30					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL
329.							11CTEC	T9924	rpri	A610MULC	SG30CCAL00024	CL
330.							11H11C	I2393	rpri	B580MRPCPH	SG30CCAL00016	CL
331.	2	31					01HTSH	04825	reso	B620MRPC3C	SG31HCAL00041	HL
332.							11CTEC	T9924	rpri	A610MULC	SG30CCAL00024	CL
333.	2	32					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00041	HL
334.							11CTEC	N0698	rpri	A610MULC	SG30CCAL00011	CL
335.	2	33					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00041	HL
336.							11CTEC	N0698	rpri	A610MULC	SG30CCAL00011	CL
337.	2	34					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00041	HL
338.							11CTEC	N0698	rpri	A610MULC	SG30CCAL00011	CL
339.	2	35					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00041	HL
40.							11CTEC	N0698	rpri	A610MULC	SG30CCAL00011	CL
11.							11H11C	S7675	rpri	B580MRPCPH	SG30CCAL00019	CL
2.	2	36					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00041	HL
3.							11CTEC	N0698	rpri	A610MULC	SG30CCAL00011	CL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: C
 DATABASE: Harris_SGC_1995

Sep. 23.1995 14:28

PAGE 9 of 128

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
344.	2	37						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00007	HL
345.								11CTEC	P4202	rpri	A610MULC	SG30CCAL00002	CL
346.								11H11C	S7675	rpri	B580MRPCPH	SG30CCAL00019	CL
347.	2	38						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00007	HL
348.								11CTEC	P4202	rpri	A610MULC	SG30CCAL00002	CL
349.	2	39						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00007	HL
350.								11CTEC	P4202	rpri	A610MULC	SG30CCAL00002	CL
351.	2	40						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00007	HL
352.								11CTEC	P4202	rpri	A610MULC	SG30CCAL00002	CL
353.	2	41			RBD			H1274	reso		B620MRPC3C	SG31HCAL00007	HL
354.								TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00029	HL
355.								11CTEC	P4202	rpri	A610MULC	SG30CCAL00002	CL
356.	2	42						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00007	HL
357.								11CTEC	P4202	rpri	A610MULC	SG30CCAL00002	CL
358.	2	43						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00007	HL
359.								11CTEC	P4202	rpri	A610MULC	SG30CCAL00002	CL
360.	2	44						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00007	HL
361.								11CTEC	P4202	rpri	A610MULC	SG30CCAL00002	CL
362.	2	45						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00007	HL
363.								11CTEC	P4202	rpri	A610MULC	SG30CCAL00002	CL
64.	2	46						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00007	HL
5.								11CTEC	P4202	rpri	A610MULC	SG30CCAL00002	CL
66.								11H11C	T7665	rpri	B580MRPCPH	SG30CCAL00015	CL
367.	2	47						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00007	HL
368.								11CTEC	P4202	rpri	A610MULC	SG30CCAL00002	CL
369.	2	48						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00007	HL
370.								11CTEC	P4202	rpri	A610MULC	SG30CCAL00002	CL
371.	2	49						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00007	HL
372.								11CTEC	P4202	rpri	A610MULC	SG30CCAL00002	CL
373.								11H11C	T7665	rpri	B580MRPCPH	SG30CCAL00015	CL
374.	2	50						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00007	HL
375.								11CTEC	P4202	rpri	A610MULC	SG30CCAL00002	CL
376.	2	51						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00007	HL
377.								11CTEC	P4202	rpri	A610MULC	SG30CCAL00002	CL
378.	2	52						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00007	HL
379.								11CTEC	P4202	rpri	A610MULC	SG30CCAL00002	CL
380.	2	53						TSHTSH	K6733	rsec	B620MRPC3C	SG31HCAL00007	HL
381.					RBD			H1274	reso		B620MRPC3C	SG31HCAL00007	HL
382.								11CTEC	P4202	rpri	A610MULC	SG30CCAL00002	CL
383.	2	54						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00007	HL
384.								11CTEC	P4202	rpri	A610MULC	SG30CCAL00002	CL
385.	2	55						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00007	HL
386.								11CTEC	P4202	rpri	A610MULC	SG30CCAL00002	CL
387.								11H11C	T7665	rpri	B580MRPCPH	SG30CCAL00015	CL
388.	2	56						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00007	HL
389.								11CTEC	P4202	rpri	A610MULC	SG30CCAL00002	CL
90.	2	57						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
91.								11CTEC	P4202	rpri	A610MULC	SG30CCAL00008	CL
92.	2	58						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: C
 DATABASE: Harris_SGC_1995

Sep. 23.1995 14:28

PAGE 10 of 128

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
393.								11CTEC	P4202	rpri	A610MULC	SG30CCAL00008	CL
394.	2	59						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
395.								11CTEC	P4202	rpri	A610MULC	SG30CCAL00008	CL
396.	2	60						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
397.								11CTEC	P4202	rpri	A610MULC	SG30CCAL00008	CL
398.	2	61						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
399.								11CTEC	P4202	rpri	A610MULC	SG30CCAL00008	CL
400.	2	62						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
401.								11CTEC	P4202	rpri	A610MULC	SG30CCAL00008	CL
402.								11H11C	N0698	rpri	B580MRPCPH	SG30CCAL00018	CL
403.	2	63						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
404.								11CTEC	P4202	rpri	A610MULC	SG30CCAL00008	CL
405.	2	64						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
406.								11CTEC	P4202	rpri	A610MULC	SG30CCAL00008	CL
407.	2	65						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
408.								11CTEC	P4202	rpri	A610MULC	SG30CCAL00008	CL
409.	2	66						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
410.								11CTEC	P4202	rpri	A610MULC	SG30CCAL00008	CL
411.								11H11C	N0698	rpri	B580MRPCPH	SG30CCAL00018	CL
412.	2	67						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
13.								11CTEC	P4202	rpri	A610MULC	SG30CCAL00008	CL
4.	2	68						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
415.								11CTEC	P4202	rpri	A610MULC	SG30CCAL00008	CL
416.	2	69						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
417.								11CTEC	P4202	rpri	A610MULC	SG30CCAL00008	CL
418.	2	70						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
419.								11CTEC	P4202	rpri	A610MULC	SG30CCAL00008	CL
420.	2	71						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
421.								11CTEC	P4202	rpri	A610MULC	SG30CCAL00008	CL
422.								11H11C	N0698	rpri	B580MRPCPH	SG30CCAL00018	CL
423.	2	72						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
424.								11CTEC	P4202	rpri	A610MULC	SG30CCAL00008	CL
425.	2	73						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
426.								11CTEC	P4202	rpri	A610MULC	SG30CCAL00008	CL
427.	2	74						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
428.								11CTEC	P4202	rpri	A610MULC	SG30CCAL00008	CL
429.	2	75						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
430.								11CTEC	P4202	rpri	A610MULC	SG30CCAL00008	CL
431.	2	76						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
432.								11CTEC	P4202	rpri	A610MULC	SG30CCAL00008	CL
433.	2	77						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00017	HL
434.								11CTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL
435.								11H11C	k6733	rsec	B580MRPCPH	SG30CCAL00022	CL
436.	2	78						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00017	HL
437.								11CTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL
438.	2	79						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00017	HL
39.								11CTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL
40.	2	80						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00017	HL
41.								11CTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: C
 DATABASE: Harris_SGC_1995

Sep. 23.1995 14:28

PAGE 11 of 128

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
442.								11H11C	N0698	rpri	B580MRPCPH	SG30CCAL00017	CL
443.	2	81						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00017	HL
444.								11CTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL
445.								11H11C	N0698	rpri	B580MRPCPH	SG30CCAL00017	CL
446.	2	82						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00017	HL
447.								11CTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL
448.	2	83						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00017	HL
449.								11CTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL
450.								11H11C	N0698	rpri	B580MRPCPH	SG30CCAL00017	CL
451.	2	84						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00017	HL
452.			1.32	153	MBM	1	04C 4.36	11CTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL
453.			1.38	165	MBM	1	04C 16.00	11CTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL
454.	2	85						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00017	HL
455.								11CTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL
456.	2	86						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00017	HL
457.								11CTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL
458.	2	87						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00017	HL
459.								11CTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL
460.								11H11C	N0698	rpri	B580MRPCPH	SG30CCAL00017	CL
461.	2	88						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00017	HL
62.								11CTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL
3.	2	89						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
464.								11CTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL
465.								11H11C	N0698	rpri	B580MRPCPH	SG30CCAL00017	CL
466.	2	90						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
467.								11CTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL
468.	2	91						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
469.								11CTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL
470.	2	92						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
471.								11CTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL
472.								11H11C	N0698	rpri	B580MRPCPH	SG30CCAL00017	CL
473.	2	93						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
474.								11CTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL
475.	2	94						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
476.								11CTEC	N0698	rpri	A610MULC	SG30CCAL00003	CL
477.								11H11C	I2393	rpri	B580MRPCPH	SG30CCAL00016	CL
478.	2	95						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
479.								11CTEC	N0698	rpri	A610MULC	SG30CCAL00003	CL
480.	2	96						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
481.								11CTEC	N0698	rpri	A610MULC	SG30CCAL00003	CL
482.								11H11C	I2393	rpri	B580MRPCPH	SG30CCAL00016	CL
483.	2	97						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
484.								11CTEC	N0698	rpri	A610MULC	SG30CCAL00003	CL
485.	2	98						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
486.								11CTEC	N0698	rpri	A610MULC	SG30CCAL00003	CL
487.								11H11C	I2393	rpri	B580MRPCPH	SG30CCAL00016	CL
488.	2	99						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
489.								11CTEC	N0698	rpri	A610MULC	SG30CCAL00003	CL
490.	2	100						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: C
 DATABASE: Harris_SGC_1995

Sep. 23,1995 14:28

PAGE 12 of 128

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
491.							11CTEC	N0698	rpri	A610MULC	SG30CCAL00003	CL
492.							11H11C	N0698	rpri	B580MRPCPH	SG30CCAL00017	CL
493.	2	101					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
494.							11CTEC	N0698	rpri	A610MULC	SG30CCAL00003	CL
495.	2	102					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
496.							11CTEC	N0698	rpri	A610MULC	SG30CCAL00003	CL
497.	2	103					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
498.							11CTEC	N0698	rpri	A610MULC	SG30CCAL00003	CL
499.	2	104					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
500.							11CTEC	C7651	rsec	A610MULC	SG30CCAL00002	CL
501.	2	105					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
502.							11CTEC	P4202	rpri	A610MULC	SG30CCAL00002	CL
503.	2	106					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
504.							11CTEC	P4202	rpri	A610MULC	SG30CCAL00002	CL
505.	2	107					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
506.							11CTEC	P4202	rpri	A610MULC	SG30CCAL00002	CL
507.	2	108					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
508.							11CTEC	P4202	rpri	A610MULC	SG30CCAL00002	CL
509.	2	109					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
510.							11CTEC	P4202	rpri	A610MULC	SG30CCAL00002	CL
11.	2	110					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
?							11CTEC	P4202	rpri	A610MULC	SG30CCAL00002	CL
13.	2	111					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
514.							11CTEC	P4202	rpri	A610MULC	SG30CCAL00002	CL
515.	2	112					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
516.							11CTEC	P4202	rpri	A610MULC	SG30CCAL00002	CL
517.	2	113					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
518.							11CTEC	P4202	rpri	A610MULC	SG30CCAL00002	CL
519.	2	114					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
520.							11CTEC	P4202	rpri	A610MULC	SG30CCAL00002	CL
521.	3	1					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00042	HL
522.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00012	CL
523.	3	2					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00043	HL
524.	3	3					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00042	HL
525.	3	4					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00043	HL
526.	3	5					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00042	HL
527.	3	6					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00043	HL
528.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00012	CL
529.	3	7					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00042	HL
530.	3	8					01HTSH	D3858	reso	B620MRPC3C	SG31HCAL00043	HL
531.	3	9					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00042	HL
532.	3	10					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00043	HL
533.	3	11					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00042	HL
534.							TEHTEC	05305	rpri	A610MULC	SG30CCAL00012	CL
535.	3	12					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00043	HL
536.	3	13					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00042	HL
7.	3	14					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00043	HL
13.	3	15					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00042	HL
19.	3	16					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00043	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: C
 DATABASE: Harris_SGC_1995

Sep. 23, 1995 14:28

PAGE 13 of 128

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
540.								TEHTEC	05305	rpri	A610MULC	SG30CCAL00012	CL
541.	3	17						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00042	HL
542.	3	18						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00043	HL
543.	3	19						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00043	HL
544.	3	20						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL
545.								TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL
546.	3	21						TSHTSH	D3858	reso	B620MRPC3C	SG31HCAL00040	HL
547.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00010	CL
548.	3	22						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL
549.	3	23						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL
550.	3	24						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL
551.	3	25						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL
552.	3	26						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL
553.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00011	CL
554.	3	27						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL
555.	3	28						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL
556.	3	29						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00044	HL
557.	3	30						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL
558.	3	31						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL
559.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00011	CL
60.	3	32						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00040	HL
61.	3	33						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00040	HL
62.	3	34						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00040	HL
63.	3	35						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00040	HL
64.	3	36						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00040	HL
65.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00011	CL
66.	3	37						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00008	HL
67.	3	38						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00008	HL
68.	3	39						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00023	HL
69.	3	40						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00008	HL
70.	3	41						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00008	HL
71.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00002	CL
72.	3	42						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00008	HL
73.	3	43						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00008	HL
74.	3	44						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00008	HL
75.	3	45						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00008	HL
76.	3	46						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00008	HL
77.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00002	CL
78.	3	47						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00008	HL
79.	3	48						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00008	HL
80.	3	49						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00008	HL
81.	3	50						TSHTSH	K6733	rsec	B620MRPC3C	SG31HCAL00008	HL
82.	3	51						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00008	HL
83.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00002	CL
84.	3	52						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00008	HL
85.	3	53						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00008	HL
86.	3	54						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00008	HL
87.	3	55						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00008	HL
88.	3	56						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00008	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: C
 DATABASE: Harris_SGC_1995

Sep. 23.1995 14:28

PAGE 14 of 128

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
589.								TEHTEC	05305	rpri	A610MULC	SG30CCAL00013	CL
590.	3	57						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
591.	3	58						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
592.	3	59						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
593.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00008	CL
594.	3	60						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
595.	3	61						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
596.	3	62						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
597.	3	63						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
598.	3	64						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
599.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00008	CL
600.	3	65						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
601.	3	66						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
602.	3	67						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
603.	3	68						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
604.	3	69						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
605.								11CTEC	P4202	rpri	A610MULC	SG30CCAL00008	CL
606.								TEHTEC	05305	rpri	A610MULC	SG30CCAL00013	CL
607.	3	70						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
608.	3	71						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
609.	3	72						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
610.	3	73						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
611.	3	74						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
612.								11CTEC	P4202	rpri	A610MULC	SG30CCAL00008	CL
613.								TEHTEC	05305	rpri	A610MULC	SG30CCAL00013	CL
614.	3	75						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
615.	3	76						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
616.	3	77						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00018	HL
617.	3	78						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00018	HL
618.	3	79						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00018	HL
619.								TEHTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL
620.	3	80						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00018	HL
621.	3	81						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00018	HL
622.	3	82						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00018	HL
623.	3	83						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00018	HL
624.	3	84						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00018	HL
625.								TEHTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL
626.	3	85						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00018	HL
627.	3	86						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00018	HL
628.	3	87						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00018	HL
629.	3	88						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
630.	3	89						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
631.								TEHTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL
632.	3	90						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
633.	3	91						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
634.	3	92						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
635.	3	93						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
636.	3	94						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
637.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00003	CL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: C
 DATABASE: Harris_SGC_1995

Sep. 23.1995 14:28

PAGE 15 of 128

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
638.	3	95					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
639.	3	96					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
640.	3	97					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
641.	3	98					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
642.	3	99					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
643.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00003	CL
644.	3	100					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
645.	3	101					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
646.	3	102					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
647.	3	103					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
648.	3	104					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
649.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00003	CL
650.	3	105					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
651.	3	106					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
652.	3	107					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
653.	3	108					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
654.	3	109					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
655.							TEHTEC	P4202	rpri	A610MULC	SG30CCAL00002	CL
656.	3	110					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
657.	3	111					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
58.	3	112					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
9.	3	113					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
60.	3	114					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
661.							TEHTEC	P4202	rpri	A610MULC	SG30CCAL00002	CL
662.	4	1					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00042	HL
663.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00012	CL
664.	4	2					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00043	HL
665.	4	3					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00042	HL
666.	4	4					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00043	HL
667.	4	5					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00042	HL
668.	4	6					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00043	HL
669.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00012	CL
670.	4	7					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00042	HL
671.	4	8					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00043	HL
672.	4	9					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00042	HL
673.	4	10					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00043	HL
674.	4	11					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00042	HL
675.							TEHTEC	05305	rpri	A610MULC	SG30CCAL00012	CL
676.							TEHTEC	05305	rpri	A610MULC	SG30CCAL00012	CL
677.	4	12					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00043	HL
678.	4	13					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00042	HL
679.	4	14					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00043	HL
680.	4	15					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00042	HL
681.	4	16					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00043	HL
682.							TEHTEC	05305	rpri	A610MULC	SG30CCAL00012	CL
683.	4	17					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00042	HL
684.	4	18					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00043	HL
685.	4	19					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00043	HL
686.	4	20					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: C
 DATABASE: Harris_SGC_1995

Sep. 23.1995 14:28

PAGE 16 of 128

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
687.								TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL
688.	4	21						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL
689.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00010	CL
690.	4	22						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL
691.	4	23						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL
692.	4	24						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL
693.	4	25						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL
694.	4	26						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL
695.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00011	CL
696.	4	27						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL
697.	4	28						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL
698.	4	29						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00044	HL
699.	4	30						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL
700.	4	31						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL
701.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00011	CL
702.	4	32						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00041	HL
703.	4	33						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00041	HL
704.	4	34						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00041	HL
705.	4	35						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00041	HL
706.	4	36						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00041	HL
07.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00011	CL
8.	4	37						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00007	HL
09.	4	38						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00007	HL
710.	4	39						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00007	HL
711.	4	40						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00007	HL
712.	4	41						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00007	HL
713.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00002	CL
714.	4	42						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00007	HL
715.	4	43						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00007	HL
716.	4	44						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00007	HL
717.	4	45						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00007	HL
718.	4	46						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00007	HL
719.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00002	CL
720.	4	47						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00007	HL
721.	4	48						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00007	HL
722.	4	49						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00007	HL
723.	4	50						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00007	HL
724.	4	51						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00007	HL
725.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00002	CL
726.	4	52						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00007	HL
727.	4	53						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00007	HL
728.	4	54						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00007	HL
729.	4	55						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00007	HL
730.	4	56						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00007	HL
731.								TEHTEC	05305	rpri	A610MULC	SG30CCAL00013	CL
732.	4	57						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
733.	4	58						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
734.	4	59						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
735.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00008	CL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: C
 DATABASE: Harris_SGC_1995

Sep. 23,1995 14:28

PAGE 17 of 128

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
736.	4	60					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
737.	4	61					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
738.	4	62					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
739.	4	63					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
740.	4	64					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
741.							TEHTEC	P4202	rpri	A610MULC	SG30CCAL00008	CL
742.	4	65					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
743.	4	66					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
744.	4	67					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
745.	4	68					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
746.	4	69					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
747.							TEHTEC	P4202	rpri	A610MULC	SG30CCAL00008	CL
748.	4	70					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
749.	4	71					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
750.	4	72					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
751.	4	73					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
752.	4	74					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
753.							TEHTEC	P4202	rpri	A610MULC	SG30CCAL00008	CL
754.	4	75					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
755.	4	76					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
56.	4	77					TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00017	HL
7.	4	78					TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00017	HL
58.	4	79					TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00017	HL
759.							TEHTEC	D3858	reso	A610MULC	SG30CCAL00005	CL
760.	4	80					TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00017	HL
761.	4	81					TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00017	HL
762.	4	82					TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00017	HL
763.	4	83					TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00017	HL
764.	4	84					TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00017	HL
765.							TEHTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL
766.	4	85					TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00017	HL
767.	4	86					TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00017	HL
768.	4	87					TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00017	HL
769.	4	88					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
770.	4	89					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
771.							TEHTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL
772.	4	90					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
773.	4	91					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
774.	4	92					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
775.	4	93					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
776.	4	94					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
777.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00003	CL
778.	4	95					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
779.	4	96					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
780.	4	97					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
781.	4	98					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
92.	4	99					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
3.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00003	CL
4.	4	100					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: C
 DATABASE: Harris_SGC_1995

Sep. 23,1995 14:28

PAGE 18 of 128

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
785.	4	101						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
786.	4	102						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
787.	4	103						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
788.	4	104						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
789.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00003	CL
790.	4	105						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
791.		0.35	138	36	1	01C	1.58	TEHTEC	F3453	reso	A610MULC	SG30CCAL00003	CL
792.	4	106						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
793.	4	107						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
794.	4	108						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
795.	4	109						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
796.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00002	CL
797.	4	110						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
798.	4	111						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
799.	4	112						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
800.	4	113						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
801.	4	114						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
802.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00002	CL
803.	5	1						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00042	HL
804.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00012	CL
805.	5	2						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00043	HL
806.	5	3						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00042	HL
807.	5	4						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00043	HL
808.	5	5						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00042	HL
809.	5	6						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00043	HL
810.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00012	CL
811.	5	7						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00042	HL
812.	5	8						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00043	HL
813.	5	9						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00042	HL
814.	5	10						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00043	HL
815.	5	11						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00042	HL
816.								TEHTEC	05305	rpri	A610MULC	SG30CCAL00012	CL
817.	5	12						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00043	HL
818.	5	13						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00042	HL
819.	5	14						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00043	HL
820.	5	15						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00042	HL
821.	5	16						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00043	HL
822.								TSHTSH	05305	rpri	A610MULC	SG30CCAL00012	CL
823.								TEHTEC	T7665	rpri	A610MULC	SG30CCAL00014	CL
824.	5	17						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00042	HL
825.								04C04C	S7675	rpri	B620MRPC3C	SG30CCAL00021	CL
826.	5	18						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00043	HL
827.								04C04C	S7675	rpri	B620MRPC3C	SG30CCAL00021	CL
828.	5	19						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00043	HL
829.	5	20						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL
830.								TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL
831.	5	21						TSHTSH	D3858	reso	B620MRPC3C	SG31HCAL00040	HL
832.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00010	CL
833.	5	22						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: C
 DATABASE: Harris_SGC_1995

Sep. 23,1995 14:28

PAGE 19 of 128

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
834.	5	23						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL
835.			1.18	169	MBM	1	09C 31.16	TEHTEC	T6956	rsec	A610MULC	SG30CCAL00011	CL
836.	5	24						TSHTSH	F7460	rsec	B620MRPC3C	SG31HCAL00040	HL
837.	5	25						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL
838.	5	26						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL
839.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00011	CL
840.	5	27						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL
841.	5	28						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL
842.	5	29						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL
843.	5	30						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL
844.	5	31						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL
845.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00011	CL
846.	5	32						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00040	HL
847.	5	33						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00040	HL
848.	5	34						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00040	HL
849.	5	35						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00040	HL
850.	5	36						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00040	HL
851.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00011	CL
852.	5	37						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00008	HL
853.	5	38						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00008	HL
54.	5	39						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00008	HL
5.	5	40						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00008	HL
56.	5	41						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00008	HL
857.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00002	CL
858.	5	42						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00008	HL
859.	5	43						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00008	HL
860.	5	44						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00008	HL
861.	5	45						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00008	HL
862.	5	46						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00008	HL
863.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00002	CL
864.	5	47						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00008	HL
865.	5	48						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00008	HL
866.	5	49						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00008	HL
867.	5	50						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00008	HL
868.	5	51						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00008	HL
869.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00002	CL
870.	5	52						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00008	HL
871.	5	53						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00008	HL
872.			1.04	149	MBM	1	08C 17.70	TEHTEC	P4202	rpri	A610MULC	SG30CCAL00002	CL
873.	5	54						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00008	HL
874.	5	55						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00008	HL
875.	5	56						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00008	HL
876.								TEHTEC	05305	rpri	A610MULC	SG30CCAL00013	CL
877.	5	57						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
878.	5	58						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
879.	5	59						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
880.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00008	CL
881.	5	60						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
882.	5	61						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: C
 DATABASE: Harris_SGC_1995

Sep. 23.1995 14:28

PAGE 20 of 128

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
883.	5	62					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
884.	5	63					TSHTSH	C7651	rsec	B620MRPC3C	SG31HCAL00032	HL
885.	5	64					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
886.							TEHTEC	H1274	reso	A610MULC	SG30CCAL00008	CL
887.	5	65					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
888.	5	66					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
889.	5	67					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
890.	5	68					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
891.	5	69					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
892.							TEHTEC	H1274	reso	A610MULC	SG30CCAL00008	CL
893.	5	70					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
894.	5	71					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
895.	5	72					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
896.	5	73					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
897.	5	74					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
898.							TEHTEC	P4202	rpri	A610MULC	SG30CCAL00008	CL
899.	5	75					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
900.	5	76					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
901.	5	77					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00018	HL
902.	5	78					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00018	HL
903.	5	79					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00018	HL
904.							TEHTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL
905.	5	80					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00018	HL
906.	5	81					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00018	HL
907.	5	82					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00018	HL
908.	5	83					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00018	HL
909.	5	84					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00018	HL
910.							TEHTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL
911.	5	85					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00018	HL
912.	5	86					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00018	HL
913.	5	87					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00018	HL
914.	5	88					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
915.	5	89					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
916.							TEHTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL
917.	5	90					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
918.	5	91					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
919.	5	92					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
920.	5	93					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
921.	5	94					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
922.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00003	CL
923.	5	95					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
924.	5	96					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
925.	5	97					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
926.	5	98					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
927.	5	99					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
928.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00003	CL
929.	5	100					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
930.	5	101					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
931.	5	102					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: C
 DATABASE: Harris_SGC_1995

Sep. 23.1995 14:28

PAGE 21 of 128

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
932.	5	103					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
933.	5	104					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
934.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00003	CL
935.	5	105					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
936.	5	106					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
937.	5	107					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
938.	5	108					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
939.	5	109					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
940.							TEHTEC	P4202	rpri	A610MULC	SG30CCAL00002	CL
941.	5	110					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
942.	5	111					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
943.	5	112					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
944.	5	113					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
945.	5	114					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
946.							TEHTEC	P4202	rpri	A610MULC	SG30CCAL00002	CL
947.	6	1					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00042	HL
948.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00012	CL
949.	6	2					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00043	HL
950.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00012	CL
951.	6	3					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00042	HL
52.	6	4					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00043	HL
53.	6	5					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00042	HL
54.	6	6					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00043	HL
955.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00012	CL
956.	6	7					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00042	HL
957.	6	8					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00043	HL
958.	6	9					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00042	HL
959.	6	10					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00043	HL
960.	6	11					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00042	HL
961.							TEHTEC	05305	rpri	A610MULC	SG30CCAL00012	CL
962.	6	12					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00043	HL
963.	6	13					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00042	HL
964.	6	14					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00043	HL
965.	6	15					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00042	HL
966.	6	16					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00043	HL
967.							TEHTEC	05305	rpri	A610MULC	SG30CCAL00012	CL
968.	6	17					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00042	HL
969.							04C04C	S7675	rpri	B620MRPC3C	SG30CCAL00021	CL
970.	6	18					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00043	HL
971.							04C04C	S7675	rpri	B620MRPC3C	SG30CCAL00021	CL
972.	6	19					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00043	HL
973.	6	20					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL
974.							TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL
975.	6	21					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL
976.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00010	CL
977.	6	22					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL
978.	6	23					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL
979.	6	24					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL
980.							TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: C
 DATABASE: Harris_SGC_1995

Sep. 23,1995 14:28

PAGE 22 of 128

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
981.	6	25					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL
982.	6	26					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL
983.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00011	CL
984.	6	27					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL
985.	6	28					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL
986.	6	29					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL
987.	6	30					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL
988.	6	31					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL
989.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00011	CL
990.	6	32					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00041	HL
991.	6	33					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00041	HL
992.	6	34					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00041	HL
993.	6	35					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00041	HL
994.	6	36					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00041	HL
995.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00011	CL
996.	6	37					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00007	HL
997.	6	38					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00007	HL
998.	6	39					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00007	HL
999.	6	40					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00007	HL
1000.	6	41					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00007	HL
01.							TEHTEC	P4202	rpri	A610MULC	SG30CCAL00002	CL
02.	6	42					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00007	HL
03.	6	43					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00007	HL
1004.	6	44					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00007	HL
1005.	6	45					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00007	HL
1006.	6	46					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00007	HL
1007.							TEHTEC	P4202	rpri	A610MULC	SG30CCAL00002	CL
1008.	6	47					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00007	HL
1009.	6	48					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00007	HL
1010.	6	49					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00007	HL
1011.	6	50					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00007	HL
1012.	6	51					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00007	HL
1013.							TEHTEC	P4202	rpri	A610MULC	SG30CCAL00002	CL
1014.	6	52					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00007	HL
1015.	6	53					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00007	HL
1016.	6	54					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00007	HL
1017.	6	55					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00007	HL
1018.	6	56					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00007	HL
1019.							TEHTEC	P4202	rpri	A610MULC	SG30CCAL00002	CL
1020.	6	57					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
1021.	6	58					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
1022.	6	59					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
1023.							TEHTEC	P4202	rpri	A610MULC	SG30CCAL00008	CL
1024.	6	60					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
1025.	6	61					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
1026.	6	62					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
1027.	6	63					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
1028.	6	64					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
1029.							TEHTEC	H1274	reso	A610MULC	SG30CCAL00008	CL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: C
 DATABASE: Harris_SGC_1995

Sep. 23.1995 14:28

PAGE 23 of 128

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
1030.	6	65						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
1031.	6	66						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
1032.	6	67						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
1033.	6	68						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
1034.	6	69						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
1035.								TEHTEC	H1274	reso	A610MULC	SG30CCAL00008	CL
1036.	6	70						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
1037.	6	71						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
1038.	6	72						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
1039.	6	73						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
1040.	6	74						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
1041.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00008	CL
1042.		1.21	159	6	1	04C	6.80	TEHTEC	05305	rpri	A610MULC	SG30CCAL00013	CL
1043.	6	75						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
1044.	6	76						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
1045.	6	77						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00017	HL
1046.	6	78						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00017	HL
1047.	6	79						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00017	HL
1048.								TEHTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL
1049.	6	80						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00017	HL
50.	6	81						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00017	HL
101.	6	82						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00017	HL
102.	6	83						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00017	HL
1053.	6	84						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00017	HL
1054.								TEHTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL
1055.	6	85						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00017	HL
1056.	6	86						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00017	HL
1057.	6	87						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00017	HL
1058.	6	88						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
1059.	6	89						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
1060.								TEHTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL
1061.	6	90						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
1062.	6	91						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
1063.	6	92						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
1064.	6	93						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
1065.	6	94						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
1066.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00003	CL
1067.	6	95						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
1068.	6	96						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
1069.	6	97						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
1070.	6	98						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
1071.	6	99						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
1072.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00003	CL
1073.	6	100						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
1074.	6	101						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
1075.	6	102						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
1076.	6	103						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
1077.	6	104						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
1078.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00003	CL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: C
 DATABASE: Harris_SGC_1995

Sep. 23.1995 14:28

PAGE 24 of 128

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
1079.	6	105					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
1080.	6	106					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
1081.	6	107					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
1082.	6	108					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
1083.	6	109					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
1084.							TEHTEC	P4202	rpri	A610MULC	SG30CCAL00002	CL
1085.	6	110					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
1086.	6	111					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
1087.	6	112					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
1088.	6	113					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
1089.							TEHTEC	P4202	rpri	A610MULC	SG30CCAL00002	CL
1090.	6	114					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
1091.							TEHTEC	P4202	rpri	A610MULC	SG30CCAL00002	CL
1092.	7	2					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00042	HL
1093.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00012	CL
1094.	7	3					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00043	HL
1095.	7	4					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00042	HL
1096.	7	5					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00043	HL
1097.	7	6					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00042	HL
1098.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00012	CL
99.	7	7					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00043	HL
101.	7	8					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00042	HL
102.	7	9					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00043	HL
1102.	7	10					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00042	HL
1103.	7	11					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00043	HL
1104.							TEHTEC	05305	rpri	A610MULC	SG30CCAL00012	CL
1105.	7	12					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00042	HL
1106.	7	13					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00043	HL
1107.	7	14					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00042	HL
1108.	7	15					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00043	HL
1109.	7	16					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00042	HL
1110.							TEHTEC	05305	rpri	A610MULC	SG30CCAL00012	CL
1111.	7	17					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00043	HL
1112.	7	18					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00042	HL
1113.	7	19					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00043	HL
1114.	7	20					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL
1115.							TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL
1116.	7	21					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL
1117.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00010	CL
1118.	7	22					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL
1119.	7	23					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL
1120.	7	24					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00044	HL
1121.	7	25					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL
1122.	7	26					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL
1123.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00011	CL
1124.	7	27					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL
1125.	7	28					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL
1126.	7	29					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL
1127.	7	30					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: C
 DATABASE: Harris_SGC_1995

Sep. 23,1995 14:28

PAGE 25 of 128

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
1128.	7	31					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL
1129.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00011	CL
1130.	7	32					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00040	HL
1131.	7	33					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00040	HL
1132.	7	34					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00040	HL
1133.	7	35					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00040	HL
1134.	7	36					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00040	HL
1135.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00011	CL
1136.	7	37					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00008	HL
1137.	7	38					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00008	HL
1138.	7	39					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00008	HL
1139.	7	40					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00008	HL
1140.	7	41					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00008	HL
1141.							TEHTEC	P4202	rpri	A610MULC	SG30CCAL00002	CL
1142.	7	42					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00008	HL
1143.	7	43					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00008	HL
1144.	7	44					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00008	HL
1145.	7	45					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00008	HL
1146.	7	46					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00008	HL
1147.							TEHTEC	P4202	rpri	A610MULC	SG30CCAL00002	CL
48.	7	47					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00008	HL
49.	7	48					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00008	HL
50.	7	49					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00008	HL
1151.	7	50					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00008	HL
1152.	7	51					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00008	HL
1153.							TEHTEC	P4202	rpri	A610MULC	SG30CCAL00002	CL
1154.	7	52					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00008	HL
1155.	7	53					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00008	HL
1156.	7	54					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00008	HL
1157.	7	55					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00008	HL
1158.	7	56					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00008	HL
1159.							TEHTEC	P4202	rpri	A610MULC	SG30CCAL00002	CL
1160.	7	57					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
1161.	7	58					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
1162.	7	59					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
1163.							TEHTEC	P4202	rpri	A610MULC	SG30CCAL00008	CL
1164.	7	60					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
1165.	7	61					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
1166.	7	62					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
1167.	7	63					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
1168.	7	64					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
1169.							TEHTEC	H1274	reso	A610MULC	SG30CCAL00008	CL
1170.	7	65					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
1171.	7	66					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
1172.	7	67					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
1173.	7	68					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
1174.	7	69					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
1175.							TEHTEC	H1274	reso	A610MULC	SG30CCAL00008	CL
1176.	7	70					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: C
 DATABASE: Harris_SGC_1995

Sep. 23.1995 14:28

PAGE 26 of 128

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
1177.	7	71						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
1178.	7	72						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
1179.	7	73						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
1180.	7	74						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
1181.								TEHTEC	H1274	reso	A610MULC	SG30CCAL00008	CL
1182.		1.21	157	MBM	1	04C	6.75	TEHTEC	H1274	reso	A610MULC	SG30CCAL00008	CL
1183.	7	75						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
1184.	7	76						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
1185.	7	77						TSHTSH	85534	rpri	B620MRPC3C	SG31HCAL00018	HL
1186.	7	78						TSHTSH	85534	rpri	B620MRPC3C	SG31HCAL00018	HL
1187.	7	79						TSHTSH	85534	rpri	B620MRPC3C	SG31HCAL00018	HL
1188.								TEHTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL
1189.	7	80						TSHTSH	85534	rpri	B620MRPC3C	SG31HCAL00018	HL
1190.	7	81						TSHTSH	85534	rpri	B620MRPC3C	SG31HCAL00018	HL
1191.	7	82						TSHTSH	85534	rpri	B620MRPC3C	SG31HCAL00018	HL
1192.	7	83						TSHTSH	85534	rpri	B620MRPC3C	SG31HCAL00018	HL
1193.	7	84						TSHTSH	85534	rpri	B620MRPC3C	SG31HCAL00018	HL
1194.								TEHTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL
1195.	7	85						TSHTSH	85534	rpri	B620MRPC3C	SG31HCAL00018	HL
1196.	7	86						TSHTSH	85534	rpri	B620MRPC3C	SG31HCAL00018	HL
97.	7	87						TSHTSH	85534	rpri	B620MRPC3C	SG31HCAL00018	HL
98.	7	88						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
99.	7	89						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
1200.								TEHTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL
1201.	7	90						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
1202.	7	91						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
1203.	7	92						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
1204.	7	93						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
1205.	7	94						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
1206.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00003	CL
1207.	7	95						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
1208.	7	96						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
1209.	7	97						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
1210.	7	98						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
1211.	7	99						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
1212.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00003	CL
1213.	7	100						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
1214.	7	101						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
1215.	7	102						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
1216.	7	103						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
1217.	7	104						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
1218.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00003	CL
1219.	7	105						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
1220.	7	106						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
1221.	7	107						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
122.	7	108						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
123.	7	109						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
124.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00002	CL
125.	7	110						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: C
 DATABASE: Harris_SGC_1995

Sep. 23,1995 14:28

PAGE 27 of 128

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
1226.	7	111						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
1227.	7	112						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
1228.	7	113						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
1229.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00002	CL
1230.	8	2						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00042	HL
1231.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00012	CL
1232.	8	3						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00043	HL
1233.	8	4						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00042	HL
1234.	8	5						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00043	HL
1235.	8	6						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00042	HL
1236.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00012	CL
1237.	8	7						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00043	HL
1238.	8	8						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00042	HL
1239.	8	9						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00043	HL
1240.	8	10						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00042	HL
1241.	8	11						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00043	HL
1242.								TEHTEC	05305	rpri	A610MULC	SG30CCAL00012	CL
1243.	8	12						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00042	HL
1244.	8	13						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00043	HL
1245.	8	14						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00042	HL
46.	8	15						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00043	HL
47.	8	16						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00042	HL
48.								TEHTEC	05305	rpri	A610MULC	SG30CCAL00012	CL
1249.	8	17						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00043	HL
1250.	8	18						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00042	HL
1251.	8	19						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00043	HL
1252.	8	20						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL
1253.								TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL
1254.	8	21						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL
1255.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00010	CL
1256.	8	22						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL
1257.	8	23						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL
1258.	8	24						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00044	HL
1259.	8	25						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL
1260.	8	26						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL
1261.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00011	CL
1262.	8	27						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL
1263.	8	28						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL
1264.	8	29						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL
1265.	8	30						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL
1266.	8	31						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL
1267.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00011	CL
1268.	8	32						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00041	HL
1269.	8	33						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00041	HL
1270.	8	34						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00041	HL
71.	8	35						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00041	HL
72.	8	36						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00041	HL
73.			1.86	148	MBM	1	03H 16.27	TEHTEC	N0698	rpri	A610MULC	SG30CCAL00011	CL
74.	8	37						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00007	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: C
 DATABASE: Harris_SGC_1995

Sep. 23,1995 14:28

PAGE 28 of 128

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
1275.	8	38						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00007	HL
1276.	8	39						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00007	HL
1277.	8	40						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00007	HL
1278.	8	41						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00007	HL
1279.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00002	CL
1280.	8	42						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00007	HL
1281.	8	43						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00007	HL
1282.	8	44						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00007	HL
1283.	8	45						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00007	HL
1284.	8	46						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00007	HL
1285.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00002	CL
1286.	8	47						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00007	HL
1287.	8	48						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00007	HL
1288.	8	49						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00007	HL
1289.	8	50						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00007	HL
1290.	8	51						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00007	HL
1291.		1.31	158	M8M	1	08C	13.64	TEHTEC	P4202	rpri	A610MULC	SG30CCAL00002	CL
1292.	8	52						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00007	HL
1293.	8	53						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00007	HL
1294.	8	54						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00007	HL
95.	8	55						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00007	HL
5.	8	56						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00007	HL
7.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00002	CL
1298.	8	57						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
1299.	8	58						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
1300.	8	59						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
1301.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00008	CL
1302.	8	60						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
1303.	8	61						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
1304.	8	62						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
1305.	8	63						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
1306.	8	64						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
1307.								TEHTEC	H1274	reso	A610MULC	SG30CCAL00008	CL
1308.	8	65						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
1309.	8	66						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
1310.	8	67						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
1311.	8	68						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
1312.	8	69						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
1313.								TEHTEC	H1274	reso	A610MULC	SG30CCAL00008	CL
1314.	8	70						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
1315.	8	71						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
1316.	8	72						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
1317.	8	73						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
1318.	8	74						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
1319.								TEHTEC	H1274	reso	A610MULC	SG30CCAL00008	CL
20.	8	75						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
21.	8	76						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
22.	8	77						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00017	HL
23.	8	78						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00017	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: C
 DATABASE: Harris_SGC_1995

Sep. 23, 1995 14:28

PAGE 29 of 128

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG	
1324.	8	79						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00017	HL	
1325.								TEHTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL	
1326.	8	80						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00017	HL	
1327.	8	81						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00017	HL	
1328.	8	82						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00017	HL	
1329.	8	83						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00017	HL	
1330.	8	84						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00017	HL	
1331.								TEHTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL	
1332.	8	85						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00017	HL	
1333.	8	86						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00017	HL	
1334.	8	87						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00017	HL	
1335.	8	88						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL	
1336.	8	89						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL	
1337.								TEHTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL	
1338.	8	90						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL	
1339.	8	91						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL	
1340.	8	92						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL	
1341.			0.38	144	MBM	1	10C	9.37	TEHTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL
1342.	8	93						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL	
1343.	8	94						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL	
44.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00003	CL	
45.	8	95						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL	
1346.	8	96						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL	
1347.	8	97						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL	
1348.	8	98						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL	
1349.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00003	CL	
1350.	8	99						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL	
1351.			0.55	156	MBM	1	10C	5.61	TEHTEC	N0698	rpri	A610MULC	SG30CCAL00003	CL
1352.	8	100						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL	
1353.	8	101						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL	
1354.	8	102						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL	
1355.	8	103						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL	
1356.	8	104						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL	
1357.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00003	CL	
1358.	8	105						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL	
1359.	8	106						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL	
1360.	8	107						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL	
1361.					INR		09C	33.78	TEHTEC	B3052	reso	A610MULC	SG30CCAL00003	CL
1362.	8	108						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL	
1363.	8	109						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL	
1364.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00002	CL	
1365.	8	110						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL	
1366.	8	111						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL	
1367.	8	112						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL	
1368.	8	113						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL	
1369.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00002	CL	
1370.	9	2						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00042	HL	
1371.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00012	CL	
1372.	9	3						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00043	HL	

*** INSPECTION FINAL REPORT LISTING ***

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: C
 DATABASE: Harris_SGC_1995

Sep. 23.1995 14:28

PAGE 30 of 128

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
1373.	9	4					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00042	HL
1374.	9	5					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00043	HL
1375.	9	6					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00042	HL
1376.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00012	CL
1377.	9	7					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00043	HL
1378.	9	8					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00042	HL
1379.	9	9					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00043	HL
1380.	9	10					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00042	HL
1381.	9	11					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00043	HL
1382.							TEHTEC	05305	rpri	A610MULC	SG30CCAL00012	CL
1383.	9	12					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00042	HL
1384.	9	13					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00043	HL
1385.	9	14					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00042	HL
1386.	9	15					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00043	HL
1387.	9	16					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00042	HL
1388.							TEHTEC	05305	rpri	A610MULC	SG30CCAL00012	CL
1389.	9	17					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00043	HL
1390.	9	18					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00042	HL
1391.	9	19					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00043	HL
1392.	9	20					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL
93.							TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL
	9	21					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL
							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00010	CL
1396.	9	22					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL
1397.	9	23					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL
1398.	9	24					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL
1399.	9	25					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL
1400.	9	26					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL
1401.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00011	CL
1402.	9	27					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL
1403.	9	30					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL
1404.	9	31					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL
1405.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00011	CL
1406.	9	32					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00040	HL
1407.	9	33					TSHTSH	D3858	reso	B620MRPC3C	SG31HCAL00040	HL
1408.	9	34					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00040	HL
1409.	9	35					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00040	HL
1410.	9	36					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00040	HL
1411.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00011	CL
1412.	9	37					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00008	HL
1413.	9	38					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00008	HL
1414.	9	39					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00008	HL
1415.	9	40					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00008	HL
1416.	9	41					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00008	HL
1417.							TEHTEC	P4202	rpri	A610MULC	SG30CCAL00002	CL
18.	9	42					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00008	HL
1.	9	43					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00008	HL
J.	9	44					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00008	HL
1.	9	45					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00008	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: C
 DATABASE: Harris_SGC_1995

Sep. 23.1995 14:28

PAGE 31 of 128

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
1422.	9	46						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00008	HL
1423.								TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00008	HL
1424.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00002	CL
1425.	9	47						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00008	HL
1426.	9	48						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00008	HL
1427.	9	49						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00008	HL
1428.	9	50						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00008	HL
1429.	9	51						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00008	HL
1430.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00002	CL
1431.	9	52						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00008	HL
1432.	9	53						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00008	HL
1433.	9	54						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00008	HL
1434.	9	55						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00008	HL
1435.	9	56						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00008	HL
1436.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00002	CL
1437.	9	59						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
1438.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00008	CL
1439.	9	60						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
1440.	9	61						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
1441.	9	62						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
42.	9	63						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
3.	9	64						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
4.								TEHTEC	H1274	reso	A610MULC	SG30CCAL00008	CL
1445.	9	65						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
1446.	9	66						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
1447.	9	67						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
1448.	9	68						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
1449.	9	69						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
1450.								TEHTEC	H1274	reso	A610MULC	SG30CCAL00008	CL
1451.	9	70						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
1452.	9	71						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
1453.	9	72						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
1454.	9	73						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
1455.	9	74						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
1456.								TEHTEC	H1274	reso	A610MULC	SG30CCAL00008	CL
1457.	9	75						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
1458.	9	76						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
1459.	9	77						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00018	HL
1460.	9	78						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00018	HL
1461.	9	79						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00018	HL
1462.								TEHTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL
1463.	9	80						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00018	HL
1464.	9	81						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00018	HL
1465.	9	82						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00018	HL
1466.	9	83						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00018	HL
1467.	9	84						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00018	HL
1468.		15.93	179	DNT	1	03C	12.87	TEHTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL
1469.	9	85						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00018	HL
1470.	9	88						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: C
 DATABASE: Harris_SGC_1995

Sep. 23,1995 14:28

PAGE 32 of 128

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
1471.	9	89					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
1472.							TEHTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL
1473.	9	90					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
1474.	9	91					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
1475.	9	92					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
1476.	9	93					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
1477.	9	94					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
1478.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00003	CL
1479.	9	95					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
1480.	9	96					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
1481.	9	97					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
1482.	9	98					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
1483.	9	99					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
1484.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00003	CL
1485.	9	100					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
1486.	9	101					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
1487.	9	102					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
1488.	9	103					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
1489.	9	104					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
1490.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00003	CL
91.	9	105					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
	9	106					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
	9	107					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
1493.	9	107					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
1494.	9	108					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
1495.	9	109					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
1496.							TEHTEC	P4202	rpri	A610MULC	SG30CCAL00002	CL
1497.	9	110					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
1498.	9	111					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
1499.	9	112					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
1500.	9	113					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
1501.							TEHTEC	P4202	rpri	A610MULC	SG30CCAL00002	CL
1502.	10	2					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00042	HL
1503.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00012	CL
1504.	10	3					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00043	HL
1505.	10	4					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00042	HL
1506.	10	5					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00043	HL
1507.	10	6					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00042	HL
1508.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00012	CL
1509.	10	7					01HTSH	03858	reso	B620MRPC3C	SG31HCAL00043	HL
1510.	10	8					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00042	HL
1511.	10	9					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00043	HL
1512.	10	10					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00042	HL
1513.	10	11					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00043	HL
1514.							TEHTEC	05305	rpri	A610MULC	SG30CCAL00012	CL
1515.	10	12					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00042	HL
1516.	10	13					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00043	HL
1517.	10	14					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00042	HL
1518.	10	15					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00043	HL
1519.	10	16					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00042	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: C
 DATABASE: Harris_SGC_1995

Sep. 23,1995 14:28

PAGE 33 of 128

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
1520.								TEHTEC	05305	rpri	A610MULC	SG30CCAL00012	CL
1521.	10	17						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00043	HL
1522.	10	18						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00042	HL
1523.	10	19						01HTSH	D3858	reso	B620MRPC3C	SG31HCAL00043	HL
1524.	10	20						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL
1525.								TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL
1526.	10	21						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL
1527.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00010	CL
1528.	10	22						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL
1529.	10	23						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL
1530.	10	24						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL
1531.	10	25						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL
1532.	10	26						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL
1533.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00011	CL
1534.	10	27						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL
1535.	10	30						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL
1536.	10	31						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL
1537.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00011	CL
1538.	10	32						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00041	HL
1539.	10	33						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00041	HL
40.	10	34						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00041	HL
1.	10	35						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00041	HL
42.	10	36						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00041	HL
1543.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00011	CL
1544.	10	37						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00007	HL
1545.	10	38						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00007	HL
1546.	10	39						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00007	HL
1547.	10	40						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00007	HL
1548.	10	41						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00007	HL
1549.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00002	CL
1550.	10	42						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00007	HL
1551.	10	43						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00007	HL
1552.	10	44						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00007	HL
1553.	10	45						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00007	HL
1554.	10	46						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00007	HL
1555.								TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00007	HL
1556.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00002	CL
1557.	10	47						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00007	HL
1558.	10	48						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00007	HL
1559.	10	49						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00007	HL
1560.	10	50						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00007	HL
1561.	10	51						TSHTSH	K6733	rsec	B620MRPC3C	SG31HCAL00007	HL
1562.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00002	CL
1563.	10	52						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00007	HL
1564.	10	53						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00007	HL
1565.	10	54						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00007	HL
1566.	10	55						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00007	HL
1567.	10	56						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00007	HL
1568.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00002	CL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: C
 DATABASE: Harris_SGC_1995

Sep. 23,1995 14:28

PAGE 34 of 128

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
1569.	10	59					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
1570.							TEHTEC	P4202	rpri	A610MULC	SG30CCAL00008	CL
1571.	10	60					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
1572.	10	61					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
1573.	10	62					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
1574.	10	63					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
1575.	10	64					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
1576.							TEHTEC	P4202	rpri	A610MULC	SG30CCAL00008	CL
1577.	10	65					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
1578.	10	66					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
1579.	10	67					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
1580.	10	68					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
1581.	10	69					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
1582.							TEHTEC	P4202	rpri	A610MULC	SG30CCAL00008	CL
1583.	10	70					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
1584.	10	71					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
1585.	10	72					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
1586.	10	73					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
1587.	10	74					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
1588.							TEHTEC	H1274	reso	A610MULC	SG30CCAL00008	CL
89.	10	75					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
90.	10	76					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
91.	10	77					TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00017	HL
1592.	10	78					TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00017	HL
1593.	10	79					TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00017	HL
1594.							TEHTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL
1595.	10	80					TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00017	HL
1596.	10	81					TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00017	HL
1597.	10	82					TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00017	HL
1598.	10	83					TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00017	HL
1599.	10	84					TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00017	HL
1600.							TEHTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL
1601.	10	85					TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00017	HL
1602.	10	88					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
1603.	10	89					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
1604.							TEHTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL
1605.	10	90					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
1606.	10	91					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
1607.	10	92					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
1608.	10	93					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
1609.	10	94					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
1610.							TEHTEC	C7651	rsec	A610MULC	SG30CCAL00003	CL
1611.	10	95					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
1612.	10	96					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
1613.	10	97					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
1614.	10	98					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
1615.	10	99					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
1616.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00003	CL
1617.	10	100					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL

*** INSPECTION FINAL REPORT LISTING ***

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: C
 DATABASE: Harris_SGC_1995

Sep. 23.1995 14:28

PAGE 35 of 128

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
1618.	10	101						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
1619.	10	102						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
1620.	10	103						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
1621.	10	104						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
1622.		14.58	181	DNT	1	11H	3.74	TEHTEC	F3453	reso	A610MULC	SG30CCAL00003	CL
1623.	10	105						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
1624.	10	106						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
1625.	10	107						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
1626.	10	108						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
1627.	10	109						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
1628.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00002	CL
1629.	10	110						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
1630.	10	111						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
1631.	10	112						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
1632.	10	113						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
1633.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00002	CL
1634.	11	2						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00040	HL
1635.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00011	CL
1636.	11	3						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00041	HL
1637.	11	4						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00040	HL
38.	11	5						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00041	HL
39.	11	6						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00041	HL
40.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00011	CL
1641.	11	7						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00041	HL
1642.	11	8						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00040	HL
1643.	11	9						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00041	HL
1644.	11	10						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00040	HL
1645.	11	11						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00041	HL
1646.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00011	CL
1647.	11	12						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00040	HL
1648.	11	13						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00041	HL
1649.	11	14						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00040	HL
1650.	11	15						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00041	HL
1651.	11	16						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00040	HL
1652.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00011	CL
1653.	11	17						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00044	HL
1654.	11	18						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00040	HL
1655.	11	19						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00041	HL
1656.	11	20						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00038	HL
1657.	11	21						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00038	HL
1658.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00010	CL
1659.	11	22						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00038	HL
1660.	11	23						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00038	HL
1661.	11	24						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL
1662.	11	25						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL
1663.	11	26						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL
1664.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00010	CL
1665.	11	27						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL
1666.	11	28						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: C
 DATABASE: Harris_SGC_1995

Sep. 23.1995 14:28

PAGE 36 of 128

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
1667.	11	29						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL
1668.	11	30						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL
1669.	11	31						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL
1670.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00010	CL
1671.	11	32						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL
1672.	11	33						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL
1673.	11	34						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL
1674.	11	35						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL
1675.	11	36						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL
1676.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00010	CL
1677.	11	37						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00006	HL
1678.	11	38						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00006	HL
1679.	11	39						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00006	HL
1680.	11	40						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00006	HL
1681.	11	41						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00006	HL
1682.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00001	CL
1683.	11	42						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00006	HL
1684.	11	43						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00006	HL
1685.	11	44						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00006	HL
1686.	11	45						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00006	HL
87.	11	46						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00006	HL
88.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00001	CL
1689.	11	47						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00006	HL
1690.	11	48						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00006	HL
1691.	11	49						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00006	HL
1692.	11	50						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00006	HL
1693.	11	51						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00006	HL
1694.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00001	CL
1695.	11	52						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00006	HL
1696.	11	53						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00008	HL
1697.	11	54						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00008	HL
1698.	11	55						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00008	HL
1699.	11	56						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00008	HL
1700.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00001	CL
1701.	11	57						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL
1702.	11	58						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL
1703.	11	59						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL
1704.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00007	CL
1705.	11	60						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL
1706.	11	61						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL
1707.	11	62						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL
1708.	11	63						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL
1709.	11	64						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL
1710.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00008	CL
1711.	11	65						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL
1712.	11	66						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL
1713.	11	67						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL
1714.	11	68						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
1715.	11	69						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: C
 DATABASE: Harris_SGC_1995

Sep. 23, 1995 14:28

PAGE 37 of 128

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
1716.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00008	CL
1717.	11	70						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
1718.	11	71						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
1719.	11	72						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
1720.	11	73						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
1721.	11	74						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
1722.								TEHTEC	H1274	reso	A610MULC	SG30CCAL00008	CL
1723.	11	75						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
1724.	11	76						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
1725.	11	77						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00016	HL
1726.	11	78						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00016	HL
1727.	11	79						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00018	HL
1728.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00004	CL
1729.	11	80						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00018	HL
1730.	11	81						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00018	HL
1731.	11	82						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00018	HL
1732.	11	83						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00018	HL
1733.	11	84						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00018	HL
1734.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00004	CL
1735.	11	85						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00018	HL
36.	11	86						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00018	HL
7.	11	87						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00018	HL
1738.	11	88						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00018	HL
1739.	11	89						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00018	HL
1740.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00004	CL
1741.	11	90						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00018	HL
1742.	11	91						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00018	HL
1743.	11	92						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00018	HL
1744.	11	93						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00018	HL
1745.	11	94						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
1746.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00003	CL
1747.	11	95						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
1748.	11	96						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
1749.	11	97						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
1750.								TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
1751.	11	98						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
1752.	11	99						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
1753.			6.00	181	DNT	1	11H 3.94	TEHTEC	N0698	rpri	A610MULC	SG30CCAL00003	CL
1754.	11	100						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
1755.	11	101						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
1756.	11	102						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
1757.	11	103						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
1758.	11	104						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
1759.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00003	CL
1760.	11	105						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
761.	11	106						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00011	HL
762.	11	107						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00012	HL
763.	11	108						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00011	HL
764.	11	109						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00012	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: C
 DATABASE: Harris_SGC_1995

Sep. 23.1995 14:28

PAGE 38 of 128

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
1765.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00003	CL
1766.	11	110					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00011	HL
1767.	11	111					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00012	HL
1768.	11	112					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00011	HL
1769.	11	113					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00012	HL
1770.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00003	CL
1771.	12	2					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00040	HL
1772.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00011	CL
1773.	12	3					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00041	HL
1774.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00011	CL
1775.	12	4					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00040	HL
1776.	12	5					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00041	HL
1777.	12	6					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00040	HL
1778.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00011	CL
1779.	12	7					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00041	HL
1780.	12	8					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00040	HL
1781.	12	9					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00041	HL
1782.	12	10					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00040	HL
1783.	12	11					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00041	HL
1784.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00011	CL
85.	12	12					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00040	HL
86.	12	13					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00041	HL
87.	12	14					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00040	HL
1788.	12	15					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00041	HL
1789.	12	16					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00040	HL
1790.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00011	CL
1791.	12	17					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00041	HL
1792.	12	18					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00040	HL
1793.	12	19					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00041	HL
1794.	12	20					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00039	HL
1795.	12	21					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00039	HL
1796.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00010	CL
1797.	12	22					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00039	HL
1798.	12	23					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00039	HL
1799.	12	24					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL
1800.	12	25					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL
1801.	12	26					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL
1802.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00010	CL
1803.	12	27					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL
1804.	12	28					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL
1805.	12	29					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL
1806.	12	30					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL
1807.	12	31					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL
1808.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00010	CL
1809.	12	32					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL
1810.	12	33					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL
1811.	12	34					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL
1812.	12	35					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL
1813.	12	36					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: C
 DATABASE: Harris_SGC_1995

Sep. 23.1995 14:28

PAGE 39 of 128

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
1814.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00010	CL
1815.	12	37					TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00005	HL
1816.	12	38					TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00005	HL
1817.	12	39					TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00005	HL
1818.	12	40					TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00005	HL
1819.	12	41					TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00005	HL
1820.							TEHTEC	P4202	rpri	A610MULC	SG30CCAL00001	CL
1821.	12	42					TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00005	HL
1822.	12	43					TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00005	HL
1823.	12	44					TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00005	HL
1824.	12	45					TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00005	HL
1825.	12	46					TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00005	HL
1826.							TEHTEC	P4202	rpri	A610MULC	SG30CCAL00001	CL
1827.	12	47					TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00005	HL
1828.	12	48					TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00005	HL
1829.	12	49					TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00005	HL
1830.	12	50					TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00005	HL
1831.	12	51					TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00005	HL
1832.							TEHTEC	P4202	rpri	A610MULC	SG30CCAL00001	CL
1833.	12	52					TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00005	HL
34.	12	53					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00007	HL
35.	12	54					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00007	HL
36.	12	55					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00007	HL
1837.	12	56					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00007	HL
1838.							TEHTEC	P4202	rpri	A610MULC	SG30CCAL00001	CL
1839.	12	57					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
1840.	12	58					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
1841.	12	59					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
1842.							TEHTEC	P4202	rpri	A610MULC	SG30CCAL00007	CL
1843.	12	60					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
1844.	12	61					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
1845.	12	62					TSH01H	C7651	rsèc	B620MRPC3C	SG31HCAL00031	HL
1846.	12	63					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
1847.	12	64					TSH01H	C7651	rsec	B620MRPC3C	SG31HCAL00031	HL
1848.							TEHTEC	P4202	rpri	A610MULC	SG30CCAL00008	CL
1849.	12	65					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
1850.	12	66					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
1851.	12	67					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
1852.	12	68					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
1853.	12	69					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
1854.							TEHTEC	P4202	rpri	A610MULC	SG30CCAL00008	CL
1855.	12	70					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
1856.	12	71					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
1857.	12	72					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
1858.	12	73					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00037	HL
1859.	12	74					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
1860.							TEHTEC	P4202	rpri	A610MULC	SG30CCAL00008	CL
1861.	12	75					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
1862.	12	76					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: C
 DATABASE: Harris_SGC_1995

Sep. 23.1995 14:28

PAGE 40 of 128

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
1863.	12	77						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00015	HL
1864.	12	78						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00015	HL
1865.	12	79						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00017	HL
1866.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00004	CL
1867.	12	80						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00017	HL
1868.	12	81						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00017	HL
1869.	12	82						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00017	HL
1870.	12	83						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00017	HL
1871.	12	84						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00017	HL
1872.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00004	CL
1873.	12	85						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00017	HL
1874.	12	86						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00017	HL
1875.	12	87						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00017	HL
1876.	12	88						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00017	HL
1877.	12	89						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00017	HL
1878.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00004	CL
1879.	12	90						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00017	HL
1880.	12	91						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00017	HL
1881.	12	92						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00017	HL
1882.	12	93						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00017	HL
1883.	12	94						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00003	CL
1885.	12	95						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
1886.	12	96						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
1887.	12	97						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
1888.	12	98						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
1889.	12	99						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
1890.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00003	CL
1891.	12	100						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
1892.	12	101						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
1893.	12	102						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
1894.	12	103						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
1895.	12	104						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
1896.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00003	CL
1897.	12	105						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
1898.	12	106						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00011	HL
1899.	12	107						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00012	HL
1900.	12	108						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00011	HL
1901.	12	109						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00012	HL
1902.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00003	CL
1903.	12	110						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00011	HL
1904.	12	111						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00012	HL
1905.	12	112						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00011	HL
1906.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00003	CL
1907.	12	113						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00012	HL
1908.		12.26	178	DNT	P1	09C	-0.42	TEHTEC	N0698	rpri	A610MULC	SG30CCAL00003	CL
1909.	13	3						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00040	HL
1910.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00011	CL
1911.	13	4						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00041	HL

*** INSPECTION FINAL REPORT LISTING ***

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: C
 DATABASE: Harris_SGC_1995

Sep. 23,1995 14:28

PAGE 41 of 128

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
1912.	13	5					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00040	HL
1913.	13	6					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00041	HL
1914.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00011	CL
1915.	13	7					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00040	HL
1916.	13	8					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00041	HL
1917.	13	9					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00040	HL
1918.	13	10					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00041	HL
1919.	13	11					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00040	HL
1920.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00011	CL
1921.	13	12					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00041	HL
1922.	13	13					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00040	HL
1923.	13	14					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00041	HL
1924.	13	15					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00040	HL
1925.	13	16					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00041	HL
1926.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00011	CL
1927.	13	17					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00040	HL
1928.	13	18					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00041	HL
1929.	13	19					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00043	HL
1930.							TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00044	HL
1931.	13	20					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00038	HL
1932.	13	21					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00038	HL
1933.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00010	CL
1934.	13	22					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00038	HL
1935.	13	23					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00038	HL
1936.	13	24					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL
1937.	13	25					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL
1938.	13	26					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL
1939.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00010	CL
1940.	13	27					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL
1941.	13	28					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL
1942.	13	29					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL
1943.	13	30					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL
1944.	13	31					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL
1945.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00010	CL
1946.	13	32					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL
1947.	13	33					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL
1948.	13	34					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL
1949.	13	35					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL
1950.	13	36					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL
1951.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00010	CL
1952.	13	37					TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00006	HL
1953.	13	38					TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00006	HL
1954.	13	39					TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00006	HL
1955.	13	40					TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00006	HL
1956.	13	41					TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00006	HL
1957.							TEHTEC	P4202	rpri	A610MULC	SG30CCAL00001	CL
1958.	13	42					TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00006	HL
1959.	13	43					TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00006	HL
1960.	13	44					TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00006	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: C
 DATABASE: Harris_SGC_1995

Sep. 23.1995 14:28

PAGE 42 of 128

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
1961.	13	45						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00006	HL
1962.	13	46						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00006	HL
1963.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00001	CL
1964.	13	47						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00006	HL
1965.	13	48						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00006	HL
1966.	13	49						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00006	HL
1967.	13	50						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00006	HL
1968.	13	51						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00006	HL
1969.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00001	CL
1970.	13	52						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00006	HL
1971.	13	53						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00008	HL
1972.	13	54						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00008	HL
1973.	13	55						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00008	HL
1974.	13	56						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00008	HL
1975.								TEHTEC	M9082	rsec	A610MULC	SG30CCAL00001	CL
1976.	13	57						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL
1977.	13	58						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL
1978.	13	59						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL
1979.								TEHTEC	C1115	rsec	A610MULC	SG30CCAL00007	CL
1980.	13	60						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL
81.	13	61						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL
82.	13	62						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL
83.	13	63						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL
1984.	13	64						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL
1985.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00008	CL
1986.	13	65						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL
1987.	13	66						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL
1988.	13	67						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL
1989.	13	68						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
1990.	13	69						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
1991.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00008	CL
1992.	13	70						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
1993.	13	71						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
1994.	13	72						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
1995.	13	73						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
1996.	13	74						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
1997.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00008	CL
1998.	13	75						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
1999.	13	76						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
2000.	13	77						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00016	HL
2001.	13	78						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00016	HL
2002.	13	79						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00018	HL
2003.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00004	CL
2004.	13	80						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00018	HL
2005.	13	81						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00018	HL
2006.	13	82						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00018	HL
2007.	13	83						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00018	HL
8.	13	84						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00018	HL
09.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00004	CL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: C
 DATABASE: Harris_SGC_1995

Sep. 23.1995 14:28

PAGE 43 of 128

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
2010.	13	85						TSHTSH	85534	rpri	B620MRPC3C	SG31HCAL00018	HL
2011.	13	86						TSHTSH	85534	rpri	B620MRPC3C	SG31HCAL00018	HL
2012.	13	87						TSHTSH	85534	rpri	B620MRPC3C	SG31HCAL00018	HL
2013.	13	88						TSHTSH	85534	rpri	B620MRPC3C	SG31HCAL00018	HL
2014.	13	89						TSHTSH	85534	rpri	B620MRPC3C	SG31HCAL00018	HL
2015.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00004	CL
2016.	13	90						TSHTSH	85534	rpri	B620MRPC3C	SG31HCAL00018	HL
2017.	13	91						TSHTSH	85534	rpri	B620MRPC3C	SG31HCAL00018	HL
2018.	13	92						TSHTSH	85534	rpri	B620MRPC3C	SG31HCAL00018	HL
2019.	13	93						TSHTSH	85534	rpri	B620MRPC3C	SG31HCAL00018	HL
2020.	13	94						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
2021.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00003	CL
2022.	13	95						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
2023.	13	96						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
2024.	13	97						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
2025.	13	98						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
2026.	13	99						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
2027.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00003	CL
2028.	13	100						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
2029.	13	101						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
30.	13	102						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
1.	13	103						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
2.	13	104						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00011	HL
2033.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00003	CL
2034.	13	105						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00012	HL
2035.	13	106						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00011	HL
2036.	13	107						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00012	HL
2037.	13	108						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00011	HL
2038.	13	109						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00012	HL
2039.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00003	CL
2040.	13	110						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00011	HL
2041.	13	111						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00012	HL
2042.	13	112						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00011	HL
2043.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00003	CL
2044.	14	3						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00040	HL
2045.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00011	CL
2046.	14	4						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00041	HL
2047.	14	5						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00040	HL
2048.	14	6						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00041	HL
2049.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00011	CL
2050.	14	7						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00040	HL
2051.	14	8						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00041	HL
2052.	14	9						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00040	HL
2053.	14	10						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00041	HL
2054.	14	11						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00040	HL
2055.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00011	CL
2056.	14	12						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00041	HL
2057.	14	13						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00040	HL
2058.	14	14						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00041	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: C
 DATABASE: Harris_SGC_1995

Sep. 23.1995 14:28

PAGE 44 of 128

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
2059.	14	15					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00040	HL
2060.	14	16					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00041	HL
2061.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00011	CL
2062.	14	17					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00040	HL
2063.	14	18					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00041	HL
2064.	14	19					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00043	HL
2065.							TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00044	HL
2066.	14	20					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00039	HL
2067.	14	21					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00039	HL
2068.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00010	CL
2069.	14	22					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00039	HL
2070.	14	23					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00039	HL
2071.	14	24					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL
2072.	14	25					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL
2073.	14	26					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL
2074.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00010	CL
2075.	14	27					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL
2076.	14	28					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL
2077.	14	29					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL
2078.	14	30					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL
79.	14	31					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL
80.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00010	CL
81.	14	32					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL
2082.	14	33					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL
2083.	14	34					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL
2084.	14	35					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL
2085.	14	36					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL
2086.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00010	CL
2087.	14	37					TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00005	HL
2088.	14	38					TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00005	HL
2089.	14	39					TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00005	HL
2090.	14	40					TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00005	HL
2091.	14	41					TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00005	HL
2092.							TEHTEC	P4202	rpri	A610MULC	SG30CCAL00001	CL
2093.	14	42					TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00005	HL
2094.	14	43					TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00005	HL
2095.	14	44					TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00005	HL
2096.	14	45					TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00005	HL
2097.	14	46					TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00005	HL
2098.							TEHTEC	P4202	rpri	A610MULC	SG30CCAL00001	CL
2099.	14	47					TSHTSH	K6733	rsec	B620MRPC3C	SG31HCAL00005	HL
2100.	14	48					TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00005	HL
2101.	14	49					TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00005	HL
2102.	14	50					TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00005	HL
2103.	14	51					TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00005	HL
2104.							TEHTEC	P4202	rpri	A610MULC	SG30CCAL00001	CL
2105.	14	52					TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00005	HL
2106.	14	53					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00007	HL
2107.	14	54					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00007	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: C
 DATABASE: Harris_SGC_1995

Sep. 23.1995 14:28

PAGE 45 of 128

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
2108.	14	55						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00007	HL
2109.	14	56						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00007	HL
2110.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00001	CL
2111.	14	57						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
2112.	14	58						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
2113.	14	59						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
2114.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00007	CL
2115.	14	60						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
2116.	14	61						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
2117.	14	62						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
2118.	14	63						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
2119.	14	64						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
2120.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00008	CL
2121.	14	65						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
2122.	14	66						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
2123.	14	67						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
2124.	14	68						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
2125.	14	69						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
2126.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00008	CL
2127.	14	70						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
28.	14	71						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
29.	14	72						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
30.	14	73						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
2131.	14	74						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
2132.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00008	CL
2133.	14	75						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
2134.	14	76						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
2135.	14	77						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00015	HL
2136.		2.29	139	29	1	02C	1.90	TEHTEC	P4202	rpri	A610MULC	SG30CCAL00004	CL
2137.	14	78						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00015	HL
2138.		42.16	154	15	1	02C	-0.03	TEHTEC	H1274	reso	A610MULC	SG30CCAL00004	CL
2139.	14	79						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00017	HL
2140.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00004	CL
2141.	14	80						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00017	HL
2142.	14	81						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00017	HL
2143.	14	82						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00017	HL
2144.	14	83						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00017	HL
2145.	14	84						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00017	HL
2146.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00004	CL
2147.	14	85						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00017	HL
2148.	14	86						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00017	HL
2149.	14	87						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00017	HL
2150.	14	88						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00017	HL
2151.	14	89						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00017	HL
2152.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00004	CL
2153.	14	90						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00017	HL
2154.	14	91						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00017	HL
2155.	14	92						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00017	HL
2156.	14	93						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00017	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: C
 DATABASE: Harris_SGC_1995

Sep. 23.1995 14:28

PAGE 46 of 128

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
2157.	14	94					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
2158.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00003	CL
2159.	14	95					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
2160.	14	96					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
2161.	14	97					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
2162.	14	98					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
2163.	14	99					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
2164.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00003	CL
2165.	14	100					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
2166.	14	101					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
2167.	14	102					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
2168.	14	103					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
2169.	14	104					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00011	HL
2170.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00003	CL
2171.	14	105					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00012	HL
2172.	14	106					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00011	HL
2173.	14	107					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00012	HL
2174.	14	108					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00011	HL
2175.	14	109					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00012	HL
2176.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00003	CL
77.	14	110					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00011	HL
78.	14	111					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00012	HL
79.	14	112					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00011	HL
2180.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00003	CL
2181.	15	3					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00040	HL
2182.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00011	CL
2183.	15	4					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00041	HL
2184.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00011	CL
2185.	15	5					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00040	HL
2186.	15	6					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00041	HL
2187.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00011	CL
2188.	15	7					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00040	HL
2189.	15	8					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00041	HL
2190.	15	9					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00040	HL
2191.	15	10					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00041	HL
2192.	15	11					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00040	HL
2193.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00011	CL
2194.	15	12					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00041	HL
2195.	15	13					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00040	HL
2196.	15	14					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00041	HL
2197.	15	15					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00040	HL
2198.	15	16					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00041	HL
2199.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00011	CL
2200.	15	17					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00040	HL
2201.	15	18					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00041	HL
2202.	15	19					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00043	HL
2203.							TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00044	HL
2204.	15	20					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00038	HL
2205.	15	21					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00038	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: C
 DATABASE: Harris_SGC_1995

Sep. 23.1995 14:28

PAGE 47 of 128

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
2206.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00010	CL
2207.	15	22						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00038	HL
2208.	15	23						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL
2209.	15	24						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL
2210.	15	25						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL
2211.	15	26						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL
2212.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00010	CL
2213.	15	27						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL
2214.	15	28						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL
2215.	15	29						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL
2216.	15	30						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL
2217.	15	31						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL
2218.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00010	CL
2219.	15	32						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL
2220.	15	33						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL
2221.	15	34						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL
2222.	15	35						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL
2223.	15	36						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL
2224.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00010	CL
2225.	15	37						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00006	HL
26.	15	38						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00006	HL
7.	15	39						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00006	HL
28.	15	40						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00006	HL
2229.	15	41						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00006	HL
2230.								TEHTEC	M9082	rsec	A610MULC	SG30CCAL00001	CL
2231.	15	42						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00006	HL
2232.	15	43						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00006	HL
2233.	15	44						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00006	HL
2234.	15	45						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00006	HL
2235.	15	46						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00006	HL
2236.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00001	CL
2237.	15	47						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00006	HL
2238.	15	48	1.37	163	SCI	1	TSH -0.14	TSHTSH	K6733	rsec	B620MRPC3C	SG31HCAL00006	HL
2239.					PID	1	TSH -0.08	TSHTSH	J9815	rsec	B620MRPC3C	SG31HCAL00023	HL
2240.	15	49						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00006	HL
2241.	15	50						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00006	HL
2242.	15	51						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00006	HL
2243.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00001	CL
2244.	15	52						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00006	HL
2245.	15	53						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00008	HL
2246.	15	54						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00008	HL
2247.	15	55						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00008	HL
2248.	15	56						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00008	HL
2249.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00001	CL
2250.	15	57						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL
2251.	15	58						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL
2252.	15	59						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL
2253.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00007	CL
2254.	15	60						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: C
 DATABASE: Harris_SGC_1995

Sep. 23.1995 14:28

PAGE 48 of 128

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
2255.	15	61						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL
2256.	15	62						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL
2257.	15	63						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL
2258.	15	64						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL
2259.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00008	CL
2260.	15	65						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL
2261.	15	66						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL
2262.	15	67						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL
2263.								TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
2264.	15	68						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
2265.	15	69						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
2266.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00008	CL
2267.	15	70						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
2268.	15	71						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
2269.	15	72						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
2270.	15	73						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
2271.	15	74						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
2272.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00008	CL
2273.	15	75						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
2274.	15	76						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
75.	15	77						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00016	HL
76.	15	78						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00016	HL
77.	15	79						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00018	HL
2278.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00004	CL
2279.	15	80						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00018	HL
2280.	15	81						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00018	HL
2281.	15	82						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00018	HL
2282.	15	83						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00018	HL
2283.	15	84						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00018	HL
2284.								01H01H	T7072	rpri	B620MRPC3C	SG31HCAL00026	HL
2285.		14.80	182	DNT	P1	01H	0.46	TEHTEC	P4202	rpri	A610MULC	SG30CCAL00004	CL
2286.	15	85						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00018	HL
2287.	15	86						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00018	HL
2288.	15	87						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00018	HL
2289.	15	88						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00018	HL
2290.	15	89						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00018	HL
2291.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00004	CL
2292.	15	90						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00018	HL
2293.	15	91						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00018	HL
2294.	15	92						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00018	HL
2295.	15	93						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00018	HL
2296.	15	94						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
2297.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00003	CL
2298.	15	95						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
2299.	15	96						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
2300.	15	97						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
2301.	15	98						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
2302.	15	99						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
2303.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00003	CL

*** INSPECTION FINAL REPORT LISTING ***

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: C
 DATABASE: Harris_SGC_1995

Sep. 23, 1995 14:28

PAGE 49 of 128

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
2304.	15	100					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
2305.	15	101					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
2306.	15	102					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
2307.	15	103					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
2308.	15	104					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00011	HL
2309.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00003	CL
2310.	15	105					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00012	HL
2311.	15	106					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00011	HL
2312.	15	107					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00012	HL
2313.	15	108					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00011	HL
2314.	15	109					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00012	HL
2315.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00003	CL
2316.	15	110					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00011	HL
2317.	15	111					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00012	HL
2318.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00003	CL
2319.	15	112					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00011	HL
2320.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00003	CL
2321.	16	4					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00040	HL
2322.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00011	CL
2323.	16	5					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00041	HL
2324.	16	6					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00040	HL
2325.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00011	CL
2326.	16	7					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00041	HL
2327.	16	8					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00040	HL
2328.	16	9					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00041	HL
2329.	16	10					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00040	HL
2330.	16	11					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00041	HL
2331.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00011	CL
2332.	16	12					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00040	HL
2333.	16	13					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00041	HL
2334.	16	14					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00040	HL
2335.	16	15					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00041	HL
2336.	16	16					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00040	HL
2337.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00011	CL
2338.	16	17					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00041	HL
2339.	16	18					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00040	HL
2340.	16	19					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00041	HL
2341.	16	20					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00039	HL
2342.	16	21					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00039	HL
2343.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00010	CL
2344.	16	22					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00039	HL
2345.	16	23					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL
2346.	16	24					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL
2347.	16	25					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL
2348.	16	26					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL
2349.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00010	CL
2350.	16	27					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL
2351.	16	28					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL
2352.	16	29					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: C
 DATABASE: Harris_SGC_1995

Sep. 23,1995 14:28

PAGE 50 of 128

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
2353.	16	30					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL
2354.	16	31					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL
2355.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00010	CL
2356.	16	32					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL
2357.	16	33					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL
2358.	16	34					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL
2359.	16	35					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL
2360.	16	36					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL
2361.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00010	CL
2362.	16	37					TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00005	HL
2363.	16	38					TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00005	HL
2364.	16	39					TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00005	HL
2365.	16	40					TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00005	HL
2366.	16	41					TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00005	HL
2367.							TEHTEC	P4202	rpri	A610MULC	SG30CCAL00001	CL
2368.	16	42					TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00005	HL
2369.	16	43					TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00005	HL
2370.	16	44					TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00005	HL
2371.	16	45					TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00005	HL
2372.	16	46					TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00005	HL
73.							TEHTEC	P4202	rpri	A610MULC	SG30CCAL00001	CL
1.	16	47					TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00005	HL
75.	16	48					TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00005	HL
2376.	16	49					TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00005	HL
2377.	16	50					TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00005	HL
2378.	16	51					TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00005	HL
2379.							TEHTEC	P4202	rpri	A610MULC	SG30CCAL00001	CL
2380.	16	52					TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00005	HL
2381.	16	53					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00007	HL
2382.	16	54					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00007	HL
2383.	16	55					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00007	HL
2384.	16	56					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00007	HL
2385.							TEHTEC	P4202	rpri	A610MULC	SG30CCAL00001	CL
2386.	16	57					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
2387.	16	58					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
2388.	16	59					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
2389.							TEHTEC	P4202	rpri	A610MULC	SG30CCAL00007	CL
2390.	16	60					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
2391.	16	61					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
2392.	16	62					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
2393.	16	63					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
2394.	16	64					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
2395.							TEHTEC	P4202	rpri	A610MULC	SG30CCAL00008	CL
2396.	16	65					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
2397.	16	66					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
2398.	16	67					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
9.							TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
0.	16	68					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
01.	16	69					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL

*** INSPECTION FINAL REPORT LISTING ***

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: C
 DATABASE: Harris_SGC_1995

Sep. 23.1995 14:28

PAGE 51 of 128

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
2402.							TEHTEC	P4202	rpri	A610MULC	SG30CCAL00008	CL
2403.	16	70					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
2404.	16	71					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
2405.	16	72					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
2406.	16	73					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
2407.	16	74					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
2408.							TEHTEC	P4202	rpri	A610MULC	SG30CCAL00008	CL
2409.	16	75					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
2410.	16	76					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
2411.	16	77					TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00015	HL
2412.	16	78					TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00015	HL
2413.	16	79					TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00017	HL
2414.							TEHTEC	P4202	rpri	A610MULC	SG30CCAL00004	CL
2415.	16	80					TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00017	HL
2416.	16	81					TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00017	HL
2417.	16	82					TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00017	HL
2418.	16	83					TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00017	HL
2419.	16	84					TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00017	HL
2420.							TEHTEC	P4202	rpri	A610MULC	SG30CCAL00004	CL
2421.	16	85					TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00017	HL
22.	16	86					TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00017	HL
3.	16	87					TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00017	HL
4.	16	88					TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00017	HL
2425.	16	89					TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00017	HL
2426.							TEHTEC	P4202	rpri	A610MULC	SG30CCAL00004	CL
2427.	16	90					TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00017	HL
2428.	16	91					TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00017	HL
2429.	16	92					TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00017	HL
2430.	16	93					TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00017	HL
2431.	16	94					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
2432.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00003	CL
2433.	16	95					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
2434.	16	96					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
2435.	16	97					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
2436.	16	98					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
2437.	16	99					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
2438.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00003	CL
2439.	16	100					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
2440.	16	101					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
2441.	16	102					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
2442.	16	103					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
2443.	16	104					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00011	HL
2444.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00003	CL
2445.	16	105					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00012	HL
2446.	16	106					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00011	HL
2447.	16	107					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00012	HL
18.	16	108					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00011	HL
9.	16	109					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00012	HL
10.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00003	CL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: C
 DATABASE: Harris_SGC_1995

Sep. 23,1995 14:28

PAGE 52 of 128

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE	SIZE	CAL GROUP	LEG
2451.	16	110						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00011	HL	
2452.	16	111						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00012	HL	
2453.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00003	CL	
2454.	17	4						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00040	HL	
2455.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00011	CL	
2456.	17	5						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00041	HL	
2457.	17	6						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00040	HL	
2458.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00011	CL	
2459.	17	7						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00041	HL	
2460.	17	8						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00040	HL	
2461.	17	9						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00041	HL	
2462.	17	10						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00040	HL	
2463.	17	11						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00041	HL	
2464.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00011	CL	
2465.	17	12						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00040	HL	
2466.	17	13						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00041	HL	
2467.	17	14						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00040	HL	
2468.	17	15						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00041	HL	
2469.	17	16						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00040	HL	
2470.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00011	CL	
71.	17	17						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00041	HL	
72.	17	18						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00040	HL	
73.	17	19						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00041	HL	
2474.	17	20						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00038	HL	
2475.	17	21						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00038	HL	
2476.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00010	CL	
2477.	17	22						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00038	HL	
2478.	17	23						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL	
2479.	17	24						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL	
2480.	17	25						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL	
2481.	17	26						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL	
2482.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00010	CL	
2483.	17	27						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL	
2484.	17	28						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL	
2485.	17	29						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL	
2486.	17	30						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL	
2487.	17	31						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL	
2488.								TEHTEC	C3335	reso	A610MULC	SG30CCAL00010	CL	
2489.	17	32						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL	
2490.	17	33						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL	
2491.	17	34						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL	
2492.	17	35						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL	
2493.	17	36						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL	
2494.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00010	CL	
2495.	17	37						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00006	HL	
2496.	17	38						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00006	HL	
2497.	17	39						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00006	HL	
2498.	17	40						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00006	HL	
2499.	17	41						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00006	HL	

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: C
 DATABASE: Harris_SGC_1995

Sep. 23.1995 14:28

PAGE 53 of 128

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
2500.							TEHTEC	P4202	rpri	A610MULC	SG30CCAL00001	CL
2501.	17	42					TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00006	HL
2502.	17	43					TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00006	HL
2503.	17	44					TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00006	HL
2504.	17	45					TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00006	HL
2505.	17	46					TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00006	HL
2506.							TEHTEC	P4202	rpri	A610MULC	SG30CCAL00001	CL
2507.	17	47					TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00006	HL
2508.	17	48					TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00006	HL
2509.	17	49					TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00006	HL
2510.	17	50					TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00006	HL
2511.	17	51					TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00006	HL
2512.							TEHTEC	P4202	rpri	A610MULC	SG30CCAL00001	CL
2513.	17	52					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00008	HL
2514.	17	53					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00008	HL
2515.	17	54					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00008	HL
2516.	17	55					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00008	HL
2517.	17	56					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00008	HL
2518.							TEHTEC	P4202	rpri	A610MULC	SG30CCAL00001	CL
2519.	17	57					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL
20.	17	58					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL
1.	17	59					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL
2.							TEHTEC	P4202	rpri	A610MULC	SG30CCAL00007	CL
2523.	17	60					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL
2524.	17	61					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL
2525.	17	62					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL
2526.	17	63					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL
2527.	17	64					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL
2528.							TEHTEC	P4202	rpri	A610MULC	SG30CCAL00008	CL
2529.	17	65					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL
2530.	17	66					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL
2531.	17	67					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
2532.	17	68					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
2533.	17	69					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
2534.							TEHTEC	P4202	rpri	A610MULC	SG30CCAL00008	CL
2535.	17	70					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
2536.	17	71					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
2537.	17	72					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
2538.	17	73					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
2539.	17	74					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
2540.							TEHTEC	P4202	rpri	A610MULC	SG30CCAL00008	CL
2541.	17	75					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
2542.	17	76					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
2543.	17	77					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00016	HL
2544.	17	78					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00016	HL
2545.	17	79					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00018	HL
16.							TEHTEC	P4202	rpri	A610MULC	SG30CCAL00004	CL
17.	17	80					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00018	HL
18.	17	81					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00018	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: C
 DATABASE: Harris_SGC_1995

Sep. 23.1995 14:28

PAGE 54 of 128

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
2549.	17	82					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00018	HL
2550.	17	83					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00018	HL
2551.	17	84					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00018	HL
2552.							TEHTEC	P4202	rpri	A610MULC	SG30CCAL00004	CL
2553.	17	85					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00018	HL
2554.	17	86					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00018	HL
2555.	17	87					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00018	HL
2556.	17	88					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00018	HL
2557.	17	89					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00018	HL
2558.							TEHTEC	P4202	rpri	A610MULC	SG30CCAL00004	CL
2559.	17	90					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00018	HL
2560.	17	91					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00018	HL
2561.	17	92					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00018	HL
2562.	17	93					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00018	HL
2563.	17	94					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
2564.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00003	CL
2565.	17	95					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
2566.	17	96					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
2567.	17	97					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
2568.	17	98					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
69.	17	99					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
70.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00003	CL
71.	17	100					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
2572.	17	101					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
2573.	17	102					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
2574.	17	103					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
2575.	17	104					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00011	HL
2576.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00003	CL
2577.	17	105					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00012	HL
2578.	17	106					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00011	HL
2579.	17	107					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00012	HL
2580.	17	108					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00011	HL
2581.	17	109					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00012	HL
2582.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00003	CL
2583.	17	110					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00011	HL
2584.	17	111					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00012	HL
2585.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00003	CL
2586.	18	4					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00040	HL
2587.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00011	CL
2588.	18	5					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00041	HL
2589.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00011	CL
2590.	18	6					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00040	HL
2591.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00011	CL
2592.	18	7					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00041	HL
2593.	18	8					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00040	HL
2594.	18	9					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00041	HL
2595.	18	10					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00040	HL
2596.	18	11					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00041	HL
2597.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00011	CL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: C
 DATABASE: Harris_SGC_1995

Sep. 23,1995 14:28

PAGE 55 of 128

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
2598.	18	12					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00040	HL
2599.	18	13					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00041	HL
2600.	18	14					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00040	HL
2601.	18	15					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00041	HL
2602.	18	16					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00040	HL
2603.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00011	CL
2604.	18	17					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00041	HL
2605.	18	18					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00040	HL
2606.	18	19					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00041	HL
2607.	18	20					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00039	HL
2608.	18	21					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00039	HL
2609.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00010	CL
2610.	18	22					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00039	HL
2611.	18	23					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL
2612.	18	24					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL
2613.	18	25					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL
2614.	18	26					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL
2615.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00010	CL
2616.	18	27					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL
2617.	18	28					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL
18.	18	29					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL
3.	18	30					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL
20.	18	31					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL
2621.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00010	CL
2622.	18	32					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL
2623.	18	33					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL
2624.	18	34					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL
2625.	18	35					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL
2626.	18	36					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL
2627.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00010	CL
2628.	18	37					TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00005	HL
2629.	18	38					TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00005	HL
2630.	18	39					TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00005	HL
2631.	18	40					TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00005	HL
2632.	18	41					TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00005	HL
2633.							TEHTEC	P4202	rpri	A610MULC	SG30CCAL00001	CL
2634.	18	42					TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00005	HL
2635.	18	43					TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00005	HL
2636.	18	44					TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00005	HL
2637.	18	45					TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00005	HL
2638.	18	46					TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00005	HL
2639.							TEHTEC	P4202	rpri	A610MULC	SG30CCAL00001	CL
2640.	18	47					TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00005	HL
2641.	18	48					TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00005	HL
2642.	18	49					TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00005	HL
43.	18	50					TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00005	HL
4.	18	51					TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00005	HL
5.							TEHTEC	P4202	rpri	A610MULC	SG30CCAL00001	CL
6.	18	52					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00007	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: C
 DATABASE: Harris_SGC_1995

Sep. 23.1995 14:28

PAGE 56 of 128

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
2647.	18	53						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00007	HL
2648.	18	54						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00007	HL
2649.	18	55						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00007	HL
2650.	18	56						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00007	HL
2651.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00001	CL
2652.	18	57						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
2653.	18	58						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
2654.	18	59						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
2655.		41.65	180	DNT	1	01H	3.78	TEHTEC	P4202	rpri	A610MULC	SG30CCAL00007	CL
2656.	18	60						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
2657.	18	61						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
2658.	18	62						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
2659.	18	63						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
2660.	18	64						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
2661.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00008	CL
2662.	18	65						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
2663.	18	66						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
2664.	18	67						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
2665.	18	68						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
2666.	18	69						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
67.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00008	CL
69.	18	70						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
69.	18	71						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
2670.	18	72						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
2671.	18	73						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
2672.	18	74						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
2673.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00008	CL
2674.	18	75						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
2675.	18	76						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
2676.	18	77						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00015	HL
2677.	18	78						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00015	HL
2678.	18	79						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00017	HL
2679.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00004	CL
2680.	18	80						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00017	HL
2681.	18	81						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00017	HL
2682.	18	82						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00017	HL
2683.	18	83						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00017	HL
2684.	18	84						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00017	HL
2685.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00004	CL
2686.	18	85						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00017	HL
2687.	18	86						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00017	HL
2688.	18	87						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00017	HL
2689.	18	88						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00017	HL
2690.	18	89						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00017	HL
2691.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00004	CL
92.	18	90						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00017	HL
93.	18	91						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00017	HL
94.	18	92						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00017	HL
95.	18	93						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00017	HL

*** INSPECTION FINAL REPORT LISTING ***

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: C
 DATABASE: Harris_SGC_1995

Sep. 23.1995 14:28

PAGE 57 of 128

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
2696.	18	94						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
2697.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00003	CL
2698.	18	95						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
2699.	18	96						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
2700.				INR		09C	7.39	TEHTEC	B3052	reso	A610MULC	SG30CCAL00003	CL
2701.	18	97						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
2702.	18	98						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
2703.	18	99						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
2704.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00003	CL
2705.	18	100						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
2706.	18	101						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
2707.	18	102						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
2708.	18	103						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
2709.	18	104						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00011	HL
2710.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00003	CL
2711.	18	105						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00012	HL
2712.	18	106						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00011	HL
2713.	18	107						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00012	HL
2714.	18	108						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00011	HL
2715.	18	109						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00012	HL
16.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00003	CL
7.	18	110						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00011	HL
18.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00003	CL
2719.	18	111						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00012	HL
2720.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00003	CL
2721.	19	5						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00040	HL
2722.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00011	CL
2723.	19	6						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00041	HL
2724.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00011	CL
2725.	19	7						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00040	HL
2726.	19	8						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00041	HL
2727.	19	9						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00040	HL
2728.	19	10						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00041	HL
2729.	19	11						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00040	HL
2730.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00011	CL
2731.	19	12						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00041	HL
2732.	19	13						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00040	HL
2733.	19	14						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00041	HL
2734.	19	15						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00040	HL
2735.	19	16						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00041	HL
2736.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00011	CL
2737.	19	17						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00040	HL
2738.	19	18						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00041	HL
2739.	19	19						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00043	HL
2740.								TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00044	HL
2741.	19	20						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00038	HL
2742.	19	21						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00038	HL
2743.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00010	CL
2744.	19	22						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00038	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: C
 DATABASE: Harris_SGC_1995

Sep. 23.1995 14:28

PAGE 58 of 128

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
2745.	19	23						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL
2746.	19	24						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL
2747.	19	25						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL
2748.	19	26						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL
2749.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00010	CL
2750.	19	27						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL
2751.	19	28						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL
2752.	19	29						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL
2753.	19	30						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL
2754.	19	31						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL
2755.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00010	CL
2756.	19	32						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL
2757.	19	33						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL
2758.	19	34						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL
2759.	19	35						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL
2760.	19	36						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL
2761.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00010	CL
2762.	19	37						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00006	HL
2763.	19	38						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00006	HL
2764.	19	39						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00006	HL
65.	19	40						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00006	HL
65.	19	41						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00006	HL
67.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00001	CL
2768.	19	42						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00006	HL
2769.	19	43						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00006	HL
2770.	19	44						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00006	HL
2771.	19	45						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00006	HL
2772.	19	46						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00006	HL
2773.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00001	CL
2774.	19	47						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00006	HL
2775.	19	48						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00006	HL
2776.	19	49						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00006	HL
2777.	19	50						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00006	HL
2778.	19	51						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00006	HL
2779.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00001	CL
2780.	19	52						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00008	HL
2781.	19	53						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00008	HL
2782.	19	54						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00008	HL
2783.	19	55						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00008	HL
2784.	19	56						TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00008	HL
2785.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00001	CL
2786.	19	57						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL
2787.	19	58						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL
2788.	19	59						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL
2789.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00007	CL
790.	19	60						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL
791.	19	61						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL
792.	19	62						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL
793.	19	63						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: C
 DATABASE: Harris_SGC_1995

Sep. 23.1995 14:28

PAGE 59 of 128

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
2794.	19	64					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL
2795.							TEHTEC	P4202	rpri	A610MULC	SG30CCAL00008	CL
2796.	19	65					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL
2797.	19	66					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL
2798.	19	67					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
2799.	19	68					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
2800.	19	69					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
2801.							TEHTEC	P4202	rpri	A610MULC	SG30CCAL00008	CL
2802.	19	70					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
2803.	19	71					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
2804.	19	72					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
2805.	19	73					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
2806.	19	74					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
2807.							TEHTEC	P4202	rpri	A610MULC	SG30CCAL00008	CL
2808.	19	75					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
2809.	19	76					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
2810.	19	77					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00016	HL
2811.	19	78					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00016	HL
2812.	19	79					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00018	HL
2813.							TEHTEC	P4202	rpri	A610MULC	SG30CCAL00004	CL
14.	19	80					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00018	HL
15.	19	81					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00018	HL
16.	19	82					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00018	HL
2817.	19	83					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00018	HL
2818.	19	84					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00018	HL
2819.							TEHTEC	P4202	rpri	A610MULC	SG30CCAL00004	CL
2820.	19	85					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00018	HL
2821.	19	86					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00018	HL
2822.	19	87					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00018	HL
2823.	19	88					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00018	HL
2824.	19	89					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00018	HL
2825.							TEHTEC	P4202	rpri	A610MULC	SG30CCAL00004	CL
2826.	19	90					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00018	HL
2827.	19	91					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00018	HL
2828.	19	92					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00018	HL
2829.	19	93					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00018	HL
2830.	19	94					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
2831.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00003	CL
2832.	19	95					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
2833.	19	96					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
2834.	19	97					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
2835.	19	98					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
2836.	19	99					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
2837.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00003	CL
2838.	19	100					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
2839.	19	101					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
100.	19	102					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
101.	19	103					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
102.	19	104					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00011	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: C
 DATABASE: Harris_SGC_1995

Sep. 23.1995 14:28

PAGE 60 of 128

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
2843.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00003	CL
2844.	19	105					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00012	HL
2845.	19	106					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00011	HL
2846.	19	107					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00012	HL
2847.	19	108					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00011	HL
2848.	19	109					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00012	HL
2849.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00003	CL
2850.	19	110					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00011	HL
2851.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00003	CL
2852.	20	5					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00040	HL
2853.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00011	CL
2854.	20	6					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00041	HL
2855.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00011	CL
2856.	20	7					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00040	HL
2857.	20	8					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00041	HL
2858.	20	9					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00040	HL
2859.	20	10					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00041	HL
2860.	20	11					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00040	HL
2861.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00011	CL
2862.	20	12					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00041	HL
63.	20	13					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00040	HL
1.	20	14					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00041	HL
5.	20	15					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00040	HL
2866.	20	16					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00041	HL
2867.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00011	CL
2868.	20	17					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00040	HL
2869.	20	18					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00041	HL
2870.	20	19					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00043	HL
2871.							TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00044	HL
2872.	20	20					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00039	HL
2873.	20	21					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00039	HL
2874.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00010	CL
2875.	20	22					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00039	HL
2876.	20	23					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL
2877.	20	24					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL
2878.	20	25					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL
2879.	20	26					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL
2880.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00010	CL
2881.	20	27					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL
2882.	20	28					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL
2883.	20	29					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL
2884.	20	30					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL
2885.	20	31					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL
2886.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00010	CL
2887.	20	32					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL
288.	20	33					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL
9.	20	34					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL
0.	20	35					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL
1.	20	36					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: C
 DATABASE: Harris_SGC_1995

Sep. 23.1995 14:28

PAGE 61 of 128

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
2892.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00010	CL
2893.	20	37					TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00005	HL
2894.	20	38					TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00005	HL
2895.	20	39					TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00005	HL
2896.	20	40					TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00005	HL
2897.	20	41					TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00005	HL
2898.							TEHTEC	P4202	rpri	A610MULC	SG30CCAL00001	CL
2899.	20	42					TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00005	HL
2900.	20	43					TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00005	HL
2901.	20	44					TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00005	HL
2902.	20	45					TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00005	HL
2903.	20	46					TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00005	HL
2904.							TEHTEC	P4202	rpri	A610MULC	SG30CCAL00001	CL
2905.	20	47					TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00005	HL
2906.	20	48					TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00005	HL
2907.	20	49					TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00005	HL
2908.	20	50					TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00005	HL
2909.	20	51					TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00005	HL
2910.							TEHTEC	C7651	rsec	A610MULC	SG30CCAL00001	CL
2911.	20	52					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00007	HL
12.	20	53					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00007	HL
.	20	54					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00007	HL
4.	20	55					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00007	HL
2915.	20	56					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00007	HL
2916.							TEHTEC	P4202	rpri	A610MULC	SG30CCAL00001	CL
2917.	20	57					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
2918.	20	58					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
2919.	20	59					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
2920.							TEHTEC	P4202	rpri	A610MULC	SG30CCAL00007	CL
2921.	20	60					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
2922.	20	61					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
2923.	20	62					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
2924.	20	63					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
2925.	20	64					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
2926.							TEHTEC	P4202	rpri	A610MULC	SG30CCAL00008	CL
2927.	20	65					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
2928.	20	66					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
2929.	20	67					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
2930.	20	68					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
2931.	20	69					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
2932.							TEHTEC	P4202	rpri	A610MULC	SG30CCAL00008	CL
2933.	20	70					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
2934.	20	71					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
2935.	20	72					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
2936.	20	73					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
2937.	20	74					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
9.							TEHTEC	P4202	rpri	A610MULC	SG30CCAL00008	CL
10.	20	75					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
10.	20	76					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: C
 DATABASE: Harris_SGC_1995

Sep. 23.1995 14:28

PAGE 62 of 128

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
2941.	20	77					TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00015	HL
2942.	20	78					TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00017	HL
2943.	20	79					TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00017	HL
2944.							TEHTEC	P4202	rpri	A610MULC	SG30CCAL00004	CL
2945.	20	80					TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00017	HL
2946.	20	81					TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00017	HL
2947.	20	82					TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00017	HL
2948.	20	83					TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00017	HL
2949.	20	84					TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00017	HL
2950.							TEHTEC	P4202	rpri	A610MULC	SG30CCAL00004	CL
2951.	20	85					TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00017	HL
2952.	20	86					TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00017	HL
2953.	20	87					TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00017	HL
2954.	20	88					TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00017	HL
2955.	20	89					TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00017	HL
2956.							TEHTEC	P4202	rpri	A610MULC	SG30CCAL00004	CL
2957.	20	90					TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00017	HL
2958.	20	91					TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00017	HL
2959.	20	92					TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00017	HL
2960.	20	93					TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00017	HL
61.	20	94					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
62.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00003	CL
63.	20	95					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
2964.	20	96					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
2965.	20	97					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
2966.	20	98					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
2967.	20	99					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
2968.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00003	CL
2969.	20	100					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
2970.	20	101					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
2971.	20	102					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00009	HL
2972.	20	103					TSHTSH	05305	rpri	B620MRPC3C	SG31HCAL00010	HL
2973.	20	104					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00011	HL
2974.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00003	CL
2975.	20	105					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00012	HL
2976.	20	106					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00011	HL
2977.	20	107					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00012	HL
2978.	20	108					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00011	HL
2979.	20	109					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00012	HL
2980.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00003	CL
2981.	20	110					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00011	HL
2982.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00003	CL
2983.	21	5					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00040	HL
2984.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00011	CL
2985.	21	6					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00041	HL
2986.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00011	CL
2987.	21	7					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00040	HL
2988.	21	8					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00041	HL
2989.	21	9					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00040	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: C
 DATABASE: Harris_SGC_1995

Sep. 23,1995 14:28

PAGE 63 of 128

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
2990.	21	10					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00041	HL
2991.	21	11					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00040	HL
2992.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00011	CL
2993.	21	12					01HTSH	D4825	reso	B620MRPC3C	SG31HCAL00041	HL
2994.	21	13					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00040	HL
2995.	21	14					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00041	HL
2996.	21	15					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00040	HL
2997.	21	16					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00041	HL
2998.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00011	CL
2999.	21	17					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00040	HL
3000.	21	18					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00041	HL
3001.	21	19					TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00043	HL
3002.							TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00044	HL
3003.	21	20					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00038	HL
3004.	21	21					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00038	HL
3005.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00010	CL
3006.	21	22					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00038	HL
3007.	21	23					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL
3008.	21	24					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL
3009.	21	25					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL
10.	21	26					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL
1.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00010	CL
12.	21	27					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL
3013.	21	28					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL
3014.	21	29					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL
3015.	21	30					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL
3016.	21	31					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL
3017.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00010	CL
3018.	21	32					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL
3019.	21	33					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL
3020.	21	34					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL
3021.	21	35					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL
3022.	21	36					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00040	HL
3023.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00010	CL
3024.	21	37					TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00004	HL
3025.	21	38					TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00003	HL
3026.	21	39					TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00004	HL
3027.	21	40					TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00003	HL
3028.	21	41					TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00004	HL
3029.							TEHTEC	P4202	rpri	A610MULC	SG30CCAL00001	CL
3030.	21	42					TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00003	HL
3031.	21	43					TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00004	HL
3032.	21	44					TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00003	HL
3033.	21	45					TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00004	HL
3034.	21	46					TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00003	HL
35.							TEHTEC	P4202	rpri	A610MULC	SG30CCAL00001	CL
36.	21	47					TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00004	HL
7.	21	48					TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00003	HL
38.	21	49					TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00004	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: C
 DATABASE: Harris_SGC_1995

Sep. 23,1995 14:28

PAGE 64 of 128

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE	SIZE	CAL GROUP	LEG
3039.	21	50						TSHTSH	T5028	rpri	B620MRPC3C		SG31HCAL00003	HL
3040.	21	51						TSHTSH	T5028	rpri	B620MRPC3C		SG31HCAL00004	HL
3041.								TEHTEC	P4202	rpri	A610MULC		SG30CCAL00001	CL
3042.	21	52						TSHTSH	T5028	rpri	B620MRPC3C		SG31HCAL00003	HL
3043.	21	53						TSHTSH	T5028	rpri	B620MRPC3C		SG31HCAL00004	HL
3044.	21	54						TSHTSH	T5028	rpri	B620MRPC3C		SG31HCAL00003	HL
3045.	21	55						TSHTSH	T5028	rpri	B620MRPC3C		SG31HCAL00004	HL
3046.	21	56						TSHTSH	T5028	rpri	B620MRPC3C		SG31HCAL00003	HL
3047.								TEHTEC	P4202	rpri	A610MULC		SG30CCAL00001	CL
3048.	21	57						TSHTSH	F9284	rpri	B620MRPC3C		SG31HCAL00031	HL
3049.	21	58						TSHTSH	F9284	rpri	B620MRPC3C		SG31HCAL00031	HL
3050.	21	59						TSHTSH	F9284	rpri	B620MRPC3C		SG31HCAL00031	HL
3051.								TEHTEC	P4202	rpri	A610MULC		SG30CCAL00007	CL
3052.	21	60						TSHTSH	F9284	rpri	B620MRPC3C		SG31HCAL00031	HL
3053.	21	61						TSHTSH	F9284	rpri	B620MRPC3C		SG31HCAL00031	HL
3054.	21	62						TSHTSH	F9284	rpri	B620MRPC3C		SG31HCAL00031	HL
3055.	21	63						TSHTSH	F9284	rpri	B620MRPC3C		SG31HCAL00031	HL
3056.	21	64						TSHTSH	F9284	rpri	B620MRPC3C		SG31HCAL00031	HL
3057.								TEHTEC	C1115	rsec	A610MULC		SG30CCAL00007	CL
3058.	21	65						TSHTSH	F9284	rpri	B620MRPC3C		SG31HCAL00031	HL
3059.	21	66						TSHTSH	F9284	rpri	B620MRPC3C		SG31HCAL00031	HL
3060.	21	67						TSHTSH	P4202	rpri	B620MRPC3C		SG31HCAL00030	HL
3061.	21	68						TSHTSH	F9284	rpri	B620MRPC3C		SG31HCAL00031	HL
3062.	21	69						TSHTSH	P4202	rpri	B620MRPC3C		SG31HCAL00030	HL
3063.								TEHTEC	P4202	rpri	A610MULC		SG30CCAL00007	CL
3064.	21	70						TSHTSH	F9284	rpri	B620MRPC3C		SG31HCAL00031	HL
3065.	21	71						TSHTSH	P4202	rpri	B620MRPC3C		SG31HCAL00030	HL
3066.	21	72						TSHTSH	F9284	rpri	B620MRPC3C		SG31HCAL00031	HL
3067.	21	73						TSHTSH	P4202	rpri	B620MRPC3C		SG31HCAL00030	HL
3068.	21	74						TSHTSH	F9284	rpri	B620MRPC3C		SG31HCAL00031	HL
3069.								TEHTEC	P4202	rpri	A610MULC		SG30CCAL00007	CL
3070.	21	75						TSHTSH	P4202	rpri	B620MRPC3C		SG31HCAL00030	HL
3071.	21	76						TSHTSH	F9284	rpri	B620MRPC3C		SG31HCAL00031	HL
3072.	21	77						TSHTSH	P4202	rpri	B620MRPC3C		SG31HCAL00030	HL
3073.	21	78						TSHTSH	F9284	rpri	B620MRPC3C		SG31HCAL00031	HL
3074.	21	79						TSHTSH	P4202	rpri	B620MRPC3C		SG31HCAL00030	HL
3075.								TEHTEC	P4202	rpri	A610MULC		SG30CCAL00007	CL
3076.	21	80						TSHTSH	F9284	rpri	B620MRPC3C		SG31HCAL00031	HL
3077.	21	81						TSHTSH	P4202	rpri	B620MRPC3C		SG31HCAL00030	HL
3078.	21	82						TSHTSH	T7072	rpri	B620MRPC3C		SG31HCAL00015	HL
3079.	21	83						TSHTSH	B5534	rpri	B620MRPC3C		SG31HCAL00016	HL
3080.	21	84						TSHTSH	T7072	rpri	B620MRPC3C		SG31HCAL00015	HL
3081.								TEHTEC	P4202	rpri	A610MULC		SG30CCAL00004	CL
3082.	21	85						TSHTSH	B5534	rpri	B620MRPC3C		SG31HCAL00016	HL
3083.	21	86						TSHTSH	T7072	rpri	B620MRPC3C		SG31HCAL00015	HL
3084.	21	87						TSHTSH	B5534	rpri	B620MRPC3C		SG31HCAL00016	HL
3085.	21	88						TSHTSH	T7072	rpri	B620MRPC3C		SG31HCAL00015	HL
3086.	21	89						TSHTSH	B5534	rpri	B620MRPC3C		SG31HCAL00016	HL
3087.								TEHTEC	P4202	rpri	A610MULC		SG30CCAL00004	CL

*** INSPECTION FINAL REPORT LISTING ***

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: C
 DATABASE: Harris_SGC_1995

Sep. 23.1995 14:28

PAGE 65 of 128

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
3088.	21	90						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00015	HL
3089.	21	91						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00016	HL
3090.	21	92						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00015	HL
3091.	21	93						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00016	HL
3092.	21	94						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00011	HL
3093.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00003	CL
3094.	21	95						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00012	HL
3095.	21	96						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00011	HL
3096.	21	97						TSHTSH	C7651	rsec	B620MRPC3C	SG31HCAL00012	HL
3097.	21	98						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00011	HL
3098.	21	99						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00012	HL
3099.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00003	CL
3100.	21	100						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00011	HL
3101.	21	101						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00012	HL
3102.	21	102						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00011	HL
3103.	21	103						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00012	HL
3104.	21	104						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00011	HL
3105.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00003	CL
3106.	21	105						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00012	HL
3107.	21	106						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00011	HL
08.	21	107						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00012	HL
9.	21	108						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00013	HL
10.	21	109						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00014	HL
3111.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00004	CL
3112.	21	110						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00014	HL
3113.								04C04C	S7675	rpri	B620MRPC3C	SG30CCAL00021	CL
3114.								06C06C	S7675	rpri	B620MRPC3C	SG30CCAL00021	CL
3115.		9.70	177	DNT	P1	06C	0.74	TEHTEC	N0698	rpri	A610MULC	SG30CCAL00004	CL
3116.		25.71	177	DNT	P1	04C	0.52	TEHTEC	N0698	rpri	A610MULC	SG30CCAL00004	CL
3117.	22	6						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00040	HL
3118.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00011	CL
3119.	22	7						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00041	HL
3120.	22	8						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00040	HL
3121.	22	9						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00041	HL
3122.	22	10						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00040	HL
3123.	22	11						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00041	HL
3124.								TEHTEC	05305	rpri	A610MULC	SG30CCAL00013	CL
3125.	22	12						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00040	HL
3126.	22	13						01HTSH	04825	reso	B620MRPC3C	SG31HCAL00041	HL
3127.	22	14						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00040	HL
3128.	22	15						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00041	HL
3129.	22	16						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00040	HL
3130.								TEHTEC	05305	rpri	A610MULC	SG30CCAL00013	CL
3131.	22	17						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00041	HL
3132.	22	18						TSHTSH	S7675	rpri	B620MRPC3C	SG31HCAL00040	HL
33.	22	19						01HTSH	04825	reso	B620MRPC3C	SG31HCAL00041	HL
4.	22	20						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00039	HL
5.	22	21						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00039	HL
6.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00010	CL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: C
 DATABASE: Harris_SGC_1995

Sep. 23,1995 14:28

PAGE 66 of 128

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG	
3137.	22	22						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00039	HL	
3138.	22	23						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL	
3139.	22	24						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL	
3140.	22	25						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL	
3141.	22	26						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL	
3142.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00010	CL	
3143.	22	27						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL	
3144.	22	28						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL	
3145.	22	29						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL	
3146.	22	30						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL	
3147.	22	31						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL	
3148.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00010	CL	
3149.	22	32						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL	
3150.	22	33						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL	
3151.	22	34						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL	
3152.	22	35						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL	
3153.	22	36						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL	
3154.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00010	CL	
3155.	22	37						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00004	HL	
3156.	22	38						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00003	HL	
57.	22	39						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00004	HL	
58.	22	40						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00003	HL	
59.	22	41						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00004	HL	
3160.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00001	CL	
3161.	22	42						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00003	HL	
3162.	22	43						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00004	HL	
3163.	22	44						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00003	HL	
3164.	22	45						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00003	HL	
3165.	22	70						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL	
3166.	22	71			PID	TSH	-0.15	TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00037	HL	
3167.			1.25	27	SAI	1	TSH	-0.12	TSHTSH	C7651	rsec	B620MRPC3C	SG31HCAL00030	HL
3168.	22	72						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL	
3169.	22	74						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL	
3170.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00007	CL	
3171.	22	75						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL	
3172.	22	76						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL	
3173.	22	77						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL	
3174.	22	78						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL	
3175.	22	79						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL	
3176.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00007	CL	
3177.	22	80						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL	
3178.	22	81						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL	
3179.	22	82						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00015	HL	
3180.	22	83						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00016	HL	
3181.	22	84						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00015	HL	
82.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00004	CL	
83.	22	85						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00016	HL	
84.	22	86						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00015	HL	
85.	22	87						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00016	HL	

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: C
 DATABASE: Harris_SGC_1995

Sep. 23, 1995 14:28

PAGE 67 of 128

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
3186.	22	88						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00015	HL
3187.	22	89						TSHTSH	85534	rpri	B620MRPC3C	SG31HCAL00016	HL
3188.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00004	CL
3189.	22	90						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00015	HL
3190.	22	91						TSHTSH	85534	rpri	B620MRPC3C	SG31HCAL00016	HL
3191.	22	92						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00015	HL
3192.	22	93						TSHTSH	85534	rpri	B620MRPC3C	SG31HCAL00016	HL
3193.	22	94						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00011	HL
3194.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00003	CL
3195.	22	95						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00012	HL
3196.	22	96						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00011	HL
3197.	22	97						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00012	HL
3198.		0.64	160	MBM	1	08C	36.33	TEHTEC	T6956	rsec	A610MULC	SG30CCAL00004	CL
3199.	22	98						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00011	HL
3200.	22	99						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00012	HL
3201.		2.27	110	37	P1	01H	0.67	TEHTEC	F3453	reso	A610MULC	SG30CCAL00003	CL
3202.	22	100						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00011	HL
3203.	22	101						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00012	HL
3204.	22	102						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00011	HL
3205.	22	103						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00012	HL
3206.	22	104						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00011	HL
3207.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00003	CL
3208.	22	105						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00012	HL
3209.	22	106						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00011	HL
3210.	22	107						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00012	HL
3211.	22	108						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00013	HL
3212.	22	109						TSHTSH	85534	rpri	B620MRPC3C	SG31HCAL00014	HL
3213.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00004	CL
3214.	23	6						TSHTSH	85534	rpri	B620MRPC3C	SG31HCAL00034	HL
3215.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL
3216.	23	7						TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
3217.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL
3218.	23	8						TSHTSH	85534	rpri	B620MRPC3C	SG31HCAL00034	HL
3219.	23	9						TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
3220.	23	10						TSHTSH	85534	rpri	B620MRPC3C	SG31HCAL00034	HL
3221.	23	11						TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
3222.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL
3223.	23	12						TSHTSH	85534	rpri	B620MRPC3C	SG31HCAL00034	HL
3224.	23	13						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00041	HL
3225.	23	14						TSHTSH	85534	rpri	B620MRPC3C	SG31HCAL00036	HL
3226.	23	15						TSHTSH	85534	rpri	B620MRPC3C	SG31HCAL00037	HL
3227.	23	16						TSHTSH	85534	rpri	B620MRPC3C	SG31HCAL00036	HL
3228.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL
3229.	23	17						TSHTSH	85534	rpri	B620MRPC3C	SG31HCAL00037	HL
3230.	23	18						TSHTSH	85534	rpri	B620MRPC3C	SG31HCAL00036	HL
3231.	23	19						TSHTSH	85534	rpri	B620MRPC3C	SG31HCAL00037	HL
3232.	23	20						TSHTSH	85534	rpri	B620MRPC3C	SG31HCAL00036	HL
3233.	23	21						TSHTSH	85534	rpri	B620MRPC3C	SG31HCAL00037	HL
3234.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: C
 DATABASE: Harris_SGC_1995

Sep. 23.1995 14:28

PAGE 68 of 128

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
3235.	23	22						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00036	HL
3236.	23	23						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00037	HL
3237.	23	24						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00036	HL
3238.	23	25						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00037	HL
3239.	23	26						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00036	HL
3240.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL
3241.	23	27						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00037	HL
3242.	23	28						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00036	HL
3243.	23	29						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00037	HL
3244.	23	32						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00036	HL
3245.	23	33						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00037	HL
3246.	23	34						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00036	HL
3247.	23	35						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00037	HL
3248.	23	36						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00037	HL
3249.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL
3250.	23	37						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00004	HL
3251.	23	38						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00003	HL
3252.	23	39						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00004	HL
3253.	23	40						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00003	HL
3254.	23	41						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00004	HL
55.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00001	CL
56.	23	42						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00003	HL
57.	23	43						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00004	HL
3258.	23	44						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00003	HL
3259.	23	45						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00003	HL
3260.		0.90		24	P2	AV2	0.00	TEHTEC	F3325	rsec	A610MULC	SG30CCAL00001	CL
3261.	23	70						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
3262.	23	71			PID	TSH	-0.20	TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00037	HL
3263.		0.29	163	SAI	1	TSH	0.13	TSHTSH	H1274	reso	B620MRPC3C	SG31HCAL00030	HL
3264.	23	72						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
3265.	23	73						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL
3266.	23	74						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
3267.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00007	CL
3268.	23	75						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL
3269.	23	76						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
3270.	23	77						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL
3271.	23	78						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
3272.	23	79						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL
3273.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00007	CL
3274.	23	80						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
3275.	23	81						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL
3276.	23	82						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00015	HL
3277.	23	83						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00016	HL
3278.	23	84						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00015	HL
3279.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00004	CL
80.	23	85						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00016	HL
81.	23	86						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00015	HL
82.	23	87						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00016	HL
83.	23	88						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00015	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: C
 DATABASE: Harris_SGC_1995

Sep. 23.1995 14:28

PAGE 69 of 128

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
3284.	23	89						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00016	HL
3285.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00004	CL
3286.	23	90						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00015	HL
3287.	23	91						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00016	HL
3288.	23	92						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00015	HL
3289.	23	93						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00016	HL
3290.	23	94						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00011	HL
3291.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00003	CL
3292.	23	95						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00012	HL
3293.	23	96						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00011	HL
3294.	23	97						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00012	HL
3295.	23	98						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00011	HL
3296.	23	99						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00012	HL
3297.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00003	CL
3298.	23	100						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00011	HL
3299.	23	101						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00012	HL
3300.	23	102						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00011	HL
3301.	23	103						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00012	HL
3302.	23	104						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00011	HL
3303.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00003	CL
04.	23	105						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00012	HL
05.	23	106						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00011	HL
06.	23	107						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00012	HL
3307.	23	108						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00013	HL
3308.								TEHTEC	T6956	rsec	A610MULC	SG30CCAL00004	CL
3309.	23	109						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00014	HL
3310.				INR		01H	19.70	TEHTEC	B3052	reso	A610MULC	SG30CCAL00004	CL
3311.	24	7						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00034	HL
3312.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL
3313.	24	8						TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
3314.	24	9						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00034	HL
3315.	24	10						TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
3316.	24	11						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00034	HL
3317.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL
3318.	24	12						TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
3319.	24	13						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00036	HL
3320.	24	14						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00037	HL
3321.	24	15						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00036	HL
3322.	24	16						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00037	HL
3323.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL
3324.	24	17						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00036	HL
3325.	24	18						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00037	HL
3326.	24	19						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00036	HL
3327.	24	20						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00037	HL
3328.	24	21						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00036	HL
329.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL
30.	24	22						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00037	HL
31.	24	23						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00036	HL
32.	24	24						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00037	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: C
 DATABASE: Harris_SGC_1995

Sep. 23.1995 14:28

PAGE 70 of 128

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
3333.	24	25					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00036	HL
3334.	24	26					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00037	HL
3335.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL
3336.	24	27					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00036	HL
3337.	24	28					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00037	HL
3338.	24	29					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00036	HL
3339.	24	32					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00037	HL
3340.	24	33					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00036	HL
3341.	24	34					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00037	HL
3342.	24	35					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00036	HL
3343.	24	36					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00037	HL
3344.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL
3345.	24	37					TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00004	HL
3346.	24	38					TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00003	HL
3347.	24	39					TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00004	HL
3348.	24	40					TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00003	HL
3349.	24	41					TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00004	HL
3350.							TEHTEC	P4202	rpri	A610MULC	SG30CCAL00001	CL
3351.	24	42					TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00003	HL
3352.	24	43					TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00004	HL
53.	24	44					TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00003	HL
1.	24	45					TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00004	HL
1.5.	24	46					TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00003	HL
3356.							TEHTEC	P4202	rpri	A610MULC	SG30CCAL00001	CL
3357.	24	47					TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00004	HL
3358.	24	48					TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00003	HL
3359.	24	49					TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00004	HL
3360.	24	50					TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00003	HL
3361.	24	51					TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00004	HL
3362.							TEHTEC	P4202	rpri	A610MULC	SG30CCAL00001	CL
3363.	24	52					TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00003	HL
3364.	24	53					TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00004	HL
3365.	24	54					TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00003	HL
3366.	24	55					TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00003	HL
3367.	24	60					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL
3368.	24	61					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL
3369.	24	62					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL
3370.	24	63					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL
3371.	24	64					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL
3372.							TEHTEC	P4202	rpri	A610MULC	SG30CCAL00007	CL
3373.	24	65					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL
3374.	24	66					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
3375.	24	67					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL
3376.	24	68					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
3377.	24	69					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL
78.							TEHTEC	P4202	rpri	A610MULC	SG30CCAL00007	CL
79.	24	70					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
80.	24	71					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL
81.	24	72					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: C
 DATABASE: Harris_SGC_1995

Sep. 23,1995 14:28

PAGE 71 of 128

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
3382.	24	73					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL
3383.	24	74					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
3384.							TEHTEC	P4202	rpri	A610MULC	SG30CCAL00007	CL
3385.	24	75					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL
3386.	24	76					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
3387.	24	77					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL
3388.	24	78					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
3389.	24	79					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL
3390.							TEHTEC	P4202	rpri	A610MULC	SG30CCAL00007	CL
3391.	24	80					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
3392.	24	81					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL
3393.	24	82					TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00015	HL
3394.	24	83					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00016	HL
3395.	24	84					TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00015	HL
3396.							TEHTEC	P4202	rpri	A610MULC	SG30CCAL00004	CL
3397.	24	85					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00016	HL
3398.	24	86					TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00015	HL
3399.	24	87					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00016	HL
3400.	24	88					TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00015	HL
3401.	24	89					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00016	HL
3402.							TEHTEC	P4202	rpri	A610MULC	SG30CCAL00004	CL
3403.	24	90					TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00015	HL
3404.	24	91					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00016	HL
3405.	24	92					TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00015	HL
3406.	24	93					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00016	HL
3407.	24	94					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00011	HL
3408.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00003	CL
3409.	24	95					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00023	HL
3410.	24	96					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00011	HL
3411.	24	97					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00012	HL
3412.	24	98					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00011	HL
3413.	24	99					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00012	HL
3414.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00003	CL
3415.	24	100					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00011	HL
3416.	24	101					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00012	HL
3417.	24	102					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00011	HL
3418.	24	103					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00012	HL
3419.	24	104					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00011	HL
3420.							TEHTEC	T6956	rsec	A610MULC	SG30CCAL00003	CL
3421.	24	105					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00012	HL
3422.	24	106					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00011	HL
3423.	24	107					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00012	HL
3424.	24	108					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00014	HL
3425.							TEHTEC	T6956	rsec	A610MULC	SG30CCAL00004	CL
3426.	25	7					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00034	HL
3427.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL
3428.	25	8					TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
3429.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL
3430.	25	9					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00034	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: C
 DATABASE: Harris_SGC_1995

Sep. 23,1995 14:28

PAGE 72 of 128

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG	
3431.	25	10						TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL	
3432.	25	11						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00034	HL	
3433.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL	
3434.	25	12						TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL	
3435.	25	13						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00036	HL	
3436.	25	14						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00037	HL	
3437.	25	15						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00036	HL	
3438.	25	16						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00037	HL	
3439.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL	
3440.	25	17						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00036	HL	
3441.	25	18						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00037	HL	
3442.	25	19						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00036	HL	
3443.	25	20						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00037	HL	
3444.	25	21						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00036	HL	
3445.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL	
3446.	25	22						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00037	HL	
3447.	25	23						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00036	HL	
3448.	25	24						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00037	HL	
3449.	25	25						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00036	HL	
3450.	25	26						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00037	HL	
51.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL	
2.	25	27						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00036	HL	
3.	25	28						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00037	HL	
3454.	25	29						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00036	HL	
3455.	25	30						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00037	HL	
3456.	25	31						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00036	HL	
3457.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL	
3458.	25	32						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00037	HL	
3459.	25	33						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00036	HL	
3460.	25	34						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00037	HL	
3461.	25	35						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00036	HL	
3462.	25	36						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00037	HL	
3463.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL	
3464.	25	37						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00004	HL	
3465.	25	38						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00003	HL	
3466.	25	39						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00004	HL	
3467.	25	40						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00003	HL	
3468.	25	41						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00004	HL	
3469.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00001	CL	
3470.	25	42						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00003	HL	
3471.	25	43						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00004	HL	
3472.	25	44						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00003	HL	
3473.	25	45						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00004	HL	
3474.			0.53		19	P2	AV2	-0.35	TEHTEC	P4202	rpri	A610MULC	SG30CCAL00001	CL
3475.	25	46						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00003	HL	
76.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00001	CL	
77.	25	47						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00004	HL	
78.	25	48						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00003	HL	
79.	25	49						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00004	HL	

*** INSPECTION FINAL REPORT LISTING ***

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: C
 DATABASE: Harris_SGC_1995

Sep. 23.1995 14:28

PAGE 73 of 128

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
3480.	25	50						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00003	HL
3481.	25	51						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00004	HL
3482.								TEHTEC	F3325	rsec	A610MULC	SG30CCAL00001	CL
3483.	25	52						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00003	HL
3484.	25	53						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00004	HL
3485.	25	54						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00003	HL
3486.	25	55						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00004	HL
3487.	25	56						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00003	HL
3488.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00001	CL
3489.	25	59						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL
3490.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00007	CL
3491.	25	60						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
3492.	25	61						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
3493.	25	62						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
3494.	25	63						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
3495.	25	64						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
3496.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00007	CL
3497.	25	65						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
3498.	25	66						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
3499.	25	67						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL
00.	25	68						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
01.	25	69						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL
002.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00007	CL
3503.	25	70						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
3504.	25	71						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL
3505.	25	72						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
3506.	25	73						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL
3507.	25	74						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
3508.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00007	CL
3509.	25	75						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL
3510.	25	76						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
3511.	25	77						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL
3512.	25	78						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
3513.	25	79						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL
3514.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00007	CL
3515.	25	80						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
3516.	25	81						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL
3517.	25	82						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00015	HL
3518.	25	83						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00016	HL
3519.	25	84						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00015	HL
3520.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00004	CL
3521.	25	85						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00016	HL
3522.	25	86						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00015	HL
3523.	25	87						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00016	HL
3524.	25	88						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00015	HL
3525.	25	89						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00016	HL
3526.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00004	CL
3527.	25	90						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00015	HL
3528.	25	91						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00016	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: C
 DATABASE: Harris_SGC_1995

Sep. 23,1995 14:28

PAGE 74 of 128

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG	
3529.	25	92						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00015	HL	
3530.	25	93						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00016	HL	
3531.	25	94						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00011	HL	
3532.								TEHTEC	T6956	rsec	A610MULC	SG30CCAL00003	CL	
3533.	25	95						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00012	HL	
3534.	25	96						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00011	HL	
3535.	25	97						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00012	HL	
3536.	25	98						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00011	HL	
3537.	25	99						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00012	HL	
3538.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00003	CL	
3539.	25	100						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00011	HL	
3540.	25	101						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00012	HL	
3541.	25	102						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00011	HL	
3542.	25	103						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00012	HL	
3543.	25	104						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00011	HL	
3544.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00003	CL	
3545.	25	105						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00012	HL	
3546.	25	106						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00011	HL	
3547.	25	107						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00012	HL	
3548.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00004	CL	
3549.	25	108						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00014	HL	
3550.			12.76	177	DNT	P1	01H	-0.36	TEHTEC	N0698	rpri	A610MULC	SG30CCAL00004	CL
3551.			12.35	178	DNT	P1	01H	0.44	TEHTEC	N0698	rpri	A610MULC	SG30CCAL00004	CL
3552.	26	8						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00034	HL	
3553.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL	
3554.	26	9						TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL	
3555.	26	10						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00034	HL	
3556.	26	11						TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL	
3557.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL	
3558.	26	12						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00034	HL	
3559.	26	13						TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL	
3560.	26	14						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00036	HL	
3561.	26	15						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00037	HL	
3562.	26	16						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00036	HL	
3563.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL	
3564.	26	17						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00037	HL	
3565.	26	18						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00036	HL	
3566.	26	19						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00037	HL	
3567.	26	20						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00036	HL	
3568.	26	21						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00037	HL	
3569.								TEHTEC	C3335	reso	A610MULC	SG30CCAL00009	CL	
3570.	26	22						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00036	HL	
3571.	26	23						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00037	HL	
3572.	26	24						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00036	HL	
3573.	26	25						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00037	HL	
3574.	26	26						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00036	HL	
3575.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL	
3576.	26	27						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00037	HL	
3577.	26	28						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00036	HL	

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: C
 DATABASE: Harris_SGC_1995

Sep. 23.1995 14:28

PAGE 75 of 128

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG	
3578.	26	29						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00037	HL	
3579.	26	30						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00036	HL	
3580.	26	31						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00037	HL	
3581.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL	
3582.	26	32						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00036	HL	
3583.	26	33						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00037	HL	
3584.	26	34						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00036	HL	
3585.	26	35						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00037	HL	
3586.	26	36						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00037	HL	
3587.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL	
3588.	26	37						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00004	HL	
3589.	26	38						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00003	HL	
3590.	26	39						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00004	HL	
3591.	26	40						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00003	HL	
3592.	26	41						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00004	HL	
3593.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00001	CL	
3594.	26	42						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00003	HL	
3595.	26	43						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00004	HL	
3596.	26	44						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00003	HL	
3597.	26	45						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00004	HL	
98.	26	46						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00003	HL	
9.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00001	CL	
10.	26	47						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00004	HL	
3601.	26	48						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00003	HL	
3602.	26	49						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00004	HL	
3603.	26	50						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00003	HL	
3604.	26	51						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00004	HL	
3605.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00001	CL	
3606.	26	52						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00003	HL	
3607.	26	53						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00004	HL	
3608.	26	54						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00003	HL	
3609.	26	55						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00004	HL	
3610.	26	56						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00003	HL	
3611.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00001	CL	
3612.	26	59						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL	
3613.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00007	CL	
3614.	26	60						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL	
3615.	26	61						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL	
3616.	26	62						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL	
3617.	26	63						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL	
3618.	26	64						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL	
3619.			8.05	183	DNT	1	11C	0.86	TEHTEC	P4202	rpri	A610MULC	SG30CCAL00007	CL
3620.	26	65						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL	
3621.	26	66						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL	
3622.	26	67						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL	
3623.	26	68						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL	
3624.	26	69						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL	
3625.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00007	CL	
3626.	26	70						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL	

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: C
 DATABASE: Harris_SGC_1995

Sep. 23.1995 14:28

PAGE 76 of 128

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
3627.	26	71					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL
3628.	26	72					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
3629.	26	73					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL
3630.	26	74					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
3631.							TEHTEC	P4202	rpri	A610MULC	SG30CCAL00007	CL
3632.	26	75					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL
3633.	26	76					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
3634.	26	77					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL
3635.	26	78					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
3636.	26	79					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL
3637.							TEHTEC	P4202	rpri	A610MULC	SG30CCAL00007	CL
3638.	26	80					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
3639.	26	81					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL
3640.	26	82					TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00015	HL
3641.	26	83					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00016	HL
3642.	26	84					TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00015	HL
3643.							TEHTEC	P4202	rpri	A610MULC	SG30CCAL00004	CL
3644.	26	85					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00016	HL
3645.	26	86					TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00015	HL
3646.	26	87					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00016	HL
47.	26	88					TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00015	HL
3.	26	89					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00016	HL
49.							TEHTEC	P4202	rpri	A610MULC	SG30CCAL00004	CL
3650.	26	90					TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00015	HL
3651.	26	91					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00016	HL
3652.	26	92					TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00015	HL
3653.	26	93					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00016	HL
3654.	26	94					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00011	HL
3655.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00003	CL
3656.	26	95					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00012	HL
3657.	26	96					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00011	HL
3658.	26	97					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00012	HL
3659.	26	98					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00011	HL
3660.	26	99					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00012	HL
3661.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00003	CL
3662.	26	100					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00011	HL
3663.	26	101					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00012	HL
3664.	26	102					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00011	HL
3665.	26	103					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00012	HL
3666.	26	104					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00011	HL
3667.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00003	CL
3668.	26	105					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00012	HL
3669.	26	106					TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00013	HL
3670.	26	107					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00014	HL
3671.							TEHTEC	T6956	rsec	A610MULC	SG30CCAL00004	CL
72.	27	8					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00034	HL
73.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL
4.	27	9					TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
75.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: C
 DATABASE: Harris_SGC_1995

Sep. 23.1995 14:28

PAGE 77 of 128

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
3676.	27	10						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00034	HL
3677.	27	11						TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
3678.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL
3679.	27	12						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00034	HL
3680.	27	13						TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
3681.	27	14						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00036	HL
3682.	27	15						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00037	HL
3683.	27	16						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00036	HL
3684.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL
3685.	27	17						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00037	HL
3686.	27	18						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00036	HL
3687.	27	19						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00037	HL
3688.	27	20						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00036	HL
3689.	27	23						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00037	HL
3690.	27	24						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00036	HL
3691.	27	25						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00037	HL
3692.	27	26						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00036	HL
3693.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL
3694.	27	27						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00037	HL
3695.	27	28						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00036	HL
3696.	27	29						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00037	HL
3697.	27	30						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00036	HL
3698.	27	31						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00037	HL
3699.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL
3700.	27	32						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00036	HL
3701.	27	33						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00037	HL
3702.	27	34						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00036	HL
3703.	27	35						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00037	HL
3704.	27	36						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00037	HL
3705.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL
3706.	27	37						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00004	HL
3707.	27	38						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00003	HL
3708.	27	39						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00004	HL
3709.	27	40						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00003	HL
3710.	27	41						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00004	HL
3711.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00001	CL
3712.	27	42						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00003	HL
3713.	27	43						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00004	HL
3714.	27	44						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00003	HL
3715.	27	45						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00004	HL
3716.	27	46						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00003	HL
3717.		0.49		18	P2	AV1	0.00	TEHTEC	H1274	reso	A610MULC	SG30CCAL00001	CL
3718.	27	47						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00004	HL
3719.	27	48						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00003	HL
3720.	27	49						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00004	HL
3721.	27	50						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00003	HL
3722.	27	51						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00004	HL
3723.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00001	CL
3724.	27	52						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00003	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: C
 DATABASE: Harris_SGC_1995

Sep. 23,1995 14:28

PAGE 78 of 128

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
3725.	27	53					TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00004	HL
3726.	27	54					TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00003	HL
3727.	27	55					TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00004	HL
3728.	27	56					TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00003	HL
3729.							TEHTEC	P4202	rpri	A610MULC	SG30CCAL00001	CL
3730.	27	59					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL
3731.							TEHTEC	P4202	rpri	A610MULC	SG30CCAL00007	CL
3732.	27	60					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
3733.	27	61					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
3734.	27	63					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
3735.	27	64					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
3736.							TEHTEC	P4202	rpri	A610MULC	SG30CCAL00007	CL
3737.	27	65					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
3738.	27	66					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
3739.	27	67					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL
3740.	27	68					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
3741.	27	69					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL
3742.							TEHTEC	P4202	rpri	A610MULC	SG30CCAL00007	CL
3743.	27	70					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
3744.	27	71					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL
45.	27	72					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
6.	27	73					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL
747.	27	74					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
3748.							TEHTEC	P4202	rpri	A610MULC	SG30CCAL00007	CL
3749.	27	75					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL
3750.	27	76					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
3751.	27	77					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL
3752.	27	78					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
3753.	27	79					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL
3754.							TEHTEC	P4202	rpri	A610MULC	SG30CCAL00007	CL
3755.	27	80					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
3756.	27	81					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL
3757.	27	82					TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00015	HL
3758.	27	83					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00016	HL
3759.	27	84					TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00015	HL
3760.							TEHTEC	P4202	rpri	A610MULC	SG30CCAL00004	CL
3761.	27	85					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00016	HL
3762.	27	86					TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00015	HL
3763.	27	87					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00016	HL
3764.	27	88					TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00015	HL
3765.	27	89					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00016	HL
3766.							TEHTEC	P4202	rpri	A610MULC	SG30CCAL00004	CL
3767.	27	90					TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00015	HL
3768.	27	91					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00016	HL
3769.	27	92					TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00015	HL
70.	27	93					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00016	HL
71.	27	94					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00011	HL
2.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00003	CL
773.	27	95					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00012	HL

*** INSPECTION FINAL REPORT LISTING ***

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: C
 DATABASE: Harris_SGC_1995

Sep. 23.1995 14:28

PAGE 79 of 128

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
3774.	27	96					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00011	HL
3775.	27	97					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00012	HL
3776.	27	98					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00011	HL
3777.	27	99					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00012	HL
3778.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00003	CL
3779.	27	100					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00011	HL
3780.	27	101					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00012	HL
3781.	27	102					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00011	HL
3782.	27	103					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00012	HL
3783.	27	104					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00011	HL
3784.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00003	CL
3785.	27	105					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00012	HL
3786.	27	106					TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00013	HL
3787.							TEHTEC	T6956	rsec	A610MULC	SG30CCAL00004	CL
3788.	27	107					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00014	HL
3789.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00004	CL
3790.	28	9					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00034	HL
3791.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL
3792.	28	10					TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
3793.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL
94.	28	11					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00034	HL
95.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL
96.	28	12					TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
3797.	28	13					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00036	HL
3798.	28	14					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00037	HL
3799.	28	15					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00036	HL
3800.	28	16					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00037	HL
3801.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL
3802.	28	17					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00036	HL
3803.	28	18					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00037	HL
3804.	28	19					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00036	HL
3805.	28	20					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00037	HL
3806.	28	21					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00036	HL
3807.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL
3808.	28	22					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00037	HL
3809.	28	23					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00036	HL
3810.	28	24					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00037	HL
3811.	28	25					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00036	HL
3812.	28	26					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00037	HL
3813.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL
3814.	28	27					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00036	HL
3815.	28	28					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00037	HL
3816.	28	29					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00036	HL
3817.	28	30					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00037	HL
3818.	28	31					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00036	HL
3819.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL
3820.	28	32					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00037	HL
3821.	28	33					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00036	HL
3822.	28	34					TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00037	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: C
 DATABASE: Harris_SGC_1995

Sep. 23.1995 14:28

PAGE 80 of 128

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
3823.	28	35						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00036	HL
3824.	28	36						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00037	HL
3825.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL
3826.	28	37						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00004	HL
3827.	28	38						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00003	HL
3828.	28	39						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00004	HL
3829.	28	40						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00003	HL
3830.	28	41						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00004	HL
3831.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00001	CL
3832.	28	42						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00003	HL
3833.	28	43						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00004	HL
3834.	28	44						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00003	HL
3835.	28	45						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00004	HL
3836.		0.49		15	P2	AV1	0.00	TEHTEC	H1274	reso	A610MULC	SG30CCAL00001	CL
3837.	28	46						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00003	HL
3838.		0.79		22	P2	AV2	0.00	TEHTEC	F3325	rsec	A610MULC	SG30CCAL00001	CL
3839.	28	47						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00004	HL
3840.	28	48						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00003	HL
3841.	28	49						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00004	HL
3842.	28	50						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00003	HL
3843.	28	51						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00004	HL
3844.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00001	CL
3845.	28	52						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00003	HL
3846.	28	53						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00004	HL
3847.	28	54						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00003	HL
3848.	28	55						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00004	HL
3849.	28	56						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00003	HL
3850.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00001	CL
3851.	28	59						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
3852.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00007	CL
3853.	28	60						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL
3854.	28	61						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL
3855.	28	62						TSHTSH	C7651	rsec	B620MRPC3C	SG31HCAL00030	HL
3856.	28	63						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL
3857.	28	64						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL
3858.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00007	CL
3859.	28	65						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL
3860.	28	66						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
3861.	28	67						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL
3862.	28	68						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
3863.	28	69						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL
3864.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00007	CL
3865.	28	70						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
3866.	28	71						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL
3867.	28	72						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
3868.	28	73						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL
3869.	28	74						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
3870.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00007	CL
3871.	28	75						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: C
 DATABASE: Harris_SGC_1995

Sep. 23.1995 14:28

PAGE 81 of 128

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
3872.	28	76						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
3873.	28	77						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL
3874.	28	78						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
3875.	28	79						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL
3876.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00007	CL
3877.	28	80						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
3878.	28	81						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL
3879.	28	82						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00015	HL
3880.	28	83						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00016	HL
3881.	28	84						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00015	HL
3882.								09H09H	T7072	rpri	B620MRPC3C	SG31HCAL00025	HL
3883.								09H09H	T7072	rpri	B620MRPC3C	SG31HCAL00026	HL
3884.		25.80	180	DNT	P1	09H	-0.36	TEHTEC	P4202	rpri	A610MULC	SG30CCAL00004	CL
3885.	28	85						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00016	HL
3886.	28	86						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00015	HL
3887.	28	87						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00016	HL
3888.	28	88						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00015	HL
3889.	28	89						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00016	HL
3890.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00004	CL
3891.	28	90						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00015	HL
3892.	28	91						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00016	HL
3893.	28	92						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00015	HL
3894.	28	93						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00016	HL
3895.	28	94						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00011	HL
3896.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00003	CL
3897.	28	95						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00012	HL
3898.	28	96						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00011	HL
3899.	28	97						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00012	HL
3900.	28	98						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00011	HL
3901.	28	99						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00012	HL
3902.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00003	CL
3903.	28	100						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00011	HL
3904.	28	101						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00012	HL
3905.	28	102						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00011	HL
3906.	28	103						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00012	HL
3907.	28	104						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00011	HL
3908.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00003	CL
3909.	28	105						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00012	HL
3910.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00003	CL
3911.	28	106						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00014	HL
3912.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00004	CL
3913.	29	10						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00034	HL
3914.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL
3915.	29	11						TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
3916.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL
3917.	29	12						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00034	HL
3918.	29	13						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00037	HL
3919.	29	14						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00036	HL
3920.	29	15						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00037	HL

*** INSPECTION FINAL REPORT LISTING ***

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: C
 DATABASE: Harris_SGC_1995

Sep. 23.1995 14:28

PAGE 82 of 128

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
3921.	29	16						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00036	HL
3922.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL
3923.	29	17						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00037	HL
3924.	29	18						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00036	HL
3925.	29	19						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00037	HL
3926.	29	20						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00036	HL
3927.	29	21						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00037	HL
3928.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL
3929.	29	22						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00036	HL
3930.	29	23						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00037	HL
3931.	29	24						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00036	HL
3932.	29	25						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00037	HL
3933.	29	26						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00036	HL
3934.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL
3935.	29	27						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00037	HL
3936.	29	28						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00036	HL
3937.	29	29						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00037	HL
3938.		1.75	142	MM	1	10C	1.07	TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL
3939.	29	30						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00036	HL
3940.	29	31						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00037	HL
41.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL
42.	29	32						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00036	HL
43.	29	33						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00037	HL
3944.	29	34						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00036	HL
3945.	29	35						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00037	HL
3946.	29	36						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00037	HL
3947.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL
3948.	29	37						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00004	HL
3949.	29	38						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00003	HL
3950.	29	39						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00004	HL
3951.	29	40						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00003	HL
3952.	29	41						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00004	HL
3953.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00001	CL
3954.	29	42						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00003	HL
3955.	29	43						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00004	HL
3956.	29	44						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00003	HL
3957.	29	46						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00003	HL
3958.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00001	CL
3959.	29	47						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00004	HL
3960.	29	48						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00003	HL
3961.	29	49						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00004	HL
3962.	29	50						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00003	HL
3963.	29	51						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00004	HL
3964.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00001	CL
3965.	29	52						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00003	HL
3966.	29	53						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00004	HL
3967.	29	54						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00003	HL
3968.	29	55						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00004	HL
3969.	29	56						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00003	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: C
 DATABASE: Harris_SGC_1995

Sep. 23.1995 14:28

PAGE 83 of 128

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
3970.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00001	CL
3971.	29	59						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL
3972.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00007	CL
3973.	29	60						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
3974.	29	61						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
3975.	29	62						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
3976.	29	63						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
3977.	29	64						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
3978.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00007	CL
3979.	29	65						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
3980.	29	66						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
3981.	29	67						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL
3982.	29	68						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
3983.	29	69						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL
3984.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00007	CL
3985.	29	70						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
3986.	29	71						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL
3987.	29	72						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
3988.	29	73						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL
3989.	29	74						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
3990.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00007	CL
3991.	29	75						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL
3992.	29	76						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
3993.	29	77						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL
3994.	29	78						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
3995.	29	79						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL
3996.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00007	CL
3997.	29	80						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
3998.	29	81						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL
3999.	29	82						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00015	HL
4000.	29	83						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00016	HL
4001.	29	84						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00015	HL
4002.								09H09H	T7072	rpri	B620MRPC3C	SG31HCAL00026	HL
4003.			8.96	181	DNT	P1	09H -1.01	TEHTEC	P4202	rpri	A610MULC	SG30CCAL00004	CL
4004.			17.43	180	DNT	P1	09H -0.24	TEHTEC	P4202	rpri	A610MULC	SG30CCAL00004	CL
4005.	29	85						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00016	HL
4006.								09H09H	T7072	rpri	B620MRPC3C	SG31HCAL00026	HL
4007.	29	86						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00015	HL
4008.	29	87						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00016	HL
4009.	29	88						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00015	HL
4010.	29	89						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00016	HL
4011.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00004	CL
4012.	29	90						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00015	HL
4013.	29	91						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00016	HL
4014.	29	92						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00015	HL
4015.	29	93						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00016	HL
4016.	29	94						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00011	HL
4017.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00003	CL
4018.	29	95						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00012	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: C
 DATABASE: Harris_SGC_1995

Sep. 23.1995 14:28

PAGE 84 of 128

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
4019.	29	96						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00011	HL
4020.	29	97						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00012	HL
4021.	29	98						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00011	HL
4022.	29	99						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00012	HL
4023.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00003	CL
4024.	29	100						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00011	HL
4025.	29	101						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00012	HL
4026.	29	102						TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00011	HL
4027.	29	103						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00012	HL
4028.	29	104						TSHTSH	C7651	rsec	B620MRPC3C	SG31HCAL00011	HL
4029.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00003	CL
4030.	29	105						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00012	HL
4031.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00003	CL
4032.	30	10						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00034	HL
4033.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL
4034.	30	11						TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
4035.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL
4036.	30	12						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00036	HL
4037.	30	13						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00037	HL
4038.	30	14						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00036	HL
4039.	30	15						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00037	HL
4040.	30	16						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00036	HL
4041.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL
4042.	30	17						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00037	HL
4043.	30	18						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00036	HL
4044.	30	19						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00037	HL
4045.	30	20						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00036	HL
4046.	30	21						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00037	HL
4047.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL
4048.	30	22						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00036	HL
4049.	30	23						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00037	HL
4050.	30	24						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00036	HL
4051.	30	25						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00037	HL
4052.	30	26						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00036	HL
4053.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL
4054.	30	27						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00037	HL
4055.	30	28						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00036	HL
4056.	30	29						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00037	HL
4057.	30	30						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00036	HL
4058.	30	31						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00037	HL
4059.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL
4060.	30	32						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00036	HL
4061.	30	33						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00037	HL
4062.	30	34						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00036	HL
4063.	30	35						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00037	HL
4064.	30	36						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00037	HL
4065.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL
4066.	30	37						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00004	HL
4067.	30	38						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00003	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: C
 DATABASE: Harris_SGC_1995

Sep. 23, 1995 14:28

PAGE 85 of 128

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
4068.	30	39						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00004	HL
4069.	30	40						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00003	HL
4070.	30	41						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00004	HL
4071.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00001	CL
4072.	30	42						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00003	HL
4073.	30	43						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00004	HL
4074.	30	44						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00003	HL
4075.		1.67		37	P2	AV2	-0.03	TEHTEC	P4202	rpri	A610MULC	SG30CCAL00001	CL
4076.	30	45						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00004	HL
4077.		2.26		39	P2	AV1	0.00	TEHTEC	F3325	rsec	A610MULC	SG30CCAL00001	CL
4078.	30	46						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00003	HL
4079.		0.67		22	P2	AV1	-0.44	TEHTEC	P4202	rpri	A610MULC	SG30CCAL00001	CL
4080.		0.33		12	P2	AV3	-0.08	TEHTEC	P4202	rpri	A610MULC	SG30CCAL00001	CL
4081.	30	47						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00004	HL
4082.	30	48						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00003	HL
4083.	30	49						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00004	HL
4084.	30	50						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00003	HL
4085.	30	51						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00004	HL
4086.								TEHTEC	F3325	rsec	A610MULC	SG30CCAL00001	CL
4087.	30	52						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00003	HL
88.	30	53						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00004	HL
89.	30	54						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00003	HL
90.	30	55						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00004	HL
4091.	30	56						TSHTSH	T5028	rpri	B620MRPC3C	SG31HCAL00003	HL
4092.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00001	CL
4093.	30	59						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
4094.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00007	CL
4095.	30	60						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
4096.	30	61						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
4097.	30	62						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
4098.	30	63						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
4099.	30	64						TSHTSH	F2217	rpri	B620MRPC3C	SG31HCAL00037	HL
4100.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00007	CL
4101.	30	65						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
4102.	30	66						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
4103.	30	67						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL
4104.	30	68						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
4105.	30	69						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL
4106.		22.86	180	DNT	1	06C	3.90	TEHTEC	P4202	rpri	A610MULC	SG30CCAL00007	CL
4107.	30	70						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
4108.	30	71						TSH01H	C7651	rsec	B620MRPC3C	SG31HCAL00030	HL
4109.	30	72						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
4110.	30	73						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL
4111.	30	74						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
4112.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00007	CL
13.	30	75						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL
14.	30	76						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
15.	30	77						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL
16.	30	78						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL

*** INSPECTION FINAL REPORT LISTING ***

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: C
 DATABASE: Harris_SGC_1995

Sep. 23.1995 14:28

PAGE 86 of 128

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
4117.	30	79					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL
4118.							TEHTEC	P4202	rpri	A610MULC	SG30CCAL00007	CL
4119.	30	80					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00031	HL
4120.	30	81					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00030	HL
4121.	30	82					TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00015	HL
4122.	30	83					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00016	HL
4123.	30	84					TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00015	HL
4124.							TEHTEC	P4202	rpri	A610MULC	SG30CCAL00004	CL
4125.	30	85					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00016	HL
4126.	30	86					TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00015	HL
4127.	30	87					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00016	HL
4128.	30	88					TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00015	HL
4129.	30	89					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00016	HL
4130.							TEHTEC	P4202	rpri	A610MULC	SG30CCAL00004	CL
4131.	30	90					TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00015	HL
4132.	30	91					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00016	HL
4133.	30	92					TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00015	HL
4134.	30	93					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00016	HL
4135.	30	94					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00011	HL
4136.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00003	CL
37.	30	95					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00012	HL
38.	30	96					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00011	HL
39.	30	97					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00012	HL
4140.	30	98					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00011	HL
4141.	30	99					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00012	HL
4142.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00003	CL
4143.	30	100					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00011	HL
4144.	30	101					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00012	HL
4145.	30	102					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00011	HL
4146.	30	103					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00012	HL
4147.	30	104					TSHTSH	T7665	rpri	B620MRPC3C	SG31HCAL00011	HL
4148.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00003	CL
4149.	30	105					TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00012	HL
4150.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00003	CL
4151.	31	11					TSHTSH	S7067	rpri	B620MRPC3C	SG31HCAL00034	HL
4152.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL
4153.	31	12					TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
4154.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL
4155.	31	13					TSHTSH	S7067	rpri	B620MRPC3C	SG31HCAL00034	HL
4156.	31	14					TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
4157.	31	15					TSHTSH	S7067	rpri	B620MRPC3C	SG31HCAL00034	HL
4158.	31	16					TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
4159.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL
4160.	31	17					TSHTSH	S7067	rpri	B620MRPC3C	SG31HCAL00034	HL
4161.	31	18					TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
4162.	31	19					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00034	HL
4163.	31	20					TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
4164.	31	21					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00034	HL
4165.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL

*** INSPECTION FINAL REPORT LISTING ***

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: C
 DATABASE: Harris_SGC_1995

Sep. 23.1995 14:28

PAGE 87 of 128

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
4166.	31	22						TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
4167.	31	23						TSHTSH	85534	rpri	B620MRPC3C	SG31HCAL00034	HL
4168.	31	24						TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
4169.	31	25						TSHTSH	85534	rpri	B620MRPC3C	SG31HCAL00034	HL
4170.	31	26						TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
4171.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL
4172.	31	27						TSHTSH	85534	rpri	B620MRPC3C	SG31HCAL00034	HL
4173.	31	28						TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
4174.	31	29						TSHTSH	85534	rpri	B620MRPC3C	SG31HCAL00034	HL
4175.	31	30						TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
4176.	31	31						TSHTSH	85534	rpri	B620MRPC3C	SG31HCAL00034	HL
4177.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL
4178.	31	32						TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
4179.	31	33						TSHTSH	85534	rpri	B620MRPC3C	SG31HCAL00034	HL
4180.	31	34						TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
4181.	31	35						TSHTSH	85534	rpri	B620MRPC3C	SG31HCAL00034	HL
4182.	31	36						TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
4183.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL
4184.	31	37						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00024	HL
4185.	31	38						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00023	HL
86.	31	39						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00024	HL
7.	31	40						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00023	HL
8.	31	41						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00024	HL
4189.		8.11	183	DNT	1	AV1	3.37	TEHTEC	P4202	rpri	A610MULC	SG30CCAL00006	CL
4190.	31	42						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00023	HL
4191.	31	43						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00024	HL
4192.	31	44						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00023	HL
4193.	31	45						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00024	HL
4194.		1.51		32	P2	AV1	0.00	TEHTEC	H1274	reso	A610MULC	SG30CCAL00007	CL
4195.	31	46						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00023	HL
4196.				RBD					P4202	rpri	A610MULC	SG30CCAL00006	CL
4197.								TEHTEC	05305	rpri	A610MULC	SG30CCAL00013	CL
4198.	31	47						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00024	HL
4199.	31	48						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00023	HL
4200.	31	49						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00024	HL
4201.	31	50						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00023	HL
4202.	31	51						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00024	HL
4203.				RBD					P4202	rpri	A610MULC	SG30CCAL00006	CL
4204.								TEHTEC	05305	rpri	A610MULC	SG30CCAL00013	CL
4205.	31	52						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00023	HL
4206.	31	53						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00024	HL
4207.	31	54						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00023	HL
4208.	31	55						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00024	HL
4209.	31	56						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00023	HL
4210.				RBD					P4202	rpri	A610MULC	SG30CCAL00006	CL
11.								TEHTEC	05305	rpri	A610MULC	SG30CCAL00013	CL
12.	31	59						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
13.								TEHTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL
14.	31	60						TSHTSH	J1978	rsec	B620MRPC3C	SG31HCAL00020	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: C
 DATABASE: Harris_SGC_1995

Sep. 23,1995 14:28

PAGE 88 of 128

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
4215.	31	61						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
4216.	31	62						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
4217.	31	63						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
4218.	31	64						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
4219.								TEHTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL
4220.	31	65						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
4221.	31	66						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
4222.	31	67						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
4223.	31	68						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
4224.	31	69						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
4225.								TEHTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL
4226.	31	70						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
4227.	31	71						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
4228.	31	72						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
4229.	31	73						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
4230.	31	74						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
4231.								TEHTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL
4232.	31	75						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
4233.	31	76						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
4234.	31	77						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
35.		0.64	142	MBM	1	07C	1.91	TEHTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL
36.	31	78						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
37.	31	79						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
4238.								TEHTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL
4239.	31	80						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
4240.	31	81						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
4241.	31	82						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00013	HL
4242.	31	83						TSHTSH	85534	rpri	B620MRPC3C	SG31HCAL00014	HL
4243.	31	84						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00013	HL
4244.								TEHTEC	T6956	rsec	A610MULC	SG30CCAL00004	CL
4245.	31	85						TSHTSH	85534	rpri	B620MRPC3C	SG31HCAL00014	HL
4246.	31	86						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00013	HL
4247.	31	87						TSHTSH	85534	rpri	B620MRPC3C	SG31HCAL00014	HL
4248.	31	88						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00015	HL
4249.	31	89						TSHTSH	85534	rpri	B620MRPC3C	SG31HCAL00016	HL
4250.								TEHTEC	T6956	rsec	A610MULC	SG30CCAL00004	CL
4251.	31	90						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00015	HL
4252.	31	91						TSHTSH	85534	rpri	B620MRPC3C	SG31HCAL00016	HL
4253.	31	92						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00015	HL
4254.	31	93						TSHTSH	85534	rpri	B620MRPC3C	SG31HCAL00016	HL
4255.	31	94						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00013	HL
4256.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00004	CL
4257.	31	95						TSHTSH	85534	rpri	B620MRPC3C	SG31HCAL00014	HL
4258.	31	96						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00013	HL
4259.	31	97						TSHTSH	85534	rpri	B620MRPC3C	SG31HCAL00014	HL
960.	31	98						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00013	HL
961.	31	99						TSHTSH	85534	rpri	B620MRPC3C	SG31HCAL00014	HL
962.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00004	CL
963.	31	100						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00013	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: C
 DATABASE: Harris_SGC_1995

Sep. 23, 1995 14:28

PAGE 89 of 128

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
4264.	31	101					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00014	HL
4265.	31	102					TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00013	HL
4266.	31	103					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00014	HL
4267.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00004	CL
4268.	31	104					TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00013	HL
4269.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00004	CL
4270.	32	12					TSHTSH	S7067	rpri	B620MRPC3C	SG31HCAL00034	HL
4271.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL
4272.	32	13					TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
4273.	32	14					TSHTSH	S7067	rpri	B620MRPC3C	SG31HCAL00034	HL
4274.	32	15					TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
4275.	32	16					TSHTSH	S7067	rpri	B620MRPC3C	SG31HCAL00034	HL
4276.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL
4277.	32	17					TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
4278.	32	18					TSHTSH	S7067	rpri	B620MRPC3C	SG31HCAL00034	HL
4279.	32	19					TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
4280.	32	20					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00034	HL
4281.	32	21					TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
4282.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL
4283.	32	22					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00034	HL
4284.	32	23					TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
4285.	32	24					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00034	HL
4286.	32	25					TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
4287.	32	26					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00034	HL
4288.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL
4289.	32	27					TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
4290.	32	28					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00034	HL
4291.	32	29					TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
4292.	32	30					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00034	HL
4293.	32	31					TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
4294.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL
4295.	32	32					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00034	HL
4296.	32	33					TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
4297.	32	34					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00034	HL
4298.	32	35					TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
4299.	32	36					TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
4300.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL
4301.	32	37					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00024	HL
4302.	32	38					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00023	HL
4303.	32	39					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00024	HL
4304.	32	40					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00023	HL
4305.	32	41					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00024	HL
4306.							TEHTEC	P4202	rpri	A610MULC	SG30CCAL00006	CL
4307.	32	42					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00023	HL
4308.	32	43					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00024	HL
4309.	32	44					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00023	HL
4310.	32	45					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00024	HL
4311.	32	46					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00023	HL
4312.							TEHTEC	F3325	rsec	A610MULC	SG30CCAL00006	CL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: C
 DATABASE: Harris_SGC_1995

Sep. 23.1995 14:28

PAGE 90 of 128

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
4313.	32	47						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00024	HL
4314.	32	48						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00023	HL
4315.	32	49						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00024	HL
4316.	32	50						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00023	HL
4317.	32	51						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00024	HL
4318.					RBD				P4202	rpri	A610MULC	SG30CCAL00006	CL
4319.								TEHTEC	05305	rpri	A610MULC	SG30CCAL00013	CL
4320.	32	52						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00023	HL
4321.	32	53						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00024	HL
4322.	32	54						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00023	HL
4323.	32	55						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00024	HL
4324.	32	56						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00023	HL
4325.					RBD				P4202	rpri	A610MULC	SG30CCAL00006	CL
4326.								TEHTEC	05305	rpri	A610MULC	SG30CCAL00013	CL
4327.	32	59						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
4328.								TEHTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL
4329.	32	60						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
4330.	32	61						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
4331.	32	62						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
4332.	32	63						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
33.	32	64						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
34.								TEHTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL
35.	32	65						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
4336.	32	66						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
4337.	32	67						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
4338.	32	68						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
4339.	32	69						01HTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
4340.								TEHTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL
4341.	32	70						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
4342.	32	71						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
4343.	32	72						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
4344.	32	73						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
4345.	32	74						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
4346.								TEHTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL
4347.	32	75						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
4348.	32	76						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
4349.	32	77						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
4350.		0.31		8	P2	AV3	-0.03	TEHTEC	B3052	reso	A610MULC	SG30CCAL00005	CL
4351.	32	78						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
4352.	32	79						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
4353.								TEHTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL
4354.	32	80						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
4355.	32	81						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
4356.	32	82						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00013	HL
4357.	32	83						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00014	HL
358.	32	84	13.17	33	SAI	1	TSH -0.08	TSHTSH	C3335	reso	B620MRPC3C	SG31HCAL00013	HL
359.					PID	1	TSH -0.08	TSHTSH	J9815	rsec	B620MRPC3C	SG31HCAL00023	HL
0.		38.52	171		DRI	P1	TSH 0.00	TEHTEC	N0698	rpri	A610MULC	SG30CCAL00004	CL
1.	32	85						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00014	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: C
 DATABASE: Harris_SGC_1995

Sep. 23.1995 14:28

PAGE 91 of 128

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
4362.	32	86					TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00013	HL
4363.	32	87					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00014	HL
4364.	32	88					TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00015	HL
4365.	32	89					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00016	HL
4366.							TEHTEC	P4202	rpri	A610MULC	SG30CCAL00004	CL
4367.	32	90					TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00015	HL
4368.	32	91					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00016	HL
4369.	32	92					TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00015	HL
4370.	32	93					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00016	HL
4371.	32	94					TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00013	HL
4372.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00004	CL
4373.	32	95					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00014	HL
4374.	32	96					TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00013	HL
4375.	32	97					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00014	HL
4376.	32	98					TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00013	HL
4377.	32	99					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00014	HL
4378.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00004	CL
4379.	32	100					TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00013	HL
4380.	32	101					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00014	HL
4381.	32	102					TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00013	HL
82.	32	103					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00014	HL
83.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00004	CL
84.	33	12					TSHTSH	S7067	rpri	B620MRPC3C	SG31HCAL00034	HL
4385.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL
4386.	33	13					TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
4387.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL
4388.	33	14					TSHTSH	S7067	rpri	B620MRPC3C	SG31HCAL00034	HL
4389.	33	15					TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
4390.	33	16					TSHTSH	S7067	rpri	B620MRPC3C	SG31HCAL00034	HL
4391.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL
4392.	33	17					TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
4393.	33	18					TSHTSH	S7067	rpri	B620MRPC3C	SG31HCAL00034	HL
4394.	33	19					TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
4395.	33	20					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00034	HL
4396.	33	21					TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
4397.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL
4398.	33	22					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00034	HL
4399.	33	23					TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
4400.	33	24					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00034	HL
4401.	33	25					TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
4402.	33	26					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00034	HL
4403.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL
4404.	33	27					TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
4405.	33	28					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00034	HL
4406.	33	29					TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
4407.	33	30					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00034	HL
4408.	33	31					TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
4409.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL
4410.	33	32					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00034	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: C
 DATABASE: Harris_SGC_1995

Sep. 23.1995 14:28

PAGE 92 of 128

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
4411.	33	33						TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
4412.	33	34						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00034	HL
4413.	33	35						TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
4414.	33	36						TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
4415.		11.84	183	DNT	1	10C	34.68	TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL
4416.	33	37						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00024	HL
4417.	33	38						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00023	HL
4418.	33	39						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00024	HL
4419.	33	40						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00023	HL
4420.	33	41						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00024	HL
4421.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00006	CL
4422.	33	42						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00023	HL
4423.	33	43						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00024	HL
4424.					RBD				P4202	rpri	A610MULC	SG30CCAL00007	CL
4425.		0.53		15	P2	AV3	0.05	TEHTEC	T9924	rpri	A610MULC	SG30CCAL00023	CL
4426.	33	44						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00023	HL
4427.	33	45						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00024	HL
4428.					RBD				P4202	rpri	A610MULC	SG30CCAL00007	CL
4429.		0.80		21	P2	AV1	-0.02	TEHTEC	T9924	rpri	A610MULC	SG30CCAL00023	CL
4430.		0.51		15	P2	AV3	-0.09	TEHTEC	T9924	rpri	A610MULC	SG30CCAL00023	CL
31.	33	46						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00023	HL
32.								TEHTEC	F3325	rsec	A610MULC	SG30CCAL00006	CL
33.	33	47						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00024	HL
4434.	33	48						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00023	HL
4435.	33	49						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00024	HL
4436.	33	50						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00023	HL
4437.	33	51						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00024	HL
4438.					RBD				P4202	rpri	A610MULC	SG30CCAL00006	CL
4439.								TEHTEC	05305	rpri	A610MULC	SG30CCAL00013	CL
4440.	33	52						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00023	HL
4441.	33	53						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00024	HL
4442.	33	54						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00023	HL
4443.	33	55						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00024	HL
4444.	33	56						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00023	HL
4445.					RBD				P4202	rpri	A610MULC	SG30CCAL00006	CL
4446.								TEHTEC	05305	rpri	A610MULC	SG30CCAL00013	CL
4447.	33	59						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
4448.								TEHTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL
4449.	33	60						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
4450.	33	61						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
4451.	33	62						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
4452.	33	63						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
4453.	33	64						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
4454.								TEHTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL
4455.	33	65						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
4456.	33	66						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
4457.	33	67						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
4458.	33	68						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
4459.	33	69						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL

*** INSPECTION FINAL REPORT LISTING ***

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: C
 DATABASE: Harris_SGC_1995

Sep. 23.1995 14:28

PAGE 93 of 128

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
4460.							TEHTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL
4461.	33	70					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
4462.	33	71					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
4463.	33	72					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
4464.	33	73					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
4465.	33	74					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
4466.							TEHTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL
4467.	33	75					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
4468.	33	76					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
4469.	33	77					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
4470.	33	78					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
4471.	33	79					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
4472.							TEHTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL
4473.	33	80					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
4474.	33	81					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
4475.	33	82					TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00013	HL
4476.	33	83					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00014	HL
4477.	33	84					TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00013	HL
4478.							TEHTEC	P4202	rpri	A610MULC	SG30CCAL00004	CL
4479.	33	85					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00014	HL
80.	33	86					TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00013	HL
81.	33	87					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00014	HL
82.	33	88					TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00015	HL
4483.	33	89					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00016	HL
4484.							TEHTEC	P4202	rpri	A610MULC	SG30CCAL00004	CL
4485.	33	90					TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00015	HL
4486.	33	91					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00016	HL
4487.	33	92					TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00015	HL
4488.	33	93					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00016	HL
4489.	33	94					TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00013	HL
4490.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00004	CL
4491.	33	95					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00014	HL
4492.	33	96					TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00013	HL
4493.	33	97					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00014	HL
4494.	33	98					TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00013	HL
4495.	33	99					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00014	HL
4496.							TEHTEC	T6956	rsec	A610MULC	SG30CCAL00004	CL
4497.	33	101					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00014	HL
4498.	33	102					TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00013	HL
4499.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00004	CL
4500.	33	103					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00014	HL
4501.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00004	CL
4502.	34	13					TSHTSH	S7067	rpri	B620MRPC3C	SG31HCAL00034	HL
4503.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL
4504.	34	14					TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
4505.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL
4506.	34	15					TSHTSH	S7067	rpri	B620MRPC3C	SG31HCAL00034	HL
4507.	34	16					TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
4508.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: C
 DATABASE: Harris_SGC_1995

Sep. 23.1995 14:28

PAGE 94 of 128

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
4509.	34	17						TSHTSH	S7067	rpri	B620MRPC3C	SG31HCAL00034	HL
4510.	34	18						TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
4511.	34	19						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00034	HL
4512.	34	20						TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
4513.	34	21						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00034	HL
4514.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL
4515.	34	22						TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
4516.	34	23						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00034	HL
4517.	34	24						TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
4518.	34	25						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00034	HL
4519.	34	26						TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
4520.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL
4521.	34	27						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00034	HL
4522.	34	28						TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
4523.	34	29						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00034	HL
4524.	34	30						TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
4525.	34	31						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00034	HL
4526.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL
4527.	34	32						TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
4528.	34	33						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00034	HL
29.	34	34						TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
30.	34	35						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00034	HL
31.	34	36						TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
4532.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL
4533.	34	37						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00024	HL
4534.	34	38						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00023	HL
4535.	34	39						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00024	HL
4536.	34	40						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00023	HL
4537.	34	41						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00024	HL
4538.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00006	CL
4539.	34	42						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00023	HL
4540.	34	43						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00024	HL
4541.	34	44						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00023	HL
4542.		1.81		31	P2	AV2	1.13	TEHTEC	C1115	rsec	A610MULC	SG30CCAL00007	CL
4543.	34	45						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00024	HL
4544.				RBD					P4202	rpri	A610MULC	SG30CCAL00007	CL
4545.		0.51		15	P2	AV3	-0.19	TEHTEC	T9924	rpri	A610MULC	SG30CCAL00023	CL
4546.	34	46						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00023	HL
4547.				RBD					P4202	rpri	A610MULC	SG30CCAL00006	CL
4548.		1.69		17	P2	AV3	-0.32	TEHTEC	05305	rpri	A610MULC	SG30CCAL00013	CL
4549.	34	47						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00024	HL
4550.	34	48						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00023	HL
4551.	34	49						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00024	HL
4552.	34	50						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00023	HL
4553.	34	51						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00024	HL
4554.				RBD					P4202	rpri	A610MULC	SG30CCAL00006	CL
4555.								TEHTEC	05305	rpri	A610MULC	SG30CCAL00013	CL
4556.	34	52						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00023	HL
4557.	34	53						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00024	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: C
 DATABASE: Harris_SGC_1995

Sep. 23, 1995 14:28

PAGE 95 of 128

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG	
4558.	34	54						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00023	HL	
4559.	34	55						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00024	HL	
4560.	34	56						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00023	HL	
4561.					RBD				P4202	rpri	A610MULC	SG30CCAL00006	CL	
4562.								TEHTEC	05305	rpri	A610MULC	SG30CCAL00013	CL	
4563.	34	59						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL	
4564.			1.17	120	5	P1	03C	0.00	TEHTEC	D3858	reso	A610MULC	SG30CCAL00005	CL
4565.	34	60						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL	
4566.	34	61						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL	
4567.	34	62						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL	
4568.	34	63						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL	
4569.	34	64						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL	
4570.								TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00023	HL	
4571.			6.63	30	NQI	P1	TEH	9.66	TEHTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL
4572.					DMR		TEH	9.66	TSHTEH	B3052	reso	B620MRPC3C	SG31HCAL00027	HL
4573.	34	65						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL	
4574.	34	66						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL	
4575.	34	67						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL	
4576.	34	68						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL	
4577.	34	69						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL	
4578.								TEHTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL	
4579.	34	70						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL	
4580.	34	71						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL	
4581.	34	72						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL	
4582.	34	73						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL	
4583.	34	74						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL	
4584.								TEHTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL	
4585.	34	75						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL	
4586.	34	76						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL	
4587.	34	77						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL	
4588.	34	78						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL	
4589.	34	79						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL	
4590.								TEHTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL	
4591.	34	80						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL	
4592.	34	81						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL	
4593.	34	82						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00013	HL	
4594.	34	83						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00014	HL	
4595.	34	84						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00013	HL	
4596.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00004	CL	
4597.	34	85						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00014	HL	
4598.	34	86						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00013	HL	
4599.	34	87						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00014	HL	
4600.	34	88						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00015	HL	
4601.	34	89						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00016	HL	
4602.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00004	CL	
4603.	34	90						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00015	HL	
4604.	34	91						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00016	HL	
4605.	34	92						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00015	HL	
4606.	34	93						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00016	HL	

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: C
 DATABASE: Harris_SGC_1995

Sep. 23.1995 14:28

PAGE 96 of 128

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
4607.	34	94					TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00013	HL
4608.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00004	CL
4609.	34	95					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00014	HL
4610.	34	96					TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00013	HL
4611.	34	97					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00014	HL
4612.	34	98					TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00013	HL
4613.	34	99					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00014	HL
4614.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00004	CL
4615.	34	100					TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00013	HL
4616.	34	101					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00014	HL
4617.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00004	CL
4618.	34	102					TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00013	HL
4619.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00004	CL
4620.	35	14					TSHTSH	S7067	rpri	B620MRPC3C	SG31HCAL00034	HL
4621.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL
4622.	35	15					TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
4623.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL
4624.	35	16					TSHTSH	S7067	rpri	B620MRPC3C	SG31HCAL00034	HL
4625.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL
4626.	35	17					TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
27.	35	18					TSHTSH	S7067	rpri	B620MRPC3C	SG31HCAL00034	HL
3.	35	19					TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
29.	35	20					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00034	HL
4630.	35	21					TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
4631.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL
4632.	35	22					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00034	HL
4633.	35	23					TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
4634.	35	24					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00034	HL
4635.	35	25					TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
4636.	35	26					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00034	HL
4637.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL
4638.	35	27					TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
4639.	35	28					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00034	HL
4640.	35	29					TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
4641.	35	30					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00034	HL
4642.	35	31					TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
4643.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL
4644.	35	32					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00034	HL
4645.	35	33					TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
4646.	35	34					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00034	HL
4647.	35	35					TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
4648.	35	36					TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
4649.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL
4650.	35	37					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00024	HL
4651.	35	38					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00023	HL
52.	35	39					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00024	HL
3.	35	40					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00023	HL
4.	35	41					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00024	HL
5.							TEHTEC	P4202	rpri	A610MULC	SG30CCAL00006	CL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: C
 DATABASE: Harris_SGC_1995

Sep. 23.1995 14:28

PAGE 97 of 128

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
4656.	35	42						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00023	HL
4657.	35	43						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00024	HL
4658.	35	44						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00023	HL
4659.	35	47						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00024	HL
4660.	35	48						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00023	HL
4661.	35	49						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00024	HL
4662.	35	50						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00023	HL
4663.	35	51						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00024	HL
4664.					RBD			P4202	rpri		A610MULC	SG30CCAL00006	CL
4665.								TEHTEC	05305	rpri	A610MULC	SG30CCAL00013	CL
4666.	35	52						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00023	HL
4667.	35	53						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00024	HL
4668.	35	54						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00023	HL
4669.	35	55						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00024	HL
4670.	35	56						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00023	HL
4671.					RBD			P4202	rpri		A610MULC	SG30CCAL00006	CL
4672.								TEHTEC	05305	rpri	A610MULC	SG30CCAL00013	CL
4673.	35	59						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
4674.								TEHTEC	T9924	rpri	A610MULC	SG30CCAL00023	CL
4675.			0.41	126	RBD	1	07C 33.44	TEHTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL
76.	35	60						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
7.	35	61						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
78.	35	62						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
4679.	35	63						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
4680.	35	64						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
4681.								TEHTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL
4682.	35	65						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
4683.	35	66						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
4684.	35	67						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
4685.	35	68						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
4686.	35	71						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
4687.	35	72						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
4688.	35	73						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
4689.	35	74						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
4690.								TEHTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL
4691.	35	75						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
4692.	35	76						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
4693.	35	77						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
4694.	35	78						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
4695.	35	79						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
4696.								TEHTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL
4697.	35	80						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
4698.	35	81						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
4699.	35	82						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00013	HL
4700.	35	83						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00014	HL
701.	35	84						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00013	HL
72.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00004	CL
73.	35	85						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00014	HL
704.	35	86						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00013	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: C
 DATABASE: Harris_SGC_1995

Sep. 23.1995 14:28

PAGE 98 of 128

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
4705.	35	87						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00014	HL
4706.	35	88						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00015	HL
4707.	35	89						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00016	HL
4708.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00004	CL
4709.	35	90						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00015	HL
4710.	35	91						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00016	HL
4711.	35	92						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00015	HL
4712.	35	93						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00016	HL
4713.	35	94						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00013	HL
4714.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00004	CL
4715.	35	95						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00014	HL
4716.	35	96						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00013	HL
4717.	35	97						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00014	HL
4718.	35	98						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00013	HL
4719.	35	99						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00014	HL
4720.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00004	CL
4721.	35	100						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00013	HL
4722.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00004	CL
4723.	35	101						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00014	HL
4724.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00004	CL
25.	36	15						TSHTSH	S7067	rpri	B620MRPC3C	SG31HCAL00034	HL
26.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL
27.	36	16						TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
4728.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL
4729.	36	17						TSHTSH	S7067	rpri	B620MRPC3C	SG31HCAL00034	HL
4730.	36	18						TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
4731.	36	19						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00034	HL
4732.	36	20						TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
4733.	36	21						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00034	HL
4734.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL
4735.	36	22						TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
4736.	36	23						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00034	HL
4737.	36	24						TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
4738.	36	25						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00034	HL
4739.	36	26						TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
4740.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL
4741.	36	27						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00034	HL
4742.	36	28						TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
4743.			1.02	164	MBM	1	05H 24.29	TEHTEC	T6956	rsec	A610MULC	SG30CCAL00009	CL
4744.	36	29						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00034	HL
4745.	36	30						TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
4746.	36	31						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00034	HL
4747.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL
4748.	36	32						TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
4749.	36	33						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00034	HL
4750.	36	34						TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
4751.	36	35						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00034	HL
4752.	36	36						TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
4753.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: C
 DATABASE: Harris_SGC_1995

Sep. 23,1995 14:28

PAGE 99 of 128

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG		
4754.	36	37						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00024	HL		
4755.	36	38						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00023	HL		
4756.	36	39						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00024	HL		
4757.	36	40						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00023	HL		
4758.	36	41						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00024	HL		
4759.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00006	CL		
4760.	36	42						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00023	HL		
4761.	36	43						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00024	HL		
4762.	36	44						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00023	HL		
4763.	36	47						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00024	HL		
4764.	36	48						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00023	HL		
4765.	36	49						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00024	HL		
4766.	36	50						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00023	HL		
4767.	36	51						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00024	HL		
4768.					RBD			P4202	rpri	A610MULC	SG30CCAL00006	CL			
4769.								TEHTEC	05305	rpri	A610MULC	SG30CCAL00013	CL		
4770.	36	52						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00023	HL		
4771.	36	53						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00024	HL		
4772.	36	54						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00023	HL		
4773.	36	55						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00024	HL		
74.	36	56						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00023	HL		
5.					RBD			P4202	rpri	A610MULC	SG30CCAL00006	CL			
76.								TEHTEC	05305	rpri	A610MULC	SG30CCAL00013	CL		
4777.	36	59						TSHTSH	D3858	reso	B620MRPC3C	SG31HCAL00019	HL		
4778.			0.62	142	26	1	TSH	1.23	TEHTEC	T6956	rsec	A610MULC	SG30CCAL00005	CL	
4779.	36	60						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL		
4780.	36	61						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL		
4781.	36	62						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL		
4782.	36	63						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL		
4783.	36	64						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL		
4784.								TEHTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL		
4785.	36	65						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL		
4786.	36	66						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL		
4787.	36	67						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL		
4788.	36	68						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL		
4789.	36	71						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL		
4790.	36	72						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL		
4791.	36	73						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL		
4792.	36	74						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL		
4793.								TEHTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL		
4794.	36	75						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL		
4795.	36	76						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL		
4796.	36	77						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL		
4797.	36	78						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL		
4798.	36	79						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL		
799.								TEHTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL		
80.	36	80						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL		
1.	36	81						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL		
802.	36	82						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00013	HL		

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: C
 DATABASE: Harris_SGC_1995

Sep. 23,1995 14:28

PAGE 100 of 128

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
4803.	36	83						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00014	HL
4804.	36	84						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00013	HL
4805.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00004	CL
4806.	36	85						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00014	HL
4807.	36	86						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00013	HL
4808.	36	87						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00014	HL
4809.	36	88						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00015	HL
4810.	36	89						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00016	HL
4811.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00004	CL
4812.	36	90						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00015	HL
4813.	36	91						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00016	HL
4814.	36	92						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00015	HL
4815.	36	93						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00016	HL
4816.	36	94						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00013	HL
4817.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00004	CL
4818.	36	95						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00014	HL
4819.	36	96						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00013	HL
4820.	36	97						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00014	HL
4821.	36	98						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00013	HL
4822.	36	99						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00014	HL
4823.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00004	CL
4824.	36	100						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00013	HL
4825.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00004	CL
4826.	37	16						TSHTSH	S7067	rpri	B620MRPC3C	SG31HCAL00034	HL
4827.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL
4828.	37	17						TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
4829.	37	18						TSHTSH	S7067	rpri	B620MRPC3C	SG31HCAL00034	HL
4830.	37	19						TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
4831.	37	20						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00034	HL
4832.	37	21						TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
4833.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL
4834.	37	22						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00034	HL
4835.	37	23						TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
4836.	37	24						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00034	HL
4837.	37	25						TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
4838.	37	26						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00034	HL
4839.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL
4840.	37	27						TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
4841.	37	28						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00034	HL
4842.	37	29						TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
4843.	37	30						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00034	HL
4844.	37	31						TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
4845.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL
4846.	37	32						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00034	HL
4847.	37	33						TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
4848.	37	34						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00034	HL
4849.	37	35						TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
4850.	37	36						TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
4851.			0.75	153	MBM	1	10C 19.29	TEHTEC	B3052	reso	A610MULC	SG30CCAL00009	CL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: C
 DATABASE: Harris_SGC_1995

Sep. 23.1995 14:28

PAGE 101 of 128

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
4852.	37	37						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00024	HL
4853.	37	38						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00023	HL
4854.	37	39						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00024	HL
4855.	37	40						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00023	HL
4856.	37	41						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00024	HL
4857.					RBD			P4202	rpri		A610MULC	SG30CCAL00006	CL
4858.								TEHTEC	05305	rpri	A610MULC	SG30CCAL00013	CL
4859.	37	42						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00023	HL
4860.	37	43						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00024	HL
4861.	37	44						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00023	HL
4862.	37	45						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00024	HL
4863.	37	46						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00023	HL
4864.								TEHTEC	F3325	rsec	A610MULC	SG30CCAL00006	CL
4865.	37	47						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00024	HL
4866.	37	48						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00023	HL
4867.	37	49						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00024	HL
4868.	37	50						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00023	HL
4869.	37	51						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00024	HL
4870.					RBD			P4202	rpri		A610MULC	SG30CCAL00006	CL
4871.								TEHTEC	05305	rpri	A610MULC	SG30CCAL00013	CL
4872.	37	52						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00023	HL
4873.	37	53						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00024	HL
4874.	37	54						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00023	HL
4875.	37	55						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00024	HL
4876.	37	56						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00023	HL
4877.					RBD			P4202	rpri		A610MULC	SG30CCAL00006	CL
4878.								TEHTEC	05305	rpri	A610MULC	SG30CCAL00013	CL
4879.	37	59						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
4880.								TEHTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL
4881.	37	60						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
4882.	37	61						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
4883.	37	62						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
4884.	37	63						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
4885.	37	64						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
4886.								TEHTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL
4887.	37	65						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
4888.	37	66						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
4889.	37	67						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
4890.	37	68						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
4891.	37	69						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
4892.								TEHTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL
4893.	37	70						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
4894.	37	71						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
4895.	37	72						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
4896.	37	73						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
4897.	37	74						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
4898.								TEHTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL
4899.	37	75						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
4900.	37	76						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: C
 DATABASE: Harris_SGC_1995

Sep. 23.1995 14:28

PAGE 102 of 128

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
4901.	37	77						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
4902.	37	78						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
4903.	37	79						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
4904.								TEHTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL
4905.	37	80						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
4906.	37	81						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
4907.	37	82						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00013	HL
4908.	37	83						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00014	HL
4909.	37	84						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00013	HL
4910.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00004	CL
4911.	37	85						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00014	HL
4912.	37	86						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00015	HL
4913.		0.33		10	P2	AV3	-0.05	TEHTEC	P4202	rpri	A610MULC	SG30CCAL00004	CL
4914.	37	87						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00016	HL
4915.	37	88						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00015	HL
4916.	37	89						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00016	HL
4917.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00004	CL
4918.	37	90						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00015	HL
4919.	37	91						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00016	HL
4920.	37	92						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00015	HL
4921.	37	93						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00016	HL
2.	37	94						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00013	HL
4923.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00004	CL
4924.	37	95						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00014	HL
4925.	37	96						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00013	HL
4926.	37	97						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00014	HL
4927.	37	98						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00013	HL
4928.	37	99						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00014	HL
4929.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00004	CL
4930.	38	16						TSHTSH	S7067	rpri	B620MRPC3C	SG31HCAL00034	HL
4931.								09H09H	T7072	rpri	B620MRPC3C	SG31HCAL00027	HL
4932.		12.56	176	DNT	P1	09H	-0.32	TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL
4933.	38	17						TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
4934.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL
4935.	38	18						TSHTSH	C7651	rsec	B620MRPC3C	SG31HCAL00034	HL
4936.	38	19						TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
4937.	38	20						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00034	HL
4938.	38	21						TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
4939.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL
4940.	38	22						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00034	HL
4941.	38	23						TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
4942.	38	24						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00034	HL
4943.	38	25						TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
4944.	38	26						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00034	HL
4945.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL
4946.	38	27						TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
4947.	38	28						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00034	HL
3.	38	29						TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
49.	38	30						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00034	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: C
 DATABASE: Harris_SGC_1995

Sep. 23, 1995 14:28

PAGE 103 of 128

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
4950.	38	31						TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
4951.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL
4952.	38	32						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00034	HL
4953.	38	33						TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
4954.	38	34						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00034	HL
4955.	38	35						TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
4956.	38	36						TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
4957.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL
4958.	38	37						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00024	HL
4959.	38	38						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00023	HL
4960.	38	39						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00024	HL
4961.	38	40						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00023	HL
4962.	38	41						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00024	HL
4963.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00006	CL
4964.	38	42						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00023	HL
4965.	38	43						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00024	HL
4966.	38	44						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00023	HL
4967.	38	45						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00024	HL
4968.	38	46						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00023	HL
4969.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00006	CL
4970.	38	47						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00024	HL
4971.	38	48						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00023	HL
4972.	38	49						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00024	HL
4973.	38	50						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00023	HL
4974.	38	51						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00024	HL
4975.					RBD			P4202	rpri		A610MULC	SG30CCAL00006	CL
4976.								TEHTEC	05305	rpri	A610MULC	SG30CCAL00013	CL
4977.	38	52						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00023	HL
4978.	38	53						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00024	HL
4979.	38	54						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00023	HL
4980.	38	55						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00024	HL
4981.	38	56						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00023	HL
4982.					RBD			P4202	rpri		A610MULC	SG30CCAL00006	CL
4983.								TEHTEC	05305	rpri	A610MULC	SG30CCAL00013	CL
4984.	38	59						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
4985.								TEHTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL
4986.	38	60						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
4987.	38	61						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
4988.	38	62						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
4989.	38	63						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
4990.	38	64						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
4991.								TEHTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL
4992.	38	65						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
4993.	38	66						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
4994.	38	67						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
4995.	38	68						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
4996.	38	69						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
4997.								TEHTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL
4998.	38	70						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: C
 DATABASE: Harris_SGC_1995

Sep. 23.1995 14:28

PAGE 104 of 128

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
4999.	38	71						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
5000.	38	72						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
5001.	38	73						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
5002.	38	74						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
5003.								TEHTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL
5004.	38	75						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
5005.	38	76						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
5006.	38	77						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
5007.	38	78						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
5008.	38	79						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
5009.								TEHTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL
5010.	38	80						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
5011.	38	81						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
5012.	38	82						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00013	HL
5013.	38	83						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00014	HL
5014.	38	84						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00013	HL
5015.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00004	CL
5016.	38	85						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00014	HL
5017.	38	86						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00015	HL
5018.	38	87						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00016	HL
5019.	38	88						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00015	HL
5020.	38	89						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00016	HL
5021.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00004	CL
5022.	38	90						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00015	HL
5023.	38	91						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00016	HL
5024.	38	92						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00015	HL
5025.	38	93						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00016	HL
5026.	38	94						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00013	HL
5027.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00004	CL
5028.	38	95						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00014	HL
5029.	38	96						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00013	HL
5030.	38	97						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00014	HL
5031.	38	98						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00013	HL
5032.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00004	CL
5033.	38	99						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00014	HL
5034.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00004	CL
5035.	39	17						TSHTSH	S7067	rpri	B620MRPC3C	SG31HCAL00034	HL
5036.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL
5037.	39	18						TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
5038.		6.58	181	DNT	1	11H	9.44	TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL
5039.		10.06	182	DNT	1	11H	10.15	TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL
5040.		15.77	183	DNT	1	10C	36.52	TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL
5041.		27.25	180	DNT	1	10C	37.32	TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL
5042.		12.74	179	DNT	1	10C	37.81	TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL
5043.		19.62	182	DNT	1	10C	38.37	TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL
5044.		28.49	180	DNT	1	10C	38.75	TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL
5045.		27.59	181	DNT	1	10C	39.07	TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL
5046.		8.12	181	DNT	1	10C	40.77	TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL
5047.		8.99	183	DNT	1	10C	41.47	TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: C
 DATABASE: Harris_SGC_1995

Sep. 23, 1995 14:28

PAGE 105 of 128

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE	SIZE	CAL	GROUP	LEG
5048.	39	19						TSHTSH	B5534	rpri	B620MRPC3C		SG31HCAL00034	HL	
5049.	39	20						TSHTSH	T9924	rpri	B620MRPC3C		SG31HCAL00035	HL	
5050.	39	21						TSHTSH	B5534	rpri	B620MRPC3C		SG31HCAL00034	HL	
5051.								TEHTEC	N0698	rpri	A610MULC		SG30CCAL00009	CL	
5052.	39	22						TSHTSH	T9924	rpri	B620MRPC3C		SG31HCAL00035	HL	
5053.	39	23						TSHTSH	B5534	rpri	B620MRPC3C		SG31HCAL00034	HL	
5054.	39	24						TSHTSH	M9082	rsec	B620MRPC3C		SG31HCAL00035	HL	
5055.	39	25						TSHTSH	B5534	rpri	B620MRPC3C		SG31HCAL00034	HL	
5056.	39	26						TSHTSH	T9924	rpri	B620MRPC3C		SG31HCAL00035	HL	
5057.								TEHTEC	N0698	rpri	A610MULC		SG30CCAL00009	CL	
5058.	39	27						TSHTSH	B5534	rpri	B620MRPC3C		SG31HCAL00034	HL	
5059.	39	28						TSHTSH	M9082	rsec	B620MRPC3C		SG31HCAL00035	HL	
5060.	39	29						TSHTSH	B5534	rpri	B620MRPC3C		SG31HCAL00034	HL	
5061.	39	30						TSHTSH	T9924	rpri	B620MRPC3C		SG31HCAL00035	HL	
5062.	39	31						TSHTSH	B5534	rpri	B620MRPC3C		SG31HCAL00034	HL	
5063.								TEHTEC	N0698	rpri	A610MULC		SG30CCAL00009	CL	
5064.	39	32						TSHTSH	T9924	rpri	B620MRPC3C		SG31HCAL00035	HL	
5065.	39	33						TSHTSH	B5534	rpri	B620MRPC3C		SG31HCAL00034	HL	
5066.	39	34						TSHTSH	T9924	rpri	B620MRPC3C		SG31HCAL00035	HL	
5067.	39	35						TSHTSH	B5534	rpri	B620MRPC3C		SG31HCAL00034	HL	
5068.	39	36						TSHTSH	T9924	rpri	B620MRPC3C		SG31HCAL00035	HL	
5069.								TEHTEC	N0698	rpri	A610MULC		SG30CCAL00009	CL	
5070.	39	37						TSHTSH	F9284	rpri	B620MRPC3C		SG31HCAL00024	HL	
5071.	39	38						TSHTSH	F9284	rpri	B620MRPC3C		SG31HCAL00023	HL	
5072.	39	39						TSHTSH	F9284	rpri	B620MRPC3C		SG31HCAL00024	HL	
5073.	39	40						TSHTSH	F9284	rpri	B620MRPC3C		SG31HCAL00023	HL	
5074.	39	41						TSHTSH	F9284	rpri	B620MRPC3C		SG31HCAL00024	HL	
5075.								TEHTEC	P4202	rpri	A610MULC		SG30CCAL00006	CL	
5076.	39	42						TSHTSH	F9284	rpri	B620MRPC3C		SG31HCAL00023	HL	
5077.	39	43						TSHTSH	F9284	rpri	B620MRPC3C		SG31HCAL00024	HL	
5078.	39	44						TSHTSH	F9284	rpri	B620MRPC3C		SG31HCAL00023	HL	
5079.	39	45						TSHTSH	F9284	rpri	B620MRPC3C		SG31HCAL00024	HL	
5080.	39	46						TSHTSH	F9284	rpri	B620MRPC3C		SG31HCAL00023	HL	
5081.								TEHTEC	P4202	rpri	A610MULC		SG30CCAL00006	CL	
5082.	39	47						TSHTSH	F9284	rpri	B620MRPC3C		SG31HCAL00024	HL	
5083.	39	48						TSHTSH	F9284	rpri	B620MRPC3C		SG31HCAL00023	HL	
5084.	39	49						TSHTSH	F9284	rpri	B620MRPC3C		SG31HCAL00024	HL	
5085.	39	50						TSHTSH	F9284	rpri	B620MRPC3C		SG31HCAL00023	HL	
5086.	39	51						TSHTSH	F9284	rpri	B620MRPC3C		SG31HCAL00024	HL	
5087.					RBD				P4202	rpri	A610MULC		SG30CCAL00006	CL	
5088.								TEHTEC	O5305	rpri	A610MULC		SG30CCAL00013	CL	
5089.	39	52						TSHTSH	F9284	rpri	B620MRPC3C		SG31HCAL00023	HL	
5090.	39	53						TSHTSH	F9284	rpri	B620MRPC3C		SG31HCAL00024	HL	
5091.	39	54						TSHTSH	F9284	rpri	B620MRPC3C		SG31HCAL00023	HL	
5092.	39	55						TSHTSH	F9284	rpri	B620MRPC3C		SG31HCAL00024	HL	
5093.	39	56						TSHTSH	F9284	rpri	B620MRPC3C		SG31HCAL00023	HL	
5094.					RBD				P4202	rpri	A610MULC		SG30CCAL00006	CL	
5095.								TEHTEC	O5305	rpri	A610MULC		SG30CCAL00013	CL	
5096.	39	59						TSHTSH	F9284	rpri	B620MRPC3C		SG31HCAL00019	HL	

*** INSPECTION FINAL REPORT LISTING ***

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: C
 DATABASE: Harris_SGC_1995

Sep. 23, 1995 14:28

PAGE 106 of 128

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
5097.								TEHTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL
5098.	39	60						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
5099.	39	61						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
5100.	39	62						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
5101.	39	63						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
5102.	39	64						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
5103.								TEHTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL
5104.	39	65						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
5105.	39	66						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
5106.	39	67						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
5107.	39	68						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
5108.	39	69						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
5109.		9.36	179	DNT	1	10C	37.21	TEHTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL
5110.	39	70						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
5111.	39	71						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
5112.	39	72						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
5113.	39	73						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
5114.	39	74						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
5115.		0.39		11	P2	AV3	0.00	TEHTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL
5116.	39	75						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
17.	39	76						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
3.	39	77						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
19.	39	78						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
5120.	39	79						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
5121.								TEHTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL
5122.	39	80						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
5123.	39	81						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
5124.	39	82						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00013	HL
5125.	39	83						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00014	HL
5126.	39	84						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00013	HL
5127.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00004	CL
5128.	39	85						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00014	HL
5129.	39	86						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00015	HL
5130.		1.08		27	P2	AV3	0.00	TEHTEC	P4202	rpri	A610MULC	SG30CCAL00004	CL
5131.	39	87						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00016	HL
5132.	39	88						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00015	HL
5133.	39	89						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00016	HL
5134.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00004	CL
5135.	39	90						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00015	HL
5136.	39	91						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00016	HL
5137.	39	92						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00015	HL
5138.	39	93						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00016	HL
5139.	39	94						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00013	HL
5140.		7.86	182	DNT	1	10C	37.59	TEHTEC	N0698	rpri	A610MULC	SG30CCAL00004	CL
5141.		16.69	181	DNT	1	10C	38.34	TEHTEC	N0698	rpri	A610MULC	SG30CCAL00004	CL
142.	39	95						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00014	HL
143.	39	96						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00013	HL
144.	39	97						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00014	HL
145.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00004	CL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: C
 DATABASE: Harris_SGC_1995

Sep. 23,1995 14:28

PAGE 107 of 128

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
5146.	39	98						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00013	HL
5147.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00004	CL
5148.	40	18						TSHTSH	S7067	rpri	B620MRPC3C	SG31HCAL00034	HL
5149.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL
5150.	40	19						TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
5151.		0.91		25	P2	AV4	-0.22	TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL
5152.	40	20						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00034	HL
5153.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL
5154.	40	21						TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
5155.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL
5156.	40	22						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00034	HL
5157.	40	23						TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
5158.	40	24						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00034	HL
5159.	40	25						TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
5160.	40	26						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00034	HL
5161.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL
5162.	40	27						TSHTSH	M9082	rsec	B620MRPC3C	SG31HCAL00035	HL
5163.	40	28						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00034	HL
5164.	40	29						TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
5165.	40	30						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00034	HL
5166.	40	31						TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
5167.		6.59	179	DNT	P1	11C	0.24	TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL
5168.		8.27	184	DNT	1	11C	1.03	TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL
5169.	40	32						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00034	HL
5170.	40	33						TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
5171.	40	34						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00034	HL
5172.	40	35						TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
5173.	40	36						TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
5174.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL
5175.	40	37						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00024	HL
5176.	40	38						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00023	HL
5177.	40	39						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00024	HL
5178.	40	40						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00023	HL
5179.	40	41						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00024	HL
5180.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00006	CL
5181.	40	42						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00023	HL
5182.	40	43						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00024	HL
5183.	40	44						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00023	HL
5184.	40	45						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00024	HL
5185.	40	46						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00023	HL
5186.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00006	CL
5187.	40	47						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00024	HL
5188.	40	48						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00023	HL
5189.	40	49						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00024	HL
5190.	40	50						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00023	HL
5191.	40	51						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00024	HL
5192.					RBD				P4202	rpri	A610MULC	SG30CCAL00006	CL
5193.								TEHTEC	05305	rpri	A610MULC	SG30CCAL00013	CL
5194.	40	52						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00023	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: C
 DATABASE: Harris_SGC_1995

Sep. 23,1995 14:28

PAGE 108 of 128

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
5195.	40	53						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00024	HL
5196.	40	54						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00023	HL
5197.	40	55						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00024	HL
5198.	40	56						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00023	HL
5199.					RBD				P4202	rpri	A610MULC	SG30CCAL00006	CL
5200.		0.50		15	P2	AV1	-0.11	TEHTEC	B3052	reso	A610MULC	SG30CCAL00013	CL
5201.		0.57		16	P2	AV3	-0.08	TEHTEC	B3052	reso	A610MULC	SG30CCAL00013	CL
5202.	40	59						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
5203.								TEHTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL
5204.	40	60						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
5205.		0.35		10	P2	AV2	0.00	TEHTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL
5206.	40	61						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
5207.	40	62						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
5208.	40	63						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
5209.	40	64						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
5210.								TEHTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL
5211.	40	65						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
5212.	40	66						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
5213.	40	67						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
5214.	40	68						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
5215.	40	69						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
5216.								TEHTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL
5217.	40	70						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
5218.	40	71						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
5219.	40	72						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
5220.	40	73						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
5221.	40	74						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
5222.								TEHTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL
5223.	40	75						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
5224.	40	76						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
5225.	40	77						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
5226.	40	78						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
5227.	40	79						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
5228.								TEHTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL
5229.	40	80						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
5230.	40	81						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
5231.	40	82						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00013	HL
5232.	40	83						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00014	HL
5233.	40	84						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00013	HL
5234.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00004	CL
5235.	40	85						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00014	HL
5236.	40	86						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00015	HL
5237.	40	87						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00016	HL
5238.	40	88						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00015	HL
5239.	40	89						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00016	HL
5240.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00004	CL
5241.	40	90						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00015	HL
5242.	40	91						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00016	HL
5243.	40	92						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00015	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: C
 DATABASE: Harris_SGC_1995

Sep. 23.1995 14:28

PAGE 109 of 128

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
5244.	40	93						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00016	HL
5245.	40	94						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00013	HL
5246.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00004	CL
5247.	40	95						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00014	HL
5248.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00004	CL
5249.	40	96						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00013	HL
5250.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00004	CL
5251.	40	97						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00014	HL
5252.		10.54	180	DNT	P1	AV2	0.65	TEHTEC	N0698	rpri	A610MULC	SG30CCAL00004	CL
5253.	41	20						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
5254.		1.76		33	P2	AV4	0.00	TEHTEC	P4202	rpri	A610MULC	SG30CCAL00008	CL
5255.		5.85	179	DNT	P1	11C	-0.42	TEHTEC	P4202	rpri	A610MULC	SG30CCAL00008	CL
5256.		9.05	180	DNT	P1	11C	0.34	TEHTEC	P4202	rpri	A610MULC	SG30CCAL00008	CL
5257.	41	21						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
5258.		8.22	180	DNT	1	10C	36.97	TEHTEC	P4202	rpri	A610MULC	SG30CCAL00008	CL
5259.	41	22						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
5260.	41	23						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
5261.	41	24						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
5262.	41	25						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
5263.	41	26						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
5264.		10.69	180	DNT	1	10C	40.29	TEHTEC	P4202	rpri	A610MULC	SG30CCAL00008	CL
5265.		22.54	179	DNT	1	10C	41.18	TEHTEC	P4202	rpri	A610MULC	SG30CCAL00008	CL
5266.	41	27						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
5267.	41	28						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
5268.	41	29						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
5269.	41	30						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
5270.	41	31						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
5271.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00008	CL
5272.	41	32						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
5273.	41	33						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
5274.	41	34						TSHTSH	S7067	rpri	B620MRPC3C	SG31HCAL00034	HL
5275.	41	35						TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
5276.	41	36						TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
5277.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL
5278.	41	37						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL
5279.	41	38						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00021	HL
5280.	41	39						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL
5281.	41	40						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00021	HL
5282.	41	41						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL
5283.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00006	CL
5284.	41	42						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00021	HL
5285.	41	43						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL
5286.	41	44						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00021	HL
5287.	41	45						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL
5288.	41	46						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00021	HL
5289.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00006	CL
5290.	41	47						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL
5291.	41	48						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00021	HL
5292.	41	49						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: C
 DATABASE: Harris_SGC_1995

Sep. 23,1995 14:28

PAGE 110 of 128

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
5293.	41	50						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00021	HL
5294.	41	51						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL
5295.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00006	CL
5296.	41	52						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00021	HL
5297.	41	53						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL
5298.	41	54						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00021	HL
5299.	41	55						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL
5300.	41	56						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00021	HL
5301.								03C02C	S7675	rpri	B620MRPC3C	SG30CCAL00020	CL
5302.		0.59		19	P2	AV2	0.00	TEHTEC	H1274	reso	A610MULC	SG30CCAL00006	CL
5303.	41	59						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
5304.								TEHTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL
5305.	41	60						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
5306.	41	61						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
5307.	41	62						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
5308.	41	63						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
5309.	41	64						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
5310.								TEHTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL
5311.	41	65						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
5312.	41	66						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
5313.	41	67						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
5314.	41	68						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
5315.	41	69						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
5316.								TEHTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL
5317.	41	70						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
5318.	41	71			RBD			F9284	rpri	B620MRPC3C	SG31HCAL00019	HL	
5319.								TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
5320.	41	72			RBD			F9284	rpri	B620MRPC3C	SG31HCAL00020	HL	
5321.								TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00021	HL
5322.	41	73						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00021	HL
5323.	41	74						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00021	HL
5324.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00006	CL
5325.	41	75						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00021	HL
5326.	41	76						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00021	HL
5327.	41	77						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00021	HL
5328.	41	78						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00021	HL
5329.	41	79						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00021	HL
5330.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00006	CL
5331.	41	80						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00021	HL
5332.	41	81						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00021	HL
5333.	41	82						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00013	HL
5334.	41	83						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00014	HL
5335.	41	84						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00013	HL
5336.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00004	CL
5337.	41	85						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00014	HL
5338.	41	86						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00013	HL
5339.	41	87						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00014	HL
5340.	41	88						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00013	HL
5341.	41	89						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00014	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: C
 DATABASE: Harris_SGC_1995

Sep. 23.1995 14:28

PAGE 111 of 128

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
5342.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00004	CL
5343.	41	90						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00013	HL
5344.	41	91						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00014	HL
5345.	41	92						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00013	HL
5346.	41	93						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00014	HL
5347.	41	94						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00013	HL
5348.								TEHTEC	T6956	rsec	A610MULC	SG30CCAL00004	CL
5349.	41	95						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00014	HL
5350.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00004	CL
5351.	42	21						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
5352.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00008	CL
5353.	42	22						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
5354.			6.74	183	DNT	1	11H 6.58	TEHTEC	H1274	reso	A610MULC	SG30CCAL00008	CL
5355.			34.52	179	DNT	1	AV4 31.17	TEHTEC	P4202	rpri	A610MULC	SG30CCAL00008	CL
5356.			10.11	181	DNT	1	AV4 31.92	TEHTEC	P4202	rpri	A610MULC	SG30CCAL00008	CL
5357.	42	23						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
5358.	42	24						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
5359.	42	25						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
5360.	42	26						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
5361.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00008	CL
5362.	42	27						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
5363.	42	28						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
5364.	42	29						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
5365.	42	30						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
5366.	42	31						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
5367.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00008	CL
5368.	42	32						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
5369.	42	33						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
5370.	42	34						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
5371.	42	35						TSHTSH	S7067	rpri	B620MRPC3C	SG31HCAL00034	HL
5372.	42	36						TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
5373.			11.57	5	DNT	1	11H 6.39	TEHTEC	C1115	rsec	A610MULC	SG30CCAL00009	CL
5374.			24.91	182	DNT	1	11H 7.09	TEHTEC	C1115	rsec	A610MULC	SG30CCAL00009	CL
5375.			16.33	183	DNT	P1	11C -0.64	TEHTEC	C1115	rsec	A610MULC	SG30CCAL00009	CL
5376.			5.52	183	DNT	1	10C 38.45	TEHTEC	C1115	rsec	A610MULC	SG30CCAL00009	CL
5377.			7.32	182	DNT	1	10C 41.54	TEHTEC	C1115	rsec	A610MULC	SG30CCAL00009	CL
5378.	42	37						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL
5379.	42	38						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00021	HL
5380.	42	39						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL
5381.	42	40						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00021	HL
5382.	42	41						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL
5383.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00006	CL
5384.	42	42						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00021	HL
5385.	42	43						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL
5386.	42	44						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00021	HL
5387.	42	45						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL
5388.	42	46						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00021	HL
5389.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00006	CL
5390.	42	47						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: C
 DATABASE: Harris_SGC_1995

Sep. 23,1995 14:28

PAGE 112 of 128

ROW	COLUMN	VOLTS	DEG	PCT	CHAN LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
5391.	42	48					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00021	HL
5392.	42	49					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL
5393.	42	50					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00021	HL
5394.	42	51					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL
5395.							TEHTEC	P4202	rpri	A610MULC	SG30CCAL00006	CL
5396.	42	52					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00021	HL
5397.	42	53					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL
5398.	42	54					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00021	HL
5399.	42	55					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL
5400.	42	59					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
5401.							TEHTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL
5402.							03C02C	S7675	rpri	B620MRPC3C	SG30CCAL00020	CL
5403.	42	60					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
5404.	42	61					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
5405.	42	62					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
5406.	42	63					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
5407.	42	64					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
5408.							TEHTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL
5409.	42	65					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
5410.	42	66					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
5411.	42	67					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
5412.	42	68					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
5413.	42	69					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
5414.							TEHTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL
5415.	42	70					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
5416.	42	71					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
5417.	42	72					TSHTSH	J9815	rsec	B620MRPC3C	SG31HCAL00022	HL
5418.	42	73					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL
5419.	42	74					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL
5420.							TEHTEC	P4202	rpri	A610MULC	SG30CCAL00006	CL
5421.	42	75					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL
5422.	42	76					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL
5423.	42	77					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL
5424.	42	78					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL
5425.	42	79					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL
5426.							TEHTEC	P4202	rpri	A610MULC	SG30CCAL00006	CL
5427.	42	80					TSHTSH	J9815	rsec	B620MRPC3C	SG31HCAL00022	HL
5428.	42	81					TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL
5429.	42	82					TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00013	HL
5430.	42	83					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00014	HL
5431.	42	84					TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00013	HL
5432.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00004	CL
5433.	42	85					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00014	HL
5434.	42	86					TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00013	HL
5435.	42	87					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00014	HL
5436.	42	88					TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00013	HL
5437.	42	89					TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00014	HL
5438.							TEHTEC	N0698	rpri	A610MULC	SG30CCAL00004	CL
5439.	42	90					TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00013	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: C
 DATABASE: Harris_SGC_1995

Sep. 23, 1995 14:28

PAGE 113 of 128

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
5440.	42	91						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00014	HL
5441.	42	92						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00013	HL
5442.	42	93						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00014	HL
5443.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00004	CL
5444.	42	94						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00013	HL
5445.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00004	CL
5446.	43	22						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
5447.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00008	CL
5448.	43	23						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
5449.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00008	CL
5450.	43	24						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
5451.	43	25						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
5452.	43	26						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
5453.			5.14	180	DNT	1	07H 25.96	TEHTEC	P4202	rpri	A610MULC	SG30CCAL00008	CL
5454.	43	27						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
5455.	43	28						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
5456.	43	29						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
5457.	43	30						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
5458.	43	31						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
5459.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00008	CL
5460.	43	32						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
5461.	43	33						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
5462.	43	34						TSHTSH	S7067	rpri	B620MRPC3C	SG31HCAL00034	HL
5463.	43	35						TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
5464.	43	36						TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
5465.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL
5466.	43	37						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL
5467.	43	38						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00021	HL
5468.	43	39						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL
5469.	43	40						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00021	HL
5470.	43	41						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL
5471.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00006	CL
5472.	43	42						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00021	HL
5473.	43	43						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL
5474.	43	44						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00021	HL
5475.	43	45						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL
5476.	43	46						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00021	HL
5477.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00006	CL
5478.	43	47						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL
5479.	43	48						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00021	HL
5480.	43	49						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL
5481.	43	50						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00021	HL
5482.	43	51						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL
5483.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00006	CL
5484.	43	52						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00021	HL
5485.	43	53						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL
5486.	43	54						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00021	HL
5487.	43	55						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL
5488.	43	56						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00021	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: C
 DATABASE: Harris_SGC_1995

Sep. 23, 1995 14:28

PAGE 114 of 128

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
5489.		0.55		18	P2	09C	-0.38	TEHTEC	H1274	reso	A610MULC	SG30CCAL00006	CL
5490.	43	59						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
5491.		0.55		15	P2	AV2	-0.05	TEHTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL
5492.	43	60						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
5493.	43	61						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
5494.	43	62						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
5495.	43	63						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
5496.	43	64						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
5497.								TEHTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL
5498.	43	65						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
5499.	43	66						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
5500.	43	67						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
5501.	43	68						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
5502.	43	69						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
5503.								TEHTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL
5504.	43	70						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
5505.	43	71						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
5506.	43	72						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00021	HL
5507.	43	73						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00021	HL
5508.	43	74						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00021	HL
5509.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00006	CL
5510.	43	75						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00021	HL
5511.	43	76						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00021	HL
5512.	43	77						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00021	HL
5513.	43	78						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00021	HL
5514.	43	79						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00021	HL
5515.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00006	CL
5516.	43	80						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00021	HL
5517.	43	81						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00021	HL
5518.	43	82						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00013	HL
5519.	43	83						TSHTSH	85534	rpri	B620MRPC3C	SG31HCAL00014	HL
5520.	43	84						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00013	HL
5521.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00004	CL
5522.	43	85						TSHTSH	85534	rpri	B620MRPC3C	SG31HCAL00014	HL
5523.	43	86						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00013	HL
5524.	43	87						TSHTSH	85534	rpri	B620MRPC3C	SG31HCAL00014	HL
5525.	43	88						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00013	HL
5526.	43	89						TSHTSH	85534	rpri	B620MRPC3C	SG31HCAL00014	HL
5527.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00004	CL
5528.	43	90						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00013	HL
5529.	43	91						TSHTSH	85534	rpri	B620MRPC3C	SG31HCAL00014	HL
5530.	43	92						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00013	HL
5531.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00004	CL
5532.	43	93						TSHTSH	85534	rpri	B620MRPC3C	SG31HCAL00014	HL
5533.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00004	CL
5534.	44	23						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
5535.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00008	CL
5536.	44	24						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
5537.								TEHTEC	H1274	reso	A610MULC	SG30CCAL00008	CL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: C
 DATABASE: Harris_SGC_1995

Sep. 23.1995 14:28

PAGE 115 of 128

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
5538.	44	25						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
5539.	44	26						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
5540.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00008	CL
5541.	44	27						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
5542.	44	28						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
5543.	44	29						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
5544.	44	30						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
5545.	44	31						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
5546.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00008	CL
5547.	44	32						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
5548.	44	33						TSHTSH	S7067	rpri	B620MRPC3C	SG31HCAL00034	HL
5549.	44	34						TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
5550.	44	35						TSHTSH	S7067	rpri	B620MRPC3C	SG31HCAL00034	HL
5551.	44	36						TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
5552.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL
5553.	44	37						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL
5554.	44	38						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00021	HL
5555.	44	39						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL
5556.	44	40						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00021	HL
5557.	44	41						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL
5558.		9.10	183	DNT	1	09H	26.98	TEHTEC	P4202	rpri	A610MULC	SG30CCAL00006	CL
5559.		13.95	184	DNT	1	11H	6.35	TEHTEC	P4202	rpri	A610MULC	SG30CCAL00006	CL
5560.		15.92	183	DNT	1	11H	7.28	TEHTEC	P4202	rpri	A610MULC	SG30CCAL00006	CL
5561.	44	42						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00021	HL
5562.	44	43						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL
5563.	44	44						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00021	HL
5564.	44	45						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL
5565.	44	46						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00021	HL
5566.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00006	CL
5567.	44	47						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL
5568.	44	48						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00021	HL
5569.	44	49						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL
5570.	44	50						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00021	HL
5571.	44	51						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL
5572.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00006	CL
5573.	44	52						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00021	HL
5574.	44	53						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL
5575.	44	54						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00021	HL
5576.	44	55						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL
5577.	44	56						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00021	HL
5578.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00006	CL
5579.	44	59						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
5580.		0.96		23	P2	AV2	0.00	TEHTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL
5581.	44	60						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
5582.	44	61						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
5583.	44	62						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
5584.	44	63						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
5585.	44	64						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
5586.								TEHTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: C
 DATABASE: Harris_SGC_1995

Sep. 23, 1995 14:28

PAGE 116 of 128

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG	
5587.	44	65						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL	
5588.	44	66						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL	
5589.	44	67						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL	
5590.	44	68						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL	
5591.	44	69						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL	
5592.								TEHTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL	
5593.	44	70						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL	
5594.	44	71						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL	
5595.	44	72						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL	
5596.	44	73						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL	
5597.	44	74						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL	
5598.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00006	CL	
5599.	44	75						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL	
5600.	44	76						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL	
5601.	44	77						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL	
5602.	44	78						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL	
5603.	44	79						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL	
5604.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00006	CL	
5605.	44	80						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL	
5606.	44	81						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL	
5607.	44	82						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00013	HL	
5608.	44	83						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00014	HL	
5609.	44	84						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00013	HL	
5610.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00004	CL	
5611.	44	85						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00014	HL	
5612.	44	86						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00013	HL	
5613.	44	87						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00014	HL	
5614.	44	88						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00013	HL	
5615.	44	89						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00014	HL	
5616.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00004	CL	
5617.	44	90						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00013	HL	
5618.	44	91						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00014	HL	
5619.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00004	CL	
5620.	44	92						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00013	HL	
5621.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00004	CL	
5622.	45	24						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL	
5623.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00008	CL	
5624.	45	25						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL	
5625.			5.55	181	DNT	P1	11C	-0.46	TEHTEC	P4202	rpri	A610MULC	SG30CCAL00008	CL
5626.	45	26							TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
5627.			7.89	178	DNT	P1	11C	-0.48	TEHTEC	N0698	rpri	A610MULC	SG30CCAL00008	CL
5628.	45	27							TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
5629.	45	28							TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
5630.	45	29							TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
5631.	45	30							TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
5632.	45	31							TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
5633.									TEHTEC	N0698	rpri	A610MULC	SG30CCAL00008	CL
5634.	45	32							TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
5635.	45	33							TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: C
 DATABASE: Harris_SGC_1995

Sep. 23,1995 14:28

PAGE 117 of 128

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
5636.	45	34						TSHTSH	S7067	rpri	B620MRPC3C	SG31HCAL00034	HL
5637.	45	35						TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
5638.	45	36						TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
5639.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL
5640.	45	37						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL
5641.	45	38						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00021	HL
5642.	45	39						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL
5643.	45	40						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00021	HL
5644.	45	41						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL
5645.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00006	CL
5646.	45	42						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00021	HL
5647.	45	43						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL
5648.	45	44						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00021	HL
5649.	45	45						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL
5650.	45	46						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00021	HL
5651.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00006	CL
5652.	45	47						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL
5653.	45	48						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00021	HL
5654.	45	49						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL
5655.	45	50						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00021	HL
5656.	45	51						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL
5657.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00006	CL
5658.	45	52						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00021	HL
5659.	45	53						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL
5660.	45	54						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00021	HL
5661.	45	55						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL
5662.	45	56						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00021	HL
5663.		1.59		35	P2	AV1	0.00	TEHTEC	P4202	rpri	A610MULC	SG30CCAL00006	CL
5664.		0.82		24	P2	AV4	0.00	TEHTEC	P4202	rpri	A610MULC	SG30CCAL00006	CL
5665.	45	60						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
5666.	45	61						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
5667.	45	62						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
5668.	45	63						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
5669.	45	64						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
5670.								TEHTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL
5671.	45	65						TSHTSH	J1978	rsec	B620MRPC3C	SG31HCAL00019	HL
5672.								TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
5673.	45	66						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
5674.	45	67						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
5675.	45	68						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
5676.	45	69						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
5677.								TEHTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL
5678.	45	70						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
5679.	45	71						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
5680.	45	72						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00021	HL
5681.	45	73						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00021	HL
5682.	45	74						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00021	HL
5683.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00006	CL
5684.	45	75						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00021	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: C
 DATABASE: Harris_SGC_1995

Sep. 23.1995 14:28

PAGE 118 of 128

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
5685.	45	76						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00021	HL
5686.	45	77						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00021	HL
5687.	45	78						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00021	HL
5688.	45	79						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00021	HL
5689.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00006	CL
5690.	45	80						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00021	HL
5691.	45	81						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00021	HL
5692.	45	82						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00013	HL
5693.	45	83						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00014	HL
5694.	45	84						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00013	HL
5695.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00004	CL
5696.	45	85						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00014	HL
5697.	45	86						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00013	HL
5698.	45	87						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00014	HL
5699.	45	88						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00013	HL
5700.	45	89						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00014	HL
5701.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00004	CL
5702.	45	90						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00013	HL
5703.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00004	CL
5704.	45	91						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00014	HL
'05.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00004	CL
5.	46	26						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
5707.		10.41	179	DNT	P1	11C	-0.46	TEHTEC	N0698	rpri	A610MULC	SG30CCAL00008	CL
5708.		10.51	178	DNT	P1	11C	0.27	TEHTEC	N0698	rpri	A610MULC	SG30CCAL00008	CL
5709.	46	27						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
5710.		19.39	178	DNT	P1	11C	0.27	TEHTEC	N0698	rpri	A610MULC	SG30CCAL00008	CL
5711.		10.31	179	DNT	P1	11C	0.27	TEHTEC	N0698	rpri	A610MULC	SG30CCAL00008	CL
5712.	46	28						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
5713.	46	29						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
5714.	46	30						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
5715.	46	31						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
5716.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00008	CL
5717.	46	32						TSHTSH	C7651	rsec	B620MRPC3C	SG31HCAL00032	HL
5718.	46	33						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
5719.	46	34						TSHTSH	S7067	rpri	B620MRPC3C	SG31HCAL00034	HL
5720.	46	35						TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
5721.	46	36						TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
5722.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL
5723.	46	37						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL
5724.	46	38						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00021	HL
5725.	46	39						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL
5726.	46	40						TSHTSH	D3858	reso	B620MRPC3C	SG31HCAL00021	HL
5727.	46	41						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL
5728.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00006	CL
5729.	46	42						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00021	HL
730.	46	43						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL
1.	46	44						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00021	HL
2.	46	45						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL
33.	46	46						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00021	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: C
 DATABASE: Harris_SGC_1995

Sep. 23.1995 14:28

PAGE 119 of 128

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
5734.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00006	CL
5735.	46	47						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL
5736.	46	48						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00021	HL
5737.	46	49						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL
5738.	46	50						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00021	HL
5739.	46	51						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL
5740.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00006	CL
5741.	46	52						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00021	HL
5742.	46	53						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL
5743.	46	54						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00021	HL
5744.	46	55						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL
5745.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00006	CL
5746.	46	56						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00021	HL
5747.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00006	CL
5748.	46	59						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
5749.		3.48		47	P2	AV2	0.00	TEHTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL
5750.				PID		AV2	0.00	TEHTEC	D4825	reso	A610MULC	SG30CCAL00013	CL
5751.		2.67		42	P2	AV3	0.00	TEHTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL
5752.				PID		AV3	0.00	TEHTEC	B3052	reso	A610MULC	SG30CCAL00013	CL
5753.		1.12		26	P2	AV4	0.00	TEHTEC	D3858	reso	A610MULC	SG30CCAL00005	CL
5754.	46	60						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
5755.								TEHTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL
5756.	46	61						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
5757.	46	62						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
5758.	46	63						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
5759.	46	64						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
5760.								TEHTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL
5761.	46	65						TSHTSH	J9815	rsec	B620MRPC3C	SG31HCAL00020	HL
5762.								TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
5763.	46	66						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
5764.	46	67						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
5765.	46	68						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
5766.	46	69						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
5767.								TEHTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL
5768.	46	70						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
5769.	46	71						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
5770.	46	72						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL
5771.	46	73						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL
5772.	46	74						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL
5773.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00006	CL
5774.	46	75						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL
5775.	46	76						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL
5776.	46	77						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL
5777.	46	78						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL
5778.	46	79						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL
5779.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00006	CL
5780.	46	80						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL
5781.	46	81						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL
5782.	46	82						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00013	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: C
 DATABASE: Harris_SGC_1995

Sep. 23.1995 14:28

PAGE 120 of 128

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG	
5783.	46	83						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00014	HL	
5784.	46	84						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00013	HL	
5785.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00004	CL	
5786.	46	85						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00014	HL	
5787.	46	86						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00013	HL	
5788.	46	87						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00014	HL	
5789.	46	88						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00013	HL	
5790.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00004	CL	
5791.	46	89						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00014	HL	
5792.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00004	CL	
5793.	47	27						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL	
5794.		11.60	179	DNT	P1	11C	-0.49	TEHTEC	N0698	rpri	A610MULC	SG30CCAL00008	CL	
5795.		13.36	180	DNT	P1	11C	0.24	TEHTEC	N0698	rpri	A610MULC	SG30CCAL00008	CL	
5796.	47	28						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL	
5797.		11.27	178	DNT	P1	11C	-0.43	TEHTEC	N0698	rpri	A610MULC	SG30CCAL00008	CL	
5798.		15.48	178	DNT	P1	11C	0.24	TEHTEC	N0698	rpri	A610MULC	SG30CCAL00008	CL	
5799.	47	29						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL	
5800.		8.50	178	DNT	P1	11C	-0.05	TEHTEC	N0698	rpri	A610MULC	SG30CCAL00008	CL	
5801.	47	30						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL	
5802.	47	31						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL	
5803.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00008	CL	
5804.	47	32						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL	
5805.	47	33						TSHTSH	S7067	rpri	B620MRPC3C	SG31HCAL00034	HL	
5806.	47	34						TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL	
5807.	47	35						TSHTSH	S7067	rpri	B620MRPC3C	SG31HCAL00034	HL	
5808.	47	36						TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL	
5809.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL	
5810.	47	37						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL	
5811.	47	38	3.86	91	PLP	11	TSH	0.37	TSHTSH	D3858	reso	B620MRPC3C	SG31HCAL00021	HL
5812.	47	39						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL	
5813.	47	40						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00021	HL	
5814.	47	41						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL	
5815.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00006	CL	
5816.	47	42						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00021	HL	
5817.	47	43						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL	
5818.	47	44						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00021	HL	
5819.	47	45						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL	
5820.	47	46						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00021	HL	
5821.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00006	CL	
5822.	47	47						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL	
5823.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00006	CL	
5824.	47	48						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00021	HL	
5825.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00006	CL	
5826.	47	49						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL	
5827.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00006	CL	
5828.	47	50						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00021	HL	
5829.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00006	CL	
5830.	47	51						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL	
5831.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00006	CL	

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: C
 DATABASE: Harris_SGC_1995

Sep. 23,1995 14:28

PAGE 121 of 128

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
5832.	47	52						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00021	HL
5833.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00006	CL
5834.								03C02C	S7675	rpri	B620MRPC3C	SG30CCAL00020	CL
5835.	47	53						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL
5836.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00006	CL
5837.	47	54						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00021	HL
5838.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00006	CL
5839.	47	55						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL
5840.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00006	CL
5841.								03C02C	S7675	rpri	B620MRPC3C	SG30CCAL00020	CL
5842.	47	56						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00021	HL
5843.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00006	CL
5844.	47	59						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
5845.		2.28		41	P2	AV1	0.00	TEHTEC	T6956	rsec	A610MULC	SG30CCAL00005	CL
5846.				PIO		AV1	0.00	TEHTEC	C1115	rsec	A610MULC	SG30CCAL00013	CL
5847.	47	60						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
5848.								TEHTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL
5849.								03C02C	S7675	rpri	B620MRPC3C	SG30CCAL00020	CL
5850.	47	61						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
5851.								TEHTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL
5852.	47	62						TSHTSH	D3858	reso	B620MRPC3C	SG31HCAL00019	HL
5853.								TEHTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL
5854.	47	63						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
5855.								TEHTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL
5856.								03C02C	S7675	rpri	B620MRPC3C	SG30CCAL00020	CL
5857.	47	64						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
5858.								TEHTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL
5859.	47	65						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
5860.								TEHTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL
5861.	47	67						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
5862.								TEHTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL
5863.	47	68						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
5864.								TEHTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL
5865.	47	69						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
5866.								TEHTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL
5867.	47	70						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
5868.	47	71						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00019	HL
5869.	47	72						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00021	HL
5870.	47	73						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00021	HL
5871.	47	74						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00021	HL
5872.		6.21	186	DNT	1	10H	37.80	TEHTEC	H1274	reso	A610MULC	SG30CCAL00006	CL
5873.		13.65	185	DNT	1	10H	38.29	TEHTEC	F3325	rsec	A610MULC	SG30CCAL00006	CL
5874.	47	75						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00021	HL
5875.	47	76						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00021	HL
5876.	47	77						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00021	HL
5877.	47	78						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00021	HL
5878.	47	79						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00021	HL
5879.								03H03H	T7072	rpri	B620MRPC3C	SG31HCAL00026	HL
5880.		13.31	179	DNT	P1	03H	0.32	TEHTEC	P4202	rpri	A610MULC	SG30CCAL00006	CL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: C
 DATABASE: Harris_SGC_1995

Sep. 23,1995 14:28

PAGE 122 of 128

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
5881.		5.70	177	DNT	P1	03H	1.24	TEHTEC	P4202	rpri	A610MULC	SG30CCAL00006	CL
5882.	47	80						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00021	HL
5883.	47	81						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00021	HL
5884.	47	82						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00013	HL
5885.	47	83						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00014	HL
5886.	47	84						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00013	HL
5887.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00004	CL
5888.	47	85						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00014	HL
5889.	47	86						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00013	HL
5890.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00004	CL
5891.	47	87						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00014	HL
5892.								TEHTEC	T6956	rsec	A610MULC	SG30CCAL00004	CL
5893.	47	88						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00013	HL
5894.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00004	CL
5895.	48	29						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
5896.								08H08H	T7072	rpri	B620MRPC3C	SG31HCAL00028	HL
5897.		76.47	177	DNT	1	08H	1.10	TEHTEC	H1274	reso	A610MULC	SG30CCAL00008	CL
5898.		5.30	182	DNT	1	11H	6.05	TEHTEC	H1274	reso	A610MULC	SG30CCAL00008	CL
5899.		10.29	179	DNT	1	11H	6.78	TEHTEC	H1274	reso	A610MULC	SG30CCAL00008	CL
5900.		7.59	181	DNT	P1	AV3	-0.05	TEHTEC	H1274	reso	A610MULC	SG30CCAL00008	CL
5901.		25.44	180	DNT	P1	11C	-0.22	TEHTEC	H1274	reso	A610MULC	SG30CCAL00008	CL
5902.		12.88	176	DNT	1	11C	0.60	TEHTEC	H1274	reso	A610MULC	SG30CCAL00008	CL
5903.		5.45	180	DNT	1	10C	31.26	TEHTEC	H1274	reso	A610MULC	SG30CCAL00008	CL
5904.		11.17	178	DNT	1	10C	32.62	TEHTEC	H1274	reso	A610MULC	SG30CCAL00008	CL
5905.		18.36	180	DNT	1	10C	33.38	TEHTEC	H1274	reso	A610MULC	SG30CCAL00008	CL
5906.		16.97	181	DNT	1	10C	37.78	TEHTEC	H1274	reso	A610MULC	SG30CCAL00008	CL
5907.		22.70	179	DNT	1	10C	38.57	TEHTEC	H1274	reso	A610MULC	SG30CCAL00008	CL
5908.		7.44	180	DNT	1	10C	39.52	TEHTEC	H1274	reso	A610MULC	SG30CCAL00008	CL
5909.	48	30						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
5910.								03C02C	S7675	rpri	B620MRPC3C	SG30CCAL00020	CL
5911.		9.49	181	DNT	P1	AV2	0.19	TEHTEC	N0698	rpri	A610MULC	SG30CCAL00008	CL
5912.		5.52	179	DNT	P1	11C	0.16	TEHTEC	N0698	rpri	A610MULC	SG30CCAL00008	CL
5913.	48	31						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
5914.		6.96	180	DNT	P1	11C	-0.11	TEHTEC	N0698	rpri	A610MULC	SG30CCAL00008	CL
5915.		5.71	181	DNT	P1	11C	0.63	TEHTEC	N0698	rpri	A610MULC	SG30CCAL00008	CL
5916.	48	32						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
5917.	48	33						TSHTSH	S7067	rpri	B620MRPC3C	SG31HCAL00034	HL
5918.	48	34						TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
5919.	48	35						TSHTSH	S7067	rpri	B620MRPC3C	SG31HCAL00034	HL
5920.	48	36						TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
5921.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL
5922.	48	37						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL
5923.	48	38						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00021	HL
5924.	48	39						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL
5925.	48	40						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00021	HL
5926.	48	41						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL
5927.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00006	CL
5928.	48	42						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00021	HL
5929.	48	43						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: C
 DATABASE: Harris_SGC_1995

Sep. 23.1995 14:28

PAGE 123 of 128

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG	
5930.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00006	CL	
5931.	48	44						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00021	HL	
5932.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00006	CL	
5933.	48	45						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL	
5934.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00006	CL	
5935.	48	46						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00021	HL	
5936.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00006	CL	
5937.	48	47						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL	
5938.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00006	CL	
5939.								03C02C	S7675	rpri	B620MRPC3C	SG30CCAL00020	CL	
5940.	48	48						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00021	HL	
5941.								TEHTSC	P4202	rpri	A610MULC	SG30CCAL00006	CL	
5942.								TEHTEC	05305	rpri	A610MULC	SG30CCAL00013	CL	
5943.	48	49						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL	
5944.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00006	CL	
5945.	48	50						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00021	HL	
5946.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00006	CL	
5947.	48	51						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL	
5948.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00006	CL	
5949.	48	52						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00021	HL	
5950.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00006	CL	
5951.	48	53						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL	
5952.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00006	CL	
5953.	48	54						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00021	HL	
5954.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00006	CL	
5955.	48	55						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL	
5956.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00006	CL	
5957.	48	56						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00021	HL	
5958.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00006	CL	
5959.	48	59						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL	
5960.		0.53		14	P2	AV1	-0.03	TEHTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL	
5961.		0.31		8	P2	AV2	0.00	TEHTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL	
5962.	48	60						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL	
5963.								TEHTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL	
5964.	48	61						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL	
5965.								TEHTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL	
5966.	48	62						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL	
5967.								TEHTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL	
5968.	48	63						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL	
5969.								TEHTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL	
5970.	48	64						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL	
5971.		0.34	127		NQI	1	TSC	1.83	TEHTEC	T6956	rsec	A610MULC	SG30CCAL00005	CL
5972.					DMR	1	TSC	1.83	01CTSC	D3858	reso	B620MRPC3C	SG30CCAL00020	CL
5973.	48	65						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL	
5974.								TEHTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL	
5975.	48	66						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL	
5976.								TEHTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL	
5977.	48	67						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL	
5978.								TEHTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL	

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: C
 DATABASE: Harris_SGC_1995

Sep. 23.1995 14:28

PAGE 124 of 128

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
5979.								03C02C	S7675	rpri	B620MRPC3C	SG30CCAL00020	CL
5980.	48	68						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
5981.								TEHTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL
5982.	48	69						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
5983.								TEHTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL
5984.	48	70						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
5985.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00006	CL
5986.	48	71						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00020	HL
5987.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00006	CL
5988.	48	72						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL
5989.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00006	CL
5990.	48	73						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL
5991.	48	74						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL
5992.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00006	CL
5993.	48	75						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL
5994.	48	76						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL
5995.	48	77						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL
5996.	48	78						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL
5997.								03H03H	T7072	rpri	B620MRPC3C	SG31HCAL00026	HL
5998.	48	79						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL
5999.								11H11H	T7072	rpri	B620MRPC3C	SG31HCAL00026	HL
6000.								03H03H	T7072	rpri	B620MRPC3C	SG31HCAL00026	HL
6001.		8.19	180	DNT	P1	03H	0.37	TEHTEC	P4202	rpri	A610MULC	SG30CCAL00006	CL
6002.		7.80	180	DNT	P1	11H	-0.46	TEHTEC	P4202	rpri	A610MULC	SG30CCAL00006	CL
6003.		5.17	180	DNT	P1	11H	0.24	TEHTEC	P4202	rpri	A610MULC	SG30CCAL00006	CL
6004.	48	80						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL
6005.	48	81						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL
6006.	48	82						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00013	HL
6007.	48	83						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00014	HL
6008.					RBD				F9284	rpri	B620MRPC3C	SG31HCAL00023	HL
6009.								11H11H	T7072	rpri	B620MRPC3C	SG31HCAL00025	HL
6010.	48	84						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00013	HL
6011.		5.32	178	DNT	P1	11C	-0.35	TEHTEC	N0698	rpri	A610MULC	SG30CCAL00004	CL
6012.	48	85						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00014	HL
6013.								03C02C	S7675	rpri	B620MRPC3C	SG30CCAL00020	CL
6014.		5.50	182	DNT	P1	11H	-0.27	TEHTEC	N0698	rpri	A610MULC	SG30CCAL00004	CL
6015.		8.76	183	DNT	P1	AV2	0.22	TEHTEC	N0698	rpri	A610MULC	SG30CCAL00004	CL
6016.		10.21	179	DNT	P1	11C	-0.46	TEHTEC	N0698	rpri	A610MULC	SG30CCAL00004	CL
6017.		10.61	179	DNT	P1	11C	0.19	TEHTEC	N0698	rpri	A610MULC	SG30CCAL00004	CL
6018.		8.48	182	DNT	1	10C	36.17	TEHTEC	N0698	rpri	A610MULC	SG30CCAL00004	CL
6019.	48	86						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00013	HL
6020.								11H11H	T7072	rpri	B620MRPC3C	SG31HCAL00025	HL
6021.		15.55	183	DNT	1	10H	39.89	TEHTEC	N0698	rpri	A610MULC	SG30CCAL00004	CL
6022.		34.11	180	DNT	1	10H	40.58	TEHTEC	N0698	rpri	A610MULC	SG30CCAL00004	CL
6023.		8.29	183	DNT	1	10H	41.16	TEHTEC	N0698	rpri	A610MULC	SG30CCAL00004	CL
6024.		11.52	181	DNT	P1	11H	1.11	TEHTEC	N0698	rpri	A610MULC	SG30CCAL00004	CL
6025.		14.24	182	DNT	P1	11H	1.87	TEHTEC	N0698	rpri	A610MULC	SG30CCAL00004	CL
6026.		7.73	181	DNT	P1	11C	-0.14	TEHTEC	N0698	rpri	A610MULC	SG30CCAL00004	CL
6027.		9.26	178	DNT	P1	11C	0.60	TEHTEC	N0698	rpri	A610MULC	SG30CCAL00004	CL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: C
 DATABASE: Harris_SGC_1995

Sep. 23.1995 14:28

PAGE 125 of 128

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
6028.	49	31						TSHTSH	P4202	rpri	B620MRPC3C	SG31HCAL00032	HL
6029.								08H08H	T7072	rpri	B620MRPC3C	SG31HCAL00026	HL
6030.		11.96	177	DNT	P1	08H	0.78	TEHTEC	N0698	rpri	A610MULC	SG30CCAL00008	CL
6031.		15.73	178	DNT	P1	11C	-0.05	TEHTEC	N0698	rpri	A610MULC	SG30CCAL00008	CL
6032.		17.27	178	DNT	P1	11C	0.65	TEHTEC	N0698	rpri	A610MULC	SG30CCAL00008	CL
6033.	49	32						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00033	HL
6034.		10.21	179	DNT	P1	11C	-0.51	TEHTEC	N0698	rpri	A610MULC	SG30CCAL00008	CL
6035.		14.15	179	DNT	P1	11C	0.22	TEHTEC	N0698	rpri	A610MULC	SG30CCAL00008	CL
6036.	49	33						TSHTSH	S7067	rpri	B620MRPC3C	SG31HCAL00034	HL
6037.		11.17	179	DNT	P1	11C	-0.49	TEHTEC	N0698	rpri	A610MULC	SG30CCAL00008	CL
6038.		10.67	178	DNT	P1	11C	0.27	TEHTEC	N0698	rpri	A610MULC	SG30CCAL00008	CL
6039.	49	34						TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
6040.		0.43		12	P2	AV2	0.24	TEHTEC	N0698	rpri	A610MULC	SG30CCAL00008	CL
6041.		14.00	179	DNT	P1	11C	-0.43	TEHTEC	N0698	rpri	A610MULC	SG30CCAL00008	CL
6042.		15.13	178	DNT	P1	11C	0.24	TEHTEC	N0698	rpri	A610MULC	SG30CCAL00008	CL
6043.	49	35						TSHTSH	S7067	rpri	B620MRPC3C	SG31HCAL00034	HL
6044.								TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL
6045.	49	36						TSHTSH	T9924	rpri	B620MRPC3C	SG31HCAL00035	HL
6046.		6.41	181	DNT	1	10H	27.43	TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL
6047.		15.56	181	DNT	1	10H	28.21	TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL
48.		6.00	182	DNT	1	10H	36.95	TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL
49.		24.21	178	DNT	P1	11C	-0.32	TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL
50.		24.37	178	DNT	P1	11C	0.46	TEHTEC	N0698	rpri	A610MULC	SG30CCAL00009	CL
6051.	49	37						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL
6052.								03C02C	S7675	rpri	B620MRPC3C	SG30CCAL00020	CL
6053.		7.31	180	DNT	P1	11C	-0.33	TEHTEC	P4202	rpri	A610MULC	SG30CCAL00006	CL
6054.		7.78	180	DNT	P1	11C	0.41	TEHTEC	P4202	rpri	A610MULC	SG30CCAL00006	CL
6055.	49	38						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00021	HL
6056.		7.99	182	DNT	1	10H	35.58	TEHTEC	P4202	rpri	A610MULC	SG30CCAL00006	CL
6057.		11.49	183	DNT	1	10H	36.29	TEHTEC	P4202	rpri	A610MULC	SG30CCAL00006	CL
6058.		8.25	180	DNT	P1	11C	-0.49	TEHTEC	P4202	rpri	A610MULC	SG30CCAL00006	CL
6059.		9.42	177	DNT	P1	11C	0.24	TEHTEC	P4202	rpri	A610MULC	SG30CCAL00006	CL
6060.	49	39						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL
6061.		9.64	180	DNT	P1	11C	-0.03	TEHTEC	P4202	rpri	A610MULC	SG30CCAL00006	CL
6062.		8.51	180	DNT	P1	11C	0.68	TEHTEC	P4202	rpri	A610MULC	SG30CCAL00006	CL
6063.	49	40						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00021	HL
6064.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00006	CL
6065.								03C02C	S7675	rpri	B620MRPC3C	SG30CCAL00020	CL
6066.	49	41						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL
6067.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00006	CL
6068.	49	42						TEHTEC	P4202	rpri	A610MULC	SG30CCAL00006	CL
6069.		4.69	90	PLP	11	TSH	0.51	TSHTSH	D3858	reso	B620MRPC3C	SG31HCAL00021	HL
6070.	49	43						TEHTEC	P4202	rpri	A610MULC	SG30CCAL00006	CL
6071.								03C02C	S7675	rpri	B620MRPC3C	SG30CCAL00020	CL
6072.		5.53	89	PLP	11	TSH	0.54	TSHTSH	D3858	reso	B620MRPC3C	SG31HCAL00022	HL
6073.	49	44						TSHTSH	D3858	reso	B620MRPC3C	SG31HCAL00021	HL
6074.		6.37	181	DNT	1	AV4	-0.87	TEHTEC	P4202	rpri	A610MULC	SG30CCAL00006	CL
6075.	49	45						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL
6076.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00006	CL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: C
 DATABASE: Harris_SGC_1995

Sep. 23.1995 14:28

PAGE 126 of 128

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG	
6077.	49	46						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00021	HL	
6078.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00006	CL	
6079.								03C02C	S7675	rpri	B620MRPC3C	SG30CCAL00020	CL	
6080.	49	47						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL	
6081.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00006	CL	
6082.	49	48						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00021	HL	
6083.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00006	CL	
6084.	49	49						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL	
6085.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00006	CL	
6086.								03C02C	S7675	rpri	B620MRPC3C	SG30CCAL00020	CL	
6087.	49	50						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00021	HL	
6088.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00006	CL	
6089.	49	51						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL	
6090.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00006	CL	
6091.	49	52						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00021	HL	
6092.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00006	CL	
6093.								03C02C	S7675	rpri	B620MRPC3C	SG30CCAL00020	CL	
6094.	49	53						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL	
6095.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00006	CL	
6096.	49	54						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00021	HL	
6097.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00006	CL	
6098.	49	55						TEHTEC	P4202	rpri	A610MULC	SG30CCAL00006	CL	
6099.								03C02C	S7675	rpri	B620MRPC3C	SG30CCAL00020	CL	
6100.		7.23	90	PLP	11	TSH	0.39	TSHTSH	D3858	reso	B620MRPC3C	SG31HCAL00022	HL	
6101.	49	56	5.12	93	PLP	11	TSH	0.33	TSHTSH	D3858	reso	B620MRPC3C	SG31HCAL00021	HL
6102.		6.69	186	DNT	1	AV4	1.40	TEHTEC	F3325	rsec	A610MULC	SG30CCAL00006	CL	
6103.	49	59						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL	
6104.		6.86	179	DNT	1	AV4	1.09	TEHTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL	
6105.		8.77	179	DNT	1	TSC	3.65	TEHTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL	
6106.	49	60						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL	
6107.								TEHTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL	
6108.								03C02C	S7675	rpri	B620MRPC3C	SG30CCAL00020	CL	
6109.	49	61						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL	
6110.								TEHTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL	
6111.	49	62						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL	
6112.								TEHTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL	
6113.	49	63						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL	
6114.								TEHTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL	
6115.								03C02C	S7675	rpri	B620MRPC3C	SG30CCAL00020	CL	
6116.	49	64						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL	
6117.								TEHTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL	
6118.	49	65						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL	
6119.								TEHTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL	
6120.	49	66						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL	
6121.								TEHTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL	
6122.								03C02C	S7675	rpri	B620MRPC3C	SG30CCAL00020	CL	
6123.	49	67						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL	
6124.		0.40		14	P2	07C	-0.32	TEHTEC	D3858	reso	A610MULC	SG30CCAL00005	CL	
6125.	49	68						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL	

*** INSPECTION FINAL REPORT LISTING ***

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: C
 DATABASE: Harris_SGC_1995

Sep. 23, 1995 14:28

PAGE 127 of 128

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
6126.								TEHTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL
6127.	49	69						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL
6128.								03C02C	S7675	rpri	B620MRPC3C	SG30CCAL00020	CL
6129.		8.48	179	DNT	1	10H	40.89	TEHTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL
6130.		17.79	179	DNT	1	10H	41.56	TEHTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL
6131.		5.83	182	DNT	1	10H	42.17	TEHTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL
6132.		8.57	181	DNT	1	11H	-0.93	TEHTEC	C3335	rpri	A610MULC	SG30CCAL00005	CL
6133.	49	70						TEHTEC	P4202	rpri	A610MULC	SG30CCAL00006	CL
6134.		3.45	88	PLP	11	TSH	0.61	TSHTSH	D3858	reso	B620MRPC3C	SG31HCAL00022	HL
6135.	49	71						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL
6136.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00006	CL
6137.	49	72						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL
6138.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00006	CL
6139.								03C02C	S7675	rpri	B620MRPC3C	SG30CCAL00020	CL
6140.	49	73						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL
6141.								11H11H	T7072	rpri	B620MRPC3C	SG31HCAL00026	HL
6142.		5.07	188	DNT	P1	11H	-0.35	TEHTEC	H1274	reso	A610MULC	SG30CCAL00006	CL
6143.	49	74						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL
6144.		5.76	184	DNT	1	01C	5.08	TEHTEC	H1274	reso	A610MULC	SG30CCAL00006	CL
6145.		6.59	184	DNT	1	01C	5.80	TEHTEC	H1274	reso	A610MULC	SG30CCAL00006	CL
46.	49	75						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL
47.								11H11H	T7072	rpri	B620MRPC3C	SG31HCAL00026	HL
6148.								03C02C	S7675	rpri	B620MRPC3C	SG30CCAL00020	CL
6149.		5.06	180	DNT	P1	11H	-0.43	TEHTEC	P4202	rpri	A610MULC	SG30CCAL00006	CL
6150.		6.10	181	DNT	P1	11H	0.45	TEHTEC	P4202	rpri	A610MULC	SG30CCAL00006	CL
6151.	49	76						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL
6152.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00006	CL
6153.	49	77						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL
6154.								11H10H	T7072	rpri	B620MRPC3C	SG31HCAL00026	HL
6155.		6.33	182	DNT	1	10H	36.86	TEHTEC	P4202	rpri	A610MULC	SG30CCAL00006	CL
6156.		11.83	182	DNT	1	10H	37.62	TEHTEC	P4202	rpri	A610MULC	SG30CCAL00006	CL
6157.		7.86	179	DNT	P1	11H	-0.38	TEHTEC	P4202	rpri	A610MULC	SG30CCAL00006	CL
6158.		5.02	179	DNT	P1	11C	-0.38	TEHTEC	P4202	rpri	A610MULC	SG30CCAL00006	CL
6159.		5.55	179	DNT	P1	11C	0.27	TEHTEC	P4202	rpri	A610MULC	SG30CCAL00006	CL
6160.	49	78						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL
6161.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00006	CL
6162.								03C02C	S7675	rpri	B620MRPC3C	SG30CCAL00020	CL
6163.	49	79						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL
6164.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00006	CL
6165.	49	80						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL
6166.		10.48	178	DNT	P1	11H	-0.38	TEHTEC	P4202	rpri	A610MULC	SG30CCAL00006	CL
6167.		6.78	180	DNT	P1	11H	0.46	TEHTEC	P4202	rpri	A610MULC	SG30CCAL00006	CL
6168.		17.05	179	DNT	P1	11C	-0.46	TEHTEC	P4202	rpri	A610MULC	SG30CCAL00006	CL
6169.		5.88	179	DNT	P1	11C	0.24	TEHTEC	P4202	rpri	A610MULC	SG30CCAL00006	CL
6170.		6.72	182	DNT	1	10C	23.49	TEHTEC	P4202	rpri	A610MULC	SG30CCAL00006	CL
6171.		6.02	179	DNT	P1	10C	41.79	TEHTEC	P4202	rpri	A610MULC	SG30CCAL00006	CL
6172.	49	81						TSHTSH	F9284	rpri	B620MRPC3C	SG31HCAL00022	HL
6173.								TEHTEC	P4202	rpri	A610MULC	SG30CCAL00006	CL
6174.								03C02C	S7675	rpri	B620MRPC3C	SG30CCAL00020	CL

**** INSPECTION FINAL REPORT LISTING ****

UTILITY: Carolina Power & Light
 PLANT: Shearon Harris
 UNIT: 1
 SG: C
 DATABASE: Harris_SGC_1995

Sep, 23, 1995 14:28

PAGE 128 of 128

ROW	COLUMN	VOLTS	DEG	PCT	CHAN	LOCATION	ELEVATION	EXTENT	NAME	TYPE	PROBE SIZE	CAL GROUP	LEG
6175.	49	82						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00013	HL
6176.		9.03	179	DNT	P1	11H	-0.33	TEHTEC	N0698	rpri	A610MULC	SG30CCAL00004	CL
6177.		6.49	180	DNT	P1	11H	0.46	TEHTEC	N0698	rpri	A610MULC	SG30CCAL00004	CL
6178.		9.74	175	DNT	P1	11C	-0.43	TEHTEC	N0698	rpri	A610MULC	SG30CCAL00004	CL
6179.		5.15	178	DNT	P1	11C	0.24	TEHTEC	N0698	rpri	A610MULC	SG30CCAL00004	CL
6180.	49	83						TSHTSH	B5534	rpri	B620MRPC3C	SG31HCAL00014	HL
6181.		5.04	177	DNT	P1	AV3	0.00	TEHTEC	H1274	reso	A610MULC	SG30CCAL00004	CL
6182.		12.44	176	DNT	P1	11C	0.14	TEHTEC	N0698	rpri	A610MULC	SG30CCAL00004	CL
6183.		16.09	177	DNT	P1	11C	0.97	TEHTEC	N0698	rpri	A610MULC	SG30CCAL00004	CL
6184.	49	84						TSHTSH	T7072	rpri	B620MRPC3C	SG31HCAL00013	HL
6185.		5.48	179	DNT	P1	11H	-0.33	TEHTEC	N0698	rpri	A610MULC	SG30CCAL00004	CL
6186.		7.42	181	DNT	1	AV1	0.90	TEHTEC	N0698	rpri	A610MULC	SG30CCAL00004	CL

ABB Combustion Engineering		Multi-Frequency Eddy Current Calibration Data Sheet		Disk #	Side
Owner: CP&L		Site/Unit: SHEARON HARRIS	Component: S/G: A / B <u>(C)</u>	Leg: <u>(HOT)</u> / COLD	Date: 9/19/95
MIZ-18A / MIZ-30 S/N- 094		Procedure: HNP-004 RO	Defect Std. (1) Z-14093	Additional Std. (2) N/A	
Cal	Date	Row Line	Standard Run	Comments	Examiner Init/Level
	Time				
01	9/19/95 0542	21/38	START CAL <u>VOID LTP 9/19/95</u>	ZONE 1	JH/IFA
3	9/19/95 1014	21/38	START CAL	ZONE 1	JH/IFA
003	9-19-95 1247	22/45	END CAL	Zone 1	JH/IFA
005	9-19-95 1257	12/37	START CAL	Zone 2	JH/IFA
005	9-19-95 1635	16/52	END CAL	Zone 2	JH/IFA
007	9/19/95 1646	18/52	BEG CAL	Zone 2	JH/IFA
007	9/19/95 2008	10/56	END CAL	ZONE ^{JH 9/19/95} 3	JH/IFA
9/19/95 008 009	9/19/95 2033	1/94	START CAL	ZONE 4	JH/IFA
009	9/20/95 0024	12/104	END CAL	ZONE 6	JH/IFA
011	9/20/95 0039	13/104	START CAL	ZONE 6	JH/IFA
9/20/95 011	9/20/95 0428	25/106	END CAL	ZONE 7	JH/IFA
Additional Comments:					
Shift Supervisor Final Review of Acceptance					
Reviewed by: <u>Amel G. Alweil</u> Level <u>II</u>					
Approved by: _____ ET Level III					

ABB Combustion Engineering		Multi-Frequency Eddy Current Calibration Data Sheet			Disk #		Side		
Owner: CP&L		Site/Unit: SHEARON HARRIS		Component: SIG: A / B (C)		Leg: (HOT) / COLD		Date: 9/20/95	
MIZ-18A / MIZ-30 S/N- 094			Procedure: HNP-004 RO		Defect Std. (1) Z-14093		Additional Std. (2) N/A		
Cal	Date	Row Line	Standard Run		Comments	Examiner			
	Time					Init/Level			
013	9/20/95	26/106	START CAL			JHP/JFA			
	0500								
013	9/20/95	36/86	End Cal			JHP/JFA			
	0846								
015	9/20/95	37/86	Start Cal			JHP/JFA			
	0908								
015	9/20/95	18/78	Probe died			JHP/JFA			
017	9/20/95	20/78	Start Cal			JHP/JFA			
	1411								
017	9/20/95	2/88	End Cal			JHP/JFA			
	1906								
019	9/20/95	4/88	Start Cal			JHP/JFA			
	1851								
019	9/20/95	47/71	END CAL			JHP/JFA			
	2237								
021	9/20/95	41/72	START CAL			JHP/JFA			
	2246								
021	9/21/95	49/56	END CAL			JHP/JFA			
	0232								
Additional Comments:									
Shift Supervisor Final Review of Acceptance									
Reviewed by: <u>And S Above</u> Level <u>II</u>									
Approved by: _____ ET Level III									

ABB Combustion Engineering		Multi-Frequency Eddy Current Calibration Data Sheet		Disk #	Side
Owner: CP&L		Site/Unit: SHEARON HARRIS	Component: S/G: A / B (C)	Leg: (HOT) / COLD	Date: 9/20/95
MIZ-18A / MIZ-30 S/N- 094		Procedure: HNP-004 RO	Defect Std. (1) 2-14094	Additional Std. (2) N/A	
Cal	Date	Row Line	Standard Run	Comments	Examiner
	Time				Init/Level
014	9/20/95 0457	26/107	START CAL		JH/IA
014	9/20/95 0845	36/87	End Cal		LJP/IA
016	9/20/95 0908	37/87	Start Cal		LJP/IA
016	9/20/95	19/78	Probe died		LJP/IA
018	9/20/95 1411	11/79	Start Cal		LJP/IA
018	9/20/95 1806	1/88	End Cal		LJP/IA
020	9/20/95 1851	3/88	Start Cal		JH/IA
020	9/20/95 2240	49/71	END CAL		JH/IA
022	9/20/95 2249	42/72	START CAL		JH/IA
022	9/21/95 0232	49/55	END CAL		JH/IA
Additional Comments:					
Shift Supervisor Final Review of Acceptance					
Reviewed by: <u>Ami C. Alcock</u> Level <u>II</u>					
Approved by: _____ ET Level III					

ABB Combustion Engineering		Multi-Frequency Eddy Current Calibration Data Sheet		Disk #	Side
Owner: CP&L		Site/Unit: SHEARON HARRIS	Component: S/G: A / B / C	Leg: (HOT) / COLD	Date: 9/21/95
MIZ-18A / MIZ-30 S/N- 024		Procedure: HNP-004 RO	Defect Std. (1) Z-14093	Additional Std. (2)	
Cal	Date	Row Line	Standard Run	Comments	Examiner
	Time				Init/Level
023	9/21/95 0248	31/38	START CAL		JA JA
025	9/21/95 0619	94 9/21/95		(JA) 9/21/95	JA
023	9/21/95 0549	3/39	END CAL		JA JA
025	9/21/95 0619	48/83	START CAL		JA JA
025	9-21-95 8:19	48/86	END CAL		DLP II
026	9-21-95 0826	28/84	START CAL		DLP II
026	9-21-95 1233	49/31	END CAL	CAL late due to conduit problem	DLP II
027	9-21-95 1237	38-16	START CAL		DLP II
027	9-21-95 1328	34-64	END CAL		DLP II
028	9-21-95 1338	48/29	START CAL	.590 3-coil	DLP II
028	9-21-95 1400	48/29	END CAL	"	DLP II
Additional Comments:					
Shift Supervisor Final Review of Acceptance					
Reviewed by: <u>David G. [Signature]</u> Level <u>II</u>					
Approved by: _____ ET Level III					

ABB Combustion Engineering		Multi-Frequency Eddy Current Calibration Data Sheet		Disk #		Side	
Owner: CP&L		Site/Unit: SHEARON HARRIS		Component: S/G: A / B <u>C</u>		Log: <u>HOT</u> COLD	
MIZ-18A / MIZ-30 S/N- <u>094</u>		Procedure: HNP-004 RO		Defect Std. (1) <u>Z-1A093</u>		Additional Std. (2)	
Cal	Date	Row Line	Standard Run	Comments	Examiner		
	Time				Init/Level		
031	9/21/95	26/59	START CAL	ZONE 18 19	1/1/FA		
	2128						
031	9/22/95	16/67	END CAL	ZONE 20	1/1/FA		
	0031						
033	9/22/95	18/67	START CAL		1/1/FA		
	0140						
033	9/22/95	42/34	END CAL		1/1/FA		
	0525						
035	9/22/95	44/34	START CAL		1/1/FA		
	0533						
035	9/22/95	27 28/13 <i>1/1/FA</i>	End Cal ^{TOP 2/24/95} Probe diled		TOP IIA		
037	9/22/95	28/13	Start Cal		TOP IIA		
	0946						
037	9/22/95	23/11	End Cal		TOP IIA		
	1311						
039	9/22/95	12/20	Start Cal		TOP IIA		
	1402						
039	9/22/95	14/23	End Cal		TOP IIA		
	1423						
041	9/22/95	16/23	Start Cal		TOP IIA		
	1639						
Additional Comments:							
Shift Supervisor Final Review of Acceptance							
Reviewed by: <u>Aurel A. Shved</u> Level <u>IF</u>							
Approved by: _____ ET Level III							

ABB Combustion Engineering		Multi-Frequency Eddy Current Calibration Data Sheet		Disk #	Side
Owner: CP&L		Site/Unit: SHEARON HARRIS	Component: S/G: A / B / C	Leg: HOT / COLD	Date: 9/21/95
MIZ-18A / MIZ-30 S/N- 094		Procedure: HNP-004 RO	Defect Std. (1) 2-14094	Additional Std. (2)	
Cal	Date	Row Line	Standard Run	Comments	Examiner
	Time				Init/Level
030	9/21/95 2128	25/59	START CAL	ZONE 18	JH/IIA
030	9/22/95 0032	15/67	END CAL		JH/IIA
032	9/22/95 0140	17/67	START CAL		JH/IIA
032	9/22/95 0523	42/33	END CAL		JH/IIA
034	9/22/95 0533	44/33	START CAL		JH/IIA
034	9/22/95 0921	29/12	End Cal		JH/IIA
036	9/22/95 0946	30/12	Start Cal		JH/IIA
036	9/22/95	11/20 ²⁸⁻³⁵	Motor Unit died No cal out		JH/IIA
038	9/22/95 1402	11-20	Start Cal		JH/IIA
038	9/22/95 1423	13-23	End Cal		JH/IIA
040	9/22/95 1639	15-23	START CAL		JH/IIA
Additional Comments:					
Shift Supervisor Final Review of Acceptance					
Reviewed by: <u>Amel A. Alwadi</u> Level <u>II</u>					
Approved by: _____ ET Level III					

ABB Combustion Engineering		Multi-Frequency Eddy Current Calibration Data Sheet			Disk #		Side		
Owner: CP&L		Site/Unit: SHEARON HARRIS		Component: SIG: A / B (C)		Log: HOT / (COLD)		Date: 7/18/95	
MIZ-18A / MIZ-30 S/N- 072		Procedure: HNP-004 RO			Defect Std. (1) Z-9047 Z-9052		Additional Std. (2) AUB Z-9052		
Cal	Date	Row	Line	Standard Run		Comments	Examiner		
	Time						Init/Level		
001	9/18	21-44		START CAL			TE II		
	7B:40								
0001	9-19-95	11-56		END CAL			TE II		
	0258								
002	9-19-95	1-37		START CAL			TE II		
	0301								
002	9-19-95	2-104		END CAL		4hr. cal late due to loss of building power	DLP II		
	0735								
003	9-19-95	3-104		START CAL			DLP II		
	0738								
003	9-19-95	28-105		END CAL			DLP II		
	1136								
004	9-19-95	27-106		START CAL			DLP II		
	1139								
004	9-19-95	14-77		END CAL			DLP II		
	1534								
005	9-19-95	1-77		START CAL			DLP II		
	1543								
005	9-19-95	49-69		END CAL			KGT II		
	19:40								
006	7-19-95	48-70		START CAL			TSE II		
	20:30								
Additional Comments:									
Shift Supervisor Final Review of Acceptance									
Reviewed by: <u>David G. Alworth</u> Level <u>4</u>									
Approved by: _____ ET Level III									

ABB Combustion Engineering	Multi-Frequency Eddy Current Calibration Data Sheet	Disk #	Side
--------------------------------------	--	--------	------

Owner: CP&L	Site/Unit: SHEARON HARRIS	Component: S/G: A / B (C)	Leg: HOT (COLD)	Date: 9-19-95
---------------------------	-------------------------------------	-------------------------------------	---------------------------	-------------------------

MIZ-18A MIZ-30 STN- 072	Procedure: HNP-004 R0	Defect Std. (1) Z-9047	Additional Std. (2) Z-9052
---	---------------------------------	----------------------------------	--------------------------------------

Cal	Date	Row Line	Standard Run	Comments	Examiner
	Time				Init/Level
006	9-19-95 2353	31-56	END CAL		R&B/II
007	9-20-95 0028	33-43	START CAL		TE II
007	9-20-95 0252	20-59	END CAL		TE II
008	9-20-95 0316	20-64	START CAL		TE II
008	9-20-95 07:07	49-34	END CAL		R.D.M. TE I
009	9-20-95 0719	49-35	START CAL		R.D.M. TE I
009	9-20-95 10:55	29-29	END CAL		R.D.M. TE I
010	9-20-95 10:56	11-21	START CAL.		LRO TE II
010	9-20-95 1347	2-26	END CAL.		LRO TE II
011	9-20-95 1400	10-26	START CAL		RDM TE I
011	9-20-95 17:29	11-26	END CAL		GAF

Additional Comments:

Shift Supervisor Final Review of Acceptance

Reviewed by: April A. Shubert Level II

Approved by: _____ ET Level III

LRO
9-20-95

ABB Combustion Engineering		Multi-Frequency Eddy Current Calibration Data Sheet			Disk #		Side		
Owner: CP&L		Site/Unit: SHEARON HARRIS		Component: SIG: A/B (C)		Leg: HOT (COLD)		Date: 9/20/95	
MIZ-18A / MIZ-30 S/N: 72			Procedure: HNP-004 RO		Defect Std. (1) 9041 2-9052		Additional Std. (2) 2-9052		
Cal	Date		Row Line	Standard Run		Comments	Examiner		
	Time						Init/Level		
0012	9/20/95 1729		2-1	START CAL			JRC II		
0012	9-20-95 1948		1-19	END CAL			JRC II		
0013	9-20 1950		31-56	START CAL			JRC II		
0013	9-20-95 1950		47-59	END CAL			JRC II		
2227 ← 0014	9-20-95 2243		1-16	START CAL			JRC II		
214	9-20-95 2354			END CAL			JRC II		
0015	9-21-95 0108			START CAL			JRC II		
0015	9-21-95 0355			END CAL			JRC II		
0016	9-21-95 0529			START CAL			JRC II		
0016	9-21-95 9:13			END CAL			R.D.M. I		
0017	9-21-95 12:17		2-18	START CAL			R.D.M. I		
Additional Comments:									
Shift Supervisor Final Review of Acceptance									
Reviewed by: <u>David G. Alford</u> Level <u>II</u>									
Approved by: _____ ET Level III									

ABB Combustion Engineering		Multi-Frequency Eddy Current Calibration Data Sheet			Disk #	Side
Owner: CP&L		Site/Unit: SHEARON HARRIS	Component: S/G: A / B (C)		Leg: HOT (COLD)	Date: 9/21/95
MIZ-18A / MIZ-30 S/N- 72		Procedure: HNP-004 R0		Defect Std. (1) Z-9047	Additional Std. (2) Z-9052	
Cal	Date	Row Line	Standard Run	Comments	Examiner	
	Time				Init/Level	
0017	9-21-95 1611	2-80	END CAL.		LJC	
0018	9-21-95 1618		START CAL.			
0018	9-21-95 1835	2-62	END CAL		R.D.M. I	
0019	9-21-95 1952	1-77	START CAL		JRC II	
0019	9-22-95 00:30	49-34	END CAL		KAT II	
0020	9-22-95 02:28	49-37	START CAL MRPC	Pre Heater Exp Tube	WAB II	
0020	9-22-95 4:38	48-64	END CALL	(1) S I Tube Pre Heater Exp Tube	WAB II	
0021	9-22-95 5:29	5-17	Dents MRPC		WAB II	
0021	9-22-95 6:06	21-110	Dents MRPC		WAB WAB	
0022	9-22-95 0903	2-77 1-78 1-74	START CAL U-BEND RETEST		WAB II	
0022	9-22-95 0952	2-77 1-78 1-74	END CAL U-BEND RETEST		WAB II	
Additional Comments:						
Shift Supervisor Final Review of Acceptance						
Reviewed by: <u>Amel A. Shoud</u> Level <u>II</u>						
Approved by: _____ ET Level III						

2238

TE II

