



M. CHRISTOPHER NOLAN
Vice President

Nuclear Regulatory Affairs, Policy &
Emergency Preparedness
526 South Church Street, EC-07C
Charlotte, NC 28202
980-382-7426
Chris.Nolan@duke-energy.com

May 9, 2019

Serial: RA-19-0104

10 CFR 50.55a(g)(5)(iii)

U.S. Nuclear Regulatory Commission
ATTN: Document Control Desk
Washington, DC 20555-0001

Subject: Brunswick Steam Electric Plant, Unit Nos. 1 and 2
Renewed Facility Operating License Nos. DPR-71 and DPR-62
Docket Nos. 50-325 and 50-324
Proposed Alternative for the Fourth 10-Year Inservice Inspection Program

Reference: Letter from Randy C. Ivey (Progress Energy) to the U.S. Nuclear Regulatory Commission, *Inservice Inspection Plan for the Fourth 10-Year Inspection Interval*, dated May 21, 2008, ADAMS Accession Number ML081500243.

Ladies and Gentlemen:

By letter dated May 21, 2008 (i.e., Reference), Duke Energy Progress, LLC (Duke Energy), submitted the Inservice Inspection Plan for the fourth 10-year inspection interval for the Brunswick Steam Electric Plant (BSEP), Units 1 and 2. During the fourth inspection interval, the 2001 Edition through 2003 Addenda of the American Society of Mechanical Engineers (ASME) Boiler and Pressure Vessel Code, Section XI, was used for Class 1, 2, and 3 components, unless otherwise permitted.

During the fourth 10-year interval, Duke Energy completed the required inservice examinations for BSEP, Units 1 and 2, in accordance with the plan, except that certain components could not fully meet the examination requirements specified in the 2001 ASME Code with 2003 Addenda, Section XI, including the clarifications provided in ASME Code Case N-460. Duke Energy has determined that conformance to the Code requirement of essentially 100 percent coverage of weld volume or area examined was impractical due to various constraints and limitations. Accordingly, in accordance with 10 CFR 50.55a(g)(5)(iii), Duke Energy requests NRC approval of the 10 CFR 50.55a relief requests for the locations identified in Table 1 and Table 2 of Enclosure 1, for BSEP Unit 1 and Unit 2, respectively. Non-destruction examination (NDE) data and coverage plots for Unit 1 and Unit 2 are provided in Enclosure 2 and 3, respectively.

The fourth 10-year inservice inspection interval for both BSEP Unit 1 and Unit 2 began on May 11, 2008, and ended on May 10, 2018. This submittal is being provided to the NRC within 12 months after the expiration of the 10-year inservice inspection interval.

A D 47
NRR

U.S. Nuclear Regulatory Commission
Page 2 of 3

No regulatory commitments are contained in this letter. Please refer any questions regarding this submittal to Mr. Art Zaremba, Director – Nuclear Fleet Licensing, at (980) 373-2062.

Sincerely,



M. Christopher Nolan

Vice President – Nuclear Regulatory Affairs,
Policy, & Emergency Preparedness

LJG/ljg

Enclosures:

1. Relief Request ISI-12, Relief Requested in Accordance with 10 CFR 50.55a(g)(5)(iii) for Volumetric Examination of Class 1 and 2 Components
2. Relief Request ISI-12, Brunswick Steam Electric Plant, Unit 1 Fourth Inservice Inspection (ISI) Interval Limited Coverage Non-Destruction Examination (NDE) Data and Coverage Plots
3. Relief Request ISI-12, Brunswick Steam Electric Plant, Unit 2 Fourth Inservice Inspection (ISI) Interval Limited Coverage Non-Destruction Examination (NDE) Data and Coverage Plots

cc (with Enclosures):

U.S. Nuclear Regulatory Commission, Region II
ATTN: Ms. Catherine Haney, Regional Administrator
245 Peachtree Center Ave, NE, Suite 1200
Atlanta, GA 30303-1257

U.S. Nuclear Regulatory Commission
ATTN: Mr. Dennis J Galvin (**Electronic Copy Only**)
11555 Rockville Pike
Rockville, MD 20852-2738
Dennis.Galvin@nrc.gov

U.S. Nuclear Regulatory Commission
ATTN: Mr. Gale Smith, NRC Senior Resident Inspector
8470 River Road
Southport, NC 28461-8869

Chair - North Carolina Utilities Commission (**Electronic Copy Only**)
4325 Mail Service Center
Raleigh, NC 27699-4300
swatson@ncuc.net

Mr. Cliff Dautrich, Bureau Chief
North Carolina Department of Labor
Boiler Safety Bureau
1101 Mail Service Center
Raleigh, NC 27699-1101

Enclosure 1

Duke Energy Progress, LLC

Brunswick Steam Electric Plant, Units 1 and 2

Relief Request ISI-12

**Relief Requested in Accordance with 10 CFR 50.55a(g)(5)(iii) for Volumetric Examination
of Class 1 and 2 Components**

1.0 ASME CODE COMPONENTS AFFECTED:

Code Class:	1 & 2
References:	IWB-2500, Table IWB-2500-1 IWC-2500, Table IWC-2500-1 ASME Code Case N-460 ASME Code Case N-578-1, Table 1
Examination Categories:	B-D, C-B, C-F-2, R-A
Item Numbers:	B3.90, C2.21, C2.22, C5.51, R1.14
Description:	Limited Volumetric Examination Coverage
Component Number:	See Tables 1 and 2 for a List of Component IDs

2.0 APPLICABLE CODE EDITION AND ADDENDA:

The Brunswick Steam Electric Plant (BSEP), Units 1 and 2 Fourth Inservice Inspection Interval is based on the American Society of Mechanical Engineers (ASME) Boiler and Pressure Vessel (B&PV) Code, Section XI, 2001 Edition through the 2003 Addenda.

3.0 APPLICABLE CODE REQUIREMENTS:

3.1 Examination Category B-D

The extent of examination requirement for Examination Category B-D, Item Number B3.90, per Table IWB-2500-1, requires a volumetric examination of all nozzle-to-vessel welds as shown in Figure IWB-2500-7(b). During the fourth interval, BSEP Units 1 and 2, was approved to use ASME Code Case N-702 in a Safety Evaluation (SE) dated January 31, 2011 (ADAMS Accession Number ML110060504), for Relief Request ISI-05. Also, as allowed by ASME Code Case N-613-1, BSEP Units 1 and 2 performed a volumetric examination using a reduced examination volume (A-B-C-D-E-F-G-H) of Figure 2 of the Code Case in lieu of the previous examination volumes of ASME Section XI, Figure IWB-2500-7(b).

3.2 Examination Category C-B

The extent of examination requirement for Examination Category C-B, Item Number C2.21, per Table IWC-2500-1, requires a volumetric and surface examination of the nozzle-to-shell weld as shown in Figure IWC-2500-4(b). Note 4 in Table IWC-2500-1 states, in the case of multiple vessels of similar design, size, and service (such as steam generators, heat exchangers), the required examinations may be limited to one vessel or distributed among the vessels.

The extent of examination requirement for Examination Category C-B, Item Number C2.22, per Table IWC-2500-1, requires a volumetric examination of the nozzle inside radius section as shown in Figure IWC-2500-4(b). Note 4 in Table IWC-2500-1 states, in the case of multiple vessels of similar design, size, and service (such as steam generators,

heat exchangers), the required examinations may be limited to one vessel or distributed among the vessels.

3.3 Examination Category C-F-2

The extent of examination requirement for Examination Category C-F-2, Item Number C5.51 requires that 100% of each weld requiring examination receive a surface and volumetric exam as shown in Figure IWC-2500-7(a). ASME Code Case N-663, as an alternative for use by the NRC Regulatory Guide (RG) 1.147, Revision 15, states that in lieu of the surface examination requirements for the piping welds of Examination Category B-F (NPS 4 and larger), B-J (NPS 4 and larger), C-F-1, and C-F-2, surface examinations may be limited to areas identified by the Owner as susceptible to outside surface attack. The requirement for a surface examination was addressed by an ASME Code Case N-663 evaluation which determined that both BSEP units had no locations that were susceptible.

3.4 Examination Category R-A

The extent of examination requirement for Examination Category R-A, Item Number R1.14, per Table 1 of ASME Code Case N-578-1, requires a volumetric examination of essentially 100% of the length of the Risk Informed Inservice Inspection (RI-ISI) weld. Relief Request ISI-02 was submitted and was approved by the NRC in a SE dated November 4, 2008 (ADAMS Accession Number ML082600075), in order to utilize Electric Power Research Institute (EPRI) Topical Report (TR) 112657, Revision B-A, as supplemented by ASME Code Case N-578-1. The RI-ISI program scope only included Code Class 1, Category B-J and B-F welds.

3.5 ASME Code Case N-460

BSEP Units 1 and 2 adopted ASME Code Case N-460, "Alternative Examination Coverage for Class 1 and Class 2 Welds, Section XI, Division 1," which defines "essentially 100%" as greater than 90% coverage of the examination volume or surface area, as applicable. The greater than 90% minimum coverage was applied to all surface and volumetric examinations required by ASME Section XI.

4.0 IMPRACTICALITY OF COMPLIANCE:

Pursuant to 10 CFR 50.55a(g)(5)(iii), relief is requested on the basis that conformance with these ASME Section XI Code requirements is impractical as conformance would require extensive structural modifications to the component or surrounding structure.

BSEP Units 1 and 2 systems and components were designed and fabricated before the examination requirements of the ASME Section XI Code were formalized and published. Therefore, the BSEP was not specifically designed to meet the requirements of the ASME Section XI Code and full compliance is not feasible or practical within the limits of the current plant design. 10 CFR 50.55a(g)(1) recognizes the limitations to inservice inspection of components in accordance with the ASME Section XI Code that are

imposed due to early plants' design and construction.

Due to the original design of these components, it is not feasible to effectively perform the examination to the extent required (i.e. greater than 90% of the required volume and/or area). Therefore, relief is requested on the basis that the ASME Section XI Code requirements to examine these components are impractical due to physical obstructions and/or component configuration.

Tables 1 and 2 provide a summary of the examination limitations for each component for which relief is requested. The tables also indicate the outage the component was examined, the coverage percentage obtained for each component, and other pertinent design information. These tables are the cumulative lists of the limited ASME Section XI examinations performed during the fourth ISI interval. Enclosures 2 and 3 provide non-destructive examination (NDE) data and coverage plots that detail the examination limitations.

Accordingly, pursuant to 10 CFR 50.55a(g)(5)(iii), Duke Energy has determined that conformance with the code requirement of essentially 100% coverage of weld volume or area examined was impractical due to various constraints and limitations as stated above. Duke Energy requests NRC approval of the proposed alternative as stated below.

5.0 BURDEN CAUSED BY COMPLIANCE:

Compliance with the applicable ASME Section XI Code volumetric examination requirements can only be accomplished by redesigning and refabricating the subject and/or surrounding components. Based on this, the ASME Section XI Code requirements are deemed impractical in accordance with 10 CFR 50.55a(g)(5)(iii).

6.0 PROPOSED ALTERNATIVE AND BASIS FOR USE:

On the basis that obtaining the required examination coverage is impractical due to physical obstructions and limitations imposed by original plant design and fabrication, no alternative examination for additional ultrasonic (UT) examination coverage is proposed. Radiography (RT) is not a desired option because RT is limited in the ability to detect service induced flaws. BSEP / Duke Energy has determined the completed UT examinations are an acceptable alternative that provides reasonable assurance of continued structural integrity.

6.1 Examination Category B-D

BSEP Units 1 and 2 have performed the ASME Section XI Code required examinations to the maximum extent practical (Code Coverage), which are documented in Tables 1 and 2. In most cases, examination for axially-oriented flaws was limited from the nozzle side of the weld due to the configuration of the nozzle. Acceptable examination coverage (> 90%) of circumferentially-oriented flaws was typically obtained for these welds. The

Brunswick Steam Electric Plant, Units 1 and 2
Relief Request ISI-12
Enclosure 1
Page 4 of 14

volume of coverage obtained during the UT examination along with ongoing leakage tests each refueling outage provide reasonable assurance that structural integrity is being maintained.

6.2 Examination Category C-B

BSEP Units 1 and 2 have performed the ASME Section XI Code required examinations to the maximum extent practical (Code Coverage), which are documented in Tables 1 and 2. Due to the component configurations causing these limitations, there are no alternative examination techniques currently available to increase coverage. In addition, VT-2 visual examinations associated with the Class 2 leakage test are performed each inspection period. The volume of coverage obtained during the UT examination along with ongoing leakage tests once every inspection period provides reasonable assurance that structural integrity is being maintained.

6.3 Examination Category C-F-2

BSEP Unit 1 has performed the ASME Section XI Code required examinations to the maximum extent practical (Code Coverage), which are documented in Table 1. Due to the component configurations causing these limitations, there are no alternative examination techniques currently available to increase coverage. In addition, VT-2 visual examinations associated with the Class 2 leakage test are performed each inspection period for these welds except for pipe-to-valve weld, 1E411X226-1-FW22, which is exempt from periodic system pressure testing via IWA-5110(c). However, this section of piping within the High Pressure Coolant Injection (HPCI) system receives an integrated leak test in accordance with Technical Specification 5.5.2 every 24 months. Therefore, the volume of coverage obtained during the UT examinations along with ongoing leakage tests provide reasonable assurance that structural integrity is being maintained.

6.4 Examination Category R-A

BSEP Unit 1 has performed the ASME Section XI Code required examinations to the maximum extent practical (Code Coverage), which are documented in Table 1. Due to the component configuration causing these limitations, there are no alternative examination techniques currently available to increase coverage. In addition, VT-2 visual examinations associated with the Class 1 leakage test are performed each refueling outage. The volume of coverage obtained during the UT examinations along with ongoing leakage tests every refueling outage provide adequate assurance that structural integrity is being maintained.

7.0 DURATION OF PROPOSED ALTERNATIVE:

This request is proposed for the BSEP Units 1 and 2, Fourth Inservice Inspection Intervals identified below:

BSEP Units 1 and 2, Fourth Inservice Inspection Interval:

Start Date: May 11, 2008 End Date: May 10, 2018

8.0 PRECEDENTS:

- 8.1 Brunswick, Unit 1 – Relief Requests RR-47, RR-48, RR-49, and RR-50 for the Third 10-Year Interval Inservice Inspection Program Plan (ADAMS Accession Number ML11175A173).
- 8.2 Brunswick, Unit 2 – Relief Requests RR-47, RR-48, RR-49, and RR-50 for the Third 10-Year Interval Inservice Inspection Program Plan (ADAMS Accession Number ML11175A173).
- 8.3 Edwin I. Hatch Nuclear Plant, Unit NOS. 1 and 2 – Relief Requests ISI-RR-13, ISI-RR-14, ISI-RR-18, ISI-RR-19, ISI-RR-23, and ISI-RR-24 for Relief from Inservice Inspection Requirements (ADAMS Accession Number ML17279A045).
- 8.4 Oyster Creek Generating Station, Fourth 10-Year Interval Inservice Inspection Program Plan Request for Relief R-44 and R-45 (ADAMS Accession Number ML15097A153).

9.0 REFERENCES:

- 9.1 2001 Edition through 2003 Addenda, ASME Code, Section XI, “Rules for Inservice Inspection of Nuclear Power Plant Components.”
- 9.2 ASME Code Case N-460, Alternative Examination Coverage for Class 1 and Class 2 Welds, Section XI, Division 1.
- 9.3 Electric Power Research Institute (EPRI) Topical Report 112657, Revision B-A, “Revised-Risk Informed Inservice Inspection Evaluation” (ADAMS Accession Number ML013470102).
- 9.4 ASME Code Case N-578-1, Risk-Informed Requirement for Class 1, 2, or 3 Piping, Method B Section XI, Division 1.
- 9.5 ASME Code Case N-702, Alternative Requirements for Boiling Water Reactor (BWR) Nozzle Inner Radius and Nozzle-to-Shell Welds Section XI, Division 1.
- 9.6 Brunswick, Units 1 and 2, Relief Request ISI-02 Regarding the Continued Use of the Risk-Informed Inservice Inspection Program (ADAMS Accession Number ML082600075).

Brunswick Steam Electric Plant, Units 1 and 2
Relief Request ISI-12
Enclosure 1
Page 6 of 14

- 9.7 Brunswick Steam Electric Plant, Units 1 and 2 – Relief Request Alternative to Reactor Pressure Vessel Nozzle-to-Vessel Weld and Inner Radius Examinations (ADAMS Accession Number ML110060504).

Table 1
Brunswick Steam Electric Plant, Unit 1
List of Components with Limited Examination Coverage

Exam Category / Item Number	Component ID (Summary #)	Exam Requirements Figure No. and (Method)	Component Description (System) ^[Note 1]	Outage Examined	Material of Construction	Nominal Pipe Size (Thickness)	Exam Angle / Frequency (MHz) / Mode	Percent Coverage Obtained	Appendix VIII Qualified Exam	Remarks (NDE Data, Coverage Plots, and Calculations)
B-D B3.90	1B11-RPV-N1A (1-B11-1058)	[See Note 2] Volumetric (UT)	Nozzle N1A to Reactor Vessel Weld (RPV)	B1R18	A-508 Cl. 2 (Nozzle) SA-533 Gr. B (Shell)	26.125" ID (5.5" @ RPV Shell)	45° / 2.25 / Shear 60° / 2.0 / R. Long	80.35%	Yes	The examination was limited due to nozzle taper configuration. No unacceptable indications were noted. (Enclosure 2, Pg. No. 1)
B-D B3.90	1B11-RPV-N1B (1-B11-1060)	[See Note 2] Volumetric (UT)	Nozzle N1B to Reactor Vessel Weld (RPV)	B1R18	A-508 Cl. 2 (Nozzle) SA-533 Gr. B (Shell)	26.125" ID (5.5" @ RPV Shell)	45° / 2.25 / Shear 60° / 2.0 / R. Long	80.35%	Yes	The examination was limited due to nozzle taper configuration. No unacceptable indications were noted. (Enclosure 2, Pg. No. 1)
B-D B3.90	2B11-RPV-N5B (2-B11-1100)	[See Note 2] Volumetric (UT)	Nozzle N5B to Reactor Vessel Weld (RPV)	B1R18	A-508 Cl. 2 (Nozzle) SA-533 Gr. B (Shell)	14.25" ID (5.5" @ RPV Shell)	45° / 2.25 / Shear 60° / 2.0 / R. Long	74.2%	Yes	The examination was limited due to nozzle taper configuration. No unacceptable indications were noted. (Enclosure 2, Pg. No. 2)
C-B C2.21	1E11HX-1A-SWN3 (1-E11-3814)	IWC-2500-4(b) Surface and Volumetric (MT & UT)	Heat Exchanger 1A Inlet Nozzle to Head (RHR)	B1R22	SA-105 Gr. LF2 (Nozzle) SA-516 Gr. 70 (Shell Head)	20.0" (0.875" @ HX Shell)	45° / 2.25 / Shear 70° / 2.25 / Shear	100% - MT 40.1% - UT	No	Single sided exam. Limitation due to Nozzle / Shell configuration. 100% coverage was achieved for surface (MT) examination. No unacceptable indications were noted. (Enclosure 2, Pg. Nos. 3 – 7)

Table 1
Brunswick Steam Electric Plant, Unit 1
List of Components with Limited Examination Coverage

Exam Category / Item Number	Component ID (Summary #)	Exam Requirements Figure No. and (Method)	Component Description (System) ^[Note 1]	Outage Examined	Material of Construction	Nominal Pipe Size (Thickness)	Exam Angle / Frequency (MHz) / Mode	Percent Coverage Obtained	Appendix VIII Qualified Exam	Remarks (NDE Data, Coverage Plots, and Calculations)
C-B C2.22	1E11HX-1A-N4NIR (1-E11-3806)	IWC-2500-4(b) Volumetric (UT)	Heat Exchanger 1A Outlet Nozzle Inner Radius (RHR)	B1R18	SA-105 Gr. LF2 (Nozzle) SA-516 Gr. 70 (Shell Head)	20.0" (1.125" @ HX Shell)	55° / 2.25 / Shear 60° / 2.25 / Shear 65° / 2.25 / Shear	55.0%	Yes	Limitation due to Nozzle / Shell configuration. No unacceptable indications were noted. (Enclosure 2, Pg. Nos. 8 – 11)
C-F-2 C5.51	1E1145-15-FW58 (1-E11-3483)	IWC-2500-7(a) Surface and Volumetric (MT & UT)	Valve 1-E11-F031D to Pipe (RHR)	B1R21	SA-106 Gr. B (Pipe) A-216 WCC (Valve)	16" (0.375")	45° / 5.0 / Shear 60° / 5.0 / Shear	87.6% - UT MT [See Note 3]	Yes	The examination was limited due to physical limitations with circumferential scans on the downstream side of the weld (valve side only). No unacceptable indications were noted. (Enclosure 2, Pg. Nos. 12 – 16)
C-F-2 C5.51	1E1173-30-FW102 (1-E11-3616)	IWC-2500-7(a) Surface and Volumetric (MT & UT)	Pipe to Valve 1-E11-F017B (RHR)	B1R21	SA-106 Gr. B (Pipe) A-216 WCC (Valve)	24" (0.562")	45° / 2.25 / Shear 60° / 2.25 / Shear	87.3% - UT MT [See Note 3]	Yes	The examination was limited due to physical limitations with circumferential scans on the downstream side of the weld (valve side only). No unacceptable indications were noted. (Enclosure 2, Pg. Nos. 17 – 22)

Table 1
Brunswick Steam Electric Plant, Unit 1
List of Components with Limited Examination Coverage

Exam Category / Item Number	Component ID (Summary #)	Exam Requirements Figure No. and (Method)	Component Description (System) ^[Note 1]	Outage Examined	Material of Construction	Nominal Pipe Size (Thickness)	Exam Angle / Frequency (MHz) / Mode	Percent Coverage Obtained	Appendix VIII Qualified Exam	Remarks (NDE Data, Coverage Plots, and Calculations)
C-F-2 C5.51	1E215-39-FW4 (1-E21-4015)	IWC-2500-7(a) Surface and Volumetric (MT & UT)	Valve 1-E21-F001A to Pipe (CS)	B1R18	SA-106 Gr. B (Pipe) A-216 WCB/WCC (Valve)	14" (0.375")	45° / 5.0 / Shear 60° / 5.0 / Shear	90.0% - UT MT [See Note 3]	Yes	The examination was limited due to physical limitations with circumferential scans on the upstream side of the weld (valve side only). Indications from previous interval data verified (Report # 39-FW4, dated 4/18/2001, no changes observed). See NDE report in Enclosure 2, Page 22 for details related to indications. (Enclosure 2, Pg. Nos. 23 – 33)
C-F-2 C5.51	1E411X226-1-FW22 (1-E41-4152)	IWC-2500-7(a) Surface and Volumetric (MT & UT)	Pipe to Valve 1-E41-F042 (HPCI)	B1R21	SA-106 Gr. B (Pipe) A-216 WCB	16" (0.375")	45° / 5.0 / Shear 60° / 5.0 / Shear 70° / 5.0 / Shear	70.5% - UT MT [See Note 3]	Yes	The examination was limited due to physical limitations with circumferential scans on the upstream and downstream side of the weld. 100% axial coverage for circumferential flaws was achieved. No unacceptable indications were noted. (Enclosure 2, Pg. Nos. 34 – 40)
R-A R1.14	1B11N2D-RPV-FWABA (1-RCR-011-RI)	Code Case N-578-1 Table 1, Note (7)	RPV Nozzle 2D to Safe End Weld (RCR)	B1R18	A-508 Cl. 2 (Nozzle) Alloy 82/182 (DM Weld) SB-166 (Safe End)	12" (0.688")	35°-65° / 1.5 / Shear 25°-70° / 1.5 / R. Long (phased array)	86.9%	Yes	Limitations due to N2D nozzle configuration. 100% axial coverage for circumferential flaws was achieved. Observed previously recorded geometric reflectors with no change. (Enclosure 2, Pg. Nos. 41 – 42)

Table 1
Brunswick Steam Electric Plant, Unit 1
List of Components with Limited Examination Coverage

Exam Category / Item Number	Component ID (Summary #)	Exam Requirements Figure No. and (Method)	Component Description (System) ^[Note 1]	Outage Examined	Material of Construction	Nominal Pipe Size (Thickness)	Exam Angle / Frequency (MHz) / Mode	Percent Coverage Obtained	Appendix VIII Qualified Exam	Remarks (NDE Data, Coverage Plots, and Calculations)
R-A R1.14	I1B1IN5B-RPV-FWRNB16A (I-CS-027-RI)	Code Case N-578-1 Table 1, Note (7)	RPV Nozzle N5B to Safe End Weld (CS)	B1R22	A-508 Cl. 2 (Nozzle) Alloy 82/182 (DM Weld) SA-336 Cl. F8 (Safe End)	15.50" (0.90")	[See Note 4]	87.9%	Yes	Limitations due to N5B nozzle configuration. 100% axial coverage for circumferential flaws was achieved. No IGSCC/SCC flaws were detected. (Enclosure 2, Pg. Nos. 43 – 52)

NOTES:

1. The following systems and their abbreviations are listed here:
 - Core Spray (CS)
 - High Pressure Coolant Injection (HPCI)
 - Reactor Coolant Recirculation (RCR)
 - Residual Heat Removal (RHR)
2. The examination was performed using the alternative examination volume defined in ASME Code Case N-613-1, which reduces the area to be examined per IWB-2500-7(b) to the weld plus $\frac{1}{2}$ " on each side.
3. ASME Code Case N-663 applied.
4. Circumferential flaw detection exams were performed from both sides of the weld using refracted longitudinal wave beam angles of 30° , 45° , 60° , and 70° along with refracted shear wave beam angles of 45° and 60° . In addition to the automated examinations, manual scans were performed utilizing 45° and 60° refracted longitudinal wave and 45° shear wave probes. Axial flaw detection exams were performed across the examination volume in both circumferential beam directions (CW/CCW) using refracted longitudinal wave beam angles of 25° , 35° , 45° , and 55° along with shear wave beam angles of 35° , 45° , and 55° . Each of the beam angles were additionally programmed to produce beam skews from -30° to $+30^\circ$ at a 2.5° skew angle resolution. In addition to the automated examination manual scans were performed utilizing a 45° shear wave probe to achieve additional coverage on the nozzle side of the weld.

Table 2
Brunswick Steam Electric Plant, Unit 2
List of Components with Limited Examination Coverage

Exam Category / Item Number	Component ID (Summary #)	Exam Requirements Figure No. and (Method)	Component Description (System) ^[Note 1]	Outage Examined	Material of Construction	Nominal Pipe Size (Thickness)	Exam Angle / Frequency (MHz) / Mode	Percent Coverage Obtained	Appendix VIII Qualified Exam	Remarks (NDE Data, Coverage Plots, and Calculations)
B-D B3.90	2B11-RPV-N1A (2-B11-1078)	[See Note 2] Volumetric (UT)	Nozzle N1A to Reactor Vessel Weld (RPV)	B2R23	A-508 Cl. 2 (Nozzle) SA-533 Gr. B (Shell)	26.125" ID (5.5" @ RPV Shell)	[See Note 3]	76.5%	Yes	The examination was limited due to nozzle taper configuration. No unacceptable indications were noted. (Enclosure 3, Pg. Nos. 1 – 8)
B-D B3.90	2B11-RPV-N1B (2-B11-1080)	[See Note 2] Volumetric (UT)	Nozzle N1B to Reactor Vessel Weld (RPV)	B2R23	A-508 Cl. 2 (Nozzle) SA-533 Gr. B (Shell)	26.125" ID (5.5" @ RPV Shell)	[See Note 3]	76.5%	Yes	The examination was limited due to nozzle taper configuration. No unacceptable indications were noted. (Enclosure 3, Pg. Nos. 9 – 16)
B-D B3.90	2B11-RPV-N2B (2-B11-1084)	[See Note 2] Volumetric (UT)	Nozzle N2B to Reactor Vessel Weld (RPV)	B2R23	A-508 Cl. 2 (Nozzle) SA-533 Gr. B (Shell)	14.125" ID (5.5" @ RPV Shell)	[See Note 3]	72.8%	Yes	The examination was limited due to nozzle taper configuration. No unacceptable indications were noted. (Enclosure 3, Pg. Nos. 17 – 24)
B-D B3.90	2B11-RPV-N2C (2-B11-1086)	[See Note 2] Volumetric (UT)	Nozzle N2C to Reactor Vessel Weld (RPV)	B2R23	A-508 Cl. 2 (Nozzle) SA-533 Gr. B (Shell)	14.125" ID (5.5" @ RPV Shell)	[See Note 3]	72.8%	Yes	The examination was limited due to nozzle taper configuration. No unacceptable indications were noted. (Enclosure 3, Pg. Nos. 25 – 32)
B-D B3.90	2B11-RPV-N2D (2-B11-1088)	[See Note 2] Volumetric (UT)	Nozzle N2D to Reactor Vessel Weld (RPV)	B2R23	A-508 Cl. 2 (Nozzle) SA-533 Gr. B (Shell)	14.125" ID (5.5" @ RPV Shell)	[See Note 3]	72.8%	Yes	The examination was limited due to nozzle taper configuration. No unacceptable indications were noted. (Enclosure 3, Pg. Nos. 33 – 40)

Table 2
Brunswick Steam Electric Plant, Unit 2
List of Components with Limited Examination Coverage

Exam Category / Item Number	Component ID (Summary #)	Exam Requirements Figure No. and (Method)	Component Description (System) ^[Note 1]	Outage Examined	Material of Construction	Nominal Pipe Size (Thickness)	Exam Angle / Frequency (MHz) / Mode	Percent Coverage Obtained	Appendix VIII Qualified Exam	Remarks (NDE Data, Coverage Plots, and Calculations)
B-D B3.90	2B11-RPV-N5B (2-B11-1120)	[See Note 2] Volumetric (UT)	Nozzle N5B to Reactor Vessel Weld (RPV)	B2R23	A-508 Cl. 2 (Nozzle) SA-533 Gr. B (Shell)	14.25" ID (5.5" @ RPV Shell)	[See Note 3]	72.8%	Yes	The examination was limited due to nozzle taper configuration. No unacceptable indications were noted. (Enclosure 3, Pg. Nos. 41 -- 48)
B-D B3.90	2B11-RPV-N8B (2-B11-1137)	[See Note 2] Volumetric (UT)	Nozzle N8B to Reactor Vessel Weld (RPV)	B2R23	A-508 Cl. 2 (Nozzle) SA-533 Gr. B (Shell)	4.2" ID (5.5" @ RPV Shell)	[See Note 3]	72.8%	Yes	The examination was limited due to nozzle taper configuration. No unacceptable indications were noted. (Enclosure 3, Pg. Nos. 49 -- 56)
B-D B3.90	2B11-RPV-N9 (2-B11-1140)	[See Note 2] Volumetric (UT)	Nozzle N9 to Reactor Vessel Weld (RPV)	B2R23	A-508 Cl. 2 (Nozzle) SA-533 Gr. B (Shell)	4.125" ID (5.5" @ RPV Shell)	[See Note 3]	72.8%	Yes	The examination was limited due to nozzle taper configuration. No unacceptable indications were noted. (Enclosure 3, Pg. Nos. 57 -- 64)
C-B C2.21	2E11HX-2A-SWN3 (2-E11-3756)	IWC-2500-4(b) Surface and Volumetric (MT & UT)	Heat Exchanger 2A Inlet Nozzle to Head (RHR)	B2R23	SA-105 Gr. LF2 (Nozzle) SA-516 Gr. 70 (Shell Head)	20.0" (0.875" @ HX Shell)	45° / 2.25 / Shear 70° / 2.25 / Shear	100% - MT 50% - UT	No	Limitation due to Nozzle / Shell configuration. 100% coverage was achieved for surface (MT) examination. 100% axial coverage for circumferential flaws was achieved. No unacceptable indications were noted. (Enclosure 3, Pg. Nos. 65 -- 69)

Table 2
Brunswick Steam Electric Plant, Unit 2
List of Components with Limited Examination Coverage

Exam Category / Item Number	Component ID (Summary #)	Exam Requirements Figure No. and (Method)	Component Description (System) ^[Note 1]	Outage Examined	Material of Construction	Nominal Pipe Size (Thickness)	Exam Angle / Frequency (MHz) / Mode	Percent Coverage Obtained	Appendix VIII Qualified Exam	Remarks (NDE Data, Coverage Plots, and Calculations)
C-B C2.21	2E11HX-2A-SWN4 (2-E11-3757)	IWC-2500-4(b) Surface and Volumetric (MT & UT)	Heat Exchanger 2A Outlet Nozzle to Shell (RHR)	B2R22	SA-105 Gr. LF2 (Nozzle) SA-516 Gr. 70 (Shell Head)	20.0" (1.125" @ HX Shell)	45° / 2.25 / Shear 60° / 2.25 / Shear	100% - MT 75% - UT	No	Limitation due to Nozzle / Shell configuration. 100% coverage was achieved for surface (MT) examination. 86% axial coverage for circumferential flaws was achieved. No unacceptable indications were noted. (Enclosure 3, Pg. Nos. 70 – 80)
C-B C2.22	2E11HX-2A-N4NIR (2-E11-3748)	IWC-2500-4(b) Volumetric (UT)	Heat Exchanger 2A Outlet Nozzle Inner Radius (RHR)	B2R22	SA-105 Gr. LF2 (Nozzle) SA-516 Gr. 70 (Shell Head)	20.0" (1.125" @ HX Shell)	55° / 2.25 / Shear 60° / 2.25 / Shear 65° / 2.25 / Shear	55.0%	Yes	Limitation due to Nozzle / Shell configuration. No unacceptable indications were noted. (Enclosure 3, Pg. Nos. 81 – 88)

NOTES:

1. The following systems and their abbreviations are listed here:
 - Residual Heat Removal (RHR)
 - Reactor Pressure Vessel (RPV)
2. The examination was performed using the alternative examination volume defined in ASME Code Case N-613-1, which reduces the area to be examined per IWB-2500-7(b) to the weld plus $\frac{1}{2}$ " on each side.

3. 60° Longitudinal wave examinations were performed from the vessel surface in both the radial and circumferential scan directions. In accordance with UT Procedure 54-ISI-850-008 and the EPRI Model No. IR-2017-680 the following examinations were performed.


Recirculation Outlet Nozzle (N1A, N1B) Nozzle Modeling Parameters		
Probe	Probe Skew	Scan Surface
50° Shear	± (59° to 82°)	Vessel
Recirculation Inlet Nozzle (N2B, N2C, N2D) Nozzle Modeling Parameters		
Probe	Probe Skew	Scan Surface
50° Shear	± (51° to 76°)	Vessel
Core Spray Nozzle (N5B) Nozzle Modeling Parameters		
Probe	Probe Skew	Scan Surface
50° Shear	± (51° to 77°)	Vessel
Jet Pump Instrumentation (N8B) Nozzle Modeling Parameters		
Probe	Probe Skew	Scan Surface
50° Shear	± (43° to 65°)	Vessel
CRD-HYD System Return (N9) Nozzle Modeling Parameters		
Probe	Probe Skew	Scan Surface
50° Shear	± (44° to 65°)	Vessel

Enclosure 2

Relief Request ISI-12

**Brunswick Steam Electric Plant, Unit 1 Fourth Inservice Inspection (ISI) Interval Limited
Coverage Non-Destruction Examination (NDE) Data and Coverage Plots**


1B11-RPV-N1A / 1B11-RPV-N1B
Nozzle to Reactor Vessel Weld
Examination Coverage Plot



DRAWN AND REVIEWED BY: JASON POLISENSKY UT LIII, 4/19/19 *Jason Polisensky*
 Reviewed by: Steven Dean UT L-III *SD* 4/10/19

1B11-RPV-N5B

Nozzle to Reactor Vessel Weld Examination Coverage Plot



DRAWN AND REVIEWED BY: JASON POLISENSKY UT L III, 4/16/19

Reviewed by: D.B King UT Level III



Enclosure 2

BSEP, Unit 1 4th ISI Interval Limited NDE Data and Coverage Plots

Magnetic Particle Examination

Site/Unit:	BNP / 1	Procedure:	NDE-NE-ALL-3101	Outage No.:	B122R1	
Summary No.:	1-E11-3814	Procedure Rev.:	0	Report No.:	MT-18-007	
Workscope:	ISI	Work Order No.:	20170837	Page:	1 of 3	
Code:	2001 EDITION/2003 ADDENDA	Cat./Item:	C-B/C2.21	Location:	Reactor Building	
Drawing No.:	C-24004 Sht. 075-1	Description: RHR HTX 1A INLET NOZZLE TO HEAD				
System ID:	2045					
Component ID:	1E11HX-1A-SWN3	Mat./Thickness: CS / 0.875"				
Limitations:	None					
Light Meter Mfg.:	N/A - EPRI Character Card	Serial No.:	0904130016	Illumination:	Adequate	
Temp. Tool Mfg.:	Fluke	Serial No.:	G503098	Surface Temp.:	72 °F	
Resolution:	0.044" Character Card					
Lift Block Serial No.:	G502277	Surface Condition:	Ground Smooth			
Lo/Wo Location:	N/A	Field Orientation:	Two Perpendicular			
Magnetic Particle Material						
Brand:	Parker	Wet	<input type="checkbox"/>	Mixed:	Yes <input type="checkbox"/>	
Type:	8A Red	Dry	<input checked="" type="checkbox"/>	No <input type="checkbox"/>	Applied By: Dusting <input checked="" type="checkbox"/>	
Batch No.:	19946	Visible	<input checked="" type="checkbox"/>	With:	Spraying <input type="checkbox"/>	
Equipment:	MAGNAFLUX		Fluorescent	<input type="checkbox"/>	Flooding <input type="checkbox"/>	
Head Shot	<input type="checkbox"/> N/A	Amperes	Fixed Spacing	<input type="checkbox"/>	AC <input checked="" type="checkbox"/> DC <input type="checkbox"/>	
Adj. Spacing	<input checked="" type="checkbox"/> 3" - 6"	inches	Encircling Coils	<input type="checkbox"/> N/A	Turns	
Prods. Spacing	<input type="checkbox"/> N/A	inches	Current (machine setting)	<input type="checkbox"/> N/A	Amperes	
Indication No.	Loc L	Loc W	Diameter	Length	Type R/L	Remarks
NRI						N/A

Comments:
Yoke technique, Attachment 13, Figure 13.1.
Lift test and illumination verified before and after exam.

Results: Sat Unsat Eval

Percent Of Coverage Obtained > 90%: 100% Reviewed Previous Data: N/A Exam Time: 1620

Examiner	Level II-N	Signature	Date	Reviewer	Signature	Date
May, Richard C.			3/8/2018	J.D. Shepard, NDE LIII	<i>J.D. Shepard</i>	3/14/18 CRW
Examiner	Level II-N	Signature	Date	Site Review	Signature	Date
Ransom, Greg J.			3/8/2018	CHRIS WINSLOW	<i>Chris Winslow</i>	3/13/18
Other	Level III-N	Signature	Date	ANII Review	Signature	Date
Williams, Christopher D			3/8/2018	DAVID M. REYNOLDS	<i>David M. Reynolds</i>	3/13/2018

Enclosure 2



BSEP, Unit 1 4th ISI Interval Limited NDE Data and Coverage Plots
UT Calibration/Examination

Site/Unit:	BNP / 1	Procedure:	NDEP-0448	Outage No.:	B122R1	
Summary No.:	1-E11-3814	Procedure Rev.:	4	Report No.:	UT-18-006	
Workscope:	ISI	Work Order No.:	20170837	Page:	1 of 6	
Code:	2001 EDITION/2003 ADDENDA	Cat./Item:	C-B/C2.21	Location:	Reactor Building	
Drawing No.:	C-24004 Sht. 075-1	Description: RHR HTX 1A INLET NOZZLE TO HEAD				
System ID:	2045					
Component ID:	1E11HX-1A-SWN3	Size/Length:		1.2" / 81.5"	Thickness/Diameter:	CS/0.875"/26.0"
Limitations:	Single side exam due to nozzle	Start Time:		1600	Finish Time:	1645
Instrument Settings		Search Unit		Axial Oriented Search Unit		
Serial No.:	15A024PE	Serial No.:	0105LM	Cal. Checks	Time	Date
Manufacturer:	GE	Manufacturer:	KBA	Initial Cal.	1145	3/8/2018
Model:	USN 60 SW	Linearity:	L-18-004	Inter. Cal.	1555	3/8/2018
Delay:	6.3712	Range:	2.0	Inter. Cal.	N/A	
M'tl Cal/Vel:	0.1271	Pulser Type:	Square	Inter. Cal.	N/A	
Damping:	500 Ohms	Reject:	0%	Measured Angle:	45°	Mode: Shear
PRF:	Auto High	SU Freq.:	2.25 MHz	Exit Point:	0.5"	# of Elements: 1
Frequency:	2.25 MHz	Rectify:	Fullwave	Config.:	Single	Focus: N/A
Voltage:	450	Pulse Width:	220	Shape:	Round	Contour: Flat
Ax. Gain (dB):	26.4	Circ. Gain (dB):	N/A	Wedge Style:	MSWQC	
1 Screen Div. =	.200	in. of Sound Path		Search Unit Cable	Couplant	
Cal. Block No.:	071B	Type:	RG-174	Length:	6'	No. Conn.: 0
Thickness:	.875	Dia.:	Flat	Exam Batch:	14M076	
Cal. Blk. Temp.:	70	Temp. Tool:	G503098	Type:	Ultragel II	
Comp. Temp.:	72	Temp. Tool:	G503098	Mfg.:	Magnaflux	
Calibration Block		Scan Coverage		Reference Block		
Upstream <input type="checkbox"/> Downstream <input checked="" type="checkbox"/> Scan dB: 32.5		CW <input checked="" type="checkbox"/> CCW <input checked="" type="checkbox"/> Scan dB: 32.5		Serial No.:	16-4112	
Exam Surface: OD		Surface Condition: Smooth		Type:	CS Rompas	
Recordable Indication(s): Yes <input type="checkbox"/> No <input checked="" type="checkbox"/> (If Yes, Ref. Attached Ultrasonic Indication Report.)				Comments: No examination from nozzle side due to configuration. Circ scan limitation due to nozzle and weld configuration.		
Results:	Sat <input checked="" type="checkbox"/>	Unsat <input type="checkbox"/>	Eval <input type="checkbox"/>	NCR 02190316		
Percent Of Coverage Obtained > 90%: 40.1%		Reviewed Previous Data: Yes				

Examiner	Level	II-PDI	Signature	Date	Reviewer	Signature	Date
Hancock, David R.				3/8/2018	Jason Polisensky LV III		3/13/18
Examiner	Level	N/A	Signature	Date	Site Review	Signature	Date
N/A					CHRIS WINSLOW		3/14/18
Other	Level	N/A	Signature	Date	ANII Review	Signature	Date
N/A					E. mastala E. kouw		3/15/18



Enclosure 2
BSEP, Unit 1 4th ISI Interval Limited NDE Data and Coverage Plots
UT Calibration/Examination

Site/Unit:	BNP	/	1	Procedure:	NDEP-0448	Outage No.:	B122R1																		
Summary No.:	1-E11-3814			Procedure Rev.:	4	Report No.:	UT-18-006																		
Workscope:	ISI			Work Order No.:	20170837	Page:	2 of 6																		
Code:	2001 EDITION/2003 ADDENDA			Cat./Item:	C-B/C2.21	Location:	Reactor Building																		
Drawing No.:	C-24004 Sht. 075-1			Description: RHR HTX 1A INLET NOZZLE TO HEAD																					
System ID:	2045																								
Component ID:	1E11HX-1A-SWN3			Size/Length:	1.2" / 81.5"	Thickness/Diameter: CS/0.875"/26.0"																			
Limitations:	Single side exam due to nozzle			Start Time:	1600	Finish Time:	1645																		
Instrument Settings Serial No.: 15A024PE Serial No.: 0105LJ Manufacturer: GE Manufacturer: KBA Model: USN 60 SW Linearity: L-18-004 Size: 0.5" Model: Comp - G Delay: 9.2794 Range: 3.0 Freq.: 2.25 MHz Center Freq.: N/A M'tl Cal/Vel: 0.1268 Pulser Type: Square Exam Angle: 70° Squint Angle: N/A Damping: 500 Ohms Reject: 0% Measured Angle: 70° Mode: Shear PRF: Auto High SU Freq.: 2.25 MHz Exit Point: 0.700" # of Elements: 1 Frequency: 2.25 MHz Rectify: Fullwave Config.: Single Focus: N/A Voltage: 450 Pulse Width: 220 Shape: Round Contour: Flat Ax. Gain (dB): 30.0 Circ. Gain (dB): N/A Wedge Style: MSWQC				Search Unit <table border="1" style="width: 100%; border-collapse: collapse;"> <thead> <tr> <th>Cal. Checks</th> <th>Time</th> <th>Date</th> </tr> </thead> <tbody> <tr> <td>Initial Cal.</td> <td>1205</td> <td>3/8/2018</td> </tr> <tr> <td>Inter. Cal.</td> <td>1623</td> <td>3/8/2018</td> </tr> <tr> <td>Inter. Cal.</td> <td>N/A</td> <td></td> </tr> <tr> <td>Inter. Cal.</td> <td>N/A</td> <td></td> </tr> <tr> <td>Final Cal.</td> <td>1720</td> <td>3/8/2018</td> </tr> </tbody> </table> Couplant Cal. Batch: 14M076 Type: Ultragel II Mfg.: Magnaflux				Cal. Checks	Time	Date	Initial Cal.	1205	3/8/2018	Inter. Cal.	1623	3/8/2018	Inter. Cal.	N/A		Inter. Cal.	N/A		Final Cal.	1720	3/8/2018
Cal. Checks	Time	Date																							
Initial Cal.	1205	3/8/2018																							
Inter. Cal.	1623	3/8/2018																							
Inter. Cal.	N/A																								
Inter. Cal.	N/A																								
Final Cal.	1720	3/8/2018																							
1 Screen Div. = .300 in. of Sound Path				Search Unit Cable Type: RG-174 Length: 6' No. Conn.: 0 Type: Ultragel II Mfg.: Magnaflux																					
Calibration Block Cal. Block No.: 071B Thickness: .875 Dia.: Flat Cal. Blk. Temp.: 70 Temp. Tool: G503098 Comp. Temp.: 72 Temp. Tool: G503098				Scan Coverage Upstream <input type="checkbox"/> Downstream <input checked="" type="checkbox"/> Scan dB: 36.0 CW <input checked="" type="checkbox"/> CCW <input checked="" type="checkbox"/> Scan dB: 36.0 Exam Surface: OD Type: CS Rompas Surface Condition: Smooth																					
Recordable Indication(s): Yes <input type="checkbox"/> No <input checked="" type="checkbox"/> (If Yes, Ref. Attached Ultrasonic Indication Report.)				Reference Block Serial No.: 16-4112																					
Results: Sat <input checked="" type="checkbox"/> Unsat <input type="checkbox"/> Eval <input type="checkbox"/>				Comments: Supplemental exam for coverage																					
Percent Of Coverage Obtained > 90%: 40.1% Reviewed Previous Data:																									
Examiner	Level	II-PDI	Signature	Date	Reviewer	Signature	Date																		
Hancock, David R.				3/8/2018	Jason Polisensky LV III		3/13/18																		
Examiner	Level	N/A	Signature	Date	Site Review	Signature	Date																		
N/A					CHRIS WINSLOW		3/14/18																		
Other	Level	N/A	Signature	Date	ANII Review	Signature	Date																		
N/A					El mostalo @koun		3/15/18																		




Supplemental Report

Report No.: UT-18-006Page: 3 of 6Summary No.: 1-E11-3814Examiner: Hancock, David R.Level: II-PDIReviewer: J. POLISENSKY LIII John PolisenskyDate: 3/13/18Examiner: N/ALevel: N/ASite Review: CHRIS WINSLOW PL 201Date: 3/14/18Other: N/ALevel: N/AANII Review: E. MOSTAFA E. KOUN E. KOUNDate: 3/15/18

Comments: Thickness Profile / Coverage Plot

Sketch or Photo: Z:\NDEess\UT\OUTAGES\BNP\Unit 1\B122R1\IDDEAL Modified Supplement Scans\1E11HX-1A-SWN3\1E11HX-1A-SWN3 (1).bmp





Enclosure 2
BSEP, Unit 1 4th ISI Interval Limited NDE Data and Coverage Plots

Supplemental Report

Report No.: UT-18-006
Page: 4 of 6

Summary No.: 1-E11-3814

Examiner: Hancock, David R.

Level: II-PDI

Reviewer: J. POLISENSKY LIII

Date: 3/13/18

Examiner: N/A

Level: N/A

Site Review: CHRIS WINSLOW PL 2015

Date: 3/14/18

Other: N/A

Level: N/A

ANII Review: E. Knostle R. Brown E. K. Brown

Date: 3/15/18

Reviewed by: D.B. King UT Level III

Date: 3/13/18

Comments: **Coverage Calculations**


Sketch or Photo: Z:\NDEess\UT\OUTAGES\BNP\Unit 1\B122R1\IDDEAL Modified Supplement Scans\1E11HX-1A-SWN3\1E11HX-1A-SWN3 (2).bmp

1EH11HX-1A-SWN3

Examination Coverage Calculation

Total Volume
 $0.561''^2$

$$1.7''^b \times .33''^h = 0.561''^2$$



45° Vessel Head side missing volume

$$[(0.9''^b_1 + 0.45''^b_2) \div 2] \times 0.33''^h = 0.222''^2$$

$$0.222 \div 0.561 = 39.6\% \text{ missing coverage}$$

$$100\% - 39.6\% = 60.4\% \text{ Total } 45^\circ \text{ Vessel Head side Coverage}$$

$60.4\% = 45^\circ \text{ Vessel Head Side}$

$100\% = 70^\circ \text{ Vessel Head Side}$

$160.4 \div 2 = 80.2\% \text{ Axial coverage}$

Circ Scans performed from Head side and skewed into the weld from weld toes.

No coverage claimed on circ scans due to width of transducer and as welded Weld Crown. $0\% = \text{Circ coverage}$

$$80.2\% + 0\% = 80.2\% \div 2 = 40.1\% \text{ Total Examination Coverage Achieved}$$



Enclosure 2
BSEP, Unit 1 4th ISI Interval Limited NDE Data and Coverage Plots
UT Calibration Examination

Site/Unit:	BNP / 1	Procedure:	NDEP-0456	Outage No.:	B118R1
Summary No.:	1-E11-3806	Procedure Rev.:	003	Report No.:	UT-10-053
Workscope:	ISI	Work Order No.:	1549261	Page:	1 of 4

Code:	2001 Edition, 2003 Addenda	Cat./Item:	C-B/C2.22	Location:	See ISO
Drawing No.:	C-24004 Sht. 75-1	Description: RHR HTX 1A OUTLET NOZZLE INNER RADIUS			
System ID:	2045				
Component ID:	1E11HX-1A-N4NIR	Size/Length:	75"	Thickness/Diameter:	2.5"
Limitations:	Nozzle / Shell Configuration	Start Time:	1605	Finish Time:	1617

Instrument Settings		Search Unit			Axial Orientated Search Unit					
Serial No.:	00FXBC	Serial No.:	00YJYX	Cal. Checks	Time	Date	Calibration Reflector	Signal Amplitude %	Sweep Division	Sound Path
Manufacturer:	Krautkramer	Manufacturer:	KBA	Initial Cal.	1440	3/11/2010	ID Notch	80%	5.7	5.122"
Model:	USN-52R	Size:	.5"	Shape:	Round					
Delay:	0.000	Range:	9.0"	Freq.:	2.25 MHz	Style: Comp-G				
M'tl Cal/Vel:	11.379	Pulser:	Single	Exam Angle:	55°	# of Elements: 1				
Damping:	1000 Ω	Reject:	0%	Mode:	Shear					
Rep. Rate:	High	Freq.:	2-8 MHz	Measured Angle:	55°		Couplant			
Filter:	Fixed	Mode:	P/E	Wedge Style:	Non-Integral		Cal. Batch:	09225		
Voltage:	Fixed	Other:	Full Wave	Type:	RG-174		Type:	Ultralag II		
Ax. Gain (dB):	N/A	Circ. Gain (dB):	49.0	Length:	12'	No. Conn.: 0	Mfg.:	Sonotech, Inc.		
1 Screen Div. =	0.90	In. of Sound Path					Exam Batch:	09225		
Linearity Report No.:	L-10-001						Type:	Ultralag II		
Calibration Block										
Cal. Block No.:	046BR			Upstream <input type="checkbox"/> Downstream <input type="checkbox"/> Scan dB: N/A	Scan Coverage		Circumferential Orientated Search Unit			
Thickness:	3.0"	Dia.:	Flat	CW <input checked="" type="checkbox"/> CCW <input checked="" type="checkbox"/> Scan dB: 65	Reference Block		Calibration Reflector	Signal Amplitude %	Sweep Division	Sound Path
Cal. Blk. Temp.:	72°	Temp. Tool:	95500813	Exam Surface: OD	Serial No.:		A01330	N/A	N/A	N/A
Comp. Temp.:	70°	Temp. Tool:	95500813	Surface Condition: As Ground	Type:		CS Rompas			
Recordable Indication(s): Yes <input type="checkbox"/> No <input checked="" type="checkbox"/>				(If Yes, Ref. Attached Ultrasonic Indication Report.)						
Results:	Sat <input checked="" type="checkbox"/>	Unsat <input type="checkbox"/>	Eval <input type="checkbox"/>	Comments: NRI Probe Zero = 11.091						

Percent Of Coverage Obtained > 90%: No - ~ 55%				Reviewed Previous Data: Yes			
Examiner	Level	III-PDI	Signature	Date	Reviewer	Signature	Date
Smith, Kenneth			<i>Kenneth R Smith</i>	3/11/2010	James Delbusso Level III	<i>J. Delbusso</i>	3/22/2010
Examiner	Level	N/A	Signature	Date	Site Review	Signature	Date
N/A					Damon Priestley NDE Level III	<i>D. Priestley</i>	3/22/2010
Other	Level	N/A	Signature	Date	ANII Review	Signature	Date
N/A					Nancy C. Ritchie-Slaughter	<i>Nancy C. Ritchie-Slaughter</i>	3/23/2010

Enclosure 2

BSEP, Unit 1 4th ISI Interval Limited NDE Data and Coverage Plots

UT Calibration Examination

Site/Unit: BNP / 1 Procedure: NDEP-0456 Outage No.: B118R1
 Summary No.: 1-E11-3806 Procedure Rev.: 003 Report No.: UT-10-053
 Workscope: ISI Work Order No.: 1549261 Page: 3 of 4

Code: 2001 Edition, 2003 Addenda Cat./Item: C-B/C2.22 Location: See ISO
 Drawing No.: C-24004 Sht. 75-1 Description: RHR HTX 1A OUTLET NOZZLE INNER RADIUS
 System ID: 2045
 Component ID: 1E11HX-1A-N4NIR Size/Length: 75" Thickness/Diameter: 2.5"
 Limitations: Nozzle / Shell Configuration Start Time: 1637 Finish Time: 1649

Instrument Settings		Search Unit			Axial Orientated Search Unit			
Serial No.:	<u>00FXBC</u>	Serial No.:	<u>00YJYX</u>		Cal. Checks	Time	Date	
Manufacturer:	<u>Krautkramer</u>	Manufacturer:	<u>KBA</u>		Initial Cal.	<u>1505</u>	<u>3/11/2010</u>	
Model:	<u>USN-52R</u>	Size:	<u>.5"</u>	Shape:	Round	Inter. Cal.	<u>1635</u>	<u>3/11/2010</u>
Delay:	<u>0.000</u>	Range:	<u>10.0"</u>	Freq.:	<u>2.25 MHz</u>	Inter. Cal.	<u>1650</u>	<u>3/11/2010</u>
M'tl Cal/Vel:	<u>0.1288</u>	Pulser:	<u>Single</u>	Exam Angle:	<u>65°</u>	# of Elements:	<u>1</u>	
Damping:	<u>1000 Ω</u>	Reject:	<u>0%</u>	Mode:	<u>Shear</u>			
Rep. Rate:	<u>High</u>	Freq.:	<u>2-8 MHz</u>	Measured Angle:	<u>65°</u>			
Filter:	<u>Fixed</u>	Mode:	<u>P/E</u>	Wedge Style:	<u>Non-Integral</u>			
Voltage:	<u>Fixed</u>	Other:	<u>Full Wave</u>	Type:	<u>RG-174</u>			
Ax: Gain (dB):	<u>N/A</u>	Circ. Gain (dB):	<u>63.0</u>	Length:	<u>12'</u>	No. Conn.:	<u>0</u>	
1 Screen Div. =	<u>1.0</u>	in. of	<u>Sound Path</u>	Type:	<u>Ultralag II</u>			
Linearity Report No.:	<u>L-10-001</u>			Mfg.:	<u>Sonotech, Inc.</u>			
Calibration Block				Exam Batch:	<u>09225</u>			
Cal. Block No.:	<u>045BR</u>			Type:	<u>Ultralag II</u>			
Thickness:	<u>3.0"</u>	Dia.:	<u>Flat</u>	Mfg.:	<u>Sonotech, Inc.</u>			
Cal. Blk. Temp.:	<u>72°</u>	Temp. Tool:	<u>95500813</u>	Upstream	<input type="checkbox"/>	Downstream	<input type="checkbox"/>	
Comp. Temp.:	<u>70°</u>	Temp. Tool:	<u>95500813</u>	CW	<input checked="" type="checkbox"/>	CCW	<input checked="" type="checkbox"/>	
Recordable Indication(s):	Yes	<input type="checkbox"/>	No	<input checked="" type="checkbox"/>	(If Yes, Ref. Attached Ultrasonic Indication Report.)			
Results:	Sat	<input checked="" type="checkbox"/>	Unsat	<input type="checkbox"/>	Eval	<input type="checkbox"/>	Comments: <u>NRI</u> <u>Probe Zero = 10.507</u>	
Percent Of Coverage Obtained > 90%: <u>No - ~ 55%</u>				Reviewed Previous Data:	<u>Yes</u>			
Examiner <u>Smith, Kenneth</u> Level <u>III-PDI</u>		Signature <u>Kenneth R Smith</u>	Date <u>3/11/2010</u>	Reviewer <u>James Delbusso</u> Level <u>III</u>	<u>J. Delbusso</u>		Date <u>3/22/2010</u>	
Examiner <u>N/A</u> Level <u>N/A</u>		Signature	Date	Site Review	<u>Damon Priestley</u>		Date <u>3/22/2010</u>	
Other <u>N/A</u> Level <u>N/A</u>		Signature	Date	ANII Review	<u>Nancy C. Ritchie-Slaughter</u>		Date <u>3/23/2010</u>	



Enclosure 2
BSEP, Unit 1 4th ISI Interval Limited NDE Data and Coverage Plots
UT Calibration Examination

Site/Unit:	BNP / 1	Procedure:	NDEP-0456		Outage No.:	B118R1						
Summary No.:	1-E11-3806	Procedure Rev.:	003		Report No.:	UT-10-053						
Workscope:	ISI	Work Order No.:	1549261		Page:	2 of 4						
Code:	2001 Edition, 2003 Addenda	Cat./Item:	C-B/C2.22		Location:	See ISO						
Drawing No.:	C-24004 Sht. 75-1	Description: RHR HTX 1A OUTLET NOZZLE INNER RADIUS										
System ID:	2045											
Component ID:	1E11HX-1A-N4NIR	Size/Length:		75"	Thickness/Diameter:		2.5"					
Limitations:	Nozzle / Shell Configuration	Start Time:		1621	Finish Time:		1632					
Instrument Settings			Search Unit									
Serial No.:	00FXBC	Serial No.:	00YJYX		Cal. Checks	Time	Date	Axial Orientated Search Unit				
Manufacturer:	Krautkramer	Manufacturer:	KBA		Initial Cal.	1455	3/11/2010	Calibration Reflector	Signal Amplitude %	Sweep Division	Sound Path	
Model:	USN-52R	Size:	.5"	Shape:	Round	Inter. Cal.	1620	3/11/2010	ID Notch	80%	5.2	5.720"
Delay:	0.000	Range:	11.0"	Freq.:	2.25 MHz	Style:	Comp-G					
M'tl Cal/Vel:	0.1288	Pulser:	Single	Exam Angle:	60°	# of Elements:	1					
Damping:	1000 Ω	Reject:	0%	Mode:	Shear							
Rep. Rate:	High	Freq.:	2-8 MHz	Measured Angle:	60°			Couplant				
Filter:	Fixed	Mode:	P/E	Wedge Style:	Non-Integral			Cal. Batch:	09225			
Voltage:	Fixed	Other:	Full Wave	Type:	RG-174			Type:	Ultragel II			
Ax. Gain (dB):	N/A	Circ. Gain (dB):	51.0	Search Unit Cable				Mfg.:	Sonotech, Inc.			
1 Screen Div. =	1.10	in. of Sound Path		Length:	12'	No. Conn.:	0	Exam Batch:	09225			
Linearity Report No.:	L-10-001			Scan Coverage				Type:	Ultragel II			
Calibration Block				Mfg.:	Sonotech, Inc.							
Cal. Block No.:	045BR			Upstream <input type="checkbox"/> Downstream <input type="checkbox"/> Scan dB: N/A				Reference Block				
Thickness:	3.0"	Dia.:	Flat	CW <input checked="" type="checkbox"/> CCW <input checked="" type="checkbox"/> Scan dB: 56				Serial No.:	A01330			
Cal. Blk. Temp.:	72°	Temp. Tool:	95500813	Exam Surface:	OD			Type:	CS Rompas			
Comp. Temp.:	70°	Temp. Tool:	95500813	Surface Condition:	As Ground							
Recordable Indication(s):	Yes <input type="checkbox"/>	No <input checked="" type="checkbox"/>	(If Yes, Ref. Attached Ultrasonic Indication Report.)									
Results:	Sat <input checked="" type="checkbox"/>	Unsat <input type="checkbox"/>	Eval <input type="checkbox"/>	Comments: NRI Probe Zero = 9.191								
Percent Of Coverage Obtained > 90%: No - ~ 55%				Reviewed Previous Data: Yes								
Examiner	Level	III-PDI	Signature	Date	Reviewer				Signature	Date		
Smith, Kenneth			<i>Kenneth R Smith</i>	3/11/2010	James Delbusso Level III				<i>J. Delbusso</i>	3/22/2010		
Examiner	Level	N/A	Signature	Date	Site Review				Signature	Date		
N/A					Damon Priestley NDE Level III				<i>D. Priestley</i>	3/22/2010		
Other	Level	N/A	Signature	Date	ANII Review				Signature	Date		
N/A					Nancy C. Ritchie-Slaughter				<i>Nancy C. Ritchie-Slaughter</i>	3/23/2010		



Supplemental Report

Report No.: UT-10-053
Page: 4 of 4

Summary No.: 1-E11-3806

Examiner: <u>Smith, Kenneth</u> <i>KRS</i>	Level: <u>III-PDI</u>	Reviewer: <u>James Delbusso Level III</u> <i>JDS</i>	Date: <u>3/22/2010</u>
Examiner: <u>N/A</u>	Level: <u>N/A</u>	Site Review: <u>Damon Priestley NDE Level III</u> <i>DP</i>	Date: <u>3/22/2010</u>
Other: <u>N/A</u>	Level: <u>N/A</u>	ANII Review: <u>Nancy C. Ritchie-Slaughter</u> <i>NRS</i>	Date: <u>3/23/2010</u>

Comments: Reference Scan Plan WDI-PJF-1304723-EPP-004, Rev. 0 (Table Parameters Below)

The 70 Degree Exam prescribed by EPRI model Report # IR-2010-396 was not performed. Due to excessive R-Dimensions and Metal Paths, it was deemed impractical and ineffective as the beam would have to complete as many as eight (8) legs (bounces) in order to cover the volume. This is a result of the relatively thin shell wall in contrast to the thicker walled nozzle.

PGN's conclusion of the 70 degree shell-side prescription in IR-2010-396 was discussed with the EPRI Project Manager that was responsible for the IR. The EPRI project manager agreed with the conclusion that this angle would be ineffective based on beam spread at such distances.

Sketch or Photo: K:\Shared\ldeallB118R1 Scanned Data\UT-10-053.jpg

Parameters	Xducer # 1	Xducer # 2
Refracted Angle	55°	60°
Incident Angle	70°	70°
Skew Angle	$\pm 123^\circ$	$\pm 118^\circ$ to 132°
Misorientation Angle (Max)	9°	22°
Inspection Zone	A	A
Scan Area ("Z")	$29.90''$ - $30.42''$	$29.87''$ - $30.60''$
Scan Area ("Z") from shell OD surface	$2.15''$ - $2.66''$	$2.12''$ - $2.85''$
Min. Metal Path	$\sim 7.09''$	$\sim 6.89''$
Max. Metal Path	$\sim 8.11''$	$\sim 10.23''$

Parameters	Xducer # 3	Xducer # 4
Refracted Angle	65°	70°
Incident Angle	70°	70°
Skew Angle	$\pm 128^\circ$	$\pm 17^\circ$ to 37°
Misorientation Angle (Max)	22°	14°
Inspection Zone	A	A
Scan Area ("Z / R")	$Z = 28.87''$ - $30.17''$	$R = 14.91''$ - $24.97''$
Scan Area ("Z / R") from shell OD or Boss OD surface	$Z = 2.12''$ - $2.42''$	$R = 3.03''$ - $13.11''$
Min. Metal Path	$\sim 6.80''$	$\sim 10.68''$
Max. Metal Path	$\sim 9.57''$	$\sim 23.07''$



UT Calibration/Examination

Site/Unit:	BNP / 1	Procedure:	NDEP-0437	Outage No.:	B121R1	
Summary No.:	1-E11-3483	Procedure Rev.:	8	Report No.:	UT-16-036	
Workscope:	ISI	Work Order No.:	13472397	Page:	1 of 7	
Code:	2001 Edition, 2003 Addenda	Cat./Item:	C-F-2/C5.51	Location:	REACTOR BUILDING	
Drawing No.:	C-24004 Sht. 072-1	Description: VALVE 1-E11-F031D TO PIPE				
System ID:	2045					
Component ID:	1E1145-15-FW58	Size/Length:	16"/50.265"	Thickness/Diameter: CS/0.375"/16"		
Limitations:	Yes - Valve	Start Time:	1228	Finish Time:	1407	
Instrument Settings		Search Unit				
Serial No.:	13G00172	Serial No.:	SC3094	Cal. Checks	Time Date	
Manufacturer:	GE	Manufacturer:	GE	Initial Cal.	0820 3/15/2016	
Model:	USN 60 SW	Linearity:	L-16-005	Inter. Cal.	N/A	
Delay:	3.5866	Range:	1.00"	Inter. Cal.	1328 3/15/2016	
M'tl Cal/Vel:	0.1266	Pulser Type:	Square	Inter. Cal.	N/A	
Damping:	500 Ohms	Reject:	0%	Measured Angle:	44 Mode: Shear	
PRF:	Auto High	SU Freq.:	5 MHz	Exam Angle:	45 Squint Angle: N/A	
Frequency:	5.0 MHz	Rectify:	Fullwave	Cal. Batch:	14H073	
Voltage:	450	Pulse Width:	100	Type:	Ultragel II	
Ax. Gain (dB):	21.0	Circ. Gain (dB):	21.0	Mfg.:	Sonotech, Inc.	
1 Screen Div. =	0.1	in. of	Sound Path	Wedge Style:	MSWQC	
Calibration Block		Search Unit Cable				
Cal. Block No.:	CB-02-85	Type:	RG-174	Length:	6' No. Conn.: 0	
Thickness:	0.5" - 2.0"	Upstream	<input checked="" type="checkbox"/>	Downstream	<input checked="" type="checkbox"/> Scan dB: 28.0	
Cal. Blk. Temp.:	73	Temp. Tool:	MCNDE40135	CW	<input checked="" type="checkbox"/> CCW <input checked="" type="checkbox"/> Scan dB: 28.0	
Comp. Temp.:	76	Temp. Tool:	MCNDE40135	Exam Surface:	O.D.	
Recordable Indication(s): Yes <input type="checkbox"/> No <input checked="" type="checkbox"/>		(If Yes, Ref. Attached Ultrasonic Indication Report.)				
Results:	Sat <input checked="" type="checkbox"/>	Unsat <input type="checkbox"/>	Eval <input type="checkbox"/>	Comments: N/A		
Percent Of Coverage Obtained > 90%: 87.6% Reviewed Previous Data: Yes						

Examiner	Level	II-N	Signature	Date	Reviewer	Signature	Date
Jaschke, Ryan A.				3/15/2016	Steven Dan L III		3/16/16
Examiner	Level	N/A	Signature	Date	Site Review	Signature	Date
N/A					John Sullivan		3.16.16
Other	Level	N/A	Signature	Date	ANII Review	Signature	Date
				3/16/16	David M. Reynolds		3-16-2016

UT Calibration/Examination



Site/Unit:	BNP / 1	Procedure:	NDEP-0437	Outage No.:	B121R1
Summary No.:	1-E11-3483	Procedure Rev.:	8	Report No.:	UT-16-036
Workscope:	ISI	Work Order No.:	13472397	Page:	2 of 7
Code:	2001 Edition, 2003 Addenda	Cat./Item:	C-F-2/C5.51	Location:	REACTOR BUILDING
Drawing No.:	C-24004 Sht. 072-1	Description: VALVE 1-E11-F031D TO PIPE			
System ID:	2045				
Component ID:	1E1145-15-FW58	Size/Length: 16"/50.265" Thickness/Diameter: CS/0.375"/16"			
Limitations:	Yes - Valve	Start Time: 1228 Finish Time: 1407			

Instrument Settings		Search Unit			Axial Orientated Search Unit						
Serial No.:	13G00172	Serial No.:	SC2843		Cal. Checks	Time	Date	Calibration Reflector	Signal Amplitude %	Sweep Division	Sound Path
Manufacturer:	GE	Manufacturer:	GE		Initial Cal.	0826	3/15/2016	0.5" Notch	80	6.1	0.911"
Model:	USN 60 SW	Linearity:	L-16-005		Size:	0.25"	Model: Comp-G				
Delay:	4.745	Range:	1.5"		Freq.:	5 MHz	Center Freq.: N/A				
M'tl Cal/Vel:	0.1268	Pulser Type:	Square		Exam Angle:	60	Squint Angle: N/A				
Damping:	500 Ohms	Reject:	0%		Measured Angle:	60	Mode: Shear				
PRF:	Auto High	SU Freq.:	5 MHz		Exit Point:	0.3"	# of Elements: 1	Cal. Batch:	14H073		
Frequency:	5.0 MHz	Rectify:	Fullwave		Config.:	Single	Focus: N/A	Type:	Ultragel II		
Voltage:	450	Pulse Width:	100		Shape:	Round	Contour: Flat	Mfg.:	Sonotech, Inc.		
Ax. Gain (dB):	40.0	Circ. Gain (dB):	N/A		Wedge Style:	MSWQC		Exam Batch:	14H073		
1 Screen Div. =	.15	in. of Sound Path			Search Unit Cable			Type:	Ultragel II		
Cal. Block No.:	CB-02-85				Type:	RG-174	Length: 6'	No. Conn.:	0	Mfg.:	Sonotech, Inc.
Calibration Block				Scan Coverage				Circumferential Orientated Search Unit			
Cal. Block No.:	CB-02-85				Upstream <input checked="" type="checkbox"/>	Downstream <input checked="" type="checkbox"/>	Scan dB: 45.0	Calibration Reflector	Signal Amplitude %	Sweep Division	Sound Path
Thickness:	0.5" - 2.0"		Flat		CW <input type="checkbox"/>	CCW <input type="checkbox"/>	Scan dB: N/A				
Cal. Blk. Temp.:	73		Temp. Tool: MCNDE40135		Exam Surface:	O.D.		Serial No.:	14-3684		
Comp. Temp.:	76		Temp. Tool: MCNDE40135		Surface Condition:	Ground		Type:	Rompas		
Recordable Indication(s):	Yes <input type="checkbox"/> No <input checked="" type="checkbox"/>		(If Yes, Ref. Attached Ultrasonic Indication Report.)								
Results:	Sat <input checked="" type="checkbox"/>		Unsat <input type="checkbox"/>		Eval <input type="checkbox"/>		Comments: N/A				
Percent Of Coverage Obtained > 90%: 87.6%				Reviewed Previous Data: Yes				Reference/Simulator Block			

Examiner	Level	II-N	Signature	Date	Reviewer	Signature	Date
Jaschke, Ryan A.				3/15/2016	Steven Dean L-III		3/16/16
Examiner	Level	N/A	Signature	Date	Site Review	Signature	Date
N/A					John Sullivan		3.16.16
Other	Level	N/A	Signature	Date	ANII Review	Signature	Date
N/A				3/16/16	David M. Reynolds		3-16-2016



UT Calibration Examination

Site/Unit:	BNP / 1	Procedure:	NDEP-0408	Outage No.:	B121R1					
Summary No.:	1-E11-3483	Procedure Rev.:	14	Report No.:	UT-16-036					
Workscope:	ISI	Work Order No.:	13472397	Page:	3 of 7					
Code:	2001 Edition, 2003 Addenda	Cat./Item:	C-F-2/C5.51	Location:	REACTOR BUILDING					
Drawing No.:	C-24004 Sht. 072-1	Description: VALVE 1-E11-F031D TO PIPE								
System ID:	2045	Size/Length:	16"/50.265"	Thickness/Diameter:	CS/0.375"/16"					
Component ID:	1E1145-15-FW58	Start Time:	1228	Finish Time:	1407					
Limitations:	Yes - Valve									
Instrument Settings		Search Unit		Axial Orientated Search Unit						
Serial No.:	13G00172	Serial No.:	57463-1708	Cal. Checks	Time	Date	Calibration Reflector	Signal Amplitude %	Sweep Division	Sound Path
Manufacturer:	GE	Manufacturer:	KBA	Initial Cal.	0730	3/15/2016	0.250	80	2.5	0.254"
Model:	USN 60 SW	Linearity:	L-16-005	Inter. Cal.	N/A		0.500	80	5.0	0.500"
Delay:	9.0334	Range:	1.00"	Inter. Cal.	1228	3/15/2016				
M'tl Cal/Vel:	0.2343	Pulser Type:	Square	Exam Angle:	0	Squint Angle:	N/A			
Damping:	500 Ohms	Reject:	0%	Measured Angle:	N/A	Mode:	Long.			
PRF:	Auto High	SU Freq.:	4.0 MHz	Exit Point:	N/A	# of Elements:	2	Cal. Batch:	14H073	Couplant
Frequency:	4.0 MHz	Rectify:	Fullwave	Config.:	Dual	Focus:	N/A	Type:	Ultragel II	
Voltage:	450	Pulse Width:	130	Shape:	Rect.	Contour:	Flat	Mfg.:	Sonotech, Inc.	
Ax. Gain (dB):	*	Circ. Gain (dB):	N/A	Wedge Style:	Integral			Exam Batch:	14H073	
Search Unit Cable		Type: RG-174 Length: 6' No. Conn.: 0		Type:	Ultragel II					
1 Screen Div. =	0.1	in. of Sound Path		Mfg.:	Sonotech, Inc.					
Calibration Block		Scan Coverage		Reference Block						
Cal. Block No.:	12-4228	Upstream <input checked="" type="checkbox"/>	Downstream <input checked="" type="checkbox"/>	Scan dB:	*	Serial No.:	14-3684			
Thickness:	0.250" - 1.00"	Dia.:	Flat	CW <input type="checkbox"/>	CCW <input type="checkbox"/>	Scan dB:	N/A			
Cal. Blk. Temp.:	70	Temp. Tool:	MCNDE40135	Exam Surface:	O.D.	Type:	Rompas			
Comp. Temp.:	76	Temp. Tool:	MCNDE40135	Surface Condition:	Ground					
Recordable Indication(s): Yes <input type="checkbox"/> No <input checked="" type="checkbox"/>		(If Yes, Ref. Attached Ultrasonic Indication Report.)				Comments: T & C - For Information only. *Gain adjusted to 80%.				
Results: Sat <input checked="" type="checkbox"/> Unsat <input type="checkbox"/> Eval <input type="checkbox"/>										
Percent Of Coverage Obtained > 90%: N/A		Reviewed Previous Data: Yes								
Examiner	Level	II-N	Signature	Date	Reviewer	Signature		Date		
Jaschke, Ryan A.				3/15/2016	Steven Dean L-III			3/16/16		
Examiner	Level	N/A	Signature	Date	Site Review	Signature		Date		
N/A					John Sullivan			3.16.16		
Other	Level	N/A	Signature	Date	ANII Review	Signature		Date		
Z. Cline				3/16/16	David M. Reynolds & David M. Reynolds			3-16-2016		



Supplemental Report

Report No.: UT-16-036

Page: 4 of 7

Summary No.: 1-E11-3483

Examiner: Jaschke, Ryan A.

Level: II-N

Reviewer: Steven Dean L-III

Date: 3/16/16

Examiner: N/A

Level: N/A

Site Review:

Date: 3.16.16

Other: N/A


Level: N/A

ANII Review: David M. Reynolds

Date: 3-16-2016


Comments: T & C

Sketch or Photo: K:\Shared\Integrated Inspections\B121R1\Contours & Profiles\1E1145-15-FW58_Page_1.jpg



Enclosure 2, BSEP, Unit 1 4th ISI Interval Limited
NDE Data and Coverage Plots

FLOW



AXIAL COVERAGE = 100%

COVERAGE PLOT

CIRC COVERAGE =

$$0.145 \times 1.5 = 0.2175 \text{ "}^3 \text{ (TOTAL VOLUME)}$$

$$0.3 \times 0.18 = 0.054 \text{ "}^3 \text{ (MISSING CIRC VOLUME)}$$

$$0.054 \div 0.2175 = 0.248$$

$$0.248 \times 100 = 24.8\%$$

$$100\% - 24.8\% = 75.2\%$$


$$A_1 = 100\%$$

$$A_2 = 100\%$$

$$C_1 = 75.2\%$$

$$C_2 = 75.2\%$$

TOTAL COVERAGE OBTAINED = 87.6%





Enclosure 2
BSEP, Unit 1 4th ISI Interval Limited NDE Data and Coverage Plots
UT Calibration/Examination

Site/Unit:	BNP	/	1	Procedure:	NDEP-0437	Outage No.:	B121R1
Summary No.:	1-E11-3616			Procedure Rev.:	8	Report No.:	UT-16-038
Workscope:	ISI			Work Order No.:	13472399	Page:	1 of 9
Code:	2001 Edition, 2003 Addenda			Cat./Item:	C-F-2/C5.51	Location:	REACTOR BUILDING
Drawing No.:	C-24004 Sht. 077-1			Description: PIPE TO VALVE 1-E11-F017B			
System ID:	2045			Size/Length:	24" / 75.398"	Thickness/Diameter:	CS / 0.562" / 24"
Component ID:	1E1173-30-FW102			Start Time:	2300	Finish Time:	0100
Limitations:	Yes - single sided exam due to valve						
Instrument Settings Serial No.: 0242D3 Search Unit Manufacturer: GE Serial No.: 01VT81 Model: USN-60 SW Linearity: L-16-009 Delay: 4.7878 Range: 3.0" M'tl Cal/Vel: 0.1244 Pulser Type: Square Damping: 500 Ohms Reject: 0% PRF: Auto High SU Freq.: 2.25 MHz Frequency: 2.25 MHz Rectify: Fullwave Voltage: 450 Pulse Width: 220				Search Unit Size: 0.375" Model: Comp - G Freq.: 2.25 MHz Center Freq.: N/A Exam Angle: 45 Squint Angle: N/A Measured Angle: 43 Mode: Shear Exit Point: 0.3" # of Elements: 1 Config.: Single Focus: N/A Shape: Round Contour: Flat Wedge Style: MSWQC			
				Couplant Couplant: Ultragel II Mfg.: Sonotech, Inc. Exam Batch: 14H073			
Ax. Gain (dB): 16.5 Circ. Gain (dB): 16.5 1 Screen Div. = 0.3 in. of Sound Path				Search Unit Cable Type: RG-174 Length: 6' No. Conn.: 0 Mfg.: Sonotech, Inc.			
				Scan Coverage Upstream <input checked="" type="checkbox"/> Downstream <input type="checkbox"/> Scan dB: 21.5 CW <input checked="" type="checkbox"/> CCW <input checked="" type="checkbox"/> Scan dB: 28.5			
Calibration Block Cal. Block No.: CB-02-85 Thickness: 0.5" - 2.0" Dia.: Flat Cal. Blk. Temp.: 73 Temp. Tool: G502480 Comp. Temp.: 83 Temp. Tool: G502480				Reference Block Exam Surface: OD Surface Condition: Ground Serial No.: 96-6521 Type: Rompas			
Recordable Indication(s): Yes <input type="checkbox"/> No <input checked="" type="checkbox"/> (If Yes, Ref. Attached Ultrasonic Indication Report.) Results: Sat <input checked="" type="checkbox"/> Unsat <input type="checkbox"/> Eval <input type="checkbox"/> NCR # 013472399 Percent Of Coverage Obtained > 90%: 87.3% Reviewed Previous Data: Yes				Comments: Actual thickness is different from thickness listed. Adjusted screen range during exam, due to varying thickness. NCR # 021199.			
Examiner	Level	II-N	Signature	Date	Reviewer	Signature	Date
Nahory, W. Jason				3/1/2016	Steven D. L. III		3/16/16
Examiner	Level	N/A	Signature	Date	Site Review	Signature	Date
N/A					J. Sullivan		3.16.16
Other	Level	N/A	Signature	Date	ANII Review	Signature	Date
R. Cline				3/16/16	David M. Reynolds		3-16-2016

Enclosure 2

BSEP, Unit 1 4th ISI Interval Limited NDE Data and Coverage Plots

UT Calibration/Examination

Site/Unit:	BNP / 1	Procedure:	NDEP-0437	Outage No.:	B121R1
Summary No.:	1-E11-3616	Procedure Rev.:	8	Report No.:	UT-16-038
Workscope:	ISI	Work Order No.:	13472399	Page:	2 of 9

Code:	2001 Edition, 2003 Addenda	Cat./Item:	C-F-2/C5.51	Location:	REACTOR BUILDING
Drawing No.:	C-24004 Sht. 077-1	Description: PIPE TO VALVE 1-E11-F017B			
System ID:	2045				
Component ID:	1E1173-30-FW102	Size/Length: 24"/75.398"			Thickness/Diameter: CS/0.562"/24"
Limitations:	Yes - single sided exam due to valve	Start Time: 2300			Finish Time: 0100

Instrument Settings		Search Unit			Axial Orientated Search Unit			
Serial No.:	0242D3	Serial No.:	01065Y		Cal. Checks	Time	Date	
Manufacturer:	GE	Manufacturer:	KBA		Initial Cal.	1925	3/15/2016	
Model:	USN-60 SW	Linearity:	L-16-009		Inter. Cal.	N/A		
Delay:	7.0628	Range:	3.5"		Inter. Cal.	0033	3/16/2016	
M'II Cal/Vel:	0.1265	Pulser Type:	Square		Inter. Cal.	N/A		
Damping:	500 Ohms	Reject:	0%		Measured Angle:	59	Mode: Shear	
PRF:	Auto High	SU Freq.:	2.25 MHz		Exam Angle:	60	Squint Angle: N/A	
Frequency:	2.25 MHz	Rectify:	Fullwave		Exit Point:	0.35"	# of Elements: 1	
Voltage:	450	Pulse Width:	220		Config.:	Single	Focus: N/A	
Ax. Gain (dB):	35.6	Circ. Gain (dB):	N/A		Shape:	Round	Contour: Flat	
1 Screen Div. = .35 in. of Sound Path		Search Unit Cable			Wedge Style:	MSWQC		
Calibration Block		Scan Coverage			Type:	Ultragel II		
Cal. Block No.:	CB-02-85		Upstream <input checked="" type="checkbox"/>	Downstream <input type="checkbox"/>	Exam Batch:	14H073		
Thickness:	0.5" - 2.0"		Dia.:	Flat	Type:	Ultragel II		
Cal. Blk. Temp.:	73		Temp. Tool:	G502480	Mfg.:	Sonotech, Inc.		
Comp. Temp.:	83		Temp. Tool:	G502480	Type:	Rompas		
Recordable Indication(s):	Yes <input type="checkbox"/> No <input checked="" type="checkbox"/>		(If Yes, Ref. Attached Ultrasonic Indication Report.)					
Results:	Sat <input checked="" type="checkbox"/> Unsat <input type="checkbox"/> Eval <input type="checkbox"/>		Comments: Actual thickness is different from thickness listed. NCR # 0211199.					
Percent Of Coverage Obtained > 90%:	87.3%		Reviewed Previous Data:	Yes				

Examiner	Level	II-N	Signature	Date	Reviewer	Signature	Date
Nahory, W. Jason				3/16/2016	Steven Dean L-III		
Examiner	Level	N/A	Signature	Date	Site Review		
N/A					John Sullivan		
Other	Level	N/A	Signature	Date	ANII Review		
R. Cline + 20e				3/16/16	David M. Reynolds		

Enclosure 2

BSEP, Unit 1 4th ISI Interval Limited NDE Data and Coverage Plots

UT Calibration/ExaminationNuclear
Generation
Group

Site/Unit:	BNP	/	1	Procedure:	NDEP-040B	Outage No.:	B121R1
Summary No.:	1-E11-3616			Procedure Rev.:	14	Report No.:	UT-16-03B
Workscope:	ISI			Work Order No.:	13472399	Page:	3 of 9
Code:	2001 Edition, 2003 Addenda			Cat./Item:	C-F-2/C5.51	Location:	REACTOR BUILDING
Drawing No.:	C-24004 Sht. 077-1			Description:	PIPE TO VALVE 1-E11-F017B		
System ID:	2045			Size/Length:	24"/75.398"	Thickness/Diameter:	CS/0.562"/24"
Component ID:	1E1173-30-FW102			Start Time:	2300	Finish Time:	0100
Limitations:	Yes - single sided exam due to valve						
Instrument Settings Serial No.: 0242D3 Search Unit Manufacturer: GE Serial No.: 15100G9H Model: USN-60 SW Linearity: L-16-009 Delay: 0.5575 Range: 1.500" M'tl Cal/Vel: 0.2338 Pulser Type: Square Damping: 500 Ohms Reject: 0% PRF: Auto High SU Freq.: 2.25 MHz Frequency: 2.25 MHz Rectify: Fullwave Voltage: 280 Pulse Width: 220 Ax. Gain (dB): Circ. Gain (dB): N/A 1 Screen Div. = .15 in. of Sound Path				Search Unit Manufacturer: GE Size: 0.25" Model: Benchmark Freq.: 2.25 MHz Center Freq.: N/A Exam Angle: 0 Squint Angle: N/A Measured Angle: N/A Mode: Shear Exit Point: N/A # of Elements: 1 Config.: Single Focus: N/A Shape: Round Contour: Flat Wedge Style: Integral			
				Couplant Cal. Batch: 14H073 Type: Ultralag II Mfg.: Sonotech, Inc.			
				Search Unit Cable Type: RG-174 Length: 6' No. Conn.: 0			
				Scan Coverage Upstream <input checked="" type="checkbox"/> Downstream <input checked="" type="checkbox"/> Scan dB: * CW <input type="checkbox"/> CCW <input type="checkbox"/> Scan dB: N/A			
				Reference Block Serial No.: 96-6521			
				Cal. Block No.: 12-4228 Thickness: 0.250" - 1.00" Dia.: Flat Cal. Blk. Temp.: 73 Temp. Tool: G502480 Comp. Temp.: 83 Temp. Tool: G502480 Recordable Indication(s): Yes <input type="checkbox"/> No <input checked="" type="checkbox"/> (If Yes, Ref. Attached Ultrasonic Indication Report.) Results: Sat <input checked="" type="checkbox"/> Unsat <input type="checkbox"/> Eval <input type="checkbox"/>			
				Comments: T & C - For information only. *Adjusted gain to maintain 80% FSH.			
Percent Of Coverage Obtained > 90%: N/A Reviewed Previous Data: Yes							

Examiner	Level	II-N	Signature	Date	Reviewer	Signature	Date
Nahory, W. Jason				3/16/2016	Steven Dean L-III		3/16/16
Examiner	Level	N/A	Signature	Date	Site Review	Signature	Date
N/A					John Sullivan		3.16.16
Other	Level	N/A	Signature	Date	ANII Review	Signature	Date
ZIA				3/16/16	David m. Reynolds		3-16-2016



Supplemental Report

Report No.: UT-16-038

Page: 4 of 9

Summary No.: 1-E11-3616

Examiner: Nahory, W. Jason

Level: II-N

Reviewer: Steven Dorn, L-III

Date: 3/16/16

Examiner: N/A

Level: N/A

Site Review:

Date: 3.16.16

Other: N/A


Level: N/A

ANII Review: David M. Reynolds, David M. Reynolds

Date: 3-16-2016

Comments: Thickness and contour

Sketch or Photo: K:\Shared\Integrated Inspections\B121R1\Contours & Profiles\1E1173-30-FW102_Page_1x.jpg

VALVEPIPE

Enclosure 2, BSEP, Unit 1 4th ISI Interval Limited NDE Data and Coverage Plots

DOWNSTREAM

$$0.43'' \times 0.215'' = 0.092 \text{ in}^2 \text{ OBTAINED}$$
$$0.87'' \times 0.215'' = 0.187 \text{ in}^2 \text{ TOTAL}$$
$$0.092 / 0.187 = 49.2\%$$


UPSTREAM

100% COVERAGE OBTAINED

$$(49.2 + 100) / 2 = \boxed{74.6\%}$$

VALVE

PIPE




**Supplemental Report**Report No.: UT-16-038Page: 6 of 9Summary No.: 1-E11-3616Examiner: Nahory, W. JasonLevel: II-NReviewed by: D.B. King, UT Level II Date: 3/16/16Examiner: N/ALevel: N/AReviewer: Steven Dean - III Date: 3/16/16Other: NAT LUCINE + LCLevel: N/ASite Review: John Sullivan Date: 3.16.16ANII Review: David M. Reynolds / Sam M. Reynolds Date: 3-16-2016

Comments: Axial scan. 100% coverage obtained.

Sketch or Photo: K:\Shared\Integrated Inspections\B121R1\Contours & Profiles\1E1173-30-FW102_Page_3.jpg

$$[100\% \text{ (AXIAL)} + 74.6\% \text{ (CIRC)}] / 2 = 87.3\% \text{ TOTAL}$$

AGGREGATE COVERAGE

VALVEPIPE



Enclosure 2
BSEP, Unit 1 4th ISI Interval Limited NDE Data and Coverage Plots
UT Calibration Examination

Site/Unit:	BNP / 1	Procedure:	NDEP-0437		Outage No.:	B118R1		
Summary No.:	1-E21-4015	Procedure Rev.:	003		Report No.:	UT-10-019		
Workscope:	ISI	Work Order No.:	1549261		Page:	1	of 2	
Code:	2001 Edition, 2003 Addenda	Cat./Item:	C-F-2/C5.51		Location:	See ISO		
Drawing No.:	C-24004 Sht. 98-1	Description:	VALVE TO PIPE					
System ID:	2035				Size/Length:	14"/43.982"	Thickness/Diameter:	0.375"/14"
Component ID:	1E215-39-FW4				Start Time:	1314	Finish Time:	1334
Limitations:	Single sided exam due to pipe to valve circ limitation due to valve.							
Instrument Settings Serial No.: 01H1LT Manufacturer: Krautkramer Model: USN 60 SW Delay: 3.5988 Range: 1.0" M'tl Cal/Vel: .1277 Pulser: Square Damping: 500 Ω Reject: 0% Rep. Rate: Auto High Freq.: 5.0 Filter: N/A Mode: Dual Off Voltage: 450 Other: PW = 100 Ax. Gain (dB): 21.5 Circ. Gain (dB): N/A 10 Screen Div. = 1 in. of Sound Path Linearity Report No.: L-10-006			Search Unit Serial No.: 00M XC7 Manufacturer: KBA Size: .25" Shape: Round Freq.: 5.0 MHz Style: Comp-G Exam Angle: 45° # of Elements: 1 Mode: Shear Measured Angle: 45° Wedge Style: MSWQC			Cal. Checks Initial Cal. 1110 3/9/2010 Inter. Cal. 1313 3/9/2010 Inter. Cal. 1335 3/9/2010 Inter. Cal. 1505 3/9/2010 Couplant Cal. Batch: 09225 Type: Ultralag II Mfg.: Sonotech, Inc. Search Unit Cable Type: RG-174 Length: 6' No. Conn.: 0 Exam Batch: 09225 Type: Ultralag II Mfg.: Sonotech, Inc.		
Calibration Block Cal. Block No.: CB-02-52 Thickness: 2.0" Dia.: N/A Cal. Blk. Temp.: 75° Temp. Tool: 95500813 Comp. Temp.: 71° Temp. Tool: 95500813			Upstream <input type="checkbox"/> Downstream <input checked="" type="checkbox"/> Scan dB: 33.5 CW <input checked="" type="checkbox"/> CCW <input checked="" type="checkbox"/> Scan dB: 36 Exam Surface: OD Surface Condition: As Found			Reference Block Serial No.: A10474 Type: CS Rompas		
Recordable Indication(s): Yes <input checked="" type="checkbox"/> No <input type="checkbox"/> (If Yes, Ref. Attached Ultrasonic Indication Report.)						Comments: Rectify = Fullwave Indications from previous data verified (Report # 39-FW4 Dated 4/18/2001), no change observed.		
Results:	Sat <input checked="" type="checkbox"/>	Unsat <input type="checkbox"/>	Eval <input type="checkbox"/>					
Percent Of Coverage Obtained > 90%: Yes- 90%			Reviewed Previous Data:	Yes				

Examiner	Level	II-PDI	Signature	Date	Reviewer	Signature	Date
Tauchen, Ryan J.				3/9/2010	James Delbusso Level III		3/10/2010
Examiner	Level	N/A	Signature	Date	Site Review	Signature	Date
N/A					Damon Priestley PGN NDE Coordinator		3/15/2010
Other	Level	N/A	Signature	Date	ANII Review	Signature	Date
N/A					Nancy C. Ritchie-Slaughter		3/15/2010

Enclosure 2

BSEP, Unit 1 4th ISI Interval Limited NDE Data and Coverage Plots

UT Calibration Examination



Site/Unit: BNP / 1 Procedure: NDEP-0437 Outage No.: B118R1
 Summary No.: 1-E21-4015 Procedure Rev.: 003 Report No.: UT-10-019
 Workscope: ISI Work Order No.: 1549261 Page: 2 of 2



Code: 2001 Edition, 2003 Addenda Cat./Item: C-F-2/C5.51 Location: See ISO
 Drawing No.: C-24004 Sht. 98-1 Description: VALVE TO PIPE
 System ID: 2035
 Component ID: 1E215-39-FW4 Size/Length: 14"/43.982" Thickness/Diameter: 0.375"/14"
 Limitations: °x248 Start Time: 1337 Finish Time: 1357

Instrument Settings.		Search Unit			Axial Orientated Search Unit						
Serial No.:	01H1LT	Serial No.:	00MM7N	Cal. Checks	Time	Date	Calibration Reflector	Signal Amplitude %	Sweep Division	Sound Path	
Manufacturer:	Krautkramer	Manufacturer:	KBA	Initial Cal.	1110	3/9/2010	.50" Notch	80%	7.1	.895"	
Model:	USN 60 SW	Size:	.25"	Shape:	Round						
Delay:	5.2522	Range:	1.25"	Freq.:	5.0 MHz	Style:	Comp-G				
M'tl Cal/Vel:	0.1283	Pulser:	Square	Exam Angle:	60°	# of Elements:	1				
Damping:	500 Ω	Reject:	0%	Mode:	Shear						
Rep. Rate:	Auto High	Freq.:	5.0	Measured Angle:	60°			Couplant			
Filter:	N/A	Mode:	Dual Off	Wedge Style:	MSWQC			Cal. Batch:	09225		
Voltage:	450	Other:	PW = 100	Type:	Search Unit Cable			Type:	Ultragel II		
Ax. Gain (dB):	36.5	Circ. Gain (dB):	N/A	Length:	6'	No. Conn.:	0	Mfg.:	Sonotech, Inc.		
10 Screen Div. =	1.25	in. of Sound Path		Type:	RG-174			Exam Batch:	09225		
Linearity Report No.:	L-10-006			Scan Coverage				Type:	Ultragel II		
Cal. Block No.:	CB-02-52			Upstream <input type="checkbox"/> Downstream <input checked="" type="checkbox"/> Scan dB: 48				Mfg.:	Sonotech, Inc.		
Thickness:	2.0"	Dia.:	0	CW <input type="checkbox"/> CCW <input type="checkbox"/> Scan dB: N/A				Reference Block			
Cal. Blk. Temp.:	75°	Temp. Tool:	95500813	Exam Surface:	OD			Serial No.:	A10474		
Comp. Temp.:	71°	Temp. Tool:	95500813	Surface Condition:	As Found			Type:	CS Rompas		
Recordable Indication(s):	Yes <input checked="" type="checkbox"/>	No <input type="checkbox"/>	(If Yes, Ref. Attached Ultrasonic Indication Report.)								
Results:	Sat <input checked="" type="checkbox"/>	Unsat <input type="checkbox"/>	Eval <input type="checkbox"/>	Comments: Rectify = Fullwave							
Indications from previous data verified (Report # 39-FW4 Dated 4/18/2001), no change observed.											

Examiner	Level	II-PDI	Signature	Date	Reviewer	Signature	Date
Tauchen, Ryan J.				3/9/2010	James Delbusso Level III		3/12/2010
Examiner	Level	N/A	Signature	Date	Site Review	Signature	Date
N/A					Damon Priestley PGN NDE Coordinator		3/15/2010
Other	Level	N/A	Signature	Date	ANII Review	Signature	Date
N/A					Nancy C. Ritchie-Slaughter		3/15/2010

Enclosure 2
BSEP, Unit 1 4th ISI Interval Limited NDE Data and Coverage Plots

NDE-30 REV 1

CAROLINA POWER & LIGHT COMPANY NDE REPORT/SUMMARY		Report No. <u>39-FW4</u> Page <u>1</u> Of <u>9</u>
Plant/Unit: BNP / Unit 1	Component(s) or Item(s) Examined <u>1E215-39-FW4</u>	
Procedure(s) Used: NDEP-301, NDEP-1011, OSP-00-001		
An MT inspection was performed on the above listed component, no indications where found.		
Ultrasonic examination was performed on the above listed weld, using a 45* and 60* shear wave. One indication was recorded with the 45 degree exam that was not identified in prior exams. This indication plots to the intersection of the heat-affected zone and weld and is not ID or OD connected. The RT film for this weld was reviewed and 3 pores of porosity were located in this area.		
Previous data for this weld was reviewed prior to this examination. Examination coverage was 100% for the MT examination and 90% for the UT examination.		
Reported By 	Level 	Date <u>4/18/01</u>
Reviewed By 	Title <u>QC SUPERVISOR</u>	Date <u>4/20/2001</u>

NGGM-PM-0011 APPENDIX A

Enclosure 2
BSEP, Unit 1 4th ISI Interval Limited NDE Data and Coverage Plots

QA MT-2 Rev 4

RECEIVED BY BNP

FEB 15 1999



Page 2 of 9

MAGNETIC PARTICLE NDE REPORT

Project: <u>BNP RNP HNP WR/JO 19769</u>		Unit: <u>1 2</u>	Date: <u>4/16/01</u>		
Drawing/ISO <u>C 24004 SH 98-1</u>	System <u>CS-A Loop 2035</u>	Line <u>39-14-152</u>	Identification Number <u>IE215-39-FW4</u>		
Design Class/Category <u>ASME CLASS II</u>	Acceptance Standard <input checked="" type="checkbox"/> ASME III <input type="checkbox"/> VIII <input type="checkbox"/> XI <input type="checkbox"/> Other <u>SECT XI</u>	<u>1989 ASME ARTICLE 3000</u>			
Mtl. Type <input checked="" type="checkbox"/> C/S <input type="checkbox"/> S/S <input type="checkbox"/> Other	Mtl. Thickness <u>.375"</u>	OD Length <u>14"</u>	Surface Finish: <input checked="" type="checkbox"/> Ground <input type="checkbox"/> As-Welded <input type="checkbox"/> Machined <input type="checkbox"/> Other		
PSI <input type="checkbox"/>	Stage of Mtg: <input type="checkbox"/> Final <input checked="" type="checkbox"/> N/A	Joint Design <input type="checkbox"/> N/A <input type="checkbox"/> BRN <input type="checkbox"/> BKS <input type="checkbox"/> Fillet <input type="checkbox"/> INS <input type="checkbox"/> Open BT <input type="checkbox"/> Socket <input type="checkbox"/> Other			
CP&L Equipment Identification Number <u>COIL #11</u>			Complete Following Equipment Info. if Subcontract MT Mfg. <u>N/A</u> Model <u>N/A</u> Serial No <u>N/A</u>		
<input checked="" type="checkbox"/> AC <input type="checkbox"/> DC	Prods <input type="checkbox"/> Yoke <u>Spacings 3" 6"</u>	Coil <input type="checkbox"/> Turns <u>N/A</u>	Heads <u>N/A</u>		
Amperage Used <u>FIXED</u>	Particles: <input checked="" type="checkbox"/> Red <input type="checkbox"/> Gray <input type="checkbox"/> Black <input type="checkbox"/> Fluorescent <input type="checkbox"/> Wet <input checked="" type="checkbox"/> Dry Fluorescent Concentration Test: <input type="checkbox"/> Settling test <input type="checkbox"/> Field Indicator				
Test Weight No. <u>WT-3</u>		Particle Mfg. <u>DETICK</u>	Batch No. <u>63-12158</u>		
L _o Location <u>RULE #1 UPSTREAM</u>	W _o Location <u>TOP & OF WELD</u>				
Indic. No.	L	Upstream W or Down	Type Indic. Round/Linear	Size Indic. Diameter/Length	Remarks
<u>N/A</u>	<u>N/A</u>	<u>N/A</u>	<u>N/A</u>	<u>N/A</u>	<u>NO INDICATIONS NOTED</u>
<p>Sketch & Remarks</p>					
<p>NOTE: Exam was performed on 4-17-01 and 4-19-01</p> <p>PIROMETER PY-15 CALC DATE: 2/16/01 DUE: 8/16/01</p>					
Examination Area Limitations (If none, so state) <u>NONE</u>					
Examination Coverage % (indicate percent of coverage) <u>100%</u>			Accept <input checked="" type="checkbox"/> Reject <input type="checkbox"/>		
Examiner <u>Ken Karpf</u>	Certification Level <u>II</u>		Date <u>4/19/01</u>		
Examiner <u>J. J. O'Brien</u>	Certification Level <u>II</u>		Date <u>4-19-01</u>		
If Applicable CP&L QA Review	Date	If Applicable ANII	A. A. Omb	Date <u>5-1-01</u>	

Enclosure 2
BSEP, Unit 1 4th ISI Interval Limited NDE Data and Coverage Plots

CPL UT-12 Rev 4												
COMPANY ULTRASONIC EXAMINATION DATA SHEET										Page <u>3</u> of <u>9</u>		
Plant: <u>BNP</u> Unit: <u>1</u> Calibration Sheet Number: <u>39-FW4 45, 39-FW4 45 1.5, 39-FW4 60</u>					Report Number: <u>39-FW4</u> Date: <u>4 / 18 / 01</u>							
Procedure: <u>OSP-00-001</u> Rev.: <u>0</u> System: <u>Core Spray</u> Weld ID: <u>1E215-39-FW4</u> Start Time: <u>09:40</u> Finish Time: <u>11:20</u>					Pipe Diameter: <u>14"</u> Scanning dB <u>28.0</u> Material Type <input checked="" type="checkbox"/> CS <input type="checkbox"/> SS <input type="checkbox"/> Other _____ Exam Surface <input type="checkbox"/> ID <input checked="" type="checkbox"/> OD Exam Surface Temp <u>75 deg F</u> Thermometer S/N: <u>PY-15A</u> L ₀ Location <u>Rule 1</u> W ₀ Location <u>Weld CL</u>							
Examination Scanning Directions 1. Angle Beam Transverse 2. Angle Beam Parallel A. Clockwise B. Counterclockwise ↵ 3. Angle Beam Parallel A. Clockwise B. Counterclockwise ↵ 4. Angle Beam Transverse 5. Base Metal L Wave 6. Weld Metal L Wave										Performed Exam Sens. 1. <input checked="" type="checkbox"/> N/A 2. <input checked="" type="checkbox"/> N/A 3. <input checked="" type="checkbox"/> N/A 4. <input checked="" type="checkbox"/> N/A 5. <input type="checkbox"/> N/A 6. <input type="checkbox"/> N/A		
Indication No.	L In. From Ref			W In. From Ref			Amplitude % Reference Sensitivity	Sweep Reading			Exam 1-6	Detection Angle
	L ₁	L _{MAX}	L ₂	W ₁	W _{MAX}	W ₂		SP ₁	SP _{MAX}	SP ₂		
1	N/A	1"	N/A	N/A	CL	N/A	60%	N/A	.28	N/A	1	45 Degree
Remarks: Scan 1 limited due to valve. Indication 1 could be seen with a 3T scan from exam 4 below recording levels. The length and through wall size is 1/8 " for indication 1 and it is not ID or OD connected. This PY-15 Cal Date 2/16/01 Cal Due 8/16/01												
Examined By: <u>J. P. Johnson</u>						Level: <u>II</u> Date: <u>04 / 18 / 01</u>						
Examined By: <u>J. P. Johnson</u>						Level: <u>IL</u> Date: <u>04 / 18 / 01</u>						
Reviewed By: <u>F. A. Smith</u>						Level: <u>ANT</u> Date: <u>5/12/01</u>						




NDE DRAWING ATTACHMENT

PROJECT	Bnp	JOB NO.	119769	UNIT 1 <input checked="" type="checkbox"/> 2 <input type="checkbox"/> 3 <input type="checkbox"/> 4 <input type="checkbox"/>	DATE
DRAWING	C 2900 S SHT 98-1	SYSTEM	CORE SPRAY	LINE	1E 215-39-FW4 WELD/ITEM NUMBER

PIPE

← Flow
Value

IND. #1

PROFILE - 15 FROM NES 1988 DATA

Larry Lewis 1 CTO. 4/18/01

4-18-01

RECEIVED BY BNP

FEB 12 1999


**SELECT
DISTRIBUTION**

NUCLEAR DOCUMENT CONTROL

Enclosure 2
BSEP, Unit 1 4th ISI Interval Limited NDE Data and Coverage Plots

CPL UT-13 Rev 4		Cal. Sheet No. 39-FW4 45 Page 5 of 9																			
ULTRASONIC CALIBRATION DATA SHEET																					
Plant: <u>BNP</u> Unit: <u>1</u>		Data Sheets: <u>39-FW4</u>																			
Procedure No.: <u>0SP-00-001</u> Rev.: <u>0</u> Couplant Brand: <u>ULTRAGEL II, 99-325</u> Cal Block Temp.: <u>75 Deg Therm.</u> SN: <u>PY-15</u>																					
Instrument Mfg.: <u>Krautkramer Branson</u> Model: <u>USK-7D</u> S/N: <u>32810-4012 (UI-2)</u>																					
Search Unit Mfg.: <u>K-B Aerotech</u> Model: <u>Comp-g</u> Shape: <u>Round</u> Size: <u>.25"</u> Freq.: <u>5.0 MHZ</u>																					
Search Unit : Angle/Mode: <u>45 s</u> Measured Angle: <u>45</u> Wedge Style : <u>MSWQC</u> S/N: <u>008NY6</u> <u>Single/Dual</u>																					
Cable Type: <u>RG174</u> Length: <u>6'</u> Connectors: <u>BNC-MDOT</u> Wedge Index to Front Meas.: <u>.35</u>																					
Calibration Block: Size: <u>14"</u> Thickness: <u>.375</u> S/N: <u>30B</u> Other Block: <u>IIW</u> S/N: <u>96-6500 (SW-9)</u>																					
<p>X = Axial Scan, O = Circ. Scan Scale Range: 0 - 10 = Metal Path <u>1"</u></p>	<p>Instrument Settings</p> <table style="width: 100%; border-collapse: collapse;"> <tr> <td style="width: 50%;">Reference Sensitivity</td> <td style="width: 50%;">Examination Sensitivity</td> </tr> <tr> <td>Gain - Axial Scan <u>20.5</u> dB</td> <td>Gain - Axial Scan <u>28.0</u> dB</td> </tr> <tr> <td>Gain - Circ. Scan <u>20.5</u> dB</td> <td>Gain - Circ. Scan <u>28.0</u> dB</td> </tr> <tr> <td>Freq. <u>1-5Mhz</u></td> <td>*PRR/PRF <u>High</u></td> </tr> <tr> <td>Range <u>1.0"</u></td> <td>Pulser <u>High</u></td> </tr> <tr> <td>Mtl. Cal/Vel. <u>127.0"</u></td> <td>Damping <u>Fixed</u></td> </tr> <tr> <td>Delay <u>3.3us</u></td> <td>Reject <u>0</u></td> </tr> <tr> <td>Filter <u>N/A</u></td> <td>Jack <input checked="" type="checkbox"/> R <input type="checkbox"/> T</td> </tr> <tr> <td>Mode <u>Shear</u></td> <td></td> </tr> </table> <p>*Pulse Repetition Rate/Pulse Repetition Frequency</p>			Reference Sensitivity	Examination Sensitivity	Gain - Axial Scan <u>20.5</u> dB	Gain - Axial Scan <u>28.0</u> dB	Gain - Circ. Scan <u>20.5</u> dB	Gain - Circ. Scan <u>28.0</u> dB	Freq. <u>1-5Mhz</u>	*PRR/PRF <u>High</u>	Range <u>1.0"</u>	Pulser <u>High</u>	Mtl. Cal/Vel. <u>127.0"</u>	Damping <u>Fixed</u>	Delay <u>3.3us</u>	Reject <u>0</u>	Filter <u>N/A</u>	Jack <input checked="" type="checkbox"/> R <input type="checkbox"/> T	Mode <u>Shear</u>	
Reference Sensitivity	Examination Sensitivity																				
Gain - Axial Scan <u>20.5</u> dB	Gain - Axial Scan <u>28.0</u> dB																				
Gain - Circ. Scan <u>20.5</u> dB	Gain - Circ. Scan <u>28.0</u> dB																				
Freq. <u>1-5Mhz</u>	*PRR/PRF <u>High</u>																				
Range <u>1.0"</u>	Pulser <u>High</u>																				
Mtl. Cal/Vel. <u>127.0"</u>	Damping <u>Fixed</u>																				
Delay <u>3.3us</u>	Reject <u>0</u>																				
Filter <u>N/A</u>	Jack <input checked="" type="checkbox"/> R <input type="checkbox"/> T																				
Mode <u>Shear</u>																					
Welds Examined <input checked="" type="checkbox"/> Ferritic <input type="checkbox"/> Austenitic	Calibration Verification																				
1E215-39-FW4	Initial Calibration Time	09:10	Verification Times																		
	Final Verification Time	12:50																			
Comments : Miniature cal block. S/N: 5226 (SW-10)																					
Examiner: <u>J. J. Smith</u> Level: <u>II</u> Date: <u>4 / 18 / 01</u> Examiner: <u>J. J. Smith</u> Level: <u>IL</u> Date: <u>4 / 18 / 01</u> Reviewed: <u>R. A. Smith</u> Level: <u>ANIE</u> Date: <u>5 / 21 / 01</u>																					

Enclosure 2
BSEP, Unit 1 4th ISI Interval Limited NDE Data and Coverage Plots

CPL UT-13 Rev 4		Cal. Sheet No. <u>39-FW4 45 1.5</u> Page <u>6</u> of <u>9</u>																			
ULTRASONIC CALIBRATION DATA SHEET																					
Plant: <u>BNP</u> Unit: <u>1</u>		Data Sheets: <u>39-FW4</u>																			
Procedure No.: <u>OSP-00-001</u> Rev.: <u>0</u> Couplant Brand: <u>ULTRAGEL II, 99-325</u> Cal Block Temp.: <u>75 Deg Therm.</u> SN: <u>PY-15</u>																					
Instrument Mfg.: <u>Krautkramer Branson</u> Model: <u>USK-7D</u> S/N: <u>32810-4012 (UI-2)</u>																					
Search Unit Mfg.: <u>K-B Aerotech</u> Model: <u>Comp-g</u> Shape: <u>Round</u> Size: <u>.25"</u> Freq.: <u>5.0 MHZ</u>																					
Search Unit : Angle/Mode: <u>45 s</u> Measured Angle: <u>45</u> Wedge Style : <u>MSWQC</u> S/N: <u>008NY6</u> <u>Single/Dual</u>																					
Cable Type: <u>RG174</u> Length: <u>6'</u> Connectors: <u>BNC-MDOT</u> Wedge Index to Front Meas.: <u>.35</u>																					
Calibration Block: Size: <u>14"</u> Thickness: <u>.375</u> S/N: <u>30B</u> Other Block: <u>IIW</u> S/N: <u>96-6500 (SW-9)</u>																					
 <p>X = Axial Scan, O = Circ. Scan Scale Range: 0 - 10 = Metal Path <u>2.5"</u></p>	<p style="text-align: center;"><u>Instrument Settings</u></p> <table style="width: 100%; border-collapse: collapse;"> <tr> <td style="width: 50%;">Reference Sensitivity</td> <td style="width: 50%;">Examination Sensitivity</td> </tr> <tr> <td>Gain - Axial Scan <u>20.5</u> dB</td> <td>Gain - Axial Scan <u>31.5</u> dB</td> </tr> <tr> <td>Gain - Circ. Scan <u>N/A</u> dB</td> <td>Gain - Circ. Scan <u>N/A</u> dB</td> </tr> <tr> <td>Freq. <u>1-5Mhz</u></td> <td>*PRR/PRF <u>High</u></td> </tr> <tr> <td>Range <u>2.5"</u></td> <td>Pulser <u>High</u></td> </tr> <tr> <td>Mtl. Cal/Vel. <u>127.0"</u></td> <td>Damping <u>Fixed</u></td> </tr> <tr> <td>Delay <u>3.3us</u></td> <td>Reject <u>0</u></td> </tr> <tr> <td>Filter <u>N/A</u></td> <td>Jack <input checked="" type="checkbox"/> R <input type="checkbox"/> T</td> </tr> <tr> <td>Mode <u>Shear</u></td> <td></td> </tr> </table> <p style="text-align: center;">*Pulse Repetition Rate/Pulse Repetition Frequency</p>			Reference Sensitivity	Examination Sensitivity	Gain - Axial Scan <u>20.5</u> dB	Gain - Axial Scan <u>31.5</u> dB	Gain - Circ. Scan <u>N/A</u> dB	Gain - Circ. Scan <u>N/A</u> dB	Freq. <u>1-5Mhz</u>	*PRR/PRF <u>High</u>	Range <u>2.5"</u>	Pulser <u>High</u>	Mtl. Cal/Vel. <u>127.0"</u>	Damping <u>Fixed</u>	Delay <u>3.3us</u>	Reject <u>0</u>	Filter <u>N/A</u>	Jack <input checked="" type="checkbox"/> R <input type="checkbox"/> T	Mode <u>Shear</u>	
Reference Sensitivity	Examination Sensitivity																				
Gain - Axial Scan <u>20.5</u> dB	Gain - Axial Scan <u>31.5</u> dB																				
Gain - Circ. Scan <u>N/A</u> dB	Gain - Circ. Scan <u>N/A</u> dB																				
Freq. <u>1-5Mhz</u>	*PRR/PRF <u>High</u>																				
Range <u>2.5"</u>	Pulser <u>High</u>																				
Mtl. Cal/Vel. <u>127.0"</u>	Damping <u>Fixed</u>																				
Delay <u>3.3us</u>	Reject <u>0</u>																				
Filter <u>N/A</u>	Jack <input checked="" type="checkbox"/> R <input type="checkbox"/> T																				
Mode <u>Shear</u>																					
Welds Examined <input checked="" type="checkbox"/> Ferritic <input type="checkbox"/> Austenitic	Calibration Verification																				
1E215-39-FW4	Initial Calibration Time	09:00	Verification Times																		
	Final Verification Time	12:50																			
Comments : Miniature cal block. S/N: 5226 (SW-10)																					
<p>Examiner: <u>[Signature]</u> Level: <u>II</u> Date: <u>4 / 18 / 01</u></p> <p>Examiner: <u>[Signature]</u> Level: <u>IL</u> Date: <u>4 / 18 / 01</u></p> <p>Reviewed: <u>R. A. comb</u> Level: <u>ANT</u> Date: <u>5 / 2 / 01</u></p>																					

Enclosure 2
BSEP, Unit 1 4th ISI Interval Limited NDE Data and Coverage Plots

CPL UT-13 Rev 4

ULTRASONIC CALIBRATION DATA SHEET

Cal. Sheet No. 39-FW4 60
Page 7 of 9

Plant: BNP Unit: 1 Data Sheets: 39-FW4

Procedure No.: 0SP-00-001 Rev.: 0 Couplant Brand: ULTRAGEL II, 99-325 Cal Block Temp.: 75 Deg Therm. SN: PY-15


Instrument Mfg.: Krautkramer Branson Model: USK-7D S/N: 32810-4012 (UI-2)

Search Unit Mfg.: K-B Aerotech Model: GAMMA Shape: Round Size: .25" Freq.: 5.0 MHZ

Search Unit : Angle/Mode: 60 s Measured Angle: 60 Wedge Style : MSWS S/N: M09875 Single/Dual

Cable Type: RG174 Length: 6' Connectors: BNC-MDOT Wedge Index to Front Meas.: .3

Calibration Block: Size: 14" Thickness: .375 S/N: 30B Other Block: IW S/N: 96-6500 (SW-9)



X = Axial Scan, O = Circ. Scan
Scale Range: 0 - 10 = Metal Path 1.25"

Instrument Settings

Reference Sensitivity

Gain - Axial Scan 41.5 dB
Gain - Circ. Scan N/A dB

Freq. 1-5Mhz
Range 1.25"
Mtl. Cal/Vel. 127.0"
Delay 4.7us
Filter N/A
Mode Shear

Examination Sensitivity

Gain - Axial Scan 41.5 dB
Gain - Circ. Scan N/A dB

*PRR/PRF High
Pulser High
Damping Fixed
Reject 0
Jack R T

*Pulse Repetition Rate/Pulse Repetition Frequency

Welds Examined Ferritic Austenitic

Calibration Verification

1E215-39-FW4

Initial
Calibration
Time

09:00

Verification Times

Final
Verification
Time

12:50

Comments: Miniature cal block. S/N: 5226 (SW-10)

Examiner:
Level: II Date: 4 / 18 / 01

Examiner:
Level: IL Date: 4 / 18 / 01

Reviewed:
Level: ANII Date: 5 / 2 / 01

EXHIBIT 2
Determination of Percent Coverage for Ultrasonic Examinations

Report No. 39-Fwy

Unit 1 Procedure OSP-00-001 R% Page 8 of 9

Weld Number 1E215-39-Fwy

45 deg

Scan 1 100 % Length X 100 % volume of length/100 = 100 % total for Scan 1

Scan 2 100 % Length X 60 % volume of length/100 = 60 % total for Scan 2

Scan 3 100 % Length X 100 % volume of length/100 = 100 % total for Scan 3

Scan 4 100 % Length X 100 % volume of length/100 = 100 % total for Scan 4

Add totals and divide by # scans = 90 % total for 45 deg

Other deg - 60 (to be used for supplemental scans)

The data to be listed below is for coverage that was not obtained with the 45 deg scans.

Scan 1 n/a % Length X n/a % volume of length/100 = n/a % total for Scan 1

Scan 2 n/a % Length X n/a % volume of length/100 = n/a % total for Scan 2

Scan 3 n/a % Length X n/a % volume of length/100 = n/a % total for Scan 3

Scan 4 n/a % Length X n/a % volume of length/100 = n/a % total for Scan 4

Percent complete coverage

Add totals for each scan required and divide by # of scans to determine:

90 % Total for complete exam

Level III/NDE Program Manager L D Shatley Date 4/19/01

*ANII
RECEIVED
PT
5-20-01*


QA NDE-CS-1 Rev 1

CP&L

NDE DRAWING ATTACHMENT

PAGE 9 OF 9

PROJECT	JOB NO.	UNIT	DATE
Bnp C24004	119769	1 <input checked="" type="checkbox"/> 2 <input type="checkbox"/> 3 <input type="checkbox"/> 4 <input type="checkbox"/>	4-18-01
DRAWING SHT 98-1	SYSTEM Core Spray	LINE 1E21-39-14-152	1E215-39-FW4
			WELD/ITEM NUMBER



Enclosure 2

BSEP, Unit 1 4th ISI Interval Limited NDE Data and Coverage Plots

UT Calibration/Examination

Site/Unit:	BNP / 1	Procedure:	NDEP-0437		Outage No.:	B121R1
Summary No.:	1-E41-4152	Procedure Rev.:	B		Report No.:	UT-16-029
Workscope:	ISI	Work Order No.:	13472402		Page:	1 of 11
Code:	2001 Edition, 2003 Addenda	Cat./Item:	C-F-2/C5.51		Location:	REACTOR BUILDING
Drawing No.:	C-24004 Sht. 105-1	Description: PIPE TO VALVE 1-E41-FO42				
System ID:	2095					
Component ID:	1E411X226-1-FW22	Size/Length: 16"/43.982"				Thickness/Diameter: CS/0.375"/16"
Limitations:	Yes - single sided due to valve	Start Time: 0348				Finish Time: 0408
Instrument Settings		Search Unit		Axial Orientated Search Unit		
Serial No.:	13G00172	Serial No.:	SC3094	Cal. Checks	Time	Date
Manufacturer:	GE	Manufacturer:	GE	Initial Cal.	2100	3/10/2016
Model:	USN 60 SW	Linearity:	L-16-005	Inter. Cal.	N/A	
Delay:	3.5866	Range:	1.00"	Inter. Cal.	0347	3/11/2016
M'l'l Cal/Vel:	0.1266	Pulser Type:	Square	Inter. Cal.	N/A	
Damping:	500 Ohms	Reject:	0%	Measured Angle:	42.4	Mode: Shear
PRF:	Auto High	SU Freq.:	5 MHz	Exit Point:	0.30"	# of Elements: 1
Frequency:	5.0 MHz	Rectify:	Fullwave	Config.:	Single	Cal. Batch: 14H073
Voltage:	450	Pulse Width:	100	Focus:	N/A	Type: Ultragel II
Ax. Gain (dB):	N/A	Circ. Gain (dB):	21.0	Shape:	Round	Mfg.: Sonotech, Inc.
1 Screen Div. =	0.1	in. of Sound Path		Contour:	Flat	Exam Batch: 14H073
Search Unit Cable		Scan Coverage		Circumferential Orientated Search Unit		
Cal. Block No.:	CB-02-52	Upstream <input type="checkbox"/>	Downstream <input type="checkbox"/>	Scan dB: N/A	Calibration Reflector	Signal Amplitude %
Thickness:	0.5" - 2.0"	Dia.:	Flat	CW <input checked="" type="checkbox"/>	CCW <input checked="" type="checkbox"/>	Sweep Division
Cal. Blk. Temp.:	74	Temp. Tool:	G502480	Scan dB: 32.0	Sound Path	
Comp. Temp.:	75	Temp. Tool:	G502480	Exam Surface: O.D.	0.5" Notch	
Recordable Indication(s):	Yes <input type="checkbox"/>	No <input checked="" type="checkbox"/>	(If Yes, Ref. Attached Ultrasonic Indication Report.)	Type: Ramps	80	6.8
Results:	Sat <input checked="" type="checkbox"/>	Unsat <input type="checkbox"/>	Eval <input type="checkbox"/> NCR # 02009905	Comments: N/A	14-3684	0.677"
Percent Of Coverage Obtained > 90%: 70.5%		Reviewed Previous Data: Yes		Reference/Simulator Block		
Examiner	Level II-N	Signature	Date	Reviewer	Signature	Date
Williams, Christopher D.		<i>Christopher D. Williams</i>	3/11/2016	<i>D.B. Kus, UT Level II</i>	<i>Signature</i>	3/15/16
Examiner	Level II-N	Signature	Date	Site Review	Signature	Date
Nahory, W. Jason		<i>W. Jason Nahory</i>	3/11/2016	<i>W. Jason Nahory</i>	<i>Signature</i>	3/16/16
Other	Level N/A	Signature	Date	ANII Review	Signature	Date
		<i>Z. Cline & L. Cline</i>	3/16/16	<i>David M. Reynolds, ANII</i>	<i>Signature</i>	3-16-2016

UT Calibration/Examination

Site/Unit:	BNP / 1	Procedure:	NDEP-0437	Outage No.:	B121R1																																																																																																																																																																																																																																																													
Summary No.:	1-E41-4152	Procedure Rev.:	8	Report No.:	UT-16-029																																																																																																																																																																																																																																																													
Workscope:	ISI	Work Order No.:	13472402	Page:	2 of 11																																																																																																																																																																																																																																																													
Code:	2001 Edition, 2003 Addenda	Cat./Item:	C-F-2/C5.51	Location:	REACTOR BUILDING																																																																																																																																																																																																																																																													
Drawing No.:	C-24004 Sht. 105-1	Description: PIPE TO VALVE 1-E41-FO42																																																																																																																																																																																																																																																																
System ID:	2095																																																																																																																																																																																																																																																																	
Component ID:	1E411X226-1-FW22	Size/Length: 16"/43.982" Thickness/Diameter: CS/0.375"/16"																																																																																																																																																																																																																																																																
Limitations:	Yes - single sided due to valve	Start Time: 0240 Finish Time: 0335																																																																																																																																																																																																																																																																
<table border="1"> <thead> <tr> <th colspan="2">Instrument Settings</th> <th colspan="3">Search Unit</th> <th colspan="3">Axial Orientated Search Unit</th> </tr> <tr> <th>Serial No.:</th> <td>13G00172</td> <th>Serial No.:</th> <td>SC3094</td> <th>Cal. Checks</th> <th>Time</th> <th>Date</th> <th>Calibration Reflector</th> <th>Signal Amplitude %</th> <th>Sweep Division</th> <th>Sound Path</th> </tr> </thead> <tbody> <tr> <td>Manufacturer:</td> <td>GE</td> <td>Manufacturer:</td> <td>GE</td> <td>Initial Cal.</td> <td>1128</td> <td>3/7/2016</td> <td>0.5" Notch</td> <td>80</td> <td>6.8</td> <td>0.677"</td> </tr> <tr> <td>Model:</td> <td>USN 60 SW</td> <td>Linearity:</td> <td>L-16-005</td> <td>Size:</td> <td>0.25"</td> <td>Model: Comp - G</td> <td></td> <td></td> <td></td> <td></td> </tr> <tr> <td>Delay:</td> <td>3.5866</td> <td>Range:</td> <td>1.00"</td> <td>Freq.:</td> <td>5 MHz</td> <td>Center Freq.:</td> <td>N/A</td> <td></td> <td></td> <td></td> </tr> <tr> <td>M'tl Cal/Vel:</td> <td>0.1266</td> <td>Pulser Type:</td> <td>Square</td> <td>Exam Angle:</td> <td>45</td> <td>Squint Angle:</td> <td>N/A</td> <td></td> <td></td> <td></td> </tr> <tr> <td>Damping:</td> <td>500 Ohms</td> <td>Reject:</td> <td>0%</td> <td>Measured Angle:</td> <td>42.4</td> <td>Mode:</td> <td>Shear</td> <td></td> <td></td> <td></td> </tr> <tr> <td>PRF:</td> <td>Auto High</td> <td>SU Freq.:</td> <td>5 MHz</td> <td>Exit Point:</td> <td>0.30"</td> <td># of Elements:</td> <td>1</td> <td></td> <td></td> <td></td> </tr> <tr> <td>Frequency:</td> <td>5.0 MHz</td> <td>Rectify:</td> <td>Fullwave</td> <td>Config.:</td> <td>Single</td> <td>Focus:</td> <td>N/A</td> <td></td> <td></td> <td></td> </tr> <tr> <td>Voltage:</td> <td>450</td> <td>Pulse Width:</td> <td>100</td> <td>Shape:</td> <td>Round</td> <td>Contour:</td> <td>Flat</td> <td></td> <td></td> <td></td> </tr> <tr> <td>Ax. Gain (dB):</td> <td>21.0</td> <td>Circ. Gain (dB):</td> <td>N/A</td> <td>Wedge Style:</td> <td>MSWQC</td> <td>Couplant</td> <td></td> <td></td> <td></td> <td></td> </tr> <tr> <td>1 Screen Div. =</td> <td>0.1</td> <td>in. of</td> <td>Sound Path</td> <td>Search Unit Cable</td> <td></td> <td>Cal. Batch:</td> <td>14H073</td> <td></td> <td></td> <td></td> </tr> <tr> <td>Cal. Block No.:</td> <td colspan="2">CB-02-52</td> <td>Type:</td> <td>RG-174</td> <td>Length: 6'</td> <td>No. Conn.:</td> <td>0</td> <td>Type:</td> <td>Ultragel II</td> <td></td> </tr> <tr> <td>Thickness:</td> <td>0.5" - 2.0"</td> <td>Dia.:</td> <td>Flat</td> <td>CW</td> <td>CCW</td> <td>Scan dB:</td> <td>31.0</td> <td>Mfg.:</td> <td>Sonotech, Inc.</td> </tr> <tr> <td>Cal. Blk. Temp.:</td> <td>73</td> <td>Temp. Tool:</td> <td>G502480</td> <td>Exam Surface:</td> <td>O.D.</td> <td>Exam Batch:</td> <td>14H073</td> <td></td> <td></td> <td></td> </tr> <tr> <td>Comp. Temp.:</td> <td>75</td> <td>Temp. Tool:</td> <td>G502480</td> <td>Surface Condition:</td> <td>Ground</td> <td>Type:</td> <td>Ultragel II</td> <td></td> <td></td> <td></td> </tr> <tr> <td>Recordable Indication(s):</td> <td>Yes <input type="checkbox"/></td> <td>No <input checked="" type="checkbox"/></td> <td colspan="4">(If Yes, Ref. Attached Ultrasonic Indication Report.)</td> <td>Mfg.:</td> <td>Sonotech, Inc.</td> <td></td> <td></td> </tr> <tr> <td>Results:</td> <td>Sat <input checked="" type="checkbox"/></td> <td>Unsat <input type="checkbox"/></td> <td>Eval <input type="checkbox"/></td> <td colspan="4"></td> <td>Comments:</td> <td colspan="2">N/A</td> </tr> <tr> <td colspan="6">Percent Of Coverage Obtained > 90%: 70.5% Reviewed Previous Data: Yes</td> <td colspan="5"></td> </tr> <tr> <td>Examiner</td> <td>Level</td> <td>II-N</td> <td>Signature</td> <td>Date</td> <td>Reviewer</td> <td>Signature</td> <td>Date</td> </tr> <tr> <td>Williams, Christopher D.</td> <td></td> <td></td> <td></td> <td>3/8/2016</td> <td>D. Williams, Level II-N</td> <td></td> <td>3/15/16</td> </tr> <tr> <td>Examiner</td> <td>Level</td> <td>II-N</td> <td>Signature</td> <td>Date</td> <td>Site Review</td> <td>Signature</td> <td>Date</td> </tr> <tr> <td>Nahory, W. Jason</td> <td></td> <td></td> <td></td> <td>3/8/2016</td> <td>J. Nahory</td> <td></td> <td>3.16.16</td> </tr> <tr> <td>Other</td> <td>Level</td> <td>N/A</td> <td>Signature</td> <td>Date</td> <td>ANII Review</td> <td>Signature</td> <td>Date</td> </tr> <tr> <td>Z. Cline</td> <td></td> <td></td> <td></td> <td>3/16/16</td> <td>D. Reynolds</td> <td></td> <td>3-16-2016</td> </tr> </tbody></table>						Instrument Settings		Search Unit			Axial Orientated Search Unit			Serial No.:	13G00172	Serial No.:	SC3094	Cal. Checks	Time	Date	Calibration Reflector	Signal Amplitude %	Sweep Division	Sound Path	Manufacturer:	GE	Manufacturer:	GE	Initial Cal.	1128	3/7/2016	0.5" Notch	80	6.8	0.677"	Model:	USN 60 SW	Linearity:	L-16-005	Size:	0.25"	Model: Comp - G					Delay:	3.5866	Range:	1.00"	Freq.:	5 MHz	Center Freq.:	N/A				M'tl Cal/Vel:	0.1266	Pulser Type:	Square	Exam Angle:	45	Squint Angle:	N/A				Damping:	500 Ohms	Reject:	0%	Measured Angle:	42.4	Mode:	Shear				PRF:	Auto High	SU Freq.:	5 MHz	Exit Point:	0.30"	# of Elements:	1				Frequency:	5.0 MHz	Rectify:	Fullwave	Config.:	Single	Focus:	N/A				Voltage:	450	Pulse Width:	100	Shape:	Round	Contour:	Flat				Ax. Gain (dB):	21.0	Circ. Gain (dB):	N/A	Wedge Style:	MSWQC	Couplant					1 Screen Div. =	0.1	in. of	Sound Path	Search Unit Cable		Cal. Batch:	14H073				Cal. Block No.:	CB-02-52		Type:	RG-174	Length: 6'	No. Conn.:	0	Type:	Ultragel II		Thickness:	0.5" - 2.0"	Dia.:	Flat	CW	CCW	Scan dB:	31.0	Mfg.:	Sonotech, Inc.	Cal. Blk. Temp.:	73	Temp. Tool:	G502480	Exam Surface:	O.D.	Exam Batch:	14H073				Comp. Temp.:	75	Temp. Tool:	G502480	Surface Condition:	Ground	Type:	Ultragel II				Recordable Indication(s):	Yes <input type="checkbox"/>	No <input checked="" type="checkbox"/>	(If Yes, Ref. Attached Ultrasonic Indication Report.)				Mfg.:	Sonotech, Inc.			Results:	Sat <input checked="" type="checkbox"/>	Unsat <input type="checkbox"/>	Eval <input type="checkbox"/>					Comments:	N/A		Percent Of Coverage Obtained > 90%: 70.5% Reviewed Previous Data: Yes											Examiner	Level	II-N	Signature	Date	Reviewer	Signature	Date	Williams, Christopher D.				3/8/2016	D. Williams, Level II-N		3/15/16	Examiner	Level	II-N	Signature	Date	Site Review	Signature	Date	Nahory, W. Jason				3/8/2016	J. Nahory		3.16.16	Other	Level	N/A	Signature	Date	ANII Review	Signature	Date	Z. Cline				3/16/16	D. Reynolds		3-16-2016
Instrument Settings		Search Unit			Axial Orientated Search Unit																																																																																																																																																																																																																																																													
Serial No.:	13G00172	Serial No.:	SC3094	Cal. Checks	Time	Date	Calibration Reflector	Signal Amplitude %	Sweep Division	Sound Path																																																																																																																																																																																																																																																								
Manufacturer:	GE	Manufacturer:	GE	Initial Cal.	1128	3/7/2016	0.5" Notch	80	6.8	0.677"																																																																																																																																																																																																																																																								
Model:	USN 60 SW	Linearity:	L-16-005	Size:	0.25"	Model: Comp - G																																																																																																																																																																																																																																																												
Delay:	3.5866	Range:	1.00"	Freq.:	5 MHz	Center Freq.:	N/A																																																																																																																																																																																																																																																											
M'tl Cal/Vel:	0.1266	Pulser Type:	Square	Exam Angle:	45	Squint Angle:	N/A																																																																																																																																																																																																																																																											
Damping:	500 Ohms	Reject:	0%	Measured Angle:	42.4	Mode:	Shear																																																																																																																																																																																																																																																											
PRF:	Auto High	SU Freq.:	5 MHz	Exit Point:	0.30"	# of Elements:	1																																																																																																																																																																																																																																																											
Frequency:	5.0 MHz	Rectify:	Fullwave	Config.:	Single	Focus:	N/A																																																																																																																																																																																																																																																											
Voltage:	450	Pulse Width:	100	Shape:	Round	Contour:	Flat																																																																																																																																																																																																																																																											
Ax. Gain (dB):	21.0	Circ. Gain (dB):	N/A	Wedge Style:	MSWQC	Couplant																																																																																																																																																																																																																																																												
1 Screen Div. =	0.1	in. of	Sound Path	Search Unit Cable		Cal. Batch:	14H073																																																																																																																																																																																																																																																											
Cal. Block No.:	CB-02-52		Type:	RG-174	Length: 6'	No. Conn.:	0	Type:	Ultragel II																																																																																																																																																																																																																																																									
Thickness:	0.5" - 2.0"	Dia.:	Flat	CW	CCW	Scan dB:	31.0	Mfg.:	Sonotech, Inc.																																																																																																																																																																																																																																																									
Cal. Blk. Temp.:	73	Temp. Tool:	G502480	Exam Surface:	O.D.	Exam Batch:	14H073																																																																																																																																																																																																																																																											
Comp. Temp.:	75	Temp. Tool:	G502480	Surface Condition:	Ground	Type:	Ultragel II																																																																																																																																																																																																																																																											
Recordable Indication(s):	Yes <input type="checkbox"/>	No <input checked="" type="checkbox"/>	(If Yes, Ref. Attached Ultrasonic Indication Report.)				Mfg.:	Sonotech, Inc.																																																																																																																																																																																																																																																										
Results:	Sat <input checked="" type="checkbox"/>	Unsat <input type="checkbox"/>	Eval <input type="checkbox"/>					Comments:	N/A																																																																																																																																																																																																																																																									
Percent Of Coverage Obtained > 90%: 70.5% Reviewed Previous Data: Yes																																																																																																																																																																																																																																																																		
Examiner	Level	II-N	Signature	Date	Reviewer	Signature	Date																																																																																																																																																																																																																																																											
Williams, Christopher D.				3/8/2016	D. Williams, Level II-N		3/15/16																																																																																																																																																																																																																																																											
Examiner	Level	II-N	Signature	Date	Site Review	Signature	Date																																																																																																																																																																																																																																																											
Nahory, W. Jason				3/8/2016	J. Nahory		3.16.16																																																																																																																																																																																																																																																											
Other	Level	N/A	Signature	Date	ANII Review	Signature	Date																																																																																																																																																																																																																																																											
Z. Cline				3/16/16	D. Reynolds		3-16-2016																																																																																																																																																																																																																																																											

UT Calibration/Examination

Site/Unit:	BNP / 1	Procedure:	NDEP-0437		Outage No.:	B121R1					
Summary No.:	1-E41-4152	Procedure Rev.:	8		Report No.:	UT-16-029					
Workscope:	ISI	Work Order No.:	13472402		Page:	3 of 11					
Code:	2001 Edition, 2003 Addenda	Cat./Item:	C-F-2/C5.51		Location:	REACTOR BUILDING					
Drawing No.:	C-24004 Sht. 105-1	Description: PIPE TO VALVE 1-E41-FO42									
System ID:	2095										
Component ID:	1E411X226-1-FW22					Size/Length: 16"/43.982"	Thickness/Diameter: CS/0.375"/16"				
Limitations:	Yes - single sided due to valve				Start Time:	0240	Finish Time:	0335			
Instrument Settings		Search Unit		Axial Orientated Search Unit							
Serial No.:	13G00172	Serial No.:	SC2843	Cal. Checks	Time	Date	Calibration Reflector	Signal Amplitude %	Sweep Division	Sound Path	
Manufacturer:	GE	Manufacturer:	GE	Initial Cal.	1135	3/7/2016	0.5" Notch	80	6.5	0.911"	
Model:	USN 60 SW	Linearity:	L-16-005	Size:	0.25"	Model:	Comp-G				
Delay:	4.745	Range:	1.4"	Freq.:	5 MHz	Center Freq.:	N/A				
Mtl Cal/Vel:	0.1268	Pulser Type:	Square	Exam Angle:	60	Squint Angle:	N/A				
Damping:	500 Ohms	Reject:	0%	Measured Angle:	60.4	Mode:	Shear				
PRF:	Auto High	SU Freq.:	5 MHz	Exit Point:	0.3"	# of Elements:	1	Cal. Batch:	14H073		
Frequency:	5.0 MHz	Rectify:	Fullwave	Config.:	Single	Focus:	N/A	Type:	Ultragel II		
Voltage:	450	Pulse Width:	100	Shape:	Round	Contour:	Flat	Mfg.:	Sonotech, Inc.		
Ax. Gain (dB):	35.0	Circ. Gain (dB):	N/A	Wedge Style:	MSWQC		Exam Batch:	14H073			
Search Unit Cable				Type:	RG-174	Length:	6'	No. Conn.:	0	Type:	Ultragel II
1 Screen Div. =	.14	in. of	Sound Path	Mfg.:	Sonotech, Inc.						
Calibration Block		Scan Coverage				Reference Block				Circumferential Orientated Search Unit	
Cal. Block No.:	CB-02-52		Upstream	<input type="checkbox"/>	Downstream	<input checked="" type="checkbox"/>	Scan dB:	41.0	Serial No.:	14-3684	
Thickness:	0.5" - 2.0"		Dia.:	Flat	CW	<input type="checkbox"/>	CCW	<input type="checkbox"/>	Type:	Rompas	Sound Path
Cal. Blk. Temp.:	73	Temp. Tool:	G502480	Exam Surface:	O.D.						
Comp. Temp.:	75	Temp. Tool:	G502480	Surface Condition:	Ground						
Recordable Indication(s): Yes <input type="checkbox"/> No <input checked="" type="checkbox"/> (If Yes, Ref. Attached Ultrasonic Indication Report.)											
Results:	Sat	<input checked="" type="checkbox"/>	Unsat	<input type="checkbox"/>	Eval	<input type="checkbox"/>	Comments: N/A				
Percent Of Coverage Obtained > 90%: 70.5% Reviewed Previous Data: Yes											

Examiner	Level	II-N	Signature	Date	Reviewer	Signature	Date
Nahory, W. Jason				3/8/2016	D.B. King, UT Level II		3/15/16
Examiner	Level	II-N	Signature	Date	Site Review	Signature	Date
Williams, Christopher D.				3/8/2016	John Sullivan		3.16.16
Other	Level	N/A	Signature	Date	ANII Review	Signature	Date
Z-AWA				3/16/16	David m Reynolds David m Reynolds		3-16-2016

Enclosure 2

BSEP, Unit 1 4th ISI Interval Limited NDE Data and Coverage Plots

UT Calibration/Examination

Site/Unit:	BNP	1	Procedure:	NDEP-0437	Outage No.:	B121R1
Summary No.:	1-E41-4152		Procedure Rev.:	8	Report No.:	UT-16-029
Workscope:	ISI		Work Order No.:	13472402	Page:	4 of 11
Code:	2001 Edition, 2003 Addenda		Cat./Item:	C-F-2/C5.51	Location:	REACTOR BUILDING
Drawing No.:	C-24004 Sht. 105-1		Description:	PIPE TO VALVE 1-E41-FO42		
System ID:	2095		Size/Length:	16"/43.982"	Thickness/Diameter:	CS/0.375"/16"
Component ID:	1E411X226-1-FW22		Start Time:	0240	Finish Time:	0335
Limitations:	Yes - single sided due to valve					
Instrument Settings			Search Unit			
Serial No.:	13G00172		Serial No.:	SC3068		
Manufacturer:	GE		Manufacturer:	GE		
Model:	USN 60 SW	Linearity:	L-16-005	Size:	0.25"	Cal. Checks
Delay:	6.4228	Range:	2.00"	Freq.:	5 MHz	Time
M'l'l Cal/Vel:	0.1275	Pulser Type:	Square	Center Freq.:	N/A	Date
Damping:	500 Ohms	Reject:	0%	Exam Angle:	70	Initial Cal.
PRF:	Auto High	SU Freq.:	5 MHz	Squint Angle:	N/A	Inter. Cal.
Frequency:	5.0 MHz	Rectify:	Fullwave	Measured Angle:	71	Inter. Cal.
Voltage:	450	Pulse Width:	100	Mode:	Shear	Inter. Cal.
Ax. Gain (dB):	44.0	Circ. Gain (dB):	N/A	Config.:	Single	Final Cal.
1 Screen Div. =	.20	in. of Sound Path		Focus:	N/A	
Calibration Block			Scan Coverage			
Cal. Block No.:	CB-02-52		Upstream <input type="checkbox"/>	Downstream <input checked="" type="checkbox"/>	Scan dB: 53.0	Reference Block
Thickness:	0.5" - 2.0"		CW <input type="checkbox"/>	CCW <input type="checkbox"/>	Scan dB: N/A	Serial No.:
Cal. Blk. Temp.:	73	Temp. Tool:	G502480	Exam Surface:	O.D.	Type:
Comp. Temp.:	75	Temp. Tool:	G502480	Surface Condition:	Ground	Rompas
Recordable Indication(s):	Yes <input type="checkbox"/> No <input checked="" type="checkbox"/>		(If Yes, Ref. Attached Ultrasonic Indication Report.)			
Results:	Sat <input checked="" type="checkbox"/>	Unsat <input type="checkbox"/>	Eval <input type="checkbox"/>	Comments: N/A		
Percent Of Coverage Obtained > 90%: 70.5%			Reviewed Previous Data: Yes			

Examiner	Level	II-N	Signature	Date	Reviewer	Signature	Date
Nahory, W. Jason				3/8/2016	D.B. King, UT Level II		3/15/16
Examiner	Level	II-N	Signature	Date	Site Review	Signature	Date
Williams, Christopher D.				3/8/2016	John Sullivan		3.16.16
Other	Level	N/A	Signature	Date	ANII Review	Signature	Date
TVA	ZACLINE	ZAC		3/16/16	David M. Reynolds	David M. Reynolds	3-16-2016

BSEP, Unit 1 4th ISI Interval Limited NDE Data and Coverage Plots

UT Calibration/Examination

Site/Unit:	BNP / 1	Procedure:	NDEP-0408	Outage No.:	B121R1
Summary No.:	1-E41-4152	Procedure Rev.:	14	Report No.:	UT-16-029
Workscope:	ISI	Work Order No.:	13472402	Page:	5 of 11
Code:	2001 Edition, 2003 Addenda	Cat./Item:	C-F-2/C5.51	Location:	REACTOR BUILDING
Drawing No.:	C-24004 Sht. 105-1	Description: PIPE TO VALVE 1-E41-FO42			
System ID:	2095				
Component ID:	1E411X226-1-FW22	Size/Length: 16"/43.982"		Thickness/Diameter: CS/0.375"/16"	
Limitations:	Yes - single sided due to valve	Start Time: 0240		Finish Time: 0335	

Instrument Settings		Search Unit			Axial Orientated Search Unit		
Serial No.:	13G00172	Serial No.:	B15027		Cal. Checks	Time	Date
Manufacturer:	GE	Manufacturer:	KBA		Initial Cal.	1123	3/7/2016
Model:	USN 60 SW	Linearity:	L-16-005		Inter. Cal.	N/A	
Delay:	0.6009	Range:	1.25"		Inter. Cal.	0239	3/8/2016
M'tl Cal/Vel:	0.2331	Pulser Type:	Square		Exam Angle:	0	Squint Angle: N/A
Damping:	500 Ohms	Reject:	0%		Measured Angle:	N/A	Mode: Long.
PRF:	Auto High	SU Freq.:	5.0 MHz		Exit Point:	N/A	# of Elements: 1
Frequency:	5.0 MHz	Rectify:	Fullwave		Config.:	Single	Focus: N/A
Voltage:	450	Pulse Width:	100		Shape:	Round	Contour: Flat
Ax. Gain (dB):	*	Circ. Gain (dB):	N/A		Wedge Style:	Integral	
1 Screen Div. = .125 in. of Sound Path		Type:	RG-174		Cal. Batch:	14H073	
Calibration Block		Search Unit Cable			Type:	Ultragel II	
Cal. Block No.:		Upstream <input checked="" type="checkbox"/> Downstream <input checked="" type="checkbox"/> Scan dB: *			Mfg.:	Sonotech, Inc.	
Thickness: 0.25"-1.0"		CW <input type="checkbox"/> CCW <input type="checkbox"/> Scan dB: N/A			Exam Batch:	14H073	
Cal. Blk. Temp.: 73		Exam Surface: O.D.			Type:	Ultragel II	
Comp. Temp.: 75		Surface Condition: Ground			Mfg.:	Sonotech, Inc.	
Recordable Indication(s): Yes <input type="checkbox"/> No <input checked="" type="checkbox"/>		(If Yes, Ref. Attached Ultrasonic Indication Report.)					
Results: Sat <input checked="" type="checkbox"/> Unsat <input type="checkbox"/> Eval <input type="checkbox"/>		Comments: T & C - For information only. *Gain adjusted to maintain 80% FSH.					
Percent Of Coverage Obtained > 90%: N/A		Reviewed Previous Data: Yes					

Examiner	Level	II-N	Signature	Date	Reviewer	Signature	Date
Williams, Christopher D.			<i>Ch. Williams</i>	3/8/2016	<i>D. B. King, II Level III</i>	<i>[Signature]</i>	3/15/16
Examiner	Level	II-N	Signature	Date	Site Review	Signature	Date
Nahory, W. Jason			<i>[Signature]</i>	3/8/2016	<i>John Sullivan</i>	<i>[Signature]</i>	3.16.16
Other	Level	N/A	Signature	Date	ANII Review	Signature	Date
<i>[Signature]</i>			<i>Z. Cline</i> → <i>Z. Cline</i>	3/16/16	<i>David M. Reynolds</i>	<i>[Signature]</i>	3-16-2016

CIRC. COVERAGE

UPSTREAM

$$0.15'' \times 0.395'' = 0.05925 \text{ in}^2 \text{ OBTAINED}$$

$$0.15'' \times 0.675'' = 0.13125 \text{ in}^2 \text{ TOTAL UPSTREAM}$$

$$0.05925 / 0.13125 = 45\% \text{ UPSTREAM OBTAINED}$$

Enclosure 2

BSEP, Unit 1 4th ISI Interval Limited NDE Data and Coverage Plots

DOWNSTREAM

$$0.16'' \times 0.25'' = 0.04 \text{ in}^2 \text{ OBTAINED}$$


$$0.16'' \times 0.675'' = 0.108 \text{ in}^2 \text{ TOTAL DOWNSTREAM}$$

$$0.04 / 0.108 = 37\% \text{ DOWNSTREAM OBTAINED}$$


$$(45 + 37) / 2 = \boxed{41\%} \text{ TOTAL CIRC COVERAGE OBTAINED}$$

PIPE

VALVE



Enclosure 2, BSEP, Unit 1 4th ISI Interval Limited
NDE Data and Coverage Plots




TOTAL AGGREGATE COVERAGE:

$$(100 + 100 + 45 + 37) / 4 = 70.5$$

Page 40 of 52

Enclosure 2
BSEP, Unit 1 4th ISI Interval Limited NDE Data and Coverage Plots

IBIIN2D-RPV-FWABA




LOWER 1/3 COVERAGE

$$1.2"(L) \times .26"(h) = .31^{\prime\prime}{}^2$$

$$1.2"(L) \times .28"(h) = .34^{\prime\prime}{}^2 +$$

TOTAL EXAM VOLUME $.65^{\prime\prime}{}^2$

CIRC MISSED COVERAGE 

$$.6"(L) \times .28"(h) = .17^{\prime\prime}{}^2$$

$$.17^{\prime\prime}{}^2 \div .65^{\prime\prime}{}^2 = 26.1\% \text{ MISSED}$$

$$100\% - 26.1\% = 73.9\% \text{ TOTAL CIRC}$$

Jason
Polisensky
PREPARED BY:

Jason Polisensky L-III 3/27/2019

Digitally signed by Jason
Polisensky
Date: 2019.03.27 15:00:24
-04'00'

REVIEWED BY:

D.B. King UT Level III


D.B. King

Digitally signed by David
King
Date: 2019.03.27 15:22:50
-04'00'

3/27/2019

Enclosure 2
BSEP, Unit 1 4th ISI Interval Limited NDE Data and Coverage Plots

IB||N2D-RPV-FWABA



1"

AXIAL = 80.4%

CIRC = 73.9% +

SCALE 1"

$154.3 \div 2 = 77.1\% \text{ TOTAL EXAM}$

COVERAGE ACHIEVED

PREPARED BY: Jason Polisensky

Jason Polisensky L-III 3/27/2019


Digitally signed by Jason Polisensky
Date: 2019.03.27 15:03:24
-04'00'

FULL VOLUME COVERAGE

$$1.2''(L) \times .86''(H) = 1.03''^2$$

$$1.2''(L) \times .80''(H) = 0.96''^2 +$$

TOTAL EXAM VOLUME $1.99''^2$




CIRC MISSED COVERAGE

$$.6''(L) \times .86''(H) = .52''^2$$

$$.52''^2 \div 1.99''^2 = 26.1\% \text{ MISSED}$$

$$100\% - 26.1\% = 73.9\% \text{ TOTAL CIRC}$$



AXIAL MISSED COVERAGE

$$(1.3''(L) \times .6''(H)) \div 2 = .39''^2$$

$$.39''^2 \div 1.99''^2 = 19.6\% \text{ MISSED}$$

$$100\% - 19.6\% = 80.4\% \text{ TOTAL AXIAL}$$

REVIEWED BY:

D.B. King D.B. King UT Level III 3/27/2019

Digitally signed by David King
Date: 2019.03.27 15:20:49
-04'00'

Enclosure 2
BSEP, Unit 1 4th ISI Interval Limited NDE Data and Coverage Plots

framatomé Automated Ultrasonic Phased Array Examination Summary Sheet				
Utility: Duke	Site: Brunswick	Unit: 1	Outage: B1R22	Summary Number: 1-CS-027-RI Report Number: BNP1-DM-2018-10
Weld Identification: 1B11N5B-RPV-FWRNB16A				WO#: 13468386
System: Core Spray	Material: SS/INC/CS	Nominal Diameter: 15.50"	Nominal Thickness: 0.90"	
Category: R1.14-2	Item No: E-7	Component Description: Safe End to Nozzle DM Weld		
Class: 1	Acceptance Criteria: ASME IWB 3514-2			
Procedure Number: 54-ISI-869 Revision: 000 SDCN: NA Procedure Title: Procedure for Encoded, Phased Array Ultrasonic Examination of Dissimilar Metal Piping Welds Technique Sheets: RS-TOPAZ-STD-02				
Procedure Number: 54-ISI-829 Revision: 013 SDCN: NA Procedure Title: PDI Generic Procedure for then Ultrasonic Examination of Dissimilar Metal Welds PDI-UT-10				
ASME Code, Section XI, Appendix VIII, Supplement 10 qualified automated ultrasonic phased array examination of weld 1B11N5B-RPV-FWRNB16A were performed by Framatome during the Brunswick Unit 1, B1R22 refueling outage. Final analysis of all examination data has identified:				
<ul style="list-style-type: none"> • No IGSCC/SCC flaws were detected. 				
Typical inside surface geometry and weld material responses were also observed.				
Circumferential flaw detection exams were performed from both sides of the weld using refracted longitudinal wave beam angles of 30°, 45°, 60° and 70° along with refracted shear wave beam angles of 45° and 60°. In addition to the automated examinations manual scans were performed utilizing 45° and 60° refracted longitudinal wave and 45° shear wave probes.				
Axial flaw detection exams were performed across the examination volume in both circumferential beam directions (CW/CCW) using refracted longitudinal wave beam angles of 25°, 35°, 45° and 55° along with shear wave beam angles of 35°, 45° and 55°. Each of the beam angles was additionally programmed to produce beam skews from -30° to +30° at a 2.5° skew angle resolution. In addition to the automated examination manual scans were performed utilizing a 45° shear wave probe to achieve additional coverage on the nozzle side of the weld.				
87.9% ASME code coverage was achieved with combining automated with manual pickups. <i>AR 02912258 WRITTEN TO DOCUMENT LIMITATION MAF 3-18-18</i>				
Previous UT examination data reports were reviewed prior to this summary. No discernible changes in any indication parameter have been observed. Examination overview images from the automated examination are provided in this report for future considerations.				
This examination meets the requirements of the ASME Code, Section XI, 2001 Edition with Addenda through 2003 as modified by the PDI program description document and 10CFR 50.55a Industry Codes and Standards, amended requirements, Final Rule.				
Prepared by: Jason Breza LVIII Signature: <i>Jason Breza</i>	Date: 03/13/2018	Reviewer: Nathan Bauman LVIII Signature: <i>Nathan Bauman</i>	Date: 03/13/2018	
Duke Review: Ned Finney Signature: <i>Ned Finney</i>	Date: 3-18-18	ANII Review: <i>David A. Reynolds</i> Signature: <i>David A. Reynolds</i>	Date: 3-18-2018	


Summary No: 1-CS-027-RI

Page 1 of 38

framatome


**Automated Ultrasonic Phased Array
Examination Summary Sheet**

Weld Configuration and Surface Condition Assessment



Surface conditioning was performed during B1R22 resulting in a procedurally acceptable scanning surface.

Brunswick Unit 1 N5B



Summary No: 1-CS-027-RI

Page 2 of 38

Document No.: 180-9283847-000


Page 361

Enclosure 2
BSEP, Unit 1 4th ISI Interval Limited NDE Data and Coverage Plots

framatom

Automated DM Piping Weld Scan Plan

Procedure:	54-ISI-869-000	Pipe Thickness T:	22.9	mm	Inches
Technique Sheet:	RS-TOPAZ-STD-02	Pipe OD:	393.2	15.48	
Plant / Unit:	Brunswick / Unit 1	Weld Extent Upstream Side Wu:	13.97	0.55	
Weld ID:	1B11N5B-RPV-FWRNB16A	Weld Extent Downstream Side Wd:	20.32	0.80	
Dual Side Access:	Yes	Access Limitation UpStream Side Lu:	165.1	6.50	
Complete Pipe:	Yes	Access Limitation Downstream Side Ld:	63.78	2.51	
Add Exam Volume (mm):	6.35	Weld Length:	1235.20	48.63	



SCANNING SEQUENCES AXIAL SCANS

Probe	Focal Law Group	Probe Type	Wedge Assembly	Scan			Index			Maximum Scan Speed mm	Done? (OK / NA)
				Start (mm)	End (mm)	Resol. (mm)	Start (mm)	End (mm)	Resol. (mm)		
LKUP	239_LKUP_TRL0_30-70	AS	360-152-230	-16.0	108.0	1.0	0.0	1280.0	2.0	50.0	OK
LKDN	239_LKDN_TRL180_30-70	AS	360-152-230	-43.0	71.1	1.0	-118.1	1141.9	2.0	50.0	OK
LKUP	239_LKUP_TRS0_45-80	AS	360-152-230	-16.0	108.0	1.0	0.0	1280.0	2.0	50.0	OK
LKDN	239_LKDN_TRS180_45-80	AS	360-152-230	-43.0	71.1	1.0	-118.1	1141.9	2.0	50.0	OK

SCANNING SEQUENCES CIRCUMFERENTIAL SCANS



Probe	Focal Law Group	Probe Type	Wedge Assembly	Scan			Index			Maximum Scan Speed mm	Done? (OK / NA)
				Start (mm)	End (mm)	Resol. (mm)	Start (mm)	End (mm)	Resol. (mm)		
LKCW	103_LKCW_TRL0_25-65	AS	10027103	0.0	1280.0	1.0	-16.0	80.0	5.0	25.0	OK
LKCCW	103_LKCCW_TRL180_25-65	AS	10027103	-154.3	1105.7	1.0	-16.0	80.0	5.0	25.0	OK
LKCW	108_LKCW_TRS0_35-85	AS	10027108	0.0	1280.0	1.0	-16.0	80.0	5.0	25.0	OK
LKCCW	108_LKCCW_TRS180_35-85	AS	10027108	-154.3	1105.2	1.0	-16.0	80.0	5.0	25.0	OK

 Highlighted values are actual mechanical scan parameters to be entered in motion control software prior to data collection

Data Analyst: Nathan Bauman

Signature: 

Date: 03/11/2018

NED FANCY
DUKE ENERGY 
UT 2-III
ANII DAVID M. REYNOLDS
Daniel M. Reynolds 

Summary No: 1-CS-027-R1

Page 3 of 38

Enclosure 2




BSEP, Unit 1 4th ISI Interval Limited NDE Data and Coverage Plots

framatom



Brunswick Unit 1 N5 LKUP Axial Scan Plan

Summary No.: 1-CS-027-RI


Document No.: 180-9283847-000



DETAIL B
SCALE 1 : 8



DETAIL A
SCALE 1 : 8



Enclosure 2



BSEP, Unit 1 4th ISI Interval Limited NDE Data and Coverage Plots

framatom




Summary No.: 1-CS-027-RI

Document No.: 180-9283847-000


Brunswick Unit 1 N5 LKDN Axial Scan Plan



DETAIL B
SCALE 1 : 8



DETAIL A
SCALE 1 : 8



Axis	Offset
Axial	-33.88
Circ	-118.14







Enclosure 2
BSEP, Unit 1 4th ISI Interval Limited NDE Data and Coverage Plots

framatomé

Summary No.: 1-CS-027-R1

Document No.: 180-9283847-000

Brunswick Unit 2 N5 Circumferential Scan Plan



Probe	Axis	Offset
L-Wave CCW	Axial	0.00
	Circ	-154.26
S-Wave CCW	Axial	0.00
	Circ	-154.76

Enclosure 2
BSEP, Unit 1 4th ISI Interval Limited NDE Data and Coverage Plots

Document No.: 1-CS-027-RI

Summary No: 1-CS-027-RI

framatome Automated Phased Array Data Analysis Report (Examination Data Sheet)				
Customer: Duke Energy	Procedure No.: 54-ISI-869	Summary Number: 1-CS-027-RI		
Site: Brunswick	Revision: 000	Report Number: BNP1-DM-2018-10		
Outage: B1R22	SOCH: N/A	Data Sheet Number: 1B11NSB-RPV-FWRNB16A-EDS-01		
Component Information				
System: Core Sprav	Measured OD: 15.4"	Weld Crown Width: 1.30" (including butter)		
Configuration: Safe End to Nozzle	Measured Thickness: 0.90"	Weld Crown Condition: Flush		
Weld ID(s): 1B11NSB-RPV-FWRNB16A	Material: SB166 Alloy 600 / Inconel / SA508 CL2	Component Temperature: 90°F		
Data Analysis Results				
Data File Name	Date/Time	Scan Type	Beam Direction	Results/Comments
1_BNP1_1B11NSB-RPV-FWRNB16A_Axis_LXUP_LXDN_LW_SW_AS_239_0-1260	03-11-2018 / 0302	Axial	LXUP / LXDN	ISG RG, CB
1_BNP1_1B11NSB-RPV-FWRNB16A_Axis_LXUP_LXDN_LW_SW_AS_249_0-1260_1	03-11-2018 / 0303	Axial	LXUP / LXDN	ISG, RG, CB
2_BNP1_1B11NSB-RPV-FWRNB16A_CRC_CW_CCW_LW_AS_103_0-1260_1	03-11-2018 / 1237	Circumferential	LXOW / LKCCW	ISG
2_BNP1_1B11NSB-RPV-FWRNB16A_CRC_CW_CCW_LW_AS_103_0-1260_2	03-11-2018 / 1238	Circumferential	LXOW / LKCCW	ISG
3_BNP1_1B11NSB-RPV-FWRNB16A_CRC_CW_CCW_SW_AS_103_0-1260	03-11-2018 / 1502	Circumferential	LXOW / LKCCW	
Data Analysis Results Legend (Classification)				
Non-Relevant Geometrical Indications	Non-Relevant Metallurgical Indications	Flaw Indications		
ISG: Inside Surface Geometry	AI: Acoustic Interface	Circ ID Flaw: ID Connected Circumferential Flaw		
RG: Root Geometry	BR: Beam Redirect	AX ID Flaw: ID Connected Axial Flaw		
CB: Counterbore		FMB: Embedded Weld Fabrication Flaw		
		Other: See Notes		
Notes: Automated scans limited due to N5 nozzle configuration (proximity to weld). Examination supplemented with manual scans to increase coverage.				
Other:				
Limitations: Yes				
Data Analyst: Jason Dreza <i>Jason Dreza</i>	Level: III Date: 03/11/2018	Data Analyst: Nathan Bauman <i>Nathan Bauman</i>	Level: III Date: 03/11/2018	
Utility Review: Ned Finney <i>Ned Finney</i>	Date: 3-18-18	ANII Review: DAVID A. REYNOLDS <i>David A. Reynolds</i>	Date: 3-18-2018	

Enclosure 2

BSEP, Unit 1 4th ISI Interval Limited NDE Data and Coverage Plots

Document No.: 180-9283847-000

Summary No.: 1-CS-027-RI

framatome		UT Examination Data Sheet Piping Welds				Report No.:	BNP1-SM-2018-10		
						Examination Data Sheet No.:		1B11N5B-RPV-FWRNB16A-EDS-01	
						Calibration Sheet No's.:		BNP1-N5-CS-04 BNP1-N5-CS-05 BNP1-N5-CS-06 BNP1-N5-CS-07	
Customer:	Duke Energy		Procedure		Component Information				
Site:	BNP	Unit:	1	54-ISI-829 Rev 013		System:	Corespray	Weld ID:	1B11N5B-RPV-FWRNB16A
Outage:	B1R22		Configuration:			SE to Nozzle	Nom. Diameter:	15.50"	
Procedure Title:	PDI Generic Procedure for the Ultrasonic Examination of Dissimilar Metal Welds PDI-UT-10				Material:	SS/INC/CS	Nom. Thickness:	0.90"	
					Scan Surface:	OD	Weld Width:	1.30"	
Examination Information									
Start Date:	03/13/2018	Start Time:	2321	Component Temperature:	90°F	Couplant Type:	Sonotech		
End Date:	03/13/2018	End Time:	2356	Thermometer Serial No.:	VH-15481	Couplant Batch No.:	17C011		
Angle / Mode	Direction	Cal Sheet No.	Scan Gain (dB)	Scan Limitation	Recordable Indications	Indication Data Sheet No.	Examiner Initials		
45° / Shear	Axial/Circ	CS-04	38.0	Yes	No	N/A	TT		
45° / RL	Axial	CS-05	47.0	No	No	N/A	TT		
60° / RL	Axial	CS-06	49.0	No	No	N/A	TT		
45° / RL	Circ	CS-07	52.0	Yes	No	N/A	TT		
Comments: Manual examination used to supplement automated examination to maximize coverage.									
Personnel		Name		Signature		Level	Date		
Examiner:	Travis Thomas				III	03/14/2018			
Examiner:	N/A		N/A		N/A	N/A			
Reviewer:	Jason Breza				III	03/14/2018			
Customer:	Ned Finney				III	3-18-18			
ANII:	DAVID M. REYNOLDS				N/A	3-18-2018			

Page 8 of 38

Page 367

Enclosure 2


BSEP, Unit 1 4th ISI Interval Limited NDE Data and Coverage Plots

framatome

Summary No: 1-CS-027-RI

Document No.: 180-9283847-000

UT Limitation Report
Circumferential Scans






Notes: During the examination of the N5B DM weld the circumferential examinations were limited due to the N5B nozzle configuration. The automated technique utilized longitudinal and shear wave probes oriented in the circumferential scan directions. -30° to 30° beam skews were used to interrogate the exam volume to its furthest extent. The beam skews provided additional coverage of the susceptible material at the wetted surface. In addition to the automated technique a manual 45° shear wave was used to interrogate additional base material on the nozzle side of the DM weld.

**Claiming coverage using beam skews isn't procedurally allowed. This calculation was provide to show how much area was interrogated during the examination.

NED FINNEY / David A. Bauman 3-18-18
DUKE ENERGY / David A. Bauman 3-18-18
UT L-III AR 02192258 WRITTEN TO DOCUMENT LIMITATION
ANII
DAVID M. REYNOLDS 3-18-2018
David M. Reynolds

Prepared by: Nathan Bauman LVIII
Date: 03/14/2018

Enclosure 2
BSEP, Unit 1 4th ISI Interval Limited NDE Data and Coverage Plots

framatome											
Automated Phased Array Indication Report											
Customer:Duke Energy			Procedure:54-ISI-869			Report Number:BNP1-DM-2018-10					
Site: Brunswick			Revision:000			Indication Report Number: 1B1IN5B-RPV-FWRNB16A-IR-01					
Outage:B1R22			SDCN:NA			Summary Number:1-CS-027-RI					
Component Information											
Weld ID:1B1IN5B-RPV-FWRNB16A			Measured OD:15.48"			Weld Crown Width: 1.30" (including butter)					
System:Core Spray			Measured Thickness: 0.60"			Weld Crown Condition:Flush					
Configuration:Seal End to Nozzle			Material:SB166 Alloy 600 / Inconel /SA508 CL2			Component Temperature:80°F					
Indication Parameters											
Indication Number (Orientation)	Beam Angle	Characterization	Indication OD Start (L1) (Inches)	Indication OD End (L2) (Inches)	Indication OD Length (L) (Inches)	Indication Axial Position	Upper Tip	Lower Tip	Indication Height (H) (Inches)	Indication Thruwall Extent %	Notes
NRI											
Notes/Comments:											
Data Analyst:Jason Greca			Level: II			Data Analyst:Nathan Bauman			Level: III		
			Date:03/11/2018						Date:03/11/2018		
Utility Review: Ned Firney			Date:  3-18-18			ANL Review: DAVID M. REYNOLDS			Date:  3-18-2018		

Enclosure 3

Relief Request ISI-12

**Brunswick Steam Electric Plant, Unit 2 Fourth Inservice Inspection (ISI) Interval Limited
Coverage Non-Destruction Examination (NDE) Data and Coverage Plots**



Ultrasonic Examination

Site/Unit:	BNP / 2	Procedure:	54-ISI-850-009	Outage No.:	B223R1
Summary No.:	2-B11-1078	Procedure Rev.:	009	Report No.:	VEN-17-010
Workscope:	ISI	Work Order No.:	20082951	Page:	1 of 1
Code:	ASME XI, 2001 Ed., 03 Ad.	Cat./Item:	B-D/B3.90	Location:	DW
Drawing No.:	C-02404 Sht. 001-1	Description: NOZZLE N1A TO REACTOR VESSEL WELD			
System ID:	1005				
Component ID:	2B11-RPV-N1A	Size/Length:	N/A	Thickness/Diameter:	N/A
Limitations:	Yes - Component configuration				

Comments:

Reference BNP Unit 2 Areva final report document # 180-9269913-000 for personnel certifications and equipment certifications.




Detection of flaw indications at the inner 15% t (measured from the clad to base metal interface) of nozzle-to-vessel welds when scanning parallel to the weld axis was performed utilizing 54-ISI-850-008 with SDCN 30-9269636-000.

Results: Sat Unsat Eval

Percent Of Coverage Obtained > 90%: No - 76.5%

Reviewed Previous Data: Yes

Examiner N/A	Level N/A	Signature	Date 3/26/2017	Reviewer Zimmerman, David Lvl III	Signature	Date 3/26/2017
Examiner N/A	Level N/A	Signature	Date	Site Review Finney, Ned Lvl III	Signature	Date 3/27/2017
Other N/A	Level N/A	Signature	Date	ANII Review Reynolds, David	Signature	Date 3/28/2017

 AREVA	<h2 style="margin: 0;">Ultrasonic Examination Summary Sheet</h2>				Summary No.: 2-B11-1078										
					Work Order: 2008295104										
	Component ID: 2B11-RPV-N1A														
	Customer: Duke Energy	Code Category: B-D	System: RPV												
Site: BNS	Unit: 2	Code Item: B3.90	Material: CS (Clad)												
Outage: B223R1	Code Class: 1	Description: RPV Nozzle to Shell Weld													
ISO / Drawing(s): C-02404 Sht. 1-1	EPRI Model No.: IR-2017-680														
Procedure Number	Procedure Revision	SDCN	Procedure Title												
54-ISI-850	008	30-9269636-000	Manual Ultrasonic Examination of BWR Reactor Vessel Nozzle Inner Radius Regions and Nozzle to Shell Welds (inner 15%)												
54-ISI-805	009	N/A	PDI Generic Procedure for Ultrasonic Examination of Reactor Pressure Vessel Welds PDI-UT-6												
Calibration Sheets	Exam Data Sheets	Indication Data Sheets	Indication Plot Sheets	Coverage Worksheet	Coverage Diagram	Exam Results									
CS-01	EDS-01	N/A	N/A	Yes	Yes	Acceptable									
CS-02	EDS-02														
CS-03															
Summary:															
Manual ultrasonic examinations were performed on the referenced weld during B223R1.															
In accordance with UT Procedure 54-ISI-805-009, 60° Longitudinal wave examinations were performed from the vessel surface in both the radial and circumferential scan directions.															
In accordance with UT Procedure 54-ISI-850-008 and the referenced EPRI model the following examinations were performed.															
<table border="1" style="width: 100%; border-collapse: collapse;"> <thead> <tr> <th colspan="3" style="padding: 2px;">Recirculation Outlet Nozzle (N1) Nozzle Modeling Parameters</th> </tr> <tr> <th style="padding: 2px;">Probe</th> <th style="padding: 2px;">Probe Skew</th> <th style="padding: 2px;">Scan Surface</th> </tr> </thead> <tbody> <tr> <td style="padding: 2px;">50° Shear</td> <td style="padding: 2px;">± (59° to 82°)</td> <td style="padding: 2px;">Vessel</td> </tr> </tbody> </table>							Recirculation Outlet Nozzle (N1) Nozzle Modeling Parameters			Probe	Probe Skew	Scan Surface	50° Shear	± (59° to 82°)	Vessel
Recirculation Outlet Nozzle (N1) Nozzle Modeling Parameters															
Probe	Probe Skew	Scan Surface													
50° Shear	± (59° to 82°)	Vessel													
76.5% coverage of the required examination volume was obtained. The percentage of coverage for this examination was calculated to the maximum extent possible allowed by the procedure qualification and actual component field conditions for this configuration.															
This examination was performed using the alternative examination volume defined in code case N-613-1 which reduces the area to be examined per IWB-2500-7 to the weld plus ½" on each side.															
This examination satisfies the requirements of ASME Sec. XI 2001 Edition with 2003 Addenda for Category B-D, item number B3.90, figure number IWB 2500-7 (b) exam volume, and was performed using ASME Sec XI, Appendix VIII qualified personnel, procedures, and equipment.															
Personnel	Name	Signature		Level	Date										
Prepared By:	John Gatica			II	03/26/2017										
AREVA Review:	David Zimmerman			III	03/27/2017										
Customer:	Ned Finney			III	3/27/2017										
ANII:	David M. Reynolds			N/A	3/28/2017										



AREVA

Supplemental Data Sheet

Page: 7 of 12

Component ID: 2B11-RPV-N1A


Utility: Duke Energy

Site / Unit: Brunswick / 2


Sketch: 1

Subject: Nozzle Overview

Scale: 10%

Weld Length @ Centerline: $(62.938 \times \pi) = 197.7"$ 

This scale is 100% in case of copier distortion

	Supplemental Data Sheet	Page: 8 of 12 Component ID: 2B11-RPV-N1A Utility: Duke Energy Site / Unit: Brunswick / 2														
Sketch: 2 Subject: Dimensions & Weld fit up Scale: 50%		<table border="1"> <thead> <tr> <th>Scan</th> <th>Description</th> </tr> </thead> <tbody> <tr> <td>R100:</td> <td>60° Radial Exam</td> </tr> <tr> <td>C85:</td> <td>60° Circ Exam / Outer 85%</td> </tr> <tr> <td>C15:</td> <td>50° Circ Exam / Inner 15%</td> </tr> </tbody> </table>	Scan	Description	R100:	60° Radial Exam	C85:	60° Circ Exam / Outer 85%	C15:	50° Circ Exam / Inner 15%						
Scan	Description															
R100:	60° Radial Exam															
C85:	60° Circ Exam / Outer 85%															
C15:	50° Circ Exam / Inner 15%															
 <table border="1" style="margin-left: auto; margin-right: auto;"> <tr> <td style="padding: 2px;">Weld Width @ OD:</td> <td style="padding: 2px;">0.625"</td> </tr> <tr> <td style="padding: 2px;">Weld Width @ ID:</td> <td style="padding: 2px;">2.0"</td> </tr> <tr> <td style="padding: 2px;">RPV Thick. (Excluding Clad):</td> <td style="padding: 2px;">5.5"</td> </tr> <tr> <td style="padding: 2px;">Weld Length:</td> <td style="padding: 2px;">197.7" @ CL</td> </tr> <tr> <td style="padding: 2px;">Exam Area:</td> <td style="padding: 2px;">16.64 in²</td> </tr> <tr> <td style="padding: 2px;">GHCD:</td> <td style="padding: 2px;">Inner 15%</td> </tr> <tr> <td colspan="2" style="padding: 2px;">Exam Area: ABCD $= (EBCD) + (AFE)$ $= (3.0 \times 5.5) + (1.4 \times 0.2)/2 = 16.64 \text{ in}^2$</td> </tr> </table>			Weld Width @ OD:	0.625"	Weld Width @ ID:	2.0"	RPV Thick. (Excluding Clad):	5.5"	Weld Length:	197.7" @ CL	Exam Area:	16.64 in ²	GHCD:	Inner 15%	Exam Area: ABCD $= (EBCD) + (AFE)$ $= (3.0 \times 5.5) + (1.4 \times 0.2)/2 = 16.64 \text{ in}^2$	
Weld Width @ OD:	0.625"															
Weld Width @ ID:	2.0"															
RPV Thick. (Excluding Clad):	5.5"															
Weld Length:	197.7" @ CL															
Exam Area:	16.64 in ²															
GHCD:	Inner 15%															
Exam Area: ABCD $= (EBCD) + (AFE)$ $= (3.0 \times 5.5) + (1.4 \times 0.2)/2 = 16.64 \text{ in}^2$																
<p>Note: Exam area extends to $\frac{1}{2}$" beyond weld per code case N-613-1</p> <div style="text-align: center;">  <p>This scale is 100% in case of copier distortion</p> </div>																

Enclosure 3
BSEP, Unit 2 4th ISI Interval Limited NDE Data and Coverage Plots




**Supplemental
Data Sheet**

Page:	9 of 12
Component ID:	2B11-RPV-N1A
Utility:	Duke Energy
Site / Unit:	Brunswick / 2

Sketch: 3

Scan: R100


Scale: 50%



Exam Area (ABCD): 16.64 in²

Examined: (KBLJ) + (JLCD)

Examined: $1.1(1.2 + 3.0)/2 + (3.0 \times 4.4) = 15.51$ in²






**Supplemental
Data Sheet**

Page:	10 of 12
Component ID:	2B11-RPV-N1A
Utility:	Duke Energy
Site / Unit:	Brunswick / 2


Sketch: 4

Scan: C85

Scale: 50%



Exam Area (ABCD): 16.64 in²
Examined: (KBHM)
Examined: $4.67(1.2 + 2.0)/2 = 7.47 \text{ in}^2$



Enclosure 3
BSEP, Unit 2 4th ISI Interval Limited NDE Data and Coverage Plots

AREVA	Supplemental Data Sheet	Page: 11 of 12 Component ID: 2B11-RPV-N1A Utility: Duke Energy Site / Unit: Brunswick / 2
--------------	--------------------------------	--

Sketch: 5
Scan: C15
Scale: 50%

The diagram illustrates a coverage plot. A large trapezoidal region is filled with diagonal hatching. Within this, a smaller trapezoidal region ABCD is shaded with vertical lines. Point A is at the top left, B is at the top right, C is at the bottom right, and D is at the bottom left. Dashed lines connect A to E (top) and D to G (bottom). Point E is on the top horizontal boundary, and point G is on the bottom horizontal boundary. Point O is located between D and C on the bottom boundary. Point H is located between G and C on the bottom boundary. The region N1A is labeled to the left of the top boundary, and RPV is labeled to the right.

Exam Area (ABCD): 16.64 in²
Examined: (GHCD)
Examined: (3.0 x 0.83) = 2.49 in²

0 1" 2" 3"

This scale is 100% in case of copier distortion



Supplemental Data Sheet

Page: 12 of 12

Component ID: 2B11-RPV-N1A

Utility: Duke Energy

Site / Unit: Brunswick / 2

ASME Code Coverage Calculation

Component Information		Scan	Description
Exam Area: 16.64 in ²		R100:	60° Radial Exam
Exam Length: 197.7"		C85:	60° Circ Exam / Outer 85%
		C15:	50° Circ Exam / Inner 15%

See Sketch	Area Scan	Exam Examined Area	Length Exam Examined Length	Percent Coverage
3	R100	(15.51 / 16.64) x (197.7 / 197.7) x 100 =		93.21%
4	C85	(7.47 / 16.64) x (197.7 / 197.7) x 100 =		44.89%
5	C15	(2.49 / 16.64) x (197.7 / 197.7) x 100 =		14.96%
		(/ ~) x (/ ~) x 100 =		~
		(/ ~) x (/ ~) x 100 =		~
				Total Percent: 153.06%
Code Examination Coverage (Total Percent / 2 Sound Beams):				76.5%

Reference the following for Nozzle Dimensions

Contract No.: 68-2471 / 72, Dwg. No.: 27 Rev 16

Note: 100% radial & circumferential coverage obtained in the lower 15% of exam volume.

Personnel	Name	Signature	Level	Date
Prepared By:	Simon Crothers	<i>Simon Crothers</i>	II	03/27/17
Reviewed By:	David K. Zimmerman	<i>David K. Zimmerman</i>	III	03/27/2017
Site Review:	NED FINNEY	<i>Ned Finney</i>	III	3/27/2017



Ultrasonic Examination

Site/Unit:	BNP / 2	Procedure:	54-ISI-805-009	Outage No.:	B223R1
Summary No.:	2-B11-1080	Procedure Rev.:	009	Report No.:	VEN-17-011
Workscope:	ISI	Work Order No.:	20082951	Page:	1 of 1
Code:	ASME XI, 2001 Ed., 03 Ad.	Cat./Item:	B-D/B3.90	Location:	DW
Drawing No.:	C-02404 Sht. 001-1	Description: NOZZLE N1B TO REACTOR VESSEL WELD			
System ID:	1005				
Component ID:	2B11-RPV-N1B	Size/Length:	N/A	Thickness/Diameter:	N/A
Limitations:	Yes - Component configuration				

Comments:

Reference BNP Unit 2 Areva final report document # 180-9269913-000 for personnel certifications and equipment certifications.

Detection of flaw indications at the inner 15% t (measured from the clad to base metal interface) of nozzle-to-vessel welds when scanning parallel to the weld axis was performed utilizing 54-ISI-850-008 with SDCN 30-9269636-000.

Results: Sat Unsat Eval

Percent Of Coverage Obtained > 90%: No - 76.5%

Reviewed Previous Data: Yes

Examiner N/A	Level N/A	Signature	Date 3/26/2017	Reviewer Zimmerman, David Lvl III	Signature	Date 3/28/2017
Examiner N/A	Level N/A	Signature	Date	Site Review Finney, Ned Lvl III	Signature	Date 3/28/2017
Other N/A	Level N/A	Signature	Date	ANII Review Reynolds, David	Signature	Date 3/28/2017

 AREVA	<h2 style="margin: 0;">Ultrasonic Examination Summary Sheet</h2>				Summary No.: 2-B11-1080	
					Work Order: 2008295114	
	Component ID: 2B11-RPV-N1B					
	Customer: Duke Energy	Code Category: B-D	System: RPV			
Site: BNS	Unit: 1	Code Item: B3.90	Material: CS (Clad)			
Outage: B223R1	Code Class: 1	Description: RPV Nozzle to Shell Weld				
ISO / Drawing(s): C-02404 -1-1	EPRI Model No.: IR-2017-680					
Procedure Number	Procedure Revision	SDCN	Procedure Title			
54-ISI-850	008	30-9269636-000	Manual Ultrasonic Examination of BWR Reactor Vessel Nozzle Inner Radius Regions and Nozzle to Shell Welds (inner 15%)			
54-ISI-805	009	N/A	PDI Generic Procedure for Ultrasonic Examination of Reactor Pressure Vessel Welds PDI-UT-6			
Calibration Sheets	Exam Data Sheets	Indication Data Sheets	Indication Plot Sheets	Coverage Worksheet	Coverage Diagram	Exam Results
CS-01	EDS-01	N/A	N/A	Yes	Yes	Acceptable
CS-02	EDS-02					
CS-03						

Summary:

Manual ultrasonic examinations were performed on the referenced weld during B223R1.

In accordance with UT Procedure 54-ISI-805-009, 60° Longitudinal wave examinations were performed from the vessel surface in both the radial and circumferential scan directions.


In accordance with UT Procedure 54-ISI-850-008 and the referenced EPRI model the following examinations were performed.

Recirculation Outlet Nozzle (N1) Nozzle Modeling Parameters		
Probe	Probe Skew	Scan Surface
50° Shear	± (59° to 82°)	Vessel

76.5% coverage of the required examination volume was obtained. The percentage of coverage for this examination was calculated to the maximum extent possible allowed by the procedure qualification and actual component field conditions for this configuration.

This examination was performed using the alternative examination volume defined in code case N-613-1 which reduces the area to be examined per IWB-2500-7 to the weld plus $\frac{1}{2}$ " on each side.

This examination satisfies the requirements of ASME Sec. XI 2001 Edition with 2003 Addenda for Category B-D, item number B3.90, figure number IWB 2500-7 (b) exam volume, and was performed using ASME Sec XI, Appendix VIII qualified personnel, procedures, and equipment.

Personnel	Name	Signature	Level	Date
Prepared By:	Wade Holloway		III	03/26/2017
AREVA Review:	David Zimmerman		III	03/28/2017
Customer:	Ned Finney		III	3/28/17
ANII:	David M. Reynolds		N/A	3/28/2017



Supplemental Data Sheet

Page: 7 of 12

Component ID: 2B11-RPV-N1B



Utility: Duke Energy

Site / Unit: Brunswick / 2

Sketch: 1

Subject: Nozzle Overview

Scale: 10%



AREVA	Supplemental Data Sheet	Page:	8 of 12
		Component ID:	2B11-RPV-N1B
		Utility:	Duke Energy
		Site / Unit:	Brunswick / 2
		Sketch:	2
Subject:	Dimensions & Weld fit up		
Scale:	50%		
Scan	Description		
R100:	60° Radial Exam		
C85:	60° Circ Exam / Outer 85%		
C15:	50° Circ Exam / Inner 15%		

Sketch: 2

Subject: Dimensions & Weld fit up

Scale: 50%

RPV

Weld Width @ OD: 0.625"

Weld Width @ ID: 2.0"

RPV Thick. (Excluding Clad): 5.5"

Weld Length: 197.7" @ CL

Exam Area: 16.64 in²


GHCD: Inner 15%

Exam Area: ABCD
 $= (EBCD) + (AFE)$
 $= (3.0 \times 5.5) + (1.4 \times 0.2)/2 = 16.64 \text{ in}^2$

Note: Exam area extends to 1/2" beyond weld per code case N-613-1

0 1" 2" 3"

This scale is 100% in case of copier distortion






Supplemental Data Sheet

Page:	10 of 12
Component ID:	2B11-RPV-N1B
Utility:	Duke Energy
Site / Unit:	Brunswick / 2

Sketch: 4

Scan: C85


Scale: 50%




Exam Area (ABCD): 16.64 in²

Examined: (KBHM)

Examined: $4.67(1.2 + 2.0)/2 = 7.47 \text{ in}^2$







Supplemental Data
Sheet

Page: 12 of 12

Component ID: 2B11-RPV-N1B

Utility: Duke Energy

Site / Unit: Brunswick / 2

ASME Code Coverage Calculation

Component Information		Scan	Description
Exam Area: 16.64 in ²		R100:	60° Radial Exam
Exam Length: 197.7"		C85:	60° Circ Exam / Outer 85%
		C15:	50° Circ Exam / Inner 15%

See		Area	Exam	Length	Exam	Percent
Sketch	Scan	Examined	Area	Examined	Length	Coverage
3	R100	(15.51 / 16.64) x (197.7 / 197.7) x 100 =				93.21%
4	C85	(7.47 / 16.64) x (197.7 / 197.7) x 100 =				44.89%
5	C15	(2.49 / 16.64) x (197.7 / 197.7) x 100 =				14.96%
		(/ ~) x (/ ~) x 100 =				~
		(/ ~) x (/ ~) x 100 =				~
Total Percent:						153.06%
Code Examination Coverage (Total Percent / 2 Sound Beams):						76.5%

Reference the following for Nozzle Dimensions

Contract No.: 68-2471 / 72, Dwg. No.: 27 Rev 16

Note: 100% radial & circumferential coverage obtained in the lower 15% of exam volume.

Personnel	Name	Signature	Level	Date
Prepared By:	Simon Crothers	<i>Simon Crothers</i>	II	03/27/17
Reviewed By:	David K. Zimmerman	<i>David K. Zimmerman</i>	III	03/27/2017
Site Review:	<i>NEO FINNISY</i>	<i>Matt Finney</i>	III	3/28/17



Ultrasonic Examination

Site/Unit: BNP / 2 Procedure: 54-ISI-805-009 Outage No.: B223R1
Summary No.: 2-B11-10B4 Procedure Rev.: 009 Report No.: VEN-17-012
Workscope: ISI Work Order No.: 20082951 Page: 1 of 1
Code: ASME XI, 2001 Ed., 03 Ad. Cat./Item: B-D/B3.90 Location: DW
Drawing No.: C-02404 Sht. 001-1 Description: NOZZLE N2B TO REACTOR VESSEL WELD
System ID: 1005
Component ID: 2B11-RPV-N2B Size/Length: N/A Thickness/Diameter: N/A
Limitations: Yes - Component configuration

Comments:

Reference BNP Unit 2 Areva final report document # 180-9269913-000 for personnel certifications and equipment certifications.

Detection of flaw indications at the inner 15% t (measured from the clad to base metal interface) of nozzle-to-vessel welds when scanning parallel to the weld axis was performed utilizing 54-ISI-850-008 with SDCN 30-9269636-000.

Results: Sat Unsat Eval

Percent Of Coverage Obtained > 90%: No - 72.8%

Reviewed Previous Data: Yes

Examiner	Level	Signature	Date	Reviewer	Signature	Date
N/A			3/22/2017	Zimmerman, David Lvl III		3/27/2017
Examiner	Level	N/A	Signature	Date	Site Review	Signature
N/A					Finney, Ned Lvl III	3/27/2017
Other	Level	N/A	Signature	Date	ANII Review	Signature
N/A					Reynolds, David	3/27/2017

AREVA		Ultrasonic Examination Summary Sheet			Summary No.: 2-B11-1084										
					Work Order: 2008295124										
			Component ID: 2B11-RPV-N2B												
Customer:	Duke Energy		Code Category:	B-D	System: RPV										
Site:	BNS	Unit: 2	Code Item:	B3.90	Material: CS (Clad)										
Outage:	B223R1		Code Class:	1	Description: RPV Nozzle to Shell Weld										
ISO / Drawing(s):	C-02404-1-1			EPRI Model No.:	IR-2017-680										
Procedure Number	Procedure Revision		SDCN		Procedure Title										
54-ISI-850	008		30-9269636-000		Manual Ultrasonic Examination of BWR Reactor Vessel Nozzle Inner Radius Regions and Nozzle to Shell Welds (inner 15%)										
54-ISI-805	009		N/A		PDI Generic Procedure for Ultrasonic Examination of Reactor Pressure Vessel Welds PDI-UT-6										
Calibration Sheets	Exam Data Sheets	Indication Data Sheets	Indication Plot Sheets	Coverage Worksheet/Diagrams		Exam Results									
CS-01	EDS-01	N/A	N/A	Yes	Yes	Acceptable									
CS-02	EDS-02														
CS-03															
Summary:															
Manual ultrasonic examinations were performed on the referenced weld during B223R1.															
In accordance with UT Procedure 54-ISI-805-009, 60° Longitudinal wave examinations were performed from the vessel surface in both the radial and circumferential scan directions.															
In accordance with UT Procedure 54-ISI-850-008 and the referenced EPRI model the following examinations were performed.															
<table border="1"> <thead> <tr> <th colspan="3">Recirculation Inlet Nozzle (N2B) Nozzle Modeling Parameters</th> </tr> <tr> <th>Probe</th> <th>Probe Skew</th> <th>Scan Surface</th> </tr> </thead> <tbody> <tr> <td>50° Shear</td> <td>± (51° to 76°)</td> <td>Vessel</td> </tr> </tbody> </table>							Recirculation Inlet Nozzle (N2B) Nozzle Modeling Parameters			Probe	Probe Skew	Scan Surface	50° Shear	± (51° to 76°)	Vessel
Recirculation Inlet Nozzle (N2B) Nozzle Modeling Parameters															
Probe	Probe Skew	Scan Surface													
50° Shear	± (51° to 76°)	Vessel													
72.8% coverage of the required examination volume was obtained. The percentage of coverage for this examination was calculated to the maximum extent possible allowed by the procedure qualification and actual component field conditions for this configuration.															
This examination was performed using the alternative examination volume defined in code case N-613-1 which reduces the area to be examined per IWB-2500-7 to the weld plus $\frac{1}{2}$ " on each side.															
This examination satisfies the requirements of ASME Sec. XI 2001 Edition with 2003 Addenda for Category B-D, item number B3.90, figure number IWB 2500-7 (b) exam volume, and was performed using ASME Sec XI, Appendix VIII qualified personnel, procedures, and equipment.															
Personnel	Name		Signature		Level	Date									
Prepared By:	George Chapman				III	03/22/2017									
Prepared By:	John Gatica				II	03/22/2017									
AREVA Review:	David Zimmerman				III	03/22/2017									
Customer:	Ned Finney				III	03/22/2017									
ANII:	David M. Reynolds				N/A	03/22/2017									

**A
REVA****Supplemental Data Sheet**

Page: 7 of 12

Component ID: 2B11-RPV-N2B


Utility: Duke Energy



Site / Unit: Brunswick / 2

Sketch: 1

Subject: Nozzle Overview

Scale: 20%




 Supplemental Data Sheet	Page: 8 of 12 Component ID: 2B11-RPV-N2B Utility: Duke Energy Site / Unit: Brunswick / 2														
Sketch: 2 Subject: Dimensions & Weld fit up Scale: 50%															
<table border="1" style="width: 100%; border-collapse: collapse;"> <thead> <tr> <th style="text-align: center;">Scan</th> <th style="text-align: center;">Description</th> </tr> </thead> <tbody> <tr> <td style="text-align: center;">R100:</td> <td>60° Radial Exam</td> </tr> <tr> <td style="text-align: center;">C85:</td> <td>60° Circ Exam / Outer 85%</td> </tr> <tr> <td style="text-align: center;">C15:</td> <td>50° Circ Exam / Inner 15%</td> </tr> </tbody> </table>		Scan	Description	R100:	60° Radial Exam	C85:	60° Circ Exam / Outer 85%	C15:	50° Circ Exam / Inner 15%						
Scan	Description														
R100:	60° Radial Exam														
C85:	60° Circ Exam / Outer 85%														
C15:	50° Circ Exam / Inner 15%														
															
<table border="1" style="width: 100%; border-collapse: collapse;"> <tr> <td style="text-align: center;">Weld Width @ OD:</td> <td>0.625"</td> </tr> <tr> <td style="text-align: center;">Weld Width @ ID:</td> <td>2.0"</td> </tr> <tr> <td colspan="2" style="text-align: center;">RPV Thick. (Excluding Clad): 5.5"</td> </tr> <tr> <td colspan="2" style="text-align: center;">Weld Length: 113.5" @ CL</td> </tr> <tr> <td colspan="2" style="text-align: center;">Exam Area: 16.71 in²</td> </tr> <tr> <td colspan="2" style="text-align: center;">GHCD: Inner 15%</td> </tr> <tr> <td colspan="2" style="text-align: center;">Exam Area: ABCD = (EBCD) + (AFE) = (3.0 x 5.5) + (1.4 x 0.3)/2 = 16.71 in²</td> </tr> </table>		Weld Width @ OD:	0.625"	Weld Width @ ID:	2.0"	RPV Thick. (Excluding Clad): 5.5"		Weld Length: 113.5" @ CL		Exam Area: 16.71 in ²		GHCD: Inner 15%		Exam Area: ABCD = (EBCD) + (AFE) = (3.0 x 5.5) + (1.4 x 0.3)/2 = 16.71 in ²	
Weld Width @ OD:	0.625"														
Weld Width @ ID:	2.0"														
RPV Thick. (Excluding Clad): 5.5"															
Weld Length: 113.5" @ CL															
Exam Area: 16.71 in ²															
GHCD: Inner 15%															
Exam Area: ABCD = (EBCD) + (AFE) = (3.0 x 5.5) + (1.4 x 0.3)/2 = 16.71 in ²															
 <p>This scale is 100% in case of copier distortion</p>															




**Supplemental
Data Sheet**

Page:	9 of 12
Component ID:	2B11-RPV-N2B
Utility:	Duke Energy
Site / Unit:	Brunswick / 2

Sketch: 3
Scan: R100
Scale: 50%



Exam Area (ABCD): 16.71 in²
Examined: (KBLJ) + (JLCD)
Examined: $1.2(1.0 + 3.0)/2 + (3.0 \times 4.3) = 15.30 \text{ in}^2$



Enclosure 3
BSEP, Unit 2 4th ISI Interval Limited NDE Data and Coverage Plots

AREVA	Supplemental Data Sheet	Page: 10 of 12
		Component ID: 2B11-RPV-N2B
		Utility: Duke Energy
		Site / Unit: Brunswick / 2

Sketch: 4
Scan: C85
Scale: 50%

N2B

RPV

A

K

B

G

M

O

D

C

Exam Area (ABCD): 16.71 in²
Examined: (KBHM)
Examined: $4.67(1.0 + 1.8)/2 = 6.54 \text{ in}^2$

0 1" 2" 3"

This scale is 100% in case of copier distortion


Enclosure 3
BSEP, Unit 2 4th ISI Interval Limited NDE Data and Coverage Plots



**Supplemental
Data Sheet**

Page:	11 of 12
Component ID:	2B11-RPV-N2B
Utility:	Duke Energy
Site / Unit:	Brunswick / 2

Sketch: 5
Scan: C15
Scale: 50%



Exam Area (ABCD): 16.71 in²
Examined: (GHCD)
Examined: (3.0 x 0.83) = 2.49 in²

0 1" 2" 3"
This scale is 100% in case of copier distortion



Supplemental Data Sheet

Page: 12 of 12

Component ID: 2B11-RPV-N2B

Utility: Duke Energy

Site / Unit: Brunswick / 2

ASME Code Coverage Calculation

Component Information		Scan	Description
Exam Area: 16.71 in ²		R100	60° Radial Exam
Exam Length: 113.5"		C85	60° Circ Exam / Outer 85%
		C15	50° Circ Exam / Inner 15%

See	Area	Exam	Length	Exam	Percent	
Sketch	Scan	Examined	Area	Examined	Length	Coverage
3	R100	(15.30 / 16.71) x (113.5 / 113.5) x 100 =				91.56%
4	C85	(6.54 / 16.71) x (113.5 / 113.5) x 100 =				39.14%
5	C15	(2.49 / 16.71) x (113.5 / 113.5) x 100 =				14.90%
		(/ ~) x (/ ~) x 100 =				~
		(/ ~) x (/ ~) x 100 =				~
						Total Percent:
						145.60%
Code Examination Coverage (Total Percent / 2 Sound Beams):						72.8%

Reference the following for Nozzle Dimensions

Contract No.: 68-2471 / 72, Dwg. No.: 28 Rev 19

Note: 100% radial & circumferential coverage obtained in the lower 15% of exam volume.

Personnel	Name	Signature	Level	Date
Prepared By:	Simon Crothers	<i>Simon Crothers</i>	II	03/27/17
Reviewed By:	David K. Zimmerman	<i>David K. Zimmerman</i>	III	03/27/2017
Site Review:	NED FENNEY	<i>Ned Fenney</i>	III	3/27/2017



Ultrasonic Examination

Site/Unit:	BNP / 2	Procedure:	54-ISI-805-009	Outage No.:	B223R1
Summary No.:	2-B11-1086	Procedure Rev.:	009	Report No.:	VEN-17-014
Workscope:	ISI	Work Order No.:	20082951	Page:	1 of 1
Code:	ASME XI, 2001 Ed., 03 Ad.	Cal./Item:	B-D/B3.90	Location:	DW
Drawing No.:	C-02404 Sht. 001-1	Description: NOZZLE N2C TO REACTOR VESSEL WELD			
System ID:	1005				
Component ID:	2B11-RPV-N2C	Size/Length:	N/A	Thickness/Diameter:	N/A
Limitations:	Yes - Component configuration				

Comments:

Reference BNP Unit 2 Areva final report document # 180-9269913-000 for personnel certifications and equipment certifications.

Detection of flaw indications at the inner 15% t (measured from the clad to base metal interface) of nozzle-to-vessel welds when scanning parallel to the weld axis was performed utilizing 54-ISI-850-008 with SDCN 30-9269636-000.






Results: Sat Unsat Eval

Percent Of Coverage Obtained > 90%: No - 72.8%

Reviewed Previous Data: Yes

Examiner	Level	Signature	Date	Reviewer	Signature	Date
N/A			3/22/2017	Zimmerman, David Lvl III		3/27/2017
Examiner	Level	N/A	Signature	Date	Site Review	Signature
N/A					Finney, Ned Lvl III	3/27/2017
Other	Level	N/A	Signature	Date	ANII Review	Signature
N/A					Reynolds, David	3/27/2017

Enclosure 3
BSEP, Unit 2 4th ISI Interval Limited NDE Data and Coverage Plots


 AREVA		Ultrasonic Examination Summary Sheet				Summary No.:	2-B11-1086									
						Work Order:	2008295134									
						Component ID:	2B11-RPV-N2C									
						Customer:	Duke Energy	Code Category:	B-D	System:	RPV					
Site:	BNS	Unit:	2	Code Item:	B3.90	Material:	CS (Clad)									
Outage:	B223R1		Code Class:	1	Description:	RPV Nozzle to Shell Weld										
ISO / Drawing(s):	C-02404-1-1				EPRI Model No.:	IR-2017-680										
Procedure Number		Procedure Revision		SDCN		Procedure Title										
54-ISI-850		008		30-9269636-000		Manual Ultrasonic Examination of BWR Reactor Vessel Nozzle Inner Radius Regions and Nozzle to Shell Welds (inner 15%)										
54-ISI-805		009		N/A		PDI Generic Procedure for Ultrasonic Examination of Reactor Pressure Vessel Welds PDI-UT-6										
Calibration Sheets	Exam Data Sheets	Indication Data Sheets	Indication Plot Sheets	Coverage Worksheet	Coverage Diagram	Exam Results										
CS-01	EDS-01	N/A	N/A	Yes	Yes	Acceptable										
CS-02	EDS-02															
CS-03																
Summary:																
Manual ultrasonic examinations were performed on the referenced weld during B223R1.																
In accordance with UT Procedure 54-ISI-805-009, 60° Longitudinal wave examinations were performed from the vessel surface in both the radial and circumferential scan directions.																
In accordance with UT Procedure 54-ISI-850-008 and the referenced EPRI model the following examinations were performed.																
<table border="1" style="width: 100%; border-collapse: collapse;"> <thead> <tr> <th colspan="3">Recirculation Inlet Nozzle (N2C) Nozzle Modeling Parameters</th> </tr> <tr> <th>Probe</th> <th>Probe Skew</th> <th>Scan Surface</th> </tr> </thead> <tbody> <tr> <td>50° Shear</td> <td>± (51° to 76°)</td> <td>Vessel</td> </tr> </tbody> </table>								Recirculation Inlet Nozzle (N2C) Nozzle Modeling Parameters			Probe	Probe Skew	Scan Surface	50° Shear	± (51° to 76°)	Vessel
Recirculation Inlet Nozzle (N2C) Nozzle Modeling Parameters																
Probe	Probe Skew	Scan Surface														
50° Shear	± (51° to 76°)	Vessel														
72.8% coverage of the required examination volume was obtained. The percentage of coverage for this examination was calculated to the maximum extent possible allowed by the procedure qualification and actual component field conditions for this configuration.																
This examination was performed using the alternative examination volume defined in code case N-613-1 which reduces the area to be examined per IWB-2500-7 to the weld plus ½" on each side.																
This examination satisfies the requirements of ASME Sec. XI 2001 Edition with 2003 Addenda for Category B-D, item number B3.90, figure number IWB 2500-7 (b) exam volume, and was performed using ASME Sec XI, Appendix VIII qualified personnel, procedures, and equipment.																
Personnel	Name		Signature		Level	Date										
Prepared By:	George Chapman				III	03/22/2017										
Prepared By:	John Gatica				II	03/22/2017										
AREVA Review:	David Zimmerman				III	03/27/2017										
Customer:	Ned Finney				III	03/27/2017										
ANII:	David M. Reynolds				N/A	03/27/2017										

A
REVA

Supplemental Data Sheet

Page:	7	of	12
Component ID:	2B11-RPV-N2C		
Utility:	Duke Energy		
Site / Unit:	Brunswick / 2		

Sketch: 1
Subject: Nozzle Overview
Scale: 20%



AREVA	Supplemental Data Sheet	Page:	8 of 12																	
		Component ID:	2B11-RPV-N2C																	
		Utility:	Duke Energy																	
		Site / Unit:	Brunswick / 2																	
Sketch: 2																				
Subject: Dimensions & Weld fit up	Scan	Description																		
Scale: 50%	R100:	60° Radial Exam																		
	C85:	60° Circ Exam / Outer 85%																		
	C15:	50° Circ Exam / Inner 15%																		
<table border="1"> <tr> <td>Weld Width @ OD:</td> <td>0.625"</td> </tr> <tr> <td>Weld Width @ ID:</td> <td>2.0"</td> </tr> <tr> <td>RPV Thick. (Excluding Clad):</td> <td>5.5"</td> </tr> <tr> <td>Weld Length:</td> <td>113.5" @ CL</td> </tr> <tr> <td>Exam Area:</td> <td>16.71 in²</td> </tr> <tr> <td>GHCD:</td> <td>Inner 15%</td> </tr> <tr> <td colspan="2">Exam Area: ABCD</td> </tr> <tr> <td colspan="2">= (EBCD) + (AFE)</td> </tr> <tr> <td colspan="2">= (3.0 x 5.5) + (1.4 x 0.3)/2 = 16.71 in²</td> </tr> </table>		Weld Width @ OD:	0.625"	Weld Width @ ID:	2.0"	RPV Thick. (Excluding Clad):	5.5"	Weld Length:	113.5" @ CL	Exam Area:	16.71 in ²	GHCD:	Inner 15%	Exam Area: ABCD		= (EBCD) + (AFE)		= (3.0 x 5.5) + (1.4 x 0.3)/2 = 16.71 in ²		
Weld Width @ OD:	0.625"																			
Weld Width @ ID:	2.0"																			
RPV Thick. (Excluding Clad):	5.5"																			
Weld Length:	113.5" @ CL																			
Exam Area:	16.71 in ²																			
GHCD:	Inner 15%																			
Exam Area: ABCD																				
= (EBCD) + (AFE)																				
= (3.0 x 5.5) + (1.4 x 0.3)/2 = 16.71 in ²																				
<p>Note: Exam area extends to $\frac{1}{2}$" beyond weld per code case N-613-1</p>																				


Enclosure 3
BSEP, Unit 2 4th ISI Interval Limited NDE Data and Coverage Plots




**Supplemental
Data Sheet**

Page:	9 of 12
Component ID:	2B11-RPV-N2C
Utility:	Duke Energy
Site / Unit:	Brunswick / 2

Sketch: 3
Scan: R100
Scale: 50%



Exam Area (ABCD): 16.71 in²
Examined: (KBLJ) + (JLCD)
Examined: $1.2(1.0 + 3.0)/2 + (3.0 \times 4.3) = 15.30$ in²






**Supplemental
Data Sheet**

Page:	10 of 12
Component ID:	2B11-RPV-N2C
Utility:	Duke Energy
Site / Unit:	Brunswick / 2

Sketch: 4

Scan: C85


Scale: 50%



Exam Area (ABCD): 16.71 in²

Examined: (KBHM)

Examined: $4.67(1.0 + 1.8)/2 = 6.54 \text{ in}^2$






**Supplemental
Data Sheet**

Page:	11 of 12
Component ID:	2B11-RPV-N2C
Utility:	Duke Energy
Site / Unit:	Brunswick / 2

Sketch: 5

Scan: C15


Scale: 50%



Exam Area (ABCD): 16.71 in²

Examined: (GHCD)

Examined: (3.0 x 0.83) = 2.49 in²





Supplemental Data Sheet

Page: 12 of 12

Component ID: 2B11-RPV-N2C

Utility: Duke Energy

Site / Unit: Brunswick / 2

ASME Code Coverage Calculation

Component Information		Scan	Description
Exam Area: 16.71 in ²		R100	60° Radial Exam
Exam Length: 113.5"		C85	60° Circ Exam / Outer 85%
		C15	50° Circ Exam / Inner 15%

See Sketch	Area Scan	Exam Examin ed Area	Length Examined	Length	Percent Coverage
3	R100	(15.30 / 16.71) x (113.5 / 113.5) x 100 =			91.56%
4	C85	(6.54 / 16.71) x (113.5 / 113.5) x 100 =			39.14%
5	C15	(2.49 / 16.71) x (113.5 / 113.5) x 100 =			14.90%
		(/ ~) x (/ ~) x 100 =			~
		(/ ~) x (/ ~) x 100 =			~
					Total Percent: 145.60%
					Code Examination Coverage (Total Percent / 2 Sound Beams): 72.8%

Reference the following for Nozzle Dimensions

Contract No.: 68-2471 / 72, Dwg. No.: 28 Rev 19

Note: 100% radial & circumferential coverage obtained in the lower 15% of exam volume.

Personnel	Name	Signature	Level	Date
Prepared By:	Simon Crothers	Simon Crothers	II	03/27/17
Reviewed By:	David K. Zimmerman	David K. Zimmerman	III	03/27/2017
Site Review:	NED FINNEY	Ned Finney	III	3-27-17



Ultrasonic Examination

Site/Unit:	BNP / 2	Procedure:	54-ISI-805-009	Outage No.:	B223R1
Summary No.:	2-B11-1088	Procedure Rev.:	009	Report No.:	VEN-17-015
Workscope:	ISI	Work Order No.:	20082951	Page:	1 of 1
Code:	ASME XI, 2001 Ed., 03 Ad.	Cat./Item:	B-D/B3.90	Location:	DW
Drawing No.:	C-02404 Sht. 001-1	Description: NOZZLE N2D TO REACTOR VESSEL WELD			
System ID:	1005				
Component ID:	2B11-RPV-N2D	Size/Length:	N/A	Thickness/Diameter:	N/A
Limitations:	Yes - Component configuration				

Comments:

Reference BNP Unit 2 Areva final report document # 180-9269913-000 for personnel certifications and equipment certifications.

Detection of flaw indications at the inner 15% t (measured from the clad to base metal interface) of nozzle-to-vessel welds when scanning parallel to the weld axis was performed utilizing 54-ISI-850-008 with SDCN 30-9269636-000.





Results: Sat Unsat Eval

Percent Of Coverage Obtained > 90%: No - 72.8%

Reviewed Previous Data: Yes

Examiner	Level	Signature	Date	Reviewer	Signature	Date
N/A			3/23/2017	Zimmerman, David Lvl III		3/27/2017
Examiner	Level	N/A	Signature	Date	Site Review	Signature
N/A					Finney, Ned Lvl III	3/27/2017
Other	Level	N/A	Signature	Date	ANII Review	Signature
N/A					Reynolds, David	3/27/2017

Enclosure 3
BSEP, Unit 2 4th ISI Interval Limited NDE Data and Coverage Plots

 AREVA		Ultrasonic Examination Summary Sheet				Summary No.:	2-B11-1088												
						Work Order:	2008295144												
						Component ID:	2B11-RPV-N2D												
						Customer:	Duke Energy		Code Category:	B-D	System:	RPV							
Site:	BNS	Unit:	2	Code Item:	B3.90	Material:	CS (Clad)												
Outage:	B223R1		Code Class:	1	Description: RPV Nozzle to Shell Weld														
ISO / Drawing(s):		C-02404-1-1			EPRI Model No.: IR-2017-680														
Procedure Number		Procedure Revision		SDCN		Procedure Title													
54-ISI-850		008		30-9269636-000		Manual Ultrasonic Examination of BWR Reactor Vessel Nozzle Inner Radius Regions and Nozzle to Shell Welds (inner 15%)													
54-ISI-805		009		N/A		PDI Generic Procedure for Ultrasonic Examination of Reactor Pressure Vessel Welds PDI-UT-6													
Calibration Sheets	Exam Data Sheets	Indication Data Sheets	Indication Plot Sheets	Coverage Worksheet	Coverage Diagram	Exam Results													
CS-01	EDS-01	N/A	N/A	Yes	Yes	Acceptable													
CS-02	EDS-02																		
CS-03																			
Summary:																			
<p>Manual ultrasonic examinations were performed on the referenced weld during B223R1.</p> <p>In accordance with UT Procedure 54-ISI-805-009, 60° Longitudinal wave examinations were performed from the vessel surface in both the radial and circumferential scan directions.</p> <p>In accordance with UT Procedure 54-ISI-850-008 and the referenced EPRI model the following examinations were performed.</p>																			
<table border="1" style="width: 100%; border-collapse: collapse;"> <thead> <tr> <th colspan="3">Recirculation Inlet Nozzle (N2D) Nozzle Modeling Parameters</th> </tr> <tr> <th>Probe</th> <th>Probe Skew</th> <th>Scan Surface</th> </tr> </thead> <tbody> <tr> <td>50° Shear</td> <td>± (51° to 76°)</td> <td>Vessel</td> </tr> <tr> <td></td> <td></td> <td></td> </tr> </tbody> </table>								Recirculation Inlet Nozzle (N2D) Nozzle Modeling Parameters			Probe	Probe Skew	Scan Surface	50° Shear	± (51° to 76°)	Vessel			
Recirculation Inlet Nozzle (N2D) Nozzle Modeling Parameters																			
Probe	Probe Skew	Scan Surface																	
50° Shear	± (51° to 76°)	Vessel																	
<p>72.8% coverage of the required examination volume was obtained. The percentage of coverage for this examination was calculated to the maximum extent possible allowed by the procedure qualification and actual component field conditions for this configuration.</p> <p>This examination was performed using the alternative examination volume defined in code case N-613-1 which reduces the area to be examined per IWB-2500-7 to the weld plus $\frac{1}{2}$" on each side.</p> <p>This examination satisfies the requirements of ASME Sec. XI 2001 Edition with 2003 Addenda for Category B-D, item number B3.90, figure number IWB 2500-7 (b) exam volume, and was performed using ASME Sec XI, Appendix VIII qualified personnel, procedures, and equipment.</p>																			
Personnel	Name		Signature		Level	Date													
Prepared By:	George Chapman				III	03/23/17													
Prepared By:	John Gatica				II	03/23/17													
AREVA Review:	David Zimmerman				III	03/23/2017													
Customer:	Ned Finney				III	3/23/2017													
ANII:	David M. Reynolds				/A	3/23/2017													

A
REVA

Supplemental Data Sheet

Page: 7 of 12

Component ID: 2B11-RPV-N2D


Utility: Duke Energy

Site / Unit: Brunswick / 2

Sketch: 1


Subject: Nozzle Overview

Scale: 20%



AREVA	Supplemental Data Sheet	Page: 8 of 12 Component ID: 2B11-RPV-N2D Utility: Duke Energy Site / Unit: Brunswick / 2								
Sketch: 2 Subject: Dimensions & Weld fit up Scale: 50%		<table border="1"><thead><tr><th>Scan</th><th>Description</th></tr></thead><tbody><tr><td>R100</td><td>60° Radial Exam</td></tr><tr><td>C85</td><td>60° Circ Exam / Outer 85%</td></tr><tr><td>C15</td><td>50° Circ Exam / Inner 15%</td></tr></tbody></table>	Scan	Description	R100	60° Radial Exam	C85	60° Circ Exam / Outer 85%	C15	50° Circ Exam / Inner 15%
Scan	Description									
R100	60° Radial Exam									
C85	60° Circ Exam / Outer 85%									
C15	50° Circ Exam / Inner 15%									
<p>Sketch: 2 Subject: Dimensions & Weld fit up Scale: 50%</p> <p>3.625" R</p> <p>N2D</p> <p>RPV</p> <p>Weld Width @ OD: 0.625"</p> <p>Weld Width @ ID: 2.0"</p> <p>RPV Thick. (Excluding Clad): 5.5"</p> <p>Weld Length: 113.5" @ CL</p> <p>Exam Area: 16.71 in²</p> <p>GHCD: Inner 15%</p> <p>Exam Area: ABCD = (EBCD) + (AFE) = (3.0 x 5.5) + (1.4 x 0.3)/2 = 16.71 in²</p>										
<p>Note: Exam area extends to $\frac{1}{2}$" beyond weld per code case N-613-1</p> <p>0 1" 2" 3"</p> <p>This scale is 100% in case of copier distortion</p>										

Enclosure 3
BSEP, Unit 2 4th ISI Interval Limited NDE Data and Coverage Plots






**Supplemental
Data Sheet**

Page:	10 of 12
Component ID:	2B11-RPV-N2D
Utility:	Duke Energy
Site / Unit:	Brunswick / 2

Sketch: 4

Scan: C85


Scale: 50%



Exam Area (ABCD): 16.71 in²

Examined: (KBHM)

Examined: $4.67(1.0 + 1.8)/2 = 6.54 \text{ in}^2$




Enclosure 3
BSEP, Unit 2 4th ISI Interval Limited NDE Data and Coverage Plots



**Supplemental
Data Sheet**

Page:	11 of 12
Component ID:	2B11-RPV-N2D
Utility:	Duke Energy
Site / Unit:	Brunswick / 2

Sketch: 5
Scan: C15
Scale: 50%



Exam Area (ABCD): 16.71 in²
Examined: (GHCD)
Examined: (3.0 x 0.83) = 2.49 in²

0 1" 2" 3"
This scale is 100% in case of copier distortion



Supplemental
Sheet

Data

Page: 12 of 12

Component ID: 2B11-RPV-N2D

Utility: Duke Energy

Site / Unit: Brunswick / 2

ASME Code Coverage Calculation

Component Information		Scan	Description
Exam Area: 16.71 in ²		R100	60° Radial Exam
Exam Length: 113.5"		C85	60° Circ Exam / Outer 85%
		C15	50° Circ Exam / Inner 15%

See	Sketch	Area	Exam	Length	Exam	Percent
		Examined	Area	Examined	Length	Coverage
3	R100	(15.30 / 16.71) x (113.5 / 113.5) x 100 =				91.56%
4	C85	(6.54 / 16.71) x (113.5 / 113.5) x 100 =				39.14%
5	C15	(2.49 / 16.71) x (113.5 / 113.5) x 100 =				14.90%
		(/ ~) x (/ ~) x 100 =				~
		(/ ~) x (/ ~) x 100 =				~
					Total Percent:	145.60%
					Code Examination Coverage (Total Percent / 2 Sound Beams):	72.8%

Reference the following for Nozzle Dimensions

Contract No.: 68-2471 / 72, Dwg. No.: 28 Rev 19

Note: 100% radial & circumferential coverage obtained in the lower 15% of exam volume.

Personnel	Name	Signature	Level	Date
Prepared By:	Simon Crothers	Simon Crothers	II	03/27/17
Reviewed By:	David K. Zimmerman	David K. Zimmerman	III	03/27/2017
Site Review:	NED FINNEY	Ned Finney	III	3/27/2017



Ultrasonic Examination

Site/Unit:	BNP / 2	Procedure:	54-ISI-805-009	Outage No.:	B223R1
Summary No.:	2-B11-1120	Procedure Rev.:	009	Report No.:	VEN-17-018
Workscope:	ISI	Work Order No.:	20082951	Page:	1 of 1
Code:	ASME XI, 2001 Ed., 03 Ad.	Cat./Item:	B-D/B3.90	Location:	DW
Drawing No.:	C-02404 Sht. 001-1	Description: NOZZLE N5B TO REACTOR VESSEL WELD			
System ID:	1005				
Component ID:	2B11-RPV-N5B	Size/Length:	N/A	Thickness/Diameter:	N/A
Limitations:	Yes - Component configuration				

Comments:

Reference BNP Unit 2 Areva final report document # 180-9269913-000 for personnel certifications and equipment certifications.





Detection of flaw indications at the inner 15% t (measured from the clad to base metal interface) of nozzle-to-vessel welds when scanning parallel to the weld axis was performed utilizing 54-ISI-850-008 with SDCN 30-9269636-000.

Results: Sat Unsat Eval

Percent Of Coverage Obtained > 90%: No - 72.8%

Reviewed Previous Data: Yes

Examiner	Level	Signature	Date	Reviewer	Signature	Date
N/A			3/22/2017	Zimmerman, David Lvl III		3/27/2017
Examiner	Level	N/A	Signature	Date	Site Review	Signature
N/A					Finney, Ned Lvl III	3/27/2017
Other	Level	N/A	Signature	Date	ANII Review	Signature
N/A					Reynolds, David	3/28/2017

 AREVA		<h3>Ultrasonic Examination Summary Sheet</h3>				Summary No.: 2-B11-1120													
						Work Order: 2008295154													
						Component ID: 2B11-RPV-N5B													
Customer:	Duke Energy		Code Category:	B-D	System:	RPV													
Site:	BNS	Unit:	2	Code Item:	B3.90	Material:	CS (Clad)												
Outage:	B223R1		Code Class:	1	Description:	RPV Nozzle to Shell Weld													
ISO / Drawing(s):	C-02404 Sht. 001-1				EPRI Model No.:	IR-2017-680													
Procedure Number	Procedure Revision		SDCN		Procedure Title														
54-ISI-850	008		30-9269636-000		Manual Ultrasonic Examination of BWR Reactor Vessel Nozzle Inner Radius Regions and Nozzle to Shell Welds (inner 15%)														
54-ISI-805	009		N/A		PDI Generic Procedure for Ultrasonic Examination of Reactor Pressure Vessel Welds PDI-UT-6														
Calibration Sheets	Exam Data Sheets	Indication Data Sheets	Indication Plot Sheets	Coverage Worksheet	Coverage Diagram	Exam Results													
CS-01	EDS-01	N/A	N/A	Yes	Yes	Acceptable													
CS-02	EDS-02																		
CS-03																			
Summary:																			
Manual ultrasonic examinations were performed on the referenced weld during B223R1.																			
In accordance with UT Procedure 54-ISI-805-009, 60° Longitudinal wave examinations were performed from the vessel surface in both the radial and circumferential scan directions.																			
In accordance with UT Procedure 54-ISI-850-008 and the referenced EPRI model the following examinations were performed.																			
<table border="1" style="width: 100%; border-collapse: collapse;"> <thead> <tr> <th colspan="3">Core Spray Nozzle (N5B) Nozzle Modeling Parameters</th> </tr> <tr> <th>Probe</th> <th>Probe Skew</th> <th>Scan Surface</th> </tr> </thead> <tbody> <tr> <td>50° Shear</td> <td>± (51° to 77°)</td> <td>Vessel</td> </tr> <tr> <td></td> <td></td> <td></td> </tr> </tbody> </table>								Core Spray Nozzle (N5B) Nozzle Modeling Parameters			Probe	Probe Skew	Scan Surface	50° Shear	± (51° to 77°)	Vessel			
Core Spray Nozzle (N5B) Nozzle Modeling Parameters																			
Probe	Probe Skew	Scan Surface																	
50° Shear	± (51° to 77°)	Vessel																	
72.8% coverage of the required examination volume was obtained. The percentage of coverage for this examination was calculated to the maximum extent possible allowed by the procedure qualification and actual component field conditions for this configuration.																			
This examination was performed using the alternative examination volume defined in code case N-613-1 which reduces the area to be examined per IWB-2500-7 to the weld plus ½" on each side.																			
This examination satisfies the requirements of ASME Sec. XI 2001 Edition with 2003 Addenda for Category B-D, item number B3.90, figure number IWB 2500-7 (b) exam volume, and was performed using ASME Sec XI, Appendix VIII qualified personnel, procedures, and equipment.																			
Personnel	Name		Signature		Level	Date													
Prepared By:	Chris Van Ruler				II	03/22/2017													
AREVA Review:	David Zimmerman				III	03/27/2017													
Customer:	Ned Finney				III	3/27/2017													
ANII:	David M. Reynolds				N/A	5/28/2017													

A
REVA


Supplemental Data Sheet


Page:	7 of 12
Component ID:	2B11-RPV-N5B
Utility:	Duke Energy
Site / Unit:	Brunswick / 2

Sketch: 1

Subject: Nozzle Overview

Scale: 20%



	Supplemental Data Sheet	Page: 8 of 12 Component ID: 2B11-RPV-N5B Utility: Duke Energy Site / Unit: Brunswick / 2												
Sketch: 2 Subject: Dimensions & Weld fit up Scale: 50%		<table border="1" style="margin-left: auto; margin-right: 0;"> <thead> <tr> <th style="text-align: center;">Scan</th> <th style="text-align: center;">Description</th> </tr> </thead> <tbody> <tr> <td style="text-align: center;">R100:</td> <td>60° Radial Exam</td> </tr> <tr> <td style="text-align: center;">C85:</td> <td>60° Circ Exam / Outer 85%</td> </tr> <tr> <td style="text-align: center;">C15:</td> <td>50° Circ Exam / Inner 15%</td> </tr> </tbody> </table>	Scan	Description	R100:	60° Radial Exam	C85:	60° Circ Exam / Outer 85%	C15:	50° Circ Exam / Inner 15%				
Scan	Description													
R100:	60° Radial Exam													
C85:	60° Circ Exam / Outer 85%													
C15:	50° Circ Exam / Inner 15%													
 <p>N5B</p> <p>Dimensions (inches): EB: 3.0" BC: 5.5" EF: 1.4" AE: 0.3" BH: 4.67" HC: 0.83" </p> <p>RPV</p> <table border="1" style="margin-left: auto; margin-right: 0;"> <tbody> <tr> <td>Weld Width @ OD:</td> <td>0.625"</td> </tr> <tr> <td>Weld Width @ ID:</td> <td>2.0"</td> </tr> <tr> <td>RPV Thick. (Excluding Clad):</td> <td>5.5"</td> </tr> <tr> <td>Weld Length:</td> <td>113.5" @ CL</td> </tr> <tr> <td>Exam Area:</td> <td>16.71 in²</td> </tr> <tr> <td>GHCD:</td> <td>Inner 15%</td> </tr> </tbody> </table> <p>Exam Area: ABCD $= (EBCD) + (AFE)$ $= (3.0 \times 5.5) + (1.4 \times 0.3)/2 = 16.71 \text{ in}^2$</p>			Weld Width @ OD:	0.625"	Weld Width @ ID:	2.0"	RPV Thick. (Excluding Clad):	5.5"	Weld Length:	113.5" @ CL	Exam Area:	16.71 in ²	GHCD:	Inner 15%
Weld Width @ OD:	0.625"													
Weld Width @ ID:	2.0"													
RPV Thick. (Excluding Clad):	5.5"													
Weld Length:	113.5" @ CL													
Exam Area:	16.71 in ²													
GHCD:	Inner 15%													
<p>Note: Exam area extends to $\frac{1}{2}$" beyond weld per code case N-613-1</p> <div style="text-align: center;">  <p>This scale is 100% in case of copier distortion</p> </div>														


Enclosure 3
BSEP, Unit 2 4th ISI Interval Limited NDE Data and Coverage Plots




**Supplemental
Data Sheet**

Page:	10	of	12
Component ID:	2B11-RPV-N5B		
Utility:	Duke Energy		
Site / Unit:	Brunswick / 2		

Sketch: 4
Scan: C85
Scale: 50%



Exam Area (ABCD): 16.71 in²
Examined: (KBHM)
Examined: $4.67(1.0 + 1.8)/2 = 6.54 \text{ in}^2$



Enclosure 3
BSEP, Unit 2 4th ISI Interval Limited NDE Data and Coverage Plots

AREVA	Supplemental Data Sheet	Page: 9 of 12
		Component ID: 2B11-RPV-N5B
		Utility: Duke Energy
		Site / Unit: Brunswick / 2

Sketch: 3
Scan: R100
Scale: 50%

N5B

RPV

Exam Area (ABCD): 16.71 in²
Examined: (KBLJ) + (JLCD)
Examined: $1.2(1.0 + 3.0)/2 + (3.0 \times 4.3) = 15.30$ in²

0 1" 2" 3"

This scale is 100% in case of copier distortion


Enclosure 3
BSEP, Unit 2 4th ISI Interval Limited NDE Data and Coverage Plots

A
AREVA

**Supplemental
Data Sheet**

Page:	11 of 12
Component ID:	2B11-RPV-N5B
Utility:	Duke Energy
Site / Unit:	Brunswick / 2

Sketch: 5
Scan: C15
Scale: 50%



Exam Area (ABCD): 16.71 in²
Examined: (GHCD)
Examined: (3.0 x 0.83) = 2.49 in²

0 1" 2" 3"
This scale is 100% in case of copier distortion



Supplemental Data Sheet

Page: 12 of 12

Component ID: 2B11-RPV-N5B

Utility: Duke Energy

Site / Unit: Brunswick / 2

ASME Code Coverage Calculation

Component Information		Scan	Description
Exam Area: 16.71 in ²		R100	60° Radial Exam
Exam Length: 113.5"		C85	60° Circ Exam / Outer 85%
		C15	50° Circ Exam / Inner 15%

See	Area	Exam	Length	Exam	Percent	
Sketch	Scan	Examined	Area	Examined	Length	Coverage
3	R100	(15.30 / 16.71) x (113.5 / 113.5) x 100 =				91.56%
4	C85	(6.54 / 16.71) x (113.5 / 113.5) x 100 =				39.14%
5	C15	(2.49 / 16.71) x (113.5 / 113.5) x 100 =				14.90%
		(/ ~) x (/ ~) x 100 =				-
		(/ ~) x (/ ~) x 100 =				-
						Total Percent:
						145.60%
Code Examination Coverage (Total Percent / 2 Sound Beams):						72.8%

Reference the following for Nozzle Dimensions

Contract No.: 68-2471 / 72, Dwg. No.: 32 Rev 16

Note: 100% radial & circumferential coverage obtained in the lower 15% of exam volume.

Personnel	Name	Signature	Level	Date
Prepared By:	Simon Crothers	Simon Crothers	II	03/27/17
Reviewed By:	David K. Zimmerman	David K. Zimmerman	III	03/27/2017
Site Review:	NED FINNEY	Ned Finney	III	3/27/2017



Ultrasonic Examination

Site/Unit: BNP / 2 Procedure: 54-ISI-805-009 Outage No.: B223R1
Summary No.: 2-B11-1137 Procedure Rev.: 009 Report No.: VEN-17-016
Workscope: ISI Work Order No.: 20082951 Page: 1 of 1
Code: ASME XI, 2001 Ed., 03 Ad. Cat./Item: B-D/B3.90 Location: DW
Drawing No.: C-02404 Sht. 001-1 Description: NOZZLE N8B TO REACTOR VESSEL WELD
System ID: 1005
Component ID: 2B11-RPV-N8B Size/Length: 218.0" Thickness/Diameter: 5.56"
Limitations: Yes - Component configuration

Comments:

Reference BNP Unit 2 Areva final report document # 180-9269913-000 for personnel certifications and equipment certifications.





Detection of flaw indications at the inner 15% t (measured from the clad to base metal interface) of nozzle-to-vessel welds when scanning parallel to the weld axis was performed utilizing 54-ISI-850-008 with SDCN 30-9269636-000.

Results: Sat Unsat Eval

Percent Of Coverage Obtained > 90%: No - 72.8%

Reviewed Previous Data: Yes

Examiner N/A	Level N/A	Signature	Date 3/25/2017	Reviewer Zimmerman, David Lvl III	Signature	Date 3/28/2017
Examiner N/A	Level N/A	Signature	Date	Site Review Finney, Ned Lvl III	Signature	Date 3/28/2017
Other N/A	Level N/A	Signature	Date	ANII Review Reynolds, David	Signature	Date 3/29/2017


 AREVA	<h3 style="margin: 0;">Ultrasonic Examination Summary Sheet</h3>			Summary No.: 2-B11-1137											
				Work Order: 2008295164											
				Component ID: 2B11-RPV-N8B											
Customer:	Duke Energy	Code Category:	B-D	System:	RPV										
Site:	BNS	Unit: 1	Code Item:	B3.90	Material:	CS (Clad)									
Outage:	B223R1		Code Class:	1	Description:	RPV Nozzle to Shell Weld									
ISO / Drawing(s):	C02404 Sht. 001-1			EPRI Model No.:	IR-2017-680										
Procedure Number	Procedure Revision	SDCN		Procedure Title											
54-ISI-850	008	30-9269636-000		Manual Ultrasonic Examination of BWR Reactor Vessel Nozzle Inner Radius Regions and Nozzle to Shell Welds (inner 15%)											
54-ISI-805	009	N/A		PDI Generic Procedure for Ultrasonic Examination of Reactor Pressure Vessel Welds PDI-UT-6											
Calibration Sheets	Exam Data Sheets	Indication Data Sheets	Indication Plot Sheets	Coverage Worksheet	Coverage Diagram	Exam Results									
CS-01	EDS-01	N/A	N/A	Yes	Yes	Acceptable									
CS-02	EDS-02														
CS-03															
Summary:															
<p>Manual ultrasonic examinations were performed on the referenced weld during B223R1.</p> <p>In accordance with UT Procedure 54-ISI-805-009, 60° Longitudinal wave examinations were performed from the vessel surface in both the radial and circumferential scan directions.</p> <p>In accordance with UT Procedure 54-ISI-850-008 and the referenced EPRI model the following examinations were performed.</p>															
<table border="1" style="width: 100%; border-collapse: collapse;"> <thead> <tr> <th colspan="3">Jet Pump Instrumentation (N8) Nozzle Modeling Parameters</th> </tr> <tr> <th>Probe</th> <th>Probe Skew</th> <th>Scan Surface</th> </tr> </thead> <tbody> <tr> <td>50° Shear</td> <td>± (43° to 65°)</td> <td>Vessel</td> </tr> </tbody> </table>							Jet Pump Instrumentation (N8) Nozzle Modeling Parameters			Probe	Probe Skew	Scan Surface	50° Shear	± (43° to 65°)	Vessel
Jet Pump Instrumentation (N8) Nozzle Modeling Parameters															
Probe	Probe Skew	Scan Surface													
50° Shear	± (43° to 65°)	Vessel													
<p>72.8% coverage of the required examination volume was obtained. The percentage of coverage for this examination was calculated to the maximum extent possible allowed by the procedure qualification and actual component field conditions for this configuration.</p> <p>This examination was performed using the alternative examination volume defined in code case N-613-1 which reduces the area to be examined per IWB-2500-7 to the weld plus ½" on each side.</p> <p>This examination satisfies the requirements of ASME Sec. XI 2001 Edition with 2003 Addenda for Category B-D, item number B3.100, figure number IWB 2500-7 (b) exam volume, and was performed using ASME Sec XI, Appendix VIII qualified personnel, procedures, and equipment.</p>															
Personnel	Name	Signature		Level	Date										
Prepared By:	Edward P. Mazyck			III	03/25/2017										
AREVA Review:	David Zimmerman			III	03/28/2017										
Customer:	Ned Finney			III	3/28/17										
ANII:	David M. Reynolds			N/A	3/29/2017										

AREVA	Supplemental Data Sheet	Page: 7 of 12
		Component ID: 2B11-RPV-N8B
		Utility: Duke Energy
		Site / Unit: Brunswick / 2

Sketch: 1


Subject: Nozzle Overview

Scale: 20%




Weld Length @ Centerline: $(18.343 \times \pi) = 57.6"$

0 1" 2" 3"
This scale is 100% in case of copier distortion


 Supplemental Data Sheet	Page: 8 of 12 Component ID: 2B11-RPV-N8B Utility: Duke Energy Site / Unit: Brunswick / 2																				
Sketch: 2 Subject: Dimensions & Weld fit up Scale: 50%	<table border="1"> <thead> <tr> <th>Scan</th> <th>Description</th> </tr> </thead> <tbody> <tr> <td>R100:</td> <td>60° Radial Exam</td> </tr> <tr> <td>C85:</td> <td>60° Circ Exam / Outer 85%</td> </tr> <tr> <td>C15:</td> <td>50° Circ Exam / Inner 15%</td> </tr> </tbody> </table>	Scan	Description	R100:	60° Radial Exam	C85:	60° Circ Exam / Outer 85%	C15:	50° Circ Exam / Inner 15%												
Scan	Description																				
R100:	60° Radial Exam																				
C85:	60° Circ Exam / Outer 85%																				
C15:	50° Circ Exam / Inner 15%																				
 <table border="1" style="margin-left: auto; margin-right: auto;"> <tr> <td style="text-align: left;">N8B</td> <td style="text-align: right;">RPV</td> </tr> <tr> <td>EB: 3.0"</td> <td>Weld Width @ OD: 0.625"</td> </tr> <tr> <td>BC: 5.5"</td> <td>Weld Width @ ID: 2.0"</td> </tr> <tr> <td>EF: 1.4"</td> <td>RPV Thick. (Excluding Clad): 5.5"</td> </tr> <tr> <td>AE: 0.3"</td> <td>Weld Length: 57.6" @ CL</td> </tr> <tr> <td>BH: 4.67"</td> <td>Exam Area: 16.71 in²</td> </tr> <tr> <td>HC: 0.83"</td> <td>GHCD: Inner 15%</td> </tr> <tr> <td colspan="2">Exam Area: ABCD</td> </tr> <tr> <td colspan="2">= (EBCD) + (AFE)</td> </tr> <tr> <td colspan="2">= (3.0 x 5.5) + (1.4 x 0.3)/2 = 16.71 in²</td> </tr> </table>		N8B	RPV	EB: 3.0"	Weld Width @ OD: 0.625"	BC: 5.5"	Weld Width @ ID: 2.0"	EF: 1.4"	RPV Thick. (Excluding Clad): 5.5"	AE: 0.3"	Weld Length: 57.6" @ CL	BH: 4.67"	Exam Area: 16.71 in ²	HC: 0.83"	GHCD: Inner 15%	Exam Area: ABCD		= (EBCD) + (AFE)		= (3.0 x 5.5) + (1.4 x 0.3)/2 = 16.71 in ²	
N8B	RPV																				
EB: 3.0"	Weld Width @ OD: 0.625"																				
BC: 5.5"	Weld Width @ ID: 2.0"																				
EF: 1.4"	RPV Thick. (Excluding Clad): 5.5"																				
AE: 0.3"	Weld Length: 57.6" @ CL																				
BH: 4.67"	Exam Area: 16.71 in ²																				
HC: 0.83"	GHCD: Inner 15%																				
Exam Area: ABCD																					
= (EBCD) + (AFE)																					
= (3.0 x 5.5) + (1.4 x 0.3)/2 = 16.71 in ²																					
<p>Note: Exam area extends to $\frac{1}{2}$" beyond weld per code case N-613-1</p> <div style="text-align: center;">  <p>This scale is 100% in case of copier distortion</p> </div>																					

AREVA	Supplemental Data Sheet	Page: 9 of 12
		Component ID: 2B11-RPV-N8B
		Utility: Duke Energy
		Site / Unit: Brunswick / 2

Sketch: 3
Scan: R100
Scale: 50%



Exam Area (ABCD): 16.71 in²
Examined: (KBLJ) + (JLCD)
Examined: $1.2(1.0 + 3.0)/2 + (3.0 \times 4.3) = 15.30$ in²






**Supplemental
Data Sheet**

Page:	10 of 12
Component ID:	2B11-RPV-N8B
Utility:	Duke Energy
Site / Unit:	Brunswick / 2


Sketch: 4

Scan: C85

Scale: 50%



Exam Area (ABCD): 16.71 in²
Examined: (KBHM)
Examined: $4.67(1.0 + 1.8)/2 = 6.54$ in²




A
AREVA

**Supplemental
Data Sheet**

Page:	11	of	12
Component ID:	2B11-RPV-N8B		
Utility:	Duke Energy		
Site / Unit:	Brunswick / 2		

Sketch: 5
Scan: C15
Scale: 50%



Exam Area (ABCD): 16.71 in²
Examined: (GHCD)
Examined: (3.0 x 0.83) = 2.49 in²

0 1" 2" 3"
This scale is 100% in case of copier distortion



Supplemental Data
Sheet

Page: 12 of 12

Component ID: 2B11-RPV-N8B

Utility: Duke Energy

Site / Unit: Brunswick / 2

ASME Code Coverage Calculation

Component Information		Scan	Description
	Exam Area: 16.71 in ²	R100	60° Radial Exam
	Exam Length: 57.6"	C85	60° Circ Exam / Outer 85%
		C15	50° Circ Exam / Inner 15%

See		Area	Exam	Length	Exam	Percent
Sketch	Scan	Examined	Area	Examined	Length	Coverage
3	R100	(15.30 / 16.71) x (57.6 / 57.6) x 100 =				91.56%
4	C85	(6.54 / 16.71) x (57.6 / 57.6) x 100 =				39.14%
5	C15	(2.49 / 16.71) x (57.6 / 57.6) x 100 =				14.90%
		(/ ~) x (/ ~) x 100 =				~
		(/ ~) x (/ ~) x 100 =				~
				Total Percent:		145.60%
				Code Examination Coverage (Total Percent / 2 Sound Beams):		72.8%

Reference the following for Nozzle Dimensions

Contract No.: 68-2471 / 72, Dwg. No.: 36 Rev 1

Note: 100% radial & circumferential coverage obtained in the lower 15% of exam volume.

Personnel	Name	Signature	Level	Date
Prepared By:	Simon Crothers	Simon Crothers	II	03/27/17
Reviewed By:	David K. Zimmerman	David K. Zimmerman	III	03/27/2017
Site Review:	NED FINNEY	Ned Finney	III	3/28/17



Ultrasonic Examination





Site/Unit:	BNP / 2	Procedure:	54-ISI-805-009	Outage No.:	B223R1
Summary No.:	2-B11-1140	Procedure Rev.:	009	Report No.:	VEN-17-017
Workscope:	ISI	Work Order No.:	20013237	Page:	1 of 1
Code:	ASME XI, 2001 Ed., 03 Ad.	Cat./Item:	B-D/B3.90	Location:	DRYWELL
Drawing No.:	C-02404 Sht. 001-1	Description: NOZZLE N9 TO REACTOR VESSEL WELD			
System ID:	1005				
Component ID:	2B11-RPV-N9	Size/Length:	3.0"	Thickness/Diameter:	5.56"
Limitations:	Yes - Component configuration				

Comments:

Reference BNP Unit 2 Areva final report document # 180-9269913-000 for personnel certifications and equipment certifications.

Detection of flaw indications at the inner 15% t (measured from the clad to base metal interface) of nozzle-to-vessel welds when scanning parallel to the weld axis was performed utilizing 54-ISI-850-008 with SDCN 30-9269636-000.

Results:	Sat <input checked="" type="checkbox"/>	Unsat <input type="checkbox"/>	Eval <input type="checkbox"/>			
Percent Of Coverage Obtained > 90%:	No - 72.8%		Reviewed Previous Data:	Yes		
Examiner	Level	Signature	Date	Reviewer	Signature	Date
N/A			3/21/2017	Zimmerman, David Lvl III		3/28/2017
Examiner	Level	N/A	Signature	Date	Site Review	Signature
N/A					Finney, Ned Lvl III	3/28/2017
Other	Level	N/A	Signature	Date	ANII Review	Signature
N/A					Reynolds, David	3/28/2017

 AREVA	<h2 style="margin: 0;">Ultrasonic Examination Summary Sheet</h2>				Summary No.: 2-B11-1140										
					Work Order: 2001323734										
					Component ID: 2B11-RPV-N9										
Customer:	Duke Energy		Code Category:	B-D	System:	RPV									
Site:	BNS	Unit: 2	Code Item:	B3.90	Material:	CS (Clad)									
Outage:	B223R1		Code Class:	1	Description:	RPV Nozzle to Shell Weld									
ISO / Drawing(s):	C-02404-1-1			EPRI Model No.:	IR-2017-680										
Procedure Number		Procedure Revision	SDCN		Procedure Title										
54-ISI-850		008	30-9269636-000		Manual Ultrasonic Examination of BWR Reactor Vessel Nozzle Inner Radius Regions and Nozzle to Shell Welds (inner 15%)										
54-ISI-805		009	N/A		PDI Generic Procedure for Ultrasonic Examination of Reactor Pressure Vessel Welds PDI-UT-6										
Calibration Sheets	Exam Data Sheets	Indication Data Sheets	Indication Plot Sheets	Coverage Worksheet	Coverage Diagram	Exam Results									
CS-01	EDS-01	N/A	N/A	Yes	Yes	Acceptable									
CS-02	EDS-02														
CS-03															
Summary:															
Manual ultrasonic examinations were performed on the referenced weld during B223R1.															
In accordance with UT Procedure 54-ISI-805-009, 60° Longitudinal wave examinations were performed from the vessel surface in both the radial and circumferential scan directions.															
In accordance with UT Procedure 54-ISI-850-008 and the referenced EPRI model the following examinations were performed.															
<table border="1" style="width: 100%; border-collapse: collapse;"> <thead> <tr> <th colspan="3" style="text-align: left;">CRD-HYD System Return (N9) Nozzle Modeling Parameters</th> </tr> <tr> <th>Probe</th> <th>Probe Skew</th> <th>Scan Surface</th> </tr> </thead> <tbody> <tr> <td>50° Shear</td> <td>± (44° to 65°)</td> <td>Vessel</td> </tr> </tbody> </table>							CRD-HYD System Return (N9) Nozzle Modeling Parameters			Probe	Probe Skew	Scan Surface	50° Shear	± (44° to 65°)	Vessel
CRD-HYD System Return (N9) Nozzle Modeling Parameters															
Probe	Probe Skew	Scan Surface													
50° Shear	± (44° to 65°)	Vessel													
72.8% coverage of the required examination volume was obtained. The percentage of coverage for this examination was calculated to the maximum extent possible allowed by the procedure qualification and actual component field conditions for this configuration.															
This examination was performed using the alternative examination volume defined in code case N-613-1 which reduces the area to be examined per IWB-2500-7 to the weld plus ½" on each side.															
This examination satisfies the requirements of ASME Sec. XI 2001 Edition with 2003 Addenda for Category B-D, item number B3.90, figure number IWB 2500-7 (b) exam volume, and was performed using ASME Sec XI, Appendix VIII qualified personnel, procedures, and equipment.															
Personnel	Name	Signature		Level	Date										
Prepared By:	Edward P. Mazick			III	03/21/2017										
Prepared By:	Wade Holloway			III	03/21/2017										
AREVA Review:	David Zimmerman			III	03/28/2017										
Customer:	Ned Finney			III	3/28/2017										
ANII:	David M. Reynolds			N/A	3/28/2017										




**Supplemental
Data Sheet**

Page:	7 of 12
Component ID:	2B11-RPV-N9
Utility:	Duke Energy
Site / Unit:	Brunswick / 2

Sketch: 1

Subject: Nozzle Overview

Scale: 20%



Weld Length @ Centerline: $(18.375 \times \pi) = 57.7"$

0 1" 2" 3"
This scale is 100% in case of copier distortion



Supplemental Data Sheet


Page:	8 of 12
Component ID:	2B11-RPV-N9
Utility:	Duke Energy
Site / Unit:	Brunswick / 2

Sketch: 2


Subject: Dimensions & Weld fit up

Scale: 50%

Scan	Description
R100:	60° Radial Exam
C85:	60° Circ Exam / Outer 85%
C15:	50° Circ Exam / Inner 15%



Note: Exam area extends to $\frac{1}{2}$ " beyond weld per code case N-613-1




Enclosure 3
BSEP, Unit 2 4th ISI Interval Limited NDE Data and Coverage Plots




**Supplemental
Data Sheet**

Page:	9 of 12
Component ID:	2B11-RPV-N9
Utility:	Duke Energy
Site / Unit:	Brunswick / 2

Sketch: 3
Scan: R100
Scale: 50%



Exam Area (ABCD): 16.71 in²
Examined: (KBLJ) + (JLCD)
Examined: $1.2(1.0 + 3.0)/2 + (3.0 \times 4.3) = 15.30$ in²






Supplemental Data Sheet

Page:	10 of 12
Component ID:	2B11-RPV-N9
Utility:	Duke Energy
Site / Unit:	Brunswick / 2

Sketch: 4

Scan: C85


Scale: 50%



Exam Area (ABCD): 16.71 in²

Examined: (KBHM)

Examined: $4.67(1.0 + 1.8)/2 = 6.54$ in²




Enclosure 3
BSEP, Unit 2 4th ISI Interval Limited NDE Data and Coverage Plots

A
AREVA

Supplemental
Data Sheet

Page:	11	of	12
Component ID:	2B11-RPV-N9		
Utility:	Duke Energy		
Site / Unit:	Brunswick / 2		

Sketch: 5
Scan: C15
Scale: 50%



Exam Area (ABCD): 16.71 in²
Examined: (GHCD)
Examined: (3.0 x 0.83) = 2.49 in²

0 1" 2" 3"
This scale is 100% in case of copier distortion



Supplemental Data Sheet

Page: 12 of 12

Component ID: 2B11-RPV-N9

Utility: Duke Energy

Site / Unit: Brunswick / 2

ASME Code Coverage Calculation

Component Information		Scan	Description
	Exam Area: 16.71 in ²	R100	60° Radial Exam
	Exam Length: 57.7"	C85	60° Circ Exam / Outer 85%
		C15	50° Circ Exam / Inner 15%

See Sketch	Area Examined	Area Examined	Length Examined	Length	Percent Coverage
3	R100 (15.30 / 16.71) x (57.7 / 57.7) x 100 =				91.56%
4	C85 (6.54 / 16.71) x (57.7 / 57.7) x 100 =				39.14%
5	C15 (2.49 / 16.71) x (57.7 / 57.7) x 100 =				14.90%
	(/ ~) x (/ ~) x 100 =				~
	(/ ~) x (/ ~) x 100 =				~
					Total Percent: 145.60%
Code Examination Coverage (Total Percent / 2 Sound Beams):					72.8%

Reference the following for Nozzle Dimensions

Contract No.: 68-2471 / 72, Dwg. No.: 37 Rev 10

Note: 100% radial & circumferential coverage obtained in the lower 15% of exam volume.

Personnel	Name	Signature	Level	Date
Prepared By:	Simon Crothers	<i>Simon Crothers</i>	II	03/27/17
Reviewed By:	David K. Zimmerman	<i>David K. Zimmerman</i>	III	03/27/17
Site Review:	NED FINNEY	<i>Ned Finney</i>	III	3/28/17



Enclosure 3
BSEP, Unit 2 4th ISI Interval Limited NDE Data and Coverage Plots

UT Calibration/Examination

Site/Unit:	BNP	/	2	Procedure:	NDEP-0448	Outage No.:	B223R1																												
Summary No.:	2-E11-3756			Procedure Rev.:	4	Report No.:	UT-18-026																												
Workscope:	ISI			Work Order No.:	20200058	Page:	1 of 7																												
Code:	2001 EDITION/2003 ADDENDA			Cal Item:	C-B/C2.21	Location:																													
Drawing No.:	C-02404 Sht. 075-1			Description:	RHR HTX 2A INLET NOZZLE TO HEAD																														
System ID:	2045			Size/Length:	1.2" / 61.5"	Thickness/Diameter:	CS/0.875"/28.0"																												
Component ID:	2E11HX-2A-SWN3			Start Time:	1450	Finish Time:	1600																												
Limitations:	Yes - Single Sided Exam Due to Nozzle configuration																																		
Instrument Settings Serial No.: 15AD24PE Manufacturer: GE Model: USN 60 SW Delay: 0.5875 MII Cal/Vel: 0.2327 Damping: 500 Ohms PRF: Auto High Frequency: 5.0 MHz Voltage: 450				Search Unit Serial No.: 0100NH Manufacturer: KBA Size: 0.250" Freq.: 5.0 MHz Exam Angle: 0 Measured Angle: N/A Exit Point: N/A Config: Single Shape: Round Wedge Style: Integral Search Unit Cable Type: RG-174 Length: 8' No. Conn.: 0																															
				Cal. Checks Initial Cal. 1010 4/19/2018 Inter. Cal. 1450 4/19/2018 Inter. Cal. N/A Inter. Cal. 1504 4/19/2018 Final Cal. 1700 4/19/2018																															
				Axial Oriented Search Unit <table border="1" style="width: 100%; border-collapse: collapse;"> <thead> <tr> <th>Calibration Reflector</th> <th>Signal Amplitude %</th> <th>Sweep Division</th> <th>Sound Path</th> </tr> </thead> <tbody> <tr> <td>1/2T Hole</td> <td>61</td> <td>4.4</td> <td>0.861</td> </tr> <tr> <td></td> <td></td> <td></td> <td></td> </tr> </tbody> </table>				Calibration Reflector	Signal Amplitude %	Sweep Division	Sound Path	1/2T Hole	61	4.4	0.861																				
Calibration Reflector	Signal Amplitude %	Sweep Division	Sound Path																																
1/2T Hole	61	4.4	0.861																																
				Circumferential Oriented Search Unit <table border="1" style="width: 100%; border-collapse: collapse;"> <thead> <tr> <th>Calibration Reflector</th> <th>Signal Amplitude %</th> <th>Sweep Division</th> <th>Sound Path</th> </tr> </thead> <tbody> <tr> <td>N/A</td> <td></td> <td></td> <td></td> </tr> <tr> <td></td> <td></td> <td></td> <td></td> </tr> </tbody> </table>				Calibration Reflector	Signal Amplitude %	Sweep Division	Sound Path	N/A																							
Calibration Reflector	Signal Amplitude %	Sweep Division	Sound Path																																
N/A																																			
				Reference/Simulator Block <table border="1" style="width: 100%; border-collapse: collapse;"> <thead> <tr> <th>Gain dB</th> <th>Reflector</th> <th>Signal Amplitude %</th> <th>Sweep Division</th> <th>Sound Path</th> </tr> </thead> <tbody> <tr> <td>20.5</td> <td>FSDH</td> <td>78</td> <td>3.6</td> <td>0.723</td> </tr> <tr> <td></td> <td></td> <td></td> <td></td> <td></td> </tr> <tr> <td></td> <td></td> <td></td> <td></td> <td></td> </tr> <tr> <td></td> <td></td> <td></td> <td></td> <td></td> </tr> </tbody> </table>				Gain dB	Reflector	Signal Amplitude %	Sweep Division	Sound Path	20.5	FSDH	78	3.6	0.723																		
Gain dB	Reflector	Signal Amplitude %	Sweep Division	Sound Path																															
20.5	FSDH	78	3.6	0.723																															
Ax. Gain (dB): 12.6 Circ. Gain (dB): N/A 1 Screen Div. = .2 In. of Sound Path				Couplant Cal. Batch: 15D016 Type: ULTRAGEL II Mfg.: MAGNAFLUX Exam Batch: 18B022 Type: Ultrigel II Mfg.: Magnaflux																															
Calibration Block Cal. Block No.: 071B Thickness: .873" Cal. Blk. Temp.: 72 Comp. Temp.: 83				Scan Coverage Upstream <input type="checkbox"/> Downstream <input checked="" type="checkbox"/> Scan dB: 33.0 CW <input type="checkbox"/> CCW <input type="checkbox"/> Scan dB: N/A Exam Surface: O.D. Surface Condition: As Ground																															
Recordable Indication(s): Yes <input type="checkbox"/> No <input checked="" type="checkbox"/> Results: Set <input checked="" type="checkbox"/> Unset <input type="checkbox"/> Eval <input type="checkbox"/> NCR # 02200157				Reference Block Serial No.: 18-4047 Type: Rompas.																															
				Comments: Initial Section XI UT exam. Lamination Scan. No examination from Nozzle side due to configuration.																															
Percent Of Coverage Obtained > 80%: No - 50% Reviewed Previous Data: N/A																																			
Examiner	Level	II-N	Signature	Date	Reviewer	Signature	Date																												
Goldsmith, C. Tony				4/19/2018	J. H. San Polinsky L-III		4/20/18																												
Examiner	Level	N/A	Signature	Date	Site Review	Comments	Date																												
N/A					Chris Welsch and Chris Welsch, et al., made this document available electronically on 2018-04-20 14:48:04Z	Signature																													
Other	Level	N/A	Signature	Date	ANII Review	Signature	Date																												
N/A					David M. Reynolds David M. Reynolds		5-9-2018																												



UT Calibration/Examination

Site/Unit:	BMP	/	2	Procedure:	NDEP-0448	Outage No.:	B223R1																		
Summary No.:	2-E11-3768		Procedure Rev.:	4	Report No.:	UT-18-028																			
Workscope:	ISI		Work Order No.:	20200656	Page:	2 of 7																			
Code:	2001 EDITION/2003 ADDENDA		Cat./Item:	C-B/C2.21	Location:																				
Drawing No.:	C-02604 Shl. 075-1		Description:	RHR HTX 2AINLET NOZZLE TO HEAD																					
System ID:	2045		Size/Length:	1.2" / 81.5"	Thickness/Diameter:	CS/0.875"/25.0"																			
Component ID:	2E11HX-2A-9WN3		Start Time:	1450	Finish Time:	1600																			
Limitations:	Yes - Due to Nozzle Configuration																								
Instrument Settings Serial No.: 18AD24PE Serial No.: SE0631 Manufacturer: GE Manufacturer: KRAUTKRAMER Model: USN 60 SW Linearity: L-18-045 Size: 0.5" Model: Comp - G Delay: 4.8592 Range: 4.0" Freq.: 2.25 MHz Center Freq.: N/A M/U Cal/Vet: 5.1202 Pulse Type: Square Exam Angle: 45 Squint Angle: N/A Damping: 500 Ohms Reject: 0% Measured Angle: 49 Mode: Shear PRF: Auto High SU Freq.: 2.25 MHz Exit Point: 50° # of Elements: 1 Frequency: 2.25 MHz Rectify: Fullwave Config.: Single Focus: N/A Voltage: 450 Pulse Width: 220 Shape: Round Contour: Flat Ax. Gain (dB): 33.0 Circ. Gain (dB): 33.0 Wedge Style: MSWQC				Search Unit <table border="1"> <thead> <tr> <th>Cal. Checks</th> <th>Time</th> <th>Date</th> </tr> </thead> <tbody> <tr> <td>Initial Cal.</td> <td>1018</td> <td>4/19/2018</td> </tr> <tr> <td>Inter. Cal.</td> <td>1803</td> <td>4/19/2018</td> </tr> <tr> <td>Inter. Cal.</td> <td>N/A</td> <td></td> </tr> <tr> <td>Inter. Cal.</td> <td>1827</td> <td>4/19/2018</td> </tr> <tr> <td>Final Cal.</td> <td>1850</td> <td>4/19/2018</td> </tr> </tbody> </table> Couplant Exam Batch: 150018 Type: ULTRAGEL II Mfg.: MAGNAFLUX				Cal. Checks	Time	Date	Initial Cal.	1018	4/19/2018	Inter. Cal.	1803	4/19/2018	Inter. Cal.	N/A		Inter. Cal.	1827	4/19/2018	Final Cal.	1850	4/19/2018
Cal. Checks	Time	Date																							
Initial Cal.	1018	4/19/2018																							
Inter. Cal.	1803	4/19/2018																							
Inter. Cal.	N/A																								
Inter. Cal.	1827	4/19/2018																							
Final Cal.	1850	4/19/2018																							
1 Screen Div. = 0.4 In. of Sound Path				Search Unit Cable Type: RG-174 Length: 6' No. Conn.: 0 Type: Ultragel II Mfg.: Magnaflux																					
Calibration Block Cal. Block No.: 0718 Thickness: .875" Dia.: Flat CW <input checked="" type="checkbox"/> CCW <input checked="" type="checkbox"/> Scan dB: 42.0 Cal. Blk. Temp.: 72 Temp. Tool: G503096 Exam Surface: O.D. Comp. Temp.: 63 Temp. Tool: G503096 Surface Condition: As Ground				Reference Block Reference Block Serial No.: 16-4047 Type: Ramps																					
Recordable Indication(s): Yes <input type="checkbox"/> No <input checked="" type="checkbox"/> (If Yes, Ref. Attached Ultrasonic Indication Report.) Results: Set <input checked="" type="checkbox"/> Unset <input type="checkbox"/> Eval <input type="checkbox"/>				Comments: Initial Section XI UT Exam. No Examination from Nozzle side due to configuration. Circ Scan limitation due to Nozzles & Weld configuration.																					
Percent Of Coverage Obtained > 90%: No - 50% Reviewed Previous Data: N/A																									
Examiner	Level	II-N	Signature	Date	Reviewer	Signature	Date																		
Goldsmith, C. Tony	<i>Tony Goldsmith</i>			4/19/2018	JASON POLISENSKY L-III	<i>Jason Polisensky</i>	4/20/18																		
Examiner	Level	N/A	Signature	Date	Site Review	Signature	Date																		
N/A					One Week Last Three Months & One Month Before Last Month 4/18 2018-04-20 09:35:09-0400																				
Other	Level	N/A	Signature	Date	ANit Review	Signature	Date																		
N/A					<i>David M. Reynolds</i>	<i>David M. Reynolds</i>	5-8-2018																		



UT Calibration/Examination

Site/Unit:	BNP	/	2	Procedure:	NDEP-0448	Outage No.:	B223R1																																								
Summary No.:	2-E11-3756			Procedure Rev.:	4	Report No.:	UT-18-026																																								
Workscope:	ISI			Work Order No.:	20200956	Page:	3 of 7																																								
Code:	2001 EDITION/2003 ADDENDA			Cal/Item:	C-B/C2.21	Location:																																									
Drawing No.:	C-02404 SHL 075-1			Description: RHR HTX 2A INLET NOZZLE TO HEAD																																											
System ID:	2045			Size/Length:	1.2" / 81.5"	Thickness/Diameter: CS/0.875"/26.0"																																									
Component ID:	2E11HX-2A-SWN3			Start Time:	1450	Finish Time:	1600																																								
Limitations:	Yes - Due to Nozzle Configuration																																														
Instrument Settings Serial No.: 15A024PE Manufacturer: GE Model: USN 60 SW Linearity: L-18-045 Delay: 0.8953 Range: 5.0" M'l Cal/Wel: 0.1280 Pulser Type: Square Damping: 500 Ohms Reject: 0% PRF: Auto High SU Freq.: 2.25 MHz Frequency: 2.25 MHz Rectify: Fullwave Voltage: 450 Pulse Width: 220 Ax. Gain (dB): 46.7 Circ. Gain (dB): N/A 1 Screen Div. = 0.5 in. of Sound Path				Search Unit Serial No.: SE0381 Manufacturer: GE Size: 0.5" Model: Comp - G Freq.: 2.25 MHz Center Freq.: N/A Exam Angle: 70 Squint Angle: N/A Measured Angle: 70 Mode: Shear Exit Point: 0.70" # of Elements: 1 Config.: Single Focus: N/A Shape: Round Contour: Flat Wedge Style: MSWQC Search Unit Cable Type: RG-174 Length: 6' No. Conn.: 0																																											
				Cal. Checks Time Date Init Cal. 1055 4/19/2018 Inter. Cal. 1528 4/19/2018 Inter. Cal. N/A Inter. Cal. 1543 4/19/2018 Final Cal. 1655 4/19/2018																																											
				Axial Oriented Search Unit <table border="1"> <thead> <tr> <th>Calibration Reflector</th> <th>Signal Amplitude %</th> <th>Sweep Division</th> <th>Sound Path</th> </tr> </thead> <tbody> <tr> <td>ID Notch</td> <td>79</td> <td>5</td> <td>2.49</td> </tr> <tr> <td></td> <td></td> <td></td> <td></td> </tr> </tbody> </table>				Calibration Reflector	Signal Amplitude %	Sweep Division	Sound Path	ID Notch	79	5	2.49																																
Calibration Reflector	Signal Amplitude %	Sweep Division	Sound Path																																												
ID Notch	79	5	2.49																																												
				Circumferential Oriented Search Unit <table border="1"> <thead> <tr> <th>Calibration Reflector</th> <th>Signal Amplitude %</th> <th>Sweep Division</th> <th>Sound Path</th> </tr> </thead> <tbody> <tr> <td>N/A</td> <td></td> <td></td> <td></td> </tr> <tr> <td></td> <td></td> <td></td> <td></td> </tr> </tbody> </table>				Calibration Reflector	Signal Amplitude %	Sweep Division	Sound Path	N/A																																			
Calibration Reflector	Signal Amplitude %	Sweep Division	Sound Path																																												
N/A																																															
				Reference/ Simulator Block <table border="1"> <thead> <tr> <th>Gain dB</th> <th>Reflector</th> <th>Signal Amplitude %</th> <th>Sweep Division</th> <th>Sound Path</th> </tr> </thead> <tbody> <tr> <td>18.4</td> <td>1" Radius</td> <td>81</td> <td>2</td> <td>1.0</td> </tr> <tr> <td></td> <td></td> <td></td> <td></td> <td></td> </tr> </tbody> </table>				Gain dB	Reflector	Signal Amplitude %	Sweep Division	Sound Path	18.4	1" Radius	81	2	1.0																														
Gain dB	Reflector	Signal Amplitude %	Sweep Division	Sound Path																																											
18.4	1" Radius	81	2	1.0																																											
				Comments: Initial Section XI UT Exam. Supplemental exam for coverage.																																											
Percent Of Coverage Obtained > 90%: No + 50% Reviewed Previous Data: N/A																																															
Examiner	Level	N-N	Signature	Date	Reviewer	Signature	Date																																								
Goldsmith, C. Tony			<i>Tony Goldsmith</i>	4/19/2018	JASON POLISENSTY L III	<i>Jason Polisensty</i>	4/20/18																																								
Examiner	Level	N/A	Signature	Date	Site Review	Chris Winkler cweChris Winkler, es, es, email: christopher.winkler@dear-energy.com, r=US 201804191414-0407	Date																																								
N/A																																															
Other	Level	N/A	Signature	Date	ANII Review	Signature	Date																																								
N/A																																															



Supplemental Report

Report No.: UT-18-026
 Page: 4 of 7

Summary No.: 2-E11-3786

Examiner: Goldsmith, C. Tony Tony Goldsmith
 Examiner: N/A
 Other: N/A

Level: II-N
 Level: N/A
 Level: N/A

Reviewer: J. Polsonay L.I.T. for OPG Date: 4/20/18
 Site Review: David M. Reynolds Date: 5-9-2018
 ANII Review: David M. Reynolds Date: 5-9-2018

Comments: T&C


Sketch or Photo: Z:\Unit 2\B223\Profiles & Contours\2E11HX-2A-SWN3 Pg1.bmp

THICKNESS2E11HX-2A-SWN3SHELL

.874 .874 .874

3.3 3.3 3.3
3.3 3.3 3.3

N.D.Z. 2 L.F.





Supplemental Report


Report No.: UT-18-026Page: 5 of 7Summary No.: 2-E11-3758Examiner: Goldsmith, C. Tony Tony GoldsmithLevel: II-NReviewer: J. Polisecky LIII Jason PolasekDate: 4/20/18Examiner: N/ALevel: N/ASite Review: CORPORATE REVIEW & NO QUALITY ASSISTDate: Other: N/ALevel: N/AANII Review: David M. Reynolds David ReynoldsDate: 5-9-2018Reviewed by: D.B.King UTI 4/20/18Date: 4/20/18

Comments: Coverage Plot
50% Examination Coverage Achieved

Sketch or Photo: Z:\Unit 2\0223\Profiles & Contours\2E11HX-2A-SWN3 Pg2.bmp

COVERAGE PLOT

AXIAL - 100%
CIRC - 0%
 $100/2 = 50\%$

2E11HX-2A-SWN3

BSEP, Unit 2 4th ISI Interval Limited NDE Data and Coverage Plots

UT Calibration/Examination

Site/Unit:	BNP	/	2	Procedure:	NDEP-0448	Outage No.:	B222R1																								
Summary No.:	2-E11-3757			Procedure Rev.:	003 TR B	Report No.:	UT-15-014																								
Workscope:	ISI			Work Order No.:	2252945	Page:	1 of 13																								
Code:	ASME XI, 2001 Ed., 03 Ad.			Cat./Item:	C-B/C2.21	Location:	See ISO																								
Drawing No.:	C-02404 Sht. 075-1			Description:	RHR HTX 2A OUTLET NOZZLE TO SHELL																										
System ID:	2045			Size/Length:	24"/75.398"	Thickness/Diameter:	1.0"/24"																								
Component ID:	2E11HX-2A-SWN4			Start Time:	1215	Finish Time:	1325																								
Limitations: SCANNED FROM SHELL SIDE ONLY																															
Instrument Settings Serial No.: 106946 Manufacturer: GEIT Model: USN 58LSW Linearity: L-15-003 Delay: 6.4641 Range: 4.0" M'tl Cal/Vel: 0.1266 Pulser Type: Square Damping: 500 Ohms Reject: 0% PRF: Auto High SU Freq.: 2.25 MHz Frequency: 2.25 MHz Rectify: Fullwave Voltage: 450 Pulse Width: 220				Search Unit Serial No.: SE2096 Manufacturer: GEIT Size: 0.5" Model: Comp-G Exam Angle: 45° Squint Angle: N/A Measured Angle: 45° Mode: Shear Exit Point: 0.35" # of Elements: 1 Config.: Single Focus: N/A Shape: Round Contour: N/A Wedge Style: Non-Integral																											
				Cal. Checks Time Date Initial Cal. 0840 3/6/2015 Inter. Cal. 1215 3/6/2015 Inter. Cal. N/A Inter. Cal. N/A Final Cal. 1607 3/6/2015																											
				Axial Orientated Search Unit <table border="1"> <tr> <th>Calibration Reflector</th> <th>Signal Amplitude %</th> <th>Sweep Division</th> <th>Sound Path</th> </tr> <tr> <td>ID NOTCH</td> <td>80%</td> <td>4.0</td> <td>1.590"</td> </tr> <tr> <td>OD NOTCH</td> <td>50%</td> <td>8.0</td> <td>3.160"</td> </tr> <tr> <td></td> <td></td> <td></td> <td></td> </tr> <tr> <td></td> <td></td> <td></td> <td></td> </tr> <tr> <td></td> <td></td> <td></td> <td></td> </tr> </table>				Calibration Reflector	Signal Amplitude %	Sweep Division	Sound Path	ID NOTCH	80%	4.0	1.590"	OD NOTCH	50%	8.0	3.160"												
Calibration Reflector	Signal Amplitude %	Sweep Division	Sound Path																												
ID NOTCH	80%	4.0	1.590"																												
OD NOTCH	50%	8.0	3.160"																												
				Couplant Cal. Batch: 14M076 Type: Ultralag II Mfg.: Magnaflux																											
				Circumferential Orientated Search Unit <table border="1"> <tr> <th>Calibration Reflector</th> <th>Signal Amplitude %</th> <th>Sweep Division</th> <th>Sound Path</th> </tr> <tr> <td>N/A</td> <td>N/A</td> <td>N/A</td> <td>N/A</td> </tr> <tr> <td></td> <td></td> <td></td> <td></td> </tr> <tr> <td></td> <td></td> <td></td> <td></td> </tr> <tr> <td></td> <td></td> <td></td> <td></td> </tr> </table>				Calibration Reflector	Signal Amplitude %	Sweep Division	Sound Path	N/A	N/A	N/A	N/A																
Calibration Reflector	Signal Amplitude %	Sweep Division	Sound Path																												
N/A	N/A	N/A	N/A																												
				Scan Coverage Upstream <input checked="" type="checkbox"/> Downstream <input type="checkbox"/> Scan dB: 37.0 CW <input checked="" type="checkbox"/> CCW <input checked="" type="checkbox"/> Scan dB: 37.0																											
				Reference Block Serial No.: 103402 Type: Römpas																											
				Reference/Simulator Block <table border="1"> <tr> <th>Gain dB</th> <th>Reflector</th> <th>Signal Amplitude %</th> <th>Sweep Division</th> <th>Sound Path</th> </tr> <tr> <td>25.0</td> <td>FSDH</td> <td>85%</td> <td>2.6</td> <td>1.040"</td> </tr> <tr> <td></td> <td></td> <td></td> <td></td> <td></td> </tr> <tr> <td></td> <td></td> <td></td> <td></td> <td></td> </tr> </table>				Gain dB	Reflector	Signal Amplitude %	Sweep Division	Sound Path	25.0	FSDH	85%	2.6	1.040"														
Gain dB	Reflector	Signal Amplitude %	Sweep Division	Sound Path																											
25.0	FSDH	85%	2.6	1.040"																											
Ax. Gain (dB): 25.0 Circ. Gain (dB): N/A 10 Screen Div. = 4.0 in. of Sound Path				Search Unit Cable Type: RG-174 Length: 6 No. Conn.: 0 Exam Batch: 14M076 Type: Ultralag II Mfg.: Magnaflux																											
Calibration Block Cal. Block No.: 072B Thickness: 1.125" Dia.: FLAT Cal. Blk. Temp.: 75° Temp. Tool: 106898 Comp. Temp.: 72° Temp. Tool: 106898				Scan Coverage Exam Surface: OD Surface Condition: As Found																											
Recordable Indication(s): Yes <input type="checkbox"/> No <input checked="" type="checkbox"/> (If Yes, Ref. Attached Ultrasonic Indication Report.) Results: Sat <input checked="" type="checkbox"/> Unsat <input type="checkbox"/> Eval <input type="checkbox"/> Percent Of Coverage Obtained > 90%: 75% Reviewed Previous Data: Yes				Comments: No recordable indications. See data report from 2004, no report number. Bottom 8" obstructed by adjacent girth weld.																											
Examiner	Level	II-PDI	Signature	Date	Reviewer	Signature	Date																								
Michael, Dickey E.	<i>Dickey, Michael</i>			3/6/2015	David King, Lvl III		3/8/2015																								
Examiner	Level	N/A	Signature	Date	Site Review	Signature	Date																								
N/A					Scott Larson	<i>Scott Larson</i>	3/12/2015																								
Other	Level	N/A	Signature	Date	ANII Review	Signature	Date																								
N/A					David M. Reynolds	<i>David M. Reynolds</i>	3/12/2015																								

UT Calibration/Examination

Site/Unit: BNP / 2 Procedure: NDEP-0448 Outage No.: B222R1
 Summary No.: 2-E11-3757 Procedure Rev.: 003 TR B Report No.: UT-15-014
 Workscope: ISI Work Order No.: 2252945 Page: 2 of 13

Code: ASME XI, 2001 Ed., 03 Ad. Cat./Item: C-B/C2.21 Location: See ISO
 Drawing No.: C-02404 Sht. 075-1 Description: RHR HTX 2A OUTLET NOZZLE TO SHELL
 System ID: 2045
 Component ID: 2E11HX-2A-SWN4 Size/Length: 24" / 75.398" Thickness/Diameter: 1.0" / 24"
 Limitations: SCANNED FROM SHELL SIDE ONLY Start Time: 1215 Finish Time: 1325

Instrument Settings		Search Unit			Axial Orientated Search Unit		
Serial No.:	<u>106946</u>	Serial No.:	<u>SE2104</u>		Cal. Checks	Time	Date
Manufacturer:	<u>GEIT</u>	Manufacturer:	<u>GEIT</u>		Initial Cal.	<u>0850</u>	<u>3/6/2015</u>
Model:	<u>USN 58LSW</u>	Linearity:	<u>L-15-003</u>		Inter. Cal.	<u>1248</u>	<u>3/6/2015</u>
Delay:	<u>8.7219</u>	Range:	<u>5.0"</u>		Inter. Cal.	<u>N/A</u>	
M'tl Cal/Vel:	<u>0.1266</u>	Pulser Type:	<u>Square</u>		Inter. Cal.	<u>N/A</u>	
Damping:	<u>500 Ohms</u>	Reject:	<u>0%</u>		Measured Angle:	<u>60°</u>	Mode: <u>Shear</u>
PRF:	<u>Auto High</u>	SU Freq.:	<u>2.25 MHz</u>		Exit Point:	<u>0.50"</u>	# of Elements: <u>1</u>
Frequency:	<u>2.25 MHz</u>	Rectify:	<u>Fullwave</u>		Config.:	<u>Single</u>	Focus: <u>N/A</u>
Voltage:	<u>450</u>	Pulse Width:	<u>220</u>		Shape:	<u>Round</u>	Contour: <u>N/A</u>
Ax. Gain (dB):	<u>44.0</u>	Circ. Gain (dB):	<u>N/A</u>		Wedge Style:	<u>Non-Integral</u>	
<u>10</u> Screen Div. = <u>5.0</u> in. of <u>Sound Path</u>		Search Unit Cable			Cal. Batch:	<u>14M076</u>	
		Type:	<u>RG-174</u>	Length:	<u>6'</u>	No. Conn.:	<u>0</u>
		Type:	<u>RG-174</u>	Length:	<u>6'</u>	No. Conn.:	<u>0</u>
Scan Coverage							
Cal. Block No.:		<u>072B</u>		Upstream <input checked="" type="checkbox"/>	Downstream <input type="checkbox"/>	Scan dB:	<u>44.0</u>
Thickness:		<u>1.125"</u>		CW <input checked="" type="checkbox"/>	CCW <input checked="" type="checkbox"/>	Scan dB:	<u>44.0</u>
Cal. Blk. Temp.:		<u>75°</u>		Exam Surface:	<u>OD</u>		
Comp. Temp.:		<u>72°</u>		Surface Condition:	<u>As Found</u>		
Recordable Indication(s): Yes <input type="checkbox"/> No <input checked="" type="checkbox"/> (If Yes, Ref. Attached Ultrasonic Indication Report.)							
Results: Sat <input checked="" type="checkbox"/> Unsat <input type="checkbox"/> Eval <input type="checkbox"/>							
Comments: Previously recorded indications, verified no changes except amplitude is higher due to using notches. See 2004 data. Bottom 8" obstructed by adjacent girth weld.							
Percent Of Coverage Obtained > 90%: <u>75%</u> Reviewed Previous Data: <u>Yes</u>							

Examiner	Level	II-PDI	Signature	Date	Reviewer	Signature	Date
<u>Michael, Dickey E.</u>	<u>Dickey Michael</u>			<u>3/6/2015</u>	<u>David King, Lvl III</u>		<u>3/8/2015</u>
Examiner	Level	N/A	Signature	Date	Site Review	Signature	Date
<u>N/A</u>					<u>Scott Larson</u>	<u>Scott Larson</u>	<u>3/12/2015</u>
Other	Level	N/A	Signature	Date	ANII Review	Signature	Date
<u>N/A</u>					<u>David M. Reynolds</u>	<u>David M. Reynolds</u>	<u>3/12/2015</u>

UT Calibration/Examination

Site/Unit:	BNP / 2	Procedure:	WDI-STD-006	Outage No.:	B222R1		
Summary No.:	2-E11-3757	Procedure Rev.:	7	Report No.:	UT-15-014		
Workscope:	ISI	Work Order No.:	2252945	Page:	3 of 13		
Code:	ASME XI, 2001 Ed., 03 Ad.	Cat./Item:	C-B/C2.21	Location:	See ISO		
Drawing No.:	C-02404 Sht. 075-1	Description: RHR HTX 2A OUTLET NOZZLE TO SHELL					
System ID:	2045			Size/Length:	24"/75.398"		
Component ID:	2E11HX-2A-SWN4			Thickness/Diameter:	1.0"/24"		
Limitations:	NONE			Start Time:	1341		
Instrument Settings		Search Unit		Axial Orientated Search Unit			
Serial No.:	105209	Serial No.:	H30049	Cal. Checks	Time		
Manufacturer:	GEIT	Manufacturer:	KBA	Initial Cal.	1100		
Model:	USN 60SW	Linearity:	L-15-002	Inter. Cal.	N/A		
Delay:	11.5103	Range:	2.5"	Inter. Cal.	1340		
M'tl Cal/Vel:	0.1268	Pulser Type:	Square	Inter. Cal.	N/A		
Damping:	500 Ohms	Reject:	0%	Measured Angle:	49°		
PRF:	Auto High	SU Freq.:	2.25 MHz	Exam Angle:	48°		
Frequency:	2.25 MHz	Rectify:	Fullwave	Squint Angle:	N/A		
Voltage:	450	Pulse Width:	220	Mode:	Shear		
Ax. Gain (dB):	N/A	Circ. Gain (dB):	34.0	Exit Point:	0.70"		
10 Screen Div. =	2.5	in. of	Sound Path	# of Elements:	1		
Calibration Block		Search Unit Cable		Cal. Batch:	14M076		
Cal. Block No.:	072B	Upstream	<input type="checkbox"/>	Downstream	<input type="checkbox"/>		
Thickness:	1.125"	Dia.:	FLAT	Scan dB:	N/A		
Cal. Blk. Temp.:	67°	Temp. Tool:	106893	CW	<input checked="" type="checkbox"/>		
Comp. Temp.:	71°	Temp. Tool:	106893	CCW	<input checked="" type="checkbox"/>		
Recordable Indication(s):	Yes <input type="checkbox"/>	No <input checked="" type="checkbox"/>	(If Yes, Ref. Attached Ultrasonic Indication Report.)				
Results:	Sat <input checked="" type="checkbox"/>	Unsat <input type="checkbox"/>	Eval <input type="checkbox"/>	Comments: Shell side scan +/- 63° to 87°. See sketch on supplemental report. Bottom 8" obstructed by adjacent girth weld.			
Percent Of Coverage Obtained > 90%:	75%	Reviewed Previous Data:	Yes	Reference Block	Reference/Simulator Block		
Examiner	Level	II-PDI	Signature	Date	Reviewer	Signature	Date
Jennings, Jason J.				3/6/2015	David King, Lvl III		3/8/2015
Examiner	Level	N/A	Signature	Date	Site Review	Signature	Date
N/A					Scott Larson	Scott Larson	3/12/2015
Other	Level	N/A	Signature	Date	ANII Review	Signature	Date
N/A					David M. Reynolds	David M. Reynolds	3/12/2015

BSEP, Unit 2 4th ISI Interval Limited NDE Data and Coverage Plots

UT Calibration/Examination

Site/Unit: BNP / 2 Procedure: WDI-STD-006 Outage No.: B222R1
 Summary No.: 2-E11-3757 Procedure Rev.: 7 Report No.: UT-15-014
 Workscope: ISI Work Order No.: 2252945 Page: 4 of 13

Code: ASME XI, 2001 Ed., 03 Ad. Cat./Item: C-B/C2.21 Location: See ISO
 Drawing No.: C-02404 Sht. 075-1 Description: RHR HTX 2A OUTLET NOZZLE TO SHELL
 System ID: 2045
 Component ID: 2E11HX-2A-SWN4 Size/Length: 24"/75.398" Thickness/Diameter: 1.0"/24"
 Limitations: NOZZLE BOSS LENGTH (SKETCH ATTACHED) Start Time: 1457 Finish Time: 1514

Instrument Settings		Search Unit			Axial Orientated Search Unit		
Serial No.:	<u>105209</u>	Serial No.:	<u>SE2123</u>		Cal. Checks	Time	Date
Manufacturer:	<u>GEIT</u>	Manufacturer:	<u>GEIT</u>		Initial Cal.	<u>1225</u>	<u>3/6/2015</u>
Model:	<u>USN 60SW</u>	Linearity:	<u>L-15-002</u>		Inter. Cal.	<u>N/A</u>	
Delay:	<u>9.2556</u>	Range:	<u>12.0"</u>		Inter. Cal.	<u>1456</u>	<u>3/6/2015</u>
M'tl Cal/Vel:	<u>0.1294</u>	Pulser Type:	<u>Square</u>		Inter. Cal.	<u>N/A</u>	
Damping:	<u>500 Ohms</u>	Reject:	<u>0%</u>		Measured Angle:	<u>70.5°</u>	Mode: <u>Shear</u>
PRF:	<u>Auto High</u>	SU Freq.:	<u>2.25 MHz</u>		Exit Point:	<u>0.65"</u>	# of Elements: <u>1</u>
Frequency:	<u>2.25 MHz</u>	Rectify:	<u>Fullwave</u>		Config.:	<u>Single</u>	Focus: <u>N/A</u>
Voltage:	<u>450</u>	Pulse Width:	<u>220</u>		Shape:	<u>Round</u>	Contour: <u>Flat</u>
Ax. Gain (dB):	<u>56.5</u>	Circ. Gain (dB):	<u>56.5</u>		Wedge Style:	<u>Non-Integral</u>	
10 Screen Div. = <u>12.0</u> in. of <u>Sound Path</u>		Search Unit Cable			Couplant		
		Type:	<u>RG-174</u>	Length:	<u>6'</u>	No. Conn.:	<u>0</u>
Calibration Block							
Scan Coverage							
Cal. Block No.:	<u>045BR</u>		Upstream <input type="checkbox"/>	Downstream <input type="checkbox"/>	Scan dB:	<u>N/A</u>	
Thickness:	<u>3.0"</u>	Dia.:	<u>FLAT</u>		CW <input checked="" type="checkbox"/>	CCW <input checked="" type="checkbox"/>	Scan dB: <u>58.0</u>
Cal. Blk. Temp.:	<u>69°</u>	Temp. Tool:	<u>106893</u>		Exam Surface:	<u>OD</u>	
Comp. Temp.:	<u>71°</u>	Temp. Tool:	<u>106893</u>		Surface Condition:	<u>As Found</u>	
Recordable Indication(s): Yes <input type="checkbox"/> No <input checked="" type="checkbox"/> (If Yes, Ref. Attached Ultrasonic Indication Report.)							
Results:	Sat <input checked="" type="checkbox"/>	Unsat <input type="checkbox"/>	Eval <input type="checkbox"/>	Comments: Nozzle side scan +/- 123° to 137°. See sketch on supplemental report.			

Examiner	Level	<u>II-PDI</u>	Signature	Date	Reviewer	Signature	Date
<u>Jennings, Jason J.</u>				<u>3/6/2015</u>	<u>David King, Lvl III</u>		<u>3/8/2015</u>
Examiner	Level	<u>N/A</u>	Signature	Date	Site Review	Signature	Date
<u>N/A</u>					<u>Scott Larson</u>		<u>3/8/2015</u>
Other	Level	<u>N/A</u>	Signature	Date	ANII Review	Signature	Date
<u>N/A</u>					<u>David M. Reynolds</u>		<u>3/21/2015</u>




Supplemental Report

Report No.: UT-15-014
Page: 5 of 13

Summary No.: 2-E11-3757

Sketch or Photo: K:\Shared\ldeal\B222R1 Scanned Data\2E11HX-2A-SWN4(1).jpg






Supplemental Report

Report No.: UT-15-014Page: 6 of 13Summary No.: 2-E11-3757

Sketch or Photo: K:\Shared\ldeal\B222R1 Scanned Data\2E11HX-2A-SWN4(2).jpg






Supplemental Report

Report No.: UT-15-014

Page: 7 of 13

Summary No.: 2-E11-3757

Sketch or Photo: K:\Shared\ldeal\B222R1 Scanned Data\2E11HX-2A-SWN4(3).jpg





Supplemental Report

Report No.: UT-15-014

Page: 8 of 13

Summary No.: 2-E11-3757

Sketch or Photo: K:\Shared\ldeall\B222R1 Scanned Data\2E11HX-2A-SWN4(4).jpg

$$\begin{array}{r} \underline{75.4 \text{ CRC}} - 8'' \text{ MISSED CIRC} \\ \text{BDC} = \underline{\underline{89.5\%}} \end{array}$$

$$\begin{array}{r} 1.6'' \\ \times 0.38'' \\ \hline 0.608'' \text{ SQ. IN.} \end{array}$$

$O+180$	$90-270$	$90-270$	$O-180$
Ax	Ax	CIRC	CIRC
$\frac{0.20}{\times 0.15}$	100%	$\frac{0.38}{\times 0.20}$	$\frac{0.38}{\times 0.20}$
$\hline 0.05$	COVERAGE ACHIEVED	$\frac{0.076}{0.190}$	$\frac{0.076}{0.190}$
$\div 2$		$\div 2$	$\div 2$
$\hline 0.035$		$\hline 0.038$	$\hline 0.038$
+		+ 0.190	+ 0.290
$\frac{0.17}{\times 0.05}$		$\hline 0.228$	$\hline 0.328$
$\hline 0.0085$		↓	↓
$\div 2$		0.23	0.33
$\hline 0.004$		23%	33%
+		MISSED	MISSED
$\hline 0.035$			
$\hline 0.039$			
↓			
0.04"			
$\div 0.608$			
$\hline 0.07$			
(7%) MISSED			
93% COVERAGE ACHIEVED			
	* 89	* 89	
	$\times 0.965$	$\times 0.72$	
	86% ACHIEVED	64% ACHIEVED	
	Ax	CIRC	

$$86 + 64 = 150 \div 2 = 75.0\%$$

TOTAL EXAM VOLUME
COVERAGE



Supplemental Report

Report No.: UT-15-014



Page: 9 of 13

Summary No.: 2-E11-3757

Examiner: <u>Michael, Dickey E.</u>	Level: <u>II-PDI</u>	Reviewer: <u>David King, Lvl III</u>	Date: <u>3/8/2015</u>
Examiner: <u>N/A</u>	Level: <u>N/A</u>	Site Review: <u>Scott Larson</u>	Date: <u>3/12/2015</u>
Other: <u>N/A</u>	Level: <u>N/A</u>	ANII Review: <u>David M. Reynolds</u>	Date: <u>3/12/2015</u>

Comments: Reference EPRI Model IR-2010-396.

Sketch or Photo: K:\Shared\ldeal\B222R1 Scanned Data\2E11HX-2A-SWN4(5).jpg






Supplemental Report

Report No.: UT-15-014Page: 10 of 13Summary No.: 2-E11-3757

Examiner: <u>Michael, Dickey E.</u>	Level: <u>II-PDI</u>	Reviewer: <u>David King, Lvl III</u>	Date: <u>3/8/2015</u>
Examiner: <u>N/A</u>	Level: <u>N/A</u>	Site Review: <u>Scott Larson</u>	Date: <u>3/12/2015</u>
Other: <u>N/A</u>	Level: <u>N/A</u>	ANII Review: <u>David M. Reynolds</u>	Date: <u>3/12/2015</u>

Comments: Reference EPRI Model IR-2010-396.

Sketch or Photo: K:\Shared\ldeall\B222R1 Scanned Data\2E11HX-2A-SWN4(6).jpg





Supplemental Report

Report No.: UT-15-014

Page: 11 of 13

Summary No.: 2-E11-3757

Examiner: <u>Michael, Dickey E.</u>	Level: <u>II-PDI</u>	Reviewer: <u>David King, Lvl III</u>	Date: <u>3/8/2015</u>
Examiner: <u>N/A</u>	Level: <u>N/A</u>	Site Review: <u>Scott Larson</u>	Date: <u>3/12/2015</u>
Other: <u>N/A</u>	Level: <u>N/A</u>	ANII Review: <u>David M. Reynolds</u>	Date: <u>3/12/2015</u>

Comments: Reference EPRI Model IR-2010-396.

Sketch or Photo: K:\Shared\ldeal\B222R1 Scanned Data\2E11HX-2A-SWN4(7).jpg

Table 6-5
Brunswick Nozzle-to-Shell Weld Examination Modeling Parameters

Brunswick Nozzle ID	Metal Path		Beam Angle at Flaw		Maximum Misorientation	Percent Coverage
	Min	Max	Min	Max		
Core Spray (N5)	6.71	8.65	45	50	11	100
Head Spray (N6)	3.27	5.35	45	50	22	100
Vent (N7)	3.27	4.13	45	50	11	100
RHR Outlet (N4)	1.35	11.69	45	50	22	19

BSEP, Unit 2 4th ISI Interval Limited NDE Data and Coverage Plots

UT Calibration/Lexamination

Site/Unit:	BNP / 2	Procedure:	WDI-STD-006	Outage No.:	B222R1			
Summary No.:	2-E11-3748	Procedure Rev.:	7	Report No.:	UT-15-013			
Workscope:	ISI	Work Order No.:	2252945	Page:	1 of 8			
Code:	ASME XI, 2001 Ed., 03 Ad.	Cat./Item:	C-B/C2.22	Location:	See ISO			
Drawing No.:	C-02404 Sht. 075-1	Description: RHR HTX 2A OUTLET NOZZLE INNER RADIUS						
System ID:	2045							
Component ID:	2E11HX-2A-N4NIR	Size/Length: 24"/75" Thickness/Diameter: 1.0"/24"						
Limitations:	NOZZLE/SHELL CONFIGURATION	Start Time: 1403 Finish Time: 1417						
Instrument Settings		Search Unit		Axial Orientated Search Unit				
Serial No.:	105209	Serial No.:	SE2123	Cal. Checks	Time	Date		
Manufacturer:	GEIT	Manufacturer:	GEIT	Initial Cal.	1205	3/6/2015		
Model:	USN 60SW	Linearity:	L-15-002	Inter. Cal.	N/A			
Delay:	10.9584	Range:	10.0	Inter. Cal.	1402	3/6/2015		
M'tl Cal/Vel:	0.1297	Pulser Type:	Square	Inter. Cal.	N/A			
Damping:	500 Ohms	Reject:	0%	Measured Angle:	55°	Mode: Shear		
PRF:	Auto High	SU Freq.:	2.25 MHz	Exit Point:	0.60"	# of Elements: 1		
Frequency:	2.25 MHz	Rectify:	Fullwave	Config.:	Single	Focus: N/A		
Voltage:	450	Pulse Width:	220	Shape:	Round	Contour: Flat		
Ax. Gain (dB):	39.0	Circ. Gain (dB):	39.0	Wedge Style:	Non-Integral			
10 Screen Div. =	10.0	in. of Sound Path	Search Unit Cable		Cal. Batch:	14M076		
Calibration Block		Scan Coverage		Type:	Ultragel II			
Cal. Block No.:	045BR	Upstream	<input type="checkbox"/>	Downstream	<input type="checkbox"/>	Scan dB: N/A		
Thickness:	3.0"	Dia.:	FLAT	CW	<input checked="" type="checkbox"/>	CCW	<input checked="" type="checkbox"/>	Scan dB: 45.0
Cal. Blk. Temp.:	69°	Temp. Tool:	106893	Exam Surface:	OD		Serial No.:	104876
Comp. Temp.:	71°	Temp. Tool:	106893	Surface Condition:	As Found		Type:	Rompas
Recordable Indication(s): Yes <input type="checkbox"/> No <input checked="" type="checkbox"/> (If Yes, Ref. Attached Ultrasonic Indication Report.)								
Comments: Nozzle side circ scan +/- 123° skew.								
Results: Sat <input checked="" type="checkbox"/> Unsat <input type="checkbox"/> Eval <input type="checkbox"/>								
Percent Of Coverage Obtained > 90%: 55% Reviewed Previous Data: Yes								

Examiner	Level	II-PDI	Signature	Date	Reviewer	Signature	Date
Jennings, Jason J.				3/6/2015	David King, Lvl III		3/8/2015
Examiner	Level	N/A	Signature	Date	Site Review	Signature	Date
N/A					Scott Larson		3/12/2015
Other	Level	N/A	Signature	Date	ANII Review	Signature	Date
N/A					David M. Reynolds		3/12/2015



Enclosure 3
BSEP, Unit 2 4th ISI Interval Limited NDE Data and Coverage Plots
UT Calibration/Lexamination

Site/Unit:	BNP	/	2	Procedure:	WDI-STD-006	Outage No.:	B222R1
Summary No.:	2-E11-3748			Procedure Rev.:	7	Report No.:	UT-15-013
Workscope:	ISI			Work Order No.:	2252945	Page:	2 of 8
Code:	ASME XI, 2001 Ed., 03 Ad.			Cat./Item:	C-B/C2.22	Location:	See ISO
Drawing No.:	C-02404 Sht. 075-1			Description:	RHR HTX 2A OUTLET NOZZLE INNER RADIUS		
System ID:	2045			Size/Length:	24"/75"	Thickness/Diameter:	1.0"/24"
Component ID:	2E11HX-2A-N4NIR			Start Time:	1420	Finish Time:	1435
Limitations: NOZZLE/SHELL CONFIGURATION							
Instrument Settings Serial No.: 105209 Manufacturer: GEIT Model: USN 60SW Linearity: L-15-002 Delay: 8.2403 Range: 11.0" M'tl Cal/Vel: 0.1289 Pulser Type: Square Damping: 500 Ohms Reject: 0% PRF: Auto High SU Freq.: 2.25 MHz Frequency: 2.25 MHz Rectify: Fullwave Voltage: 450 Pulse Width: 220 Ax. Gain (dB): 46.0 Circ. Gain (dB): 46.0 10 Screen Div. = 11.0 in. of Sound Path				Search Unit Serial No.: SE2123 Manufacturer: GEIT Size: 0.5" Model: Comp-G Freq.: 2.25 MHz Center Freq.: N/A Exam Angle: 60° Squint Angle: N/A Measured Angle: 60° Mode: Shear Exit Point: 0.60" # of Elements: 1 Config.: Single Focus: N/A Shape: Round Contour: Flat Wedge Style: Non-Integral			
				Couplant Cal. Batch: 14M076 Type: Ultragel II Mfg.: Magnaflux			
				Search Unit Cable Type: RG-174 Length: 6' No. Conn.: 0 Mfg.: Sonotech, Inc.			
Calibration Block Cal. Block No.: 045BR Thickness: 3.0" Dia.: FLAT Cal. Blk. Temp.: 69° Temp. Tool: 106893 Comp. Temp.: 71° Temp. Tool: 106893				Scan Coverage Upstream <input type="checkbox"/> Downstream <input type="checkbox"/> Scan dB: N/A CW <input checked="" type="checkbox"/> CCW <input checked="" type="checkbox"/> Scan dB: 53.0 Exam Surface: OD Surface Condition: As Found			
				Reference Block Serial No.: 104876 Type: Rompas			
Recordable Indication(s): Yes <input type="checkbox"/> No <input checked="" type="checkbox"/> (If Yes, Ref. Attached Ultrasonic Indication Report.) Results: Sat <input checked="" type="checkbox"/> Unsat <input type="checkbox"/> Eval <input type="checkbox"/>				Comments: Nozzle side circ scan +/- 118° to 132° skew.			
Percent Of Coverage Obtained > 90%: 55%				Reviewed Previous Data: Yes			
Examiner	Level	II-PDI	Signature	Date	Reviewer	Signature	Date
Jennings, Jason J.				3/6/2015	David King, Lvl III		3/8/2015
Examiner	Level	N/A	Signature	Date	Site Review	Signature	Date
N/A					Scott Larson		3/8/2015
Other	Level	N/A	Signature	Date	ANII Review	Signature	Date
N/A					David M. Reynolds		3/12/2015



BSEP, Unit 2 4th ISI Interval Limited NDE Data and Coverage Plots

UT Calibration/Examination

Site/Unit:	BNP / 2	Procedure:	WDI-STD-006	Outage No.:	B222R1									
Summary No.:	2-E11-3748	Procedure Rev.:	7	Report No.:	UT-15-013									
Workscope:	ISI	Work Order No.:	2252945	Page:	3 of 8									
Code:	ASME XI, 2001 Ed., 03 Ad.	Cat./Item:	C-B/C2.22	Location:	See ISO									
Drawing No.:	C-02404 Sht. 075-1	Description: RHR HTX 2A OUTLET NOZZLE INNER RADIUS												
System ID:	2045	Size/Length:	24"/75"	Thickness/Diameter:	1.0"/24"									
Component ID:	2E11HX-2A-N4NIR	Start Time:	1438	Finish Time:	1454									
Limitations:	NOZZLE/SHELL CONFIGURATION													
Instrument Settings		Search Unit		Axial Orientated Search Unit										
Serial No.:	105209	Serial No.:	SE2123	Cal. Checks	Time	Date	Calibration Reflector	Signal Amplitude %	Sweep Division	Sound Path				
Manufacturer:	GEIT	Manufacturer:	GEIT	Initial Cal.	1220	3/6/2015	ID NOTCH	80%	7.10	7.058"				
Model:	USN 60SW	Linearity:	L-15-002	Inter. Cal.	N/A									
Delay:	10.3859	Range:	10.0"	Inter. Cal.	1437	3/6/2015								
M'tl Cal/Vel:	0.1297	Pulser Type:	Square	Inter. Cal.	N/A									
Damping:	500 Ohms	Reject:	0%	Measured Angle:	65°	Mode: Shear								
PRF:	Auto High	SU Freq.:	2.25 MHz	Exam Angle:	65°	Squint Angle: N/A								
Frequency:	2.25 MHz	Rectify:	Fullwave	Exit Point:	0.65"	# of Elements: 1								
Voltage:	450	Pulse Width:	220	Config.:	Single	Focus: N/A								
Ax. Gain (dB):	52.0	Circ. Gain (dB):	52.0	Shape:	Round	Contour: Flat								
10 Screen Div. = 10.0 in. of Sound Path		Wedge Style:	Non-Integral		Couplant									
		Search Unit Cable		Cal. Batch:	14M076									
		Type:	RG-174	Length:	6'	No. Conn.:	0	Type:	Ultragel II					
							Mfg.:	Magnaflux						
							Exam Batch:	09225						
							Type:	Ultragel II						
							Mfg.:	Sonotech, Inc.						
Calibration Block		Scan Coverage				Circumferential Orientated Search Unit								
Cal. Block No.:	045BR	Upstream	<input type="checkbox"/>	Downstream	<input type="checkbox"/>	Scan dB:	N/A	Calibration Reflector	Signal Amplitude %	Sweep Division	Sound Path			
Thickness:	3.0"	Dia.:	FLAT	CW	<input checked="" type="checkbox"/>	CCW	<input checked="" type="checkbox"/>	Scan dB:	55.0					
Cal. Blk. Temp.:	69°	Temp. Tool:	106893	Exam Surface:	OD		Type:	Rompas						
Comp. Temp.:	71°	Temp. Tool:	106893	Surface Condition:	As Found		Serial No.:	104876						
Recordable Indication(s): Yes <input type="checkbox"/> No <input checked="" type="checkbox"/>		(If Yes, Ref. Attached Ultrasonic Indication Report.)				Reference Block				Reference/Simulator Block				
Results:	Sat <input checked="" type="checkbox"/>	Unsat <input type="checkbox"/>	Eval <input type="checkbox"/>					Type:	Rompas	Gain dB	Reflector	Signal Amplitude %	Sweep Division	Sound Path
Percent Of Coverage Obtained > 90%:		55%	Reviewed Previous Data:	Yes						27.0	NSDH	80%	0.80	0.791"
Examiner	Level	II-PDI	Signature		Date	Reviewer			Signature	Date				
Jennings, Jason J.					3/6/2015	David King, Lvl III				3/8/2015				
Examiner	Level	N/A	Signature		Date	Site Review			Signature	Date				
N/A						Scott Larson				3/8/2015				
Other	Level	N/A	Signature		Date	ANII Review			Signature	Date				
N/A						David M. Reynolds				3/12/2015				



Supplemental Report

Report No.: UT-15-013

Page: 4 of 8

Summary No.: 2-E11-3748

Examiner: Jennings, Jason J.	Level: II-PDI	Reviewer: David King, Lvl III	Date: 3/8/2015
Examiner: N/A	Level: N/A	Site Review: Scott Larson	Date: 3/12/2015
Other: N/A	Level: N/A	ANII Review: David M. Reynolds	Date: 3/12/2015

Comments: Reference Scan Plan WDI-PJF-1314381-EPP-001, Rev. 2 (Table parameters below).

The 70° Exam prescribed by EPRI model Report # IR-2010-396 was not performed. Due to excessive R-Dimensions and Metal Paths, it was deemed impractical and ineffective as the beam would have to complete as many as eight legs (bounces) in order to cover the volume. This is a result of the relatively thin shell wall in contrast to the thicker walled nozzle.

Conclusion of the 70° shell-side prescription in IR-2010-396 was discussed with the EPRI Project Manager that was responsible for the IR. The EPRI Project Manager agreed with the conclusion that this angle would be ineffective based on beam spread at such distances.

Sketch or Photo: K:\Shared\lideal\B222R1 Scanned Data\2E11HX-2A-N4NIR(1).jpg

Refracted Angle	55°	60°	65°	70°
Wedge Radius	Flat	Flat	Flat	Flat
Skew Angle	± 123°	± (118° to 132°)	± 128°	± (17° to 37°)
Misorientation Angle (Max)	9°	22°	22°	14°
Inspection Surface	Nozzle Boss	Nozzle Boss	Nozzle Boss	Vessel Shell
Scan Area("R" or "Z" from barrel O.D. surface or shell surface)	2.15" – 2.66" (Z)	2.12 – 2.85" (Z)	2.12" – 2.42" (Z)	3.03" – 13.11" (R)
Min. Metal Path	~7.09"	~6.89"	~6.80"	~10.68"
Max. Metal Path	~8.11"	~10.23"	~9.57"	~23.07"





Supplemental Report

Report No.: UT-15-013

Page: 5 of 8

Summary No.: 2-E11-3748

Sketch or Photo: K:\Shared\ldeal\B222R1 Scanned Data\2E11HX-2A-N4NIR(2).jpg






Supplemental Report

Report No.: UT-15-013

Page: 6 of 8

Summary No.: 2-E11-3748

Sketch or Photo: K:\Shared\ldeal\B222R1 Scanned Data\2E11HX-2A-N4NIR(3).jpg






Supplemental Report

Report No.: UT-15-013
Page: 7 of 8

Summary No.: 2-E11-3748

Sketch or Photo: K:\Shared\ldeal\B222R1 Scanned Data\2E11HX-2A-N4NIR(4).jpg





Supplemental Report

Report No.: UT-15-013

Page: 8 of 8

Summary No.: 2-E11-3748

Sketch or Photo: K:\Shared\ldeall\B222R1 Scanned Data\2E11HX-2A-N4NIR(5).jpg

Table 6-2 lists the summary of the modeling parameters for the detection techniques to examine the Brunswick nozzle inner corner regions.

Table 6-2
Brunswick Detection Technique Inner Corner Region Modeling Parameters

Nozzle ID	Metal Path		Beam Angle at Flaw		Maximum Misorientation	Percent Coverage
	Min	Max	Min	Max		
RHR Outlet (N4)	6.80	23.07	65	90	22	79