

PROPOSED TECHNICAL SPECIFICATION CHANGES

9110250211 911015  
PDR ADOCK 05000368  
P PDR

TABLE 3.6-1 (Cont.)

CONTAINMENT ISOLATION VALVES

<u>PENETRATION NUMBER</u>	<u>VALVE NUMBER</u>	<u>FUNCTION</u>	<u>ISOLATION TIME (SEC)</u>
A. CONTAINMENT ISOLATION (Cont.)			
2P68	2CV-2060-1	Containment Sump Isolation (inside)	≤ 20
	2CV-2061-2	Containment Sump Drain Isolation (outside)	≤ 20
2P69	2CV-2202-1	Reactor Drain Tank Discharge (inside)	≤ 20
	2CV-2201-2	Reactor Drain Tank Discharge (outside)	≤ 20
B. CONTAINMENT PURGE			
2P6	2SV-8231-2	H <sub>2</sub> Purge Inlet Isolation (outside)	≤ 20
	2SV-8273-1	H <sub>2</sub> Purge Outlet Isolation (inside)	≤ 20
	2SV-8271-2	H <sub>2</sub> Purge Outlet Isolation (outside)	≤ 20
2P58	2SV-8261-2	Containment Atmosphere Sample (outside)	≤ 20
	2SV-8265-1	Containment Atmosphere Sample (inside)	≤ 20
	2SV-8263-2	Containment Atmosphere Sample (outside)	≤ 20
2V1	2CV-8284-2	Containment Purge Inlet Isolation (outside)	≤ 5
	2CV-8283-1	Containment Purge Inlet Isolation (outside)	≤ 5
2V2	2CV-8286-2	Containment Purge Outlet Isolation (outside)	≤ 5
	2CV-8285-1	Containment Purge Outlet Isolation (outside)	≤ 5

MARK UP OF ORIGINAL SPEC FOR INFO

TABLE 3.6-1 (Cont.)

CONTAINMENT ISOLATION VALVES

<u>PENETRATION NUMBER</u>	<u>VALVE NUMBER</u>	<u>FUNCTION</u>	<u>ISOLATION TIME (SEC)</u>
A. CONTAINMENT ISOLATION (Cont.)			
2P68	2CV-2060-1	Containment Sump Isolation (inside)	≤ 20
	2CV-2061-2	Containment Sump Drain Isolation (outside)	≤ 20
2P69	2CV-2202-1	Reactor Drain Tank Discharge (inside)	≤ 20
	2CV-2201-2	Reactor Drain Tank Discharge (outside)	≤ 20
B. CONTAINMENT PURGE			
2P6	2SV-8231-2	H <sub>2</sub> Purge Inlet Isolation (outside)	≤ 20
	2SV-8273-1	H <sub>2</sub> Purge Outlet Isolation (inside)	≤ 20
	2SV-8271-2	H <sub>2</sub> Purge Outlet Isolation (outside)	≤ 20
2P58	2SV-8261-2	Containment Atmosphere Sample (outside)	≤ 20
	2SV-8265-1	Containment Atmosphere Sample (inside)	≤ 20
	2SV-8263-2	Containment Atmosphere Sample (outside)	≤ 20
2V1	<del>2CV-8289-1</del>	<del>Containment Purge Inlet Isolation (inside)</del>	<del>≤ 5</del>
	2CV-8284-2	Containment Purge Inlet Isolation (outside)	≤ 5
	2CV-8283-1	Containment Purge Inlet Isolation (outside)	≤ 5
2V2	<del>2CV-8291-1</del>	<del>Containment Purge Outlet Isolation (outside)</del>	<del>≤ 5</del>
	2CV-8286-2	Containment Purge Outlet Isolation (outside)	≤ 5
	2CV-8285-1	Containment Purge Outlet Isolation (outside)	≤ 5