



NOTES:
 1. PS-300.4 CAN BE USED FOR 2" AND SMALLER PIPING.
 2. 1/2" PIPING SHOWN ON THIS FLOW DIAGRAM REQUIRES INSULATION.

PRESSURE BOUNDARY FREEZE IMPLEMENTED (3-6-78)

DESIGN PARAMETERS			
SIZE	PRESSURE	TEMP.	CLASS
0.2	300.5	395 PSIA	TRFP
			C
			CS

© CLEAR'S FOR PRESSURE BOUNDARY TESTING REL. I. (COZ-3-6-78)

SYSTEM CHANGE ORDER NUMBER CN-1590-1.7-0005

DUKE POWER COMPANY
 CENTRAL POWER STATION UNIT 1

NO.	DESCRIPTION	DATE	BY	APPROVED
1	ISSUED TO START-UP	10/4/78	WJG	
2	ISSUED TO START-UP	10/4/78	WJG	
3	ISSUED TO START-UP	10/4/78	WJG	

FLOW DIRECTION OF CONDENSATE SYSTEM (CCW)

SCALE: DWG NO. CN-1590-1.7

UNCONTROLLED
 COPY

TI APERATURE CARD

10.4.7-8

8406270225

PDR RIDS

8406270225

